

Thread former HSSE TiN type VA Max M ISO 2X (6HX) 0° 371 C

For universal use up to 1300 N/mm²



Application

For producing metric threads in through holes and blind holes on CNC or conventional machines in **stainless steel and non-ferrous metals**.

Advantage

- Innovative mould geometry for stainless steel machining ensures very high dimensional accuracy and process reliability
- High-quality, torsion-resistant HSSE cutting material and surface finish for very high service life requirements

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	25			18	20	40	60	25	40	20	30								

Art. no.	13395 600
Surface	TiN
Lead angle shape	C
Thread type	Metric thread
Thread type x nominal diameter	M10
Pitch	1.5 mm
Cutting material	HSSE
Core hole diameter	9.3 mm
Length	100 mm
Hole type	Clearance/blind hole ≤ 3xD
Shaft diameter	10 mm
Shank square	8 mm
Coolant supply	Internal radial
Tolerance of screw taps	ISO 2X (6HX)
Application type/machine type	CNC, Conventional
Cutting speed (steel 1000) suitability	3
Cutting speed (steel 1300) suitability	3
Overall stainless steel suitability	1
fitness not iron total	2
Cutting speed (cast) suitability	3
fitness Titan/Nickel/Super total	3
Cutting speed (hard 65) suitability	3
DIN	371

EAN-Code

4050293437508