

## Measuring beams

accuracy class I++



### Application:

For simple and accurate checking of straightness and parallelism deviations on travelling axes of e.g. coordinate measuring instruments and machine tools.

### Version:

- Carefully selected and flawless South African hard stone material – Diabas.
- torsion-resistant, distortion-proof, anti-magnetic
- Exactly 2-sided. The two narrow longitudinal surfaces are finely machined to a high-quality finish to be flat and parallel to one another
- accuracy I++: finely ground and lapped
- Calibration certificate included in the scope of delivery. measurement results are based on national standards
- DAkkS calibration certificate available on request



<b>Art. no.</b>	<b>35342 050</b>
<b>Length x width x height</b>	500 x 45 x 90 mm
<b>JFA accuracy I++</b>	0.002 mm
<b>Weight</b>	6 kg