

Electronic crane scales HFM

with high resolution, up to a maximum of 10 tonnes

KERN

Application:

For applications in production, quality control and logistics. Also suitable for continuous use in industrial environments thanks to the sturdy construction and robust design.

Execution:

- Precision: 0.2 % of the respective MAX. value of the selected measuring range
- Data hold function
- Wireless remote control with a range of approx. 20 m
- large LCD display
- powered by internal rechargeable battery, operating time up to 50 h without backlight, charging time approx. 14 h
- HFM with robust die-cast aluminium housing
- HFM includes rotating hook with safety lock

Advantage:

- If the hold function is activated, the value will be „frozen“ (no weight change) when not in use.

Delivery:

Mains charger, radio remote control



Art. no.	44267 220
Brand	KERN
Manufacturer Part Number	HFM 3T0.5
Type description	HFM 3T0.5
Max. weight measuring range	3000 kg
Digit increment, weight	500 g
Housing dimensions (LxWxH)	175 x 270 x 200 mm
Weight	16.5 kg
Gross Weight	18.000 kg
Product Group	447

EAN

4045761111721