




DO NOT SCALE
DIMENSIONS IN mm

METRIC



NOTES:

- ① CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS. FOR CABLE REQUIREMENTS SEE APPLICATION SPECIFICATION 114-19008.
- ② INDICATION OF FIRST CABLE POSITION REFERRING TO CORRESPONDING CONTACT POSITION.
- ③ SOLDER-TINES FOR 0,8^{±0,1} DIA. HOLES.



86,36	78,74	64	6-216093-4
81,28	73,66	60	6-216093-0
68,58	60,96	50	5-216093-0
60,96	53,34	44	4-216093-4
55,88	48,26	40	4-216093-0
48,26	40,64	34	3-216093-4
38,10	30,48	26	2-216093-6
30,48	22,86	20	2-216093-0
25,40	17,78	16	1-216093-6
22,86	15,24	14	1-216093-4
17,78	10,16	10	1-216093-0
12,70	5,08	6	216093-6
DIM. "B" REF.	DIM. "A" REF.	NR. OF POS.	PARTNUMBER

B1	REVISED PER ET00-0023-04	D. C.	C. T.	09FEB2004
B	-	-	-	22MAY1989
LTR.	REVISION RECORD	DR.	CHK.	DATE

CUSTOMER DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

DR.	DATE
W. R. VERBEET.	22-8'88
CHK.	DATE
R. VERSTIJNEN.	23-8'88
APP.	DATE
L. v SOEST.	23-8'88

③ CONTACTS	PHOSPHORBRONZE	3,0-5,1 μm TIN
② HOUSING AND COVER	THERMOPLASTIC POLYESTER	GREY
① HOUSING		
COMPONENT NAME	MATERIAL	PLATING / COLOUR

tyco Electronics

AMP ITALIA S.p.A.
Corso F.lli Cervi, 15
COLLEGNO (TORINO)

RELEASED FOR PUBLICATION 22-8, 1988

© COPYRIGHT 1988 BY AMP-HOLLAND B. V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

WIRE RANGE: SEE NOTE ①
INSUL. RANGE: SEE NOTE ①

NAME: AMP-LATCH
2,54 DIL-PLUG CONNECTOR
WITHOUT RETENTION LEGS.

SIZE: A3
SHEET: 1 OF 1
DWG. No.: C-216093
REV. LTR.: B1