
Belden CDT

TECHNICAL DATA SHEET	code	MRG1791
	version	1
	date	2006-07-12
Coax RG179 PE PVC	page	1/2

APPLICATION

Coaxial communication cable based on MIL-C-17.

CONSTRUCTION



1 Inner conductor Silver plated, copper cladded steel

2 Dielectric Solid PE3 Braid Tinned copper

4 Sheath PVC according the European Standard HD 624.

REQUIREMENTS AND TEST METHODS

Test methods in accordance with European standard EN 50289.

Mechanical characteristics

1. Inner conductor. 7 x 0.1 mm

Diameter: $0.3 \text{ mm} \pm 0.02 \text{ mm}$

2. Dielectric:

Diameter: $1.5 \text{ mm} \pm 0.15 \text{ mm}$

3. Outer conductor:

Diameter screen: $1.97 \text{ mm} \pm 0.15 \text{ mm}$

Coverage braid: $85 \% \pm 4 \%$

4. Sheath:

Diameter: $2.8 \text{ mm} \pm 0.1 \text{ mm}$

5. Cable:

Storage/operating temperature: -25°C to +70°C

Minimum installation temperature: -5 °C Total weight: 11.5 g/m



TECHNICAL DATA SHEET	code	MRG1791
	version	1
	date	2006-07-12
Coax RG179 PE PVC	page	2/2

Electrical characteristics

Mean characteristic impedance: $75 \pm 3 \Omega$ Regularity of impedance: > 40 dB

DC resistance inner conductor: \leq 802 Ohm/km Capacitance: \leq 7 pF/m \pm 3 pF/m

Nominal velocity of propagation: 66 %

Voltage Rating

DC: 2.0 kVdc RMS 1.0 kVrms

Nominal Attenuation:

10 MHz: 8 dB/100m 100 MHz: 27 dB/100m 1000 MHz: 88 dB/100m



Belden CDT believes this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.