

SCAC clamp holder for lathes, positive

For facing and longitudinal turning using CC indexable inserts

ATORN[®]

Application

For facing and longitudinal turning using CC 80° indexable inserts



Version

- Precision-made steel carrier, bronzed, hardened, type C, pitch angle 90°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for facing and longitudinal turning
- Positive body geometry ensures low cutting forces
- Excellent surface quality for medium infeed and finishing

Art. no.	17829 006
ISO name	SCAC R/L 1212 X06-A
Shaft height	12 mm
Shank width	12 mm
Length	130 mm
Programming size	12 mm
Suitable for indexable inserts	CC.. 0602..
Tool design	Left
DIN	4983

EAN-Code

4050293692723