












## Heatsinks for transistors in plastic case

		<p><b>FK 219 CB 1 ...</b></p> 	<p><b>FK 219 CB 2 ...</b></p> 
<p><b>art. no.</b></p>	<p>± [mm]</p>	<p><math>R_{th}</math> [K/W]</p>	<p>☒</p>
<p><b>FK 219 CB 1 ...</b></p>	<p>12.6</p>	<p>14</p>	<p>CB 1 (TO 220)</p>
<p><b>FK 219 CB 2 ...</b></p>	<p>12.6</p>	<p>14</p>	<p>CB 2 (TO 220)</p>
			
<p><b>art. no.</b></p>	<p>± [mm]</p>	<p><math>R_{th}</math> [K/W]</p>	<p>☒</p>
<p><b>FK 219 CB 3 ...</b></p>	<p>12.6</p>	<p>14</p>	<p>CB 3 (TO 220)</p>
		<p><b>FK 236 CB ...</b></p> 	<p><b>FK 236 220 ...</b></p> 
<p><b>art. no.</b></p>	<p>± [mm]</p>	<p><math>R_{th}</math> [K/W]</p>	<p>☒</p>
<p><b>FK 236 220 ...</b></p>	<p>5</p>	<p>18</p>	<p>TO 220</p>
<p><b>FK 236 CB ...</b></p>	<p>5</p>	<p>18</p>	<p>CB</p>
<p><b>please indicate:</b>      ... surface          SA = black anodised          MI = solderable surface</p>			
<p><b>material:</b></p>	<p>aluminium</p>		