# Ruggedized Electrical Double Layer Energy Storage Capacitors




Image is not to scale

QUICK REFERENCE DATA						
DESCRIPTION	VALUE					
Nominal case sizes (Ø D x L in mm)	10 x 20; 10 x 25; 10 x 30; 12.5 x 20; 12.5 x 25; 12.5 x 30; 12.5 x 40; 16 x 20; 18 x 20; 16 x 25, 18 x 25; 16 x 31; 18 x 31, 18 x 35, 18 x 40					
Rated capacitance range, C <sub>R</sub>	5 F to 60 F					
Rated voltage, U <sub>R</sub> (65 °C / 85 °C)	2.7 V / 2.3 V					
Category temperature range	-40 °C to +85 °C					
Endurance test at 85 °C	Up to 1000 h					
Useful life at 85 °C	Up to 2000 h					
Useful life at 20 °C	> 10 years					
Shelf life at 20 °C	2 years					
Cycle life	> 500 000 cycles					

## **FEATURES**

 Polarized energy storage capacitor with high capacity and energy density



RoHS

- Rated voltage: 2.7 V
- Available in through-hole (radial) version
- Useful life: up to 2000 h at 85 °C
- Ruggedized for high humidity operation
- · Rapid charge and discharge
- · Maintenance-free, no service necessary
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see <a href="https://www.vishav.com/doc?99912"><u>www.vishav.com/doc?99912</u></a>

## **APPLICATIONS**

- Power backup
- Burst power support
- · Storage device for energy harvesting
- Micro UPS power source
- Energy recovery

## **MARKING**

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in F)
- Rated voltage (in V)
- Date code, in accordance with IEC 60062
- · Code indicating factory of origin
- Logo of manufacturer
- · Negative terminal identification
- Series number (225)

## **PACKAGING**

Supplied loose in box, taped ammo, or in ESD trays.

SELECTION CHART FOR C <sub>R</sub> , U <sub>R</sub> , AND RELEVAN	T NOMINAL CASE SIZES (Ø D x L in mm)
C <sub>R</sub> (F)	U <sub>R</sub> (V) = 2.7 V
5	10 x 20
7	10 x 25
8	12.5 x 20
10	10 x 30
12	12.5 x 25
15	12.5 x 30
20	16 x 20
22	12.5 x 40
25	16 x 25; 18 x 20
30	18 x 25
35	16 x 31
40	18 x 31 <sup>(1)</sup>
50	18 x 35
60	18 x 40

### Note

(1) Preferred case size



## **DIMENSIONS** in millimeters **AND AVAILABLE FORMS**




Fig. 1 - Form CA / TRAY: Long leads




Fig. 2 - Form TFA: Taped in box (ammopack)

## Table 1

<b>DIMENSIONS</b> in 1	DIMENSIONS in millimeters, MASS, AND PACKAGING QUANTITIES								
NOMINAL CASE SIZE	NAL CASE SIZE CASE Ø d Ø Dmay Lmay F	MASS	PACKAGING QUANTITIES						
ØDxL	CODE	øα	Ø D <sub>max</sub> .	∟ <sub>max</sub> .		(g)	FORM CA	FORM TFA	FORM TRAY
10 x 20	16	0.6	10.5	22	$5.0 \pm 0.5$	≈ 2.2	500	800	-
10 x 25	16L	0.6	10.5	27	$5.0 \pm 0.5$	≈ 3.0	500	800	-
10 x 30	16LL	0.8	10.5	32	$5.0 \pm 0.5$	≈ 3.5	500	800	-
12.5 x 20	17	0.6	13.0	22	$5.0 \pm 0.5$	≈ 4.0	500	500	-
12.5 x 25	18	0.6	13.0	27	$5.0 \pm 0.5$	≈ 5.0	250	500	-
12.5 x 30	18L	0.8	13.0	33.5	$5.0 \pm 0.5$	≈ 5.5	250	500	-
12.5 x 40	18LL	0.8	13.0	42.5	$5.0 \pm 0.5$	≈ 7.0	250	-	-
16 x 20	19a	0.8	16.5	22	$7.5 \pm 0.5$	≈ 6.0	250	250	200
16 x 25	19	0.8	16.5	27	$7.5 \pm 0.5$	≈ 8.0	250	250	200
18 x 20	1820	0.8	18.5	22	$7.5 \pm 0.5$	≈ 7.0	100	250	200
18 x 25	1825	0.8	18.5	27	$7.5 \pm 0.5$	≈ 10.0	100	250	200
16 x 31	20	0.8	16.5	33.5	$7.5 \pm 0.5$	≈ 9.0	100	250	200
18 x 31	1831	0.8	18.5	33.5	$7.5 \pm 0.5$	≈ 12.5	100	250	200
18 x 35	22	0.8	18.5	37.5	$7.5 \pm 0.5$	≈ 14.5	100	250	200
18 x 40	1840	0.8	18.5	42.5	$7.5 \pm 0.5$	≈ 16.5	100	-	150

ELECTRICAL DATA					
SYMBOL	DESCRIPTION				
C <sub>R</sub>	Rated capacitance, tolerance -20 % / +50 %				
I <sub>P</sub>	Max. peak current				
IL	Max. leakage current after 0.5 h / 72 h at U <sub>R</sub>				

## Note

• Unless otherwise specified, all electrical values in Table 2 apply at  $T_{amb}$  = 20 °C, P = 86 kPa to 106 kPa and RH = 45 % to 75 %

## **ORDERING EXAMPLE**

Capacitor series 225 EDLC-R

40 F / 2.7 V

Nominal case size: Ø 18 mm x 31 mm; Form CA

Ordering code: MAL222551001E3

Table 2

EL	ELECTRICAL DATA AND ORDERING INFORMATION																
U <sub>R</sub> (V)	U <sub>СТ</sub> <sup>(1)</sup> (V)	U <sub>S</sub> (V) (< 1 s)	C <sub>R</sub> (2) 100 Hz	NOMINAL CASE SIZE Ø D x L (mm)	MAX. ESR <sub>DC</sub> <sup>(2)</sup> INITIAL (mΩ)	SR <sub>DC</sub> (2) INITIAL, CURRENT AFTER (Wh)		RGY 「U <sub>R</sub>	ENERGY		ORDERING CODE MAL2225						
65 °C	85 °C					(11122)	65 °C	85 °C	0.5 h	72 h	65 °C	85 °C	65 °C	85 °C	FORM CA	FORM TFA	FORM TRAY
2.7	2.3	2.85	5	10 x 20	35	28	12	10	2	25	0.005	0.004	2.3	1.8	51011E3	31011E3	-
2.7	2.3	2.85	7	10 x 25	31	24	12	10	3	35	0.007	0.005	2.3	1.7	51012E3	31012E3	-
2.7	2.3	2.85	8	12.5 x 20	28	21	15	12	4	40	0.008	0.006	2.0	1.5	51014E3	31014E3	-
2.7	2.3	2.85	10	10 x 30	27	20	15	12	4	45	0.009	0.007	2.6	2.0	51013E3	31013E3	-
2.7	2.3	2.85	12	12.5 x 25	26	19	17	14	5	55	0.011	0.008	2.2	1.6	51015E3	31015E3	-
2.7	2.3	2.85	15	12.5 x 30	23	16	20	17	6	70	0.015	0.011	2.7	2.0	51016E3	31016E3	-
2.7	2.3	2.85	20	16 x 20	24	18	25	20	8	75	0.020	0.015	3.4	2.3	51003E3	31003E3	91003E3
2.7	2.3	2.85	22	12.5 x 40	18	11	25	20	9	75	0.021	0.015	3.0	2.1	51017E3	-	-
2.7	2.3	2.85	25	16 x 25	22	16	25	20	8	75	0.025	0.018	3.2	2.3	51006E3	31006E3	91006E3
2.7	2.3	2.85	25	18 x 20	20	15	25	20	8	75	0.025	0.018	3.6	2.6	51004E3	31004E3	91004E3
2.7	2.3	2.85	30	18 x 25	19	13	30	25	12	140	0.030	0.022	3.0	2.2	51007E3	31007E3	91007E3
2.7	2.3	2.85	35	16 x 31	20	14	30	25	15	200	0.035	0.026	3.9	2.9	51002E3	31002E3	91002E3
2.7	2.3	2.85	40	18 x 31	18	12	35	30	20	200	0.041	0.029	3.3	2.3	51001E3	31001E3	91001E3
2.7	2.3	2.85	50	18 x 35	15	10	35	30	25	250	0.051	0.037	3.5	2.6	51008E3	31008E3	91008E3
2.7	2.3	2.85	60	18 x 40	13	9	35	30	30	300	0.061	0.044	3.7	2.7	51009E3	-	91009E3

Table 3

NOMINAL CASE SIZE Ø D x L	CASE CODE	ENDURANCE AT 85 °C (h)	USEFUL LIFE AT 85 °C (h)	
10 x 20	16	750	1000	
10 x 25	16L	750	1000	
10 x 30	16LL	750	1000	
12.5 x 20	17	1000	1500	
12.5 x 25	18	1000	1500	
12.5 x 30	18L	1000	1500	
12.5 x 40	18LL	1000	1500	
16 x 20	19a	1000	2000	
16 x 25	19	1000	2000	
18 x 20	1820	1000	2000	
18 x 25	1825	1000	2000	
16 x 31	20	1000	2000	
18 x 31	1831	1000	2000	
18 x 35	22	1000	2000	
18 x 40	1840	1000	2000	

<sup>(1)</sup>  $U_{CT}$  = rated voltage at upper category temperature (2) Rated capacitance  $C_R$  and  $ESR_{DC}$ 



## Table 4

RUGGEDIZED FOR HIGH HUMIDITY - BIASED HUMIDITY TESTING							
PARAMETER	PROCEDURE (AT RATED VOLTAGE)	REQUIREMENTS					
Humidity (relative)	85 %	After loading the capacitor for the specified time at maximum category temperature $T_{max}$ . = 85 °C and 85 % relative humidity, and derated permissible maximum operating voltage U = 2.3 V, following parameters are valid within a timeframe of 1000 h:					
Temperature	85 °C	No visible damage No leakage of electrolyte △C/C: within ± 30 % of minimum initial specified value ESR: less than 3 x initial specified value Leakage: less than initial specified value					

NAME OF TEST	PROCEDURE (quick reference)						
Capacitance C <sub>R</sub> and ESR <sub>DC</sub>	Measured by DC discharging method as described in "Measuring of Characteristics". (2)						
Maximum peak current	Non-repetitive current for maximum 1 s at specified operating temperature.  Maximum operating voltage (refer to derating table) must not be exceeded.  Usually to be tested with constant current discharge from U <sub>R</sub> to 0.5 x U <sub>R</sub> .  Maximum current should not be used in normal operation and is only provided as reference value.						
Leakage current I <sub>L</sub>	Measured at U <sub>R</sub> . Capacitor is charged to the rated voltage at 20 °C. Leakage current is the current at spectime that is required to keep the capacitor charged at the rated voltage.						
	After loading the capermissible maxim 1000 h:	apacitor for specified time at maximum category temperature $T_{max.}=85^{\circ}C$ and derated num operating voltage U = 2.3 V, following parameters are valid within a timeframe of					
Endurance	Capacitance	Within ± 30 % of minimum initial specified value					
	ESR	Less than 3 x initial specified value					
	Leakage	Within specified value					
	After loading the capermissible maxim 2000 h:	apacitor for specified time at maximum category temperature $T_{max.} = 85^{\circ}\text{C}$ and derated num operating voltage U = 2.3 V, following parameters are valid within a timeframe of					
Useful life	Capacitance	Within ± 50 % of minimum initial specified value					
	ESR	Less than 4 x initial specified value					
	Leakage	Within specified value					
		apacitor of specified time at maximum category temperature T <sub>max.</sub> = 85 °C and without 40 % RH, following parameters are valid within a timeframe of 1000 h:					
Storage at upper	Capacitance	Within ± 30 % of minimum initial specified value					
category temperature	ESR	Less than 3 x initial specified value					
	Leakage	Within specified value					
Shelf life	Stored uncharged at 20 °C. Parameter within initial specification						
Ovela life	charge and discha	tween rated voltage and half of rated voltage $U_R$ with constant current and 1 s rest between rge: $>$ 500 000 cycles					
Cycle life	Capacitance	Within ± 30 % of minimum initial specified value					
	ESR	Less than 3 x initial specified value					
Stared anarous F	$E[Wh] = \frac{1}{2} \times C \times ($	$(U_{R})^{2} \times 1/3600$					
Stored energy E, specific energy Ed and Ev	Ed [Wh/kg] = $\frac{1}{2}$ x C x (U <sub>R</sub> ) <sup>2</sup> x 1/3600 x 1/mass						
speeme energy La ana Lv	Ev [Wh/L] = $\frac{1}{2}$ x C x (U <sub>R</sub> ) <sup>2</sup> x 1/3600 x 1/volume						
Soldering	Hand or wave soldering allowed. For details refer to soldering requirements for radial aluminum electrolytic capacitors in supplementary document.						
Cleaning	For details refer to	board cleaning apply non-aggressive cleaning agents only. cleaning requirements for aluminum electrolytic capacitors in supplementary document.					
Environmental conditions	Do not expose capacitors to  • temperatures outside specified range  • high humidity atmospheres; except series 225 which is ruggedized for high humidity 85 °C and 85 % RH  • corrosive atmospheres, e.g. halogenides, sulphurous or nitrous gases, acid or alkaline solutions, etc.  • environments containing oil and grease						

### Notes

- General remark: temperatures to be measured at capacitor case Conditions: electrical measurements at 20 °C, unless otherwise specified
- $^{(2)}$  Rated capacitance  $C_R$  and  $ESR_{DC}$

Document Number: 28449

## **MEASURING OF CHARACTERISTICS**

## **CAPACITANCE (C)**

Capacitance shall be measured by constant current discharge method.

- Constant current charge with 10 mA/F to UR
- Constant voltage charge at UR
- Constant current discharge with 10 mA/F to 0.1 V




Fig. 3 - Voltage Diagram for Capacitance Measurement

Capacitance value C<sub>R</sub> is given by discharge current I<sub>D</sub>, time t and rated voltage U<sub>B</sub>, according to the following equation:

$$C_{R}[F] = \frac{I_{D}[A] \times (t_{2}[s] - t_{1}[s])}{U_{1}[V] - U_{2}[V]}$$

 $C_R$ Rated capacitance, in F  $U_{R}$ Rated voltage, in V

U<sub>1</sub> Starting voltage, 0.8 x U<sub>R</sub> in V U2 Ending voltage, 0.4 x U<sub>R</sub> in V

Voltage drop at internal resistance, in V  $\Delta U_3$ 

Time from start of discharge until voltage U<sub>1</sub> is t<sub>1</sub>

reached, in s

Time from start of discharge until voltage U2 is  $t_2$ 

reached, in s

Revision: 19-Nov-2019

 $I_D$ Absolute value of discharge current, in A

## EQUIVALENT SERIES RESISTANCE (ESRDC)

- Constant current charge to UR

- Constant voltage charge at UR

- Constant current discharge to 0.1 V

$$\mathsf{ESR}_{\mathsf{DC}}\left[\Omega\right] = \frac{\Delta \mathsf{U}_3\left[\mathsf{V}\right]}{\mathsf{I}_{\mathsf{D}}\left[\mathsf{A}\right]}$$

ESR<sub>DC</sub> Equivalent series resistance, in  $\Omega$  $\Delta U_R$ Voltage drop at internal resistance, in V Absolute value of discharge current, in A  $I_D$ 

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.