

Product type designation

Product description

Cable RS422, M12 / M12

Highly flexible communication line (6-core)
SIMATIC RF, MV CONNECT. CABLE, PREASSEMBLED,
BETWEEN ASM 456, RF160C, RF170C, RF18XC AND READER,
OR EXTENSION CABLE FOR ASM 456, RF160C, RF170C,
RF18XC MIT RF, MV, MOBY PUR, CMG, TRAILING, LENGTH 20 M



Suitability for use	Plug-in or extension cable for connecting a reader to a communication module
Cable designation	L-YC11Y 6x1x0.25 6x24AWG CMG
Cable length	20 m

Electrical data

Number of electrical connections	2
Type of electrical connection	M12 (male, 8 pin, straight) / M12 (female, 8 pin, straight)
Loop resistance per length / maximum	160 mΩ/m
Insulation resistance coefficient	20 GΩ·m
Operating voltage	
• maximum	300 V

Mechanical data

Number of electrical cores	6
Design of the shield	Braided shield made of tin-plated copper wires
Outer diameter	
• of cable sheath	5.4 mm
Symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
Material	
• of the wire insulation	PVC
• of cable sheath	PUR
Color	
• of the insulation of data wires	DIN 47100

• of cable sheath	Black
Bending radius	
• with single bend / minimum permissible	21.6 mm
• with multiple bends / minimum permissible	43 mm
• with continuous bending	75 mm
Number of bending cycles	3000000
Tensile load / maximum	200 N
Weight per length	45 kg/km

Permitted ambient conditions

Ambient temperature	
• during operation	-30 ... +80 °C
• during storage	-30 ... +80 °C
• during transport	-30 ... +80 °C
• during installation	-30 ... +80 °C
Burning behavior	flame resistant according to IEC 60332-1-2
Chemical resistance	
• to mineral oil	resistant
• to grease	Resistant
Radiological resistance / to UV radiation	resistant

Product properties, functions, components / general

Product property	
• halogen-free	No
• silicon-free	Yes

Further Information / Internet Links

Internet-Link	
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/automation/net/catalog
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified: 12.03.2015