

## BLOC BRIDE clamping unit



### Application:

For use on machine tools for drilling, milling, thread cutting and countersinking.

### Execution:

- Stepless and simple adjustment of clamping height
- Clamping force infinitely variable up to 16 kN depending on stability and machining of workpiece (distortion-free clamping).
- Simultaneous clamping of the workpiece and fixing of the clamping unit to any point on the table by turning the spanner.
- Adjusts to shape of workpiece surface using interchangeable function shoes.
- Base elements without spanner

### Advantage:

- Exchangeable T-shaped sliding blocks with compression spring for each groove width for fast assembly of the clamping unit.
- Interchangeable lever arms, short and long version, for good access to workpiece.



|                                  |                  |
|----------------------------------|------------------|
| <b>Art. no.</b>                  | <b>26245 020</b> |
| <b>Brand</b>                     | KOPAL            |
| <b>Manufacturer Part Number</b>  | 05 031           |
| <b>Max. left arm depth</b>       | 61 mm            |
| <b>Max. right arm depth</b>      | 105 mm           |
| <b>Min./max. clamping height</b> | 8-102 mm         |
| <b>Gross Weight</b>              | 1.510 kg         |
| <b>Product Group</b>             | 265              |