



Miniature circuit breaker (MCB), 50 A, 3p, characteristic: D, 6 kA

Part no. FAZ6-D50/3
Catalog No. 168086
Alternate Catalog No. FAZ6-D50/3

Similar to illustration

Delivery program

| | | |
|-----------------|--|--------|
| Number of poles | | 3 pole |
|-----------------|--|--------|

Design verification as per IEC/EN 61439

| Technical data for design verification | | | |
|-----------------------------------------------------------------------------|------------|----|------|
| Rated operational current for specified heat dissipation | I_n | A | 50 |
| Equipment heat dissipation, current-dependent | P_{vid} | W | 14.6 |
| Static heat dissipation, non-current-dependent | P_{vs} | W | 0 |
| Heat dissipation capacity | P_{diss} | W | 0 |
| Operating ambient temperature min. | | °C | -40 |
| Operating ambient temperature max. | | °C | 70 |
| linear, per +1 °C, results in a 0.5% reduction of current carrying capacity | | | |

Technical data ETIM 7.0

| Circuit breakers and fuses (EG000020) / Miniature circuit breaker (MCB) (EC000042) | | | |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------|----------|
| Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Miniature circuit breaker (MCB) (ecl@ss10.0.1-27-14-19-01 [AAB905014]) | | | |
| Release characteristic | | | D |
| Number of poles (total) | | | 3 |
| Number of protected poles | | | 3 |
| Rated current | | A | 50 |
| Rated voltage | | V | 230 |
| Rated insulation voltage U_i | | V | 440 |
| Rated impulse withstand voltage U_{imp} | | kV | 4 |
| Rated short-circuit breaking capacity I_{cn} EN 60898 at 230 V | | kA | 6 |
| Rated short-circuit breaking capacity I_{cn} EN 60898 at 400 V | | kA | 6 |
| Rated short-circuit breaking capacity I_{cu} IEC 60947-2 at 230 V | | kA | 6 |
| Rated short-circuit breaking capacity I_{cu} IEC 60947-2 at 400 V | | kA | 6 |
| Voltage type | | | AC |
| Frequency | | Hz | 50 - 60 |
| Current limiting class | | | 3 |
| Suitable for flush-mounted installation | | | No |
| Concurrently switching N-neutral | | | No |
| Over voltage category | | | 3 |
| Pollution degree | | | 2 |
| Additional equipment possible | | | Yes |
| Width in number of modular spacings | | | 3 |
| Built-in depth | | mm | 70.5 |
| Degree of protection (IP) | | | IP20 |
| Ambient temperature during operating | | °C | -25 - 75 |
| Connectable conductor cross section multi-wired | | mm ² | 1 - 25 |
| Connectable conductor cross section solid-core | | mm ² | 1 - 25 |

Additional product information (links)

| | |
|----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Temperature dependency, derating | https://www.eaton.com/content/dam/eaton/technicaldocumentation/technical-data-tables/Derating table FAZ6.pdf |
|----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

