



TEGERA® 874

Synthetic glove, nitrile foam, 3/4 dipped, Lycra®, nylon, foam grip pattern, Cat. II, black, grey, oil and grease resistant palm, for precision work

PROPERTIES

Good fingertip sensitivity, durable, good fit, comfortable, light

SPECIFICATION

TYPE OF GLOVE Work gloves - General handling

CATEGORY Cat. II

SIZE RANGE (EU) 7, 8, 9, 10, 11

LINER MATERIAL Lycra®, nylon

DIPPING 3/4 dipped

DIPPING MATERIAL Nitrile foam

DEXTERITY 5

GRIP PATTERN Foam grip pattern

CUFF STYLE Knitwrist cuff

LENGTH RANGE 220 -260mm

COLOUR Black, grey

PAIRS PER PACKAGE/CARTON 12/120

DISPLAY Bulk pack

MATERIAL SPECIFICATION Nitrile 30%, nylon 60%, elastane 10%

1(3)

TEGERA® 874

FEATURES

Water and oil repellent palm and knuckle

PRIMARY PROTECTION

Prevents risk of, abraision injuries, scratches, lacerations, contact with dirt

PRIMARY ENVIRONMENTS OF USE

Oil and greasy environments, dirty environments

PRIMARY AREAS OF USE

Fine assembly, assembly, inspection work, machine operating, building and construction, carpentry, painting, installation work, electrical installation, construction, soil preparation, warehouse work, airport work

PRIMARY INDUSTRIES OF USE



Machinery and equipment, MRO, automotive

TYPE OF WORK

Light weight



 Cat. II

 EN 388:2003
4131 

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2017-11-17

2(3)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

TEGERA® 874

EC TYPE EXAMINATION

Notified Body: 0075 CTC, 4 rue Hermann Frenkel, 69367 Lyon Cedex 07 France

COMPLIANCE DESCRIPTION

EN 420:2003 + A1:2009 Protective gloves - general requirements and test methods

EN 388:2003 Protective gloves against mechanical risks


Property	Level Achieved	(Maximum Performance)
A) Resistance to abrasion (No. of revolutions)	4	(4)
B) Resistance to cutting (Index)	1	(5)
C) Tear resistance (Newton)	3	(4)
D) Puncturing resistance (Newton)	1	(4)

EN 388 - Testing (specifies the requirements that apply for each safety level).

Level of protection/Performance level	1	2	3	4	5
A) Resistance to abrasion (No. of revolutions)	100	500	2 000	8 000	
B) Resistance to cutting (Index)	1,2	2,5	5,0	10,0	20,0
C) Tear resistance (Newton)	10	25	50	75	
D) Puncturing resistance (Newton)	20	60	100	150	



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.