



Figure similar

TRANSFORMER SITAS; PHASES:1;
 PN/PN(S6)(KVA):0,5 /2; UPRI(V):400-230+/-15;
 USEC(V):2X115; ISEC(A):2X2,17; F(HZ):50...60;
 VECTOR GR./SHIELD WNG.:II0 /0; TA/ISOKL:40 /B;
 IP00; TYPE OF TERMINALS:SCREW/TAB
 CONNECTION; INSTALLATION:SCREW; EN 61558-2-
 1, -2-2, -2-4 >UL/CSA-RECOGNIZED< >CONTROL
 CIRCUIT TRANSFORMER< >ISOLATION
 TRANSFORMER<

General technical data:

Product designation		transformer SITAS
product brand name		SIDAC
Operating apparent output Rated value	V·A	500
Efficiency		0.91
Connection method for transformers		II0
Certificate of suitability		CE / cRUus
Product function		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
Number of shielding windings		0
Short-term vector power	V·A	2 000
Relative short-circuit voltage	%	3.8

Inputs:

Phase number of the inputs		1
Input voltage		
• _1 Rated value	V	415
• _2 Rated value	V	400
• _3 Rated value	V	385
• _4 Rated value	V	245
• _5 Rated value	V	230
• _6 Rated value	V	215
Electrical input frequency		

• minimum	Hz	50
• maximum	Hz	60

Outputs:

Phase number of the outputs		1
Output voltage		
• _1 Rated value	V	230
• _2 Rated value	V	115
Electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50

Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature Rated value	°C	40
Protection class IP		IP00

Mechanical data:

Type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals
Mounting type		screws
Construction form of the iron core		EI 120/72
Width	m	0.122
Height	m	0.121
Depth	m	0.134

Certificates/ approvals:

General Product Approval

Shipping Approval

other



[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM48428JD400FA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM48428JD400FA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM48428JD400FA0&lang=en

last modified:

15.01.2015