

# PIC18F97J60 Family Data Sheet

64/80/100-Pin High-Performance, 1-Mbit Flash Microcontrollers with Ethernet

**Preliminary** 

© 2007 Microchip Technology Inc.

#### Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not
  mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION. INCLUDING BUT NOT LIMITED TO ITS CONDITION. QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

### QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV ISO/TS 16949:2002

#### Trademarks

The Microchip name and logo, the Microchip logo, Accuron, dsPIC, KEELOQ, KEELOQ logo, microID, MPLAB, PIC, PICmicro, PICSTART, PRO MATE, rfPIC and SmartShunt are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AmpLab, FilterLab, Linear Active Thermistor, Migratable Memory, MXDEV, MXLAB, SEEVAL, SmartSensor and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Application Maestro, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, ECAN, ECONOMONITOR, FanSense, FlexROM, fuzzyLAB, In-Circuit Serial Programming, ICSP, ICEPIC, Mindi, MiWi, MPASM, MPLAB Certified logo, MPLIB, MPLINK, PICkit, PICDEM, PICDEM.net, PICLAB, PICtail, PowerCal, PowerInfo, PowerMate, PowerTool, REAL ICE, rfLAB, Select Mode, Smart Serial, SmartTel, Total Endurance, UNI/O, WiperLock and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

All other trademarks mentioned herein are property of their respective companies.

© 2007, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

Printed on recycled paper.

Microchip received ISO/TS-16949:2002 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.



### 64/80/100-Pin High-Performance, 1-Mbit Flash Microcontrollers with Ethernet

#### **Ethernet Features:**

- IEEE 802.3™ Compatible Ethernet Controller
- Integrated MAC and 10Base-T PHY
- 8-Kbyte Transmit/Receive Packet Buffer SRAM
- Supports One 10Base-T Port
- Programmable Automatic Retransmit on Collision
- Programmable Padding and CRC Generation
- Programmable Automatic Rejection of Erroneous Packets
- · Activity Outputs for 2 LED Indicators
- Buffer:
  - Configurable transmit/receive buffer size
  - Hardware-managed circular receive FIFO
  - Byte-wide random and sequential access
  - Internal DMA for fast memory copying
  - Hardware assisted checksum calculation for various protocols
- MAC:
  - Support for Unicast, Multicast and Broadcast packets
  - Programmable Pattern Match of up to 64 bytes within packet at user-defined offset
  - Programmable wake-up on multiple packet formats
- PHY:
  - Wave shaping output filter

#### Flexible Oscillator Structure:

- Selectable System Clock derived from Single 25 MHz External Source:
  - 2.778 to 41.667 MHz
- Internal 31 kHz Oscillator
- Secondary Oscillator using Timer1 @ 32 kHz
- Fail-Safe Clock Monitor:
- Allows for safe shutdown if oscillator stops
- Two-Speed Oscillator Start-up

### External Memory Bus (100-pin devices only):

- · Address Capability of up to 2 Mbytes
- · 8-Bit or 16-Bit Interface
- 12-Bit, 16-Bit and 20-Bit Addressing modes

### **Peripheral Highlights:**


- High-Current Sink/Source: 25 mA/25 mA on PORTB and PORTC
- Five Timer modules (Timer0 to Timer4)
- · Four External Interrupt pins
- Two Capture/Compare/PWM (CCP) modules
- Three Enhanced Capture/Compare/PWM (ECCP) modules:
  - One, two or four PWM outputs
  - Selectable polarity
  - Programmable dead time
  - Auto-shutdown and auto-restart
- Up to Two Master Synchronous Serial Port (MSSP) modules supporting SPI (all 4 modes) and I<sup>2</sup>C<sup>™</sup> Master and Slave modes
- Up to Two Enhanced USART modules:
  - Supports RS-485, RS-232 and LIN 1.2
  - Auto-wake-up on Start bit
  - Auto-Baud Detect (ABD)
- 10-Bit, Up to 16-Channel Analog-to-Digital Converter module (A/D):
  - Auto-acquisition capability
  - Conversion available during Sleep
- · Dual Analog Comparators with Input Multiplexing
- Parallel Slave Port (PSP) module (100-pin devices only)

#### Special Microcontroller Features:


- 5.5V Tolerant Inputs (digital-only pins)
- Low-Power, High-Speed CMOS Flash Technology:
   Self-reprogrammable under software control
- C compiler Optimized Architecture for Reentrant Code
- Power Management Features:
  - Run: CPU on, peripherals on
  - Idle: CPU off, peripherals on
  - Sleep: CPU off, peripherals off
- Priority Levels for Interrupts
- 8 x 8 Single-Cycle Hardware Multiplier
- Extended Watchdog Timer (WDT):
  - Programmable period from 4 ms to 134s
- Single-Supply 3.3V In-Circuit Serial Programming™ (ICSP™) via Two Pins
- In-Circuit Debug (ICD) with 3 Breakpoints via Two Pins
- Operating Voltage Range of 2.35V to 3.6V (3.1V to 3.6V using Ethernet module)
- On-Chip 2.5V Regulator

	Program Da Memory Men	sh SRAM	SRAM	SRAM	SRAM	SRAM	SRAM	SRAM	SRAM	SRAM	SRAM	Ethernet					MSS	SP	RT	tors			al Bus
Device		Data Memory (bytes)	TX/RX Buffer (bytes)	I/O	10-Bit A/D (ch)	CCP/ ECCP		SPI	Master I <sup>2</sup> C™	EUSAF	Comparators	Timers 8/16-Bit	PSP	External Memory B									
PIC18F66J60	64K	3808	8192	39	11	2/3	1	Y	Y	1	2	2/3	Ν	Ν									
PIC18F66J65	96K	3808	8192	39	11	2/3	1	Y	Y	1	2	2/3	Ν	Ν									
PIC18F67J60	128K	3808	8192	39	11	2/3	1	Y	Y	1	2	2/3	Ν	Ν									
PIC18F86J60	64K	3808	8192	55	15	2/3	1	Υ	Y	2	2	2/3	Ν	Ν									
PIC18F86J65	96K	3808	8192	55	15	2/3	1	Υ	Y	2	2	2/3	Ν	Ν									
PIC18F87J60	128K	3808	8192	55	15	2/3	1	Y	Y	2	2	2/3	Ν	Ν									
PIC18F96J60	64K	3808	8192	70	16	2/3	2	Y	Y	2	2	2/3	Y	Y									
PIC18F96J65	96K	3808	8192	70	16	2/3	2	Υ	Y	2	2	2/3	Y	Y									
PIC18F97J60	128K	3808	8192	70	16	2/3	2	Y	Y	2	2	2/3	Y	Y									


### Pin Diagrams



#### **Pin Diagrams (Continued)**



#### **Pin Diagrams (Continued)**



### **Table of Contents**

1.0	Device Overview	7
2.0	Oscillator Configurations	39
3.0	Power-Managed Modes	45
4.0	Reset	53
5.0	Memory Organization	67
6.0	Flash Program Memory	
7.0	External Memory Bus	105
8.0	8 x 8 Hardware Multiplier	117
9.0	Interrupts	119
10.0	I/O Ports	135
11.0	Timer0 Module	163
12.0	Timer1 Module	167
13.0	Timer2 Module	173
14.0	Timer3 Module	175
15.0	Timer4 Module	179
16.0	Capture/Compare/PWM (CCP) Modules	181
17.0		189
18.0		
19.0	Master Synchronous Serial Port (MSSP) Module	255
20.0	Enhanced Universal Synchronous Asynchronous Receiver Transmitter (EUSART)	301
21.0	10-Bit Analog-to-Digital Converter (A/D) Module	325
22.0	Comparator Module	335
23.0	Comparator Voltage Reference Module	341
24.0	Special Features of the CPU	345
25.0	Instruction Set Summary	359
26.0	Development Support	409
27.0	Electrical Characteristics	
28.0	Packaging Information	449
29.0	DC and AC Characteristics Graphs and Tables	455
Appe	endix A: Revision History	457
Appe	andix B: Device Differences	457
Index	<	459
The N	Microchip Web Site	471
Custo	omer Change Notification Service	471
Custo	omer Support	471
Read	ler Response	472
Produ	uct Identification System	473

### TO OUR VALUED CUSTOMERS

It is our intention to provide our valued customers with the best documentation possible to ensure successful use of your Microchip products. To this end, we will continue to improve our publications to better suit your needs. Our publications will be refined and enhanced as new volumes and updates are introduced.

If you have any questions or comments regarding this publication, please contact the Marketing Communications Department via E-mail at **docerrors@microchip.com** or fax the **Reader Response Form** in the back of this data sheet to (480) 792-4150. We welcome your feedback.

#### Most Current Data Sheet

To obtain the most up-to-date version of this data sheet, please register at our Worldwide Web site at:

http://www.microchip.com

You can determine the version of a data sheet by examining its literature number found on the bottom outside corner of any page. The last character of the literature number is the version number, (e.g., DS30000A is version A of document DS30000).

#### Errata

An errata sheet, describing minor operational differences from the data sheet and recommended workarounds, may exist for current devices. As device/documentation issues become known to us, we will publish an errata sheet. The errata will specify the revision of silicon and revision of document to which it applies.

To determine if an errata sheet exists for a particular device, please check with one of the following:

- Microchip's Worldwide Web site; http://www.microchip.com
- Your local Microchip sales office (see last page)

When contacting a sales office, please specify which device, revision of silicon and data sheet (include literature number) you are using.

#### **Customer Notification System**

Register on our web site at www.microchip.com to receive the most current information on all of our products.

### 1.0 DEVICE OVERVIEW

This document contains device-specific information for the following devices:

- PIC18F66J60 PIC18F87J60
- PIC18F66J65 PIC18F96J60
- PIC18F67J60 PIC18F96J65
- PIC18F86J60 PIC18F97J60
- PIC18F86J65

This family introduces a new line of low-voltage devices with the foremost traditional advantage of all PIC18 microcontrollers – namely, high computational performance and a rich feature set at an extremely competitive price point. These features make the PIC18F97J60 family a logical choice for many high-performance applications where cost is a primary consideration.

#### 1.1 Core Features

#### 1.1.1 OSCILLATOR OPTIONS AND FEATURES

All of the devices in the PIC18F97J60 family offer five different oscillator options, allowing users a range of choices in developing application hardware. These options include:

- Two Crystal modes, using crystals or ceramic resonators.
- Two External Clock modes, offering the option of a divide-by-4 clock output.
- A Phase Lock Loop (PLL) frequency multiplier, available to the external oscillator modes, which allows clock speeds of up to 41.667 MHz.
- An internal RC oscillator with a fixed 31 kHz output which provides an extremely low-power option for timing-insensitive applications.

The internal oscillator block provides a stable reference source that gives the family additional features for robust operation:

- Fail-Safe Clock Monitor: This option constantly monitors the main clock source against a reference signal provided by the internal oscillator. If a clock failure occurs, the controller is switched to the internal oscillator, allowing for continued low-speed operation or a safe application shutdown.
- **Two-Speed Start-up:** This option allows the internal oscillator to serve as the clock source from Power-on Reset, or wake-up from Sleep mode, until the primary clock source is available.

#### 1.1.2 EXPANDED MEMORY

The PIC18F97J60 family provides ample room for application code, from 64 Kbytes to 128 Kbytes of code space. The Flash cells for program memory are rated to last 100 erase/write cycles. Data retention without refresh is conservatively estimated to be greater than 20 years.

The PIC18F97J60 family also provides plenty of room for dynamic application data with 3808 bytes of data RAM.

#### 1.1.3 EXTERNAL MEMORY BUS

In the unlikely event that 128 Kbytes of memory are inadequate for an application, the 100-pin members of the PIC18F97J60 family also implement an External Memory Bus (EMB). This allows the controller's internal program counter to address a memory space of up to 2 Mbytes, permitting a level of data access that few 8-bit devices can claim. This allows additional memory options, including:

- Using combinations of on-chip and external memory up to the 2-Mbyte limit
- Using external Flash memory for reprogrammable application code or large data tables
- Using external RAM devices for storing large amounts of variable data

#### 1.1.4 EXTENDED INSTRUCTION SET

The PIC18F97J60 family implements the optional extension to the PIC18 instruction set, adding eight new instructions and an Indexed Addressing mode. Enabled as a device configuration option, the extension has been specifically designed to optimize reentrant application code originally developed in high-level languages, such as C.

#### 1.1.5 EASY MIGRATION

Regardless of the memory size, all devices share the same rich set of peripherals, allowing for a smooth migration path as applications grow and evolve.

### 1.2 Other Special Features

- Communications: The PIC18F97J60 family incorporates a range of serial communication peripherals, including up to two independent Enhanced USARTs and up to two Master SSP modules, capable of both SPI and I<sup>2</sup>C<sup>™</sup> (Master and Slave) modes of operation. In addition, one of the general purpose I/O ports can be reconfigured as an 8-bit Parallel Slave Port for direct processor-to-processor communications.
- CCP Modules: All devices in the family incorporate two Capture/Compare/PWM (CCP) modules and three Enhanced CCP (ECCP) modules to maximize flexibility in control applications. Up to four different time bases may be used to perform several different operations at once. Each of the three ECCP modules offers up to four PWM outputs, allowing for a total of twelve PWMs. The ECCP modules also offer many beneficial features, including polarity selection, programmable dead time, auto-shutdown and restart and Half-Bridge and Full-Bridge Output modes.
- **10-Bit A/D Converter:** This module incorporates programmable acquisition time, allowing for a channel to be selected and a conversion to be initiated without waiting for a sampling period and thus, reducing code overhead.
- Extended Watchdog Timer (WDT): This enhanced version incorporates a 16-bit prescaler, allowing an extended time-out range. See Section 27.0 "Electrical Characteristics" for time-out periods.

#### 1.3 Details on Individual Family Members

Devices in the PIC18F97J60 family are available in 64-pin, 80-pin and 100-pin packages. Block diagrams for the three groups are shown in Figure 1-1, Figure 1-2 and Figure 1-3.

The devices are differentiated from each other in four ways:

- Flash program memory (three sizes, ranging from 64 Kbytes for PIC18FX6J60 devices to 128 Kbytes for PIC18FX7J60 devices).
- A/D channels (eleven for 64-pin devices, fifteen for 80-pin pin devices and sixteen for 100-pin devices).
- Serial communication modules (one EUSART module and one MSSP module on 64-pin devices, two EUSART modules and one MSSP module on 80-pin devices and two EUSART modules and two MSSP modules on 100-pin devices).
- 4. I/O pins (39 on 64-pin devices, 55 on 80-pin devices and 70 on 100-pin devices).

All other features for devices in this family are identical. These are summarized in Table 1-1, Table 1-2 and Table 1-3.

The pinouts for all devices are listed in Table 1-4, Table 1-5 and Table 1-6.

Features	PIC18F66J60	PIC18F66J65	PIC18F67J60			
Operating Frequency	DC – 41.667 MHz	DC – 41.667 MHz	DC – 41.667 MHz			
Program Memory (Bytes)	64K	96K	128K			
Program Memory (Instructions)	32764	49148	65532			
Data Memory (Bytes)		3808				
Interrupt Sources		26				
I/O Ports	F	Ports A, B, C, D, E, F, G				
I/O Pins	39					
Timers	5					
Capture/Compare/PWM Modules		2				
Enhanced Capture/Compare/PWM Modules		3				
Serial Communications	MSS	P (1), Enhanced USAF	RT (1)			
Ethernet Communications (10Base-T)		Yes				
Parallel Slave Port Communications (PSP)		No				
External Memory Bus		No				
10-Bit Analog-to-Digital Module		11 Input Channels				
Resets (and Delays)		POR, BOR, RESET Instruction, Stack Full, Stack Underflow, MCLR , WDT (PWRT, OST)				
Instruction Set	75 Instructions, 8	3 with Extended Instru	ction Set Enabled			
Packages	64-Pin TQFP					

#### TABLE 1-1: DEVICE FEATURES FOR THE PIC18F97J60 FAMILY (64-PIN DEVICES)


#### TABLE 1-2: DEVICE FEATURES FOR THE PIC18F97J60 FAMILY (80-PIN DEVICES)

Features	PIC18F86J60	PIC18F86J65	PIC18F87J60		
Operating Frequency	DC – 41.667 MHz	DC – 41.667 MHz	DC – 41.667 MHz		
Program Memory (Bytes)	64K	96K	128K		
Program Memory (Instructions)	32764	49148	65532		
Data Memory (Bytes)		3808			
Interrupt Sources					
I/O Ports	Por	ts A, B, C, D, E, F, G, I	H, J		
I/O Pins	55				
Timers		5			
Capture/Compare/PWM Modules	2				
Enhanced Capture/Compare/PWM Modules		3			
Serial Communications	MSS	P (1), Enhanced USAF	RT (2)		
Ethernet Communications (10Base-T)		Yes			
Parallel Slave Port Communications (PSP)		No			
External Memory Bus		No			
10-Bit Analog-to-Digital Module		15 Input Channels			
Resets (and Delays)	POR, BOR, RESET Instruction, Stack Full, Stack Underflow, MCLR, WDT (PWRT, OST)				
Instruction Set	75 Instructions, 8	75 Instructions, 83 with Extended Instruction Set Enabled			
Packages		80-Pin TQFP			


© 2007 Microchip Technology Inc.


### TABLE 1-3: DEVICE FEATURES FOR THE PIC18F97J60 FAMILY (100-PIN DEVICES)

Features	PIC18F96J65	PIC18F97J60	PIC18F86J10		
Operating Frequency	DC – 41.667 MHz	DC – 41.667 MHz	DC – 41.667 MHz		
Program Memory (Bytes)	64K	96K	128K		
Program Memory (Instructions)	32764	49148	65532		
Data Memory (Bytes)		3808			
Interrupt Sources		29			
I/O Ports	Por	rts A, B, C, D, E, F, G, I	H, J		
I/O Pins	70				
Timers		5			
Capture/Compare/PWM Modules	2				
Enhanced Capture/Compare/PWM Modules	3				
Serial Communications	MSS	P (2), Enhanced USAF	RT (2)		
Ethernet Communications (10Base-T)		Yes			
Parallel Slave Port Communications (PSP)		Yes			
External Memory Bus		Yes			
10-Bit Analog-to-Digital Module		16 Input Channels			
Resets (and Delays)		R, RESET Instruction, Serflow, MCLR , WDT (P			
Instruction Set	75 Instructions, 8	3 with Extended Instru	ction Set Enabled		
Packages	100-Pin TQFP				









#### PIC18F66J60/66J65/67J60 PINOUT I/O DESCRIPTIONS **TABLE 1-4:**

Din Nom c	Pin Number	Pin	Buffer	Description
Pin Name	TQFP	Туре	Туре	Description
MCLR	7	Ι	ST	Master Clear (Reset) input. This pin is an active-low Reset to the device.
OSC1/CLKI OSC1	39	I	ST	Oscillator crystal or external clock input. Oscillator crystal input or external clock source input. ST buffer when configured in internal RC mode; CMOS otherwise.
CLKI		I	CMOS	External clock source input. Always associated with pin function OSC1. (See related OSC2/CLKO pin.)
OSC2/CLKO OSC2	40	0	_	Oscillator crystal or clock output. Oscillator crystal output. Connects to crystal or resonator in Crystal Oscillator mode.
СГКО		Ο	-	In Internal RC mode, OSC2 pin outputs CLKO which has 1/4 the frequency of OSC1 and denotes the instruction cycle rate.
				PORTA is a bidirectional I/O port.
RA0/LEDA/AN0 RA0 LEDA AN0	24	I/O O I	TTL — Analog	Digital I/O. Ethernet LEDA indicator output. Analog input 0.
RA1/LEDB/AN1 RA1 LEDB AN1	23	I/O O I	TTL — Analog	Digital I/O. Ethernet LEDB indicator output. Analog input 1.
RA2/AN2/VREF- RA2 AN2 VREF-	22	I/O I I	TTL Analog Analog	Digital I/O. Analog input 2. A/D reference voltage (low) input.
RA3/AN3/VREF+ RA3 AN3 VREF+	21	I/O I I	TTL Analog Analog	Digital I/O. Analog input 3. A/D reference voltage (high) input.
RA4/T0CKI RA4 T0CKI	28	I/O I	ST ST	Digital I/O. Timer0 external clock input.
RA5/AN4 RA5 AN4	27	I/O I	TTL Analog	Digital I/O. Analog input 4.
•		ith CMO	S levels	CMOS = CMOS compatible input or output Analog = Analog input O = Output

Р = Power = Open-Drain (no P diode to VDD)

OD

Pin Name	Pin Number	Pin	Buffer	Description
Pin Name	TQFP	Туре	Туре	Description
				PORTB is a bidirectional I/O port. PORTB can be software programmed for internal weak pull-ups on all inputs.
RB0/INT0/FLT0	3			
RB0		I/O	TTL	Digital I/O.
INT0			ST	External interrupt 0.
FLT0		I	ST	Enhanced PWM Fault input (ECCP modules); enabled in software.
RB1/INT1	4			
RB1		I/O	TTL	Digital I/O.
INT1		I	ST	External interrupt 1.
RB2/INT2	5			
RB2 INT2		I/O	TTL ST	Digital I/O. External interrupt 2.
		I	51	External Interrupt 2.
RB3/INT3	6	1/0		
RB3 INT3		I/O	TTL ST	Digital I/O. External interrupt 3.
-			01	External interrupt 5.
RB4/KBI0 RB4	44	I/O	TTL	Divite I/O
KB4 KBI0		1/0	TTL	Digital I/O. Interrupt-on-change pin.
-	10			interrupt on change pin.
RB5/KBI1 RB5	43	I/O	TTL	Digital I/O.
KBI1		1/0	TTL	Interrupt-on-change pin.
RB6/KBI2/PGC	42	-		
RB6	42	I/O	TTL	Digital I/O.
KBI2		1	TTL	Interrupt-on-change pin.
PGC		I/O	ST	In-Circuit Debugger and ICSP™ programming clock pin.
RB7/KBI3/PGD	37			
RB7		I/O	TTL	Digital I/O.
KBI3		I	TTL	Interrupt-on-change pin.
PGD		I/O	ST	In-Circuit Debugger and ICSP programming data pin.
Legend: TTL = TTL co				CMOS = CMOS compatible input or output
	t Trigger input w		evels	Analog = Analog input O = Output
I = Input P = Power				O = Output OD = Open-Drain (no P diode to VDD)

Pin Name	Pin Number	Pin	Buffer	Description
	TQFP	Туре	Туре	Description
RC0/T10SO/T13CKI	30			PORTC is a bidirectional I/O port.
RC0 T10SO T13CKI		I/O O I	ST — ST	Digital I/O. Timer1 oscillator output. Timer1/Timer3 external clock input.
RC1/T1OSI/ECCP2/P2A RC1 T1OSI ECCP2 P2A	29	I/O I I/O O	ST CMOS ST	Digital I/O. Timer1 oscillator input. Capture 2 input/Compare 2 output/PWM2 output. ECCP2 PWM output A.
RC2/ECCP1/P1A RC2 ECCP1 P1A	33	I/O I/O O	ST ST	Digital I/O. Capture 1 input/Compare 1 output/PWM1 output. ECCP1 PWM output A.
RC3/SCK1/SCL1 RC3 SCK1 SCL1	34	I/O I/O I/O	ST ST ST	Digital I/O. Synchronous serial clock input/output for SPI mode. Synchronous serial clock input/output for I <sup>2</sup> C™ mode.
RC4/SDI1/SDA1 RC4 SDI1 SDA1	35	I/O I I/O	ST ST ST	Digital I/O. SPI data in. I <sup>2</sup> C data I/O.
RC5/SDO1 RC5 SDO1	36	I/O O	SТ —	Digital I/O. SPI data out.
RC6/TX1/CK1 RC6 TX1 CK1	31	I/O O I/O	ST — ST	Digital I/O. EUSART1 asynchronous transmit. EUSART1 synchronous clock (see related RX1/DT1 pin).
RC7/RX1/DT1 RC7 RX1 DT1	32	I/O I I/O	ST ST ST	Digital I/O. EUSART1 asynchronous receive. EUSART1 synchronous data (see related TX1/CK1 pin).
Legend: TTL = TTL co ST = Schmit I = Input	mpatible input t Trigger input w	ith CMOS	6 levels	CMOS = CMOS compatible input or output Analog = Analog input O = Output

#### PIC18F66J60/66J65/67J60 PINOUT I/O DESCRIPTIONS (CONTINUED) **TABLE 1-4:**

Ρ = Power

= Output OD

= Open-Drain (no P diode to VDD)

Pin Name	Pin Number	Pin	Buffer	Description
	TQFP	Туре Туре		Description
				PORTD is a bidirectional I/O port.
RD0/P1B	60			
RD0		I/O	ST	Digital I/O.
P1B		0		ECCP1 PWM output B.
RD1/ECCP3/P3A	59			
RD1		I/O	ST	Digital I/O.
ECCP3		I/O	ST	Capture 3 input/Compare 3 output/PWM3 output.
P3A		0		ECCP3 PWM output A.
RD2/CCP4/P3D	58			
RD2		I/O	ST	Digital I/O.
CCP4		I/O	ST	Capture 4 input/Compare 4 output/PWM4 output.
P3D		0		CCP4 PWM output D.
•	mpatible input			CMOS = CMOS compatible input or output
	t Trigger input w	ith CMOS	S levels	Analog = Analog input
I = Input				O = Output
P = Power				OD = Open-Drain (no P diode to VDD)

© 2007 Microchip Technology Inc.

		Pin Number		D. (()			
Pir	n Name	TQFP	Pin Type	Buffer Type	Description		
		IQFF	,,	,,			
					PORTE is a bidirectional I/O port.		
RE0/P2D		2					
RE0			I/O	ST	Digital I/O.		
P2D			0	—	ECCP2 PWM output D.		
RE1/P2C		1					
RE1			I/O	ST	Digital I/O.		
P2C			0	_	ECCP2 PWM output C.		
RE2/P2B		64					
RE2		04	I/O	ST	Digital I/O.		
P2B			0	_	ECCP2 PWM output B.		
			Ū.				
RE3/P3C RE3		63		от	Divital I/O		
P3C			I/O O	ST	Digital I/O.		
P3C			0	_	ECCP3 PWM output C.		
RE4/P3B		62					
RE4			I/O	ST	Digital I/O.		
P3B			0	_	ECCP3 PWM output B.		
RE5/P1C		61					
RE5			I/O	ST	Digital I/O.		
P1C			0		ECCP1 PWM output C.		
Legend:	TTL = TTL co	mpatible input			CMOS = CMOS compatible input or output		
	ST = Schmit	t Trigger input w	ith CMOS	S levels	Analog = Analog input		
	I = Input				O = Output		
	P = Power				OD = Open-Drain (no P diode to VDD)		

#### TABLE 1-4: PIC18F66J60/66J65/67J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

Pin Name	Pin Number	Pin	Buffer	Description
Pin Name	TQFP	Туре	Туре	Description
				PORTF is a bidirectional I/O port.
RF1/AN6/C2OUT	17			
RF1		I/O	ST	Digital I/O.
AN6		1	Analog	Analog input 6.
C2OUT		0	—	Comparator 2 output.
RF2/AN7/C1OUT	16			
RF2		I/O	ST	Digital I/O.
AN7		I.	Analog	Analog input 7.
C10UT		0	—	Comparator 1 output.
RF3/AN8	15			
RF3		I/O	ST	Digital I/O.
AN8		I	Analog	Analog input 8.
RF4/AN9	14			
RF4	17	I/O	ST	Digital I/O.
AN9		1	Analog	Analog input 9.
RF5/AN10/CVREF	13		0	
RF5	15	I/O	ST	Digital I/O.
AN10		1	Analog	Analog input 10.
CVREF		0		Comparator reference voltage output.
RF6/AN11	12			
RF6	12	I/O	ST	Digital I/O.
AN11			Analog	Analog input 11.
			, analog	
RF7/SS1	11	1/0	ST	
RF7 SS1		I/O	TTL	Digital I/O.
			116	SPI slave select input.
	compatible input		Clavela	CMOS = CMOS compatible input or output
ST = Schi I = Inpu	mitt Trigger input w		5 ieveis	Analog = Analog input O = Output
	<i>.</i>			

TABLE 1-4:	PIC18F66J60/66J65/67J60 PINOUT I/O DESCRIPTIONS (	(CONTINUED)	
		USITINUED/	

Р = Power

= Open-Drain (no P diode to VDD) OD

Din Nome	Pin Number	Pin Buffer Type Type	Buffer	Description
Pin Name	TQFP Typ		Туре	Description
				PORTG is a bidirectional I/O port.
RG4/CCP5/P1D	8			
RG4		I/O	ST	Digital I/O.
CCP5		I/O	ST	Capture 5 input/Compare 5 output/PWM5 output.
P1D		0	—	ECCP1 PWM output D.
Vss	9, 25, 41, 56	Р	—	Ground reference for logic and I/O pins.
Vdd	26, 38, 57	Р	_	Positive supply for peripheral digital logic and I/O pins.
AVss	20	Р		Ground reference for analog modules.
AVdd	19	Р		Positive supply for analog modules.
ENVREG	18	I	ST	Enable for on-chip voltage regulator.
Vddcore/Vcap Vddcore	10	Р	_	Core logic power or external filter capacitor connection. Positive supply for microcontroller core logic (regulator disabled).
VCAP		Р	_	External filter capacitor connection (regulator enabled).
VSSPLL	55	Р	_	Ground reference for Ethernet PHY PLL.
VDDPLL	54	Р	_	Positive 3.3V supply for Ethernet PHY PLL.
Vsstx	52	Р	_	Ground reference for Ethernet PHY transmit subsystem.
Vddtx	49	Р	_	Positive 3.3V supply for Ethernet PHY transmit subsystem.
Vssrx	45	Р	_	Ground reference for Ethernet PHY receive subsystem.
Vddrx	48	Р	_	Positive 3.3V supply for Ethernet PHY receive subsystem.
RBIAS	53	I	Analog	Bias current for Ethernet PHY. Must be tied to Vss via a resistor; see <b>Section 18.0 "Ethernet Module"</b> for specification.
TPOUT+	51	0	_	Ethernet differential signal output.
TPOUT-	50	0	_	Ethernet differential signal output.
TPIN+	47	I	Analog	Ethernet differential signal input.
TPIN-	46	I	Analog	Ethernet differential signal input.

#### **TABLE 1-4**: PIC18F66J60/66J65/67J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

**Legend:** TTL = TTL compatible input

ST = Schmitt Trigger input with CMOS levels

CMOS = CMOS compatible input or output

Analog = Analog input

0

= Output

OD = Open-Drain (no P diode to VDD)

Pin Name	Pin Number	Pin Type	Buffer	Description
	TQFP		Туре	
MCLR	9	I	ST	Master Clear (Reset) input. This pin is an active-low Reset to the device.
OSC1/CLKI OSC1	49	I	ST	Oscillator crystal or external clock input. Oscillator crystal input or external clock source input. ST buffer when configured in internal RC mode; CMOS otherwise.
CLKI		Ι	CMOS	External clock source input. Always associated with pin function OSC1. (See related OSC2/CLKO pin.)
OSC2/CLKO OSC2 CLKO	50	0 0	_	Oscillator crystal or clock output. Oscillator crystal output. Connects to crystal or resonator in Crystal Oscillator mode. In Internal RC mode, OSC2 pin outputs CLKO which has 1/4 the frequency of OSC1 and denotes the
				instruction cycle rate.
RA0/LEDA/AN0 RA0 LEDA AN0	30	I/O O I	TTL — Analog	PORTA is a bidirectional I/O port. Digital I/O. Ethernet LEDA indicator output. Analog input 0.
RA1/LEDB/AN1 RA1 LEDB AN1	29	I/O O I	TTL — Analog	Digital I/O. Ethernet LEDB indicator output. Analog input 1.
RA2/AN2/VREF- RA2 AN2 VREF-	28	I/O I I	TTL Analog Analog	Digital I/O. Analog input 2. A/D reference voltage (low) input.
RA3/AN3/VREF+ RA3 AN3 VREF+	27	I/O I I	TTL Analog Analog	Digital I/O. Analog input 3. A/D reference voltage (high) input.
RA4/T0CKI RA4 T0CKI	34	I/O I	ST ST	Digital I/O. Timer0 external clock input.
RA5/AN4 RA5 AN4	33	I/O I	TTL Analog	Digital I/O. Analog input 4.

#### **TABLE 1-5**: PIC18F86J60/86J65/87J60 PINOUT I/O DESCRIPTIONS

Р = Power

= Output OD = Open-Drain (no P diode to VDD)

Note 1: Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.

2: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

3: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared.

Pin Name	Pin Number	Pin	Buffer	Description	
Pin Name	TQFP	Туре	Туре	Description	
				PORTB is a bidirectional I/O port. PORTB can be software programmed for internal weak pull-ups on all inputs.	
RB0/INT0/FLT0 RB0 INT0 FLT0	5	I/O I I	TTL ST ST	Digital I/O. External interrupt 0. Enhanced PWM Fault input (ECCP modules); enabled in software.	
RB1/INT1 RB1 INT1	6	I/O I	TTL ST	Digital I/O. External interrupt 1.	
RB2/INT2 RB2 INT2	7	I/O I	TTL ST	Digital I/O. External interrupt 2.	
RB3/INT3 RB3 INT3	8	I/O I	TTL ST	Digital I/O. External interrupt 3.	
RB4/KBI0 RB4 KBI0	54	I/O I	TTL TTL	Digital I/O. Interrupt-on-change pin.	
RB5/KBI1 RB5 KBI1	53	I/O I	TTL TTL	Digital I/O. Interrupt-on-change pin.	
RB6/KBI2/PGC RB6 KBI2 PGC	52	I/O I I/O	TTL TTL ST	Digital I/O. Interrupt-on-change pin. In-Circuit Debugger and ICSP™ programming clock pin.	
RB7/KBI3/PGD RB7 KBI3 PGD	47	I/O I I/O	TTL TTL ST	Digital I/O. Interrupt-on-change pin. In-Circuit Debugger and ICSP programming data pin.	
Legend:       TTL = TTL compatible input       CMOS       = CMOS compatible input or output         ST = Schmitt Trigger input with CMOS levels       Analog       = Analog input         I = Input       O       = Output					

#### **TABLE 1-5**: PIC18F86J60/86J65/87J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

$$P = Power$$

OD

= Open-Drain (no P diode to VDD)

Note 1: Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.

2: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

3: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared.

	Pin Number	Pin	Buffer	Description
Pin Name	TQFP	Туре	Туре Туре	Description
				PORTC is a bidirectional I/O port.
RC0/T1OSO/T13CKI RC0 T1OSO T13CKI	36	I/O O I	ST — ST	Digital I/O. Timer1 oscillator output. Timer1/Timer3 external clock input.
RC1/T1OSI/ECCP2/P2A RC1 T1OSI ECCP2 <sup>(1)</sup> P2A <sup>(1)</sup>	35	I/O I I/O O	ST CMOS ST —	Digital I/O. Timer1 oscillator input. Capture 2 input/Compare 2 output/PWM2 output. ECCP2 PWM output A.
RC2/ECCP1/P1A RC2 ECCP1 P1A	43	I/O I/O O	ST ST	Digital I/O. Capture 1 input/Compare 1 output/PWM1 output. ECCP1 PWM output A.
RC3/SCK1/SCL1 RC3 SCK1 SCL1	44	I/O I/O I/O	ST ST ST	Digital I/O. Synchronous serial clock input/output for SPI mode. Synchronous serial clock input/output for I <sup>2</sup> C™ mode.
RC4/SDI1/SDA1 RC4 SDI1 SDA1	45	I/O I I/O	ST ST ST	Digital I/O. SPI data in. I <sup>2</sup> C data I/O.
RC5/SDO1 RC5 SDO1	46	I/O O	ST —	Digital I/O. SPI data out.
RC6/TX1/CK1 RC6 TX1 CK1	37	I/O O I/O	ST — ST	Digital I/O. EUSART1 asynchronous transmit. EUSART1 synchronous clock (see related RX1/DT1 pin).
RC7/RX1/DT1 RC7 RX1 DT1	38	I/O I I/O	ST ST ST	Digital I/O. EUSART1 asynchronous receive. EUSART1 synchronous data (see related TX1/CK1 pin).
I = Input P = Power	tt Trigger input v			CMOS = CMOS compatible input or output Analog = Analog input O = Output OD = Open-Drain (no P diode to VDD)

Note 1: Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.

2: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

3: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared.

Dia Nama	Pin Number	Pin	Buffer	Description
Pin Name	TQFP	Туре	Туре	Description
				PORTD is a bidirectional I/O port.
RD0	72	I/O	ST	Digital I/O.
RD1	69	I/O	ST	Digital I/O.
RD2	68	I/O	ST	Digital I/O.
				PORTE is a bidirectional I/O port.
RE0/P2D RE0 P2D	4	I/O O	ST —	Digital I/O. ECCP2 PWM output D.
RE1/P2C RE1 P2C	3	I/O O	ST —	Digital I/O. ECCP2 PWM output C.
RE2/P2B RE2 P2B	78	I/O O	ST —	Digital I/O. ECCP2 PWM output B.
RE3/P3C RE3 P3C <sup>(2)</sup>	77	I/O O	ST —	Digital I/O. ECCP3 PWM output C.
RE4/P3B RE4 P3B <sup>(2)</sup>	76	I/O O	ST —	Digital I/O. ECCP3 PWM output B.
RE5/P1C RE5 P1C <sup>(2)</sup>	75	I/O O	ST —	Digital I/O. ECCP1 PWM output C.
RE6/P1B RE6 P1B <sup>(2)</sup>	74	I/O O	ST —	Digital I/O. ECCP1 PWM output B.
RE7/ECCP2/P2A RE7 ECCP2 <sup>(3)</sup> P2A <sup>(3)</sup>	73	I/O I/O O	ST ST	Digital I/O. Capture 2 input/Compare 2 output/PWM2 output. ECCP2 PWM output A.
		with CM0	OS levels	CMOS = CMOS compatible input or output Analog = Analog input O = Output OD = Open-Drain (no P diode to VDD)

#### **TABLE 1-5**: PIC18F86J60/86J65/87J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

Note 1: Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.

2: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

3: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared.

Die News	Pin Number	Pin	Buffer	Description
Pin Name	TQFP	Туре	Туре	
				PORTF is a bidirectional I/O port.
RF1/AN6/C2OUT RF1 AN6 C2OUT	23	I/O I O	ST Analog —	Digital I/O. Analog input 6. Comparator 2 output.
RF2/AN7/C1OUT RF2 AN7 C1OUT	18	I/O I O	ST Analog —	Digital I/O. Analog input 7. Comparator 1 output.
RF3/AN8 RF3 AN8	17	I/O I	ST Analog	Digital I/O. Analog input 8.
RF4/AN9 RF4 AN9	16	I/O I	ST Analog	Digital I/O. Analog input 9.
RF5/AN10/CVREF RF5 AN10 CVREF	15	I/O I O	ST Analog —	Digital I/O. Analog input 10. Comparator reference voltage output.
RF6/AN11 RF6 AN11	14	I/O I	ST Analog	Digital I/O. Analog input 11.
RF7/ <u>SS1</u> RF7 SS1	13	I/O I	ST TTL	Digital I/O. SPI slave select input.
		with CM0	OS levels	CMOS=CMOS compatible input or outputAnalog=Analog inputO=OutputOD=Open-Drain (no P diode to VDD)

Note 1: Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.

2: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

3: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared.

Pin Name	Pin Number	Pin	Pin Buffer Type Type	Description	
	TQFP	Туре		Description	
				PORTG is a bidirectional I/O port.	
RG0/ECCP3/P3A	56				
RG0		I/O	ST	Digital I/O.	
ECCP3		I/O	ST	Capture 3 input/Compare 3 output/PWM3 output.	
P3A		0	—	ECCP3 PWM output A.	
RG1/TX2/CK2	55				
RG1		I/O	ST	Digital I/O.	
TX2		0	—	EUSART2 asynchronous transmit.	
CK2		I/O	ST	EUSART2 synchronous clock (see related RX2/DT2 pin).	
RG2/RX2/DT2	42				
RG2		I/O	ST	Digital I/O.	
RX2		I	ST	EUSART2 asynchronous receive.	
DT2		I/O	ST	EUSART2 synchronous data (see related TX2/CK2 pin).	
RG3/CCP4/P3D	41				
RG3		I/O	ST	Digital I/O.	
CCP4		I/O	ST	Capture 4 input/Compare 4 output/PWM4 output.	
P3D		0	—	ECCP3 PWM output D.	
RG4/CCP5/P1D	10				
RG4		I/O	ST	Digital I/O.	
CCP5		I/O	ST	Capture 5 input/Compare 5 output/PWM5 output.	
P1D		0	—	ECCP1 PWM output D.	
-	compatible input			CMOS = CMOS compatible input or output	
	nitt Trigger input v	with CM0	OS levels	Analog = Analog input	
I = Input				O = Output	
P = Powe	-			OD = Open-Drain (no P diode to VDD)	
<b>Note 1:</b> Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.					

2: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

3: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared.

<b>5</b> 1 11	Pin Number	Pin	Buffer			
Pin Name	TQFP	Туре	Туре	Description		
				PORTH is a bidirectional I/O port.		
RH0	79	I/O	ST	Digital I/O.		
RH1	80	I/O	ST	Digital I/O.		
RH2	1	I/O	ST	Digital I/O.		
RH3	2	I/O	ST	Digital I/O.		
RH4/AN12/P3C RH4 AN12 P3C <sup>(4)</sup>	22	I/O I O	ST Analog —	Digital I/O. Analog input 12. ECCP3 PWM output C.		
RH5/AN13/P3B RH5 AN13 P3B <sup>(4)</sup>	21	I/O I O	ST Analog —	Digital I/O. Analog input 13. ECCP3 PWM output B.		
RH6/AN14/P1C RH6 AN14 P1C <sup>(4)</sup>	20	I/O I O	ST Analog —	Digital I/O. Analog input 14. ECCP1 PWM output C.		
RH7/AN15/P1B RH7 AN15 P1B <sup>(4)</sup>	19	I/O I O	ST Analog —	Digital I/O. Analog input 15. ECCP1 PWM output B.		
P1B***       O       ECCP1 PWM output B.         Legend:       TTL = TTL compatible input       CMOS       = CMOS compatible input or output         ST = Schmitt Trigger input with CMOS levels       Analog       = Analog input         I = Input       O       = Output         P = Power       OD       = Output         Note 1:       Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.						

TABLE 1-5:	PIC18F86J60/86J65/87J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

INOTE **1:** Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.

2: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

3: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared.

Dia Nama	Pin Number	Pin	Buffer	<b>-</b>		
Pin Name	TQFP	Туре	Туре	Description		
				PORTJ is a bidirectional I/O port.		
RJ4	39	I/O	ST	Digital I/O.		
RJ5	40	I/O	ST	Digital I/O		
Vss	11, 31, 51, 70	Р	_	Ground reference for logic and I/O pins.		
Vdd	32, 48, 71	Р	_	Positive supply for peripheral digital logic and I/O pins.		
AVss	26	Р	_	Ground reference for analog modules.		
AVdd	25	Р	_	Positive supply for analog modules.		
ENVREG	24	I	ST	Enable for on-chip voltage regulator.		
VDDCORE/VCAP VDDCORE	12	Р	_	Core logic power or external filter capacitor connection. Positive supply for microcontroller core logic (regulator disabled).		
VCAP		Р	_	External filter capacitor connection (regulator enabled).		
VSSPLL	67	Р	—	Ground reference for Ethernet PHY PLL.		
Vddpll	66	Р	—	Positive 3.3V supply for Ethernet PHY PLL.		
Vsstx	64	Р	—	Ground reference for Ethernet PHY transmit subsystem.		
Vddtx	61	Р	_	Positive 3.3V supply for Ethernet PHY transmit subsystem.		
VSSRX	57	Р	_	Ground reference for Ethernet PHY receive subsystem.		
Vddrx	60	Р	_	Positive 3.3V supply for Ethernet PHY receive subsystem.		
RBIAS	65	I	Analog	Bias current for Ethernet PHY. Must be tied to Vss via a resistor; see <b>Section 18.0 "Ethernet Module"</b> for specification.		
TPOUT+	63	0	_	Ethernet differential signal output.		
TPOUT-	62	0	_	Ethernet differential signal output.		
TPIN+	59	I	Analog	Ethernet differential signal input.		
TPIN-	58		Analog	Ethernet differential signal input.		
Legend: TTL = TTL compatible input CMOS = CMOS compatible input or output						

#### TABLE 1-5: PIC18F86J60/86J65/87J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

ST = Schmitt Trigger input with CMOS levels

- Analog = Analog input
- O = Output

OD

I = Input P = Power

= Open-Drain (no P diode to VDD)

Note 1: Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.

2: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

3: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared.

Pin Name	Pin Number	Pin	Buffer	Devel (free
	TQFP	Туре	Туре	Description
MCLR	13	I	ST	Master Clear (Reset) input. This pin is an active-low Reset to the device.
OSC1/CLKI OSC1	63	I	ST	Oscillator crystal or external clock input. Oscillator crystal input or external clock source input. ST buffer when configured in internal RC mode; CMOS otherwise.
CLKI		I	CMOS	External clock source input. Always associated with pin function OSC1. (See related OSC2/CLKO pin.)
OSC2/CLKO OSC2	64	0	_	Oscillator crystal or clock output. Oscillator crystal output. Connects to crystal or resonator in Crystal Oscillator mode.
CLKO		0	—	In Internal RC mode, OSC2 pin outputs CLKO which has 1/4 the frequency of OSC1 and denotes the instruction cycle rate
				PORTA is a bidirectional I/O port.
RA0/LEDA/AN0 RA0 LEDA AN0	35	I/O O I	TTL — Analog	Digital I/O. Ethernet LEDA indicator output. Analog input 0.
RA1/LEDB/AN1 RA1 LEDB AN1	34	I/O O I	TTL — Analog	Digital I/O. Ethernet LEDB indicator output. Analog input 1.
RA2/AN2/VREF- RA2 AN2 VREF-	33	I/O I I	TTL Analog Analog	Digital I/O. Analog input 2. A/D reference voltage (low) input.
RA3/AN3/Vref+ RA3 AN3 Vref+	32	I/O I I	TTL Analog Analog	Digital I/O. Analog input 3. A/D reference voltage (high) input.
RA4/T0CKI RA4 T0CKI	42	I/O I	ST ST	Digital I/O. Timer0 external clock input.
RA5/AN4 RA5 AN4	41	I/O I	TTL Analog	Digital I/O. Analog input 4.
		with CM0	OS levels	CMOS = CMOS compatible input or output Analog = Analog input O = Output OD = Open-Drain (no P diode to VDD)

Note 1: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Extended Microcontroller mode).

2: Default assignment for ECCP2/P2A for all devices in all operating modes (CCP2MX Configuration bit is set).

3: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

Pin Name	Pin Number	Pin Type	Buffer Type	Description
	TQFP			
				PORTB is a bidirectional I/O port. PORTB can be software programmed for internal weak pull-ups on all inputs.
RB0/INT0/FLT0 RB0 INT0 FLT0	5	I/O I I	TTL ST ST	Digital I/O. External interrupt 0. Enhanced PWM Fault input (ECCP modules); enabled in software.
RB1/INT1 RB1 INT1	6	I/O I	TTL ST	Digital I/O. External interrupt 1.
RB2/INT2 RB2 INT2	7	I/O I	TTL ST	Digital I/O. External interrupt 2.
RB3/INT3/ECCP2/P2A RB3 INT3 ECCP2 <sup>(1)</sup> P2A <sup>(1)</sup>	8	I/O I I/O O	TTL ST ST —	Digital I/O. External interrupt 3. Capture 2 input/Compare 2 output/PWM2 output. ECCP2 PWM output A.
RB4/KBI0 RB4 KBI0	69	I/O I	TTL TTL	Digital I/O. Interrupt-on-change pin.
RB5/KBI1 RB5 KBI1	68	I/O I	TTL TTL	Digital I/O. Interrupt-on-change pin.
RB6/KBI2/PGC RB6 KBI2 PGC	67	I/O I I/O	TTL TTL ST	Digital I/O. Interrupt-on-change pin. In-Circuit Debugger and ICSP™ programming clock pin.
RB7/KBI3/PGD RB7 KBI3 PGD	57	I/O I I/O	TTL TTL ST	Digital I/O. Interrupt-on-change pin. In-Circuit Debugger and ICSP programming data pin.
ST = Schm I = Input P = Power				CMOS = CMOS compatible input or output Analog = Analog input O = Output OD = Open-Drain (no P diode to VDD) 2MX Configuration bit is cleared (Extended Microcontroller mod

#### **TABLE 1-6**: PIC18F96J60/96J65/97J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

2: Default assignment for ECCP2/P2A for all devices in all operating modes (CCP2MX Configuration bit is set).

3: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

Pin Name	Pin Number	Pin Type	Buffer	Description
	TQFP		Туре	Description
				PORTC is a bidirectional I/O port.
RC0/T1OSO/T13CKI	44			
RC0		I/O	ST	Digital I/O.
T10SO		0	—	Timer1 oscillator output.
T13CKI		I	ST	Timer1/Timer3 external clock input.
RC1/T1OSI/ECCP2/P2A	43			
RC1		I/O	ST	Digital I/O.
T1OSI		I	CMOS	Timer1 oscillator input.
ECCP2 <sup>(2)</sup>		I/O	ST	Capture 2 input/Compare 2 output/PWM2 output.
P2A <sup>(2)</sup>		0	—	ECCP2 PWM output A.
RC2/ECCP1/P1A	53			
RC2		I/O	ST	Digital I/O.
ECCP1		I/O	ST	Capture 1 input/Compare 1 output/PWM1 output.
P1A		0	_	ECCP1 PWM output A.
RC3/SCK1/SCL1	54			
RC3		I/O	ST	Digital I/O.
SCK1		I/O	ST	Synchronous serial clock input/output for SPI mode.
SCL1		I/O	ST	Synchronous serial clock input/output for $I^2C^{TM}$ mode.
RC4/SDI1/SDA1	55			
RC4		I/O	ST	Digital I/O.
SDI1		I	ST	SPI data in. I <sup>2</sup> C data I/O.
SDA1		I/O	ST	
RC5/SDO1	56			
RC5		I/O	ST	Digital I/O.
SDO1		0		SPI data out.
RC6/TX1/CK1	45			
RC6		I/O	ST	Digital I/O.
TX1		0	-	EUSART1 asynchronous transmit.
CK1		I/O	ST	EUSART1 synchronous clock (see related RX1/DT1 pin).
RC7/RX1/DT1	46			
RC7		I/O	ST	Digital I/O.
RX1		I	ST	EUSART1 asynchronous receive.
DT1	L	I/O	ST	EUSART1 synchronous data (see related TX1/CK1 pin).
Legend: TTL = TTL co				CMOS = CMOS compatible input or output
	tt Trigger input v	with CM0	JS levels	Analog = Analog input O = Output
I = Input P = Power				OD = Output OD = Open-Drain (no P diode to VDD)

Note 1: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Extended Microcontroller mode).

2: Default assignment for ECCP2/P2A for all devices in all operating modes (CCP2MX Configuration bit is set).

**3:** Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

Pin Name	Pin Number	Pin	Buffer	Description
Fininanie	TQFP	Туре	Туре	Description
				PORTD is a bidirectional I/O port.
RD0/AD0/PSP0 RD0 AD0 PSP0	92	I/O I/O I/O	ST TTL TTL	Digital I/O. External memory address/data 0. Parallel Slave Port data.
RD1/AD1/PSP1 RD1 AD1 PSP1	91	I/O I/O I/O	ST TTL TTL	Digital I/O. External memory address/data 1. Parallel Slave Port data.
RD2/AD2/PSP2 RD2 AD2 PSP2	90	I/O I/O I/O	ST TTL TTL	Digital I/O. External memory address/data 2. Parallel Slave Port data.
RD3/AD3/PSP3 RD3 AD3 PSP3	89	I/O I/O I/O	ST TTL TTL	Digital I/O. External memory address/data 3. Parallel Slave Port data.
RD4/AD4/PSP4/SDO2 RD4 AD4 PSP4 SDO2	88	I/O I/O I/O O	ST TTL TTL —	Digital I/O. External memory address/data 4. Parallel Slave Port data. SPI data out.
RD5/AD5/PSP5/ SDI2/SDA2 RD5 AD5 PSP5 SDI2 SDA2	87	I/O I/O I/O I	ST TTL TTL ST ST	Digital I/O. External memory address/data 5. Parallel Slave Port data. SPI data in. I <sup>2</sup> C™ data I/O.
RD6/AD6/PSP6/ SCK2/SCL2 RD6 AD6 PSP6 SCK2 SCL2	84	I/O I/O I/O I/O I/O	ST TTL TTL ST ST	Digital I/O. External memory address/data 6. Parallel Slave Port data. Synchronous serial clock input/output for SPI mode. Synchronous serial clock input/output for I <sup>2</sup> C mode.
RD7/AD7/PSP7/ <del>SS2</del> RD7 AD7 PSP7 SS2	83	I/O I/O I/O I	ST TTL TTL TTL	Digital I/O. External memory address/data 7. Parallel Slave Port data. SPI slave select input.
-				CMOS = CMOS compatible input or output Analog = Analog input O = Output OD = Open-Drain (no P diode to VDD) 2MX Configuration bit is cleared (Extended Microcontroller mode). es in all operating modes (CCP2MX Configuration bit is set).

**3:** Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

Pin Name	Pin Number	Pin Type	Buffer Type	Description
	TQFP			
				PORTE is a bidirectional I/O port.
RE0/AD8/RD/P2D RE0 AD8 RD P2D	4	I/O I/O I O	ST TTL TTL —	Digital I/O. External memory address/data 8. Read control for Parallel Slave Port. ECCP2 PWM output D.
RE1/AD9/WR/P2C	3			
RE1 AD9 WR P2C		I/O I/O I O	ST TTL TTL —	Digital I/O. External memory address/data 9. Write control for Parallel Slave Port. ECCP2 PWM output C.
RE2/AD10/CS/P2B RE2 AD10 CS P2B	98	I/O I/O I O	ST TTL TTL —	Digital I/O. External memory address/data 10. Chip select control for Parallel Slave Port. ECCP2 PWM output B.
RE3/AD11/P3C RE3 AD11 P3C <sup>(3)</sup>	97	I/O I/O O	ST TTL	Digital I/O. External memory address/data 11. ECCP3 PWM output C.
RE4/AD12/P3B RE4 AD12 P3B <sup>(3)</sup>	96	I/O I/O O	ST TTL	Digital I/O. External memory address/data 12. ECCP3 PWM output B.
RE5/AD13/P1C RE5 AD13 P1C <sup>(3)</sup>	95	I/O I/O O	ST TTL	Digital I/O. External memory address/data 13. ECCP1 PWM output C.
RE6/AD14/P1B RE6 AD14 P1B <sup>(3)</sup>	94	I/O I/O O	ST TTL	Digital I/O. External memory address/data 14. ECCP1 PWM output B.
RE7/AD15/ECCP2/P2A RE7 AD15 ECCP2 <sup>(4)</sup> P2A <sup>(4)</sup>	93	I/O I/O I/O O	ST TTL ST	Digital I/O. External memory address/data 15. Capture 2 input/Compare 2 output/PWM2 output. ECCP2 PWM output A.
-	ompatible input itt Trigger input r	with CM	OS levels	CMOS = CMOS compatible input or output Analog = Analog input O = Output OD = Open-Drain (no P diode to VDD)

Note 1: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Extended Microcontroller mode).

2: Default assignment for ECCP2/P2A for all devices in all operating modes (CCP2MX Configuration bit is set).

3: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

Pin Name	Pin Number	Pin	Buffer	Description
	TQFP	Туре	Туре	Description
				PORTF is a bidirectional I/O port.
RF0/AN5	12			
RF0		I/O	ST	Digital I/O.
AN5		I	Analog	Analog input 5.
RF1/AN6/C2OUT	28			
RF1		I/O	ST	Digital I/O.
AN6 C2OUT		I O	Analog	Analog input 6. Comparator 2 output.
	00	0		
RF2/AN7/C1OUT RF2	23	I/O	ST	Digital I/O.
AN7		1/0	Analog	Analog input 7.
C1OUT		Ō		Comparator 1 output.
RF3/AN8	22			
RF3		I/O	ST	Digital I/O.
AN8		I.	Analog	Analog input 8.
RF4/AN9	21			
RF4		I/O	ST	Digital I/O.
AN9		I	Analog	Analog input 9.
RF5/AN10/CVREF	20			
RF5		I/O	ST	Digital I/O.
AN10		I	Analog	Analog input 10.
CVREF		0	—	Comparator reference voltage output.
RF6/AN11	19			
RF6		I/O	ST	Digital I/O.
AN11		I	Analog	Analog input 11.
RF7/SS1	18	1/2	о <b>т</b>	
RF7 SS1		I/O	ST TTL	Digital I/O. SPI slave select input.
Legend: TTL = TTL co	mpatible input	CMOS = CMOS compatible input or output		
ST = Schmit	Analog = Analog input			
I = Input O = Output				
P = Power OD = Open-Drain (no P diode to VDD)				

Note 1: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Extended Microcontroller mode).

2: Default assignment for ECCP2/P2A for all devices in all operating modes (CCP2MX Configuration bit is set).

3: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

Pin Name	Pin Number	Pin	Buffer	Bassister	
Pin Name	TQFP	Туре	Туре	Description	
				PORTG is a bidirectional I/O port.	
RG0/ECCP3/P3A	71				
RG0		I/O	ST	Digital I/O.	
ECCP3 P3A		1/O O	ST	Capture 3 input/Compare 3 output/PWM3 output. ECCP3 PWM output A.	
		0			
RG1/TX2/CK2 RG1	70	I/O	ST	Digital I/O.	
TX2		0		EUSART2 asynchronous transmit.	
CK2		I/O	ST	EUSART2 synchronous clock (see related RX2/DT2 pin).	
RG2/RX2/DT2	52				
RG2		I/O	ST	Digital I/O.	
RX2		I	ST	EUSART2 asynchronous receive.	
DT2		I/O	ST	EUSART2 synchronous data (see related TX2/CK2 pin).	
RG3/CCP4/P3D	51				
RG3		I/O	ST	Digital I/O.	
CCP4 P3D		1/O 0	ST	Capture 4 input/Compare 4 output/PWM4 output.	
		0		ECCP3 PWM output D.	
RG4/CCP5/P1D RG4	14	I/O	ST	Digital I/O.	
CCP5		1/O	ST	Capture 5 input/Compare 5 output/PWM5 output.	
P1D		0	_	ECCP1 PWM output D.	
RG5	11	I/O	ST	Digital I/O.	
RG6	10	I/O	ST	Digital I/O.	
RG7	38	I/O	ST	Digital I/O.	
	compatible input			CMOS = CMOS compatible input or output	
	itt Trigger input	with CM0	OS levels	Analog = Analog input	
I = Input P = Powe	r			O = Output OD = Open-Drain (no P diode to VDD)	
		2/P2A v	vhen CCP	2MX Configuration bit is cleared (Extended Microcontroller mod	
				es in all operating modes (CCP2MX Configuration bit is set).	

#### TABLE 1-6: PIC18F96J60/96J65/97J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

**3:** Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

5: Alternate assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is cleared).

Din Nome	Pin Number	Pin	Buffer	Description		
Pin Name	TQFP	Туре	Туре	Description		
				PORTH is a bidirectional I/O port.		
RH0/A16 RH0	99	I/O	ST	Digital I/O.		
A16		0	_	External memory address 16.		
RH1/A17 RH1 A17	100	I/O O	ST —	Digital I/O. External memory address 17.		
RH2/A18	1					
RH2 A18		I/O O	ST —	Digital I/O. External memory address 18.		
RH3/A19 RH3 A19	2	I/O O	ST —	Digital I/O. External memory address 19.		
RH4/AN12/P3C RH4 AN12 P3C <sup>(5)</sup>	27	I/O I O	ST Analog —	Digital I/O. Analog input 12. ECCP3 PWM output C.		
RH5/AN13/P3B RH5 AN13 P3B <sup>(5)</sup>	26	I/O I O	ST Analog —	Digital I/O. Analog input 13. ECCP3 PWM output B.		
RH6/AN14/P1C RH6 AN14 P1C <sup>(5)</sup>	25	I/O I O	ST Analog —	Digital I/O. Analog input 14. ECCP1 PWM output C.		
RH7/AN15/P1B RH7 AN15 P1B <sup>(5)</sup>	24	I/O I O	ST Analog —	Digital I/O. Analog input 15. ECCP1 PWM output B.		
P1B <sup>(5)</sup> Legend: TTL = TTL	compatible input mitt Trigger input	0	_			

#### TABLE 1-6: PIC18F96J60/96J65/97J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

P = Power OD = Open-Drain (no P diode to VDD) Note 1: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Extended Microcontroller mode).

Default assignment for ECCP2/P2A for all devices in all operating modes (CCP2MX Configuration bit is set).

Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

5: Alternate assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is cleared).

Din Nome	Pin Number	Pin	Buffer	Description		
Pin Name	TQFP	Туре	Туре	Description		
				PORTJ is a bidirectional I/O port.		
RJ0/ALE	49		07			
RJ0 ALE		I/O O	ST —	Digital I/O. External memory address latch enable.		
RJ1/OE	50					
RJ1 OE		I/O	ST	Digital I/O.		
-		0	_	External memory output enable.		
RJ2/WRL RJ2	66	I/O	ST	Digital I/O.		
WRL		0	—	External memory write low control.		
RJ3/WRH	61		0.7			
RJ3 WRH		1/O O	ST —	Digital I/O. External memory write high control.		
RJ4/BA0	47	-				
RJ4		I/O	ST	Digital I/O.		
BAO		0	_	External memory byte address 0 control.		
RJ5/CE RJ5	48	I/O	ST	Digital I/O		
CE		0		External memory chip enable control.		
RJ6/LB	58					
RJ6 LB		1/O O	ST —	Digital I/O. External memory low byte control.		
RJ7/UB	39	-				
RJ7		I/O	ST	Digital I/O.		
UB		0	—	External memory high byte control.		
	ompatible input itt Trigger input v	with CM0	OS levels	CMOS = CMOS compatible input or output Analog = Analog input		
I = Input				O = Output		

TABLE 1-6:	PIC18F96J60/96J65/97J60 PINOUT I/O DESCRIPTIONS (	(CONTINUED)	

P = Power

OD = Open-Drain (no P diode to VDD)

Note 1: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Extended Microcontroller mode).

2: Default assignment for ECCP2/P2A for all devices in all operating modes (CCP2MX Configuration bit is set).

3: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

**5:** Alternate assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is cleared).

Dia Nama	Pin Number	Pin Buffer	Description			
Pin Name	TQFP	Туре	Туре	Description		
NC	9	_	—	No connect.		
Vss	15, 36, 40, 60, 65, 85	Р	_	Ground reference for logic and I/O pins.		
Vdd	17, 37, 59, 62, 86	Р		Positive supply for peripheral digital logic and I/O pins.		
AVss	31	Р	_	Ground reference for analog modules.		
AVdd	30	Р	_	Positive supply for analog modules.		
ENVREG	29	I	ST	Enable for on-chip voltage regulator.		
VDDCORE/VCAP VDDCORE	16	Р	_	Core logic power or external filter capacitor connection. Positive supply for microcontroller core logic (regulator disabled).		
VCAP		Р	_	External filter capacitor connection (regulator enabled).		
VSSPLL	82	Р	_	Ground reference for Ethernet PHY PLL.		
Vddpll	81	Р	_	Positive 3.3V supply for Ethernet PHY PLL.		
Vsstx	79	Р	_	Ground reference for Ethernet PHY transmit subsystem.		
Vddtx	76	Р	_	Positive 3.3V supply for Ethernet PHY transmit subsystem.		
Vssrx	72	Р	_	Ground reference for Ethernet PHY receive subsystem.		
Vddrx	75	Р		Positive 3.3V supply for Ethernet PHY receive subsystem.		
RBIAS	80	I	Analog	Bias current for Ethernet PHY. Must be tied to Vss via a resistor; see <b>Section 18.0 "Ethernet Module"</b> for specification.		
TPOUT+	78	0	_	Ethernet differential signal output.		
TPOUT-	77	0	_	Ethernet differential signal output.		
TPIN+	74	I	Analog	Ethernet differential signal input.		
TPIN-	73	I	Analog	Ethernet differential signal input.		
-	compatible input	with CM		CMOS = CMOS compatible input or output		

#### **TABLE 1-6**: PIC18F96J60/96J65/97J60 PINOUT I/O DESCRIPTIONS (CONTINUED)

= Schmitt Trigger input with CMOS levels ST = Input

= Analog input Analog 0

OD

= Output

= Open-Drain (no P diode to VDD)

Note 1: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Extended Microcontroller mode).

2: Default assignment for ECCP2/P2A for all devices in all operating modes (CCP2MX Configuration bit is set).

3: Default assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is set).

4: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (Microcontroller mode).

5: Alternate assignments for P1B/P1C/P3B/P3C (ECCPMX Configuration bit is cleared).

Т

Р

= Power

# 2.0 OSCILLATOR CONFIGURATIONS

### 2.1 Overview

Devices in the PIC18F97J60 family incorporate an oscillator and microcontroller clock system that differs from standard PIC18FXXJXX devices. The addition of the Ethernet module, with its requirement for a stable 25 MHz clock source, makes it necessary to provide a primary oscillator that can provide this frequency as well as a range of different microcontroller clock speeds. An overview of the oscillator structure is shown in Figure 2-1.

Other oscillator features used in PIC18FXXJXX enhanced microcontrollers, such as the internal RC oscillator and clock switching, remain the same. They are discussed later in this chapter.

# 2.2 Oscillator Types

The PIC18F97J60 family of devices can be operated in five different oscillator modes:

- 1. HS High-Speed Crystal/Resonator
- 2. HSPLL High-Speed Crystal/Resonator with Software PLL Control
- 3. EC External Clock with Fosc/4 Output
- 4. ECPLL External Clock with Software PLL Control
- 5. INTRC Internal 31 kHz Oscillator


#### 2.2.1 OSCILLATOR CONTROL

The oscillator mode is selected by programming the FOSC2:FOSC0 Configuration bits. FOSC1:FOSC0 bits select the default primary oscillator modes, while FOSC2 selects when INTRC may be invoked.

The OSCCON register (Register 2-2) selects the Active Clock mode. It is primarily used in controlling clock switching in power-managed modes. Its use is discussed in **Section 2.7.1 "Oscillator Control Register"**.

The OSCTUNE register (Register 2-1) is used to select the system clock frequency from the primary oscillator source by selecting combinations of prescaler/postscaler settings and enabling the PLL. Its use is described in **Section 2.6.1 "PLL Block"**.

#### FIGURE 2-1: PIC18F97J60 FAMILY CLOCK DIAGRAM




## 2.3 Crystal Oscillator/Ceramic Resonators (HS Modes)

In HS or HSPLL Oscillator modes, a crystal is connected to the OSC1 and OSC2 pins to establish oscillation. Figure 2-2 shows the pin connections.

The oscillator design requires the use of a crystal that is rated for parallel resonant operation.

Note:	Use of a crystal rated for series resonant
	operation may give a frequency out of the
	crystal manufacturer's specifications.

#### FIGURE 2-2: CRYSTAL OSCILLATOR OPERATION (HS OR HSPLL CONFIGURATION)



3: RF varies with the oscillator mode chosen.

# TABLE 2-1:CAPACITOR SELECTION FOR<br/>CRYSTAL OSCILLATOR

Osc Type	Crystal Freq.	Typical Capacitor Values Tested:			
	Fled.	C1	C2		
HS	25 MHz	33 pF	33 pF		

Capacitor values are for design guidance only.

Different capacitor values may be required to produce acceptable oscillator operation. The user should test the performance of the oscillator over the expected VDD and temperature range for the application. Refer to the following application notes for oscillator specific information:

- AN588, "PIC<sup>®</sup> Microcontroller Oscillator Design Guide"
- AN826, "Crystal Oscillator Basics and Crystal Selection for rfPIC<sup>®</sup> and PIC<sup>®</sup> Devices"
- AN849, "Basic PIC<sup>®</sup> Oscillator Design"
- AN943, "Practical PIC<sup>®</sup> Oscillator Analysis and Design"
- AN949, "Making Your Oscillator Work"


See the notes following this table for additional information.

- **Note 1:** Higher capacitance increases the stability of the oscillator but also increases the start-up time.
  - 2: Since each crystal has its own characteristics, the user should consult the crystal manufacturer for appropriate values of external components.
  - 3: Rs may be required to avoid overdriving crystals with low drive level specifications.
  - Always verify oscillator performance over the VDD and temperature range that is expected for the application.

# 2.4 External Clock Input (EC Modes)

The EC and ECPLL Oscillator modes require an external clock source to be connected to the OSC1 pin. There is no oscillator start-up time required after a Power-on Reset or after an exit from Sleep mode.


In the EC Oscillator mode, the oscillator frequency divided by 4 is available on the OSC2 pin. This signal may be used for test purposes or to synchronize other logic. Figure 2-3 shows the pin connections for the EC Oscillator mode.



An external clock source may also be connected to the OSC1 pin in the HS mode, as shown in Figure 2-4. In this configuration, the OSC2 pin is left open. Current consumption in this configuration will be somewhat higher than EC mode, as the internal oscillator's feedback circuitry will be enabled (in EC mode, the feedback circuit is disabled).

FIGURE 2-4:

#### EXTERNAL CLOCK INPUT OPERATION (HS CONFIGURATION)



# 2.5 Internal Oscillator Block

The PIC18F97J60 family of devices includes an internal oscillator source (INTRC) which provides a nominal 31 kHz output. The INTRC is enabled on device power-up and clocks the device during its configuration cycle until it enters operating mode. INTRC is also enabled if it is selected as the device clock source or if any of the following are enabled:

- Fail-Safe Clock Monitor
- Watchdog Timer
- Two-Speed Start-up

These features are discussed in greater detail in Section 24.0 "Special Features of the CPU".

The INTRC can also be optionally configured as the default clock source on device start-up by setting the FOSC2 Configuration bit. This is discussed in **Section 2.7.1 "Oscillator Control Register"**.

#### 2.6 Ethernet Operation and the Microcontroller Clock

Although devices of the PIC18F97J60 family can accept a wide range of crystals and external oscillator inputs, they must always have a 25 MHz clock source when used for Ethernet applications. No provision is made for internally generating the required Ethernet clock from a primary oscillator source of a different frequency. A frequency tolerance is specified, likely excluding the use of ceramic resonators. See **Section 27.0 "Electrical Characteristics"**, Table 27-6, parameter 5, for more details.

#### 2.6.1 PLL BLOCK

To accommodate a range of applications and microcontroller clock speeds, a separate PLL block is incorporated into the clock system. It consists of three components:

- A configurable prescaler (1:2 or 1:3)
- A 5x PLL frequency multiplier
- A configurable postscaler (1:1, 1:2, or 1:3)

The operation of the PLL block's components is controlled by the OSCTUNE register (Register 2-1). The use of the PLL block's prescaler and postscaler, with or without the PLL itself, provides a range of system clock frequencies to choose from, including the unaltered 25 MHz of the primary oscillator. The full range of possible oscillator configurations compatible with Ethernet operation is shown in Table 2-2.

#### REGISTER 2-1: OSCTUNE: PLL BLOCK CONTROL REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	U-0	U-0	U-0	U-0
PPST1	PLLEN <sup>(1)</sup>	PPST0	PPRE		—	_	—
bit 7							bit 0
Legend:							
R = Readal	ole bit	W = Writable	bit	U = Unimpler	mented bit, read	l as '0'	
-n = Value a	at POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unk	nown
bit 7	PPST1: PLL	Postscaler Con	figuration bit				
	1 = Divide-by						
	0 = Divide-by						
bit 6	PLLEN: 5x F	PLLEN: 5x Frequency Multiplier PLL Enable bit <sup>(1)</sup>					
	1 = PLL enal						
	0 = PLL disabled						
bit 5	it 5 <b>PPST0:</b> PLL Postscaler Enable bit						
	1 = Postscaler enabled						
	0 = Postscal						
bit 4	PPRE: PLL Prescaler Configuration bit						
	1 = Divide-by-2						
	0 = Divide-by						
bit 3-0	Unimplemen	ited: Read as '	0'				
	Available only for E as '0'.	ECPLL and HSP	PLL oscillator	configurations	otherwise, this	bit is unavailat	ble and is read

© 2007 Microchip Technology Inc.

5x PLL	PLL Prescaler	PLL Postscaler	PLL Block Configuration (OSCTUNE<7:4>)	Clock Frequency (MHz)
		Disabled	x101	(Note 1)
	÷2	÷2	1111	31.2500
Enabled		÷3	0111	20.8333
Enabled		Disabled	x100	41.6667
	÷3	÷2	1110	20.8333
		÷3	0110	13.8889
	Disabled <sup>(2)</sup>	Disabled	x00x	25 (Default)
	÷2	÷2	1011	6.2500
Disabled	÷Ζ	÷3	0011	4.1667
	÷3	÷2	1010	4.1667
	C÷	÷3	0010	2.7778

#### TABLE 2-2: DEVICE CLOCK SPEEDS FOR VARIOUS PLL BLOCK CONFIGURATIONS

Legend: x = Don't care

**Note 1:** Reserved configuration; represents a clock frequency beyond the microcontroller's operating range.

2: The prescaler is automatically disabled when the PLL and postscaler are both disabled.

# 2.7 Clock Sources and Oscillator Switching

The PIC18F97J60 family of devices includes a feature that allows the device clock source to be switched from the main oscillator to an alternate clock source. These devices also offer two alternate clock sources. When an alternate clock source is enabled, the various power-managed operating modes are available.

Essentially, there are three clock sources for these devices:

- · Primary oscillators
- · Secondary oscillators
- Internal oscillator block

The **primary oscillators** include the External Crystal and Resonator modes and the External Clock modes. The particular mode is defined by the FOSC2:FOSC0 Configuration bits. The details of these modes are covered earlier in this chapter. The **secondary oscillators** are those external sources not connected to the OSC1 or OSC2 pins. These sources may continue to operate even after the controller is placed in a power-managed mode. The PIC18F97J60 family of devices offers the Timer1 oscillator as a secondary oscillator. In all power-managed modes, this oscillator is often the time base for functions such as a Real-Time Clock (RTC).

Most often, a 32.768 kHz watch crystal is connected between the RC0/T1OSO/T13CKI and RC1/T1OSI pins. Loading capacitors are also connected from each pin to ground. The Timer1 oscillator is discussed in greater detail in **Section 12.3 "Timer1 Oscillator**".

In addition to being a primary clock source, the **internal oscillator** is available as a power-managed mode clock source. The INTRC source is also used as the clock source for several special features, such as the WDT and Fail-Safe Clock Monitor.

The clock sources for the PIC18F97J60 family devices are shown in Figure 2-1. See **Section 24.0** "**Special Features of the CPU**" for Configuration register details.

# 2.7.1 OSCILLATOR CONTROL REGISTER

The OSCCON register (Register 2-2) controls several aspects of the device clock's operation, both in full power operation and in power-managed modes.

The System Clock Select bits, SCS1:SCS0, select the clock source. The available clock sources are the primary clock (defined by the FOSC2:FOSC0 Configuration bits), the secondary clock (Timer1 oscillator) and the internal oscillator. The clock source changes after one or more of the bits are changed, following a brief clock transition interval.

The OSTS (OSCCON<3>) and T1RUN (T1CON<6>) bits indicate which clock source is currently providing the device clock. The T1RUN bit indicates when the Timer1 oscillator is providing the device clock in secondary clock modes. In power-managed modes, only one of these bits will be set at any time. If neither bit is set, the INTRC source is providing the clock, or the internal oscillator has just started and is not yet stable.

The IDLEN bit determines if the device goes into Sleep mode or one of the Idle modes when the SLEEP instruction is executed.

The use of the flag and control bits in the OSCCON register is discussed in more detail in **Section 3.0** "Power-Managed Modes".

- Note 1: The Timer1 oscillator must be enabled to select the secondary clock source. The Timer1 oscillator is enabled by setting the T1OSCEN bit in the Timer1 Control register (T1CON<3>). If the Timer1 oscillator is not enabled, then any attempt to select a secondary clock source will be ignored.
  - 2: It is recommended that the Timer1 oscillator be operating and stable before executing the SLEEP instruction or a very long delay may occur while the Timer1 oscillator starts.

#### REGISTER 2-2: OSCCON: OSCILLATOR CONTROL REGISTER

R/W-0	U-0	U-0	U-0	R-q	U-0	R/W-0	R/W-0
IDLEN	—	—	—	OSTS <sup>(1)</sup>	_	SCS1	SCS0
bit 7							bit 0

Legend:	q = Value determined by configuration				
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'		
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 7	IDLEN: Idle Enable bit
	1 = Device enters Idle mode on SLEEP instruction
	0 = Device enters Sleep mode on SLEEP instruction
bit 6-4	Unimplemented: Read as '0'
bit 3	<b>OSTS</b> : Oscillator Status bit <sup>(1)</sup>
	<ul> <li>1 = Device is running from oscillator source defined when SCS1:SCS0 = 00</li> <li>0 = Device is running from oscillator source defined when SCS1:SCS0 = 01, 10 or 11</li> </ul>
bit 2	Unimplemented: Read as '0'
bit 1-0	SCS1:SCS0: System Clock Select bits
	11 = Internal oscillator
	10 = Primary oscillator
	01 = Timer1 oscillator
	<u>When FOSC2 = 1:</u>
	00 = Primary oscillator
	<u>When FOSC2 = 0:</u>
	00 = Internal oscillator



# 2.7.1.1 System Clock Selection and the FOSC2 Configuration Bit

The SCS bits are cleared on all forms of Reset. In the device's default configuration, this means the primary oscillator defined by FOSC1:FOSC0 (that is, one of the HC or EC modes) is used as the primary clock source on device Resets.

The default clock configuration on Reset can be changed with the FOSC2 Configuration bit. This bit affects the clock source selection setting when SCS1:SCS0 = 00. When FOSC2 = 1 (default), the oscillator source defined by FOSC1:FOSC0 is selected whenever SCS1:SCS0 = 00. When FOSC2 = 0, the INTRC oscillator is selected whenever SCS1:SCS2 = 00. Because the SCS bits are cleared on Reset, the FOSC2 setting also changes the default oscillator mode on Reset.

Regardless of the setting of FOSC2, INTRC will always be enabled on device power-up. It will serve as the clock source until the device has loaded its configuration values from memory. It is at this point that the FOSC Configuration bits are read and the oscillator selection of operational mode is made.

Note that either the primary clock or the internal oscillator will have two bit setting options, at any given time, depending on the setting of FOSC2.

# 2.7.2 OSCILLATOR TRANSITIONS

PIC18F97J60 family devices contain circuitry to prevent clock "glitches" when switching between clock sources. A short pause in the device clock occurs during the clock switch. The length of this pause is the sum of two cycles of the old clock source and three to four cycles of the new clock source. This formula assumes that the new clock source is stable.

Clock transitions are discussed in greater detail in **Section 3.1.2 "Entering Power-Managed Modes"**.

# 2.8 Effects of Power-Managed Modes on the Various Clock Sources

When PRI\_IDLE mode is selected, the designated primary oscillator continues to run without interruption. For all other power-managed modes, the oscillator using the OSC1 pin is disabled. The OSC1 pin (and OSC2 pin if used by the oscillator) will stop oscillating.

In secondary clock modes (SEC\_RUN and SEC\_IDLE), the Timer1 oscillator is operating and providing the device clock. The Timer1 oscillator may also run in all power-managed modes if required to clock Timer1 or Timer3.

In RC\_RUN and RC\_IDLE modes, the internal oscillator provides the device clock source. The 31 kHz INTRC output can be used directly to provide the clock and may be enabled to support various special features, regardless of the power-managed mode (see **Section 24.2 "Watchdog Timer (WDT)"** through **Section 24.5 "Fail-Safe Clock Monitor**" for more information on WDT, Fail-Safe Clock Monitor and Two-Speed Start-up).

If the Sleep mode is selected, all clock sources are stopped. Since all the transistor switching currents have been stopped, Sleep mode achieves the lowest current consumption of the device (only leakage currents).

Enabling any on-chip feature that will operate during Sleep will increase the current consumed during Sleep. The INTRC is required to support WDT operation. The Timer1 oscillator may be operating to support a Real-Time Clock. Other features may be operating that do not require a device clock source (i.e., MSSP slave, PSP, INTx pins and others). Peripherals that may add significant current consumption are listed in Section 27.2 "DC Characteristics: Power-Down and Supply Current".

# 2.9 Power-up Delays

Power-up delays are controlled by two timers, so that no external Reset circuitry is required for most applications. The delays ensure that the device is kept in Reset until the device power supply is stable under normal circumstances and the primary clock is operating and stable. For additional information on power-up delays, see **Section 4.6 "Power-up Timer (PWRT)**".

The first timer is the Power-up Timer (PWRT), which provides a fixed delay on power-up (parameter 33, Table 27-12); it is always enabled.

The second timer is the Oscillator Start-up Timer (OST), intended to keep the chip in Reset until the crystal oscillator is stable (HS modes). The OST does this by counting 1024 oscillator cycles before allowing the oscillator to clock the device.

There is a delay of interval TCSD (parameter 38, Table 27-12), following POR, while the controller becomes ready to execute instructions.

Oscillator Mode	OSC1 Pin	OSC2 Pin
EC, ECPLL	Floating, pulled by external clock	At logic low (clock/4 output)
,	Feedback inverter disabled at quiescent voltage level	Feedback inverter disabled at quiescent voltage level

TABLE 2-3:OSC1 AND OSC2 PIN STATES IN SLEEP MODE

Note: See Table 4-2 in Section 4.0 "Reset" for time-outs due to Sleep and MCLR Reset.

# 3.0 POWER-MANAGED MODES

The PIC18F97J60 family devices provide the ability to manage power consumption by simply managing clocking to the CPU and the peripherals. In general, a lower clock frequency and a reduction in the number of circuits being clocked constitutes lower consumed power. For the sake of managing power in an application, there are three primary modes of operation:

- Run mode
- Idle mode
- · Sleep mode

These modes define which portions of the device are clocked and at what speed. The Run and Idle modes may use any of the three available clock sources (primary, secondary or internal oscillator block); the Sleep mode does not use a clock source.

The power-managed modes include several power-saving features offered on previous PIC<sup>®</sup> MCU devices. One is the clock switching feature, offered in other PIC18 devices, allowing the controller to use the Timer1 oscillator in place of the primary oscillator. Also included is the Sleep mode, offered by all PIC MCU devices, where all device clocks are stopped.

# 3.1 Selecting Power-Managed Modes

Selecting a power-managed mode requires two decisions: if the CPU is to be clocked or not and which clock source is to be used. The IDLEN bit (OSCCON<7>) controls CPU clocking, while the SCS1:SCS0 bits (OSCCON<1:0>) select the clock source. The individual modes, bit settings, clock sources and affected modules are summarized in Table 3-1.

# 3.1.1 CLOCK SOURCES

The SCS1:SCS0 bits allow the selection of one of three clock sources for power-managed modes. They are:

- The primary clock, as defined by the FOSC2:FOSC0 Configuration bits
- The secondary clock (Timer1 oscillator)
- The internal oscillator

#### 3.1.2 ENTERING POWER-MANAGED MODES

Switching from one power-managed mode to another begins by loading the OSCCON register. The SCS1:SCS0 bits select the clock source and determine which Run or Idle mode is to be used. Changing these bits causes an immediate switch to the new clock source, assuming that it is running. The switch may also be subject to clock transition delays. These are discussed in **Section 3.1.3 "Clock Transitions and Status Indicators"** and subsequent sections.

Entry to the power-managed Idle or Sleep modes is triggered by the execution of a SLEEP instruction. The actual mode that results depends on the status of the IDLEN bit.

Depending on the current mode and the mode being switched to, a change to a power-managed mode does not always require setting all of these bits. Many transitions may be done by changing the oscillator select bits, or changing the IDLEN bit, prior to issuing a SLEEP instruction. If the IDLEN bit is already configured correctly, it may only be necessary to perform a SLEEP instruction to switch to the desired mode.

	osco	CON<7,1:0>	Modul	e Clocking	
Mode	IDLEN <sup>(1)</sup>	SCS1:SCS0	CPU	Peripherals	Available Clock and Oscillator Source
Sleep	0	N/A	Off	Off	None – All clocks are disabled
PRI_RUN	N/A	10	Clocked	Clocked	Primary – HS, EC, HSPLL, ECPLL; this is the normal, full power execution mode
SEC_RUN	N/A	01	Clocked	Clocked	Secondary – Timer1 Oscillator
RC_RUN	N/A	11	Clocked	Clocked	Internal Oscillator
PRI_IDLE	1	10	Off	Clocked	Primary – HS, EC, HSPLL, ECPLL
SEC_IDLE	1	01	Off	Clocked	Secondary – Timer1 Oscillator
RC_IDLE	1	11	Off	Clocked	Internal Oscillator

TABLE 3-1: POWER-MANAGED MODES

**Note 1:** IDLEN reflects its value when the **SLEEP** instruction is executed.

# 3.1.3 CLOCK TRANSITIONS AND STATUS INDICATORS

The length of the transition between clock sources is the sum of two cycles of the old clock source and three to four cycles of the new clock source. This formula assumes that the new clock source is stable.

Two bits indicate the current clock source and its status: OSTS (OSCCON<3>) and T1RUN (T1CON<6>). In general, only one of these bits will be set while in a given power-managed mode. When the OSTS bit is set, the primary clock is providing the device clock. When the T1RUN bit is set, the Timer1 oscillator is providing the clock. If neither of these bits is set, INTRC is clocking the device.

Note: Executing a SLEEP instruction does not necessarily place the device into Sleep mode. It acts as the trigger to place the controller into either the Sleep mode, or one of the Idle modes, depending on the setting of the IDLEN bit.

#### 3.1.4 MULTIPLE SLEEP COMMANDS

The power-managed mode that is invoked with the SLEEP instruction is determined by the setting of the IDLEN bit at the time the instruction is executed. If another SLEEP instruction is executed, the device will enter the power-managed mode specified by IDLEN at that time. If IDLEN has changed, the device will enter the new power-managed mode specified by the new setting.

#### 3.2 Run Modes

In the Run modes, clocks to both the core and peripherals are active. The difference between these modes is the clock source.

#### 3.2.1 PRI\_RUN MODE

The PRI\_RUN mode is the normal, full power execution mode of the microcontroller. This is also the default mode upon a device Reset unless Two-Speed Start-up is enabled (see **Section 24.4 "Two-Speed Start-up"** for details). In this mode, the OSTS bit is set. (see **Section 2.7.1 "Oscillator Control Register"**).


# 3.2.2 SEC\_RUN MODE


The SEC\_RUN mode is the compatible mode to the "clock switching" feature offered in other PIC18 devices. In this mode, the CPU and peripherals are clocked from the Timer1 oscillator. This gives users the option of lower power consumption while still using a high accuracy clock source.

SEC\_RUN mode is entered by setting the SCS1:SCS0 bits to '01'. The device clock source is switched to the Timer1 oscillator (see Figure 3-1), the primary oscillator is shut down, the T1RUN bit (T1CON<6>) is set and the OSTS bit is cleared.

Note: The Timer1 oscillator should already be running prior to entering SEC\_RUN mode. If the T1OSCEN bit is not set when the SCS1:SCS0 bits are set to '01', entry to SEC\_RUN mode will not occur. If the Timer1 oscillator is enabled, but not yet running, device clocks will be delayed until the oscillator has started. In such situations, initial oscillator operation is far from stable and unpredictable operation may result.

On transitions from SEC\_RUN mode to PRI\_RUN, the peripherals and CPU continue to be clocked from the Timer1 oscillator while the primary clock is started. When the primary clock becomes ready, a clock switch back to the primary clock occurs (see Figure 3-2). When the clock switch is complete, the T1RUN bit is cleared, the OSTS bit is set and the primary clock is providing the clock. The IDLEN and SCS bits are not affected by the wake-up; the Timer1 oscillator continues to run.






# 3.2.3 RC\_RUN MODE

In RC\_RUN mode, the CPU and peripherals are clocked from the internal oscillator; the primary clock is shut down. This mode provides the best power conservation of all the Run modes while still executing code. It works well for user applications which are not highly timing sensitive or do not require high-speed clocks at all times.


This mode is entered by setting SCS<1:0> to '11'. When the clock source is switched to the INTRC (see Figure 3-3), the primary oscillator is shut down and the OSTS bit is cleared.

On transitions from RC\_RUN mode to PRI\_RUN mode, the device continues to be clocked from the INTRC while the primary clock is started. When the primary clock becomes ready, a clock switch to the primary clock occurs (see Figure 3-4). When the clock switch is complete, the OSTS bit is set and the primary clock is providing the device clock. The IDLEN and SCS bits are not affected by the switch. The INTRC source will continue to run if either the WDT or Fail-Safe Clock Monitor is enabled.





#### FIGURE 3-4: TRANSITION TIMING FROM RC RUN MODE TO PRI RUN MODE



# 3.3 Sleep Mode

The power-managed Sleep mode is identical to the legacy Sleep mode offered in all other PIC MCU devices. It is entered by clearing the IDLEN bit (the default state on device Reset) and executing the SLEEP instruction. This shuts down the selected oscillator (Figure 3-5). All clock source status bits are cleared.

Entering the Sleep mode from any other mode does not require a clock switch. This is because no clocks are needed once the controller has entered Sleep. If the WDT is selected, the INTRC source will continue to operate. If the Timer1 oscillator is enabled, it will also continue to run.

When a wake event occurs in Sleep mode (by interrupt, Reset or WDT time-out), the device will not be clocked until the clock source selected by the SCS1:SCS0 bits becomes ready (see Figure 3-6), or it will be clocked from the internal oscillator if either the Two-Speed Start-up or the Fail-Safe Clock Monitor is enabled (see **Section 24.0 "Special Features of the CPU"**). In either case, the OSTS bit is set when the primary clock is providing the device clocks. The IDLEN and SCS bits are not affected by the wake-up.

#### 3.4 Idle Modes

The Idle modes allow the controller's CPU to be selectively shut down while the peripherals continue to operate. Selecting a particular Idle mode allows users to further manage power consumption.


If the IDLEN bit is set to '1' when a SLEEP instruction is executed, the peripherals will be clocked from the clock source selected using the SCS1:SCS0 bits; however, the CPU will not be clocked. The clock source status bits are not affected. Setting IDLEN and executing a SLEEP instruction provides a quick method of switching from a given Run mode to its corresponding Idle mode.

If the WDT is selected, the INTRC source will continue to operate. If the Timer1 oscillator is enabled, it will also continue to run.


Since the CPU is not executing instructions, the only exits from any of the Idle modes are by interrupt, WDT time-out or a Reset. When a wake event occurs, CPU execution is delayed by an interval of TCsD (parameter 38, Table 27-12) while it becomes ready to execute code. When the CPU begins executing code, it resumes with the same clock source for the current Idle mode. For example, when waking from RC\_IDLE mode, the internal oscillator block will clock the CPU and peripherals (in other words, RC\_RUN mode). The IDLEN and SCS bits are not affected by the wake-up.

While in any Idle mode or the Sleep mode, a WDT time-out will result in a WDT wake-up to the Run mode currently specified by the SCS1:SCS0 bits.

#### FIGURE 3-5: TRANSITION TIMING FOR ENTRY TO SLEEP MODE







# 3.4.1 PRI\_IDLE MODE

This mode is unique among the three low-power Idle modes in that it does not disable the primary device clock. For timing sensitive applications, this allows for the fastest resumption of device operation with its more accurate primary clock source, since the clock source does not have to "warm up" or transition from another oscillator.

PRI\_IDLE mode is entered from PRI\_RUN mode by setting the IDLEN bit and executing a SLEEP instruction. If the device is in another Run mode, set IDLEN first, then set the SCS<1:0> bits to '10' and execute SLEEP. Although the CPU is disabled, the peripherals continue to be clocked from the primary clock source specified by the FOSC1:FOSC0 Configuration bits. The OSTS bit remains set (see Figure 3-7).

When a wake event occurs, the CPU is clocked from the primary clock source. A delay of interval TCSD is required between the wake event and when code execution starts. This is required to allow the CPU to become ready to execute instructions. After the wake-up, the OSTS bit remains set. The IDLEN and SCS bits are not affected by the wake-up (see Figure 3-8).


# 3.4.2 SEC\_IDLE MODE

In SEC\_IDLE mode, the CPU is disabled but the peripherals continue to be clocked from the Timer1 oscillator. This mode is entered from SEC\_RUN by setting the IDLEN bit and executing a SLEEP instruction. If the device is in another Run mode, set IDLEN first, then set SCS<1:0> to '01' and execute SLEEP. When the clock source is switched to the Timer1 oscillator, the primary oscillator is shut down, the OSTS bit is cleared and the T1RUN bit is set.


When a wake event occurs, the peripherals continue to be clocked from the Timer1 oscillator. After an interval of TCSD following the wake event, the CPU begins executing code being clocked by the Timer1 oscillator. The IDLEN and SCS bits are not affected by the wake-up; the Timer1 oscillator continues to run (see Figure 3-8).

Note: The Timer1 oscillator should already be running prior to entering SEC\_IDLE mode. If the T1OSCEN bit is not set when the SLEEP instruction is executed, the SLEEP instruction will be ignored and entry to SEC\_IDLE mode will not occur. If the Timer1 oscillator is enabled, but not yet running, peripheral clocks will be delayed until the oscillator has started. In such situations, initial oscillator operation is far from stable and unpredictable operation may result.

#### FIGURE 3-7: TRANSITION TIMING FOR ENTRY TO IDLE MODE



#### FIGURE 3-8: TRANSITION TIMING FOR WAKE FROM IDLE TO RUN MODE



# 3.4.3 RC\_IDLE MODE

In RC\_IDLE mode, the CPU is disabled but the peripherals continue to be clocked from the internal oscillator. This mode allows for controllable power conservation during Idle periods.

From RC\_RUN mode, RC\_IDLE mode is entered by setting the IDLEN bit and executing a SLEEP instruction. If the device is in another Run mode, first set IDLEN, then clear the SCS bits and execute SLEEP. When the clock source is switched to the INTRC, the primary oscillator is shut down and the OSTS bit is cleared.

When a wake event occurs, the peripherals continue to be clocked from the INTRC. After a delay of TCSD following the wake event, the CPU begins executing code being clocked by the INTRC. The IDLEN and SCS bits are not affected by the wake-up. The INTRC source will continue to run if either the WDT or the Fail-Safe Clock Monitor is enabled.

# 3.5 Exiting Idle and Sleep Modes

An exit from Sleep mode, or any of the Idle modes, is triggered by an interrupt, a Reset or a WDT time-out. This section discusses the triggers that cause exits from power-managed modes. The clocking subsystem actions are discussed in each of the power-managed modes sections (see Section 3.2 "Run Modes", Section 3.3 "Sleep Mode" and Section 3.4 "Idle Modes").

#### 3.5.1 EXIT BY INTERRUPT

Any of the available interrupt sources can cause the device to exit from an Idle mode, or the Sleep mode, to a Run mode. To enable this functionality, an interrupt source must be enabled by setting its enable bit in one of the INTCON or PIE registers. The exit sequence is initiated when the corresponding interrupt flag bit is set.

On all exits from Idle or Sleep modes by interrupt, code execution branches to the interrupt vector if the GIE/GIEH bit (INTCON<7>) is set. Otherwise, code execution continues or resumes without branching (see Section 9.0 "Interrupts").

A fixed delay of interval TCSD following the wake event is required when leaving the Sleep and Idle modes. This delay is required for the CPU to prepare for execution. Instruction execution resumes on the first clock cycle following this delay.

## 3.5.2 EXIT BY WDT TIME-OUT

A WDT time-out will cause different actions depending on which power-managed mode the device is in when the time-out occurs.

If the device is not executing code (all Idle modes and Sleep mode), the time-out will result in an exit from the power-managed mode (see Section 3.2 "Run Modes" and Section 3.3 "Sleep Mode"). If the device is executing code (all Run modes), the time-out will result in a WDT Reset (see Section 24.2 "Watchdog Timer (WDT)").

The WDT timer and postscaler are cleared by one of the following events:

- Executing a SLEEP or CLRWDT instruction
- The loss of a currently selected clock source (if the Fail-Safe Clock Monitor is enabled)

3.5.3 EXIT BY RESET

Exiting an Idle or Sleep mode by Reset automatically forces the device to run from the INTRC.

#### 3.5.4 EXIT WITHOUT AN OSCILLATOR START-UP TIMER DELAY

Certain exits from power-managed modes do not invoke the OST at all. There are two cases:

- PRI\_IDLE mode, where the primary clock source is not stopped
- The primary clock source is either the EC or ECPLL mode

In these instances, the primary clock source either does not require an oscillator start-up delay since it is already running (PRI\_IDLE), or normally does not require an oscillator start-up delay (EC). However, a fixed delay of interval TCSD following the wake event is still required when leaving the Sleep and Idle modes to allow the CPU to prepare for execution. Instruction execution resumes on the first clock cycle following this delay.

NOTES:

# 4.0 RESET

The PIC18F97J60 family of devices differentiates between various kinds of Reset:

- a) MCLR Reset during normal operation
- b) MCLR Reset during power-managed modes
- c) Power-on Reset (POR)
- d) Brown-out Reset (BOR)
- e) Configuration Mismatch (CM)
- f) RESET Instruction
- g) Stack Full Reset
- h) Stack Underflow Reset
- i) Watchdog Timer (WDT) Reset during execution


This section discusses Resets generated by hard events (MCLR), power events (POR and BOR) and Configuration Mismatches (CM). It also covers the operation of the various start-up timers. Stack Reset events are covered in **Section 5.1.6.4 "Stack Full and Underflow Resets**". WDT Resets are covered in **Section 24.2 "Watchdog Timer (WDT)**". A simplified block diagram of the on-chip Reset circuit is shown in Figure 4-1.

# 4.1 RCON Register

Device Reset events are tracked through the RCON register (Register 4-1). The lower six bits of the register indicate that a specific Reset event has occurred. In most cases, these bits can only be set by the event and must be cleared by the application after the event. The state of these flag bits, taken together, can be read to indicate the type of Reset that just occurred. This is described in more detail in **Section 4.7** "**Reset State of Registers**".

The RCON register also has a control bit for setting interrupt priority (IPEN). Interrupt priority is discussed in **Section 9.0 "Interrupts"**.

# FIGURE 4-1: SIMPLIFIED BLOCK DIAGRAM OF ON-CHIP RESET CIRCUIT



R/W-0	U-0	R/W-1	R/W-1	R-1	R-1	R/W-0	R/W-0
IPEN	_	CM	RI	TO	PD	POR	BOR
bit 7							bit 0
Legend:			L :4			-l (0)	
R = Readabl -n = Value at		W = Writable '1' = Bit is se		0 = Unimpler '0' = Bit is cle	mented bit, rea	a as '0 x = Bit is unkr	2011/2
	FUR	I - DILISSE			aleu	X – DIL IS ULIKI	IOWII
bit 7	IPEN: Interrup	ot Priority Enal	ble bit				
	1 = Enable pri	iority levels on	interrupts	IC16CXXX Co	mpatibility mod	e)	
bit 6	Unimplement	ted: Read as	0'				
bit 5	CM: Configura		-				
	1 = A Configu					(i	<b>C</b>
		Reset occurs		occurred (mus	t de set in sott	ware after a Cor	itiguration
bit 4	RI: RESET INS		,				
				uted (set by firm			
		ET instruction It Reset occur		d causing a de	vice Reset (m	ust be set in so	oftware after a
bit 3	TO: Watchdog	g Timer Time-o	out Flag bit				
	1 = Set by po 0 = A WDT ti			or SLEEP instr	uction		
bit 2	PD: Power-Do	own Detection	Flag bit				
	1 = Set by po 0 = Set by ex						
bit 1	POR: Power-o	on Reset Statu	us bit				
				(set by firmware			
bit 0	0 = A Power-			e set in software	e atter a Power	-on Reset occu	rs)
				(set by firmwar	e only)		
						n-out Reset occ	urs)
			-				
	t is recommended Power-on Resets			er a Power-on I	Reset has beer	n detected so th	at subsequent
	f the on-chip volta <b>BOR</b> " for more int		is disabled, B	OR remains '0	' at all times. S	See Section 4.4	.1 "Detecting
	Brown-out Reset i 1' by software imi				nd POR is '1' (a	assuming that $\overline{P}$	OR was set to

# REGISTER 4-1: RCON: RESET CONTROL REGISTER

# 4.2 Master Clear (MCLR)

The MCLR pin provides a method for triggering a hard external Reset of the device. A Reset is generated by holding the pin low. PIC18 extended microcontroller devices have a noise filter in the MCLR Reset path which detects and ignores small pulses.

The  $\overline{\text{MCLR}}$  pin is not driven low by any internal Resets, including the WDT.

# 4.3 Power-on Reset (POR)

A Power-on Reset condition is generated on-chip whenever VDD rises above a certain threshold. This allows the device to start in the initialized state when VDD is adequate for operation.

To take advantage of the POR circuitry, tie the  $\overline{\text{MCLR}}$  pin through a resistor (1 k $\Omega$  to 10 k $\Omega$ ) to VDD. This will eliminate external RC components usually needed to create a Power-on Reset delay. A minimum rise rate for VDD is specified (parameter D004). For a slow rise time, see Figure 4-2.

When the device starts normal operation (i.e., exits the Reset condition), device operating parameters (voltage, frequency, temperature, etc.) must be met to ensure operation. If these conditions are not met, the device must be held in Reset until the operating conditions are met.

POR events are captured by the POR bit (RCON<1>). The state of the bit is set to '0' whenever a Power-on Reset occurs; it does not change for any other Reset event. POR is not reset to '1' by any hardware event. To capture multiple events, the user manually resets the bit to '1' in software following any Power-on Reset.


# 4.4 Brown-out Reset (BOR)

The PIC18F97J60 family of devices incorporates a simple BOR function when the internal regulator is enabled (ENVREG pin is tied to VDD). Any drop of VDD below VBOR (parameter D005), for greater than time TBOR (parameter 35), will reset the device. A Reset may or may not occur if VDD falls below VBOR for less than TBOR. The chip will remain in Brown-out Reset until VDD rises above VBOR.

Once a BOR has occurred, the Power-up Timer will keep the chip in Reset for TPWRT (parameter 33). If VDD drops below VBOR while the Power-up Timer is running, the chip will go back into a Brown-out Reset and the Power-up Timer will be initialized. Once VDD rises above VBOR, the Power-up Timer will execute the additional time delay.

#### FIGURE 4-2:

#### EXTERNAL POWER-ON RESET CIRCUIT (FOR SLOW VDD POWER-UP)



- Note 1: External Power-on Reset circuit is required only if the VDD power-up slope is too slow. The diode D helps discharge the capacitor quickly when VDD powers down.
  - **2:**  $R < 40 \text{ k}\Omega$  is recommended to make sure that the voltage drop across R does not violate the device's electrical specification.
  - 3:  $R1 \ge 1 \ k\Omega$  will limit any current flowing into  $\overline{\text{MCLR}}$  from external capacitor C in the event of  $\overline{\text{MCLR}}/\text{VPP}$  pin breakdown, due to Electrostatic Discharge (ESD), or Electrical Overstress (EOS).

# 4.4.1 DETECTING BOR

The BOR bit always resets to '0' on any Brown-out Reset or Power-on Reset event. This makes it difficult to determine if a Brown-out Reset event has occurred just by reading the state of BOR alone. A more reliable method is to simultaneously check the state of both POR and BOR. This assumes that the POR bit is reset to '1' in software immediately after any Power-on Reset event. If BOR is '0' while POR is '1', it can be reliably assumed that a Brown-out Reset event has occurred.

If the voltage regulator is disabled, Brown-out Reset functionality is disabled. In this case, the  $\overline{\text{BOR}}$  bit cannot be used to determine a Brown-out Reset event. The  $\overline{\text{BOR}}$  bit is still cleared by a Power-on Reset event.

# 4.5 Configuration Mismatch (CM)

The Configuration Mismatch (CM) Reset is designed to detect and attempt to recover from random, memory corrupting events. These include Electrostatic Discharge (ESD) events which can cause widespread single-bit changes throughout the device and result in catastrophic failure.

In PIC18FXXJ Flash devices, the device Configuration registers (located in the configuration memory space) are continuously monitored during operation by comparing their values to complimentary shadow registers. If a mismatch is detected between the two sets of registers, a CM Reset automatically occurs. These events are captured by the  $\overline{CM}$  bit (RCON<5>). The state of the bit is set to '0' whenever a CM event occurs; it does not change for any other Reset event.

A CM Reset behaves similarly to a Master Clear Reset, RESET instruction, WDT time-out or Stack Event Reset. As with all hard and power Reset events, the device Configuration Words are reloaded from the Flash Configuration Words in program memory as the device restarts.

# 4.6 **Power-up Timer (PWRT)**


PIC18F97J60 family of devices incorporates an on-chip Power-up Timer (PWRT) to help regulate the Power-on Reset process. The PWRT is always enabled. The main function is to ensure that the device voltage is stable before code is executed.

The Power-up Timer (PWRT) of the PIC18F97J60 family devices is an 11-bit counter which uses the INTRC source as the clock input. This yields an approximate time interval of 2048 x 32  $\mu$ s = 66 ms. While the PWRT is counting, the device is held in Reset. The power-up time delay depends on the INTRC clock and will vary from chip-to-chip due to temperature and process variation. See DC parameter 33 for details.

#### 4.6.1 TIME-OUT SEQUENCE


The PWRT time-out is invoked after the POR pulse has cleared. The total time-out will vary based on the status of the PWRT. Figure 4-3, Figure 4-4, Figure 4-5 and Figure 4-6 all depict time-out sequences on power-up.


Since the time-outs occur from the POR pulse, if MCLR is kept low long enough, the PWRT will expire. Bringing MCLR high will begin execution immediately (Figure 4-5). This is useful for testing purposes or to synchronize more than one PIC18FXXJ6X device operating in parallel.




#### FIGURE 4-3: TIME-OUT SEQUENCE ON POWER-UP (MCLR TIED TO VDD, VDD RISE < TPWRT)

#### FIGURE 4-4: TIME-OUT SEQUENCE ON POWER-UP (MCLR NOT TIED TO VDD): CASE 1





# FIGURE 4-6: SLOW RISE TIME (MCLR TIED TO VDD, VDD RISE > TPWRT)



# 4.7 Reset State of Registers

Most registers are unaffected by a Reset. Their status is unknown on POR and unchanged by all other Resets. The other registers are forced to a "Reset state" depending on the type of Reset that occurred.

Most registers are not affected by a WDT wake-up since this is viewed as the resumption of normal operation. Status bits from the RCON register (CM, RI,

TO, PD, POR and BOR) are set or cleared differently in different Reset situations, as indicated in Table 4-1. These bits are used in software to determine the nature of the Reset.

Table 4-2 describes the Reset states for all of the Special Function Registers. These are categorized by Power-on and Brown-out Resets, Master Clear and WDT Resets and WDT wake-ups.

TABLE 4-1:	STATUS BITS, THEIR SIGNIFICANCE AND THE INITIALIZATION CONDITION FOR
	RCON REGISTER

0	Program			RCON	Registe	r		STKPTR	Register
Condition	Counter <sup>(1)</sup>	СМ	RI	то	PD	POR	BOR	STKFUL	STKUNF
Power-on Reset	0000h	1	1	1	1	0	0	0	0
RESET Instruction	0000h	u	0	u	u	u	u	u	u
Brown-out Reset	0000h	1	1	1	1	u	0	u	u
Configuration Mismatch Reset	0000h	0	u	u	u	u	u	u	u
MCLR during power-managed Run modes	0000h	u	u	1	u	u	u	u	u
MCLR during power-managed Idle modes and Sleep mode	0000h	u	u	1	0	u	u	u	u
MCLR during full power execution	0000h	u	u	u	u	u	u	u	u
Stack Full Reset (STVREN = 1)	0000h	u	u	u	u	u	u	1	u
Stack Underflow Reset (STVREN = 1)	0000h	u	u	u	u	u	u	u	1
Stack Underflow Error (not an actual Reset, STVREN = 0)	0000h	u	u	u	u	u	u	u	1
WDT time-out during full power or power-managed Run modes	0000h	u	u	0	u	u	u	u	u
WDT time-out during power-managed Idle or Sleep modes	PC + 2	u	u	0	0	u	u	u	u
Interrupt exit from power-managed modes	PC + 2	u	u	u	0	u	u	u	u

**Legend:** u = unchanged

**Note 1:** When the wake-up is due to an interrupt, and the GIEH or GIEL bit is set, the PC is loaded with the interrupt vector (0008h or 0018h).

Register	А	pplicable Device	es	Power-on Reset, Brown-out Reset	MCLR Reset, WDT Reset, RESET Instruction, Stack Resets, CM Reset	Wake-up via WDT or Interrupt
TOSU	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	0 uuuu <b>(1)</b>
TOSH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu <b>(1)</b>
TOSL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu <b>(1)</b>
STKPTR	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	00-0 0000	uu-0 0000	uu-u uuuu <b>(1)</b>
PCLATU	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
PCLATH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
PCL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	PC + 2 <sup>(2)</sup>
TBLPTRU	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	00 0000	00 0000	uu uuuu
TBLPTRH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
TBLPTRL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
TABLAT	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
PRODH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	uuuu uuuu
PRODL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
INTCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 000x	0000 000u	uuuu uuuu <b>(3)</b>
INTCON2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	uuuu uuuu <b>(3)</b>
INTCON3	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1100 0000	1100 0000	uuuu uuuu <b>(3)</b>
INDF0	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
POSTINC0	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
POSTDEC0	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
PREINC0	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
PLUSW0	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
FSR0H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xxxx	uuuu	uuuu
FSR0L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
WREG	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
INDF1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
POSTINC1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
POSTDEC1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
PREINC1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
PLUSW1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
FSR1H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xxxx	uuuu	uuuu
FSR1L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	uuuu uuuu
BSR	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000	0000	uuuu
INDF2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
POSTINC2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
POSTDEC2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
PREINC2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
PLUSW2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	N/A	N/A	N/A
FSR2H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xxxx	uuuu	uuuu
FSR2L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս

TABLE 4-2:	INITIALIZATION CONDITIONS FOR ALL REGISTERS

**Legend:** u = unchanged, x = unknown, - = unimplemented bit, read as '0', q = value depends on condition. Shaded cells indicate conditions do not apply for the designated device.

**Note 1:** When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the TOSU, TOSH and TOSL are updated with the current value of the PC. The STKPTR is modified to point to the next location in the hardware stack.

2: When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the PC is loaded with the interrupt vector (0008h or 0018h).

3: One or more bits in the INTCONx or PIRx registers will be affected (to cause wake-up).

Register	A	pplicable Device	95	Power-on Reset, Brown-out Reset	MCLR Reset, WDT Reset, RESET Instruction, St <u>ack</u> Resets, CM Reset	Wake-up via WDT or Interrupt
STATUS	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x xxxx	u uuuu	u uuuu
TMR0H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
TMR0L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
TOCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս
OSCCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 q-00	0 q-00	u q-uu
ECON1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 00	0000 00	uuuu uu
WDTCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0	0	u
RCON <sup>(4)</sup>	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0-q1 1100	0-uq qquu	u-uu qquu
TMR1H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	սսսս սսսս	սսսս սսսս
TMR1L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	սսսս սսսս	นนนน นนนน
T1CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	u0uu uuuu	սսսս սսսս
TMR2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
PR2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	1111 1111
T2CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-000 0000	-000 0000	-uuu uuuu
SSP1BUF	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	uuuu uuuu
SSP1ADD	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
SSP1STAT	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
SSP1CON1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
SSP1CON2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
ADRESH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
ADRESL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
ADCON0	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0-00 0000	0-00 0000	u-uu uuuu
ADCON1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	00 0000	00 0000	uu uuuu
ADCON2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0-00 0000	0-00 0000	u-uu uuuu
CCPR1H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
CCPR1L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
CCP1CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
CCPR2H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
CCPR2L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
CCP2CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
CCPR3H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	սսսս սսսս	սսսս սսսս
CCPR3L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
CCP3CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
ECCP1AS	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
CVRCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
CMCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0111	0000 0111	นนนน นนนน
TMR3H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	นนนน นนนน
TMR3L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս

#### TABLE 4-2: INITIALIZATION CONDITIONS FOR ALL REGISTERS (CONTINUED)

**Legend:** u = unchanged, x = unknown, - = unimplemented bit, read as '0', q = value depends on condition. Shaded cells indicate conditions do not apply for the designated device.

**Note 1:** When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the TOSU, TOSH and TOSL are updated with the current value of the PC. The STKPTR is modified to point to the next location in the hardware stack.

2: When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the PC is loaded with the interrupt vector (0008h or 0018h).

3: One or more bits in the INTCONx or PIRx registers will be affected (to cause wake-up).

Register	er Applicable Devices		Applicable Devic		95	Power-on Reset, Brown-out Reset	MCLR Reset, WDT Reset, RESET Instruction, St <u>ack</u> Resets, CM Reset	Wake-up via WDT or Interrupt
T3CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	սսսս սսսս	սսսս սսսս		
PSPCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000	0000	uuuu		
SPBRG1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս		
RCREG1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս		
TXREG1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	սսսս սսսս	սսսս սսսս		
TXSTA1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0010	0000 0010	սսսս սսսս		
RCSTA1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x000 0000x	0000 000x	սսսս սսսս		
EECON2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X					
EECON1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 x00-	0 x00-	u uuu-		
IPR3	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
PIR3	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu <sup>(3)</sup>		
PIE3	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս		
IPR2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1-11	1111 1-11	uuuu u-uu		
PIR2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0-00	0000 0-00	uuuu u-uu <sup>(3)</sup>		
PIE2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0-00	0000 0-00	uuuu u-uu		
IPR1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	uuuu uuuu		
PIR1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu <sup>(3)</sup>		
PIE1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս		
MEMCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0-0000	0-0000	u-uuuu		
OSCTUNE	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000	0000	uuuu		
TRISJ	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	11	11	uu		
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
TRISH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
TRISG	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1	1	u		
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1 1111	1 1111	u uuuu		
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
TRISF	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 111-	1111 111-	uuuu uuu-		
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
TRISE	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	11 1111	11 1111	uu uuuu		
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
TRISD	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	111	111	uuu		
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
TRISC	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
TRISB	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս		
TRISA	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	11 1111	11 1111	uu uuuu		
LATJ	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xx	uu	uu		
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս		
LATH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս		

### TABLE 4-2: INITIALIZATION CONDITIONS FOR ALL REGISTERS (CONTINUED)

Legend: u = unchanged, x = unknown, - = unimplemented bit, read as '0', q = value depends on condition.

Shaded cells indicate conditions do not apply for the designated device.

**Note 1:** When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the TOSU, TOSH and TOSL are updated with the current value of the PC. The STKPTR is modified to point to the next location in the hardware stack.

2: When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the PC is loaded with the interrupt vector (0008h or 0018h).

3: One or more bits in the INTCONx or PIRx registers will be affected (to cause wake-up).

Register	A	pplicable Device	95	Power-on Reset, Brown-out Reset	MCLR Reset, WDT Reset, RESET Instruction, St <u>ack</u> Resets, CM Reset	Wake-up via WDT or Interrupt
LATG	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x	u	u
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x xxxx	u uuuu	u uuuu
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
LATF	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXX-	uuuu uuu-	uuuu uuu-
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
LATE	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xx xxxx	uu uuuu	uu uuuu
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
LATD	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xxx	uuu	uuu
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
LATC	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
LATB	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
LATA	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	00xx xxxx	00uu uuuu	սսսս սսսս
PORTJ	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xx	uu	uu
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
PORTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
PORTG	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x	u	u
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x xxxx	u uuuu	u uuuu
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	111x xxxx	111u uuuu	սսսս սսսս
PORTF	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x000 000-	x000 000-	uuuu uuu-
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x000 000-	x000 000-	uuuu uuu-
PORTE	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xx xxxx	uu uuuu	uu uuuu
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	uuuu uuuu
PORTD	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	xxx	uuu	uuu
	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	սսսս սսսս	սսսս սսսս
PORTC	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	սսսս սսսս
PORTB	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	սսսս սսսս	սսսս սսսս
PORTA	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0-0x 0000	0-0u 0000	u-uu uuuu
SPBRGH1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
BAUDCON1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0100 0-00	0100 0-00	uuuu u-uu
SPBRGH2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
BAUDCON2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0100 0-00	0100 0-00	uuuu u-uu
ERDPTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 1010	0 1010	u uuuu
ERDPTL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 0101	1111 0101	սսսս սսսս
ECCP1DEL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
TMR4	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
PR4	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	1111 1111
T4CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-000 0000	-000 0000	-uuu uuuu
CCPR4H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	սսսս սսսս	սսսս սսսս
CCPR4L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	սսսս սսսս	սսսս սսսս

#### TABLE 4-2: INITIALIZATION CONDITIONS FOR ALL REGISTERS (CONTINUED)

 $\label{eq:lagend: Legend: u = unchanged, x = unknown, - = unimplemented bit, read as `0', q = value depends on condition. Shaded cells indicate conditions do not apply for the designated device.$ 

**Note 1:** When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the TOSU, TOSH and TOSL are updated with the current value of the PC. The STKPTR is modified to point to the next location in the hardware stack.

2: When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the PC is loaded with the interrupt vector (0008h or 0018h).

3: One or more bits in the INTCONx or PIRx registers will be affected (to cause wake-up).

Register	Applicable Devices		Power-on Reset, Brown-out Reset	MCLR Reset, WDT Reset, RESET Instruction, St <u>ack</u> Resets, CM Reset	Wake-up via WDT or Interrupt	
CCP4CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	00 0000	00 0000	uu uuuu
CCPR5H	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	uuuu uuuu
CCPR5L	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	uuuu uuuu
CCP5CON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	00 0000	00 0000	uu uuuu
SPBRG2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
RCREG2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
TXREG2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
TXSTA2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0010	0000 0010	uuuu uuuu
RCSTA2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	x000 0000x	0000 000x	uuuu uuuu
ECCP3AS	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
ECCP3DEL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
ECCP2AS	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
ECCP2DEL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
SSP2BUF	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	uuuu uuuu
SSP2ADD	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
SSP2STAT	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
SSP2CON1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
SSP2CON2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EDATA	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	XXXX XXXX	uuuu uuuu	uuuu uuuu
EIR	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-000 0-00	-000 0-00	-uuu u-uu
ECON2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	100	100	uuu
ESTAT	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-0-0 -000	-0-0 -000	-u-u -uuu
EIE	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-000 0-00	-000 0-00	-uuu u-uu
EDMACSH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EDMACSL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EDMADSTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
EDMADSTL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EDMANDH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
EDMANDL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EDMASTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
EDMASTL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
ERXWRPTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
ERXWRPTL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
ERXRDPTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0101	0 0101	u uuuu
ERXRDPTL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1010	1111 1010	սսսս սսսս
ERXNDH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1 1111	1 1111	u uuuu
ERXNDL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1111	1111 1111	սսսս սսսս
ERXSTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0101	0 0101	u uuuu
ERXSTL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1111 1010	1111 1010	սսսս սսսս

#### TABLE 4-2: INITIALIZATION CONDITIONS FOR ALL REGISTERS (CONTINUED)

**Legend:** u = unchanged, x = unknown, - = unimplemented bit, read as '0', q = value depends on condition. Shaded cells indicate conditions do not apply for the designated device.

**Note 1:** When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the TOSU, TOSH and TOSL are updated with the current value of the PC. The STKPTR is modified to point to the next location in the hardware stack.

2: When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the PC is loaded with the interrupt vector (0008h or 0018h).

3: One or more bits in the INTCONx or PIRx registers will be affected (to cause wake-up).

Register	A	pplicable Device	95	Power-on Reset, Brown-out Reset	MCLR Reset, WDT Reset, RESET Instruction, St <u>ack</u> Resets, CM Reset	Wake-up via WDT or Interrupt
ETXNDH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
ETXNDL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
ETXSTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
ETXSTL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EWRPTH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
EWRPTL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
EPKTCNT	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
ERXFCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	1010 0001	1010 0001	uuuu uuuu
EPMOH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
EPMOL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
EPMCSH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
EPMCSL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
EPMM7	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
EPMM6	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
EPMM5	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EPMM4	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu
EPMM3	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EPMM2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EPMM1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EPMM0	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EHT7	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EHT6	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
EHT5	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EHT4	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EHT3	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
EHT2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EHT1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս
EHT0	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
MIRDH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
MIRDL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
MIWRH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
MIWRL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	นนนน นนนน
MIREGADR	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu
MICMD	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	00	00	uu
MAMXFLH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0110	0000 0110	นนนน นนนน
MAMXFLL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu

#### TABLE 4-2: INITIALIZATION CONDITIONS FOR ALL REGISTERS (CONTINUED)

**Legend:** u = unchanged, x = unknown, - = unimplemented bit, read as '0', q = value depends on condition.

Shaded cells indicate conditions do not apply for the designated device.

**Note 1:** When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the TOSU, TOSH and TOSL are updated with the current value of the PC. The STKPTR is modified to point to the next location in the hardware stack.

2: When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the PC is loaded with the interrupt vector (0008h or 0018h).

3: One or more bits in the INTCONx or PIRx registers will be affected (to cause wake-up).

TABLE 4-2. INITIALIZATION CONDITIONS FOR ALL REGISTERS (CONTINUED)								
Register	Applicable Devices			Power-on Reset, Brown-out Reset	MCLR Reset, WDT Reset, RESET Instruction, St <u>ack</u> Resets, CM Reset	Wake-up via WDT or Interrupt		
MAIPGH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-000 0000	-000 0000	-uuu uuuu		
MAIPGL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-000 0000	-000 0000	-uuu uuuu		
MABBIPG	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-000 0000	-000 0000	-uuu uuuu		
MACON4	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	-00000	-00000	-uuuuu		
MACON3	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu		
MACON1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0 0000	0 0000	u uuuu		
EPAUSH	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0001 0000	0001 0000	000u uuuu		
EPAUSL	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu		
EFLOCON	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	000	000	uuu		
MISTAT	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000	0000	uuuu		
MAADR2	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu		
MAADR1	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu		
MAADR4	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	սսսս սսսս		
MAADR3	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu		
MAADR6	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu		
MAADR5	PIC18F6XJ6X	PIC18F8XJ6X	PIC18F9XJ6X	0000 0000	0000 0000	uuuu uuuu		

#### TABLE 4-2: INITIALIZATION CONDITIONS FOR ALL REGISTERS (CONTINUED)

**Legend:** u = unchanged, x = unknown, - = unimplemented bit, read as '0', q = value depends on condition. Shaded cells indicate conditions do not apply for the designated device.

**Note 1:** When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the TOSU, TOSH and TOSL are updated with the current value of the PC. The STKPTR is modified to point to the next location in the hardware stack.

2: When the wake-up is due to an interrupt and the GIEL or GIEH bit is set, the PC is loaded with the interrupt vector (0008h or 0018h).

**3:** One or more bits in the INTCONx or PIRx registers will be affected (to cause wake-up).

NOTES:

# 5.0 MEMORY ORGANIZATION

There are two types of memory in PIC18 Flash microcontroller devices:

- Program Memory
- Data RAM


As Harvard architecture devices, the data and program memories use separate busses. This allows for concurrent access of the two memory spaces.

Additional detailed information on the operation of the Flash program memory is provided in **Section 6.0 "Flash Program Memory"**.

# 5.1 Program Memory Organization

PIC18 microcontrollers implement a 21-bit program counter which is capable of addressing a 2-Mbyte program memory space. Accessing a location between the upper boundary of the physically implemented memory and the 2-Mbyte address will return all '0's (a NOP instruction).

The entire PIC18F97J60 family offers three sizes of on-chip Flash program memory, from 64 Kbytes (up to 32,764 single-word instructions) to 128 Kbytes (65,532 single-word instructions). The program memory maps for individual family members are shown in Figure 5-1.




#### FIGURE 5-1: MEMORY MAPS FOR PIC18F97J60 FAMILY DEVICES

#### 5.1.1 HARD MEMORY VECTORS

All PIC18 devices have a total of three hard-coded return vectors in their program memory space. The Reset vector address is the default value to which the program counter returns on all device Resets; it is located at 0000h.

PIC18 devices also have two interrupt vector addresses for the handling of high priority and low priority interrupts. The high priority interrupt vector is located at 0008h and the low priority interrupt vector is at 0018h. Their locations in relation to the program memory map are shown in Figure 5-2.

#### FIGURE 5-2: HARD VECTOR AND CONFIGURATION WORD LOCATIONS FOR PIC18F97J60 FAMILY DEVICES



# 5.1.2 FLASH CONFIGURATION WORDS

Because the PIC18F97J60 family devices do not have persistent configuration memory, the top four words of on-chip program memory are reserved for configuration information. On Reset, the configuration information is copied into the Configuration registers.

The Configuration Words are stored in their program memory location in numerical order, starting with the lower byte of CONFIG1 at the lowest address and ending with the upper byte of CONFIG4. For these devices, only Configuration Words, CONFIG1 through CONFIG3, are used; CONFIG4 is reserved. The actual addresses of the Flash Configuration Words for devices in the PIC18F97J60 family are shown in Table 5-1. Their location in the memory map is shown with the other memory vectors in Figure 5-2.

Additional details on the device Configuration Words are provided in **Section 24.1** "Configuration Bits".

TABLE 5-1:	FLASH CONFIGURATION			
	WORDS FOR PIC18F97J60			
	FAMILY DEVICES			

Device	Program Memory (Kbytes)	Configuration Word Addresses
PIC18F66J60		
PIC18F86J60	64	FFF8h to FFFFh
PIC18F96J60		
PIC18F66J65		
PIC18F86J65	96	17FF8h to 17FFFh
PIC18F96J65		
PIC18F67J60		
PIC18F87J60	128	1FFF8h to 1FFFFh
PIC18F97J60		

#### 5.1.3 PIC18F9XJ60/9XJ65 PROGRAM MEMORY MODES

The 100-pin devices in this family can address up to a total of 2 Mbytes of program memory. This is achieved through the external memory bus. There are two distinct operating modes available to the controllers:

- Microcontroller (MC)
- Extended Microcontroller (EMC)

The program memory mode is determined by setting the EMB Configuration bits (CONFIG3L<5:4>), as shown in Register 5-1. (See also **Section 24.1 "Configuration Bits"** for additional details on the device Configuration bits.)

The program memory modes operate as follows:

 The Microcontroller Mode accesses only on-chip Flash memory. Attempts to read above the top of on-chip memory causes a read of all '0's (a NOP instruction).

The Microcontroller mode is also the only operating mode available to 64-pin and 80-pin devices.

 The Extended Microcontroller Mode allows access to both internal and external program memories as a single block. The device can access its entire on-chip program memory. Above this, the device accesses external program memory up to the 2-Mbyte program space limit. Execution automatically switches between the two memories as required.

The setting of the EMB Configuration bits also controls the address bus width of the external memory bus. This is covered in more detail in **Section 7.0** "**External Memory Bus**".

In all modes, the microcontroller has complete access to data RAM.

Figure 5-3 compares the memory maps of the different program memory modes. The differences between on-chip and external memory access limitations are more fully explained in Table 5-2.

# REGISTER 5-1: CONFIG3L: CONFIGURATION REGISTER 3 LOW


R/WO-1	R/WO-1	R/WO-1	R/WO-1	R/WO-1	U-0	U-0	U-0
WAIT <sup>(1)</sup>	BW <sup>(1)</sup>	EMB1 <sup>(1)</sup>	EMB0 <sup>(1)</sup>	EASHFT <sup>(1)</sup>	—	—	—
bit 7			•	•			bit 0

Legend:							
R = Readable bit WO = Write-Once bit		U = Unimplemented bit, read as '0'					
-n = Value v	when device is unprogrammed	'1' = Bit is set	'0' = Bit is cleared				
<b>h</b> it <b>7</b>	WAIT: External Bus Wait Enable bit <sup>(1)</sup>						
bit 7	1 = Wait states for operations on external memory bus disabled						
	and selected by MEMCON<5:4>						
bit 6	<b>BW:</b> Data Bus Width Select bit <sup>(1)</sup>						
	1 = 16-Bit Data Width mode						
	0 = 8-Bit Data Width mode						
bit 5-4	EMB1:EMB0: External Memory Bus Configuration bits <sup>(1)</sup>						
	11 = Microcontroller mode, external bus disabled						
	10 = Extended Microcontroller mode, 12-Bit Addressing mode						
	01 = Extended Microcontroller mode, 16-Bit Addressing mode						
	00 = Extended Microcontroller mode, 20-Bit Addressing mode						
bit 3	EASHFT: External Address Bus Shift Enable bit <sup>(1)</sup>						
	1 = Address shifting enabled; address on external bus is offset to start at 000000h						
	0 = Address shifting disabled; address of	on external bus reflects th	e PC value				
bit 2-0	Unimplemented: Read as '0'						

#### 5.1.4 EXTENDED MICROCONTROLLER MODE AND ADDRESS SHIFTING

By default, devices in Extended Microcontroller mode directly present the program counter value on the external address bus for those addresses in the range of the external memory space. In practical terms, this means addresses in the external memory device below the top of on-chip memory are unavailable. To avoid this, the Extended Microcontroller mode implements an address shifting option to enable automatic address translation. In this mode, addresses presented on the external bus are shifted down by the size of the on-chip program memory and are remapped to start at 0000h. This allows the complete use of the external memory device's memory space.





#### TABLE 5-2: MEMORY ACCESS FOR PIC18F9XJ60/9XJ65 PROGRAM MEMORY MODES

	Intern	al Program Me	emory	External Program Memory		
Operating Mode	Execution From	Table Read From	Table Write To	Execution From	Table Read From	Table Write To
Microcontroller	Yes	Yes	Yes	No Access	No Access	No Access
Extended Microcontroller	Yes	Yes	Yes	Yes	Yes	Yes

### 5.1.5 PROGRAM COUNTER

The Program Counter (PC) specifies the address of the instruction to fetch for execution. The PC is 21 bits wide and is contained in three separate 8-bit registers. The low byte, known as the PCL register, is both readable and writable. The high byte, or PCH register, contains the PC<15:8> bits; it is not directly readable or writable. Updates to the PCH register are performed through the PCLATH register. The upper byte is called PCU. This register contains the PC<20:16> bits; it is also not directly readable or writable. Updates to the PCH register. Updates to the PCU register are performed through the PCLATH register or writable. Updates to the PCU register are performed through the PCU register are performed through the PCU register are performed through the PCLATU register.

The contents of PCLATH and PCLATU are transferred to the program counter by any operation that writes to the PCL. Similarly, the upper two bytes of the program counter are transferred to PCLATH and PCLATU by an operation that reads PCL. This is useful for computed offsets to the PC (see **Section 5.1.8.1 "Computed GOTO"**).

The PC addresses bytes in the program memory. To prevent the PC from becoming misaligned with word instructions, the Least Significant bit of PCL is fixed to a value of '0'. The PC increments by 2 to address sequential instructions in the program memory.

The CALL, RCALL, GOTO and program branch instructions write to the program counter directly. For these instructions, the contents of PCLATH and PCLATU are not transferred to the program counter.

### 5.1.6 RETURN ADDRESS STACK

The return address stack allows any combination of up to 31 program calls and interrupts to occur. The PC is pushed onto the stack when a CALL or RCALL instruction is executed, or an interrupt is Acknowledged. The PC value is pulled off the stack on a RETURN, RETLW or a RETFIE instruction (and on ADDULNK and SUBULNK instructions if the extended instruction set is enabled). PCLATU and PCLATH are not affected by any of the RETURN or CALL instructions.

The stack operates as a 31-word by 21-bit RAM and a 5-bit Stack Pointer, STKPTR. The stack space is not part of either program or data space. The Stack Pointer is readable and writable and the address on the top of the stack is readable and writable through the Top-of-Stack Special Function Registers. Data can also be pushed to, or popped from the stack, using these registers.

A CALL type instruction causes a push onto the stack. The Stack Pointer is first incremented and the location pointed to by the Stack Pointer is written with the contents of the PC (already pointing to the instruction following the CALL). A RETURN type instruction causes a pop from the stack. The contents of the location pointed to by the STKPTR are transferred to the PC and then the Stack Pointer is decremented.


The Stack Pointer is initialized to '00000' after all Resets. There is no RAM associated with the location corresponding to a Stack Pointer value of '00000'; this is only a Reset value. Status bits indicate if the stack is full, has overflowed or has underflowed.

### 5.1.6.1 Top-of-Stack Access

Only the top of the return address stack (TOS) is readable and writable. A set of three registers, TOSU:TOSH:TOSL, holds the contents of the stack location pointed to by the STKPTR register (Figure 5-4). This allows users to implement a software stack if necessary. After a CALL, RCALL or interrupt (and ADDULNK and SUBULNK instructions if the extended instruction set is enabled), the software can read the pushed value by reading the TOSU:TOSH:TOSL registers. These values can be placed on a user-defined software stack. At return time. the software can return these values to TOSU:TOSH:TOSL and do a return.

The user must disable the global interrupt enable bits while accessing the stack to prevent inadvertent stack corruption.

### FIGURE 5-4: RETURN ADDRESS STACK AND ASSOCIATED REGISTERS



### 5.1.6.2 Return Stack Pointer (STKPTR)

The STKPTR register (Register 5-2) contains the Stack Pointer value, the STKFUL (Stack Full) status bit and the STKUNF (Stack Underflow) status bit. The value of the Stack Pointer can be 0 through 31. The Stack Pointer increments before values are pushed onto the stack and decrements after values are popped off the stack. On Reset, the Stack Pointer value will be zero. The user may read and write the Stack Pointer value. This feature can be used by a Real-Time Operating System (RTOS) for return stack maintenance.

After the PC is pushed onto the stack 31 times (without popping any values off the stack), the STKFUL bit is set. The STKFUL bit is cleared by software or by a POR.

The action that takes place when the stack becomes full depends on the state of the STVREN (Stack Overflow Reset Enable) Configuration bit. (Refer to **Section 24.1 "Configuration Bits**" for a description of the device Configuration bits.) If STVREN is set (default), the 31st push will push the (PC + 2) value onto the stack, set the STKFUL bit and reset the device. The STKFUL bit will remain set and the Stack Pointer will be set to zero.

If STVREN is cleared, the STKFUL bit will be set on the 31st push and the Stack Pointer will increment to 31. Any additional pushes will not overwrite the 31st push and the STKPTR will remain at 31.

When the stack has been popped enough times to unload the stack, the next pop returns a value of zero to the PC, and sets the STKUNF bit, while the Stack Pointer remains at zero. The STKUNF bit will remain set until cleared by software or until a POR occurs.

Note:	Returning a value of zero to the PC on an underflow has the effect of vectoring the program to the Reset vector, where the stack conditions can be verified and appropriate actions can be taken. This is not the same as a Reset, as the contents
	of the SFRs are not affected.

### 5.1.6.3 PUSH and POP Instructions

Since the Top-of-Stack is readable and writable, the ability to push values onto the stack and pull values off the stack, without disturbing normal program execution, is a desirable feature. The PIC18 instruction set includes two instructions, PUSH and POP, that permit the TOS to be manipulated under software control. TOSU, TOSH and TOSL can be modified to place data or a return address on the stack.

The PUSH instruction places the current PC value onto the stack. This increments the Stack Pointer and loads the current PC value onto the stack.

The POP instruction discards the current TOS by decrementing the Stack Pointer. The previous value pushed onto the stack then becomes the TOS value.

#### R/C-0 R/C-0 U-0 R/W-0 R/W-0 R/W-0 R/W-0 R/W-0 STKFUL<sup>(1)</sup> STKUNF<sup>(1)</sup> SP4 SP2 SP1 SP0 SP3 \_\_\_\_ bit 7 bit 0

STKPTR: STACK POINTER REGISTER

Legend:	C = Clearable bit				
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'			
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown		

bit 7	STKFUL: Stack Full Flag bit <sup>(1)</sup>
	1 = Stack became full or overflowed
	0 = Stack has not become full or overflowed
bit 6	STKUNF: Stack Underflow Flag bit <sup>(1)</sup>
	1 = Stack underflow occurred
	0 = Stack underflow did not occur
bit 5	Unimplemented: Read as '0'
bit 4-0	SP4:SP0: Stack Pointer Location bits

Note 1: Bit 7 and bit 6 are cleared by user software or by a POR.

**REGISTER 5-2:** 

### 5.1.6.4 Stack Full and Underflow Resets

Device Resets on stack overflow and stack underflow conditions are enabled by setting the STVREN bit in Configuration Register 1L. When STVREN is set, a full or underflow condition will set the appropriate STKFUL or STKUNF bit and then cause a device Reset. When STVREN is cleared, a full or underflow condition will set the appropriate STKFUL or STKUNF bit, but not cause a device Reset. The STKFUL or STKUNF bit is cleared by user software or a Power-on Reset.

### 5.1.7 FAST REGISTER STACK

A Fast Register Stack is provided for the STATUS, WREG and BSR registers to provide a "fast return" option for interrupts. This stack is only one level deep and is neither readable nor writable. It is loaded with the current value of the corresponding register when the processor vectors for an interrupt. All interrupt sources will push values into the Stack registers. The values in the registers are then loaded back into the working registers if the RETFIE, FAST instruction is used to return from the interrupt.

If both low and high priority interrupts are enabled, the Stack registers cannot be used reliably to return from low priority interrupts. If a high priority interrupt occurs while servicing a low priority interrupt, the Stack register values stored by the low priority interrupt will be overwritten. In these cases, users must save the key registers in software during a low priority interrupt.

If interrupt priority is not used, all interrupts may use the Fast Register Stack for returns from interrupt. If no interrupts are used, the Fast Register Stack can be used to restore the STATUS, WREG and BSR registers at the end of a subroutine call. To use the Fast Register Stack for a subroutine call, a CALL label, FAST instruction must be executed to save the STATUS, WREG and BSR registers to the Fast Register Stack. A RETURN, FAST instruction is then executed to restore these registers from the Fast Register Stack.

Example 5-1 shows a source code example that uses the Fast Register Stack during a subroutine call and return.

#### EXAMPLE 5-1: FAST REGISTER STACK CODE EXAMPLE

CALL	SUB1, FAST •	;STATUS, WREG, BSR ;SAVED IN FAST REGISTER ;STACK
SUB1	• • RETURN FAST	;RESTORE VALUES SAVED ;IN FAST REGISTER STACK

### 5.1.8 LOOK-UP TABLES IN PROGRAM MEMORY

There may be programming situations that require the creation of data structures, or look-up tables, in program memory. For PIC18 devices, look-up tables can be implemented in two ways:

- Computed GOTO
- Table Reads

### 5.1.8.1 Computed GOTO

A computed GOTO is accomplished by adding an offset to the program counter. An example is shown in Example 5-2.

A look-up table can be formed with an ADDWF PCL instruction and a group of RETLW nn instructions. The W register is loaded with an offset into the table before executing a call to that table. The first instruction of the called routine is the ADDWF PCL instruction. The next instruction executed will be one of the RETLW nn instructions, that returns the value 'nn' to the calling function.

The offset value (in WREG) specifies the number of bytes that the program counter should advance and should be multiples of 2 (LSb = 0).

In this method, only one data byte may be stored in each instruction location and room on the return address stack is required.

#### EXAMPLE 5-2: COMPUTED GOTO USING AN OFFSET VALUE

	MOVF	OFFSET, W
	CALL	TABLE
ORG	nn00h	
TABLE	ADDWF	PCL
	RETLW	nnh
	RETLW	nnh
	RETLW	nnh

### 5.1.8.2 Table Reads

A better method of storing data in program memory allows two bytes of data to be stored in each instruction location.

Look-up table data may be stored two bytes per program word while programming. The Table Pointer (TBLPTR) specifies the byte address and the Table Latch (TABLAT) contains the data that is read from the program memory. Data is transferred from program memory one byte at a time.

Table read operation is discussed further in **Section 6.1 "Table Reads and Table Writes**".

### 5.2 PIC18 Instruction Cycle

#### 5.2.1 CLOCKING SCHEME


The microcontroller clock input, whether from an internal or external source, is internally divided by four to generate four non-overlapping quadrature clocks (Q1, Q2, Q3 and Q4). Internally, the program counter is incremented on every Q1. The instruction is fetched from the program memory and latched into the Instruction Register (IR) during Q4. The instruction is decoded and executed during the following Q1 through Q4. The clocks and instruction execution flow are shown in Figure 5-5.

### 5.2.2 INSTRUCTION FLOW/PIPELINING

An "Instruction Cycle" consists of four Q cycles, Q1 through Q4. The instruction fetch and execute are pipelined in such a manner that a fetch takes one instruction cycle, while the decode and execute take another instruction cycle. However, due to the pipelining, each instruction effectively executes in one cycle. If an instruction causes the program counter to change (e.g., GOTO), then two cycles are required to complete the instruction (Example 5-3).

A fetch cycle begins with the Program Counter (PC) incrementing in Q1.

In the execution cycle, the fetched instruction is latched into the Instruction Register (IR) in cycle Q1. This instruction is then decoded and executed during the Q2, Q3 and Q4 cycles. Data memory is read during Q2 (operand read) and written during Q4 (destination write).



### FIGURE 5-5: CLOCK/INSTRUCTION CYCLE

### EXAMPLE 5-3: INSTRUCTION PIPELINE FLOW

	Тсү0	TCY1	TCY2	TCY3	TCY4	TcY5
1. MOVLW 55h F	etch 1	Execute 1				
2. MOVWF PORTB		Fetch 2	Execute 2			
3. BRA SUB_1	_		Fetch 3	Execute 3		
4. BSF PORTA, BIT3 (Forc	ed NOP)			Fetch 4	Flush (NOP)	
5. Instruction @ address S	SUB_1				Fetch SUB_1	Execute SUB_1

All instructions are single cycle, except for any program branches. These take two cycles since the fetch instruction is "flushed" from the pipeline while the new instruction is being fetched and then executed.

### 5.2.3 INSTRUCTIONS IN PROGRAM MEMORY

The program memory is addressed in bytes. Instructions are stored as two bytes or four bytes in program memory. The Least Significant Byte of an instruction word is always stored in a program memory location with an even address (LSb = 0). To maintain alignment with instruction boundaries, the PC increments in steps of 2 and the LSb will always read '0' (see Section 5.1.5 "Program Counter").

Figure 5-6 shows an example of how instruction words are stored in the program memory.

The CALL and GOTO instructions have the absolute program memory address embedded into the instruction. Since instructions are always stored on word boundaries, the data contained in the instruction is a word address. The word address is written to PC<20:1> which accesses the desired byte address in program memory. Instruction #2 in Figure 5-6 shows how the instruction, GOTO 0006h, is encoded in the program memory. Program branch instructions, which encode a relative address offset, operate in the same manner. The offset value stored in a branch instruction represents the number of single-word instructions that the PC will be offset by. Section 25.0 "Instruction Set Summary" provides further details of the instruction set.

		_		<b>LSB =</b> 1	LSB = 0	Word Address $\downarrow$
	Program M					000000h
	Byte Locat	ions $\rightarrow$				000002h
						000004h
						000006h
Instruction 1:	MOVLW	055h		0Fh	55h	000008h
Instruction 2:	GOTO	0006h		EFh	03h	00000Ah
				F0h	00h	00000Ch
Instruction 3:	MOVFF	123h,	456h	C1h	23h	00000Eh
				F4h	56h	000010h
						000012h
						000014h

### FIGURE 5-6: INSTRUCTIONS IN PROGRAM MEMORY

### 5.2.4 TWO-WORD INSTRUCTIONS

The standard PIC18 instruction set has four, two-word instructions: CALL, MOVFF, GOTO and LSFR. In all cases, the second word of the instructions always has '1111' as its four Most Significant bits; the other 12 bits are literal data, usually a data memory address.

The use of '1111' in the 4 MSbs of an instruction specifies a special form of NOP. If the instruction is executed in proper sequence – immediately after the first word – the data in the second word is accessed

and used by the instruction sequence. If the first word is skipped for some reason and the second word is executed by itself, a NOP is executed instead. This is necessary for cases when the two-word instruction is preceded by a conditional instruction that changes the PC. Example 5-4 shows how this works.

Note:	See Section 5.5 "Program Memory and
	the Extended Instruction Set" for
	information on two-word instructions in the
	extended instruction set.

EXAMPLE 3-4. INVO-WORD INSTRUCTIONS	EXAMPLE 5-4:	<b>TWO-WORD INSTRUCTIONS</b>
-------------------------------------	--------------	------------------------------

CASE 1:						
Object Code Source Code						
0110 0110 0000 0000	TSTFSZ REG1	; is RAM location 0?				
1100 0001 0010 0011	MOVFF REG1, R	EG2 ; No, skip this word				
1111 0100 0101 0110		; Execute this word as a NOP				
0010 0100 0000 0000	ADDWF REG3	; continue code				
CASE 2:						
Object Code	Source Code					
0110 0110 0000 0000	TSTFSZ REG1	; is RAM location 0?				
1100 0001 0010 0011	MOVFF REG1, R	EG2 ; Yes, execute this word				
1111 0100 0101 0110		; 2nd word of instruction				
0010 0100 0000 0000	ADDWF REG3	; continue code				

### 5.3 Data Memory Organization

Note:	The operation of some aspects of data						
	memory are changed when the PIC18						
	extended instruction set is enabled. See						
	Section 5.6 "Data Memory and the						
	Extended Instruction Set" for more						
	information.						

The data memory in PIC18 devices is implemented as static RAM. Each register in the data memory has a 12-bit address, allowing up to 4096 bytes of addressable memory. The memory space is divided into 16 banks that contain 256 bytes each. All of the PIC18F97J60 family devices implement all available banks and provide 3808 bytes of data memory available to the user. Figure 5-7 shows the data memory organization for the devices.

The data memory contains Special Function Registers (SFRs) and General Purpose Registers (GPRs). The SFRs are used for control and status of the controller and peripheral functions, while GPRs are used for data storage and scratchpad operations in the user's application. Any read of an unimplemented location will read as '0's.

The instruction set and architecture allow operations across all banks. The entire data memory may be accessed by Direct, Indirect or Indexed Addressing modes. Addressing modes are discussed later in this section.

To ensure that commonly used registers (most SFRs and select GPRs) can be accessed in a single cycle, PIC18 devices implement an Access Bank. This is a 256-byte memory space that provides fast access to the majority of SFRs and the lower portion of GPR Bank 0 without using the BSR. **Section 5.3.2 "Access Bank"** provides a detailed description of the Access RAM.

### 5.3.1 BANK SELECT REGISTER

Large areas of data memory require an efficient addressing scheme to make rapid access to any address possible. Ideally, this means that an entire address does not need to be provided for each read or write operation. For PIC18 devices, this is accomplished with a RAM banking scheme. This divides the memory space into 16 contiguous banks of 256 bytes. Depending on the instruction, each location can be addressed directly by its full 12-bit address, or an 8-bit low-order address and a 4-bit Bank Pointer.

Most instructions in the PIC18 instruction set make use of the Bank Pointer, known as the Bank Select Register (BSR). This SFR holds the 4 Most Significant bits of a location's address; the instruction itself includes the 8 Least Significant bits. Only the four lower bits of the BSR are implemented (BSR3:BSR0). The upper four bits are unused; they will always read '0' and cannot be written to. The BSR can be loaded directly by using the MOVLB instruction.


The value of the BSR indicates the bank in data memory. The 8 bits in the instruction show the location in the bank and can be thought of as an offset from the bank's lower boundary. The relationship between the BSR's value and the bank division in data memory is shown in Figure 5-8.


Since up to 16 registers may share the same low-order address, the user must always be careful to ensure that the proper bank is selected before performing a data read or write. For example, writing what should be program data to an 8-bit address of F9h, while the BSR is 0Fh, will end up resetting the program counter.

While any bank can be selected, only those banks that are actually implemented can be read or written to. Writes to unimplemented banks are ignored, while reads from unimplemented banks will return '0's. Even so, the STATUS register will still be affected as if the operation was successful. The data memory map in Figure 5-7 indicates which banks are implemented.

In the core PIC18 instruction set, only the MOVFF instruction fully specifies the 12-bit address of the source and target registers. This instruction ignores the BSR completely when it executes. All other instructions include only the low-order address as an operand and must use either the BSR or the Access Bank to locate their target registers.

#### FIGURE 5-7: DATA MEMORY MAP FOR PIC18F97J60 FAMILY DEVICES





#### FIGURE 5-8: USE OF THE BANK SELECT REGISTER (DIRECT ADDRESSING)

### 5.3.2 ACCESS BANK

While the use of the BSR with an embedded 8-bit address allows users to address the entire range of data memory, it also means that the user must always ensure that the correct bank is selected. Otherwise, data may be read from or written to the wrong location. This can be disastrous if a GPR is the intended target of an operation but an SFR is written to instead. Verifying and/or changing the BSR for each read or write to data memory can become very inefficient.

To streamline access for the most commonly used data memory locations, the data memory is configured with an Access Bank, which allows users to access a mapped block of memory without specifying a BSR. The Access Bank consists of the first 96 bytes of memory (00h-5Fh) in Bank 0 and the last 160 bytes of memory (60h-FFh) in Bank 15. The lower block is known as the "Access RAM" and is composed of GPRs. The upper block is where the device's SFRs are mapped. These two areas are mapped contiguously in the Access Bank and can be addressed in a linear fashion by an 8-bit address (Figure 5-7).

The Access Bank is used by core PIC18 instructions that include the Access RAM bit (the 'a' parameter in the instruction). When 'a' is equal to '1', the instruction uses the BSR and the 8-bit address included in the opcode for the data memory address. When 'a' is '0', however, the instruction is forced to use the Access Bank address map; the current value of the BSR is ignored entirely.

Using this "forced" addressing allows the instruction to operate on a data address in a single cycle without updating the BSR first. For 8-bit addresses of 60h and above, this means that users can evaluate and operate on SFRs more efficiently. The Access RAM below 60h is a good place for data values that the user might need to access rapidly, such as immediate computational results or common program variables. Access RAM also allows for faster and more code efficient context saving and switching of variables.

The mapping of the Access Bank is slightly different when the extended instruction set is enabled (XINST Configuration bit = 1). This is discussed in more detail in Section 5.6.3 "Mapping the Access Bank in Indexed Literal Offset Mode".

### 5.3.3 GENERAL PURPOSE REGISTER FILE

PIC18 devices may have banked memory in the GPR area. This is data RAM which is available for use by all instructions. GPRs start at the bottom of Bank 0 (address 000h) and grow upwards towards the bottom of the SFR area. GPRs are not initialized by a Power-on Reset and are unchanged on all other Resets.

### 5.3.4 SPECIAL FUNCTION REGISTERS

The Special Function Registers (SFRs) are registers used by the CPU and peripheral modules for controlling the desired operation of the device. These registers are implemented as static RAM.

The main group of SFRs start at the top of data memory (FFFh) and extend downward to occupy more than the top half of Bank 15 (F60h to FFFh). These SFRs can be classified into two sets: those associated with the "core" device functionality (ALU, Resets and interrupts) and those related to the peripheral functions. The

Reset and Interrupt registers are described in their respective chapters, while the ALU's STATUS register is described later in this section. Registers related to the operation of the peripheral features are described in the chapter for that peripheral.

The SFRs are typically distributed among the peripherals whose functions they control. Unused SFR locations are unimplemented and read as '0's. A list of SFRs is given in Table 5-3; a full description is provided in Table 5-5.

### TABLE 5-3: SPECIAL FUNCTION REGISTER MAP FOR PIC18F97J60 FAMILY DEVICES

Address	Name	Address	Name	Address	Name	Address	Name	Address	Name
FFFh	TOSU	FDFh	INDF2 <sup>(1)</sup>	FBFh	CCPR1H	F9Fh	IPR1	F7Fh	SPBRGH1
FFEh	TOSH	FDEh	POSTINC2 <sup>(1)</sup>	FBEh	CCPR1L	F9Eh	PIR1	F7Eh	BAUDCON1
FFDh	TOSL	FDDh	POSTDEC2 <sup>(1)</sup>	FBDh	CCP1CON	F9Dh	PIE1	F7Dh	SPBRGH2
FFCh	STKPTR	FDCh	PREINC2 <sup>(1)</sup>	FBCh	CCPR2H	F9Ch	MEMCON <sup>(4)</sup>	F7Ch	BAUDCON2
FFBh	PCLATU	FDBh	PLUSW2 <sup>(1)</sup>	FBBh	CCPR2L	F9Bh	OSCTUNE	F7Bh	ERDPTH
FFAh	PCLATH	FDAh	FSR2H	FBAh	CCP2CON	F9Ah	TRISJ <sup>(3)</sup>	F7Ah	ERDPTL
FF9h	PCL	FD9h	FSR2L	FB9h	CCPR3H	F99h	TRISH <sup>(3)</sup>	F79h	ECCP1DEL
FF8h	TBLPTRU	FD8h	STATUS	FB8h	CCPR3L	F98h	TRISG	F78h	TMR4
FF7h	TBLPTRH	FD7h	TMR0H	FB7h	CCP3CON	F97h	TRISF	F77h	PR4
FF6h	TBLPTRL	FD6h	TMR0L	FB6h	ECCP1AS	F96h	TRISE	F76h	T4CON
FF5h	TABLAT	FD5h	TOCON	FB5h	CVRCON	F95h	TRISD	F75h	CCPR4H
FF4h	PRODH	FD4h	(2)	FB4h	CMCON	F94h	TRISC	F74h	CCPR4L
FF3h	PRODL	FD3h	OSCCON	FB3h	TMR3H	F93h	TRISB	F73h	CCP4CON
FF2h	INTCON	FD2h	ECON1	FB2h	TMR3L	F92h	TRISA	F72h	CCPR5H
FF1h	INTCON2	FD1h	WDTCON	FB1h	T3CON	F91h	LATJ <sup>(3)</sup>	F71h	CCPR5L
FF0h	INTCON3	FD0h	RCON	FB0h	PSPCON	F90h	LATH <sup>(3)</sup>	F70h	CCP5CON
FEFh	INDF0 <sup>(1)</sup>	FCFh	TMR1H	FAFh	SPBRG1	F8Fh	LATG	F6Fh	SPBRG2
FEEh	POSTINC0 <sup>(1)</sup>	FCEh	TMR1L	FAEh	RCREG1	F8Eh	LATF	F6Eh	RCREG2
FEDh	POSTDEC0 <sup>(1)</sup>	FCDh	T1CON	FADh	TXREG1	F8Dh	LATE	F6Dh	TXREG2
FECh	PREINC0 <sup>(1)</sup>	FCCh	TMR2	FACh	TXSTA1	F8Ch	LATD	F6Ch	TXSTA2
FEBh	PLUSW0 <sup>(1)</sup>	FCBh	PR2	FABh	RCSTA1	F8Bh	LATC	F6Bh	RCSTA2
FEAh	FSR0H	FCAh	T2CON	FAAh	(2)	F8Ah	LATB	F6Ah	ECCP3AS
FE9h	FSR0L	FC9h	SSP1BUF	FA9h	(2)	F89h	LATA	F69h	ECCP3DEL
FE8h	WREG	FC8h	SSP1ADD	FA8h	(2)	F88h	PORTJ <sup>(3)</sup>	F68h	ECCP2AS
FE7h	INDF1 <sup>(1)</sup>	FC7h	SSP1STAT	FA7h	EECON2 <sup>(1)</sup>	F87h	PORTH <sup>(3)</sup>	F67h	ECCP2DEL
FE6h	POSTINC1 <sup>(1)</sup>	FC6h	SSP1CON1	FA6h	EECON1	F86h	PORTG	F66h	SSP2BUF
FE5h	POSTDEC1 <sup>(1)</sup>	FC5h	SSP1CON2	FA5h	IPR3	F85h	PORTF	F65h	SSP2ADD
FE4h	PREINC1 <sup>(1)</sup>	FC4h	ADRESH	FA4h	PIR3	F84h	PORTE	F64h	SSP2STAT
FE3h	PLUSW1 <sup>(1)</sup>	FC3h	ADRESL	FA3h	PIE3	F83h	PORTD	F63h	SSP2CON1
FE2h	FSR1H	FC2h	ADCON0	FA2h	IPR2	F82h	PORTC	F62h	SSP2CON2
FE1h	FSR1L	FC1h	ADCON1	FA1h	PIR2	F81h	PORTB	F61h	EDATA
FE0h	BSR	FC0h	ADCON2	FA0h	PIE2	F80h	PORTA	F60h	EIR

Note 1: This is not a physical register.

2: Unimplemented registers are read as '0'.

3: This register is not available on 64-pin devices.

4: This register is not available on 64 and 80-pin devices.

### 5.3.5 ETHERNET SFRs

In addition to the standard SFR set in Bank 15, members of the PIC18F97J60 family have a second set of SFRs. This group, associated exclusively with the Ethernet module, occupies the top half of Bank 14 (E80h to EFFh).

# Note: To improve performance, frequently accessed Ethernet registers are located in the standard SFR bank (F60h through FFFh).

A complete list of Ethernet SFRs is given in Table 5-4. All SFRs are fully described in Table 5-5

### TABLE 5-4: ETHERNET SFR MAP FOR PIC18F97J60 FAMILY DEVICES

Address	Name	Address	Name	Address	Name	Address	Name
EFFh	(1)	EDFh	(1)	EBFh	(1)	E9Fh	(1)
EFEh	ECON2	EDEh	(1)	EBEh	(1)	E9Eh	(1)
EFDh	ESTAT	EDDh	(1)	EBDh	(1)	E9Dh	(1)
EFCh	(1)	EDCh	(1)	EBCh	(1)	E9Ch	(1)
EFBh	EIE	EDBh	(1)	EBBh	(1)	E9Bh	(1)
EFAh	(1)	EDAh	(1)	EBAh	(1)	E9Ah	(1)
EF9h	(2)	ED9h	EPKTCNT	EB9h	MIRDH	E99h	EPAUSH
EF8h	(2)	ED8h	ERXFCON	EB8h	MIRDL	E98h	EPAUSL
EF7h	EDMACSH	ED7h	(1)	EB7h	MIWRH	E97h	EFLOCON
EF6h	EDMACSL	ED6h	(1)	EB6h	MIWRL	E96h	(2)
EF5h	EDMADSTH	ED5h	EPMOH	EB5h	(1)	E95h	(2)
EF4h	EDMADSTL	ED4h	EPMOL	EB4h	MIREGADR	E94h	(2)
EF3h	EDMANDH	ED3h	(2)	EB3h	(2)	E93h	(2)
EF2h	EDMANDL	ED2h	(2)	EB2h	MICMD	E92h	(2)
EF1h	EDMASTH	ED1h	EPMCSH	EB1h	(1)	E91h	(2)
EF0h	EDMASTL	ED0h	EPMCSL	EB0h	(1)	E90h	(2)
EEFh	ERXWRPTH	ECFh	EPMM7	EAFh	(2)	E8Fh	(2)
EEEh	ERXWRPTL	ECEh	EPMM6	EAEh	(1)	E8Eh	(2)
EEDh	ERXRDPTH	ECDh	EPMM5	EADh	(1)	E8Dh	(2)
EECh	ERXRDPTL	ECCh	EPMM4	EACh	(1)	E8Ch	(2)
EEBh	ERXNDH	ECBh	EPMM3	EABh	MAMXFLH	E8Bh	(2)
EEAh	ERXNDL	ECAh	EPMM2	EAAh	MAMXFLL	E8Ah	MISTAT
EE9h	ERXSTH	EC9h	EPMM1	EA9h	(1)	E89h	(1)
EE8h	ERXSTL	EC8h	EPMM0	EA8h	(1)	E88h	(1)
EE7h	ETXNDH	EC7h	EHT7	EA7h	MAIPGH	E87h	(1)
EE6h	ETXNDL	EC6h	EHT6	EA6h	MAIPGL	E86h	(1)
EE5h	ETXSTH	EC5h	EHT5	EA5h	(2)	E85h	MAADR2
EE4h	ETXSTL	EC4h	EHT4	EA4h	MABBIPG	E84h	MAADR1
EE3h	EWRPTH	EC3h	EHT3	EA3h	MACON4	E83h	MAADR4
EE2h	EWRPTL	EC2h	EHT2	EA2h	MACON3	E82h	MAADR3
EE1h	(1)	EC1h	EHT1	EA1h	(1)	E81h	MAADR6
EE0h	(1)	EC0h	EHT0	EA0h	MACON1	E80h	MAADR5

**Note 1:** Reserved register location; do not modify.

2: Unimplemented registers are read as '0'.

File Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Values on POR, BOR	Details on Page:
TOSU	_	_	_	Top-of-Stack	Register Uppe	r Byte (TOS<2	20:16>)		0 0000	59, 71
TOSH	Top-of-Stack	Register High	n Byte (TOS<1	5:8>)					0000 0000	59, 71
TOSL	Top-of-Stack	Register Low	Byte (TOS<7	:0>)					0000 0000	59, 71
STKPTR	STKFUL <sup>(1)</sup>	STKUNF <sup>(1)</sup>	—	SP4	SP3	SP2	SP1	SP0	00-0 0000	59, 72
PCLATU	_	—	bit 21 <sup>(2)</sup>	Holding Regi	ster for PC<20	:16>		•	0 0000	59, 71
PCLATH	Holding Reg	ister for PC<1	5:8>						0000 0000	59, 71
PCL	PC Low Byte (PC<7:0>)								0000 0000	59, 71
TBLPTRU	—	—	bit 21	Program Mer	nory Table Poi	nter Upper By	te (TBLPTR<2	20:16>)	00 0000	59, 98
TBLPTRH	Program Me	mory Table Po	ointer High Byt	e (TBLPTR<1	5:8>)				0000 0000	59, 98
TBLPTRL	Program Me	mory Table Po	ointer Low Byte	e (TBLPTR<7:	0>)				0000 0000	59, 98
TABLAT	Program Me	mory Table La	tch						0000 0000	59, 98
PRODH	Product Reg	ister High Byte	Э						XXXX XXXX	59, 117
PRODL	Product Reg	ister Low Byte	)						XXXX XXXX	59, 117
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	0000 000x	59, 121
INTCON2	RBPU	INTEDG0	INTEDG1	INTEDG2	INTEDG3	TMR0IP	INT3IP	RBIP	1111 1111	59, 122
INTCON3	INT2IP	INT1IP	INT3IE	INT2IE	INT1IE	INT3IF	INT2IF	INT1IF	1100 0000	59, 123
INDF0	Uses conten	ts of FSR0 to	address data	memory – valu	ie of FSR0 not	changed (not	a physical reg	jister)	N/A	59, 89
POSTINC0	Uses conten	ts of FSR0 to	address data i	memory – valu	ie of FSR0 pos	t-incremented	(not a physic	al register)	N/A	59, 90
POSTDEC0	Uses conten	ts of FSR0 to	address data i	memory – valu	ie of FSR0 pos	t-decremente	d (not a physic	cal register)	N/A	59, 90
PREINC0	Uses contents of FSR0 to address data memory – value of FSR0 pre-incremented (not a physical register)						N/A	59, 90		
PLUSW0		its of FSR0 to R0 offset by W	address data i	memory – valu	ie of FSR0 pre	-incremented	(not a physica	l register) –	N/A	59, 90
FSR0H	—	_	_		Indirect Data	Memory Addre	ess Pointer 0 I	High Byte	xxxx	59, 89
FSR0L	Indirect Data	a Memory Add	ress Pointer 0	Low Byte					XXXX XXXX	59, 90
WREG	Working Reg	gister							XXXX XXXX	59
INDF1	Uses conten	ts of FSR1 to	address data i	memory – valu	ie of FSR1 not	changed (not	a physical reg	jister)	N/A	59, 89
POSTINC1	Uses conten	ts of FSR1 to	address data i	memory – valu	ie of FSR1 pos	t-incremented	(not a physic	al register)	N/A	59, 90
POSTDEC1	Uses conten	ts of FSR1 to	address data i	memory – valu	ie of FSR1 pos	t-decremente	d (not a physic	cal register)	N/A	59, 90
PREINC1	Uses conten	ts of FSR1 to	address data i	memory – valu	ie of FSR1 pre	-incremented	(not a physica	l register)	N/A	59, 90
PLUSW1		its of FSR1 to R1 offset by W		memory – valu	ie of FSR1 pre	-incremented	(not a physica	l register) –	N/A	59, 90
FSR1H	—	—	—	—	Indirect Data	Memory Addre	ess Pointer 1 I	ligh Byte	xxxx	59, 89
FSR1L	Indirect Data	Memory Add	ress Pointer 1	Low Byte	•				XXXX XXXX	59, 89
BSR	—	—	—	—	Bank Select F	Register			0000	59, 89
INDF2	Uses conten	ts of FSR2 to	address data i	memory – valu	ie of FSR2 not	changed (not	a physical reg	jister)	N/A	59, 89
POSTINC2	Uses conten	ts of FSR2 to	address data i	memory – valu	ie of FSR2 pos	t-incremented	(not a physic	al register)	N/A	59, 90
POSTDEC2	Uses conten	ts of FSR2 to	address data i	memory – valu	ie of FSR2 pos	t-decremente	d (not a physic	cal register)	N/A	59, 90
PREINC2	Uses conten	ts of FSR2 to	address data i	memory – valu	ie of FSR2 pre	-incremented	(not a physica	l register)	N/A	59, 90
PLUSW2		its of FSR2 to R2 offset by W		memory – valu	ie of FSR2 pre	-incremented	(not a physica	l register) –	N/A	59, 90
FSR2H	—	_	—	_	Indirect Data	Memory Addre	ess Pointer 2 I	ligh Byte	xxxx	59, 89
FSR2L	Indirect Data	Memory Add	ress Pointer 2	Low Byte					XXXX XXXX	59, 89

TABLE 5-5: REGISTER FILE SUMMARY (PIC18F97J60 FAMILY
--

Legend: x = unknown, u = unchanged, - = unimplemented, read as '0', q = value depends on condition, r = reserved bit, do not modify. Shaded cells are unimplemented, read as '0'.

Note 1: Bit 7 and bit 6 are cleared by user software or by a POR.

**2**: Bit 21 of the PC is only available in Serial Programming modes.

**3:** Reset value is '0' when Two-Speed Start-up is enabled and '1' if disabled.

**4:** Alternate names and definitions for these bits when the MSSP module is operating in  $l^2C^{TM}$  Slave mode.

5: These bits and/or registers are only available in 100-pin devices; otherwise, they are unimplemented and read as '0'. Reset values shown apply only to 100-pin devices.

6: These bits and/or registers are only available in 80-pin and 100-pin devices; in 64-pin devices, they are unimplemented and read as '0'. Reset values are shown for 100-pin devices.

7: In Microcontroller mode, the bits in this register are unwritable and read as '0'.

8: PLLEN is only available when either ECPLL or HSPLL Oscillator mode is selected; otherwise, read as '0'.

File Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Values on POR, BOR	Details on Page:
STATUS	_	_	_	N	OV	Z	DC	С	x xxxx	60, 87
TMR0H	Timer0 Regi	ster High Byte							0000 0000	60, 163
TMR0L	Timer0 Regi	ster Low Byte							XXXX XXXX	60, 163
T0CON	TMR0ON	T08BIT	TOCS	T0SE	PSA	T0PS2	T0PS1	T0PS0	1111 1111	60, 163
OSCCON	IDLEN	-	—	—	OSTS <sup>(3)</sup>	—	SCS1	SCS0	0 q-00	60, 43
ECON1	TXRST	RXRST	DMAST	CSUMEN	TXRTS	RXEN	_	_	0000 00	60, 213
WDTCON	—	_	—	_	—	—	_	SWDTEN	0	60, 353
RCON	IPEN	_	CM	RI	TO	PD	POR	BOR	0-q1 1100	60, 54, 133
TMR1H	Timer1 Regi	ster High Byte							XXXX XXXX	60, 167
TMR1L	Timer1 Regi	ster Low Byte							XXXX XXXX	60, 167
T1CON	RD16	T1RUN	T1CKPS1	T1CKPS0	T1OSCEN	T1SYNC	TMR1CS	TMR10N	0000 0000	60, 167
TMR2	Timer2 Regi	ster							0000 0000	60, 173
PR2	Timer2 Peric	Timer2 Period Register								60, 173
T2CON	_	T2OUTPS3	T2OUTPS2	T2OUTPS1	T2OUTPS0	TMR2ON	T2CKPS1	T2CKPS0	-000 0000	60, 173
SSP1BUF	MSSP1 Rec	eive Buffer/Tra	ansmit Registe	r					XXXX XXXX	60, 265
SSP1ADD	MSSP1 Add	ress Register	(I <sup>2</sup> C™ Slave n	node), MSSP1	Baud Rate R	eload Register	(I <sup>2</sup> C Master n	node)	0000 0000	60, 265
SSP1STAT	SMP	CKE	D/Ā	Р	S	R/W	UA	BF	0000 0000	60, 256, 266
SSP1CON1	WCOL	SSPOV	SSPEN	СКР	SSPM3	SSPM2	SSPM1	SSPM0	0000 0000	60, 257, 267
SSP1CON2	GCEN	ACKSTAT	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN	0000 0000	60, 268
	GCEN	ACKSTAT	ADMSK5 <sup>(4)</sup>	ADMSK4 <sup>(4)</sup>	ADMSK3(4)	ADMSK2(4)	ADMSK1(4)	SEN		
ADRESH	A/D Result F	Register High E	Byte	•	•	•	•		XXXX XXXX	60, 333
ADRESL	A/D Result F	Register Low B	Byte						XXXX XXXX	60, 333
ADCON0	ADCAL	_	CHS3	CHS2	CHS1	CHS0	GO/DONE	ADON	0-00 0000	60, 325
ADCON1	_		VCFG1	VCFG0	PCFG3	PCFG2	PCFG1	PCFG0	00 0000	60, 326
ADCON2	ADFM	-	ACQT2	ACQT1	ACQT0	ADCS2	ADCS1	ADCS0	0-00 0000	60, 327
CCPR1H	Capture/Con	npare/PWM R	egister 1 High	Byte	•	•	•		XXXX XXXX	60, 185
CCPR1L	Capture/Con	npare/PWM R	egister 1 Low	Byte					XXXX XXXX	60, 185
CCP1CON	P1M1	P1M0	DC1B1	DC1B0	CCP1M3	CCP1M2	CCP1M1	CCP1M0	0000 0000	60, 189
CCPR2H	Capture/Con	npare/PWM R	egister 2 High	Byte					XXXX XXXX	60, 185
CCPR2L	Capture/Con	npare/PWM R	egister 2 Low	Byte					XXXX XXXX	60, 185
CCP2CON	P2M1	P2M0	DC2B1	DC2B0	CCP2M3	CCP2M2	CCP2M1	CCP2M0	0000 0000	60, 189
CCPR3H	Capture/Compare/PWM Register 3 High Byte								XXXX XXXX	60, 185
CCPR3L	Capture/Con	npare/PWM R	egister 3 Low	Byte					XXXX XXXX	60, 185
CCP3CON	P3M1	P3M0	DC3B1	DC3B0	CCP3M3	CCP3M2	CCP3M1	CCP3M0	0000 0000	60, 189
ECCP1AS	ECCP1ASE	ECCP1AS2	ECCP1AS1	ECCP1AS0	PSS1AC1	PSS1AC0	PSS1BD1	PSS1BD0	0000 0000	60, 201
CVRCON	CVREN	CVROE	CVRR	CVRSS	CVR3	CVR2	CVR1	CVR0	0000 0000	60, 341
CMCON	C2OUT	C1OUT	C2INV	C1INV	CIS	CM2	CM1	CM0	0000 0111	60, 335
TMR3H	Timer3 Regi	ster High Byte							XXXX XXXX	60, 175
TMR3L	Timer3 Regi	ster Low Byte							XXXX XXXX	60, 175

### TABLE 5-5: REGISTER FILE SUMMARY (PIC18F97J60 FAMILY) (CONTINUED)

Legend: x = unknown, u = unchanged, - = unimplemented, read as '0', q = value depends on condition, r = reserved bit, do not modify. Shaded cells are unimplemented, read as '0'.

**Note 1:** Bit 7 and bit 6 are cleared by user software or by a POR.

2: Bit 21 of the PC is only available in Serial Programming modes.

3: Reset value is '0' when Two-Speed Start-up is enabled and '1' if disabled.

4: Alternate names and definitions for these bits when the MSSP module is operating in  $I^2C^{TM}$  Slave mode.

5: These bits and/or registers are only available in 100-pin devices; otherwise, they are unimplemented and read as '0'. Reset values shown apply only to 100-pin devices.

6: These bits and/or registers are only available in 80-pin and 100-pin devices; in 64-pin devices, they are unimplemented and read as '0'. Reset values are shown for 100-pin devices.

7: In Microcontroller mode, the bits in this register are unwritable and read as '0'.

8: PLLEN is only available when either ECPLL or HSPLL Oscillator mode is selected; otherwise, read as '0'.

File Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Values on POR, BOR	Details on Page:
T3CON	RD16	T3CCP2	T3CKPS1	T3CKPS0	T3CCP1	T3SYNC	TMR3CS	TMR3ON	0000 0000	61, 175
PSPCON <sup>(5)</sup>	IBF	OBF	IBOV	PSPMODE	_	_	_	_	0000	61, 160
SPBRG1	EUSART1 B	aud Rate Gen	erator Registe	er Low Byte					0000 0000	61, 306
RCREG1	EUSART1 R	eceive Regist	er						0000 0000	61, 313
TXREG1	EUSART1 T	ransmit Regist	ter						XXXX XXXX	61, 315
TXSTA1	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	0000 0010	61, 306
RCSTA1	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	0000 000x	61, 306
EECON2	Program Me	mory Control I	Register (not a	a physical regis	ster)					61, 96
EECON1	_	FREE WRERR WREN WR _								
IPR3	SSP2IP <sup>(5)</sup>	BCL2IP <sup>(5)</sup>	RC2IP <sup>(6)</sup>	TX2IP <sup>(6)</sup>	TMR4IP	CCP5IP	CCP4IP	CCP3IP	1111 1111	61, 132
PIR3	SSP2IF <sup>(5)</sup>	BCL2IF <sup>(5)</sup>	RC2IF <sup>(6)</sup>	TX2IF <sup>(6)</sup>	TMR4IF	CCP5IF	CCP4IF	CCP3IF	0000 0000	61, 126
PIE3	SSP2IE <sup>(5)</sup>	BCL2IE <sup>(5)</sup>	RC2IE <sup>(6)</sup>	TX2IE <sup>(6)</sup>	TMR4IE	CCP5IE	CCP4IE	CCP3IE	0000 0000	61, 129
IPR2	OSCFIP	CMIP	ETHIP	r	BCL1IP	_	TMR3IP	CCP2IP	1111 1-11	61, 131
PIR2	OSCFIF	CMIF	ETHIF	r	BCL1IF	_	TMR3IF	CCP2IF	0000 0-00	61, 125
PIE2	OSCFIE	CMIE	ETHIE	r	BCL1IE	_	TMR3IE	CCP2IE	0000 0-00	61, 128
IPR1	PSPIP <sup>(9)</sup>	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	1111 1111	61, 130
PIR1	PSPIF <sup>(9)</sup>	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	0000 0000	61, 124
PIE1	PSPIE <sup>(9)</sup>	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	0000 0000	61, 127
MEMCON <sup>(5,7)</sup>	EBDIS	_	WAIT1	WAIT0	_	_	WM1	WM0	0-0000	61, 106
OSCTUNE	PPST1	PLLEN <sup>(8)</sup>	PPST0	PPRE	_	—	_	—	0000	61, 41
TRISJ <sup>(6)</sup>	TRISJ7 <sup>(5)</sup>	TRISJ6 <sup>(5)</sup>	TRISJ5 <sup>(6)</sup>	TRISJ4 <sup>(6)</sup>	TRISJ3 <sup>(5)</sup>	TRISJ2 <sup>(5)</sup>	TRISJ1 <sup>(5)</sup>	TRISJ0 <sup>(5)</sup>	1111 1111	61, 158
TRISH <sup>(6)</sup>	TRISH7 <sup>(6)</sup>	TRISH6 <sup>(6)</sup>	TRISH5 <sup>(6)</sup>	TRISH4 <sup>(6)</sup>	TRISH3 <sup>(6)</sup>	TRISH2 <sup>(6)</sup>	TRISH1 <sup>(6)</sup>	TRISH0 <sup>(6)</sup>	1111 1111	61, 156
TRISG	TRISG7 <sup>(5)</sup>	TRISG6 <sup>(5)</sup>	TRISG5 <sup>(5)</sup>	TRISG4	TRISG3 <sup>(6)</sup>	TRISG2 <sup>(6)</sup>	TRISG1 <sup>(6)</sup>	TRISG0 <sup>(6)</sup>	1111 1111	61, 154
TRISF	TRISF7	TRISF6	TRISF5	TRISF4	TRISF3	TRISF2	TRISF1	TRISF0 <sup>(5)</sup>	1111 1111	61, 151
TRISE	TRISE7 <sup>(6)</sup>	TRISE6 <sup>(6)</sup>	TRISE5	TRISE4	TRISE3	TRISE2	TRISE1	TRISE0	1111 1111	61, 149
TRISD	TRISD7 <sup>(5)</sup>	TRISD6 <sup>(5)</sup>	TRISD5 <sup>(5)</sup>	TRISD4 <sup>(5)</sup>	TRISD3 <sup>(5)</sup>	TRISD2	TRISD1	TRISD0	1111 1111	61, 146
TRISC	TRISC7	TRISC6	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	1111 1111	61, 143
TRISB	TRISB7	TRISB6	TRISB5	TRISB4	TRISB3	TRISB2	TRISB1	TRISB0	1111 1111	61, 140
TRISA	—		TRISA5	TRISA4	TRISA3	TRISA2	TRISA1	TRISA0	11 1111	61, 137
LATJ <sup>(6)</sup>	LATJ7 <sup>(5)</sup>	LATJ6 <sup>(5)</sup>	LATJ5 <sup>(6)</sup>	LATJ4 <sup>(6)</sup>	LATJ3 <sup>(5)</sup>	LATJ2 <sup>(5)</sup>	LATJ1 <sup>(5)</sup>	LATJO <sup>(5)</sup>	XXXX XXXX	61, 158
LATH <sup>(6)</sup>	LATH7 <sup>(6)</sup>	LATH6 <sup>(6)</sup>	LATH5 <sup>(6)</sup>	LATH4 <sup>(6)</sup>	LATH3 <sup>(6)</sup>	LATH2 <sup>(6)</sup>	LATH1 <sup>(6)</sup>	LATH0 <sup>(6)</sup>	XXXX XXXX	61, 156
LATG	LATG7 <sup>(5)</sup>	LATG6 <sup>(5)</sup>	LATG5 <sup>(5)</sup>	LATG4	LATG3 <sup>(6)</sup>	LATG2 <sup>(6)</sup>	LATG1 <sup>(6)</sup>	LATG0 <sup>(6)</sup>	XXXX XXXX	62, 154
LATF	LATF7	LATF6	LATF5	LATF4	LATF3	LATF2	LATF1	LATF0 <sup>(5)</sup>	XXXX XXXX	62, 151
LATE	LATE7 <sup>(6)</sup>	LATE6 <sup>(6)</sup>	LATE5	LATE4	LATE3	LATE2	LATE1	LATE0	XXXX XXXX	62, 149
LATD	LATD7 <sup>(5)</sup>	LATD6 <sup>(5)</sup>	LATD5 <sup>(5)</sup>	LATD4 <sup>(5)</sup>	LATD3 <sup>(5)</sup>	LATD2	LATD1	LATD0	XXXX XXXX	62, 146
LATC	LATC7	LATC6	LATC5	LATC4	LATC3	LATC2	LATC1	LATC0	XXXX XXXX	62, 143
LATB	LATB7	LATB6	LATB5	LATB4	LATB3	LATB2	LATB1	LATB0	XXXX XXXX	62, 140
LATA	RDPU	REPU	LATA5	LATA4	LATA3	LATA2	LATA1	LATA0	00xx xxxx	62, 137
PORTJ <sup>(6)</sup>	RJ7 <sup>(5)</sup>	RJ6 <sup>(5)</sup>	RJ5 <sup>(6)</sup>	RJ4 <sup>(6)</sup>	RJ3 <sup>(5)</sup>	RJ2 <sup>(5)</sup>	RJ1 <sup>(5)</sup>	RJ0 <sup>(5)</sup>	XXXX XXXX	62, 158
PORTH <sup>(6)</sup>	RH7 <sup>(6)</sup>	RH6 <sup>(6)</sup>	RH5 <sup>(6)</sup>	RH4 <sup>(6)</sup>	RH3 <sup>(6)</sup>	RH2 <sup>(6)</sup>	RH1 <sup>(6)</sup>	RH0 <sup>(6)</sup>	0000 xxxx	62, 156
PORTG	RG7 <sup>(5)</sup>	RG6 <sup>(5)</sup>	RG5 <sup>(5)</sup>	RG4	RG3 <sup>(6)</sup>	RG2 <sup>(6)</sup>	RG1 <sup>(6)</sup>	RG0 <sup>(6)</sup>	111x xxxx	62, 154

### TABLE 5-5: REGISTER FILE SUMMARY (PIC18F97J60 FAMILY) (CONTINUED)

Legend: x = unknown, u = unchanged, - = unimplemented, read as '0', q = value depends on condition, r = reserved bit, do not modify. Shaded cells are unimplemented, read as '0'.

Note 1: Bit 7 and bit 6 are cleared by user software or by a POR.

**2:** Bit 21 of the PC is only available in Serial Programming modes.

 $\label{eq:constraint} \textbf{3:} \quad \text{Reset value is `0' when Two-Speed Start-up is enabled and `1' if disabled.}$ 

4: Alternate names and definitions for these bits when the MSSP module is operating in  $I^2C^{TM}$  Slave mode.

5: These bits and/or registers are only available in 100-pin devices; otherwise, they are unimplemented and read as '0'. Reset values shown apply only to 100-pin devices.

6: These bits and/or registers are only available in 80-pin and 100-pin devices; in 64-pin devices, they are unimplemented and read as '0'. Reset values are shown for 100-pin devices.

7: In Microcontroller mode, the bits in this register are unwritable and read as '0'.

8: PLLEN is only available when either ECPLL or HSPLL Oscillator mode is selected; otherwise, read as '0'.

TABLE 5-5:	REGISTER FILE SUMMARY (PIC18F97J60 FAMILY) (CONTINUED)
------------	--

File Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Values on POR, BOR	Details on Page:
PORTF	RF7	RF6	RF5	RF4	RF3	RF2	RF1	RF0 <sup>(5)</sup>	0000 0000	62, 151
PORTE	RE7 <sup>(6)</sup>	RE6 <sup>(6)</sup>	RE5	RE4	RE3	RE2	RE1	RE0	XXXX XXXX	62, 149
PORTD	RD7 <sup>(5)</sup>	RD6 <sup>(5)</sup>	RD5 <sup>(5)</sup>	RD4 <sup>(5)</sup>	RD3 <sup>(5)</sup>	RD2	RD1	RD0	XXXX XXXX	62, 146
PORTC	RC7	RC6	RC5	RC4	RC3	RC2	RC1	RC0	XXXX XXXX	62, 143
PORTB	RB7	RB6	RB5	RB4	RB3	RB2	RB1	RB0	XXXX XXXX	62, 140
PORTA	RJPU <sup>(6)</sup>	_	RA5	RA4	RA3	RA2	RA1	RA0	0-0x 0000	62, 137
SPBRGH1	EUSART1 B	aud Rate Gen	erator Registe	er High Byte					0000 0000	62, 306
BAUDCON1	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	—	WUE	ABDEN	0100 0-00	62, 304
SPBRGH2	EUSART2 B	aud Rate Gen	erator Registe	er High Byte	•		•		0000 0000	62, 306
BAUDCON2	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	_	WUE	ABDEN	0100 0-00	62, 304
ERDPTH	_	-	—	Buffer Read F	Pointer High B	yte			0 0101	62, 209
ERDPTL	Buffer Read Pointer Low Byte								1111 1010	62, 209
ECCP1DEL	P1RSEN	P1DC6	P1DC5	P1DC4	P1DC3	P1DC2	P1DC1	P1DC0	0000 0000	62, 200
TMR4	Timer4 Regis	ster	•	•	•		•		0000 0000	62, 179
PR4	Timer4 Perio	od Register							1111 1111	62, 179
T4CON	_	T4OUTPS3	T4OUTPS2	T4OUTPS1	T4OUTPS0	TMR4ON	T4CKPS1	T4CKPS0	-000 0000	62, 179
CCPR4H	Capture/Con	npare/PWM R	egister 4 High	Byte	•		•		XXXX XXXX	62, 185
CCPR4L	Capture/Compare/PWM Register 4 Low Byte								XXXX XXXX	62, 185
CCP4CON	_	_	DC4B1	DC4B0	CCP4M3	CCP4M2	CCP4M1	CCP4M0	00 0000	63, 181
CCPR5H	Capture/Con	npare/PWM R	egister 5 High	Byte					XXXX XXXX	63, 185
CCPR5L	Capture/Con	npare/PWM R	egister 5 Low	Byte					XXXX XXXX	63, 185
CCP5CON	_	_	DC5B1	DC5B0	CCP5M3	CCP5M2	CCP5M1	CCP5M0	00 0000	63, 181
SPBRG2	EUSART2 B	aud Rate Gen	erator Registe	er Low Byte					0000 0000	63, 306
RCREG2	EUSART2 R	eceive Regist	er						0000 0000	63, 313
TXREG2	EUSART2 T	ransmit Regist	ter						0000 0000	63, 315
TXSTA2	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	0000 0010	63, 302
RCSTA2	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	0000 000x	63, 303
ECCP3AS	ECCP3ASE	ECCP3AS2	ECCP3AS1	ECCP3AS0	PSS3AC1	PSS3AC0	PSS3BD1	PSS3BD0	0000 0000	63, 201
ECCP3DEL	P3RSEN	P3DC6	P3DC5	P3DC4	P3DC3	P3DC2	P3DC1	P3DC0	0000 0000	63, 200
ECCP2AS	ECCP2ASE	ECCP2AS2	ECCP2AS1	ECCP2AS0	PSS2AC1	PSS2AC0	PSS2BD1	PSS2BD0	0000 0000	63, 201
ECCP2DEL	P2RSEN	P2DC6	P2DC5	P2DC4	P2DC3	P2DC2	P2DC1	P2DC0	0000 0000	63, 200
SSP2BUF	MSSP2 Rec	eive Buffer/Tra	ansmit Registe	er	•		•		XXXX XXXX	63, 265
SSP2ADD	MSSP2 Add	ress Register	(I <sup>2</sup> C™ Slave n	node), MSSP2	Baud Rate Re	eload Register	(I <sup>2</sup> C Master m	node)	0000 0000	63, 265
SSP2STAT	SMP	CKE	D/A	Р	S	R/W	UA	BF	0000 0000	63, 256
SSP2CON1	WCOL	SSPOV	SSPEN	СКР	SSPM3	SSPM2	SSPM1	SSPM0	0000 0000	63, 257, 267
SSP2CON2	GCEN	ACKSTAT	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN	0000 0000	63, 268
	GCEN	ACKSTAT	ADMSK5 <sup>(4)</sup>	ADMSK4 <sup>(4)</sup>	ADMSK3 <sup>(4)</sup>	ADMSK2 <sup>(4)</sup>	ADMSK1 <sup>(4)</sup>	SEN		,
EDATA				er (EDATA<7:0		-		I	XXXX XXXX	63, 209
EIR	_	PKTIF	DMAIF	LINKIF	TXIF	_	TXERIF	RXERIF	-000 0-00	63, 227
ECON2	AUTOINC	PKTDEC	ETHEN	_	_	_	_	_	100	63, 214
LOUNZ	AUTOINC	FRIDEG		_		_	_	_	+00	03, 2

Legend: x = unknown, u = unchanged, - = unimplemented, read as '0', q = value depends on condition, r = reserved bit, do not modify. Shaded cells are unimplemented, read as '0'.

**Note 1:** Bit 7 and bit 6 are cleared by user software or by a POR.

2: Bit 21 of the PC is only available in Serial Programming modes.

3: Reset value is '0' when Two-Speed Start-up is enabled and '1' if disabled.

4: Alternate names and definitions for these bits when the MSSP module is operating in  $I^2C^{TM}$  Slave mode.

5: These bits and/or registers are only available in 100-pin devices; otherwise, they are unimplemented and read as '0'. Reset values shown apply only to 100-pin devices.

6: These bits and/or registers are only available in 80-pin and 100-pin devices; in 64-pin devices, they are unimplemented and read as '0'. Reset values are shown for 100-pin devices.

7: In Microcontroller mode, the bits in this register are unwritable and read as '0'.

8: PLLEN is only available when either ECPLL or HSPLL Oscillator mode is selected; otherwise, read as '0'.

File Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Values on POR, BOR	Details on Page:
ESTAT	—	BUFER	—	r	—	RXBUSY	TXABRT	PHYRDY	-0-0 -000	63, 214
EIE	_	PKTIE	DMAIE	LINKIE	TXIE	_	TXERIE	RXERIE	-000 0-00	63, 226
EDMACSH	DMA Check	sum Register I	High Byte						0000 0000	63, 251
EDMACSL	DMA Check	sum Register I	_ow Byte						0000 0000	63, 251
EDMADSTH	_	_	_	DMA Destina	tion Register I	High Byte			0 0000	63, 251
EDMADSTL	DMA Destina	ation Register	Low Byte						0000 0000	63, 251
EDMANDH	_	_	_	DMA End Re	gister High By	0 0000	63, 251			
EDMANDL	DMA End Re	egister Low By	rte				0000 0000	63, 251		
EDMASTH	_	—	_	DMA Start Re	egister High B	yte			0 0000	63, 251
EDMASTL	DMA Start R	egister Low B	yte						0000 0000	63, 251
ERXWRPTH	_	—	—	Receive Buff	er Write Pointe	er High Byte			0 0000	63, 211
ERXWRPTL	Receive Buf	fer Write Point	er Low Byte						0000 0000	63, 211
ERXRDPTH	_	_	_	Receive Buffe	er Read Pointe	er High Byte			0 0101	63, 211
ERXRDPTL	Receive Buf	fer Read Point	er Low Byte						1111 1010	63, 211
ERXNDH	_	_	_	Receive End	Register High	Byte			1 1111	63, 211
ERXNDL	Receive End	Register Low	Byte						1111 1111	63, 211
ERXSTH	— — Receive Start Register High Byte							0 0101	63, 211	
ERXSTL	Receive Start Register Low Byte							1111 1010	63, 211	
ETXNDH	_	_	_	Transmit End	Register High	n Byte			0 0000	64, 212
ETXNDL	Transmit En	d Register Lov	v Byte						0000 0000	64, 212
ETXSTH	_	—	—	Transmit Star	t Register Hig	h Byte			0 0000	64, 212
ETXSTL	Transmit Sta	rt Register Lo	w Byte						0000 0000	64, 212
EWRPTH	_	—	—	Buffer Write F	Pointer High B	yte			0 0000	64, 209
EWRPTL	Buffer Write	Pointer Low B	yte						0000 0000	64, 209
EPKTCNT	Ethernet Pac	cket Count Re	gister						0000 0000	64, 238
ERXFCON	UCEN	ANDOR	CRCEN	PMEN	MPEN	HTEN	MCEN	BCEN	1010 0001	64, 246
EPMOH	_	_	_	Pattern Matc	h Offset Regis	ter High Byte		•	0 0000	64, 249
EPMOL	Pattern Mate	ch Offset Regis	ster Low Byte						0000 0000	64, 249
EPMCSH	Pattern Mate	ch Checksum I	Register High	Byte					0000 0000	64, 249
EPMCSL	Pattern Mate	ch Checksum I	Register Low	Byte					0000 0000	64, 249
EPMM7	Pattern Mate	ch Mask Regis	ter Byte 7						0000 0000	64, 249
EPMM6	Pattern Match Mask Register Byte 6								0000 0000	64, 249
EPMM5	Pattern Match Mask Register Byte 5								0000 0000	64, 249
EPMM4	Pattern Match Mask Register Byte 4								0000 0000	64, 249
EPMM3	Pattern Match Mask Register Byte 3								0000 0000	64, 249
EPMM2	Pattern Match Mask Register Byte 2								0000 0000	64, 249
EPMM1	Pattern Match Mask Register Byte 1								0000 0000	64, 249
EPMM0	Pattern Mate	ch Mask Regis	ter Byte 0						0000 0000	64, 249

### TABLE 5-5: REGISTER FILE SUMMARY (PIC18F97J60 FAMILY) (CONTINUED)

Legend: x = unknown, u = unchanged, - = unimplemented, read as '0', q = value depends on condition, r = reserved bit, do not modify. Shaded cells are unimplemented, read as '0'.

Note 1: Bit 7 and bit 6 are cleared by user software or by a POR.

2: Bit 21 of the PC is only available in Serial Programming modes.

3: Reset value is '0' when Two-Speed Start-up is enabled and '1' if disabled.

**4:** Alternate names and definitions for these bits when the MSSP module is operating in  $l^2C^{TM}$  Slave mode.

5: These bits and/or registers are only available in 100-pin devices; otherwise, they are unimplemented and read as '0'. Reset values shown apply only to 100-pin devices.

6: These bits and/or registers are only available in 80-pin and 100-pin devices; in 64-pin devices, they are unimplemented and read as '0'. Reset values are shown for 100-pin devices.

7: In Microcontroller mode, the bits in this register are unwritable and read as '0'.

8: PLLEN is only available when either ECPLL or HSPLL Oscillator mode is selected; otherwise, read as '0'.

File Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Values on POR, BOR	Details on Page:
EHT7	Hash Table	Register Byte	7						0000 0000	64, 245
EHT6	Hash Table	Register Byte	6						0000 0000	64, 245
EHT5	Hash Table	Register Byte	5						0000 0000	64, 245
EHT4	Hash Table	Register Byte	4						0000 0000	64, 245
EHT3	Hash Table	Register Byte		0000 0000	64, 245					
EHT2	Hash Table	Register Byte 2	2						0000 0000	64, 245
EHT1	Hash Table	Register Byte	1						0000 0000	64, 245
EHT0	Hash Table	Register Byte	0						0000 0000	64, 245
MIRDH	MII Read Da	ata Register Hi	gh Byte						0000 0000	64, 218
MIRDL	MII Read Da	ata Register Lo	ow Byte						0000 0000	64, 218
MIWRH	MII Write Da	ta Register Hi	gh Byte						0000 0000	64, 218
MIWRL	MII Write Da	III Write Data Register Low Byte								64, 218
MIREGADR	—	— — MII Address Register								64, 218
MICMD	_	_	_	_	_	_	MIISCAN	MIIRD	00	64, 217
MAMXFLH	Maximum Fi	rame Length R	Register High E	Byte					0000 0110	64, 231
MAMXFLL	Maximum Frame Length Register Low Byte								0000 0000	64, 231
MAIPGH	_	MAC Non Ba	ck-to-Back Inte	er-Packet Gap	Register High	Byte			-000 0000	65, 231
MAIPGL	_	MAC Non Ba	ck-to-Back Inte	er-Packet Gap	Register Low	Byte			-000 0000	65, 231
MABBIPG	_	BBIPG6	BBIPG5	BBIPG4	BBIPG3	BBIPG2	BBIPG1	BBIPG0	-000 0000	65, 232
MACON4	_	DEFER	r	r	—		r	r	-00000	65, 217
MACON3	PADCFG2	PADCFG1	PADCFG0	TXCRCEN	PHDREN	HFRMEN	FRMLNEN	FULDPX	0000 0000	65, 216
MACON1	_	—	—	r	TXPAUS	RXPAUS	PASSALL	MARXEN	0 0000	65, 215
EPAUSH	Pause Time	r Value Registe	er High Byte						0001 0000	65, 244
EPAUSL	Pause Time	r Value Registe	er Low Byte						0000 0000	65, 244
EFLOCON	_	—	—	—	_	r	FCEN1	FCEN0	000	65, 244
MISTAT	—	—	—	—	r	NVALID	SCAN	BUSY	0000	65, 218
MAADR2	MAC Addres	ss Register By	te 2 (MAADR<	<39:32>), OUI	Byte 2				0000 0000	65, 231
MAADR1	MAC Addres	ss Register By	te 1 (MAADR<	<47:40>), OUI	Byte 1				0000 0000	65, 231
MAADR4	MAC Addres	ss Register By	te 4 (MAADR<	<23:16>)					0000 0000	65, 231
MAADR3	MAC Addres	MAC Address Register Byte 3 (MAADR<31:24>), OUI Byte 3								
MAADR6	MAC Addres	AC Address Register Byte 6 (MAADR<7:0>)								
MAADR5	MAC Addres	ss Register By	te 5 (MAADR<	<15:8>)					0000 0000	65, 231

### TABLE 5-5: REGISTER FILE SUMMARY (PIC18F97J60 FAMILY) (CONTINUED)

Legend: x = unknown, u = unchanged, - = unimplemented, read as '0', g = value depends on condition, r = reserved bit, do not modify. Shaded cells are unimplemented, read as '0'.

**Note 1:** Bit 7 and bit 6 are cleared by user software or by a POR.

2: Bit 21 of the PC is only available in Serial Programming modes.

3: Reset value is '0' when Two-Speed Start-up is enabled and '1' if disabled.

4: Alternate names and definitions for these bits when the MSSP module is operating in  $I^2C^{TM}$  Slave mode.

5: These bits and/or registers are only available in 100-pin devices; otherwise, they are unimplemented and read as '0'. Reset values shown apply only to 100-pin devices.

6: These bits and/or registers are only available in 80-pin and 100-pin devices; in 64-pin devices, they are unimplemented and read as '0'. Reset values are shown for 100-pin devices.

7: In Microcontroller mode, the bits in this register are unwritable and read as '0'.

8: PLLEN is only available when either ECPLL or HSPLL Oscillator mode is selected; otherwise, read as '0'.

### 5.3.6 STATUS REGISTER

The STATUS register, shown in Register 5-3, contains the arithmetic status of the ALU. The STATUS register can be the operand for any instruction, as with any other register. If the STATUS register is the destination for an instruction that affects the Z, DC, C, OV or N bits, then the write to these five bits is disabled.

These bits are set or cleared according to the device logic. Therefore, the result of an instruction with the STATUS register as destination may be different than intended. For example, CLRF STATUS will set the Z bit but leave the other bits unchanged. The STATUS

register then reads back as '000u u1uu'. It is recommended, therefore, that only BCF, BSF, SWAPF, MOVFF and MOVWF instructions are used to alter the STATUS register because these instructions do not affect the Z, C, DC, OV or N bits in the STATUS register.

For other instructions not affecting any Status bits, see the instruction set summaries in Table 25-2 and Table 25-3.

Note: The C and DC bits operate as a Borrow and Digit Borrow bit respectively, in subtraction.

### **REGISTER 5-3:** STATUS REGISTER

U-0	U-0	U-0	R/W-x	R/W-x	R/W-x	R/W-x	R/W-x
_	_	_	N	OV	Z	DC <sup>(1)</sup>	C <sup>(2)</sup>
oit 7	Letter and the second sec						bit (
Legend:							
R = Read		W = Writable		•	nented bit, rea		
-n = Valu	e at POR	'1' = Bit is se	t	'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7-5	Unimpleme	ented: Read as	ʻ0'				
bit 4	(ALU MSb = 1 = Result v	sed for signed a	rithmetic (2's d	complement). It	indicates whe	ther the result w	vas negative
oit 3	which cause 1 = Overflow	w bit sed for signed a es the sign bit (b w occurred for s rflow occurred	oit 7 of the resu	ult) to change s	tate.		bit magnitude
bit 2		ult of an arithme	• •		ero		
bit 1	DC: Digit C For ADDWF, 1 = A carry-	arry/Borrow bit <sup>(1</sup> ADDLW, SUBLW a -out from the 4th y-out from the 4	) and SUBWF ins low-order bit	structions: of the result oc			
bit 0	C: Carry/Bc For ADDWF, 1 = A carry-		and SUBWF ins	structions: bit of the result			
Note 1: 2:	For Borrow, the p operand. For rota For Borrow, the p operand. For rota source register.	ate (RRF, RLF) ir polarity is reverse	nstructions, this ed. A subtracti	s bit is loaded v on is executed	vith either bit 4 by adding the	or bit 3 of the s 2's complement	ource register of the second

### 5.4 Data Addressing Modes

Note:	The execution of some instructions in the
	core PIC18 instruction set are changed
	when the PIC18 extended instruction set is
	enabled. See Section 5.6 "Data Memory
	and the Extended Instruction Set" for
	more information.

While the program memory can be addressed in only one way – through the program counter – information in the data memory space can be addressed in several ways. For most instructions, the addressing mode is fixed. Other instructions may use up to three modes, depending on which operands are used and whether or not the extended instruction set is enabled.

The addressing modes are:

- Inherent
- Literal
- Direct
- Indirect

An additional addressing mode, Indexed Literal Offset, is available when the extended instruction set is enabled (XINST Configuration bit = 1). Its operation is discussed in greater detail in **Section 5.6.1 "Indexed Addressing with Literal Offset**".

### 5.4.1 INHERENT AND LITERAL ADDRESSING

Many PIC18 control instructions do not need any argument at all. They either perform an operation that globally affects the device, or they operate implicitly on one register. This addressing mode is known as Inherent Addressing. Examples include SLEEP, RESET and DAW.

Other instructions work in a similar way, but require an additional explicit argument in the opcode. This is known as Literal Addressing mode because they require some literal value as an argument. Examples include ADDLW and MOVLW, which respectively, add or move a literal value to the W register. Other examples include CALL and GOTO, which include a 20-bit program memory address.

#### 5.4.2 DIRECT ADDRESSING

Direct Addressing mode specifies all or part of the source and/or destination address of the operation within the opcode itself. The options are specified by the arguments accompanying the instruction.

In the core PIC18 instruction set, bit-oriented and byte-oriented instructions use some version of Direct Addressing by default. All of these instructions include some 8-bit literal address as their Least Significant Byte. This address specifies either a register address in one of the banks of data RAM (Section 5.3.3 "General Purpose Register File") or a location in the Access Bank (Section 5.3.2 "Access Bank") as the data source for the instruction. The Access RAM bit, 'a', determines how the address is interpreted. When 'a' is '1', the contents of the BSR (Section 5.3.1 "Bank Select Register") are used with the address to determine the complete 12-bit address of the register. When 'a' is '0', the address is interpreted as being a register in the Access Bank. Addressing that uses the Access RAM is sometimes also known as Direct Forced Addressing mode.

A few instructions, such as MOVFF, include the entire 12-bit address (either source or destination) in their opcodes. In these cases, the BSR is ignored entirely.

The destination of the operation's results is determined by the destination bit, 'd'. When 'd' is '1', the results are stored back in the source register, overwriting its original contents. When 'd' is '0', the results are stored in the W register. Instructions without the 'd' argument have a destination that is implicit in the instruction. Their destination is either the target register being operated on or the W register.

### 5.4.3 INDIRECT ADDRESSING

Indirect Addressing mode allows the user to access a location in data memory without giving a fixed address in the instruction. This is done by using File Select Registers (FSRs) as pointers to the locations to be read or written to. Since the FSRs are themselves located in RAM as Special Function Registers, they can also be directly manipulated under program control. This makes FSRs very useful in implementing data structures, such as tables and arrays in data memory.

The registers for Indirect Addressing are also implemented with Indirect File Operands (INDFs) that permit automatic manipulation of the pointer value with auto-incrementing, auto-decrementing or offsetting with another value. This allows for efficient code using loops, such as the example of clearing an entire RAM bank in Example 5-5. It also enables users to perform indexed addressing and other Stack Pointer operations for program memory in data memory.

### EXAMPLE 5-5: HOW TO CLEAR RAM (BANK 1) USING INDIRECT ADDRESSING


	LFSR	FSR0,	100h	;	
NEXT	CLRF	POSTIN	C0	;	Clear INDF
				;	register then
				;	inc pointer
	BTFSS	FSROH,	1	;	All done with
				;	Bank1?
	BRA	NEXT		;	NO, clear next
CONTINUE				;	YES, continue

### 5.4.3.1 FSR Registers and the INDF Operand

At the core of Indirect Addressing are three sets of registers: FSR0, FSR1 and FSR2. Each represents a pair of 8-bit registers: FSRnH and FSRnL. The four upper bits of the FSRnH register are not used, so each FSR pair holds a 12-bit value. This represents a value that can address the entire range of the data memory in a linear fashion. The FSR register pairs, then, serve as pointers to data memory locations.

Indirect Addressing is accomplished with a set of Indirect File Operands: INDF0 through INDF2. These can be thought of as "virtual" registers; they are mapped in the SFR space but are not physically implemented. Reading or writing to a particular INDF register actually accesses its corresponding FSR register pair. A read from INDF1, for example, reads the data at the address indicated by FSR1H:FSR1L. Instructions that use the INDF registers as operands actually use the contents of their corresponding FSR as a pointer to the instruction's target. The INDF operand is just a convenient way of using the pointer.

Because Indirect Addressing uses a full 12-bit address, data RAM banking is not necessary. Thus, the current contents of the BSR and Access RAM bit have no effect on determining the target address.



### 5.4.3.2 FSR Registers and POSTINC, POSTDEC, PREINC and PLUSW

In addition to the INDF operand, each FSR register pair also has four additional indirect operands. Like INDF, these are "virtual" registers that cannot be indirectly read or written to. Accessing these registers actually accesses the associated FSR register pair, but also performs a specific action on its stored value. They are:

- POSTDEC: accesses the FSR value, then automatically decrements it by '1' afterwards
- POSTINC: accesses the FSR value, then automatically increments it by '1' afterwards
- PREINC: increments the FSR value by '1', then uses it in the operation
- PLUSW: adds the signed value of the W register (range of -128 to 127) to that of the FSR and uses the new value in the operation

In this context, accessing an INDF register uses the value in the FSR registers without changing them. Similarly, accessing a PLUSW register gives the FSR value offset by the value in the W register; neither value is actually changed in the operation. Accessing the other virtual registers changes the value of the FSR registers.

Operations on the FSRs with POSTDEC, POSTINC and PREINC affect the entire register pair; that is, rollovers of the FSRnL register from FFh to 00h carry over to the FSRnH register. On the other hand, results of these operations do not change the value of any flags in the STATUS register (e.g., Z, N, OV, etc.).

The PLUSW register can be used to implement a form of Indexed Addressing in the data memory space. By manipulating the value in the W register, users can reach addresses that are fixed offsets from pointer addresses. In some applications, this can be used to implement some powerful program control structure, such as software stacks, inside of data memory.

### 5.4.3.3 Operations by FSRs on FSRs

Indirect Addressing operations that target other FSRs, or virtual registers, represent special cases. For example, using an FSR to point to one of the virtual registers will not result in successful operation. As a specific case, assume that the FSR0H:FSR0L pair contains FE7h, the address of INDF1. Attempts to read the value of the INDF1, using INDF0 as an operand, will return 00h. Attempts to write to INDF1, using INDF0 as the operand, will result in a NOP.

On the other hand, using the virtual registers to write to an FSR pair may not occur as planned. In these cases, the value will be written to the FSR pair but without any incrementing or decrementing. Thus, writing to INDF2 or POSTDEC2 will write the same value to the FSR2H:FSR2L pair.

Since the FSRs are physical registers mapped in the SFR space, they can be manipulated through all direct operations. Users should proceed cautiously when working on these registers, particularly if their code uses Indirect Addressing.

Similarly, operations by Indirect Addressing are generally permitted on all other SFRs. Users should exercise the appropriate caution that they do not inadvertently change settings that might affect the operation of the device.

### 5.5 Program Memory and the Extended Instruction Set

The operation of program memory is unaffected by the use of the extended instruction set.

Enabling the extended instruction set adds five additional two-word commands to the existing PIC18 instruction set: ADDFSR, CALLW, MOVSF, MOVSS and SUBFSR. These instructions are executed as described in Section 5.2.4 "Two-Word Instructions".

### 5.6 Data Memory and the Extended Instruction Set

Enabling the PIC18 extended instruction set (XINST Configuration bit = 1) significantly changes certain aspects of data memory and its addressing. Specifically, the use of the Access Bank for many of the core PIC18 instructions is different. This is due to the introduction of a new addressing mode for the data memory space. This mode also alters the behavior of Indirect Addressing using FSR2 and its associated operands.

What does not change is just as important. The size of the data memory space is unchanged, as well as its linear addressing. The SFR map remains the same. Core PIC18 instructions can still operate in both Direct and Indirect Addressing mode; inherent and literal instructions do not change at all. Indirect Addressing with FSR0 and FSR1 also remains unchanged.

### 5.6.1 INDEXED ADDRESSING WITH LITERAL OFFSET

Enabling the PIC18 extended instruction set changes the behavior of Indirect Addressing using the FSR2 register pair and its associated file operands. Under the proper conditions, instructions that use the Access Bank – that is, most bit-oriented and byte-oriented instructions – can invoke a form of Indexed Addressing using an offset specified in the instruction. This special addressing mode is known as Indexed Addressing with Literal Offset, or Indexed Literal Offset mode.

When using the extended instruction set, this addressing mode requires the following:

- The use of the Access Bank is forced ('a' = 0); and
- The file address argument is less than or equal to 5Fh.

Under these conditions, the file address of the instruction is not interpreted as the lower byte of an address (used with the BSR in Direct Addressing) or as an 8-bit address in the Access Bank. Instead, the value is interpreted as an offset value to an Address Pointer specified by FSR2. The offset and the contents of FSR2 are added to obtain the target address of the operation.

### 5.6.2 INSTRUCTIONS AFFECTED BY INDEXED LITERAL OFFSET MODE

Any of the core PIC18 instructions that can use Direct Addressing are potentially affected by the Indexed Literal Offset Addressing mode. This includes all byte-oriented and bit-oriented instructions, or almost half of the standard PIC18 instruction set. Instructions that only use Inherent or Literal Addressing modes are unaffected.

Additionally, byte-oriented and bit-oriented instructions are not affected if they use the Access Bank (Access RAM bit is '1') or include a file address of 60h or above. Instructions meeting these criteria will continue to execute as before. A comparison of the different possible addressing modes when the extended instruction set is enabled is shown in Figure 5-10.

Those who desire to use byte-oriented or bit-oriented instructions in the Indexed Literal Offset mode should note the changes to assembler syntax for this mode. This is described in more detail in **Section 25.2.1** "Extended Instruction Syntax".


### FIGURE 5-10: COMPARING ADDRESSING OPTIONS FOR BIT-ORIENTED AND BYTE-ORIENTED INSTRUCTIONS (EXTENDED INSTRUCTION SET ENABLED)

### **EXAMPLE INSTRUCTION:** ADDWF, f, d, a (Opcode: 0010 01da ffff ffff)

#### When a = 0 and $f \ge 60h$ :

The instruction executes in Direct Forced mode. 'f' is interpreted as a location in the Access RAM between 060h and FFFh. This is the same as locations F60h to FFFh (Bank 15) of data memory.

Locations below 060h are not available in this addressing mode.




The instruction executes in Indexed Literal Offset mode. 'f' is interpreted as an offset to the address value in FSR2. The two are added together to obtain the address of the target register for the instruction. The address can be anywhere in the data memory space.

Note that in this mode, the correct syntax is now: ADDWF [k], d where 'k' is the same as 'f'.

#### When a = 1 (all values of f):

The instruction executes in Direct mode (also known as Direct Long mode). 'f' is interpreted as a location in one of the 16 banks of the data memory space. The bank is designated by the Bank Select Register (BSR). The address can be in any implemented bank in the data memory space.



### 5.6.3 MAPPING THE ACCESS BANK IN INDEXED LITERAL OFFSET MODE


The use of Indexed Literal Offset Addressing mode effectively changes how the lower part of Access RAM (00h to 5Fh) is mapped. Rather than containing just the contents of the bottom part of Bank 0, this mode maps the contents from Bank 0 and a user-defined "window" that can be located anywhere in the data memory space. The value of FSR2 establishes the lower boundary of the addresses mapped into the window, while the upper boundary is defined by FSR2 plus 95 (5Fh). Addresses in the Access RAM above 5Fh are mapped as previously described (see **Section 5.3.2** "**Access Bank**"). An example of Access Bank remapping in this addressing mode is shown in Figure 5-11.

Remapping of the Access Bank applies *only* to operations using the Indexed Literal Offset mode. Operations that use the BSR (Access RAM bit is '1') will continue to use Direct Addressing as before. Any indirect or indexed operation that explicitly uses any of the indirect file operands (including FSR2) will continue to operate as standard Indirect Addressing. Any instruction that uses the Access Bank, but includes a register address of greater than 05Fh, will use Direct Addressing and the normal Access Bank map.

### 5.6.4 BSR IN INDEXED LITERAL OFFSET MODE

Although the Access Bank is remapped when the extended instruction set is enabled, the operation of the BSR remains unchanged. Direct Addressing, using the BSR to select the data memory bank, operates in the same manner as previously described.

### FIGURE 5-11: REMAPPING THE ACCESS BANK WITH INDEXED LITERAL OFFSET ADDRESSING



NOTES:

### 6.0 FLASH PROGRAM MEMORY

The Flash program memory is readable, writable and erasable during normal operation over the entire VDD range.

A read from program memory is executed on one byte at a time. A write to program memory is executed on blocks of 64 bytes at a time. Program memory is erased in blocks of 1024 bytes at a time. A Bulk Erase operation may not be issued from user code.

Writing or erasing program memory will cease instruction fetches until the operation is complete. The program memory cannot be accessed during the write or erase, therefore, code cannot execute. An internal programming timer terminates program memory writes and erases.

A value written to program memory does not need to be a valid instruction. Executing a program memory location that forms an invalid instruction results in a NOP.

### 6.1 Table Reads and Table Writes

In order to read and write program memory, there are two operations that allow the processor to move bytes between the program memory space and the data RAM:

- Table Read (TBLRD)
- Table Write (TBLWT)


The program memory space is 16 bits wide, while the data RAM space is 8 bits wide. Table reads and table writes move data between these two memory spaces through an 8-bit register (TABLAT).

Table read operations retrieve data from program memory and place it into the data RAM space. Figure 6-1 shows the operation of a table read with program memory and data RAM.

Table write operations store data from the data memory space into holding registers in program memory. The procedure to write the contents of the holding registers into program memory is detailed in **Section 6.5 "Writing to Flash Program Memory"**. Figure 6-2 shows the operation of a table write with program memory and data RAM.


Table operations work with byte entities. A table block containing data, rather than program instructions, is not required to be word-aligned. Therefore, a table block can start and end at any byte address. If a table write is being used to write executable code into program memory, program instructions will need to be word-aligned.

FIGURE 6-1: TABLE READ OPERATION



© 2007 Microchip Technology Inc.

### FIGURE 6-2: TABLE WRITE OPERATION



### 6.2 Control Registers

Several control registers are used in conjunction with the  ${\tt TBLRD}$  and  ${\tt TBLWT}$  instructions. These include the:

- EECON1 register
- · EECON2 register
- TABLAT register
- TBLPTR registers

### 6.2.1 EECON1 AND EECON2 REGISTERS

The EECON1 register (Register 6-1) is the control register for memory accesses. The EECON2 register is not a physical register; it is used exclusively in the memory write and erase sequences. Reading EECON2 will read all '0's.

The FREE bit, when set, will allow a program memory erase operation. When FREE is set, the erase operation is initiated on the next WR command. When FREE is clear, only writes are enabled. The WREN bit, when set, will allow a write operation. On power-up, the WREN bit is clear. The WRERR bit is set in hardware when the WR bit is set, and cleared when the internal programming timer expires and the write operation is complete.

**Note:** During normal operation, the WRERR is read as '1'. This can indicate that a write operation was prematurely terminated by a Reset, or a write operation was attempted improperly.

The WR control bit initiates write operations. The bit cannot be cleared, only set, in software; it is cleared in hardware at the completion of the write operation.

### REGISTER 6-1: EECON1: EEPROM CONTROL REGISTER 1

U-0	U-0	U-0	R/W-0	R/W-x	R/W-0	R/S-0	U-0
—	—	—	FREE	WRERR	WREN	WR	—
bit 7							bit 0

Legend:	S = Settable bit		
R = Readable bit	W = Writable bit	U = Unimplemented bit	t, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-5	Unimplemented: Read as '0'
bit 4	FREE: Flash Row Erase Enable bit
	1 = Erase the program memory row addressed by TBLPTR on the next WR command (cleared by completion of erase operation)
	0 = Perform write-only
bit 3	WRERR: Flash Program Error Flag bit
	<ul> <li>1 = A write operation is prematurely terminated (any Reset during self-timed programming in normal operation, or an improper write attempt)</li> </ul>
	0 = The write operation completed
bit 2	WREN: Flash Program Write Enable bit
	1 = Allows write cycles to Flash program memory
	<ul><li>Inhibits write cycles to Flash program memory</li></ul>
bit 1	WR: Write Control bit
	<ul> <li>1 = Initiates a program memory erase cycle or write cycle.</li> <li>(The operation is self-timed and the bit is cleared by hardware once write is complete.</li> <li>The WR bit can only be set (not cleared) in software.)</li> </ul>
	0 = Write cycle complete
bit 0	Unimplemented: Read as '0'

### 6.2.2 TABLE LATCH REGISTER (TABLAT)

The Table Latch (TABLAT) is an 8-bit register mapped into the SFR space. The Table Latch register is used to hold 8-bit data during data transfers between program memory and data RAM.

#### 6.2.3 TABLE POINTER REGISTER (TBLPTR)

The Table Pointer (TBLPTR) register addresses a byte within the program memory. The TBLPTR is comprised of three SFR registers: Table Pointer Upper Byte, Table Pointer High Byte and Table Pointer Low Byte (TBLPTRU:TBLPTRH:TBLPTRL). These three registers join to form a 22-bit wide pointer. The low-order 21 bits allow the device to address up to 2 Mbytes of program memory space. The 22nd bit allows access to the Device ID and Configuration bits.

The Table Pointer register, TBLPTR, is used by the TBLRD and TBLWT instructions. These instructions can update the TBLPTR in one of four ways based on the table operation. These operations are shown in Table 6-1. The table operations on the TBLPTR only affect the low-order 21 bits.

### 6.2.4 TABLE POINTER BOUNDARIES

TBLPTR is used in reads, writes and erases of the Flash program memory.

When a TBLRD is executed, all 22 bits of the TBLPTR determine which byte is read from program memory into TABLAT.


When a TBLWT is executed, the six LSbs of the Table Pointer register (TBLPTR<5:0>) determine which of the 64 program memory holding registers is written to. When the timed write to program memory begins (via the WR bit), the 15 MSbs of the TBLPTR (TBLPTR<20:6>) determine which program memory block of 64 bytes is written to. For more detail, see **Section 6.5 "Writing to Flash Program Memory"**.

When an erase of program memory is executed, the 11 MSbs of the Table Pointer register (TBLPTR<20:10>) point to the 1024-byte block that will be erased. The Least Significant bits (TBLPTR<9:0>) are ignored.

Figure 6-3 describes the relevant boundaries of TBLPTR based on Flash program memory operations.

Example	Operation on Table Pointer
TBLRD* TBLWT*	TBLPTR is not modified
TBLRD*+ TBLWT*+	TBLPTR is incremented after the read/write
TBLRD*- TBLWT*-	TBLPTR is decremented after the read/write
TBLRD+* TBLWT+*	TBLPTR is incremented before the read/write

#### FIGURE 6-3: TABLE POINTER BOUNDARIES BASED ON OPERATION




### 6.3 Reading the Flash Program Memory

The TBLRD instruction is used to retrieve data from program memory and places it into data RAM. Table reads from program memory are performed one byte at a time.

TBLPTR points to a byte address in program space. Executing TBLRD places the byte pointed to into TABLAT. In addition, TBLPTR can be modified automatically for the next table read operation.

The internal program memory is typically organized by words. The Least Significant bit of the address selects between the high and low bytes of the word. Figure 6-4 shows the interface between the internal program memory and the TABLAT.

#### FIGURE 6-4: READS FROM FLASH PROGRAM MEMORY



#### EXAMPLE 6-1: READING A FLASH PROGRAM MEMORY WORD

	MOVLW MOVWF MOVWF MOVLW MOVLW MOVWF	CODE_ADDR_UPPER TBLPTRU CODE_ADDR_HIGH TBLPTRH CODE_ADDR_LOW TBLPTRL	; Load TBLPTR with the base ; address of the word
READ_WORD			
	TBLRD*+		; read into TABLAT and increment
	MOVF	TABLAT, W	; get data
	MOVWF	WORD_EVEN	
	TBLRD*+		; read into TABLAT and increment
	MOVFW	TABLAT, W	; get data
	MOVF	WORD_ODD	

### 6.4 Erasing Flash Program Memory

The minimum erase block is 1024 bytes. Only through the use of an external programmer, or through ICSP control, can larger blocks of program memory be Bulk Erased. Word Erase in the Flash array is not supported.

When initiating an erase sequence from the microcontroller itself, a block of 1024 bytes of program memory is erased. The Most Significant 11 bits of the TBLPTR<20:10> point to the block being erased. TBLPTR<9:0> are ignored.

The EECON1 register commands the erase operation. The WREN bit must be set to enable write operations. The FREE bit is set to select an erase operation.

For protection, the write initiate sequence for EECON2 must be used.

A long write is necessary for erasing the internal Flash. Instruction execution is halted while in a long write cycle. The long write will be terminated by the internal programming timer. An on-chip timer controls the erase time. The write/erase voltages are generated by an on-chip charge pump, rated to operate over most of the voltage range of the device. See parameter D132B (VPEW) for specific limits.

### 6.4.1 FLASH PROGRAM MEMORY ERASE SEQUENCE

The sequence of events for erasing a block of internal program memory location is:

- 1. Load Table Pointer register with address of row being erased.
- 2. Set the EECON1 register for the erase operation:
  - set WREN bit to enable writes;
  - set FREE bit to enable the erase.
- 3. Disable interrupts.
- 4. Write 55h to EECON2.
- 5. Write 0AAh to EECON2.
- 6. Set the WR bit. This will begin the Row Erase cycle.
- 7. The CPU will stall for duration of the erase.
- 8. Re-enable interrupts.

#### EXAMPLE 6-2: ERASING A FLASH PROGRAM MEMORY ROW

	MOVLW MOVWF MOVLW MOVWF MOVLW MOVWF	CODE_ADDR_UPPER TBLPTRU CODE_ADDR_HIGH TBLPTRH CODE_ADDR_LOW TBLPTRL	; load TBLPTR with the base ; address of the memory block
ERASE_ROW	5.65		
	BSF	EECON1, WREN	; enable write to memory
	BSF	EECON1, FREE	; enable Row Erase operation
	BCF	INTCON, GIE	; disable interrupts
Required	MOVLW	55h	
Sequence	MOVWF	EECON2	; write 55h
	MOVLW	0AAh	
	MOVWF	EECON2	; write OAAh
	BSF	EECON1, WR	; start erase (CPU stall)
	BSF	INTCON, GIE	; re-enable interrupts

### 6.5 Writing to Flash Program Memory

The minimum programming block is 32 words or 64 bytes. Word or byte programming is not supported.


Table writes are used internally to load the holding registers needed to program the Flash memory. There are 64 holding registers used by the table writes for programming.

Since the Table Latch (TABLAT) is only a single byte, the TBLWT instruction may need to be executed 64 times for each programming operation. All of the table write operations will essentially be short writes because only the holding registers are written. At the end of updating the 64 holding registers, the EECON1 register must be written to in order to start the programming operation with a long write.

The long write is necessary for programming the internal Flash. Instruction execution is halted while in a long write cycle. The long write will be terminated by the internal programming timer.

An on-chip timer controls the write time. The write/erase voltages are generated by an on-chip charge pump, rated to operate over most of the voltage range of the device. See parameter D132B (VPEW) for specific limits.

- Note 1: Unlike previous PIC MCU devices, members of the PIC18F97J60 family do not reset the holding registers after a write occurs. The holding registers must be cleared or overwritten before a programming sequence.
  - 2: To maintain the endurance of the program memory cells, each Flash byte should not be programmed more than one time between erase operations. Before attempting to modify the contents of the target cell a second time, a Row Erase of the target row, or a Bulk Erase of the entire memory, must be performed.



### FIGURE 6-5: TABLE WRITES TO FLASH PROGRAM MEMORY

### 6.5.1 FLASH PROGRAM MEMORY WRITE SEQUENCE

The sequence of events for programming an internal program memory location should be:

- 1. If the section of program memory to be written to has been programmed previously, then the memory will need to be erased before the write occurs (see Section 6.4.1 "Flash Program Memory Erase Sequence").
- 2. Write the 64 bytes into the holding registers with auto-increment.
- 3. Set the WREN bit to enable byte writes.
- 4. Disable interrupts.

- 5. Write 55h to EECON2.
- 6. Write AAh to EECON2.
- 7. Set the WR bit. This will begin the write cycle.
- 8. The CPU will stall for duration of the write.
- 9. Re-enable interrupts.
- 10. Verify the memory (table read).

An example of the required code is shown in Example 6-3.

**Note:** Before setting the WR bit, the Table Pointer address needs to be within the intended address range of the 64 bytes in the holding register.

EXAMPLE 6-3:	WRITING TO FLASH PROGRAM MEMORY

	MOVLW	CODE ADDR UPPER	; Load TBLPTR with the base
	MOVWF	TBLPTRU	; address of the memory block
	MOVLW	CODE ADDR HIGH	
	MOVWF	TBLPTRH	
	MOVLW	CODE ADDR LOW	
	MOVWF	TBLPTRL	
ERASE BLOCK			
	BSF	EECON1, WREN	; enable write to memory
	BSF	EECON1, FREE	; enable Row Erase operation
	BCF	INTCON, GIE	; disable interrupts
	MOVLW	55h	,
	MOVWF	EECON2	; write 55h
	MOVLW	OAAh	,
	MOVWF	EECON2	; write OAAh
	BSF	EECON1, WR	; start erase (CPU stall)
	BSF	INTCON, GIE	; re-enable interrupts
	MOVLW	D'16'	, ic enable incertapes
	MOVLW MOVWF		; Need to write 16 blocks of 64 to write
	MOVWE	WRITE_COUNTER	
			; one erase block of 1024
RESTART_BUFFER	MONTH	D'64'	
	MOVLW MOVWF		
		COUNTER	. point to buffor
	MOVLW	BUFFER_ADDR_HIGH FSR0H	; point to buffer
	MOVWF		
	MOVLW	BUFFER_ADDR_LOW	
	MOVWF	FSROL	
FILL_BUFFER			, wood the new data from TOG ODT
	•••		; read the new data from I2C, SPI,
NOTHE DIFEED			; PSP, USART, etc.
WRITE_BUFFER	MOVLW	D'64	· number of butes in holding register
	MOVLW MOVWF		; number of bytes in holding register
WRITER RYEE TO URECO		COUNTER	
WRITE_BYTE_TO_HREGS		DOGETNICO MIDEC	, not low hote of buffer date
	MOVFF	POSTINCO, WREG	; get low byte of buffer data
	MOVWF	TABLAT	; present data to table latch
	TBLWT+*		; write data, perform a short write
	DECEC	COUNTER	; to internal TBLWT holding register.
	DECFSZ	COUNTER	; loop until buffers are full
	BRA	WRITE_BYTE_TO_HREGS	
PROGRAM_MEMORY	5.65		
	BSF	EECON1, WREN	; enable write to memory
	BCF	INTCON, GIE	; disable interrupts
	MOVLW	55h	
Required	MOVWF	EECON2	; write 55h
Sequence	MOVLW	OAAh	
	MOVWF	EECON2	; write OAAh
	BSF	EECON1, WR	; start program (CPU stall)
	BSF	INTCON, GIE	; re-enable interrupts
	BCF	EECON1, WREN	; disable write to memory
	DECFSZ	WRITE_COUNTER	; done with one write cycle
	BRA	RESTART_BUFFER	; if not done replacing the erase block

### 6.5.2 WRITE VERIFY

Depending on the application, good programming practice may dictate that the value written to the memory should be verified against the original value. This should be used in applications where excessive writes can stress bits near the specification limit.

### 6.5.3 UNEXPECTED TERMINATION OF WRITE OPERATION

If a write is terminated by an unplanned event, such as loss of power or an unexpected Reset, the memory location just programmed should be verified and reprogrammed if needed. If the write operation is interrupted by a MCLR Reset, or a WDT Time-out Reset during normal operation, the user can check the WRERR bit and rewrite the location(s) as needed.

### 6.5.4 PROTECTION AGAINST SPURIOUS WRITES

To protect against spurious writes to Flash program memory, the write initiate sequence must also be followed. See **Section 24.0** "**Special Features of the CPU**" for more details.

### 6.6 Flash Program Operation During Code Protection

See Section 24.6 "Program Verification and Code Protection" for details on code protection of Flash program memory.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
TBLPTRU	—	_	bit 21	Program Me	emory Table F	Pointer Uppe	r Byte (TBLP	TR<20:16>)	59
TBPLTRH	Program Memory Table Pointer High Byte (TBLPTR<15:8>)						59		
TBLPTRL	Program M	Program Memory Table Pointer Low Byte (TBLPTR<7:0>)							59
TABLAT	Program M	Program Memory Table Latch							59
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
EECON2	EEPROM Control Register 2 (not a physical register)							61	
EECON1	_	_		FREE	WRERR	WREN	WR	_	61

### TABLE 6-2: REGISTERS ASSOCIATED WITH PROGRAM FLASH MEMORY

Legend: — = unimplemented, read as '0'. Shaded cells are not used during Flash/EEPROM access.

NOTES:

### 7.0 EXTERNAL MEMORY BUS

Note:	The external		m	emory	bus	is	not
	implemented		on	64-pin	and	80	)-pin
	devic	es.					

The External Memory Bus (EMB) allows the device to access external memory devices (such as Flash, EPROM, SRAM, etc.) as program or data memory. It supports both 8 and 16-Bit Data Width modes, and three address widths of up to 20 bits.

The bus is implemented with 28 pins, multiplexed across four I/O ports. Three ports (PORTD, PORTE and PORTH) are multiplexed with the address/data bus for a total of 20 available lines, while PORTJ is multiplexed with the bus control signals.

A list of the pins and their functions is provided in Table 7-1.

Name	Port	Bit	External Memory Bus Function
RD0/AD0	PORTD	0	Address bit 0 or Data bit 0
RD1/AD1	PORTD	1	Address bit 1 or Data bit 1
RD2/AD2	PORTD	2	Address bit 2 or Data bit 2
RD3/AD3	PORTD	3	Address bit 3 or Data bit 3
RD4/AD4	PORTD	4	Address bit 4 or Data bit 4
RD5/AD5	PORTD	5	Address bit 5 or Data bit 5
RD6/AD6	PORTD	6	Address bit 6 or Data bit 6
RD7/AD7	PORTD	7	Address bit 7 or Data bit 7
RE0/AD8	PORTE	0	Address bit 8 or Data bit 8
RE1/AD9	PORTE	1	Address bit 9 or Data bit 9
RE2/AD10	PORTE	2	Address bit 10 or Data bit 10
RE3/AD11	PORTE	3	Address bit 11 or Data bit 11
RE4/AD12	PORTE	4	Address bit 12 or Data bit 12
RE5/AD13	PORTE	5	Address bit 13 or Data bit 13
RE6/AD14	PORTE	6	Address bit 14 or Data bit 14
RE7/AD15	PORTE	7	Address bit 15 or Data bit 15
RH0/A16	PORTH	0	Address bit 16
RH1/A17	PORTH	1	Address bit 17
RH2/A18	PORTH	2	Address bit 18
RH3/A19	PORTH	3	Address bit 19
RJ0/ALE	PORTJ	0	Address Latch Enable (ALE) Control bit
RJ1/OE	PORTJ	1	Output Enable (OE) Control bit
RJ2/WRL	PORTJ	2	Write Low (WRL) Control bit
RJ3/WRH	PORTJ	3	Write High (WRH) Control bit
RJ4/BA0	PORTJ	4	Byte Address (BA0) bit 0
RJ5/CE	PORTJ	5	Chip Enable (CE) Control bit
RJ6/LB	PORTJ	6	Lower Byte Enable (LB) Control bit
RJ7/UB	PORTJ	7	Upper Byte Enable (UB) Control bit

### TABLE 7-1:PIC18F96J60/96J65/97J60 EXTERNAL MEMORY BUS – I/O PORT FUNCTIONS

**Note:** For the sake of clarity, only I/O port and external bus assignments are shown here. One or more additional multiplexed features may be available on some pins.

### 7.1 External Memory Bus Control

The operation of the interface is controlled by the MEMCON register (Register 7-1). This register is available in all program memory operating modes except Microcontroller mode. In this mode, the register is disabled and cannot be written to.

The EBDIS bit (MEMCON<7>) controls the operation of the bus and related port functions. Clearing EBDIS enables the interface and disables the I/O functions of the ports, as well as any other functions multiplexed to those pins. Setting the bit enables the I/O ports and other functions, but allows the interface to override everything else on the pins when an external memory operation is required. By default, the external bus is always enabled and disables all other I/Os. The operation of the EBDIS bit is also influenced by the program memory mode being used. This is discussed in more detail in Section 7.5 "Program Memory Modes and the External Memory Bus".

The WAIT bits allow for the addition of wait states to external memory operations. The use of these bits is discussed in **Section 7.3 "Wait States"**.

The WM bits select the particular operating mode used when the bus is operating in 16-Bit Data Width mode. These operating modes are discussed in more detail in **Section 7.6 "16-Bit Data Width Modes"**. The WM bits have no effect when an 8-Bit Data Width mode is selected.

### REGISTER 7-1: MEMCON: EXTERNAL MEMORY BUS CONTROL REGISTER

R/W-0	U-0	R/W-0	R/W-0	U-0	U-0	R/W-0	R/W-0
EBDIS	_	WAIT1	WAIT0		_	WM1	WM0
bit 7				bit 0			
Legend:							
R = Readable bit		W = Writable bit		U = Unimplemented bit, read as '0'			
n = Value at POP		'1' - Bit is set		'0' - Bit is cleared		x = Bit is unknown	

-n = Value	at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown
L:1 7				
bit 7	EBDIS: I	External Bus Disable bit		
		ernal bus enabled when micr ers are mapped as I/O ports		nemory; otherwise, all external bus
0 = External bus always enabled, I/O ports are disabled				

bit 6	Unimplemented: Read as '0'

bit 5-4	WAIT1:WAIT0: Table Reads and Writes Bus Cycle Wait Count bits

- 11 = Table reads and writes will wait 0 Tcy
- 10 = Table reads and writes will wait 1 TCY
- 01 = Table reads and writes will wait 2 TCY
- 00 = Table reads and writes will wait 3 TCY

#### bit 3-2 Unimplemented: Read as '0'

#### bit 1-0 WM1:WM0: TBLWT Operation with 16-Bit Data Bus Width Select bits

- 1x = Word Write mode: WRH active when TABLAT is written to and TBLPTR contains an odd address. When TBLPTR contains an even address, writing to TABLAT loads a holding latch with the value written.
- 01 = Byte Select mode: TABLAT data copied on both MSB and LSB; WRH and (UB or LB) will activate
- 00 = Byte Write mode: TABLAT data copied on both MSB and LSB; WRH or WRL will activate

# 7.2 Address and Data Width

The PIC18F97J60 family of devices can be independently configured for different address and data widths on the same memory bus. Both address and data widths are set by Configuration bits in the CONFIG3L register. As Configuration bits, this means that these options can only be configured by programming the device and are not controllable in software.

The BW bit selects an 8-bit or 16-bit data bus width. Setting this bit (default) selects a data width of 16 bits.

The EMB1:EMB0 bits determine both the program memory operating mode and the address bus width. The available options are 20-bit, 16-bit and 12-bit, as well as the default Microcontroller mode (external bus disabled). Selecting a 16-bit or 12-bit width makes a corresponding number of high-order lines available for I/O functions. These pins are no longer affected by the setting of the EBDIS bit. For example, selecting a 16-Bit Addressing mode (EMB1:EMB0 = 01) disables A19:A16 and allows the PORTH<3:0> bits to function without interruptions from the bus. Using the smaller address widths allows users to tailor the memory bus to the size of the external memory space for a particular design while freeing up pins for dedicated I/O operation.

Because the EMB bits have the effect of disabling pins for memory bus operations, it is important to always select an address width at least equal to the data width. If a 12-bit address width is used with a 16-bit data width, the upper four bits of data will not be available on the bus.

All combinations of address and data widths require multiplexing of address and data information on the same lines. The address and data multiplexing, as well as I/O ports made available by the use of smaller address widths, are summarized in Table 7-2.

# 7.2.1 ADDRESS SHIFTING ON THE EXTERNAL BUS

By default, the address presented on the external bus is the value of the PC. In practical terms, this means that addresses in the external memory device below the top of on-chip memory are unavailable to the microcontroller. To access these physical locations, the glue logic between the microcontroller and the external memory must somehow translate addresses.

To simplify the interface, the external bus offers an extension of Extended Microcontroller mode that automatically performs address shifting. This feature is controlled by the EASHFT Configuration bit. Setting this bit offsets addresses on the bus by the size of the microcontroller's on-chip program memory and sets the bottom address at 0000h. This allows the device to use the entire range of physical addresses of the external memory.

#### 7.2.2 21-BIT ADDRESSING

As an extension of 20-bit address width operation, the external memory bus can also fully address a 2-Mbyte memory space. This is done by using the Bus Address (BA0) bit 0 control line as the Least Significant bit of the address. The UB and LB control signals may also be used with certain memory devices to select the upper and lower bytes within a 16-bit wide data word.

This addressing mode is available in both 8-Bit Data Width and certain 16-Bit Data Width modes. Additional details are provided in Section 7.6.3 "16-Bit Byte Select Mode" and Section 7.7 "8-Bit Data Width Mode".

Data Width	Address Width	Multiplexed Data and Address Lines (and corresponding ports)	Address Only Lines (and corresponding ports)	Ports Available for I/O
	12-bit		AD11:AD8 (PORTE<3:0>)	PORTE<7:4>, All of PORTH
8-bit	16-bit	AD7:AD0 (PORTD<7:0>)	AD15:AD8 (PORTE<7:0>)	All of PORTH
	20-bit		A19:A16, AD15:AD8 (PORTH<3:0>, PORTE<7:0>)	—
	16-bit	AD15:AD0	—	All of PORTH
16-bit	20-bit	(PORTD<7:0>, PORTE<7:0>)	A19:A16 (PORTH<3:0>)	—

#### TABLE 7-2: ADDRESS AND DATA LINES FOR DIFFERENT ADDRESS AND DATA WIDTHS

# 7.3 Wait States

While it may be assumed that external memory devices will operate at the microcontroller clock rate, this is often not the case. In fact, many devices require longer times to write or retrieve data than the time allowed by the execution of table read or table write operations.

To compensate for this, the external memory bus can be configured to add a fixed delay to each table operation using the bus. Wait states are enabled by setting the WAIT Configuration bit. When enabled, the amount of delay is set by the WAIT1:WAIT0 bits (MEMCON<5:4>). The delay is based on multiples of microcontroller instruction cycle time and are added following the instruction cycle when the table operation is executed. The range is from no delay to 3 Tcy (default value).

# 7.4 Port Pin Weak Pull-ups

With the exception of the upper address lines, A19:A16, the pins associated with the external memory bus are equipped with weak pull-ups. The pull-ups are controlled by bits located at LATA<7:6> and PORTA<7>. They are named RDPU, REPU and RJPU and control pull-ups on PORTD, PORTE and PORTJ, respectively. Setting one of these bits enables the corresponding pull-ups for that port. All pull-ups are disabled by default on all device Resets.

In Extended Microcontroller mode, the port pull-ups can be useful in preserving the memory state on the external bus while the bus is temporarily disabled (EBDIS = 1).

## 7.5 Program Memory Modes and the External Memory Bus

The PIC18F97J60 family of devices is capable of operating in one of two program memory modes, using combinations of on-chip and external program memory. The functions of the multiplexed port pins depend on the program memory mode selected, as well as the setting of the EBDIS bit.

In **Microcontroller Mode**, the bus is not active and the pins have their port functions only. Writes to the MEMCOM register are not permitted. The Reset value of EBDIS ('0') is ignored and the EMB pins behave as I/O ports.

In **Extended Microcontroller Mode**, the external program memory bus shares I/O port functions on the pins. When the device is fetching, or doing table read/table write operations on the external program memory space, the pins will have the external bus function.

If the device is fetching and accessing internal program memory locations only, the EBDIS control bit will change the pins from external memory to I/O port functions. When EBDIS = 0, the pins function as the external bus. When EBDIS = 1, the pins function as I/O ports.

If the device fetches or accesses external memory while EBDIS = 1, the pins will switch to the external bus. If the EBDIS bit is set by a program executing from external memory, the action of setting the bit will be delayed until the program branches into the internal memory. At that time, the pins will change from external bus to I/O ports.

If the device is executing out of internal memory when EBDIS = 0, the memory bus address/data and control pins will not be active. They will go to a state where the active address/data pins are tri-state; the  $\overline{CE}$ ,  $\overline{OE}$ ,  $\overline{WRH}$ ,  $\overline{WRL}$ ,  $\overline{UB}$  and  $\overline{LB}$  signals are '1' and ALE and BA0 are '0'. Note that only those pins associated with the current address width are forced to tri-state; the other pins continue to function as I/O. In the case of 16-bit address width, for example, only AD<15:0> (PORTD and PORTE) are affected; A19:A16 (PORTH<3:0>) continue to function as I/O.

In all external memory modes, the bus takes priority over any other peripherals that may share pins with it. This includes the Parallel Slave Port and serial communication modules which would otherwise take priority over the I/O port.

## 7.6 16-Bit Data Width Modes

In 16-Bit Data Width mode, the external memory interface can be connected to external memories in three different configurations:

- 16-Bit Byte Write
- 16-Bit Word Write
- 16-Bit Byte Select

The configuration to be used is determined by the WM1:WM0 bits in the MEMCON register (MEMCON<1:0>). These three different configurations allow the designer maximum flexibility in using both 8-bit and 16-bit devices with 16-bit data.


For all 16-Bit Data Width modes, the Address Latch Enable (ALE) pin indicates that the address bits, AD<15:0>, are available on the external memory interface bus. Following the address latch, the Output Enable signal ( $\overline{OE}$ ) will enable both bytes of program memory at once to form a 16-bit instruction word. The Chip Enable signal ( $\overline{CE}$ ) is active at any time that the microcontroller accesses external memory, whether reading or writing. It is inactive (asserted high) whenever the device is in Sleep mode.

In Byte Select mode, JEDEC standard Flash memories will require BA0 for the byte address line and one I/O line to select between Byte and Word mode. The other 16-Bit Data Width modes do not need BA0. JEDEC standard, static RAM memories will use the UB or LB signals for byte selection.

#### 7.6.1 16-BIT BYTE WRITE MODE

Figure 7-1 shows an example of 16-Bit Byte Write mode for PIC18F97J60 family devices. This mode is used for two separate 8-bit memories connected for 16-bit operation. This generally includes basic EPROM and Flash devices. It allows table writes to byte-wide external memories. During a TBLWT instruction cycle, the TABLAT data is presented on the upper and <u>lower bytes</u> of the AD15:AD0 bus. The appropriate WRH or WRL control line is strobed on the LSb of the TBLPTR.






# 7.6.2 16-BIT WORD WRITE MODE

Figure 7-2 shows an example of 16-Bit Word Write mode for PIC18F97J60 devices. This mode is used for word-wide memories which include some of the EPROM and Flash type memories. This mode allows opcode fetches and table reads from all forms of 16-bit memory, and table writes to any type of word-wide external memories. This method makes a distinction between TBLWT cycles to even or odd addresses.

During a TBLWT cycle to an even address (TBLPTR<0>= 0), the TABLAT data is transferred to a holding latch and the external address data bus is tri-stated for the data portion of the bus cycle. No write signals are activated.

During a TBLWT cycle to an odd address (TBLPTR<0> = 1), the TABLAT data is presented on the upper byte of the AD15:AD0 bus. The contents of the holding latch are presented on the lower byte of the AD15:AD0 bus.

<u>The WRH</u> signal is strobed for each write cycle; the WRL pin is unused. The signal on the BA0 pin indicates the LSb of the TBLPTR but it is left unconnected. Instead, the UB and LB signals are active to select both bytes. The obvious limitation to this method is that the table write must be done in pairs on a specific word boundary to correctly write a word location.



#### FIGURE 7-2: 16-BIT WORD WRITE MODE EXAMPLE


### 7.6.3 16-BIT BYTE SELECT MODE

Figure 7-3 shows an example of 16-Bit Byte Select mode. This mode allows table write operations to word-wide external memories with byte selection capability. This generally includes both word-wide Flash and SRAM devices.

During a TBLWT cycle, the TABLAT data is presented on the upper and lower byte of the AD15:AD0 bus. The WRH signal is strobed for each write cycle; the WRL pin is not used. The BA0 or UB/LB signals are used to select the byte to be written based on the Least Significant bit of the TBLPTR register.


Flash and SRAM devices use different control signal combinations to implement Byte Select mode. JEDEC standard Flash memories require that a controller I/O port pin be connected to the memory's BYTE/WORD pin to provide the select signal. They also use the BA0 signal from the controller as a byte address. JEDEC standard, static RAM memories, on the other hand, use the UB or LB signals to select the byte.







#### 7.6.4 16-BIT MODE TIMING

The presentation of control signals on the external memory bus is different for the various operating modes. Typical signal timing diagrams are shown in Figure 7-4 and Figure 7-5.





# FIGURE 7-5: EXTERNAL MEMORY BUS TIMING FOR SLEEP (EXTENDED MICROCONTROLLER MODE)



# 7.7 8-Bit Data Width Mode

In 8-Bit Data Width mode, the external memory bus operates only in Multiplexed mode; that is, data shares the eight Least Significant bits of the address bus.

Figure 7-6 shows an example of 8-Bit Multiplexed mode for 100-pin devices. This mode is used for a single 8-bit memory connected for 16-bit operation. The instructions will be fetched as two 8-bit bytes on a shared data/address bus. The two bytes are sequentially fetched within one instruction cycle (Tcr). Therefore, the designer must choose external memory devices according to timing calculations based on 1/2 Tcr (2 times the instruction rate). For proper memory speed selection, glue logic propagation delay times must be considered, along with setup and hold times.

The Address Latch Enable (ALE) pin indicates that the address bits, AD<15:0>, are available on the external memory interface bus. The Output Enable signal (OE)

will enable one byte of program memory for a portion of the instruction cycle, then BA0 will change and the second byte will be enabled to form the 16-bit instruction word. The Least Significant bit of the address, BA0, must be connected to the memory devices in this mode. The Chip Enable signal ( $\overline{CE}$ ) is active at any time that the microcontroller accesses external memory, whether reading or writing. It is inactive (asserted high) whenever the device is in Sleep mode.

This process generally includes basic EPROM and Flash devices. It allows table writes to byte-wide external memories.

During a TBLWT instruction cycle, the TABLAT data is presented on the upper and lower bytes of the AD15:AD0 bus. The appropriate level of the BA0 control line is strobed on the LSb of the TBLPTR.





FIGURE 7-6: 8-BIT MULTIPLEXED MODE EXAMPLE


### 7.7.1 8-BIT MODE TIMING

The presentation of control signals on the external memory bus is different for the various operating modes. Typical signal timing diagrams are shown in Figure 7-7 and Figure 7-8.



# FIGURE 7-7: EXTERNAL MEMORY BUS TIMING FOR TBLRD (EXTENDED MICROCONTROLLER MODE)

# FIGURE 7-8: EXTERNAL MEMORY BUS TIMING FOR SLEEP (EXTENDED MICROCONTROLLER MODE)



#### 7.8 Operation in Power-Managed Modes

In alternate power-managed Run modes, the external bus continues to operate normally. If a clock source with a lower speed is selected, bus operations will run at that speed. In these cases, excessive access times for the external memory may result if wait states have been enabled and added to external memory operations. If operations in a lower power Run mode are anticipated, user applications should provide memory access time adjustments at the lower clock speeds. In Sleep and Idle modes, the microcontroller core does not need to access data; bus operations are suspended. The state of the external bus is frozen, with the address/data pins and most of the control pins holding at the same state they were in when the mode was invoked. The only potential changes are the  $\overline{CE}$ ,  $\overline{LB}$  and  $\overline{UB}$  pins, which are held at logic high.

NOTES:

# 8.0 8 x 8 HARDWARE MULTIPLIER

### 8.1 Introduction

All PIC18 devices include an 8 x 8 hardware multiplier as part of the ALU. The multiplier performs an unsigned operation and yields a 16-bit result that is stored in the product register pair, PRODH:PRODL. The multiplier's operation does not affect any flags in the STATUS register.

Making multiplication a hardware operation allows it to be completed in a single instruction cycle. This has the advantages of higher computational throughput and reduced code size for multiplication algorithms and allows the PIC18 devices to be used in many applications previously reserved for digital signal processors. A comparison of various hardware and software multiply operations, along with the savings in memory and execution time, is shown in Table 8-1.

## 8.2 Operation

Example 8-1 shows the instruction sequence for an 8 x 8 unsigned multiplication. Only one instruction is required when one of the arguments is already loaded in the WREG register.

Example 8-2 shows the sequence to do an 8 x 8 signed multiplication. To account for the sign bits of the arguments, each argument's Most Significant bit (MSb) is tested and the appropriate subtractions are done.

#### EXAMPLE 8-1: 8 x 8 UNSIGNED MULTIPLY ROUTINE

MOVF	ARG1, W	;
MULWF	ARG2	; ARG1 * ARG2 ->
		; PRODH:PRODL

#### EXAMPLE 8-2: 8 x 8 SIGNED MULTIPLY ROUTINE

MOVF	ARG1, W			
MULWF	ARG2	;	ARG1 * ARG2 ->	
		;	PRODH:PRODL	
BTFSC	ARG2, SB	;	Test Sign Bit	
SUBWF	PRODH, F	;	PRODH = PRODH	
		;	- ARG1	
MOVF	ARG2, W			
BTFSC	ARG1, SB	;	Test Sign Bit	
SUBWF	PRODH, F	;	PRODH = PRODH	
		;	- ARG2	

		Program	Cycles	Time			
Routine	Multiply Method	Memory (Words)	(Max)	@ 40 MHz	@ 10 MHz	@ 4 MHz	
	Without hardware multiply	13	69	6.9 μs	27.6 μs	69 μs	
8 x 8 unsigned	Hardware multiply	1	1	100 ns	400 ns	1 μs	
	Without hardware multiply	33	91	9.1 μs	36.4 μs	91 μs	
8 x 8 signed	Hardware multiply	6	6	600 ns	2.4 μs	6 μs	
16 x 16 uppigpod	Without hardware multiply	21	242	24.2 μs	96.8 μs	242 μs	
16 x 16 unsigned	Hardware multiply	28	28	2.8 μs	11.2 μs	28 μs	
16 x 16 signed	Without hardware multiply	52	254	25.4 μs	102.6 μs	254 μs	
16 x 16 signed	Hardware multiply	35	40	4.0 μs	16.0 μs	40 μs	

# TABLE 8-1: PERFORMANCE COMPARISON FOR VARIOUS MULTIPLY OPERATIONS

Example 8-3 shows the sequence to do a 16 x 16 unsigned multiplication. Equation 8-1 shows the algorithm that is used. The 32-bit result is stored in four registers (RES3:RES0).

#### EQUATION 8-1: 16 x 16 UNSIGNED MULTIPLICATION ALGORITHM

RES3:RES0	=	ARG1H:ARG1L • ARG2H:ARG2L (ARG1H • ARG2H • $2^{16}$ ) + (ARG1H • ARG2L • $2^{8}$ ) + (ARG1L • ARG2H • $2^{8}$ ) + (ARG1L • ARG2L)
		$(ARG1L \bullet ARG2L)$

## EXAMPLE 8-3: 16 x 16 UNSIGNED MULTIPLY ROUTINE

М	OVF	ARG1L,	W		
	ULWF			;	ARG1L * ARG2L->
				;	PRODH:PRODL
М	OVFF	PRODH,	RES1	;	
М	OVFF	PRODL,	res0	;	
;					
М	OVF	ARG1H,	W		
М	ULWF	ARG2H		;	ARG1H * ARG2H->
				;	PRODH:PRODL
М	OVFF	PRODH,	RES3	;	
М	OVFF	PRODL,	RES2	;	
;					
М	OVF	ARG1L,	W		
M	ULWF	ARG2H		;	ARG1L * ARG2H->
				;	PRODH:PRODL
M	OVF	PRODL,	W	;	
A	DDWF	RES1, E			Add cross
		PRODH,		;	products
A	DDWFC	RES2, E	P	;	
-		WREG		;	
A	DDWFC	RES3, E	7	;	
;					
		ARG1H,		;	
M	ULWF	ARG2L			ARG1H * ARG2L->
				;	PRODH:PRODL
		PRODL,		;	
		RES1, F			Add cross
					products
		RES2, E	7	;	
	LRF			;	
A	DDWFC	RES3, E	7	;	

Example 8-4 shows the sequence to do a 16 x 16 signed multiply. Equation 8-2 shows the algorithm used. The 32-bit result is stored in four registers (RES3:RES0). To account for the sign bits of the arguments, the MSb for each argument pair is tested and the appropriate subtractions are done.

#### EQUATION 8-2: 16 x 16 SIGNED MULTIPLICATION ALGORITHM

$RES3:RES0 = ARG1H:ARG1L \bullet ARG2H:ARG2L$
$= (ARG1H \bullet ARG2H \bullet 2^{16}) +$
$(ARG1H \bullet ARG2L \bullet 2^8) +$
$(ARG1L \bullet ARG2H \bullet 2^8) +$
$(ARG1L \bullet ARG2L) +$
$(-1 \bullet ARG2H < 7 \ge \bullet ARG1H:ARG1L \bullet 2^{16}) +$
$(-1 \bullet ARG1H \le 7 \ge \bullet ARG2H:ARG2L \bullet 2^{16})$

#### EXAMPLE 8-4: 16 x 16 SIGNED MULTIPLY ROUTINE

		IVI		
	MOVF	ARG1L, W		
	MULWF	ARG2L		ARG1L * ARG2L ->
				PRODH: PRODL
	MOVFF	PRODH, RE	ES1 ;	
	MOVFF	PRODL, RE	ESO ;	
;				
	MOVF	ARG1H, W		
	MULWF	ARG2H	;	ARG1H * ARG2H ->
			;	PRODH:PRODL
	MOVFF	PRODH, RE	ES3 ;	
	MOVFF	PRODL, RE	ES2 ;	
;				
	MOVF	ARG1L, W		
	MULWF	ARG2H		ARG1L * ARG2H ->
			;	PRODH:PRODL
		PRODL, W	;	
	ADDWF	RES1, F		Add cross
		PRODH, W		products
		RES2, F	;	
	CLRF		;	
	ADDWFC	RES3, F	;	
;				
	MOVE	ARG1H, W		
	MULWF	ARG2L		ARG1H * ARG2L ->
	MOTE	DDODI M		PRODH:PRODL
	MOVE	PRODL, W RES1, F		Ad areas
		PRODH, W		Add cross products
		RES2, F	;	produces
		WREG	;	
		RES3, F	;	
;	11001110	10007 1	,	
,	BTFSS	ARG2H, 7	;	ARG2H:ARG2L neg?
	BRA	SIGN ARG1		no, check ARG1
	MOVF	ARG1L, W		
	SUBWF	RES2	;	
	MOVF	ARG1H, W	;	
	SUBWFB	RES3		
;				
SIG	N_ARG1			
		ARG1H, 7		ARG1H:ARG1L neg?
	BRA	CONT_CODE	Ξ ;	no, done
		ARG2L, W	;	
	SUBWF	RES2	;	
	MOVF	ARG2H, W	;	
	SUBWFB	RES3		
;				
CON	T_CODE			
	:			

# 9.0 INTERRUPTS

Members of the PIC18F97J60 family of devices have multiple interrupt sources and an interrupt priority feature that allows most interrupt sources to be assigned a high priority level or a low priority level. The high priority interrupt vector is at 0008h and the low priority interrupt vector is at 0018h. High priority interrupt events will interrupt any low priority interrupts that may be in progress.

There are thirteen registers which are used to control interrupt operation. These registers are:

- RCON
- INTCON
- INTCON2
- INTCON3
- PIR1, PIR2, PIR3
- PIE1, PIE2, PIE3
- IPR1, IPR2, IPR3

It is recommended that the Microchip header files supplied with MPLAB<sup>®</sup> IDE be used for the symbolic bit names in these registers. This allows the assembler/compiler to automatically take care of the placement of these bits within the specified register.

In general, interrupt sources have three bits to control their operation. They are:

- Flag bit to indicate that an interrupt event occurred
- Enable bit that allows program execution to branch to the interrupt vector address when the flag bit is set
- **Priority bit** to select high priority or low priority

The interrupt priority feature is enabled by setting the IPEN bit (RCON<7>). When interrupt priority is enabled, there are two bits which enable interrupts globally. Setting the GIEH bit (INTCON<7>) enables all interrupts that have the priority bit set (high priority). Setting the GIEL bit (INTCON<6>) enables all interrupts that have the priority bit cleared (low priority). When the interrupt flag, enable bit and appropriate global interrupt enable bit are set, the interrupt will vector immediately to address 0008h or 0018h, depending on the priority bit setting. Individual interrupts can be disabled through their corresponding enable bits.

When the IPEN bit is cleared (default state), the interrupt priority feature is disabled and interrupts are compatible with PIC<sup>®</sup> mid-range devices. In Compatibility mode, the interrupt priority bits for each source have no effect. INTCON<6> is the PEIE bit which enables/disables all peripheral interrupt sources. INTCON<7> is the GIE bit which enables/disables all interrupt sources. All interrupts branch to address 0008h in Compatibility mode.

When an interrupt is responded to, the global interrupt enable bit is cleared to disable further interrupts. If the IPEN bit is cleared, this is the GIE bit. If interrupt priority levels are used, this will be either the GIEH or GIEL bit. High priority interrupt sources can interrupt a low priority interrupt. Low priority interrupts are not processed while high priority interrupts are in progress.


The return address is pushed onto the stack and the PC is loaded with the interrupt vector address (0008h or 0018h). Once in the Interrupt Service Routine, the source(s) of the interrupt can be determined by polling the interrupt flag bits. The interrupt flag bits must be cleared in software before re-enabling interrupts to avoid recursive interrupts.

The "return from interrupt" instruction, RETFIE, exits the interrupt routine and sets the GIE bit (GIEH or GIEL if priority levels are used) which re-enables interrupts.

For external interrupt events, such as the INTx pins or the PORTB input change interrupt, the interrupt latency will be three to four instruction cycles. The exact latency is the same for one or two-cycle instructions. Individual interrupt flag bits are set regardless of the status of their corresponding enable bit or the GIE bit.

Note: Do not use the MOVFF instruction to modify any of the interrupt control registers while any interrupt is enabled. Doing so may cause erratic microcontroller behavior.





## 9.1 INTCON Registers

The INTCON registers are readable and writable registers which contain various enable, priority and flag bits.

**Note:** Interrupt flag bits are set when an interrupt condition occurs regardless of the state of its corresponding enable bit or the global interrupt enable bit. User software should ensure the appropriate interrupt flag bits are clear prior to enabling an interrupt. This feature allows for software polling.

#### REGISTER 9-1: INTCON: INTERRUPT CONTROL REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-x
GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INTOIF	RBIF <sup>(1)</sup>
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	d as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7	GIE/GIEH: Global Interrupt Enable bit <u>When IPEN = 0:</u> 1 = Enables all unmasked interrupts 0 = Disables all interrupts <u>When IPEN = 1:</u> 1 = Enables all high priority interrupts 0 = Disables all interrupts
bit 6	PEIE/GIEL: Peripheral Interrupt Enable bit         When IPEN = 0:         1 = Enables all unmasked peripheral interrupts         0 = Disables all peripheral interrupts         When IPEN = 1:         1 = Enables all low priority peripheral interrupts         0 = Disables all low priority peripheral interrupts         0 = Disables all low priority peripheral interrupts
bit 5	<pre>TMR0IE: TMR0 Overflow Interrupt Enable bit 1 = Enables the TMR0 overflow interrupt 0 = Disables the TMR0 overflow interrupt</pre>
bit 4	INTOIE: INTO External Interrupt Enable bit 1 = Enables the INTO external interrupt 0 = Disables the INTO external interrupt
bit 3	<b>RBIE:</b> RB Port Change Interrupt Enable bit 1 = Enables the RB port change interrupt 0 = Disables the RB port change interrupt
bit 2	<b>TMR0IF:</b> TMR0 Overflow Interrupt Flag bit 1 = TMR0 register has overflowed (must be cleared in software) 0 = TMR0 register did not overflow
bit 1	INTOIF: INTO External Interrupt Flag bit 1 = The INTO external interrupt occurred (must be cleared in software) 0 = The INTO external interrupt did not occur
bit 0	<b>RBIF:</b> RB Port Change Interrupt Flag bit <sup>(1)</sup> 1 = At least one of the RB7:RB4 pins changed state (must be cleared in software) 0 = None of the RB7:RB4 pins have changed state

**Note 1:** A mismatch condition will continue to set this bit. Reading PORTB will end the mismatch condition and allow the bit to be cleared.

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	
RBPU	INTEDG0	INTEDG1	INTEDG2	INTEDG3	TMR0IP	INT3IP	RBIP	
bit 7							bit	
Legend:								
R = Readable	e bit	W = Writable	bit	U = Unimplen	nented bit, rea	d as '0'		
-n = Value at	POR	'1' = Bit is set		'0' = Bit is clea		x = Bit is unkr	nown	
		ГВ Pull-up Ena	ble bit					
		TB pull-ups are						
				idual port latch	values			
bit 6	INTEDG0: E>	kternal Interrup	t 0 Edge Seleo	ct bit				
		on rising edge						
		on falling edge						
bit 5		kternal Interrup	•	ct bit				
		on rising edge on falling edge						
bit 4	•	External Interrupt 2 Edge Select bit						
		on rising edge	•					
		on falling edge						
bit 3	INTEDG3: EX	External Interrupt 3 Edge Select bit						
		on rising edge						
	•	on falling edge						
bit 2		R0 Overflow In	terrupt Priority	bit				
	1 = High pric 0 = Low pric	•						
bit 1	•	External Interr	unt Priority hit					
	1 = High pric		upt i nonty bit					
	0 = Low prior	•						
bit 0	RBIP: RB Po	rt Change Inter	rupt Priority b	it				
	1 = High pric		-					
	0 = Low prio	rity						

#### REGISTER 9-2: INTCON2: INTERRUPT CONTROL REGISTER 2

**Note:** Interrupt flag bits are set when an interrupt condition occurs regardless of the state of its corresponding enable bit or the global interrupt enable bit. User software should ensure the appropriate interrupt flag bits are clear prior to enabling an interrupt. This feature allows for software polling.

# REGISTER 9-3: INTCON3: INTERRUPT CONTROL REGISTER 3

R/W-1	R/W-1	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
INT2IF	P INT1IP	INT3IE	INT2IE	INT1IE	INT3IF	INT2IF	INT1IF
bit 7	•				•		bit 0
Legend: R = Reada	abla hit		hit	II – Unimploy	monted bit rea	d aa 'O'	
-n = Value		W = Writable '1' = Bit is set		'0' = Bit is cle	mented bit, read		
	alPOR	I = DILIS SEL			areu	x = Bit is unkr	IOWII
bit 7	INT2IP: INT	2 External Interr	upt Priority bit	t			
	1 = High pri						
	0 = Low price	•					
bit 6		1 External Interr	upt Priority bit	t			
	1 = High pri 0 = Low pric	•					
bit 5	•	3 External Interr	unt Enable bit	ł			
		the INT3 extern	•				
		s the INT3 exter					
bit 4	INT2IE: INT	2 External Interr	upt Enable bit	t			
		the INT2 extern					
		s the INT2 exter	•				
bit 3		1 External Interr	•	t			
		the INT1 extern the INT1 extern					
bit 2		3 External Interr					
		3 external interi		(must be clear	ed in software)		
	0 = The INT	3 external inter	rupt did not oc	cur			
bit 1		2 External Interr					
		2 external interi 2 external interi			ed in software)		
bit 0		1 External Interr	•				
		1 external interi	•	(must be clear	ed in software)		
		1 external inter	•	•	,		
Note:	Interrupt flag bits	are set when a	an interrupt co	ondition occurs	regardless of	the state of its	corresponding
	enable bit or the are clear prior to	global interrupt e	enable bit. Us	er software sho	ould ensure the	appropriate int	

### 9.2 PIR Registers

The PIR registers contain the individual flag bits for the peripheral interrupts. Due to the number of peripheral interrupt sources, there are three Peripheral Interrupt Request (Flag) registers (PIR1, PIR2, PIR3).

- Note 1: Interrupt flag bits are set when an interrupt condition occurs regardless of the state of its corresponding enable bit or the Global Interrupt Enable bit, GIE (INTCON<7>).
  - 2: User software should ensure the appropriate interrupt flag bits are cleared prior to enabling an interrupt and after servicing that interrupt.

#### REGISTER 9-4: PIR1: PERIPHERAL INTERRUPT REQUEST (FLAG) REGISTER 1

R/W-0	R/W-0	R-0	R-0	R/W-0	R/W-0	R/W-0	R/W-0
PSPIF <sup>(1)</sup>	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF
bit 7							bit 0
Legend:							
R = Readable		W = Writable		-	mented bit, read		
-n = Value at	POR	'1' = Bit is set		'0' = Bit is cle	eared	x = Bit is unki	nown
bit 7	<b>PSPIF</b> : Para	llel Slave Port F	Read/Write In	terrupt Elag bit	(1)		
		or a write operat				tware)	
	0 = No read	or write has oc	curred			,	
bit 6		onverter Interru					
		conversion com		be cleared in s	oftware)		
L:1 F		conversion is r	-	<b>b</b> :4			
bit 5		ART1 Receive			ared when RCR	EG1 is read)	
		SART1 receive					
bit 4		ART1 Transmit	-	-			
		SART1 transmit SART1 transmit		G1, is empty (	cleared when T	XREG1 is writte	en)
bit 3	SSP1IF: MS	SP1 Interrupt F	lag bit				
		ismission/recep to transmit/rece		ete (must be cle	eared in softwar	re)	
bit 2	CCP1IF: EC	CP1 Interrupt F	lag bit				
		<u>le:</u> register capture 1 register captu		ust be cleared	in software)		
		<u>ode:</u> register compa 1 register comp			cleared in softw	/are)	
	PWM mode:		are match oc	curreu			
	Unused in th						
bit 1	TMR2IF: TM	R2 to PR2 Mate	ch Interrupt F	lag bit			
		PR2 match oc 2 to PR2 match	•	be cleared in s	oftware)		
bit 0	TMR1IF: TM	R1 Overflow In	terrupt Flag b	it			
		egister overflow egister did not o		cleared in softw	vare)		
Noto 1: Im	plomontod in 1	00 nin dovicos i	n Microcontr	oller mode only			

**Note 1:** Implemented in 100-pin devices in Microcontroller mode only.

#### REGISTER 9-5: PIR2: PERIPHERAL INTERRUPT REQUEST (FLAG) REGISTER 2

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0
OSCFIF	CMIF	ETHIF	r	BCL1IF	_	TMR3IF	CCP2IF
bit 7	÷						bit (
Legend:							
R = Readabl	e bit	W = Writable	bit	U = Unimplem	ented bit, re	ad as '0'	
-n = Value at	POR	'1' = Bit is set		'0' = Bit is clea		x = Bit is unkr	nown
bit 7	OSCFIF: Osc	cillator Fail Inte	rrupt Flag bit				
	1 = System o			as changed to II	NTRC (must	be cleared in so	ftware)
bit 6	CMIF: Compa	arator Interrupt	Flag bit				
				t be cleared in s	oftware)		
	0 = Compara	ator input has n	ot changed				
bit 5		net Module Inte					
					ery EIR regis	ster to resolve so	urce
L:1 4		net interrupt ev	ent has occu	rrea			
bit 4	Reserved: M						
bit 3				MSSP1 module)			
		collision occurred	•	ared in software	)		
bit 2	Unimplemen	ted: Read as '	0'				
bit 1	TMR3IF: TM	R3 Overflow Int	terrupt Flag b	it			
		gister overflow gister did not o		leared in softwa	re)		
bit 0	CCP2IF: ECO	CP2 Interrupt F	lag bit				
				rred (must be cl	eared in soft	ware)	
	<u>Compare mo</u> 1 = A TMR1/	de:	compare mat	ch occurred (mu	ist be cleare	d in software)	
	<u>PWM mode:</u> Unused in thi	s mode.					

R/W-0	R/W-0	R-0	R-0	R/W-0	R/W-0	R/W-0	R/W-0
SSP2IF <sup>(1)</sup>	BCL2IF <sup>(1)</sup>	RC2IF <sup>(2)</sup>	TX2IF <sup>(2)</sup>	TMR4IF	CCP5IF	CCP4IF	CCP3IF
bit 7							bit
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimple	emented bit, rea	d as '0'	
-n = Value at I	POR	'1' = Bit is set	t	'0' = Bit is c	leared	x = Bit is unk	nown
bit 7	SSP2IF: MS	SP2 Interrupt F	lag bit(1)				
			•	ete (must be c	leared in softwa	re)	
	0 = Waiting	to transmit/rece	eive	·			
bit 6		s Collision Inter					
		ollision occurred	•	ared in softwa	are)		
bit 5		ART2 Receive		bit( <b>2</b> )			
					ared when RCR	EG2 is read)	
		SART2 receive		-			
bit 4		ART2 Transmit					
		SART2 transmit SART2 transmit		G2, is empty	(cleared when T	XREG2 is writt	en)
bit 3		IR4 to PR4 Mat		lag bit			
		o PR4 match oc		be cleared in	software)		
		R4 to PR4 match					
bit 2		P5 Interrupt Fla	ig bit				
					cleared in softw	vare)	
					must be cleared	in software)	
	<u>PWM mode:</u> Unused in th						
bit 1	CCP4IF: CC	P4 Interrupt Fla	ag bit				
					cleared in softw	vare)	
	Compare mo 1 = A TMR1	ode:	compare ma	tch occurred (	must be cleared	in software)	
	<u>PWM mode:</u> Unused in th						
bit 0	CCP3IF: EC	CP3 Interrupt F	lag bit				
					cleared in softw	vare)	
					must be cleared	in software)	
	<u>PWM mode:</u> Unused in th						

# REGISTER 9-6: PIR3: PERIPHERAL INTERRUPT REQUEST (FLAG) REGISTER 3

**Note 1:** Implemented in 100-pin devices only.

2: Implemented in 80-pin and 100-pin devices only.

# 9.3 PIE Registers

The PIE registers contain the individual enable bits for the peripheral interrupts. Due to the number of peripheral interrupt sources, there are three Peripheral Interrupt Enable registers (PIE1, PIE2, PIE3). When IPEN = 0, the PEIE bit must be set to enable any of these peripheral interrupts.

#### REGISTER 9-7: PIE1: PERIPHERAL INTERRUPT ENABLE REGISTER 1

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
PSPIE <sup>(1)</sup>	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE
bit 7							bit 0
Legend: R = Readable	hit	M = Mritable	hit	II – Unimplor	monted hit rea	d oo 'O'	
		W = Writable		-	mented bit, rea		
-n = Value at	PUR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkı	IOWII
bit 7	<b>PSPIE</b> : Paral	llel Slave Port F	Read/Write Int	errupt Enable I	bit(1)		
	1 = Enabled 0 = Disabled						
bit 6	ADIE: A/D Co 1 = Enabled 0 = Disabled	onverter Interru	pt Enable bit				
bit 5	RC1IE: EUS/ 1 = Enabled 0 = Disabled	ART1 Receive	Interrupt Enat	ble bit			
bit 4	TX1IE: EUSA	ART1 Transmit	Interrupt Enal	ole bit			
	1 = Enabled 0 = Disabled	l					
bit 3	SSP1IE: MSS	SP1 Interrupt E	nable bit				
	1 = Enabled 0 = Disabled						
bit 2	CCP1IE: ECC 1 = Enabled 0 = Disabled	CP1 Interrupt E	nable bit				
bit 1	TMR2IE: TM 1 = Enabled 0 = Disabled	R2 to PR2 Mate	ch Interrupt E	nable bit			
bit 0		R1 Overflow In	terrupt Enable	e bit			

**Note 1:** Implemented in 100-pin devices in Microcontroller mode only.

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0
OSCFIE	CMIE	ETHIE	r	BCL1IE	_	TMR3IE	CCP2IE
bit 7							bit 0
Legend:							
R = Readabl	e bit	W = Writable	bit	U = Unimplem		d as '0'	
-n = Value at	POR	'1' = Bit is set		'0' = Bit is clea	ired	x = Bit is unkr	nown
bit 7		villatar Fail Into	rrupt Epoble k				
	1 = Enabled	cillator Fail Inte	inupi Enable i	JIL			
	0 = Disabled						
bit 6	CMIE: Compa	arator Interrupt	Enable bit				
	1 = Enabled						
	0 = Disabled						
bit 5	ETHIE: Ether	met Module Int	errupt Enable	bit			
	1 = Enabled 0 = Disabled						
bit 4	Reserved: M	aintain as '0'					
bit 3	BCL1IE: Bus	Collision Inter	rupt Enable bi	it (MSSP1 modu	le)		
	1 = Enabled						
	0 = Disabled						
bit 2	Unimplemen	ted: Read as '	0'				
bit 1		R3 Overflow In	terrupt Enable	e bit			
	1 = Enabled						
	0 = Disabled						
bit 0		CP2 Interrupt E	nadie dit				
	1 = Enabled						

#### REGISTER 9-8: PIE2: PERIPHERAL INTERRUPT ENABLE REGISTER 2

## REGISTER 9-9: PIE3: PERIPHERAL INTERRUPT ENABLE REGISTER 3

R/W-0	R/W-0	R-0	R-0	R/W-0	R/W-0	R/W-0	R/W-0
SSP2IE <sup>(1)</sup>	BCL2IE <sup>(1)</sup>	RC2IE <sup>(2)</sup>	TX2IE <sup>(2)</sup>	TMR4IE	CCP5IE	CCP4IE	CCP3IE
bit 7						·	bit C
Legend:							
R = Readable I	bit	W = Writable	bit	U = Unimpler	nented bit, read	d as '0'	
-n = Value at P	OR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7	1 = Enabled	SP2 Interrupt E	nable bit(",				
	1 = Enabled 0 = Disabled						
bit 6	BCL2IE: Bus	Collision Interr	upt Enable bit	t (MSSP2 mod	ule) <sup>(1)</sup>		
	1 = Enabled		•	·			
	0 = Disabled						
bit 5		ART2 Receive	Interrupt Enab	le bit <sup>(2)</sup>			
	1 = Enabled 0 = Disabled						
bit 4		RT2 Transmit	Interrunt Engh	he hit(2)			
	1 = Enabled		interrupt Enac				
	0 = Disabled						
bit 3	TMR4IE: TMF	R4 to PR4 Mate	ch Interrupt Er	nable bit			
	1 = Enabled						
	0 = Disabled						
bit 2		P5 Interrupt En	able bit				
	1 = Enabled 0 = Disabled						
bit 1		P4 Interrupt En	able bit				
	1 = Enabled						
	0 = Disabled						
bit 0	CCP3IE: ECC	CP3 Interrupt E	nable bit				
	1 = Enabled						
	0 = Disabled						

2: Implemented in 80-pin and 100-pin devices only.

## 9.4 IPR Registers

The IPR registers contain the individual priority bits for the peripheral interrupts. Due to the number of peripheral interrupt sources, there are three Peripheral Interrupt Priority registers (IPR1, IPR2, IPR3). Using the priority bits requires that the Interrupt Priority Enable (IPEN) bit be set.

#### REGISTER 9-10: IPR1: PERIPHERAL INTERRUPT PRIORITY REGISTER 1

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1
PSPIP <sup>(1)</sup>	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP
bit 7							bit (
Legend:	L:4		L :4			-1 (0)	
R = Readable		W = Writable			mented bit, rea		
-n = Value at	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7	PSPIP: Para	allel Slave Port F	Read/Write Int	terrupt Priority	bit <sup>(1)</sup>		
	1 = High pri						
	0 = Low price						
bit 6	ADIP: A/D C	Converter Interru	pt Priority bit				
	1 = High pri	•					
	0 = Low price	ority					
bit 5	RC1IP: EUS	SART1 Receive	Interrupt Prior	rity bit			
	1 = High pri						
	0 = Low price	•					
bit 4		ART1 Transmit	Interrupt Prio	rity bit			
	1 = High pri	•					
1.11.0	0 = Low price	-					
bit 3		SP1 Interrupt P	riority dit				
	1 = High pri 0 = Low pric						
bit 2	•	CP1 Interrupt P	riority bit				
	1 = High pri	-					
	0 = Low pric						
bit 1	TMR2IP: TM	IR2 to PR2 Mate	ch Interrupt P	riority bit			
	1 = High pri	ority					
	0 = Low price	ority					
bit 0	TMR1IP: TM	IR1 Overflow In	terrupt Priority	y bit			
	1 = High pri						
	0 = Low price	ority					

**Note 1:** Implemented in 100-pin devices in Microcontroller mode only.

# REGISTER 9-11: IPR2: PERIPHERAL INTERRUPT PRIORITY REGISTER 2

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	U-0	R/W-1	R/W-1
OSCFIP	CMIP	ETHIP	r	BCL1IP		TMR3IP	CCP2IP
bit 7							bit 0
Legend:							
R = Readable	e bit	W = Writable	bit	U = Unimpler	nented bit, rea	d as '0'	
-n = Value at	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7		cillator Fail Inte	rrupt Priority I	Dit			
	1 = High prio 0 = Low prior						
bit 6	•	arator Interrupt	Priority bit				
	1 = High prio	ority	-				
	0 = Low prior	rity					
bit 5	ETHIP: Ether	met Module Int	errupt Priority	bit			
	1 = High price						
	0 = Low prior	5					
bit 4	Reserved: M						
bit 3			rupt Priority bi	it (MSSP1 mod	ule)		
	1 = High prio 0 = Low prior						
bit 2	•	i <b>ted:</b> Read as '	0'				
bit 1	-	R3 Overflow In		v bit			
	1 = High pric			, 510			
	0 = Low prior	•					
bit 0	CCP2IP: ECO	CP2 Interrupt F	riority bit				
	1 = High pric						
	0 = Low prior	rity					

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1
SSP2IP <sup>(1)</sup>	BCL2IP <sup>(1)</sup>	RC2IP <sup>(2)</sup>	TX2IP <sup>(2)</sup>	TMR4IP	CCP5IP	CCP4IP	CCP3IP
bit 7							bit
Legend:							
R = Readable		W = Writable		•	nented bit, rea		
-n = Value at F	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7	SSP2IP: MSS	SP2 Interrupt P	riority bit <sup>(1)</sup>				
	1 = High prio	•	,				
	0 = Low prior	rity					
bit 6		Collision Intern	rupt Priority bit	t (MSSP2 mod	ule) <sup>(1)</sup>		
	1 = High prio						
bit 5		ART2 Receive	Interrupt Prior	ity bit(-)			
	1 = High prio 0 = Low prior						
bit 4	•	RT2 Transmit	Interrupt Prior	ity bit <sup>(2)</sup>			
	1 = High prio	ority					
	0 = Low prior	rity					
bit 3	TMR4IE: TMI	R4 to PR4 Inte	rrupt Priority b	it			
	1 = High prio						
1.1.0	0 = Low prior	•					
bit 2		P5 Interrupt Pri	ority dit				
	1 = High prio 0 = Low prior						
bit 1	•	P4 Interrupt Pri	ority bit				
	1 = High prio		- <b>,</b>				
	0 = Low prior	rity					
bit 0		CP3 Interrupt P	riority bit				
	1 = High prio						
	0 = Low prior	rity					

#### **REGISTER 9-12: IPR3: PERIPHERAL INTERRUPT PRIORITY REGISTER 3**

- - 2: Implemented in 80-pin and 100-pin devices only.

# 9.5 RCON Register

The RCON register contains bits used to determine the cause of the last Reset or wake-up from Idle or Sleep modes. RCON also contains the bit that enables interrupt priorities (IPEN).

#### REGISTER 9-13: RCON: RESET CONTROL REGISTER

R/W-0	U-0	R/W-1	R/W-1	R-1	R-1	R/W-0	R/W-0
IPEN	_	CM	RI	TO	PD	POR	BOR
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	t, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7	IPEN: Interrupt Priority Enable bit
	1 = Enable priority levels on interrupts
	0 = Disable priority levels on interrupts (PIC16CXXX Compatibility mode)
bit 6	Unimplemented: Read as '0'
bit 5	CM: Configuration Mismatch Flag bit
	For details of bit operation, see Register 4-1.
bit 4	RI: RESET Instruction Flag bit
	For details of bit operation, see Register 4-1.
bit 3	TO: Watchdog Timer Time-out Flag bit
	For details of bit operation, see Register 4-1.
bit 2	PD: Power-Down Detection Flag bit
	For details of bit operation, see Register 4-1.
bit 1	<b>POR</b> : Power-on Reset Status bit <sup>(2)</sup>
	For details of bit operation, see Register 4-1.
bit 0	BOR: Brown-out Reset Status bit
	For details of bit operation, see Register 4-1.

© 2007 Microchip Technology Inc.

## 9.6 INTx Pin Interrupts

External interrupts on the RB0/INT0/FLT0, RB1/INT1, RB2/INT2 and RB3/INT3 pins are edge-triggered. If the corresponding INTEDGx bit in the INTCON2 register is set (= 1), the interrupt is triggered by a rising edge; if the bit is clear, the trigger is on the falling edge. When a valid edge appears on the RBx/INTx pin, the corresponding flag bit, INTxIF, is set. This interrupt can be disabled by clearing the corresponding enable bit, INTxIE. Flag bit, INTxIF, must be cleared in software in the Interrupt Service Routine before re-enabling the interrupt.

All external interrupts (INT0, INT1, INT2 and INT3) can wake-up the processor from the power-managed modes if bit INTxIE was set prior to going into the power-managed modes. If the Global Interrupt Enable bit, GIE, is set, the processor will branch to the interrupt vector following wake-up.

Interrupt priority for INT1, INT2 and INT3 is determined by the value contained in the Interrupt Priority bits, INT1IP (INTCON3<6>), INT2IP (INTCON3<7>) and INT3IP (INTCON2<1>). There is no priority bit associated with INT0. It is always a high priority interrupt source.

### 9.7 TMR0 Interrupt

In 8-bit mode (which is the default), an overflow in the TMR0 register (FFh  $\rightarrow$  00h) will set flag bit, TMR0IF. In 16-bit mode, an overflow in the TMR0H:TMR0L register pair (FFFh  $\rightarrow$  0000h) will set TMR0IF. The interrupt can be enabled/disabled by setting/clearing enable bit, TMR0IE (INTCON<5>). Interrupt priority for Timer0 is determined by the value contained in the interrupt priority bit, TMR0IP (INTCON2<2>). See Section 11.0 "Timer0 Module" for further details on the Timer0 module.

#### 9.8 PORTB Interrupt-on-Change

An input change on PORTB<7:4> sets flag bit, RBIF (INTCON<0>). The interrupt can be enabled/disabled by setting/clearing enable bit, RBIE (INTCON<3>). Interrupt priority for PORTB interrupt-on-change is determined by the value contained in the interrupt priority bit, RBIP (INTCON2<0>).

# 9.9 Context Saving During Interrupts

During interrupts, the return PC address is saved on the stack. Additionally, the WREG, STATUS and BSR registers are saved on the fast return stack. If a fast return from interrupt is not used (see **Section 5.3 "Data Memory Organization"**), the user may need to save the WREG, STATUS and BSR registers on entry to the Interrupt Service Routine. Depending on the user's application, other registers may also need to be saved. Example 9-1 saves and restores the WREG, STATUS and BSR registers during an Interrupt Service Routine.

MOVWF MOVFF MOVFF	W_TEMP STATUS, STATUS_TEMP BSR, BSR TEMP	; W_TEMP is in virtual bank ; STATUS_TEMP located anywhere ; BSR TMEP located anywhere
;	ISR CODE	, DSK_IMBI IOCALEU ANYWHELE
MOVFF	BSR TEMP, BSR	; Restore BSR
MOVF	W_TEMP, W	; Restore WREG
MOVFF	STATUS_TEMP, STATUS	; Restore STATUS

EXAMPLE 9-1: SAVING STATUS, WREG AND BSR REGISTERS IN RAM

# 10.0 I/O PORTS

Depending on the device selected and features enabled, there are up to nine ports available. Some pins of the I/O ports are multiplexed with an alternate function from the peripheral features on the device. In general, when a peripheral is enabled, that pin may not be used as a general purpose I/O pin.


Each port has three registers for its operation. These registers are:

- TRIS register (Data Direction register)
- PORT register (reads the levels on the pins of the device)
- LAT register (Output Latch register)

The Output Latch (LAT register) is useful for read-modify-write operations on the value that the I/O pins are driving.

A simplified model of a generic I/O port, without the interfaces to other peripherals, is shown in Figure 10-1.

FIGURE 10-1: GENERIC I/O PORT OPERATION



# 10.1 I/O Port Pin Capabilities

When developing an application, the capabilities of the port pins must be considered. Outputs on some pins have higher output drive strength than others. Similarly, some pins can tolerate higher than VDD input levels.

### 10.1.1 PIN OUTPUT DRIVE

The output pin drive strengths vary for groups of pins intended to meet the needs for a variety of applications. PORTB and PORTC are designed to drive higher loads, such as LEDs. The external memory interface ports (PORTD, PORTE and PORTJ) are designed to drive medium loads. All other ports are designed for small loads, typically indication only. Table 10-1 summarizes the output capabilities. Refer to **Section 27.0 "Electrical Characteristics"** for more details.

TABLE 10-1:	OUTPUT DRIVE LEVELS
-------------	---------------------

Port	Drive	Description
PORTA <sup>(1)</sup>	Minimum	Intended for indication.
PORTF <sup>(2)</sup>		
PORTG <sup>(2)</sup>		
PORTH <sup>(3)</sup>		
PORTD <sup>(2)</sup>	Medium	Sufficient drive levels for
PORTE		external memory interfacing,
PORTJ <sup>(3)</sup>		as well as indication.
PORTB	High	Suitable for direct LED drive
PORTC		levels.

**Note 1:** The exceptions are RA0:RA1, which are capable of directly driving LEDs.

2: Partially implemented on 64-pin and 80-pin devices; fully implemented on 100-pin devices.

**3:** Unimplemented on 64-pin devices.

# 10.1.2 INPUT PINS AND VOLTAGE CONSIDERATIONS

The voltage tolerance of pins used as device inputs is dependent on the pin's input function. Pins that are used as digital only inputs are able to handle DC voltages up to 5.5V, a level typical for digital logic circuits. In contrast, pins that also have analog input functions of any kind can only tolerate voltages up to VDD. Voltage excursions beyond VDD on these pins are always to be avoided. Table 10-2 summarizes the input capabilities. Refer to **Section 27.0 "Electrical Characteristics"** for more details.

Port or Pin	Tolerated Input	Description
PORTA<5,3:0>	Vdd	Only VDD input levels
PORTF<6:1> <sup>(1)</sup>		tolerated.
PORTH<7:4> <sup>(2)</sup>		
PORTA<4>	5.5V	Tolerates input levels
PORTB<7:0>		above VDD, useful for
PORTC<7:0>		most standard logic.
PORTD<7:0>(1)		
PORTE<7:0>		
PORTF<7>		
PORTG<7:0>(1)		
PORTH<3:0>(2)		
PORTJ<7:0> <sup>(2)</sup>		

TABLE 10-2: INPUT VOLTAGE LEVELS

Note 1: Partially implemented on 64-pin and 80-pin devices; fully implemented on 100-pin devices.

**2:** Unavailable on 64-pin devices.

# 10.2 PORTA, TRISA and LATA Registers

PORTA is a 6-bit wide, bidirectional port; it is fully implemented on all devices. The corresponding Data Direction register is TRISA. Setting a TRISA bit (= 1) will make the corresponding PORTA pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISA bit (= 0) will make the corresponding PORTA pin an output (i.e., put the contents of the output latch on the selected pin).

Reading the PORTA register reads the status of the pins, whereas writing to it, will write to the port latch.

The Output Latch register (LATA) is also memory mapped. Read-modify-write operations on the LATA register read and write the latched output value for PORTA.

The RA4 pin is multiplexed with the Timer0 module clock input to become the RA4/T0CKI pin. The other PORTA pins are multiplexed with the analog VREF+ and VREF- inputs. The operation of pins RA5:RA0 as A/D converter inputs is selected by clearing or setting the PCFG3:PCFG0 control bits in the ADCON1 register.

Note:	RA5 and RA3:RA0 are configured as
	analog inputs on any Reset and are read
	as '0'. RA4 is configured as a digital input.

The RA4/T0CKI pin is a Schmitt Trigger input. All other PORTA pins have TTL input levels and full CMOS output drivers.

The TRISA register controls the direction of the PORTA pins, even when they are being used as analog inputs. The user must ensure the bits in the TRISA register are maintained set when using them as analog inputs.

The RA0 and RA1 pins can also be configured as the outputs for the two Ethernet LED indicators. When configured, these two pins are the only pins on PORTA that are capable of high output drive levels.

Although the port is only six bits wide, PORTA<7> is implemented as RJPU, the weak pull-up control bit for PORTJ. In a similar fashion, the LATA<7:6> bits are implemented, not as latch bits, but the pull-up control bits, RDPU and REPU, for PORTD and PORTE. Setting these bits enables the pull-ups for the corresponding port. Because their port pins are not used, the TRISA<7:6> bits are not implemented.

#### EXAMPLE 10-1: INITIALIZING PORTA

CLRF	PORTA	; Initialize PORTA by ; clearing output
		, <u>,</u>
		; data latches
CLRF	LATA	; Alternate method
		; to clear output
		; data latches
MOVLW	07h	; Configure A/D
MOVWF	ADCON1	; for digital inputs
MOVWF	07h	; Configure comparators
MOVWF	CMCON	; for digital input
MOVLW	OCFh	; Value used to
		; initialize data
		; direction
MOVWF	TRISA	; Set RA<3:0> as inputs
		; RA<5:4> as outputs
1		

IADLE IV-J.		FUNCTIC				
Pin Name	Function I/O			l/O Type	Description	
RA0/LEDA/AN0	RA0	0	0	DIG	LATA<0> data output; not affected by analog input.	
		1	I	TTL	PORTA<0> data input; disabled when analog input enabled.	
	LEDA	0	0	DIG	Ethernet LEDA output; takes priority over digital data.	
	AN0	1	I	ANA	A/D input channel 0. Default input configuration on POR; does not affect digital output.	
RA1/LEDB/AN1	RA1	0	0	DIG	LATA<1> data output; not affected by analog input.	
		1	I	TTL	PORTA<1> data input; disabled when analog input enabled.	
	LEDB	0	0	DIG	Ethernet LEDB output; takes priority over digital data.	
	AN1	1	I	ANA	A/D input channel 1. Default input configuration on POR; does not affect digital output.	
RA2/AN2/VREF-	RA2	0	0	DIG	LATA<2> data output; not affected by analog input. Disabled when CVREF output enabled.	
		1	I	TTL	PORTA<2> data input. Disabled when analog functions enabled; disabled when CVREF output enabled.	
	AN2	1	I	ANA	A/D input channel 2 and comparator C2+ input. Default input configuration on POR; not affected by analog output.	
	VREF-	1	I	ANA	A/D and comparator low reference voltage input.	
RA3/AN3/VREF+	RA3	0	0	DIG	LATA<3> data output; not affected by analog input.	
		1	I	TTL	PORTA<3> data input; disabled when analog input enabled.	
	AN3	1	I	ANA	A/D input channel 3. Default input configuration on POR.	
	VREF+	1	I	ANA	A/D high reference voltage input.	
RA4/T0CKI	RA4	0	0	DIG	LATA<4> data output.	
		1	I	ST	PORTA<4> data input; default configuration on POR.	
	TOCKI	х	Ι	ST	Timer0 clock input.	
RA5/AN4	RA5	0	0	DIG	LATA<5> data output; not affected by analog input.	
		1	Ι	TTL	PORTA<5> data input; disabled when analog input enabled.	
	AN4	1	I	ANA	A/D input channel 4. Default configuration on POR.	

TABLE 10-3:PORTA FUNCTIONS

**Legend:** O = Output, I = Input, ANA = Analog Signal, DIG = Digital Output, ST = Schmitt Buffer Input, TTL = TTL Buffer Input, x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTA	RJPU <sup>(1)</sup>		RA5	RA4	RA3	RA2	RA1	RA0	62
LATA	RDPU	REPU	LATA5	LATA4	LATA3	LATA2	LATA1	LATA0	62
TRISA	_	_	TRISA5	TRISA4	TRISA3	TRISA2	TRISA1	TRISA0	61
ADCON1	_	_	VCFG1	VCFG0	PCFG3	PCFG2	PCFG1	PCFG0	60

Legend: — = unimplemented, read as '0'. Shaded cells are not used by PORTA.

Note 1: Implemented in 80-pin and 100-pin devices only.

# 10.3 PORTB, TRISB and LATB Registers

PORTB is an 8-bit wide, bidirectional port; it is fully implemented on all devices. The corresponding Data Direction register is TRISB. Setting a TRISB bit (= 1) will make the corresponding PORTB pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISB bit (= 0) will make the corresponding PORTB pin an output (i.e., put the contents of the output latch on the selected pin). All pins on PORTB are digital only and tolerate voltages up to 5.5V.

The Output Latch register (LATB) is also memory mapped. Read-modify-write operations on the LATB register read and write the latched output value for PORTB.

#### EXAMPLE 10-2: INITIALIZING PORTB

CLRF E	;	Initialize PORTB by clearing output data latches
CLRF I	LATB ;	Alternate method
		to clear output
	;	data latches
MOVLW (	)CFh ;	Value used to
	;	initialize data
	;	direction
MOVWF 1	TRISB ;	Set RB<3:0> as inputs
	;	RB<5:4> as outputs
	;	RB<7:6> as inputs

Each of the PORTB pins has a weak internal pull-up. A single control bit can turn on all of the pull-ups. This is performed by clearing bit, RBPU (INTCON2<7>). The weak pull-up is automatically turned off when the port pin is configured as an output. The pull-ups are disabled on all Resets.

Four of the PORTB pins (RB7:RB4) have an interrupt-on-change feature. Only pins configured as inputs can cause this interrupt to occur (i.e., any RB7:RB4 pin configured as an output is excluded from the interrupt-on-change comparison). The input pins (of RB7:RB4) are compared with the old value latched on the last read of PORTB. The "mismatch" outputs of RB7:RB4 are ORed together to generate the RB Port Change Interrupt with Flag bit, RBIF (INTCON<0>).

This interrupt can wake the device from power-managed modes. The user, in the Interrupt Service Routine, can clear the interrupt in the following manner:

- a) Any read or write of PORTB (except with the MOVFF (ANY), PORTB instruction). This will end the mismatch condition.
- b) Clear flag bit, RBIF.

A mismatch condition will continue to set flag bit, RBIF. Reading PORTB will end the mismatch condition and allow flag bit, RBIF, to be cleared.

The interrupt-on-change feature is recommended for wake-up on key depression operation and operations where PORTB is only used for the interrupt-on-change feature. Polling of PORTB is not recommended while using the interrupt-on-change feature.

For 100-pin devices operating in Extended Microcontroller mode, RB3 can be configured as the alternate peripheral pin for the ECCP2 module and Enhanced PWM output 2A by clearing the CCP2MX Configuration bit. If the devices are in Microcontroller mode, the alternate assignment for ECCP2 is RE7. As with other ECCP2 configurations, the user must ensure that the TRISB<3> bit is set appropriately for the intended operation.

IABLE 10-5:	PURIE	BFUNCT		_				
Pin Name	Function	TRIS Setting	I/O	l/O Type	Description			
RB0/INT0/FLT0	RB0	0	0	DIG	LATB<0> data output.			
		1	I	TTL	PORTB<0> data input; weak pull-up when RBPU bit is cleared.			
	INT0	1	I	ST	External interrupt 0 input.			
	FLT0	1	I	ST	Enhanced PWM Fault input (ECCP1 module); enabled in software.			
RB1/INT1	RB1	0	0	DIG	LATB<1> data output.			
		1	I	TTL	PORTB<1> data input; weak pull-up when RBPU bit is cleared.			
	INT1	1	I	ST	External interrupt 1 input.			
RB2/INT2	RB2	0	0	DIG	LATB<2> data output.			
		1	I	TTL	PORTB<2> data input; weak pull-up when RBPU bit is cleared.			
	INT2	1	I	ST	External interrupt 2 input.			
RB3/INT3/	RB3	0	0	DIG	LATB<3> data output.			
ECCP2/P2A		1	I	TTL	PORTB<3> data input; weak pull-up when RBPU bit is cleared.			
	INT3	1	I	ST	External interrupt 3 input.			
	ECCP2 <sup>(1)</sup>	0	0	DIG	ECCP2 compare output and PWM output; takes priority over port data.			
		1	I	ST	ECCP2 capture input.			
	P2A <sup>(1)</sup>	0	0	DIG	ECCP2 Enhanced PWM output, channel A. May be configured for tri-state during Enhanced PWM shutdown events. Takes priority over port data.			
RB4/KBI0	RB4	0	0	DIG	LATB<4> data output.			
		1	I	TTL	PORTB<4> data input; weak pull-up when RBPU bit is cleared.			
	KBI0	1	I	TTL	Interrupt-on-pin change.			
RB5/KBI1	RB5	0	0	DIG	LATB<5> data output.			
		1	I	TTL	PORTB<5> data input; weak pull-up when RBPU bit is cleared.			
	KBI1	1	I	TTL	Interrupt-on-pin change.			
RB6/KBI2/PGC	RB6	0	0	DIG	LATB<6> data output.			
		1	I	TTL	PORTB<6> data input; weak pull-up when RBPU bit is cleared.			
	KBI2	1	I	TTL	Interrupt-on-pin change.			
	PGC	х	I	ST	Serial execution (ICSP <sup>™</sup> ) clock input for ICSP and ICD operation. <sup>(2)</sup>			
RB7/KBI3/PGD	RB7	0	0	DIG	LATB<7> data output.			
		1	I	TTL	PORTB<7> data input; weak pull-up when RBPU bit is cleared.			
	KBI3	1	I	TTL	Interrupt-on-pin change.			
	PGD	X	0	DIG	Serial execution data output for ICSP and ICD operation. <sup>(2)</sup>			
		х	I	ST	Serial execution data input for ICSP and ICD operation. <sup>(2)</sup>			

TABLE 10-5: PORTB FUNCTIONS

Legend: O = Output, I = Input, DIG = Digital Output, ST = Schmitt Buffer Input, TTL = TTL Buffer Input,

x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

**Note 1:** Alternate assignment for ECCP2/P2A when the CCP2MX Configuration bit is cleared (100-pin devices in Extended Microcontroller mode). Default assignment is RC1.

2: All other pin functions are disabled when ICSP or ICD is enabled.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTB	RB7	RB6	RB5	RB4	RB3	RB2	RB1	RB0	62
LATB	LATB7	LATB6	LATB5	LATB4	LATB3	LATB2	LATB1	LATB0	62
TRISB	TRISB7	TRISB6	TRISB5	TRISB4	TRISB3	TRISB2	TRISB1	TRISB0	61
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
INTCON2	RBPU	INTEDG0	INTEDG1	INTEDG2	INTEDG3	TMR0IP	INT3IP	RBIP	59
INTCON3	INT2IP	INT1IP	INT3IE	INT2IE	INT1IE	INT3IF	INT2IF	INT1IF	59

# TABLE 10-6: SUMMARY OF REGISTERS ASSOCIATED WITH PORTB

Legend: Shaded cells are not used by PORTB.

# 10.4 PORTC, TRISC and LATC Registers

PORTC is an 8-bit wide, bidirectional port; it is fully implemented on all devices. The corresponding Data Direction register is TRISC. Setting a TRISC bit (= 1) will make the corresponding PORTC pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISC bit (= 0) will make the corresponding PORTC pin an output (i.e., put the contents of the output latch on the selected pin). Only PORTC pins, RC2 through RC7, are digital only pins and can tolerate input voltages up to 5.5V.

The Output Latch register (LATC) is also memory mapped. Read-modify-write operations on the LATC register read and write the latched output value for PORTC.

PORTC is multiplexed with several peripheral functions (Table 10-7). The pins have Schmitt Trigger input buffers. RC1 is normally configured by Configuration bit, CCP2MX, as the default peripheral pin for the ECCP2 module and Enhanced PWM output P2A (default state, CCP2MX = 1).

When enabling peripheral functions, care should be taken in defining TRIS bits for each PORTC pin. Some peripherals override the TRIS bit to make a pin an output, while other peripherals override the TRIS bit to make a pin an input. The user should refer to the corresponding peripheral section for the correct TRIS bit settings. Note: These pins are configured as digital inputs on any device Reset.

The contents of the TRISC register are affected by peripheral overrides. Reading TRISC always returns the current contents, even though a peripheral device may be overriding one or more of the pins.

EXAMPLE 10-3:	INITIALIZING PORTC

PORTC	; Initialize PORTC by ; clearing output
	; data latches
LATC	; Alternate method ; to clear output
005	; data latches
UCFN	; Value used to ; initialize data
	; direction
TRISC	; Set RC<3:0> as inputs ; RC<5:4> as outputs ; RC<7:6> as inputs
	LATC OCFh

Pin Name	Function	TRIS Setting	I/O	I/O Type	Description	
RC0/T1OSO/ T13CKI	RC0	0	0	DIG	LATC<0> data output.	
		1	Ι	ST	PORTC<0> data input.	
	T10SO	х	0	ANA	Timer1 oscillator output; enabled when Timer1 oscillator enabled. Disables digital I/O.	
	T13CKI	1	Ι	ST	Timer1/Timer3 counter input.	
RC1/T1OSI/ ECCP2/P2A	RC1	RC1 0 0 [		DIG	LATC<1> data output.	
		1	I	ST	PORTC<1> data input.	
	T10SI	х	I	ANA	A Timer1 oscillator input; enabled when Timer1 oscillator enabled. Disa digital I/O.	
	ECCP2 <sup>(1)</sup>	0	0	DIG	ECCP2 compare output and PWM output; takes priority over port data.	
		1	Ι	ST	ECCP2 capture input.	
	P2A <sup>(1)</sup>	0	0	DIG	ECCP2 Enhanced PWM output, channel A. May be configured for tri-state during Enhanced PWM shutdown events. Takes priority over port data.	
RC2/ECCP1/	RC2	0	0	DIG	LATC<2> data output.	
P1A		1	I	ST	PORTC<2> data input.	
	ECCP1	0	0	DIG	ECCP1 compare output and PWM output; takes priority over port data.	
		1	I	ST	ECCP1 capture input.	
	P1A	0	0	DIG	ECCP1 Enhanced PWM output, channel A. May be configured for tri-state during Enhanced PWM shutdown events. Takes priority over port data.	
RC3/SCK1/ SCL1	RC3	0	0	DIG	LATC<3> data output.	
		1	Ι	ST	PORTC<3> data input.	
	SCK1	0	0	DIG	SPI clock output (MSSP1 module); takes priority over port data.	
		1	I	ST	SPI clock input (MSSP1 module).	
	SCL1	0	0	DIG	I <sup>2</sup> C <sup>™</sup> clock output (MSSP1 module); takes priority over port data.	
		1	I	ST	I <sup>2</sup> C clock input (MSSP1 module); input type depends on module setting.	
RC4/SDI1/	RC4	0	0	DIG	LATC<4> data output.	
SDA1		1	I	ST	PORTC<4> data input.	
	SDI1	1	I	ST	SPI data input (MSSP1 module).	
	SDA1	1	0	DIG	I <sup>2</sup> C data output (MSSP1 module); takes priority over port data.	
		1	I	ST	I <sup>2</sup> C data input (MSSP1 module); input type depends on module setting.	
RC5/SDO1	RC5	0	0	DIG	LATC<5> data output.	
		1	I	ST	PORTC<5> data input.	
	SDO1	0	0	DIG	SPI data output (MSSP1 module); takes priority over port data.	
RC6/TX1/CK1	RC6	0	0	DIG	LATC<6> data output.	
		1	I	ST	PORTC<6> data input.	
	TX1	1	0	DIG	Synchronous serial data output (EUSART1 module); takes priority over port data	
	CK1	1	0	DIG	Synchronous serial data input (EUSART1 module). User must configure as an input.	
		1	I	ST	Synchronous serial clock input (EUSART1 module).	
RC7/RX1/DT1	RC7	0	0	DIG	LATC<7> data output.	
		1	Ι	ST	PORTC<7> data input.	
	RX1	1	Ι	ST	Asynchronous serial receive data input (EUSART1 module).	
	DT1	1	0	DIG	Synchronous serial data output (EUSART1 module); takes priority over port data.	
		1	Ι	ST	Synchronous serial data input (EUSART1 module). User must configure as an input.	

## TABLE 10-7: PORTC FUNCTIONS

Legend: O = Output, I = Input, ANA = Analog Signal, DIG = Digital Output, ST = Schmitt Buffer Input,

x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

Note 1: Default assignment for ECCP2/P2A when CCP2MX Configuration bit is set.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTC	RC7	RC6	RC5	RC4	RC3	RC2	RC1	RC0	62
LATC	LATC7	LATC6	LATC5	LATC4	LATC3	LATC2	LATC1	LATC0	62
TRISC	TRISC7	TRISC6	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	61

TABLE 10-8: SUMMARY OF REGISTERS ASSOCIATED WITH PORTC

## 10.5 PORTD, TRISD and LATD Registers

PORTD is implemented as a bidirectional port in two ways:

- 64-pin and 80-pin devices: 3 bits (RD<2:0>)
- 100-pin devices: 8 bits (RD<7:0>)

The corresponding Data Direction register is TRISD. Setting a TRISD bit (= 1) will make the corresponding PORTD pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISD bit (= 0) will make the corresponding PORTD pin an output (i.e., put the contents of the output latch on the selected pin). All pins on PORTD are digital only and tolerate voltages up to 5.5V.

The Output Latch register (LATD) is also memory mapped. Read-modify-write operations on the LATD register read and write the latched output value for PORTD.

All pins on PORTD are implemented with Schmitt Trigger input buffers. Each pin is individually configurable as an input or output.

Note:	These pins are configured as digital inputs	
	on any device Reset.	

On 100-pin devices, PORTD is multiplexed with the system bus as part of the external memory interface. I/O port and other functions are only available when the interface is disabled by setting the EBDIS bit (MEMCON<7>). When the interface is enabled, PORTD is the low-order byte of the multiplexed address/data bus (AD7:AD0). The TRISD bits are also overridden.

Each of the PORTD pins has a weak internal pull-up. A single control bit can turn on all of the pull-ups. This is performed by setting the RDPU bit (LATA<7>). The weak pull-up is automatically turned off when the port pin is configured as an output. The pull-ups are disabled on all device Resets.

On 100-pin devices, PORTD can also be configured to function as an 8-bit wide, parallel microprocessor port by setting the PSPMODE control bit (PSPCON<4>). In this mode, parallel port data takes priority over other digital I/O (but not the external memory interface). When the parallel port is active, the input buffers are TTL. For more information, refer to **Section 10.11** "**Parallel Slave Port**".

EXAMPLE 10-4:	INITIALIZING PORTD

CLRF	PORTD	; Initialize PORTD by ; clearing output
CLRF	LATD	; data latches ; Alternate method ; to clear output
MOVLW	OCFh	; data latches ; Value used to ; initialize data
MOVWF	TRISD	; direction
		; RD<5:4> as outputs ; RD<7:6> as inputs

TABLE 10-9:	PORTD	FUNCTIO	ONS		Τ
Pin Name	Function	TRIS Setting	I/O	I/O Type	Description
RD0/AD0/PSP0	RD0	0	0	DIG	LATD<0> data output.
(RD0/P1B)		1	I	ST	PORTD<0> data input; weak pull-up when RDPU bit is set.
	AD0 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 0 output. <sup>(2)</sup>
		х	I	TTL	External memory interface, data bit 0 input. <sup>(2)</sup>
	PSP0 <sup>(1)</sup>	х	0	DIG	PSP read output data (LATD<0>); takes priority over port data.
		х	I	TTL	PSP write data input.
	P1B <sup>(3)</sup>	0	0	DIG	ECCP1 Enhanced PWM output, channel B; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RD1/AD1/PSP1	RD1	0	0	DIG	LATD<1> data output.
(RD1/ECCP3/		1	I	ST	PORTD<1> data input; weak pull-up when RDPU bit is set.
P3A)	AD1 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 1 output. <sup>(2)</sup>
		х	I	TTL	External memory interface, data bit 1 input. <sup>(2)</sup>
	PSP1 <sup>(1)</sup>	х	0	DIG	PSP read output data (LATD<1>); takes priority over port data.
		х	I	TTL	PSP write data input.
	ECCP3 <sup>(3)</sup>	0	0	DIG	ECCP3 compare and PWM output; takes priority over port data.
		1	I	ST	ECCP3 capture input.
	P3A(3)	0	0	DIG	ECCP3 Enhanced PWM output, channel A; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RD2/AD2/PSP2	RD2	0	0	DIG	LATD<2> data output.
(RD2/CCP4/		1	I	ST	PORTD<2> data input; weak pull-up when RDPU bit is set.
P3D)	AD2 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 2 output. <sup>(2)</sup>
		х	I	TTL	External memory interface, data bit 2 input. <sup>(2)</sup>
	PSP2 <sup>(1)</sup>	х	0	DIG	PSP read output data (LATD<2>); takes priority over port data.
		х	I	TTL	PSP write data input.
	CCP4 <sup>(3)</sup>	0	0	DIG	CCP4 compare output and PWM output; takes priority over port data.
		1	I	ST	CCP4 capture input.
	P3D <sup>(3)</sup>	0	0	DIG	ECCP3 Enhanced PWM output, channel D; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RD3/AD3/	RD3 <sup>(1)</sup>	0	0	DIG	LATD<3> data output.
PSP3 <sup>(1)</sup>		1	I	ST	PORTD<3> data input; weak pull-up when RDPU bit is set.
	AD3 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 3 output. <sup>(2)</sup>
		х	I	TTL	External memory interface, data bit 3 input. <sup>(2)</sup>
	PSP3 <sup>(1)</sup>	х	0	DIG	PSP read output data (LATD<3>); takes priority over port data.
		х	I	TTL	PSP write data input.
RD4/AD4/	RD4 <sup>(1)</sup>	0	0	DIG	LATD<4> data output.
		1	I	ST	PORTD<4> data input; weak pull-up when RDPU bit is set.
PSP4/SDO2 <sup>(1)</sup>			0	DIG	External memory interface, address/data bit 4 output. <sup>(2)</sup>
PSP4/SDO2 <sup>(1)</sup>	AD4 <sup>(1)</sup>	x	0	DIO	External memory interface, address/data bit 4 output.
PSP4/SDO2 <sup>(1)</sup>	AD4 <sup>(1)</sup>	x	1	TTL	External memory interface, data bit 4 input. <sup>(2)</sup>
PSP4/SDO2 <sup>(1)</sup>	AD4 <sup>(1)</sup> PSP4 <sup>(1)</sup>				
PSP4/SDO2 <sup>(1)</sup>		х	I	TTL	External memory interface, data bit 4 input. <sup>(2)</sup>

TABLE 10-9: PORTD FUNCTIONS

Legend: O = Output, I = Input, DIG = Digital Output, ST = Schmitt Buffer Input, TTL = TTL Buffer Input,

x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

**Note 1:** These features or port pins are implemented only on 100-pin devices.

2: External memory interface I/O takes priority over all other digital and PSP I/O.

**3:** These features are implemented on this pin only on 64-pin devices; for all other devices, they are multiplexed with RE6/RH7 (P1B), RG0 (ECCP3/P3A) or RG3 (CCP4/P3D).

Pin Name	Function	TRIS Setting	I/O	l/O Type	Description
RD5/AD5/	RD5 <sup>(1)</sup>	0	0	DIG	LATD<5> data output.
PSP5/SDI2/		1	I	ST	PORTD<5> data input; weak pull-up when RDPU bit is set.
SDA2 <sup>(1)</sup>	AD5 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 5 output. <sup>(2)</sup>
		х	I	TTL	External memory interface, data bit 5 input. <sup>(2)</sup>
	PSP5 <sup>(1)</sup>	х	0	DIG	PSP read output data (LATD<5>); takes priority over port data.
		х	Ι	TTL	PSP write data input.
	SDI2 <sup>(1)</sup>	1	Ι	ST	SPI data input (MSSP2 module).
	SDA2 <sup>(1)</sup>	1	0	DIG	I <sup>2</sup> C <sup>™</sup> data output (MSSP2 module); takes priority over port data.
		1	I	ST	I <sup>2</sup> C data input (MSSP2 module); input type depends on module setting.
RD6/AD6/	RD6 <sup>(1)</sup>	0	0	DIG	LATD<6> data output.
PSP6/SCK2/		1	Ι	ST	PORTD<6> data input; weak pull-up when RDPU bit is set.
SCL2 <sup>(1)</sup>	AD6 <sup>(1)</sup>	х	0	DIG-3	External memory interface, address/data bit 6 output. <sup>(2)</sup>
		х	Ι	TTL	External memory interface, data bit 6 input. <sup>(2)</sup>
	PSP6 <sup>(1)</sup>	х	0	DIG	PSP read output data (LATD<6>); takes priority over port data.
		х		TTL	PSP write data input.
	SCK2 <sup>(1)</sup>	0	0	DIG	SPI clock output (MSSP2 module); takes priority over port data.
		1	-	ST	SPI clock input (MSSP2 module).
	SCL2 <sup>(1)</sup>	0	0	DIG	I <sup>2</sup> C clock output (MSSP2 module); takes priority over port data.
		1	Ι	ST	I <sup>2</sup> C clock input (MSSP2 module); input type depends on module setting.
RD7/A <u>D7/</u>	RD7 <sup>(1)</sup>	0	0	DIG	LATD<7> data output.
PSP7/SS2 <sup>(1)</sup>		1	I	ST	PORTD<7> data input; weak pull-up when RDPU bit is set.
	AD7 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 7 output. <sup>(2)</sup>
		х	I	TTL	External memory interface, data bit 7 input. <sup>(2)</sup>
	PSP7 <sup>(1)</sup>	х	0	DIG	PSP read output data (LATD<7>); takes priority over port data.
		х	Ι	TTL	PSP write data input.
	SS2 <sup>(1)</sup>	х	I	TTL	Slave select input for MSSP2 module.

### TABLE 10-9: PORTD FUNCTIONS (CONTINUED)

**Legend:** O = Output, I = Input, DIG = Digital Output, ST = Schmitt Buffer Input, TTL = TTL Buffer Input, x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

**Note 1:** These features or port pins are implemented only on 100-pin devices.

**Ste 1:** These realures of port pins are implemented only of 100-pin devices.

2: External memory interface I/O takes priority over all other digital and PSP I/O.

**3:** These features are implemented on this pin only on 64-pin devices; for all other devices, they are multiplexed with RE6/RH7 (P1B), RG0 (ECCP3/P3A) or RG3 (CCP4/P3D).

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTD	RD7 <sup>(1)</sup>	RD6 <sup>(1)</sup>	RD5 <sup>(1)</sup>	RD4 <sup>(1)</sup>	RD3 <sup>(1)</sup>	RD2	RD1	RD0	62
LATD	LATD7 <sup>(1)</sup>	LATD6 <sup>(1)</sup>	LATD5 <sup>(1)</sup>	LATD4 <sup>(1)</sup>	LATD3 <sup>(1)</sup>	LATD2	LATD1	LATD0	62
TRISD	TRISD7 <sup>(1)</sup>	TRISD6 <sup>(1)</sup>	TRISD5 <sup>(1)</sup>	TRISD4 <sup>(1)</sup>	TRISD3 <sup>(1)</sup>	TRISD2	TRISD1	TRISD0	61
LATA	RDPU	REPU	LATA5	LATA4	LATA3	LATA2	LATA1	LATA0	62

Legend: Shaded cells are not used by PORTD.

Note 1: Unimplemented on 64-pin and 80-pin devices; read as '0'.

## 10.6 PORTE, TRISE and LATE Registers

PORTE is implemented as a bidirectional port in two different ways:

- 64-pin devices: 6 bits wide (RE<5:0>)
- 80-pin and 100-pin devices: 8 bits wide (RE<7:0>)

The corresponding Data Direction register is TRISE. Setting a TRISE bit (= 1) will make the corresponding PORTE pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISE bit (= 0) will make the corresponding PORTE pin an output (i.e., put the contents of the output latch on the selected pin). All pins on PORTE are digital only and tolerate voltages up to 5.5V.

The Output Latch register (LATE) is also memory mapped. Read-modify-write operations on the LATE register read and write the latched output value for PORTE.

All pins on PORTE are implemented with Schmitt Trigger input buffers. Each pin is individually configurable as an input or output.

Note:	These pins are configured as digital inputs
	on any device Reset.

On 100-pin devices, PORTE is multiplexed with the system bus as part of the external memory interface. I/O port and other functions are only available when the interface is disabled by setting the EBDIS bit (MEMCON<7>). When the interface is enabled, PORTE is the high-order byte of the multiplexed address/data bus (AD15:AD8). The TRISE bits are also overridden.

Each of the PORTE pins has a weak internal pull-up. A single control bit can turn on all of the pull-ups. This is performed by setting bit REPU (LATA<6>). The weak pull-up is automatically turned off when the port pin is configured as an output. The pull-ups are disabled on all device Resets.

PORTE is also multiplexed with Enhanced PWM outputs B and C for ECCP1 and ECCP3 and outputs B, C and D for ECCP2. For 80-pin and 100-pin devices, their default assignments are on PORTE<6:0>. For 64-pin devices, their default assignments are on PORTE<5:0> and PORTD<0>. On 80-pin and 100-pin devices, the multiplexing for the outputs of ECCP1 and ECCP3 is controlled by the ECCPMX Configuration bit. Clearing this bit reassigns the P1B/P1C and P3B/P3C outputs to PORTH.

For 80-pin and 100-pin devices operating in Microcontroller mode, pin RE7 can be configured as the alternate peripheral pin for the ECCP2 module and Enhanced PWM output 2A. This is done by clearing the CCP2MX Configuration bit.

When the Parallel Slave Port is active on PORTD, three of the PORTE pins (RE0, RE1 and RE2) are configured as digital control inputs for the port. The control functions are summarized in Table 10-11. The reconfiguration occurs automatically when the PSPMODE control bit (PSPCON<4>) is set. Users must still make certain the corresponding TRISE bits are set to configure these pins as digital inputs.

#### EXAMPLE 10-5: INITIALIZING PORTE

CLRF	PORTE	; Initialize PORTE by ; clearing output ; data latches
CLRF	LATE	; Alternate method ; to clear output
MOVLW	03h	; data latches ; Value used to ; initialize data
MOVWF	TRISE	; direction ; Set RE<1:0> as inputs ; RE<7:2> as outputs

Pin Name	Function	TRIS Setting	I/O	I/O Type	Description
RE0/AD8/RD/	RE0	0	0	DIG	LATE<0> data output.
P2D		1	I	ST	PORTE<0> data input; weak pull-up when REPU bit is set.
	AD8 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 8 output. <sup>(2)</sup>
		х	I	TTL	External memory interface, data bit 8 input. <sup>(2)</sup>
	RD <sup>(6)</sup>	1	Ι	TTL	Parallel Slave Port read enable control input.
	P2D	0	0	DIG	ECCP2 Enhanced PWM output, channel D; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RE1/AD9/WR/	RE1	0	0	DIG	LATE<1> data output.
P2C		1		ST	PORTE<1> data input; weak pull-up when REPU bit is set.
	AD9 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 9 output. <sup>(2)</sup>
		х	Ι	TTL	External memory interface, data bit 9 input. <sup>(2)</sup>
	WR(6)	1	Ι	TTL	Parallel Slave Port write enable control input.
	P2C	0	0	DIG	ECCP2 Enhanced PWM output, channel C; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RE2/AD10/CS/	RE2	0	0	DIG	LATE<2> data output.
P2B		1	I	ST	PORTE<2> data input; weak pull-up when REPU bit is set.
	AD10 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 10 output. <sup>(2)</sup>
		х	Ι	TTL	External memory interface, data bit 10 input. <sup>(2)</sup>
	CS <sup>(6)</sup>	1	Ι	TTL	Parallel Slave Port chip select control input.
	P2B	0	0	DIG	ECCP2 Enhanced PWM output, channel B; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RE3/AD11/	RE3	0	0	DIG	LATE<3> data output.
P3C		1		ST	PORTE<3> data input; weak pull-up when REPU bit is set.
	AD11 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 11 output. <sup>(2)</sup>
		х	-	TTL	External memory interface, data bit 11 input. <sup>(2)</sup>
	P3C <sup>(3)</sup>	0	0	DIG	ECCP3 Enhanced PWM output, channel C; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RE4/AD12/	RE4	0	0	DIG	LATE<4> data output.
P3B		1	Ι	ST	PORTE<4> data input; weak pull-up when REPU bit is set.
	AD12 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 12 output. <sup>(2)</sup>
		х	Ι	TTL	External memory interface, data bit 12 input. <sup>(2)</sup>
	P3B <sup>(3)</sup>	0	0	DIG	ECCP3 Enhanced PWM output, channel B; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.

## TABLE 10-11: PORTE FUNCTIONS

Legend: O = Output, I = Input, DIG = Digital Output, ST = Schmitt Buffer Input, TTL = TTL Buffer Input,

x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

Note 1: EMB functions implemented on 100-pin devices only.

2: External memory interface I/O takes priority over all other digital and PSP I/O.

3: Default assignments for P1B/P1C and P3B/P3C when ECCPMX Configuration bit is set (80-pin and 100-pin devices).

**4:** Unimplemented on 64-pin devices.

5: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (80-pin and 100-pin devices in Microcontroller mode).

6: Unimplemented on 64-pin and 80-pin devices.

Pin Name	Function	TRIS Setting	I/O	l/O Type	Description
RE5/AD13/	RE5	0	0	DIG	LATE<5> data output.
P1C		1	I	ST	PORTE<5> data input; weak pull-up when REPU bit is set.
	AD13 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 13 output. <sup>(2)</sup>
		х	Ι	TTL	External memory interface, data bit 13 input. <sup>(2)</sup>
	P1C <sup>(3)</sup>	0	0	DIG	ECCP1 Enhanced PWM output, channel C; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RE6/AD14/	RE6	0	0	DIG	LATE<6> data output.
P1B <sup>(4)</sup>		1	I	ST	PORTE<6> data input; weak pull-up when REPU bit is set.
	AD14 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 14 output. <sup>(2)</sup>
		х	Ι	TTL	External memory interface, data bit 14 input. <sup>(2)</sup>
	P1B <sup>(3)</sup>	0	0	DIG	ECCP1 Enhanced PWM output, channel B; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RE7/AD15/	RE7	0	0	DIG	LATE<7> data output.
ECCP2/P2A <sup>(4)</sup>		1	I	ST	PORTE<7> data input; weak pull-up when REPU bit is set.
	AD15 <sup>(1)</sup>	х	0	DIG	External memory interface, address/data bit 15 output. <sup>(2)</sup>
		х	I	TTL	External memory interface, data bit 15 input. <sup>(2)</sup>
	ECCP2 <sup>(5)</sup>	0	0	DIG	ECCP2 compare output and PWM output; takes priority over port data.
		1	Ι	ST	ECCP2 capture input.
	P2A <sup>(5)</sup>	0	0	DIG	ECCP2 Enhanced PWM output, channel A; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.

## TABLE 10-11: PORTE FUNCTIONS (CONTINUED)

Legend: O = Output, I = Input, DIG = Digital Output, ST = Schmitt Buffer Input, TTL = TTL Buffer Input,

x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

Note 1: EMB functions implemented on 100-pin devices only.

2: External memory interface I/O takes priority over all other digital and PSP I/O.

3: Default assignments for P1B/P1C and P3B/P3C when ECCPMX Configuration bit is set (80-pin and 100-pin devices).

**4:** Unimplemented on 64-pin devices.

5: Alternate assignment for ECCP2/P2A when CCP2MX Configuration bit is cleared (80-pin and 100-pin devices in Microcontroller mode).

6: Unimplemented on 64-pin and 80-pin devices.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTE	RE7 <sup>(1)</sup>	RE6 <sup>(1)</sup>	RE5	RE4	RE3	RE2	RE1	RE0	62
LATE	LATE7 <sup>(1)</sup>	LATE6 <sup>(1)</sup>	LATE5	LATE4	LATE3	LATE2	LATE1	LATE0	62
TRISE	TRISE7 <sup>(1)</sup>	TRISE6 <sup>(1)</sup>	TRISE5	TRISE4	TRISE3	TRISE2	TRISE1	TRISE0	61
LATA	RDPU	REPU	LATA5	LATA4	LATA3	LATA2	LATA1	LATA0	62

#### TABLE 10-12: SUMMARY OF REGISTERS ASSOCIATED WITH PORTE

Legend: — = unimplemented, read as '0'. Shaded cells are not used by PORTE.

**Note 1:** Unimplemented on 64-pin devices; read as '0'.

## 10.7 PORTF, LATF and TRISF Registers

PORTF is implemented as a bidirectional port in two different ways:

- 64-pin and 80-pin devices: 7 bits wide (RF<7:1>)
- 100-pin devices: 8 bits wide (RF<7:0>)

The corresponding Data Direction register is TRISF. Setting a TRISF bit (= 1) will make the corresponding PORTF pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISF bit (= 0) will make the corresponding PORTF pin an output (i.e., put the contents of the output latch on the selected pin). Only pin 7 of PORTF has no analog input; it is the only pin that can tolerate voltages up to 5.5V.

The Output Latch register (LATF) is also memory mapped. Read-modify-write operations on the LATF register read and write the latched output value for PORTF.

All pins on PORTF are implemented with Schmitt Trigger input buffers. Each pin is individually configurable as an input or output.

PORTF is multiplexed with several analog peripheral functions, including the A/D converter and comparator inputs, as well as the comparator outputs. Pins RF1 through RF6 may be used as comparator inputs or outputs by setting the appropriate bits in the CMCON register. To use RF6:RF1 as digital inputs, it is also necessary to turn off the comparators.

- Note 1: On device Resets, pins RF6:RF1 are configured as analog inputs and are read as '0'.
  - **2:** To configure PORTF as digital I/O, turn off comparators and set ADCON1 value.

#### EXAMPLE 10-6: INITIALIZING PORTF

CLRF PORT	; clearing output
	; data latches
CLRF LATF	; Alternate method
	; to clear output
	; data latches
MOVLW 07h	;
MOVWF CMCO	N ; Turn off comparators
MOVLW 0Fh	;
MOVWF ADCO	N1 ; Set PORTF as digital I/O
MOVLW 0CEh	; Value used to
	; initialize data
	; direction
MOVWF TRIS	F ; Set RF3:RF1 as inputs
	; RF5:RF4 as outputs
	; RF7:RF6 as inputs

RF0/AN5 <sup>(1)</sup> 	RF0 <sup>(1)</sup>	0			
RF1/AN6/	(1)		0	DIG	LATF<0> data output; not affected by analog input.
RF1/AN6/		1	Ι	ST	PORTF<0> data input; disabled when analog input enabled.
RF1/AN6/	AN5 <sup>(1)</sup>	1	I	ANA	A/D input channel 5. Default configuration on POR.
	RF1	0	0	DIG	LATF<1> data output; not affected by analog input.
C2OUT		1	I	ST	PORTF<1> data input; disabled when analog input enabled.
	AN6	1	I	ANA	A/D input channel 6. Default configuration on POR.
	C2OUT	0	0	DIG	Comparator 2 output; takes priority over port data.
RF2/AN7/	RF2	0	0	DIG	LATF<2> data output; not affected by analog input.
C1OUT		1	I	ST	PORTF<2> data input; disabled when analog input enabled.
	AN7	1	I	ANA	A/D input channel 7. Default configuration on POR.
	C1OUT	0	0	TTL	Comparator 1 output; takes priority over port data.
RF3/AN8	RF3	0	0	DIG	LATF<3> data output; not affected by analog input.
		1	I	ST	PORTF<3> data input; disabled when analog input enabled.
	AN8	1	I	ANA	A/D input channel 8 and comparator C2+ input. Default input configuration on POR; not affected by analog output.
RF4/AN9	RF4	0	0	DIG	LATF<4> data output; not affected by analog input.
		1	I	ST	PORTF<4> data input; disabled when analog input enabled.
	AN9	1	Ι	ANA	A/D input channel 9 and comparator C2- input. Default input configuration on POR; does not affect digital output.
RF5/AN10/ CVREF	RF5	0	0	DIG	LATF<5> data output; not affected by analog input. Disabled when CVREF output enabled.
		1	I	ST	PORTF<5> data input; disabled when analog input enabled. Disabled when CVREF output enabled.
F	AN10	1	I	ANA	A/D input channel 10 and comparator C1+ input. Default input configuration on POR.
	CVREF	х	0	ANA	Comparator voltage reference output. Enabling this feature disables digital I/O.
RF6/AN11	RF6	0	0	DIG	LATF<6> data output; not affected by analog input.
		1	I	ST	PORTF<6> data input; disabled when analog input enabled.
	AN11	1	I	ANA	A/D input channel 11 and comparator C1- input. Default input configuration on POR; does not affect digital output.
RF7/SS1	RF7	0	0	DIG	LATF<7> data output.
		1	I	ST	PORTF<7> data input.
F	SS1	1	I	TTL	Slave select input for MSSP1 module.

### TABLE 10-13: PORTF FUNCTIONS

**Legend:** O = Output, I = Input, ANA = Analog Signal, DIG = Digital Output, ST = Schmitt Buffer Input, TTL = TTL Buffer Input, x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

Note 1: Implemented on 100-pin devices only.

#### TABLE 10-14: SUMMARY OF REGISTERS ASSOCIATED WITH PORTF

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTF	RF7	RF6	RF5	RF4	RF3	RF2	RF1	RF0 <sup>(1)</sup>	62
LATF	LATF7	LATF6	LATF5	LATF4	LATF3	LATF2	LATF1	LATF0 <sup>(1)</sup>	62
TRISF	TRISF7	TRISF6	TRISF5	TRISF4	TRISF3	TRISF2	TRISF1	TRISF0 <sup>(1)</sup>	61
ADCON1	_	—	VCFG1	VCFG0	PCFG3	PCFG2	PCFG1	PCFG0	60
CMCON	C2OUT	C10UT	C2INV	C1INV	CIS	CM2	CM1	CM0	60
CVRCON	CVREN	CVROE	CVRR	CVRSS	CVR3	CVR2	CVR1	CVR0	60

Legend: — = unimplemented, read as '0'. Shaded cells are not used by PORTF.

Note 1: Implemented on 100-pin devices only.

## 10.8 PORTG, TRISG and LATG Registers

Depending on the particular device, PORTG is implemented as a bidirectional port in one of three ways:

- 64-pin devices: 1 bit wide (RG<4>)
- 80-pin devices: 5 bits wide (RG<4:0>)
- 100-pin devices: 8 bits wide (RG<7:0>)

The corresponding Data Direction register is TRISG. Setting a TRISG bit (= 1) will make the corresponding PORTG pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISG bit (= 0) will make the corresponding PORTG pin an output (i.e., put the contents of the output latch on the selected pin). All pins on PORTG are digital only and tolerate voltages up to 5.5V.

The Output Latch register (LATG) is also memory mapped. Read-modify-write operations on the LATG register read and write the latched output value for PORTG.

PORTG is multiplexed with EUSART2 functions on 80-pin and 100-pin devices (Table 10-15). PORTG pins have Schmitt Trigger input buffers.

When enabling peripheral functions, care should be taken in defining TRIS bits for each PORTG pin. Some peripherals override the TRIS bit to make a pin an output, while other peripherals override the TRIS bit to make a pin an input. The user should refer to the corresponding peripheral section for the correct TRIS bit settings. The pin override value is not loaded into the TRIS register. This allows read-modify-write of the TRIS register without concern due to peripheral overrides.

	L 10-7.	INTRALIZING FORTG
CLRF	PORTG	; Initialize PORTG by ; clearing output : data latches
CLRF	LATG	; data fatches ; Alternate method ; to clear output ; data latches
MOVLW	04h	; Value used to ; initialize data
MOVWF	TRISG	; direction ; Set RG1:RG0 as outputs ; RG2 as input ; RG4:RG3 as inputs

EXAMPLE 10-7: INITIALIZING PORTG

Pin Name	Function	TRIS Setting	I/O	I/O Туре	Description
RG0/ECCP3/	RG0 <sup>(1)</sup>	0	0	DIG	LATG<0> data output.
P3A <sup>(1)</sup>		1	I	ST	PORTG<0> data input.
	ECCP3 <sup>(1)</sup>	0	0	DIG	ECCP3 compare and PWM output; takes priority over port data.
		1	I	ST	ECCP3 capture input.
	P3A <sup>(1)</sup>	0	0	DIG	ECCP3 Enhanced PWM output, channel A; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RG1/TX2/	RG1 <sup>(1)</sup>	0	0	DIG	LATG<1> data output.
CK2 <sup>(1)</sup>		1	I	ST	PORTG<1> data input.
	TX2 <sup>(1)</sup>	1	0	DIG	Synchronous serial data output (EUSART2 module); takes priority over port data.
	CK2 <sup>(1)</sup>	1	0	DIG	Synchronous serial data input (EUSART2 module). User must configure as an input.
		1	Ι	ST	Synchronous serial clock input (EUSART2 module).
RG2/RX2/	RG2 <sup>(1)</sup>	0	0	DIG	LATG<2> data output.
DT2 <sup>(1)</sup>		1	I	ST	PORTG<2> data input.
	RX2 <sup>(1)</sup>	1	Ι	ST	Asynchronous serial receive data input (EUSART2 module).
	DT2 <sup>(1)</sup>	1	0	DIG	Synchronous serial data output (EUSART2 module); takes priority over port data.
		1	I	ST	Synchronous serial data input (EUSART2 module). User must configure as an input.
RG3/CCP4/	RG3 <sup>(1)</sup>	0	0	DIG	LATG<3> data output.
P3D <sup>(1)</sup>		1	I	ST	PORTG<3> data input.
	CCP4 <sup>(1)</sup>	0	0	DIG	CCP4 compare output and PWM output; takes priority over port data.
		1	I	ST	CCP4 capture input.
	P3D <sup>(1)</sup>	0	0	DIG	ECCP3 Enhanced PWM output, channel D; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RG4/CCP5/	RG4	0	0	DIG	LATG<4> data output.
P1D		1	I	ST	PORTG<4> data input.
	CCP5	0	0	DIG	CCP5 compare output and PWM output; takes priority over port data.
		1	I	ST	CCP5 capture input.
	P1D	0	0	DIG	ECCP1 Enhanced PWM output, channel D; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RG5 <sup>(2)</sup>	RG5 <sup>(2)</sup>	0	0	DIG	LATG<0> data output.
		1	I	ST	PORTG<0> data input.
RG6 <sup>(2)</sup>	RG6 <sup>(2)</sup>	0	0	DIG	LATG<0> data output.
		1	Ι	ST	PORTG<0> data input.
RG7 <sup>(2)</sup>	RG7 <sup>(2)</sup>	0	0	DIG	LATG<0> data output.
		1	I	ST	PORTG<0> data input.

TABLE 10-15: PORTG FUNCTIONS

**Legend:** O = Output, I = Input, DIG = Digital Output, ST = Schmitt Buffer Input,

 $\rm x$  = Don't care (TRIS bit does not affect port direction or is overridden for this option).

Note 1: Implemented on 80-pin and 100-pin devices only.

2: Implemented on 100-pin devices only.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTG	RG7 <sup>(1)</sup>	RG6 <sup>(1)</sup>	RG5 <sup>(1)</sup>	RG4	RG3 <sup>(2)</sup>	RG2 <sup>(2)</sup>	RG1 <sup>(2)</sup>	RG0 <sup>(2)</sup>	62
LATG	LATG7 <sup>(1)</sup>	LATG6 <sup>(1)</sup>	LATG5 <sup>(1)</sup>	LATG4	LATG3 <sup>(2)</sup>	LATG2 <sup>(2)</sup>	LATG1 <sup>(2)</sup>	LATG0 <sup>(2)</sup>	62
TRISG	TRISG7 <sup>(1)</sup>	TRISG6 <sup>(1)</sup>	TRISG5 <sup>(1)</sup>	TRISG4	TRISG3 <sup>(2)</sup>	TRISG2 <sup>(2)</sup>	TRISG1 <sup>(2)</sup>	TRISG0 <sup>(2)</sup>	61

#### TABLE 10-16: SUMMARY OF REGISTERS ASSOCIATED WITH PORTG

**Note 1:** Implemented on 100-pin devices only.

2: Implemented on 80-pin and 100-pin devices only.

### 10.9 PORTH, LATH and TRISH Registers

Note:	PORTH is available only on 80-pin and
	100-pin devices.

PORTH is an 8-bit wide, bidirectional I/O port; it is fully implemented on 80-pin and 100-pin devices. The corresponding Data Direction register is TRISH. Setting a TRISH bit (= 1) will make the corresponding PORTH pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISH bit (= 0) will make the corresponding PORTH pin an output (i.e., put the contents of the output latch on the selected pin). PORTH<3:0> pins are digital only and tolerate voltages up to 5.5V.

The Output Latch register (LATH) is also memory mapped. Read-modify-write operations on the LATH register read and write the latched output value for PORTH.

All pins on PORTH are implemented with Schmitt Trigger input buffers. Each pin is individually configurable as an input or output. When the external memory interface is enabled, four of the PORTH pins function as the high-order address lines for the interface. The address output from the interface takes priority over other digital I/O. The corresponding TRISH bits are also overridden.

PORTH pins, RH4 through RH7, are multiplexed with analog converter inputs. The operation of these pins as analog inputs is selected by clearing or setting the PCFG3:PCFG0 control bits in the ADCON1 register.

PORTH can also be configured as the alternate Enhanced PWM output channels B and C for the ECCP1 and ECCP3 modules. This is done by clearing the ECCPMX Configuration bit.

EXAMP	LE 10-8:	INITIALIZING PORTH
CLRF	PORTH	; Initialize PORTH by
		; clearing output
		; data latches
CLRF	LATH	; Alternate method
		; to clear output
		; data latches
MOVLW	OFh	; Configure PORTH as
MOVWF	ADCON1	; digital I/O
MOVLW	OCFh	; Value used to
		; initialize data
		; direction
MOVWF	TRISH	; Set RH3:RH0 as inputs
		; RH5:RH4 as outputs
		; RH7:RH6 as inputs

Pin Name	Function	TRIS Setting	I/O	l/O Type	Description
RH0/A16	RH0	0	0	DIG	LATH<0> data output.
		1	Ι	ST	PORTH<0> data input.
	A16 <sup>(1)</sup>	x	0	DIG	External memory interface, address line 16. Takes priority over port data.
RH1/A17	RH1	0	0	DIG	LATH<1> data output.
		1	Ι	ST	PORTH<1> data input.
	A17 <sup>(1)</sup>	х	0	DIG	External memory interface, address line 17. Takes priority over port data.
RH2/A18	RH2	0	0	DIG	LATH<2> data output.
		1	Ι	ST	PORTH<2> data input.
	A18 <sup>(1)</sup>	х	0	DIG	External memory interface, address line 18. Takes priority over port data.
RH3/A19	RH3	0	0	DIG	LATH<3> data output.
		1	Ι	ST	PORTH<3> data input.
	A19 <sup>(1)</sup>	х	0	DIG	External memory interface, address line 19. Takes priority over port data.
RH4/AN12/P3C	RH4	0	0	DIG	LATH<4> data output.
		1	Ι	ST	PORTH<4> data input.
	AN12		I	ANA	A/D input channel 12. Default input configuration on POR; does not affect digital output.
	P3C <sup>(2)</sup>	0	0	DIG	ECCP3 Enhanced PWM output, channel C; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RH5/AN13/P3B	RH5	0	0	DIG	LATH<5> data output.
		1	I	ST	PORTH<5> data input.
	AN13		Ι	ANA	A/D input channel 13. Default input configuration on POR; does not affect digital output.
	P3B <sup>(2)</sup>	0	0	DIG	ECCP3 Enhanced PWM output, channel B; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RH6/AN14/P1C	RH6	0	0	DIG	LATH<6> data output.
		1	I	ST	PORTH<6> data input.
	AN14		I	ANA	A/D input channel 14. Default input configuration on POR; does not affect digital output.
	P1C <sup>(2)</sup>	0	0	DIG	ECCP1 Enhanced PWM output, channel C; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.
RH7/AN15/P1B	RH7	0	0	DIG	LATH<7> data output.
		1	I	ST	PORTH<7> data input.
	AN15		Ι	ANA	A/D input channel 15. Default input configuration on POR; does not affect digital output.
	P1B <sup>(2)</sup>	0	0	DIG	ECCP1 Enhanced PWM output, channel B; takes priority over port and PSP data. May be configured for tri-state during Enhanced PWM shutdown events.

### TABLE 10-17: PORTH FUNCTIONS

Legend: O = Output, I = Input, ANA = Analog Signal, DIG = Digital Output, ST = Schmitt Buffer Input, x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

Note 1: Unimplemented on 80-pin devices.

2: Alternate assignments for P1B/P1C and P3B/P3C when ECCPMX Configuration bit is cleared (80-pin and 100-pin devices only). Default assignments are PORTE<6:3>.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTH	RH7	RH6	RH5	RH4	RH3	RH2	RH1	RH0	62
LATH	LATH7	LATH6	LATH5	LATH4	LATH3	LATH2	LATH1	LATH0	61
TRISH	TRISH7	TRISH6	TRISH5	TRISH4	TRISH3	TRISH2	TRISH1	TRISH0	61

## TABLE 10-18: SUMMARY OF REGISTERS ASSOCIATED WITH PORTH

## 10.10 PORTJ, TRISJ and LATJ Registers

Note:	PORTJ is	available	only	on	80-pin	and
	100-pin de	vices.				

PORTJ is implemented as a bidirectional port in two different ways:

- 80-pin devices: 2 bits wide (RJ<5:4>)
- 100-pin devices: 8 bits wide (RJ<7:0>)

The corresponding Data Direction register is TRISJ. Setting a TRISJ bit (= 1) will make the corresponding PORTJ pin an input (i.e., put the corresponding output driver in a high-impedance mode). Clearing a TRISJ bit (= 0) will make the corresponding PORTJ pin an output (i.e., put the contents of the output latch on the selected pin). All pins on PORTJ are digital only and tolerate voltages up to 5.5V.

The Output Latch register (LATJ) is also memory mapped. Read-modify-write operations on the LATJ register read and write the latched output value for PORTJ.

All pins on PORTJ are implemented with Schmitt Trigger input buffers. Each pin is individually configurable as an input or output.

**Note:** These pins are configured as digital inputs on any device Reset.

When the external memory interface is enabled, all of the PORTJ pins function as control outputs for the interface. This occurs automatically when the interface is enabled by clearing the EBDIS control bit (MEMCON<7>). The TRISJ bits are also overridden.

Each of the PORTJ pins has a weak internal pull-up. A single control bit can turn on all the pull-ups. This is performed by setting bit, RJPU (PORTA<7>). The weak pull-up is automatically turned off when the port pin is configured as an output. The pull-ups are disabled on all device Resets.

#### EXAMPLE 10-9: INITIALIZING PORTJ

CLRF	PORTJ	; Initialize PORTG by ; clearing output : data latches
CLRF	LATJ	; Alternate method
		; to clear output ; data latches
MOVLW	OCFh	; Value used to ; initialize data
		; direction
MOVWF	TRISJ	; Set RJ3:RJ0 as inputs ; RJ5:RJ4 as output ; RJ7:RJ6 as inputs
	CLRF	CLRF LATJ MOVLW OCFh

Pin Name	Function	TRIS Setting	I/O	l/O Type	Description	
RJ0/ALE <sup>(1)</sup>	RJ0 <sup>(1)</sup>	0	0	DIG	LATJ<0> data output.	
		1	I	ST	PORTJ<0> data input; weak pull-up when RJPU bit is set.	
	ALE <sup>(1)</sup>	х	0	DIG	External memory interface address latch enable control output; takes priority over digital I/O.	
RJ1/OE <sup>(1)</sup>	RJ1 <sup>(1)</sup>	0	0	DIG	LATJ<1> data output.	
		1	I	ST	PORTJ<1> data input; weak pull-up when RJPU bit is set.	
	OE <sup>(1)</sup>	Х	0	DIG	External memory interface output enable control output; takes priority over digital I/O.	
RJ2/WRL <sup>(1)</sup>	RJ2 <sup>(1)</sup>	0	0	DIG	LATJ<2> data output.	
		1	I	ST	PORTJ<2> data input; weak pull-up when RJPU bit is set.	
	WRL <sup>(1)</sup>	Х	0	DIG	External memory bus write low byte control; takes priority over digital I/O.	
RJ3/WRH <sup>(1)</sup>	RJ3 <sup>(1)</sup>	0	0	DIG	LATJ<3> data output.	
		1	I	ST	PORTJ<3> data input; weak pull-up when RJPU bit is set.	
	WRH <sup>(1)</sup>	Х	0	DIG	External memory interface write high byte control output; takes priority over digital I/O.	
RJ4/BA0	RJ4	0	0	DIG	LATJ<4> data output.	
		1	I	ST	PORTJ<4> data input; weak pull-up when RJPU bit is set.	
	BA0 <sup>(2)</sup>	х	0	DIG	External memory interface byte address 0 control output; takes priority over digital I/O.	
RJ5/CE	RJ5	0	0	DIG	LATJ<5> data output.	
		1	Ι	ST	PORTJ<5> data input; weak pull-up when RJPU bit is set.	
	CE <sup>(2)</sup>	х	0	DIG	External memory interface chip enable control output; takes priority over digital I/O.	
RJ6/LB <sup>(1)</sup>	RJ6 <sup>(1)</sup>	0	0	DIG	LATJ<6> data output.	
		1	I	ST	PORTJ<6> data input; weak pull-up when RJPU bit is set.	
	LB <sup>(1)</sup>	Х	0	DIG	External memory interface lower byte enable control output; takes priority over digital I/O.	
RJ7/UB <sup>(1)</sup>	RJ7 <sup>(1)</sup>	0	0	DIG	LATJ<7> data output.	
		1	I	ST	PORTJ<7> data input; weak pull-up when RJPU bit is set.	
	UB <sup>(1)</sup>	Х	0	DIG	External memory interface upper byte enable control output; takes priority over digital I/O.	

**Legend:** O = Output, I = Input, DIG = Digital Output, ST = Schmitt Buffer Input,

x = Don't care (TRIS bit does not affect port direction or is overridden for this option).

**Note 1:** Implemented on 100-pin devices only.

2: EMB functions are implemented on 100-pin devices only.

#### TABLE 10-20: SUMMARY OF REGISTERS ASSOCIATED WITH PORTJ

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTJ	RJ7 <sup>(1)</sup>	RJ6 <sup>(1)</sup>	RJ5	RJ4	RJ3 <sup>(1)</sup>	RJ2 <sup>(1)</sup>	RJ1 <sup>(1)</sup>	RJ0 <sup>(1)</sup>	62
LATJ	LATJ7 <sup>(1)</sup>	LATJ6 <sup>(1)</sup>	LATJ5	LATJ4	LATJ3 <sup>(1)</sup>	LATJ2 <sup>(1)</sup>	LATJ1 <sup>(1)</sup>	LATJ0 <sup>(1)</sup>	61
TRISJ	TRISJ7 <sup>(1)</sup>	TRISJ6 <sup>(1)</sup>	TRISJ5	TRISJ4	TRISJ3 <sup>(1)</sup>	TRISJ2 <sup>(1)</sup>	TRISJ1 <sup>(1)</sup>	TRISJ0 <sup>(1)</sup>	61
PORTA	RJPU		RA5	RA4	RA3	RA2	RA1	RA0	62

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used by PORTJ.

Note 1: Implemented on 100-pin devices only.

#### 10.11 Parallel Slave Port

Note:	The Parallel Slave Port is only implemented
	in 100-pin devices.

PORTD can also function as an 8-bit wide, Parallel Slave Port, or microprocessor port, when control bit, PSPMODE (PSPCON<4>), is set. It is asynchronously readable and writable by the external world through the RD control input pin, RE0/AD8/RD/P2D and WR control input pin, RE1/AD9//WR/P2C.

Note:	The Parallel Slave Port is available only in
	Microcontroller mode.

The PSP can directly interface to an 8-bit microprocessor data bus. The external microprocessor can read or write the PORTD latch as an 8-bit latch. Setting bit, PSPMODE, enables port pin RE0/AD8/RD/P2D to be the RD input, RE1/AD9//WR/P2C to be the WR input and RE2/AD10//CS/P2B to be the CS (Chip Select) input. For this functionality, the corresponding data direction bits of the TRISE register (TRISE<2:0>) must be configured as inputs (set).

A write to the PSP occurs when both the  $\overline{CS}$  and  $\overline{WR}$  lines are first detected low and ends when either are detected high. The PSPIF and IBF flag bits are both set when the write ends.


A read from the PSP occurs when both the  $\overline{CS}$  and  $\overline{RD}$  lines are first detected low. The data in PORTD is read out and the OBF bit is set. If the user writes new data to PORTD to set OBF, the data is immediately read out; however, the OBF bit is not set.

When either the  $\overline{CS}$  or  $\overline{RD}$  lines is detected high, the PORTD pins return to the input state and the PSPIF bit is set. User applications should wait for PSPIF to be set before servicing the PSP. When this happens, the IBF and OBF bits can be polled and the appropriate action taken.

The timing for the control signals in Write and Read modes is shown in Figure 10-3 and Figure 10-4, respectively.

## FIGURE 10-2: PORTD

#### PORTD AND PORTE BLOCK DIAGRAM (PARALLEL SLAVE PORT)




#### REGISTER 10-1: PSPCON: PARALLEL SLAVE PORT CONTROL REGISTER

-										
R-0	R-0	R/W-0	R/W-0	U-0	U-0	U-0	U-0			
IBF	OBF	IBOV	PSPMODE	—	—	—	—			
bit 7							bit 0			
Legend:										
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	as '0'				
-n = Value at F	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkn	own			
bit 7	IBF: Input But	ffer Full Status	bit							
		as been receive		ng to be read l	by the CPU					
	•	nas been recei								
bit 6	OBF: Output	Buffer Full Stat	us bit							
		It buffer still ho	•	ly written word	I					
	•	it buffer has be								
bit 5	•	uffer Overflow								
			previously inp	out word has n	ot been read (m	lust be cleared	in software)			
	0 = No overflo									
bit 4	PSPMODE: F	Parallel Slave F	ort Mode Sele	ect bit						
	1 = Parallel Slave Port mode									
		Purpose I/O mo								
bit 3-0	Unimplemen	ted: Read as '	0'							

### FIGURE 10-3: PARALLEL SLAVE PORT WRITE WAVEFORMS

	Q1   Q2   Q3   Q4 Q1   Q2   Q3   Q4 Q1   Q2   Q3   Q4
cs _	
WR	
RD -	
PORTD<7:0> -	
IBF	
OBF	
PSPIF	



#### TABLE 10-21: REGISTERS ASSOCIATED WITH PARALLEL SLAVE PORT

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
PORTD	RD7	RD6	RD5	RD4	RD3	RD2	RD1	RD0	62
LATD	LATD7	LATD6	LATD5	LATD4	LATD3	LATD2	LATD1	LATD0	62
TRISD	TRISD7	TRISD6	TRISD5	TRISD4	TRISD3	TRISD2	TRISD1	TRISD0	61
PORTE	RE7	RE6	RE5	RE4	RE3	RE2	RE1	RE0	62
LATE	LATE7	LATE6	LATE5	LATE4	LATE3	LATE2	LATE1	LATE0	62
TRISE	TRISE7	TRISE6	TRISE5	TRISE4	TRISE3	TRISE2	TRISE1	TRISE0	61
PSPCON	IBF	OBF	IBOV	PSPMODE	_	_	—	_	61
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INTOIE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61

Legend: — = unimplemented, read as '0'. Shaded cells are not used by the Parallel Slave Port.

NOTES:

## 11.0 TIMER0 MODULE

The Timer0 module incorporates the following features:

- Software selectable operation as a timer or counter in both 8-bit or 16-bit modes
- · Readable and writable registers
- Dedicated, 8-bit, software programmable prescaler
- Selectable clock source (internal or external)
- Edge select for external clock
- · Interrupt on overflow

The T0CON register (Register 11-1) controls all aspects of the module's operation, including the prescale selection. It is both readable and writable.

A simplified block diagram of the Timer0 module in 8-bit mode is shown in Figure 11-1. Figure 11-2 shows a simplified block diagram of the Timer0 module in 16-bit mode.

#### REGISTER 11-1: TOCON: TIMERO CONTROL REGISTER

R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1	R/W-1
TMR0ON	T08BIT	TOCS	TOSE	PSA	T0PS2	T0PS1	T0PS0
bit 7 bit C							

Legend:									
R = Reada	ble bit	W = Writable bit	U = Unimplemented bit,	read as '0'					
-n = Value	at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown					
bit 7	TMR0ON	I: Timer0 On/Off Control bit							
	1 = Enables Timer0								
	0 = Stops								
bit 6	T08BIT: <sup>-</sup>	Timer0 8-Bit/16-Bit Control b	it						
		r0 is configured as an 8-bit ti r0 is configured as a 16-bit ti							
bit 5	TOCS: Ti	mer0 Clock Source Select bi	t						
	1 = Trans	1 = Transition on T0CKI pin							
0 = Internal instruction cycle clock (CLKO)									
bit 4	TOSE: Ti	TOSE: Timer0 Source Edge Select bit							
	1 = Incre	1 = Increment on high-to-low transition on T0CKI pin							
	0 = Incre	ment on low-to-high transitio	n on T0CKI pin						
bit 3	PSA: Tim	PSA: Timer0 Prescaler Assignment bit							
	1 = TIme	r0 prescaler is NOT assigne	d. Timer0 clock input bypasse	s prescaler.					
	0 <b>= Time</b>	r0 prescaler is assigned. Tim	ner0 clock input comes from p	rescaler output.					
bit 2-0	T0PS2:T	0PS0: Timer0 Prescaler Sel	ect bits						
	111 = 1:256 Prescale value								
		110 = 1:128 Prescale value							
		101 = 1:64 Prescale value							
		100 = 1:32 Prescale value 011 = 1:16 Prescale value							
		B Prescale value							
		Prescale value							
	000 = 1:2								

## 11.1 Timer0 Operation

Timer0 can operate as either a timer or a counter; the mode is selected with the TOCS bit (TOCON<5>). In Timer mode (TOCS = 0), the module increments on every clock by default unless a different prescaler value is selected (see **Section 11.3 "Prescaler"**). If the TMR0 register is written to, the increment is inhibited for the following two instruction cycles. The user can work around this by writing an adjusted value to the TMR0 register.

The Counter mode is selected by setting the T0CS bit (= 1). In this mode, Timer0 increments either on every rising or falling edge of pin RA4/T0CKI. The incrementing edge is determined by the Timer0 Source Edge Select bit, T0SE (T0CON<4>); clearing this bit selects the rising edge. Restrictions on the external clock input are discussed below.


An external clock source can be used to drive Timer0; however, it must meet certain requirements to ensure that the external clock can be synchronized with the internal phase clock (Tosc). There is a delay between synchronization and the onset of incrementing the timer/counter.

#### 11.2 Timer0 Reads and Writes in 16-Bit Mode


TMR0H is not the actual high byte of Timer0 in 16-bit mode. It is actually a buffered version of the real high byte of Timer0 which is not directly readable nor writable (refer to Figure 11-2). TMR0H is updated with the contents of the high byte of Timer0 during a read of TMR0L. This provides the ability to read all 16 bits of Timer0 without having to verify that the read of the high and low byte were valid, due to a rollover between successive reads of the high and low byte.

Similarly, a write to the high byte of Timer0 must also take place through the TMR0H Buffer register. The high byte is updated with the contents of TMR0H when a write occurs to TMR0L. This allows all 16 bits of Timer0 to be updated at once.

#### FIGURE 11-1: TIMER0 BLOCK DIAGRAM (8-BIT MODE)



#### FIGURE 11-2: TIMER0 BLOCK DIAGRAM (16-BIT MODE)



### 11.3 Prescaler

An 8-bit counter is available as a prescaler for the Timer0 module. The prescaler is not directly readable or writable. Its value is set by the PSA and T0PS2:T0PS0 bits (T0CON<3:0>) which determine the prescaler assignment and prescale ratio.

Clearing the PSA bit assigns the prescaler to the Timer0 module. When it is assigned, prescale values from 1:2 through 1:256 in power-of-2 increments are selectable.

When assigned to the Timer0 module, all instructions writing to the TMR0 register (e.g., CLRF TMR0, MOVWF TMR0, BSF TMR0, etc.) clear the prescaler count.

Note:	Writing to TMR0 when the prescaler is
	assigned to Timer0 will clear the prescaler
	count but will not change the prescaler
	assignment.

#### 11.3.1 SWITCHING PRESCALER ASSIGNMENT

The prescaler assignment is fully under software control and can be changed "on-the-fly" during program execution.

## 11.4 Timer0 Interrupt

The TMR0 interrupt is generated when the TMR0 register overflows from FFh to 00h in 8-bit mode, or from FFFFh to 0000h in 16-bit mode. This overflow sets the TMR0IF flag bit. The interrupt can be masked by clearing the TMR0IE bit (INTCON<5>). Before re-enabling the interrupt, the TMR0IF bit must be cleared in software by the Interrupt Service Routine.

Since Timer0 is shut down in Sleep mode, the TMR0 interrupt cannot awaken the processor from Sleep.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
TMR0L	Timer0 Register Low Byte								
TMR0H	Timer0 Register High Byte								60
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
INTCON2	RBPU	INTEDG0	INTEDG1	INTEDG2	INTEDG3	TMR0IP	INT3IP	RBIP	59
TOCON	TMR0ON	T08BIT	TOCS	T0SE	PSA	T0PS2	T0PS1	T0PS0	60
TRISA	—	_	TRISA5	TRISA4	TRISA3	TRISA2	TRISA1	TRISA0	61

 TABLE 11-1:
 REGISTERS ASSOCIATED WITH TIMER0

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used by Timer0.

NOTES:

## 12.0 TIMER1 MODULE

The Timer1 timer/counter module incorporates these features:

- Software selectable operation as a 16-bit timer or counter
- Readable and writable 8-bit registers (TMR1H and TMR1L)
- Selectable clock source (internal or external) with device clock or Timer1 oscillator internal options
- Interrupt on overflow
- Reset on ECCP Special Event Trigger
- Device clock status flag (T1RUN)

A simplified block diagram of the Timer1 module is shown in Figure 12-1. A block diagram of the module's operation in Read/Write mode is shown in Figure 12-2.

The module incorporates its own low-power oscillator to provide an additional clocking option. The Timer1 oscillator can also be used as a low-power clock source for the microcontroller in power-managed operation.

Timer1 can also be used to provide Real-Time Clock (RTC) functionality to applications with only a minimal addition of external components and code overhead.

Timer1 is controlled through the T1CON Control register (Register 12-1). It also contains the Timer1 Oscillator Enable bit (T1OSCEN). Timer1 can be enabled or disabled by setting or clearing control bit, TMR1ON (T1CON<0>).

R/W-0	R-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
RD16	T1RUN	T1CKPS1	T1CKPS0	T1OSCEN	T1SYNC	TMR1CS	TMR10N
bit 7							bit 0

### REGISTER 12-1: T1CON: TIMER1 CONTROL REGISTER


Legend:										
R = Reada	ble bit	W = Writable bit	U = Unimplemented bit, read as '0'							
-n = Value	at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknowr						
bit 7	<b>RD16:</b> 1	6-Bit Read/Write Mode Enal	ole bit							
			mer1 in one 16-bit operation mer1 in two 8-bit operations							
bit 6	T1RUN:	T1RUN: Timer1 System Clock Status bit								
	-	ice clock is derived from Tin ice clock is derived from and								
bit 5-4	T1CKPS	1:T1CKPS0: Timer1 Input (	Clock Prescale Select bits							
		= 1:8 Prescale value								
		Prescale value								
		Prescale value Prescale value								
bit 3		T10SCEN: Timer1 Oscillator Enable bit								
	1 = Time	er1 oscillator is enabled								
		er1 oscillator is shut off								
		The oscillator inverter and feedback resistor are turned off to eliminate power drain.								
bit 2		T1SYNC: Timer1 External Clock Input Synchronization Select bit								
		<u>When TMR1CS = 1:</u>								
		L = Do not synchronize external clock input								
	•	When TMR1CS = $0$ :								
	This bit is	This bit is ignored. Timer1 uses the internal clock when TMR1CS = $0$ .								
bit 1	TMR1CS	3: Timer1 Clock Source Sele	ect bit							
			D/T13CKI pin (on the rising edg	je)						
		rnal clock (Fosc/4)								
bit 0		N: Timer1 On bit								
	1 = Ena	bles Timer1								

## 12.1 Timer1 Operation


Timer1 can operate in one of these modes:

- Timer
- Synchronous Counter
- Asynchronous Counter

The operating mode is determined by the clock select bit, TMR1CS (T1CON<1>). When TMR1CS is cleared (= 0), Timer1 increments on every internal instruction



#### FIGURE 12-2: TIMER1 BLOCK DIAGRAM (16-BIT READ/WRITE MODE)



## = 0), Timer1 increments on every internal instruction

cycle (Fosc/4). When the bit is set, Timer1 increments on every rising edge of the Timer1 external clock input or the Timer1 oscillator, if enabled.

When Timer1 is enabled, the RC1/T1OSI and RC0/T1OSO/T13CKI pins become inputs. This means the values of TRISC<1:0> are ignored and the pins are read as '0'.

### 12.2 Timer1 16-Bit Read/Write Mode

Timer1 can be configured for 16-bit reads and writes (see Figure 12-2). When the RD16 control bit (T1CON<7>) is set, the address for TMR1H is mapped to a buffer register for the high byte of Timer1. A read from TMR1L will load the contents of the high byte of Timer1 into the Timer1 High Byte Buffer register. This provides the user with the ability to accurately read all 16 bits of Timer1 without having to determine whether a read of the high byte, followed by a read of the low byte, has become invalid due to a rollover between reads.

A write to the high byte of Timer1 must also take place through the TMR1H Buffer register. The Timer1 high byte is updated with the contents of TMR1H when a write occurs to TMR1L. This allows a user to write all 16 bits to both the high and low bytes of Timer1 at once.


The high byte of Timer1 is not directly readable or writable in this mode. All reads and writes must take place through the Timer1 High Byte Buffer register. Writes to TMR1H do not clear the Timer1 prescaler. The prescaler is only cleared on writes to TMR1L.

### 12.3 Timer1 Oscillator

An on-chip crystal oscillator circuit is incorporated between pins T1OSI (input) and T1OSO (amplifier output). It is enabled by setting the Timer1 Oscillator Enable bit, T1OSCEN (T1CON<3>). The oscillator is a low-power circuit rated for 32 kHz crystals. It will continue to run during all power-managed modes. The circuit for a typical LP oscillator is shown in Figure 12-3. Table 12-1 shows the capacitor selection for the Timer1 oscillator.

The user must provide a software time delay to ensure proper start-up of the Timer1 oscillator.

#### FIGURE 12-3: EXTERNAL COMPONENTS FOR THE TIMER1 OSCILLATOR



#### TABLE 12-1: CAPACITOR SELECTION FOR THETIMEROSCILLATOR<sup>(2,3,4)</sup>

Oscillator Type	Freq. C1		C2					
LP	32 kHz	27 pF <sup>(1)</sup>	27 pF <sup>(1)</sup>					
<b>Note 1:</b> Microchip suggests these values as a starting point in validating the oscillator circuit.								
(	Higher capacita of the oscillate start-up time.		,					
t t	Since each resonator/crystal has its own characteristics, the user should consult the resonator/crystal manufacturer for appropriate values of external components.							
4: (	Capacitor valu	es are for des	ign guidance					

#### 12.3.1 USING TIMER1 AS A CLOCK SOURCE

only.

The Timer1 oscillator is also available as a clock source in power-managed modes. By setting the Clock Select bits, SCS1:SCS0 (OSCCON<1:0>), to '01', the device switches to SEC\_RUN mode; both the CPU and peripherals are clocked from the Timer1 oscillator. If the IDLEN bit (OSCCON<7>) is cleared and a SLEEP instruction is executed, the device enters SEC\_IDLE mode. Additional details are available in **Section 3.0 "Power-Managed Modes"**.

Whenever the Timer1 oscillator is providing the clock source, the Timer1 system clock status flag, T1RUN (T1CON<6>), is set. This can be used to determine the controller's current clocking mode. It can also indicate the clock source being currently used by the Fail-Safe Clock Monitor. If the Clock Monitor is enabled and the Timer1 oscillator fails while providing the clock, polling the T1RUN bit will indicate whether the clock is being provided by the Timer1 oscillator or another source.


## 12.3.2 TIMER1 OSCILLATOR LAYOUT CONSIDERATIONS

The Timer1 oscillator circuit draws very little power during operation. Due to the low-power nature of the oscillator, it may also be sensitive to rapidly changing signals in close proximity.

The oscillator circuit, shown in Figure 12-3, should be located as close as possible to the microcontroller. There should be no circuits passing within the oscillator circuit boundaries other than Vss or VDD.

If a high-speed circuit must be located near the oscillator (such as the ECCP1 pin in Output Compare or PWM mode, or the primary oscillator using the OSC2 pin), a grounded guard ring around the oscillator circuit, as shown in Figure 12-4, may be helpful when used on a single-sided PCB or in addition to a ground plane.





## 12.4 Timer1 Interrupt

The TMR1 register pair (TMR1H:TMR1L) increments from 0000h to FFFFh and rolls over to 0000h. The Timer1 interrupt, if enabled, is generated on overflow which is latched in interrupt flag bit, TMR1IF (PIR1<0>). This interrupt can be enabled or disabled by setting or clearing the Timer1 Interrupt Enable bit, TMR1IE (PIE1<0>).

## 12.5 Resetting Timer1 Using the ECCPx Special Event Trigger

If ECCP1 or ECCP2 is configured to use Timer1 and to generate a Special Event Trigger in Compare mode (CCPxM3:CCPxM0 = 1011), this signal will reset Timer3. The trigger from ECCP2 will also start an A/D conversion if the A/D module is enabled (see **Section 17.2.1 "Special Event Trigger"** for more information).

The module must be configured as either a timer or a synchronous counter to take advantage of this feature. When used this way, the CCPRxH:CCPRxL register pair effectively becomes a Period register for Timer1.

If Timer1 is running in Asynchronous Counter mode, this Reset operation may not work.

In the event that a write to Timer1 coincides with a Special Event Trigger, the write operation will take precedence.

Note: The Special Event Triggers from the ECCPx module will not set the TMR1IF interrupt flag bit (PIR1<0>).

## 12.6 Using Timer1 as a Real-Time Clock

Adding an external LP oscillator to Timer1 (such as the one described in **Section 12.3 "Timer1 Oscillator**") gives users the option to include RTC functionality to their applications. This is accomplished with an inexpensive watch crystal to provide an accurate time base and several lines of application code to calculate the time. When operating in Sleep mode and using a battery or supercapacitor as a power source, it can completely eliminate the need for a separate RTC device and battery backup.

The application code routine, RTCisr, shown in Example 12-1, demonstrates a simple method to increment a counter at one-second intervals using an Interrupt Service Routine. Incrementing the TMR1 register pair to overflow triggers the interrupt and calls the routine which increments the seconds counter by one. Additional counters for minutes and hours are incremented as the previous counter overflows.

Since the register pair is 16 bits wide, counting up to overflow the register directly from a 32.768 kHz clock would take 2 seconds. To force the overflow at the required one-second intervals, it is necessary to preload it. The simplest method is to set the MSb of TMR1H with a BSF instruction. Note that the TMR1L register is never preloaded or altered; doing so may introduce cumulative error over many cycles.

For this method to be accurate, Timer1 must operate in Asynchronous mode and the Timer1 overflow interrupt must be enabled (PIE1<0> = 1), as shown in the routine, RTCinit. The Timer1 oscillator must also be enabled and running at all times.

## 12.7 Considerations in Asynchronous Counter Mode

Following a Timer1 interrupt and an update to the TMR1 registers, the Timer1 module uses a falling edge on its clock source to trigger the next register update on the rising edge. If the update is completed after the clock input has fallen, the next rising edge will not be counted.

If the application can reliably update TMR1 before the timer input goes low, no additional action is needed. Otherwise, an adjusted update can be performed following a later Timer1 increment. This can be done by monitoring TMR1L within the interrupt routine until it increments, and then updating the TMR1H:TMR1L register pair while the clock is low, or one-half of the period of the clock source. Assuming that Timer1 is being used as a Real-Time Clock, the clock source is a 32.768 kHz crystal oscillator. In this case, one-half period of the clock is 15.25  $\mu$ s.

The Real-Time Clock application code in Example 12-1 shows a typical ISR for Timer1, as well as the optional code required if the update cannot be done reliably within the required interval.

	12-1. 1		A REAL-TIME CLOCK USING A TIMERT INTERRUPT SERVICE
RTCinit			
	MOVLW	80h	; Preload TMR1 register pair
	MOVWF	TMR1H	; for 1 second overflow
	CLRF	TMR1L	
	MOVLW	b'00001111'	; Configure for external clock,
	MOVWF	T1CON	; Asynchronous operation, external oscillator
	CLRF	secs	; Initialize timekeeping registers
	CLRF	mins	;
	MOVLW	.12	
	MOVWF	hours	
	BSF	PIE1, TMR1IE	; Enable Timer1 interrupt
	RETURN		
RTCisr			
			; Insert the next 4 lines of code when TMR1
			; can not be reliably updated before clock pulse goes low
	BTFSC	TMR1L,0	; wait for TMR1L to become clear
	BRA	\$-2	; (may already be clear)
	BTFSS	TMR1L,0	; wait for TMR1L to become set
	BRA	\$-2	; TMR1 has just incremented
			; If TMR1 update can be completed before clock pulse goes lo
			; Start ISR here
	BSF	TMR1H, 7	; Preload for 1 sec overflow
	BCF	PIR1, TMR1IF	; Clear interrupt flag
	INCF	secs, F	; Increment seconds
	MOVLW	.59	; 60 seconds elapsed?
	CPFSGT	secs	
	RETURN		; No, done
	CLRF	secs	; Clear seconds
	INCF	mins, F	; Increment minutes
	MOVLW	.59	; 60 minutes elapsed?
	CPFSGT	mins	-
	RETURN		; No, done
	CLRF	mins	; clear minutes
	INCF	hours, F	; Increment hours
	MOVLW	.23	; 24 hours elapsed?
	CPFSGT	hours	-
	RETURN		; No, done
	CLRF	hours	; Reset hours
	RETURN		; Done
			,

EXAMPLE 12-1: IMPLEMENTING A REAL-TIME CLOCK USING A TIMER1 INTERRUPT SERVICE

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
TMR1L	Timer1 Reg	gister Low By	/te						60
TMR1H	Timer1 Register High Byte								
T1CON	RD16 T1RUN T1CKPS1 T1CKPS0 T1OSCEN T1SYNC TMR1CS TMR1ON								60
Legend:	Shaded cells	s are not use	d by the Tin	ner1 module	· · · · ·		-	-	

Legend: Shaded cells are not used by the Timer1 module.

© 2007 Microchip Technology Inc.

NOTES:

## 13.0 TIMER2 MODULE

The Timer2 timer module incorporates the following features:

- 8-Bit Timer and Period registers (TMR2 and PR2, respectively)
- Readable and writable (both registers)
- Software programmable prescaler (1:1, 1:4 and 1:16)
- Software programmable postscaler (1:1 through 1:16)
- · Interrupt on TMR2 to PR2 match
- Optional use as the shift clock for the MSSPx modules

The module is controlled through the T2CON register (Register 13-1) which enables or disables the timer and configures the prescaler and postscaler. Timer2 can be shut off by clearing control bit, TMR2ON (T2CON<2>), to minimize power consumption.

A simplified block diagram of the module is shown in Figure 13-1.

## 13.1 Timer2 Operation

In normal operation, TMR2 is incremented from 00h on each clock (Fosc/4). A 4-bit counter/prescaler on the clock input gives direct input, divide-by-4 and divide-by-16 prescale options. These options are prescaler selected by the control bits. T2CKPS1:T2CKPS0 (T2CON<1:0>). The value of TMR2 is compared to that of the Period register, PR2, on each clock cycle. When the two values match, the comparator generates a match signal as the timer output. This signal also resets the value of TMR2 to 00h on the next cycle and drives the output counter/postscaler (see Section 13.2 "Timer2 Interrupt").

The TMR2 and PR2 registers are both directly readable and writable. The TMR2 register is cleared on any device Reset, while the PR2 register initializes at FFh. Both the prescaler and postscaler counters are cleared on the following events:

- a write to the TMR2 register
- · a write to the T2CON register
- any device Reset (Power-on Reset, MCLR Reset, Watchdog Timer Reset or Brown-out Reset)

TMR2 is not cleared when T2CON is written.

### REGISTER 13-1: T2CON: TIMER2 CONTROL REGISTER

-												
U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0					
_	T2OUTPS3	T2OUTPS2	T2OUTPS1	T2OUTPS0	TMR2ON	T2CKPS1	T2CKPS0					
bit 7			•				bit 0					
Logondi												
Legend:												
R = Readable bit		W = Writable	bit	U = Unimpler	nented bit, read	las 0						
-n = Value at POR		'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown					
bit 7	Unimplemen	Unimplemented: Read as '0'										
bit 6-3	T2OUTPS3:T	T2OUTPS3:T2OUTPS0: Timer2 Output Postscale Select bits										
	0000 <b>= 1:1 P</b>	0000 = 1:1 Postscale										
	0001 = 1:2 Pe	0001 = 1:2 Postscale										
	•	•										
	•	•										
	•	•										
	1111 <b>= 1:16</b> F	1111 = 1:16 Postscale										
bit 2	TMR2ON: Tin	ner2 On bit										
	1 = Timer2 is	on										
	0 = Timer2 is	0 = Timer2 is off										
bit 1-0	T2CKPS1:T2	T2CKPS1:T2CKPS0: Timer2 Clock Prescale Select bits										
	00 = Prescale	00 = Prescaler is 1										
	01 = Prescale											
	$1 \times = $ Prescale	-										
	110000410											

## 13.2 Timer2 Interrupt


Timer2 can also generate an optional device interrupt. The Timer2 output signal (TMR2 to PR2 match) provides the input for the 4-bit output counter/postscaler. This counter generates the TMR2 match interrupt flag which is latched in TMR2IF (PIR1<1>). The interrupt is enabled by setting the TMR2 Match Interrupt Enable bit, TMR2IE (PIE1<1>).

A range of 16 postscale options (from 1:1 through 1:16 inclusive) can be selected with the postscaler control bits, T2OUTPS3:T2OUTPS0 (T2CON<6:3>).

## 13.3 Timer2 Output

The unscaled output of TMR2 is available primarily to the CCP modules, where it is used as a time base for operations in PWM mode.

Timer2 can be optionally used as the shift clock source for the MSSPx modules operating in SPI mode. Additional information is provided in Section 19.0 "Master Synchronous Serial Port (MSSP) Module".



## FIGURE 13-1: TIMER2 BLOCK DIAGRAM

#### TABLE 13-1: REGISTERS ASSOCIATED WITH TIMER2 AS A TIMER/COUNTER

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	<b>INTOIE</b>	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
TMR2	Timer2 Reg	jister							60
T2CON	_	T2OUTPS3	T2OUTPS2	T2OUTPS1	T2OUTPS0	TMR2ON	T2CKPS1	T2CKPS0	60
PR2	Timer2 Peri	iod Register							60

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used by the Timer2 module.

## 14.0 TIMER3 MODULE

The Timer3 timer/counter module incorporates these features:

- Software selectable operation as a 16-bit timer or counter
- Readable and writable 8-bit registers (TMR3H and TMR3L)
- Selectable clock source (internal or external) with device clock or Timer1 oscillator internal options
- Interrupt on overflow
- Module Reset on CCPx/ECCPx Special Event Trigger

A simplified block diagram of the Timer3 module is shown in Figure 14-1. A block diagram of the module's operation in Read/Write mode is shown in Figure 14-2.

The Timer3 module is controlled through the T3CON register (Register 14-1). It also selects the clock source options for the CCPx and ECCPx modules; see Section 16.1.1 "CCPx/ECCPx Modules and Timer Resources" for more information.

### REGISTER 14-1: T3CON: TIMER3 CONTROL REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
RD16	T3CCP2	T3CKPS1	T3CKPS0	T3CCP1	T3SYNC	TMR3CS	TMR3ON
bit 7							bit 0

Legend:										
R = Readab	ole bit	W = Writable bit	U = Unimplemented bit,	, read as '0'						
-n = Value a	at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown						
bit 7	<b>RD16:</b> 16	-Bit Read/Write Mode Enabl	le bit							
		<ul> <li>1 = Enables register read/write of Timer3 in one 16-bit operation</li> <li>0 = Enables register read/write of Timer3 in two 8-bit operations</li> </ul>								
bit 6,3	T3CCP2:	T3CCP1: Timer3 and Timer	1 to CCPx/ECCPx Enable bits	5						
	10 = Time Time 01 = Time Time	<ul> <li>11 = Timer3 and Timer4 are the clock sources for all CCPx/ECCPx modules</li> <li>10 = Timer3 and Timer4 are the clock sources for ECCP3, CCP4 and CCP5; Timer1 and Timer2 are the clock sources for ECCP1 and ECCP2</li> <li>01 = Timer3 and Timer4 are the clock sources for ECCP2, ECCP3, CCP4 and CCP5; Timer1 and Timer2 are the clock sources for ECCP1</li> <li>00 = Timer1 and Timer2 are the clock sources for all CCPx/ECCPx modules</li> </ul>								
bit 5-4	T3CKPS	I:T3CKPS0: Timer3 Input C	lock Prescale Select bits							
	11 = 1:8   10 = 1:4   01 = 1:2	11 = 1:8 Prescale value 10 = 1:4 Prescale value 01 = 1:2 Prescale value 00 = 1:1 Prescale value								
bit 2	(not usab <u>When TM</u> 1 = Do no 0 = Synch <u>When TM</u>	Timer3 External Clock Inpu le if the device clock comes IR3CS = 1: ot synchronize external clock pronize external clock input IR3CS = 0: ignored. Timer3 uses the in	from Timer1/Timer3)	· 0.						
bit 1	TMR3CS 1 = Exter	: Timer3 Clock Source Selec	ct bit	ing edge after the first falling edge						
bit 0	TMR3ON	: Timer3 On bit les Timer3								


### 14.1 Timer3 Operation

Timer3 can operate in one of three modes:


- Timer
- Synchronous Counter
- Asynchronous Counter

The operating mode is determined by the clock select bit, TMR3CS (T3CON<1>). When TMR3CS is cleared (= 0), Timer3 increments on every internal instruction cycle (Fosc/4). When the bit is set, Timer3 increments on every rising edge of the Timer1 external clock input or the Timer1 oscillator, if enabled.

As with Timer1, the RC1/T1OSI and RC0/T1OSO/T13CKI pins become inputs when the Timer1 oscillator is enabled. This means the values of TRISC<1:0> are ignored and the pins are read as '0'.



#### FIGURE 14-2: TIMER3 BLOCK DIAGRAM (16-BIT READ/WRITE MODE)



### 14.2 Timer3 16-Bit Read/Write Mode

Timer3 can be configured for 16-bit reads and writes (see Figure 14-2). When the RD16 control bit (T3CON<7>) is set, the address for TMR3H is mapped to a buffer register for the high byte of Timer3. A read from TMR3L will load the contents of the high byte of Timer3 into the Timer3 High Byte Buffer register. This provides the user with the ability to accurately read all 16 bits of Timer1 without having to determine whether a read of the high byte, followed by a read of the low byte, has become invalid due to a rollover between reads.

A write to the high byte of Timer3 must also take place through the TMR3H Buffer register. The Timer3 high byte is updated with the contents of TMR3H when a write occurs to TMR3L. This allows a user to write all 16 bits to both the high and low bytes of Timer3 at once.

The high byte of Timer3 is not directly readable or writable in this mode. All reads and writes must take place through the Timer3 High Byte Buffer register.

Writes to TMR3H do not clear the Timer3 prescaler. The prescaler is only cleared on writes to TMR3L.

### 14.3 Using the Timer1 Oscillator as the Timer3 Clock Source

The Timer1 internal oscillator may be used as the clock source for Timer3. The Timer1 oscillator is enabled by setting the T1OSCEN (T1CON<3>) bit. To use it as the Timer3 clock source, the TMR3CS bit must also be set. As previously noted, this also configures Timer3 to increment on every rising edge of the oscillator source.

The Timer1 oscillator is described in Section 12.0 "Timer1 Module".

### 14.4 Timer3 Interrupt

The TMR3 register pair (TMR3H:TMR3L) increments from 0000h to FFFFh and overflows to 0000h. The Timer3 interrupt, if enabled, is generated on overflow and is latched in interrupt flag bit, TMR3IF (PIR2<1>). This interrupt can be enabled or disabled by setting or clearing the Timer3 Interrupt Enable bit, TMR3IE (PIE2<1>).

### 14.5 Resetting Timer3 Using the ECCPx Special Event Trigger

If ECCP1 or ECCP2 is configured to use Timer3 and to generate a Special Event Trigger in Compare mode (CCPxM3:CCPxM0 = 1011), this signal will reset Timer3. The trigger from ECCP2 will also start an A/D conversion if the A/D module is enabled (see **Section 17.2.1 "Special Event Trigger"** for more information).

The module must be configured as either a timer or synchronous counter to take advantage of this feature. When used this way, the CCPRxH:CCPRxL register pair effectively becomes a Period register for Timer3.

If Timer3 is running in Asynchronous Counter mode, the Reset operation may not work.

In the event that a write to Timer3 coincides with a Special Event Trigger from an ECCPx module, the write will take precedence.

Note: The Special Event Triggers from the ECCPx module will not set the TMR3IF interrupt flag bit (PIR2<1>).

TABLE 14-1. REGISTERS ASSOCIATED WITH TIMERS AS A TIMER/COUNTER									
Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR2	OSCFIF	CMIF	ETHIF	r	BCL1IF		TMR3IF	CCP2IF	61
PIE2	OSCFIE	CMIE	ETHIE	r	BCL1IE	_	TMR3IE	CCP2IE	61
IPR2	OSCFIP	CMIP	ETHIP	r	BCL1IP	_	TMR3IP	CCP2IP	61
TMR3L	Timer3 Reg	gister Low B	yte						60
TMR3H	Timer3 Reg	gister High B	yte						60
T1CON	RD16	T1RUN	T1CKPS1	T1CKPS0	T1OSCEN	T1SYNC	TMR1CS	TMR10N	60
T3CON	RD16	T3CCP2	T3CKPS1	T3CKPS0	T3CCP1	<b>T3SYNC</b>	TMR3CS	TMR3ON	61

 TABLE 14-1:
 REGISTERS ASSOCIATED WITH TIMER3 AS A TIMER/COUNTER

**Legend:** — = unimplemented, read as '0', r = reserved. Shaded cells are not used by the Timer3 module.

NOTES:

# 15.0 TIMER4 MODULE

The Timer4 module has the following features:

- 8-Bit Timer register (TMR4)
- 8-Bit Period register (PR4)
- Readable and writable (both registers)
- Software programmable prescaler (1:1, 1:4, 1:16)
- Software programmable postscaler (1:1 to 1:16)
- Interrupt on TMR4 match of PR4

Timer4 has a control register shown in Register 15-1. Timer4 can be shut off by clearing control bit, TMR4ON (T4CON<2>), to minimize power consumption. The prescaler and postscaler selection of Timer4 are also controlled by this register. Figure 15-1 is a simplified block diagram of the Timer4 module.

# 15.1 Timer4 Operation

Timer4 can be used as the PWM time base for the PWM mode of the CCP module. The TMR4 register is readable and writable and is cleared on any device Reset. The input clock (Fosc/4) has a prescale option of 1:1, 1:4 or 1:16, selected by control bits T4CKPS1:T4CKPS0 (T4CON<1:0>). The match output of TMR4 goes through a 4-bit postscaler (which gives a 1:1 to 1:16 scaling inclusive) to generate a TMR4 interrupt, latched in flag bit, TMR4IF (PIR3<3>).

The prescaler and postscaler counters are cleared when any of the following occurs:

- · a write to the TMR4 register
- a write to the T4CON register
- any device Reset (Power-on Reset, MCLR Reset, Watchdog Timer Reset or Brown-out Reset)

TMR4 is not cleared when T4CON is written.

# REGISTER 15-1: T4CON: TIMER4 CONTROL REGISTER

U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
—	T4OUTPS3	T4OUTPS2	T4OUTPS1	T4OUTPS0	TMR4ON	T4CKPS1	T4CKPS0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit, read	as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

#### bit 7 Unimplemented: Read as '0'


# 15.2 Timer4 Interrupt

The Timer4 module has an 8-Bit Period register, PR4, which is both readable and writable. Timer4 increments from 00h until it matches PR4 and then resets to 00h on the next increment cycle. The PR4 register is initialized to FFh upon Reset.

# FIGURE 15-1: TIMER4 BLOCK DIAGRAM

# 15.3 Output of TMR4

The output of TMR4 (before the postscaler) is used only as a PWM time base for the CCPx/ECCPx modules. It is not used as a baud rate clock for the MSSPx modules as is the Timer2 output.



#### TABLE 15-1: REGISTERS ASSOCIATED WITH TIMER4 AS A TIMER/COUNTER

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
IPR3	SSP2IP	BCL2IP	RC2IP	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
PIR3	SSP2IF	BCL2IF	RC2IF	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE	BCL2IE	RC2IE	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
TMR4	Timer4 Register							62	
T4CON	_	T4OUTPS3	T4OUTPS2	T4OUTPS1	T4OUTPS0	TMR4ON	T4CKPS1	T4CKPS0	62
PR4	Timer4 Period Register								62

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used by the Timer4 module.

# 16.0 CAPTURE/COMPARE/PWM (CCP) MODULES

Members of the PIC18F97J60 family of devices all have a total of five CCP (Capture/Compare/PWM) modules. Two of these (CCP4 and CCP5) implement standard Capture, Compare and Pulse-Width Modulation (PWM) modes and are discussed in this section. The other three modules (ECCP1, ECCP2, ECCP3) implement standard Capture and Compare modes, as well as Enhanced PWM modes. These are discussed in Section 17.0 "Enhanced Capture/Compare/PWM (ECCP) Modules".

Each CCPx/ECCPx module contains a 16-bit register which can operate as a 16-Bit Capture register, a 16-Bit Compare register or a PWM Master/Slave Duty Cycle register. For the sake of clarity, all CCPx module operation in the following sections is described with respect to CCP4, but is equally applicable to CCP5.

Capture and Compare operations described in this chapter apply to all standard and Enhanced CCPx modules. The operations of PWM mode, described in **Section 16.4 "PWM Mode"**, apply to CCP4 and CCP5 only.

Note: Throughout this section and Section 17.0 "Enhanced Capture/Compare/PWM (ECCP) Modules", references to register and bit names that may be associated with a specific CCP module are referred to generically by the use of 'x' or 'y' in place of the specific module number. Thus, "CCPxCON" might refer to the control register for ECCP1, ECCP2, ECCP3, CCP4 or CCP5.

# **REGISTER 16-1:** CCPxCON: CCPx CONTROL REGISTER (CCP4 AND CCP5)

U-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
—	—	DCxB1	DCxB0	CCPxM3	CCPxM2	CCPxM1	CCPxM0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	t, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-6	Unimplemented: Read as '0'
bit 5-4	DCxB1:DCxB0: CCPx Module PWM Duty Cycle bit 1 and bit 0
	Capture mode:
	Unused.
	Compare mode:
	Unused.
	PWM mode:
	These bits are the two Least Significant bits (bit 1 and bit 0) of the 10-bit PWM duty cycle. The eight
	Most Significant bits (DCxB9:DCxB2) of the duty cycle are found in CCPRxL.
bit 3-0	CCPxM3:CCPxM0: CCPx Module Mode Select bits
	0000 = Capture/Compare/PWM disabled (resets CCPx module)
	0001 = Reserved
	0010 = Compare mode; toggle output on match (CCPxIF bit is set)
	0011 = Reserved
	0100 = Capture mode; every falling edge
	0101 = Capture mode; every rising edge
	0110 = Capture mode; every 4th rising edge
	0111 = Capture mode; every 16th rising edge
	1000 = Compare mode; initialize CCPx pin low; on compare match, force CCPx pin high
	(CCPxIF bit is set)
	1001 = Compare mode; initialize CCPx pin high; on compare match, force CCPx pin low
	(CCPxIF bit is set)
	1010 = Compare mode; generate software interrupt on compare match (CCPxIF bit is set,
	CCPx pin reflects I/O state)
	1011 = Reserved
	11xx = PWM mode

# 16.1 CCPx Module Configuration

Each Capture/Compare/PWM module is associated with a control register (generically, CCPxCON) and a data register (CCPRx). The data register, in turn, is comprised of two 8-bit registers: CCPRxL (low byte) and CCPRxH (high byte). All registers are both readable and writable.

#### 16.1.1 CCPx/ECCPx MODULES AND TIMER RESOURCES

The CCPx/ECCPx modules utilize Timers 1, 2, 3 or 4, depending on the mode selected. Timer1 and Timer3 are available to modules in Capture or Compare modes, while Timer2 and Timer4 are available for modules in PWM mode.

# TABLE 16-1:CCPx/ECCPx MODE – TIMER<br/>RESOURCE

CCPx/ECCPx Mode	Timer Resource
Capture	Timer1 or Timer3
Compare	Timer1 or Timer3
PWM	Timer2 or Timer4


The assignment of a particular timer to a module is determined by the timer to CCPx enable bits in the T3CON register (Register 14-1, page 175). Depending on the configuration selected, up to four timers may be active at once, with modules in the same configuration (Capture/Compare or PWM) sharing timer resources. The possible configurations are shown in Figure 16-1.

# 16.1.2 ECCP2 PIN ASSIGNMENT

The pin assignment for ECCP2 (Capture input, Compare and PWM output) can change based on device configuration. The CCP2MX Configuration bit determines which pin ECCP2 is multiplexed to. By default, it is assigned to RC1 (CCP2MX = 1). If the Configuration bit is cleared, ECCP2 is multiplexed with RE7 on 80-pin and 100-pin devices in Microcontroller mode and RB3 on 100-pin devices in Extended Microcontroller mode.

Changing the pin assignment of ECCP2 does not automatically change any requirements for configuring the port pin. Users must always verify that the appropriate TRIS register is configured correctly for ECCP2 operation regardless of where it is located.

# FIGURE 16-1: CCPx/ECCPx AND TIMER INTERCONNECT CONFIGURATIONS



Timer1 is used for all Capture and Compare operations for all CCPx modules. Timer2 is used for PWM operations for all CCPx modules. Modules may share either timer resource as a common time base.

Timer3 and Timer4 are not available.

TMR1 TMR3

T3CCP<2:1> = 01

Timer1 and Timer2 are used for Capture and Compare or PWM operations for ECCP1 only (depending on selected mode).

All other modules use either Timer3 or Timer4. Modules may share either timer resource as a common time base if they are in Capture/Compare or PWM modes. Timer1 and Timer2 are used for Capture and Compare or PWM operations for ECCP1 and ECCP2 only (depending on the mode selected for each module). Both modules may use a timer as a common time base if they are both in Capture/Compare or PWM modes

T3CCP<2:1> = 10

TMR1

ECCP1

ECCP2

TMR2

TMR3

ECCP3

CCP4

CCP5

TMR4

The other modules use either Timer3 or Timer4. Modules may share either timer resource as a common time base if they are in Capture/Compare or PWM modes. TMR2 TMR4 Timer3 is used for all Capture and Compare operations for all CCPx modules. Timer4 is used for PWM operations for all CCPx modules. Modules may share either timer resource as a common time base.

T3CCP<2:1> = 11

TMR3

ECCP1

ECCP2

ECCP3

CCP4

CCP5

TMR1

Timer1 and Timer2 are not available.

# 16.2 Capture Mode

In Capture mode, the CCPRxH:CCPRxL register pair captures the 16-bit value of the TMR1 or TMR3 registers when an event occurs on the corresponding CCPx pin. An event is defined as one of the following:

- · every falling edge
- · every rising edge
- every 4th rising edge
- · every 16th rising edge

The event is selected by the mode select bits, CCPxM3:CCPxM0 (CCPxCON<3:0>). When a capture is made, the interrupt request flag bit, CCPxIF, is set; it must be cleared in software. If another capture occurs before the value in register CCPRx is read, the old captured value is overwritten by the new captured value.

# 16.2.1 CCPx PIN CONFIGURATION

In Capture mode, the appropriate CCPx pin should be configured as an input by setting the corresponding TRIS direction bit.

Note:	If RG4/CCP5/P1D is configured as an
	output, a write to the port can cause a
	capture condition.

# 16.2.2 TIMER1/TIMER3 MODE SELECTION

The timers that are to be used with the capture feature (Timer1 and/or Timer3) must be running in Timer mode or Synchronized Counter mode. In Asynchronous Counter mode, the capture operation will not work. The timer to be used with each CCPx module is selected in the T3CON register (see Section 16.1.1 "CCPx/ECCPx Modules and Timer Resources").

# 16.2.3 SOFTWARE INTERRUPT

When the Capture mode is changed, a false capture interrupt may be generated. The user should keep the CCPxIE interrupt enable bit clear to avoid false interrupts. The interrupt flag bit, CCPxIF, should also be cleared following any such change in operating mode.

# 16.2.4 CCPx PRESCALER


There are four prescaler settings in Capture mode. They are specified as part of the operating mode selected by the mode select bits (CCPxM3:CCPxM0). Whenever the CCPx module is turned off or Capture mode is disabled, the prescaler counter is cleared. This means that any Reset will clear the prescaler counter.

Switching from one capture prescaler to another may generate an interrupt. Also, the prescaler counter will not be cleared; therefore, the first capture may be from a non-zero prescaler. Example 16-1 shows the recommended method for switching between capture prescalers. This example also clears the prescaler counter and will not generate the "false" interrupt.

### EXAMPLE 16-1: CHANGING BETWEEN CAPTURE PRESCALERS (CCP5 SHOWN)

			Turn CCP module off
MOVLW	NEW_CAPT_PS	;	Load WREG with the
		;	new prescaler mode
		;	value and CCP ON
MOVWF	CCP5CON	;	Load CCP5CON with
		;	this value

### FIGURE 16-2: CAPTURE MODE OPERATION BLOCK DIAGRAM



# 16.3 Compare Mode

In Compare mode, the 16-bit CCPRx register value is constantly compared against either the TMR1 or TMR3 register pair value. When a match occurs, the CCPx pin:

- can be driven high
- · can be driven low
- can be toggled (high-to-low or low-to-high)
- remains unchanged (that is, reflects the state of the I/O latch)

The action on the pin is based on the value of the mode select bits (CCPxM3:CCPxM0). At the same time, the interrupt flag bit, CCPxIF, is set.

#### 16.3.1 CCPx PIN CONFIGURATION

The user must configure the CCPx pin as an output by clearing the appropriate TRIS bit.


Note: Clearing the CCP5CON register will force the RG4 compare output latch (depending on device configuration) to the default low level. This is not the PORTB or PORTC I/O data latch.

# 16.3.2 TIMER1/TIMER3 MODE SELECTION

Timer1 and/or Timer3 must be running in Timer mode or Synchronized Counter mode if the CCPx module is using the compare feature. In Asynchronous Counter mode, the compare operation may not work.

# 16.3.3 SOFTWARE INTERRUPT MODE

When the Generate Software Interrupt mode is chosen (CCPxM3:CCPxM0 = 1010), the corresponding CCPx pin is not affected. Only a CCPx interrupt is generated, if enabled and the CCPxIE bit is set.



# FIGURE 16-3: COMPARE MODE OPERATION BLOCK DIAGRAM

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
RCON	IPEN	_	CM	RI	TO	PD	POR	BOR	60
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR2	OSCFIF	CMIF	ETHIF	r	BCL1IF	_	TMR3IF	CCP2IF	61
PIE2	OSCFIE	CMIE	ETHIE	r	BCL1IE	_	TMR3IE	CCP2IE	61
IPR2	OSCFIP	CMIP	ETHIP	r	BCL1IP		TMR3IP	CCP2IP	61
PIR3	SSP2IF	BCL2IF	RC2IF	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE	BCL2IE	RC2IE	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP	BCL2IP	RC2IP	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
TRISG	TRISG7	TRISG6	TRISG5	TRISG4	TRISG3 <sup>(1)</sup>	TRISG2	TRISG1	TRISG0	61
TMR1L	Timer1 Reg	gister Low E	syte						60
TMR1H	Timer1 Reg	gister High E	Byte						60
T1CON	RD16	T1RUN	T1CKPS1	T1CKPS0	T1OSCEN	T1SYNC	TMR1CS	TMR10N	60
TMR3H	Timer3 Reg	gister High E	Byte						60
TMR3L	Timer3 Reg	gister Low B	syte						60
T3CON	RD16	T3CCP2	T3CKPS1	T3CKPS0	T3CCP1	T3SYNC	TMR3CS	TMR3ON	61
CCPR4L	Capture/Compare/PWM Register 4 Low Byte							62	
CCPR4H	Capture/Compare/PWM Register 4 High Byte								62
CCPR5L	Capture/Compare/PWM Register 5 Low Byte								63
CCPR5H	Capture/Co	ompare/PW	M Register :	5 High Byte					63
CCP4CON			DC4B1	DC4B0	CCP4M3	CCP4M2	CCP4M1	CCP4M0	63
CCP5CON	—	—	DC5B1	DC5B0	CCP5M3	CCP5M2	CCP5M1	CCP5M0	63

TABLE 16-2: F	REGISTERS ASSOCIATED WITH CAPTURE, COMPARE, TIMER1 AND TIMER3
---------------	---

**Legend:** — = unimplemented, read as '0', r = reserved. Shaded cells are not used by Capture/Compare, Timer1 or Timer3.

Note 1: This bit is only available in 80-pin and 100-pin devices; otherwise, it is unimplemented and reads as '0'.

# 16.4 PWM Mode


In Pulse-Width Modulation (PWM) mode, the CCPx pin produces up to a 10-bit resolution PWM output. Since the CCP4 and CCP5 pins are multiplexed with a PORTG data latch, the appropriate TRISG bit must be cleared to make the CCP4 or CCP5 pin an output.

Note:	Clearing the CCP4CON or CCP5CON register will force the RG3 or RG4 output latch (depending on device configuration)
	to the default low level. This is not the PORTG I/O data latch.

Figure 16-4 shows a simplified block diagram of the CCPx module in PWM mode.


For a step-by-step procedure on how to set up a CCPx module for PWM operation, see **Section 16.4.3** "Setup for PWM Operation".

# FIGURE 16-4: SIMPLIFIED PWM BLOCK DIAGRAM



A PWM output (Figure 16-5) has a time base (period) and a time that the output stays high (duty cycle). The frequency of the PWM is the inverse of the period (1/period).





# 16.4.1 PWM PERIOD

The PWM period is specified by writing to the PR2 (PR4) register. The PWM period can be calculated using Equation 16-1:

# EQUATION 16-1:

 $PWM Period = [(PR2) + 1] \cdot 4 \cdot TOSC \cdot (TMR2 Prescale Value)$ 

PWM frequency is defined as 1/[PWM period].

When TMR2 (TMR4) is equal to PR2 (PR4), the following three events occur on the next increment cycle:

- TMR2 (TMR4) is cleared
- The CCPx pin is set (exception: if PWM duty cycle = 0%, the CCPx pin will not be set)
- The PWM duty cycle is latched from CCPRxL into CCPRxH
- Note: The Timer2 and Timer4 postscalers (see Section 13.0 "Timer2 Module" and Section 15.0 "Timer4 Module") are not used in the determination of the PWM frequency. The postscaler could be used to have a servo update rate at a different frequency than the PWM output.

# 16.4.2 PWM DUTY CYCLE

The PWM duty cycle is specified by writing to the CCPRxL register and to the CCPxCON<5:4> bits. Up to 10-bit resolution is available. The CCPRxL contains the eight MSbs and the CCPxCON<5:4> contains the two LSbs. This 10-bit value is represented by CCPRxL:CCPxCON<5:4>. Equation 16-2 is used to calculate the PWM duty cycle in time.

# EQUATION 16-2:

PWM Duty Cycle = (CCPRxL:CCPxCON<5:4>) • Tosc • (TMRx Prescale Value)

CCPRxL and CCPxCON<5:4> can be written to at any time, but the duty cycle value is not latched into CCPRxH until after a match between PR2 (PR4) and TMR2 (TMR4) occurs (i.e., the period is complete). In PWM mode, CCPRxH is a read-only register.

The CCPRxH register and a 2-bit internal latch are used to double-buffer the PWM duty cycle. This double-buffering is essential for glitchless PWM operation.

When the CCPRxH and 2-bit latch match TMR2 (TMR4), concatenated with an internal 2-bit Q clock or 2 bits of the TMR2 (TMR4) prescaler, the CCPx pin is cleared.

The maximum PWM resolution (bits) for a given PWM frequency is given by Equation 16-3:

# EQUATION 16-3:

PWM Resolution (max) = 
$$\frac{\log(\frac{FOSC}{FPWM})}{\log(2)}$$
 bits

**Note:** If the PWM duty cycle value is longer than the PWM period, the CCPx pin will not be cleared.

# 16.4.3 SETUP FOR PWM OPERATION

The following steps should be taken when configuring the CCPx module for PWM operation:

- 1. Set the PWM period by writing to the PR2 (PR4) register.
- 2. Set the PWM duty cycle by writing to the CCPRxL register and CCPxCON<5:4> bits.
- 3. Make the CCPx pin an output by clearing the appropriate TRIS bit.
- 4. Set the TMR2 (TMR4) prescale value, then enable Timer2 (Timer4) by writing to T2CON (T4CON).
- 5. Configure the CCPx module for PWM operation.

# TABLE 16-3: EXAMPLE PWM FREQUENCIES AND RESOLUTIONS AT 40 MHz

PWM Frequency	2.44 kHz	9.77 kHz	39.06 kHz	156.25 kHz	312.50 kHz	416.67 kHz
Timer Prescaler (1, 4, 16)	16	4	1	1	1	1
PR2 Value	FFh	FFh	FFh	3Fh	1Fh	17h
Maximum Resolution (bits)	10	10	10	8	7	6.58

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	<b>GIE/GIEH</b>	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	<b>INT0IF</b>	RBIF	59
RCON	IPEN	_	CM	RI	TO	PD	POR	BOR	60
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR3	SSP2IF	BCL2IF	RC2IF	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE	BCL2IE	RC2IE	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP	BCL2IP	RC2IP	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
TRISG	TRISG7	TRISG6	TRISG5	TRISG4	TRISG3 <sup>(1)</sup>	TRISG2	TRISG1	TRISG0	61
TMR2	Timer2 Reg	jister							60
PR2	Timer2 Peri	od Register							60
T2CON		T2OUTPS3	T2OUTPS2	T2OUTPS1	T2OUTPS0	TMR2ON	T2CKPS1	T2CKPS0	60
TMR4	Timer4 Reg	jister							62
PR4	Timer4 Peri	od Register							62
T4CON		T4OUTPS3	T4OUTPS2	T4OUTPS1	T4OUTPS0	TMR40N	T4CKPS1	T4CKPS0	62
CCPR4L	Capture/Co	ompare/PWN	I Register 4	Low Byte					62
CCPR4H	Capture/Co	ompare/PWN	I Register 4	High Byte					62
CCPR5L	Capture/Compare/PWM Register 5 Low Byte								
CCPR5H	Capture/Co	ompare/PWN	I Register 5	High Byte					63
CCP4CON	—	—	DC4B1	DC4B0	CCP4M3	CCP4M2	CCP4M1	CCP4M0	63
CCP5CON	_	_	DC5B1	DC5B0	CCP5M3	CCP5M2	CCP5M1	CCP5M0	63

# TABLE 16-4: REGISTERS ASSOCIATED WITH PWM, TIMER2 AND TIMER4

Legend: — = unimplemented, read as '0'. Shaded cells are not used by PWM, Timer2 or Timer4.

Note 1: This bit is only available in 80-pin and 100-pin devices; otherwise, it is unimplemented and reads as '0'.

# 17.0 ENHANCED CAPTURE/ COMPARE/PWM (ECCP) MODULES

In the PIC18F97J60 family of devices, three of the CCP modules are implemented as standard CCP modules with Enhanced PWM capabilities. These include the provision for 2 or 4 output channels, user-selectable polarity, dead-band control and automatic shutdown and restart. The Enhanced features are discussed in detail in **Section 17.4 "Enhanced PWM Mode"**. Capture, Compare and single-output PWM functions of the ECCPx modules are the same as described for the standard CCPx modules.

The control register for the Enhanced CCPx module is shown in Register 17-1. It differs from the CCP4CON/ CCP5CON registers in that the two Most Significant bits are implemented to control PWM functionality.

In addition to the expanded range of modes available through the Enhanced CCPxCON register, the ECCPx modules each have two additional registers associated with Enhanced PWM operation and auto-shutdown features. They are:

- ECCPxDEL (Dead-Band Delay)
- ECCPxAS (Auto-Shutdown Configuration)

# **REGISTER 17-1:** CCPxCON: ENHANCED CCPx CONTROL REGISTER (ECCP1/ECCP2/ECCP3)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
PxM1	PxM0	DCxB1	DCxB0	CCPxM3	CCPxM2	CCPxM1	CCPxM0
bit 7							bit C
<del></del>							
Legend:							
R = Readable		W = Writable		•	nented bit, reac		
-n = Value at	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unki	nown
bit 7-6	If CCPxM3:C xx = PxA as: If CCPxM3:C 00 = Single o 01 = Full-brid 10 = Half-brid	$\frac{CPxM2 = 00, 0}{CPxM2 = 11:}$ $\frac{CPxM2 = 11:}{CPxM2 = 11:}$ $\frac{CPxM2 = 0}{CPxM2 = 11:}$	0 <u>1, 10:</u> ure/Compare dulated; PxB /ard: P1D mo A, P1B modula	, PxC, PxD ass dulated; P1A ad ated with dead-l	xB, PxC, PxD a igned as port pi ctive; P1B, P1C band control; P1 ctive; P1A, P1D	ins inactive IC, P1D assign	
bit 5-4		BO: ECCPx Mo		uty Cycle bit 1 a		induite	
		the 2 LSbs of th			8 MSbs of the du	ity cycle are fou	nd in CCPRxL
bit 3-0	0000 = Cap 0001 = Rese 0010 = Com 0011 = Cap 0100 = Cap 0101 = Cap 0110 = Cap 0111 = Cap 1000 = Com 1001 = Com 1010 = Com	erved pare mode; tog ture mode; eve ture mode; eve ture mode; eve ture mode; eve pare mode; ini pare mode; ini pare mode; tri pare mode; tri	PWM disabled ggle output or ry falling edge ry rising edge ry 4th rising e ry 16th rising tialize ECCP tialize ECCP nerate softwa igger special	d (resets ECCP n match e edge edge c pin low; set ou c pin high; clear re interrupt only event (ECCP)	Itput on compar output on com K ECCPx pin rev c resets TMR1	pare match (se verts to I/O stat or TMR3, set	t CCPxIF) e)
	1100 = PWN 1101 = PWN 1110 = PWN	M mode; PxA, F M mode; PxA, F M mode; PxA, F	PxC active-hig PxC active-hig PxC active-lov	onversion if A/D gh; PxB, PxD ao gh; PxB, PxD ao w; PxB, PxD ac w; PxB, PxD ac	ctive-low tive-high	bled)'''	

Note 1: Implemented only for ECCP1 and ECCP2; same as '1010' for ECCP3.

# 17.1 ECCPx Outputs and Configuration

Each of the Enhanced CCPx modules may have up to four PWM outputs, depending on the selected operating mode. These outputs, designated PxA through PxD, are multiplexed with various I/O pins. Some ECCPx pin assignments are constant, while others change based on device configuration. For those pins that do change, the controlling bits are:

- CCP2MX Configuration bit (80-pin and100-pin devices only)
- ECCPMX Configuration bit (80-pin and100-pin devices only)
- Program memory operating mode set by the EMB Configuration bits (100-pin devices only)

The pin assignments for the Enhanced CCPx modules are summarized in Table 17-1, Table 17-2 and Table 17-3. To configure the I/O pins as PWM outputs, the proper PWM mode must be selected by setting the PxMx and CCPxMx bits (CCPxCON<7:6> and <3:0>, respectively). The appropriate TRIS direction bits for the corresponding port pins must also be set as outputs.

### 17.1.1 ECCP1/ECCP3 OUTPUTS AND PROGRAM MEMORY MODE

In 100-pin devices, the use of Extended Microcontroller mode has an indirect effect on the ECCP1 and ECCP3 pins in Enhanced PWM modes. By default, PWM outputs, P1B/P1C and P3B/P3C, are multiplexed to PORTE pins, along with the high-order byte of the external memory bus. When the bus is active in Extended Microcontroller mode, it overrides the Enhanced CCPx outputs and makes them unavailable. Because of this, ECCP1 and ECCP3 can only be used in compatible (single output) PWM modes when the device is in Extended Microcontroller mode and default pin configuration.

An exception to this configuration is when a 12-bit address width is selected for the external bus (EMB1:EMB0 Configuration bits = 10). In this case, the upper pins of PORTE continue to operate as digital I/O, even when the external bus is active. P1B/P1C and P3B/P3C remain available for use as Enhanced PWM outputs.

If an application requires the use of additional PWM outputs during Extended Microcontroller mode, the P1B/P1C and P3B/P3C outputs can be reassigned to the upper bits of PORTH. This is done by clearing the ECCPMX Configuration bit.

# 17.1.2 ECCP2 OUTPUTS AND PROGRAM MEMORY MODES

For 100-pin devices, the program memory mode of the device (Section 5.1.3 "PIC18F9XJ60/9XJ65 Program Memory Modes") also impacts pin multiplexing for the module.

The ECCP2 input/output (ECCP2/P2A) can be multiplexed to one of three pins. The default assignment (CCP2MX Configuration bit is set) for all devices is RC1. Clearing CCP2MX reassigns ECCP2/P2A to RE7 in 80-pin and 100-pin devices.

An additional option exists for 100-pin devices. When these devices are operating in Microcontroller mode, the multiplexing options described above still apply. In Extended Microcontroller mode, clearing CCP2MX reassigns ECCP2/P2A to RB3.

# 17.1.3 USE OF CCP4 AND CCP5 WITH ECCP1 AND ECCP3

Only the ECCP2 module has four dedicated output pins that are available for use. Assuming that the I/O ports or other multiplexed functions on those pins are not needed, they may be used without interfering with any other CCPx module.

ECCP1 and ECCP3, on the other hand, only have three dedicated output pins: ECCPx/PxA, PxB and PxC. Whenever these modules are configured for Quad PWM mode, the pin normally used for CCP4 or CCP5 becomes the PxD output pin for ECCP3 and ECCP1, respectively. The CCP4 and CCP5 modules remain functional but their outputs are overridden.

# 17.1.4 ECCPx MODULES AND TIMER RESOURCES

Like the standard CCPx modules, the ECCPx modules can utilize Timers 1, 2, 3 or 4, depending on the mode selected. Timer1 and Timer3 are available for modules in Capture or Compare modes, while Timer2 and Timer4 are available for modules in PWM mode. Additional details on timer resources are provided in Section 16.1.1 "CCPx/ECCPx Modules and Timer Resources".

CCP1CON Configuration	RE5	RG4	RH7 <sup>(2)</sup>	RH6 <sup>(2)</sup>						
64-Pin Devices; 80-Pin Devices, ECCPMX = 1;										
100-Pin Devices, ECCPMX = 1, Microcontroller mode or Extended Microcontroller mode with 12-Bit Address Width:										
00xx 11xx	ECCP1	RD0/RE6	RE5	RG4/CCP5	RH7/AN15	RH6/AN14				
10xx 11xx	P1A	P1B	RE5	RG4/CCP5	RH7/AN15	RH6/AN14				
x1xx 11xx	P1A	P1B	P1C	P1D	RH7/AN15	RH6/AN14				
100-Pin D		,	,	mory modes:	:					
00xx 11xx	ECCP1	RD0/RE6	RE5/AD13	RG4/CCP5	RH7/AN15	RH6/AN14				
10xx 11xx	P1A	RD0/RE6	RE5/AD13	RG4/CCP5	P1B	RH6/AN14				
x1xx 11xx	P1A	RD0/RE6	RE5/AD13	P1D	P1B	P1C				
100-Pin Devices, ECCPMX = 1, Extended Microcontroller mode with 16-Bit or 20-Bit Address Width:										
00xx 11xx	ECCP1	RD0/RE6	RE5/AD13	RG4/CCP5	RH7/AN15	RH6/AN14				
	Configuration 64- 100-Pin Extended 00xx 11xx 10xx 11xx x1xx 11xx 100-Pin D 00xx 11xx 10xx 11xx x1xx 11xx x1xx 11xx es, ECCPMX = 1 00xx 11xx	Configuration         RC2           64-Pin Devices, EC           100-Pin Devices, EC           Extended Microcontro           00xx 11xx         ECCP1           10xx 11xx         P1A           x1xx 11xx         P1A           100-Pin Devices, ECCI         80-Pin           100-Pin Devices, ECCI         00xx 11xx           10xx 11xx         P1A           x1xx 11xx         ECCP1           00xx 11xx         ECCP1	RC2         RE6 <sup>(1)</sup> 64-Pin Devices; 80-Pin Devices; 100-Pin Devices, ECCPMX = 1, N           Extended         Microcontroller mode w           00xx         11xx         ECCP1         RD0/RE6           10xx         11xx         P1A         P1B           x1xx         11xx         P1A         P1B           00xx         11xx         P1A         RD0/RE6           10xx         11xx         P1A         RD0/RE6           10xx         11xx         P1A         RD0/RE6           10xx         11xx         P1A         RD0/RE6           x1xx         11xx         P1A         RD0/RE6           x0xx         11xx         ECCP1         RD0/RE6	Configuration         RC2         RE6 <sup>(1)</sup> RE5           64-Pin Devices; 80-Pin Devices, ECCPM 100-Pin Devices, ECCPMX = 1, Microcontroller Extended Microcontroller mode with 12-Bit Add 00xx 11xx         Microcontroller Microcontroller mode with 12-Bit Add 00xx 11xx           00xx 11xx         ECCP1         RD0/RE6         RE5           10xx 11xx         P1A         P1B         RE5           x1xx 11xx         P1A         P1B         P1C           80-Pin Devices, ECCPMX = 0; 100-Pin Devices, ECCPMX = 0, All Program Mer           00xx 11xx         ECCP1         RD0/RE6         RE5/AD13           10xx 11xx         P1A         RD0/RE6         RE5/AD13           10xx 11xx         P1A         RD0/RE6         RE5/AD13           10xx 11xx         P1A         RD0/RE6         RE5/AD13           x1xx 11xx         P1A         RD0/RE6         RE5/AD13	ConfigurationRC2RE6(1)RE5RG464-Pin Devices; 80-Pin Devices, ECCPMX = 1; 100-Pin Devices, ECCPMX = 1, Microcontroller mode or Extended Microcontroller mode with 12-Bit Address Width: 00xx 11xxECCP1RD0/RE6RE5RG4/CCP510xx 11xxP1AP1BRE5RG4/CCP510xx 11xxP1AP1BP1CP1D80-Pin Devices, ECCPMX = 0; 100-Pin Devices, ECCPMX = 0, All Program Memory modes: 00xx 11xx00xx 11xxP1ARD0/RE6RE5/AD13RG4/CCP510xx 11xxP1ARD0/RE6RE5/AD13RG4/CCP510xx 11xxP1ARD0/RE6RE5/AD13P1Des, ECCPMX = 1, Extended Microcontroller mode with 16-Bit or 2000xx 11xxECCP1RD0/RE600xx 11xxECCP1RD0/RE6RE5/AD13RG4/CCP5	ConfigurationRC2RE6(1)RE5RG4RH7(2)64-Pin Devices; 80-Pin Devices, ECCPMX = 1; 100-Pin Devices, ECCPMX = 1, Microcontroller mode or Extended Microcontroller mode with 12-Bit Address Width:00xx 11xxECCP1RD0/RE6RE5RG4/CCP5RH7/AN1510xx 11xxP1AP1BRE5RG4/CCP5RH7/AN15x1xx 11xxP1AP1BP1CP1DRH7/AN1580-Pin Devices, ECCPMX = 0; 100-Pin Devices, ECCPMX = 0, All Program Memory modes:00xx 11xxECCP1RD0/RE6RE5/AD13RG4/CCP5RH7/AN1510xx 11xxP1ARD0/RE6RE5/AD13RG4/CCP5P1Bx1xx 11xxP1ARD0/RE6RE5/AD13RG4/CCP5P1Bx1xx 11xxP1ARD0/RE6RE5/AD13RG4/CCP5P1Bx1xx 11xxP1ARD0/RE6RE5/AD13P1DP1Bes, ECCPMX = 1, Extended Microcontroller mode with 16-Bit or 20-Bit Address				

# TABLE 17-1: PIN CONFIGURATIONS FOR ECCP1

**Legend:** x = Don't care. Shaded cells indicate pin assignments not used by ECCP1 in a given mode.

**Note 1:** P1B is multiplexed with RD0 on 64-pin devices, and RE6 on 80-pin and 100-pin devices.

- 2: These pin options are not available on 64-pin devices.
- **3:** With ECCP1 in Quad PWM mode, the CCP5 pin's output is overridden by P1D; otherwise, CCP5 is fully operational.

			-							
ECCP Mode	CCP2CON Configuration	RB3	RC1	RE7	RE2	RE1	RE0			
All Devices, CCP2MX = 1, All Program Memory modes:										
Compatible CCP	00xx 11xx	RB3/INT3	ECCP2	RE7	RE2	RE1	RE0			
Dual PWM	10xx 11xx	RB3/INT3	P2A	RE7	P2B	RE1	RE0			
Quad PWM	x1xx 11xx	RB3/INT3	P2A	RE7	P2B	P2C	P2D			
	80-Pin and 100-Pin Devices, CCP2MX = 0, Microcontroller mode:									
Compatible CCP	00xx 11xx	RB3/INT3	RC1/T1OS1	ECCP2	RE2	RE1	RE0			
Dual PWM	10xx 11xx	RB3/INT3	RC1/T1OS1	P2A	P2B	RE1	RE0			
Quad PWM	x1xx 11xx	RB3/INT3	RC1/T1OS1	P2A	P2B	P2C	P2D			
	100-Pin I	Devices, CCP	<b>2MX = 0, Ext</b>	ended Microc	ontroller mo	de:				
Compatible CCP	00xx 11xx	ECCP2	RC1/T1OS1	RE7/AD15	RE2/CS	RE1/WR	RE0/RD			
Dual PWM	10xx 11xx	P2A	RC1/T1OS1	RE7/AD15	P2B	RE1/WR	RE0/RD			
Quad PWM	x1xx 11xx	P2A	RC1/T1OS1	RE7/AD15	P2B	P2C	P2D			

# TABLE 17-2:PIN CONFIGURATIONS FOR ECCP2

**Legend:** x = Don't care. Shaded cells indicate pin assignments not used by ECCP2 in a given mode.

ECCP Mode	CCP3CON Configuration	RD1 or RG0 <sup>(1)</sup>	RE4	RE3	RD2 or RG3 <sup>(1)</sup>	RH5 <sup>(2)</sup>	RH4 <sup>(2)</sup>				
64-Pin Devices; 80-Pin Devices, ECCPMX = 1; 100-Pin Devices, ECCPMX = 1, Microcontroller mode:											
Compatible CCP	00xx 11xx	ECCP3	RE4	RE3	RD2/RG3	RH5/AN13	RH4/AN12				
Dual PWM	10xx 11xx	P3A	P3B	RE3	RD2/RG3	RH5/AN13	RH4/AN12				
Quad PWM	x1xx 11xx	P3A	P3B	P3C	P3D	RH5/AN13	RH4/AN12				
80-Pin Devices, ECCPMX = 0; 100-Pin Devices, ECCPMX = 0, All Program Memory modes:											
Compatible CCP	00xx 11xx	ECCP3	RE6/AD14	RE5/AD13	RD2/RG3	RH5/AN13	RH4/AN12				
Dual PWM	10xx 11xx	P3A	RE6/AD14	RE5/AD13	RD2/RG3	P3B	RH4/AN12				
Quad PWM <sup>(3)</sup>	x1xx 11xx	P3A	RE6/AD14	RE5/AD13	P3D	P3B	P3C				
100	-Pin Devices, E	CCPMX = 1, I	Extended Mic	rocontroller v	with 12-Bit Ac	Idress Width:					
Compatible CCP	00xx 11xx	ECCP3	RE4/AD12	RE3/AD11	RD2/RG3	RH5/AN13	RH4/AN12				
Dual PWM	10xx 11xx	P3A	P3B	RE3/AD11	RD2/RG3	RH5/AN13	RH4/AN12				
100-Pin Dev	vices, ECCPMX	= 1, Extende	d Microcontr	oller mode wi	th 16-Bit or 2	0-Bit Address	s Width:				
Compatible CCP	00xx 11xx	ECCP3	RE6/AD14	RE5/AD13	RD2/RG3	RH5/AN13	RH4/AN12				
100-Pin Dev Compatible CCP Legend: x = Do	00xx 11xx	ECCP3	RE6/AD14	RE5/AD13	RD2/RG3	RH5/AN13					

#### **TABLE 17-3**: **PIN CONFIGURATIONS FOR ECCP3**

**Legend:** x = Don't care. Shaded cells indicate pin assignments not used by ECCP3 in a given mode.

Note 1: ECCP3/P3A and CCP4/P3D are multiplexed with RD1 and RD2 on 64-pin devices, and RG0 and RG3 on 80-pin and 100-pin devices.

These pin options are not available on 64-pin devices.

3: With ECCP3 in Quad PWM mode, the CCP4 pin's output is overridden by P3D; otherwise, CCP4 is fully operational.

#### 17.2 **Capture and Compare Modes**

Except for the operation of the Special Event Trigger discussed below, the Capture and Compare modes of the ECCPx modules are identical in operation to that of CCP4. These are discussed in detail in Section 16.2 "Capture Mode" and Section 16.3 "Compare Mode".

#### SPECIAL EVENT TRIGGER 17.2.1

ECCP1 and ECCP2 incorporate an internal hardware trigger that is generated in Compare mode on a match between the CCPRx register pair and the selected timer. This can be used in turn to initiate an action. This mode is selected by setting CCPxCON<3:0> to '1011'.

The Special Event Trigger output of either ECCP1 or ECCP2 resets the TMR1 or TMR3 register pair, depending on which timer resource is currently selected. This allows the CCPRx register to effectively be a 16-Bit Programmable Period register for Timer1 or Timer3. In addition, the ECCP2 Special Event Trigger will also start an A/D conversion if the A/D module is enabled.

Special Event Triggers are not implemented for ECCP3, CCP4 or CCP5. Selecting the Special Event Trigger mode for these modules has the same effect as selecting the Compare with Software Interrupt mode (CCPxM3:CCPxM0 = 1010).

The Special Event Trigger from ECCP2 Note: will not set the Timer1 or Timer3 interrupt flag bits.

#### 17.3 Standard PWM Mode

When configured in Single Output mode, the ECCPx modules function identically to the standard CCPx modules in PWM mode, as described in Section 16.4 "PWM Mode". This is also sometimes referred to as "Compatible CCP" mode, as in Tables 17-1 through 17-3.

Note: When setting up single output PWM operations, users are free to use either of the processes described in Section 16.4.3 "Setup for PWM Operation" or Section 17.4.9 "Setup for PWM Operation". The latter is more generic but will work for either single or multi-output PWM.

# 17.4 Enhanced PWM Mode

The Enhanced PWM mode provides additional PWM output options for a broader range of control applications. The module is a backward compatible version of the standard CCPx modules and offers up to four outputs, designated PxA through PxD. Users are also able to select the polarity of the signal (either active-high or active-low). The module's output mode and polarity are configured by setting the PxM1:PxM0 and CCPxM3CCPxM0 bits of the CCPxCON register (CCPxCON<7:6> and <3:0>, respectively).

For the sake of clarity, Enhanced PWM mode operation is described generically throughout this section with respect to ECCP1 and TMR2 modules. Control register names are presented in terms of ECCP1. All three Enhanced modules, as well as the two timer resources, can be used interchangeably and function identically. TMR2 or TMR4 can be selected for PWM operation by selecting the proper bits in T3CON.

Figure 17-1 shows a simplified block diagram of PWM operation. All control registers are double-buffered and are loaded at the beginning of a new PWM cycle (the period boundary when Timer2 resets) in order to prevent glitches on any of the outputs. The exception is the ECCP1 Dead-Band Delay register, ECCP1DEL, which is loaded at either the duty cycle boundary or the boundary period (whichever comes first). Because of the buffering, the module waits until the assigned timer resets instead of starting immediately. This means that

Enhanced PWM waveforms do not exactly match the standard PWM waveforms, but are instead, offset by one full instruction cycle (4 Tosc).

As before, the user must manually configure the appropriate TRIS bits for output.

#### 17.4.1 PWM PERIOD

The PWM period is specified by writing to the PR2 register. The PWM period can be calculated using the following equation:

### **EQUATION 17-1:**


```
PWM Period = [(PR2) + 1] \cdot 4 \cdot TOSC \cdot (TMR2 Prescale Value)
```

PWM frequency is defined as 1/[PWM period]. When TMR2 is equal to PR2, the following three events occur on the next increment cycle:

- · TMR2 is cleared
- The ECCP1 pin is set (if PWM duty cycle = 0%, the ECCP1 pin will not be set)
- The PWM duty cycle is copied from CCPR1L into CCPR1H

Note: The Timer2 postscaler (see Section 13.0 "Timer2 Module") is not used in the determination of the PWM frequency. The postscaler could be used to have a servo update rate at a different frequency than the PWM output.

# FIGURE 17-1: SIMPLIFIED BLOCK DIAGRAM OF THE ENHANCED PWM MODULE



© 2007 Microchip Technology Inc.

# 17.4.2 PWM DUTY CYCLE

The PWM duty cycle is specified by writing to the CCPR1L register and to the CCP1CON<5:4> bits. Up to 10-bit resolution is available. The CCPR1L contains the eight MSbs and the CCP1CON<5:4> bits contain the two LSbs. This 10-bit value is represented by CCPR1L:CCP1CON<5:4>. The PWM duty cycle is calculated by the equation:

# EQUATION 17-2:

PWM Duty Cycle = (CCPR1L:CCP1CON<5:4>) • TOSC • (TMR2 Prescale Value)

CCPR1L and CCP1CON<5:4> can be written to at any time but the duty cycle value is not copied into CCPR1H until a match between PR2 and TMR2 occurs (i.e., the period is complete). In PWM mode, CCPR1H is a read-only register.

The CCPR1H register and a 2-bit internal latch are used to double-buffer the PWM duty cycle. This double-buffering is essential for glitchless PWM operation. When the CCPR1H and 2-bit latch match TMR2, concatenated with an internal 2-bit Q clock or two bits of the TMR2 prescaler, the ECCP1 pin is cleared. The maximum PWM resolution (bits) for a given PWM frequency is given by the following equation:

# EQUATION 17-3:

PWM Resolution (max) =	$\log\left(\frac{FOSC}{FPWM}\right)$ bits
1 www.resolution(inax) -	log(2)

Note: If the PWM duty cycle value is longer than the PWM period, the ECCP1 pin will not be cleared.

# 17.4.3 PWM OUTPUT CONFIGURATIONS

The P1M1:P1M0 bits in the CCP1CON register allow one of four configurations:

- Single Output
- Half-Bridge Output
- · Full-Bridge Output, Forward mode
- Full-Bridge Output, Reverse mode

The Single Output mode is the standard PWM mode discussed in **Section 17.4 "Enhanced PWM Mode"**. The Half-Bridge and Full-Bridge Output modes are covered in detail in the sections that follow.

The general relationship of the outputs in all configurations is summarized in Figure 17-2.

PWM Frequency	2.44 kHz	9.77 kHz	39.06 kHz	156.25 kHz	312.50 kHz	416.67 kHz
Timer Prescaler (1, 4, 16)	16	4	1	1	1	1
PR2 Value	FFh	FFh	FFh	3Fh	1Fh	17h
Maximum Resolution (bits)	10	10	10	8	7	6.58

(	CCP1CON<7:6>	SIGNAL		uty Incle	PR2 + 7
				Period	
00	(Single Output)	P1A Modulated	Delay <sup>(1)</sup>	Delay <sup>(1)</sup>	
		P1A Modulated			1 1
10	(Half-Bridge)	P1B Modulated	— I — <u>I</u>	i	
		P1A Active	_ <u> </u>	I	!
01	(Full-Bridge, Forward)	P1B Inactive	- ; - ;		1 
	i orward)	P1C Inactive	— ı — <u> </u>		 
		P1D Modulated			
		P1A Inactive	- ¦ 		
11	(Full-Bridge,	P1B Modulated		`  '	ı i
	Reverse)	P1C Active	_ ; _ ;		i i
		P1D Inactive		1	1 1 1

# FIGURE 17-2: PWM OUTPUT RELATIONSHIPS (ACTIVE-HIGH STATE)

# FIGURE 17-3: PWM OUTPUT RELATIONSHIPS (ACTIVE-LOW STATE)

00	(Single Output)	P1A Modulated				
		P1A Modulated				
10	(Half-Bridge)	P1B Modulated		Delay <sup>(1)</sup>	Delay <sup>(1)</sup>	
		P1A Active			1 1 	1 1
	(Full-Bridge,	P1B Inactive				 
01	Forward)	P1C Inactive	<u>'</u>			 
		P1D Modulated	_ —'			
		P1A Inactive			· · ·	
11	(Full-Bridge,	P1B Modulated				- 
11	Reverse)	P1C Active	'		1 1 1	1 1 1
		P1D Inactive			1 1 1	
Rela	tionships:		1		!	1
Pe	eriod = 4 * Tosc * (I	PR2 + 1) * (TMR2 Presc (CCPR1L<7:0>:CCP1C				


# 17.4.4 HALF-BRIDGE MODE

In the Half-Bridge Output mode, two pins are used as outputs to drive push-pull loads. The PWM output signal is output on the P1A pin, while the complementary PWM output signal is output on the P1B pin (Figure 17-4). This mode can be used for half-bridge applications, as shown in Figure 17-5, or for full-bridge applications, where four power switches are being modulated with two PWM signals.


In Half-Bridge Output mode, the programmable dead-band delay can be used to prevent shoot-through current in half-bridge power devices. The value of bits, P1DC6:P1DC0, sets the number of instruction cycles before the output is driven active. If the value is greater than the duty cycle, the corresponding output remains inactive during the entire cycle. See **Section 17.4.6** "**Programmable Dead-Band Delay**" for more details on dead-band delay operations.

Since the P1A and P1B outputs are multiplexed with the PORTC<2> and PORTE<6> data latches, the TRISC<2> and TRISE<6> bits must be cleared to configure P1A and P1B as outputs.

#### FIGURE 17-4: HALF-BRIDGE PWM OUTPUT




# FIGURE 17-5: EXAMPLES OF HALF-BRIDGE OUTPUT MODE APPLICATIONS




# 17.4.5 FULL-BRIDGE MODE

In Full-Bridge Output mode, four pins are used as outputs; however, only two outputs are active at a time. In the Forward mode, pin P1A is continuously active and pin P1D is modulated. In the Reverse mode, pin P1C is continuously active and pin P1B is modulated. These are illustrated in Figure 17-6. P1A, P1B, P1C and P1D outputs are multiplexed with the data latches of the port pins listed in Table 17-1 and Table 17-3. The corresponding TRIS bits must be cleared to make the P1A, P1B, P1C and P1D pins outputs.





# FIGURE 17-7: EXAMPLE OF FULL-BRIDGE APPLICATION



# 17.4.5.1 Direction Change in Full-Bridge Mode

In the Full-Bridge Output mode, the P1M1 bit in the CCP1CON register allows users to control the forward/ reverse direction. When the application firmware changes this direction control bit, the module will assume the new direction on the next PWM cycle.

Just before the end of the current PWM period, the modulated outputs (P1B and P1D) are placed in their inactive state, while the unmodulated outputs (P1A and P1C) are switched to drive in the opposite direction. This occurs in a time interval of (4 Tosc \* (Timer2 Prescale Value) before the next PWM period begins. The Timer2 prescaler will be either 1, 4 or 16, depending on the value of the T2CKPS bits (T2CON<1:0>). During the interval from the switch of the unmodulated outputs to the beginning of the next period, the modulated outputs (P1B and P1D) remain inactive. This relationship is shown in Figure 17-8.

Note that in Full-Bridge Output mode, the ECCP1 module does not provide any dead-band delay. In general, since only one output is modulated at all times, dead-band delay is not required. However, there is a situation where a dead-band delay might be required. This situation occurs when both of the following conditions are true:

- 1. The direction of the PWM output changes when the duty cycle of the output is at or near 100%.
- 2. The turn-off time of the power switch, including the power device and driver circuit, is greater than the turn-on time.


Figure 17-9 shows an example where the PWM direction changes from forward to reverse at a near 100% duty cycle. At time t1, the outputs, P1A and P1D, become inactive, while output, P1C, becomes active. In this example, since the turn-off time of the power devices is longer than the turn-on time, a shoot-through current may flow through power devices, QC and QD (see Figure 17-7), for the duration of 't'. The same phenomenon will occur to power devices, QA and QB, for PWM direction change from reverse to forward.

If changing PWM direction at high duty cycle is required for an application, one of the following requirements must be met:


- 1. Reduce PWM for a PWM period before changing directions.
- 2. Use switch drivers that can drive the switches off faster than they can drive them on.

Other options to prevent shoot-through current may exist.









© 2007 Microchip Technology Inc.

#### 17.4.6 PROGRAMMABLE DEAD-BAND DELAY

In half-bridge applications, where all power switches are modulated at the PWM frequency at all times, the power switches normally require more time to turn off than to turn on. If both the upper and lower power switches are switched at the same time (one turned on and the other turned off), both switches may be on for a short period of time until one switch completely turns off. During this brief interval, a very high current (*shoot-through current*) may flow through both power switches, shorting the bridge supply. To avoid this potentially destructive shoot-through current from flowing during switching, turning on either of the power switches is normally delayed to allow the other switch to completely turn off.

In the Half-Bridge Output mode, a digitally programmable dead-band delay is available to avoid shoot-through current from destroying the bridge power switches. The delay occurs at the signal transition from the non-active state to the active state. See Figure 17-4 for illustration. The lower seven bits of the ECCP1DEL register (Register 17-2) set the delay period in terms of microcontroller instruction cycles (TcY or 4 Tosc).

### 17.4.7 ENHANCED PWM AUTO-SHUTDOWN

When the ECCP1 is programmed for any of the Enhanced PWM modes, the active output pins may be configured for auto-shutdown. Auto-shutdown immediately places the Enhanced PWM output pins into a defined shutdown state when a shutdown event occurs.

A shutdown event can be caused by either of the two comparator modules or the FLT0 pin (or any combination of these three sources). The comparators may be used to monitor a voltage input proportional to a current being monitored in the bridge circuit. If the voltage exceeds a threshold, the comparator switches state and triggers a shutdown. Alternatively, a low-level digital signal on the FLT0 pin can also trigger a shutdown. The auto-shutdown feature can be disabled by not selecting any auto-shutdown sources. The auto-shutdown sources to be used are selected using the ECCP1AS2:ECCP1AS0 bits (ECCP1AS<6:4>).

When a shutdown occurs, the output pins are asynchronously placed in their shutdown states, specified by the PSS1AC1:PSS1AC0 and PSS1BD1:PSS1BD0 bits (ECCP1AS<3:0>). Each pin pair (P1A/P1C and P1B/P1D) may be set to drive high, drive low or be tri-stated (not driving). The ECCP1ASE bit (ECCP1AS<7>) is also set to hold the Enhanced PWM outputs in their shutdown states.

The ECCP1ASE bit is set by hardware when a shutdown event occurs. If automatic restarts are not enabled, the ECCP1ASE bit is cleared by firmware when the cause of the shutdown clears. If automatic restarts are enabled, the ECC1PASE bit is automatically cleared when the cause of the auto-shutdown has cleared.

If the ECCP1ASE bit is set when a PWM period begins, the PWM outputs remain in their shutdown state for that entire PWM period. When the ECCP1ASE bit is cleared, the PWM outputs will return to normal operation at the beginning of the next PWM period.

**Note:** Writing to the ECCP1ASE bit is disabled while a shutdown condition is active.

# REGISTER 17-2: ECCP1DEL: ECCP1 DEAD-BAND DELAY REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
P1RSEN	P1DC6	P1DC5	P1DC4	P1DC3	P1DC2	P1DC1	P1DC0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit,	read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown
n = Value at POR	"1" = Bit is set	U = Bit is cleared	x = Bit is unknown
bit 7 <b>P1F</b>	SEN: PWM Restart Enable bit		

1 = Upon auto-shutdown, the ECCP1ASE bit clears automatically once the sh	utdown event goes
away; the PWM restarts automatically	

0 = Upon auto-shutdown, ECCP1ASE must be cleared in software to restart the PWM

# bit 6-0 P1DC6:P1DC0: PWM Delay Count bits

Delay time, in number of Fosc/4 (4 \* Tosc) cycles, between the scheduled time and actual time for a PWM signal to transition to active.

# REGISTER 17-3: ECCP1AS: ECCP1 AUTO-SHUTDOWN CONFIGURATION REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			
ECCP1ASE	ECCP1AS2	ECCP1AS1	ECCP1AS0	PSS1AC1	PSS1AC0	PSS1BD1	PSS1BD0			
bit 7			•	•			bit 0			
Legend:										
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	l as '0'				
-n = Value at F	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown			
bit 7	ECCP1ASE:	ECCP1 Auto-S	Shutdown Eve	nt Status bit						
	0 = ECCP1 o	utputs are ope	rating							
				P1 outputs are	in shutdown sta	ate				
bit 6-4	ECCP1AS2:E	ECCP1AS0: E	CCP1 Auto-Sh	utdown Sourc	e Select bits					
	000 = Auto-s	hutdown is dis	abled							
	001 = Compa	rator 1 output								
		arator 2 output								
		Comparator 1	or 2							
		100 = FLTO								
	101 = FLT0 or Comparator 1 110 = FLT0 or Comparator 2									
	110 = FLT0 or Comparator 1 or Comparator 2									
bit 3-2		SIACO: Pins	•		ntrol bits					
	00 = Drive Pir	ns A and C to '	0'							
	01 = Drive Pins A and C to '1'									
	1x = Pins A a	nd C tri-state								
bit 1-0	PSS1BD1:PS	S1BD0: Pins	B and D Shuto	lown State Co	ntrol bits					
	00 = Drive Pir	ns B and D to '	0'							
	01 = Drive Pir	ns B and D to '	1'							
	1x = Pins B a	nd D tri-state								

1x = Pins B and D tri-state

# 17.4.7.1 Auto-Shutdown and Automatic Restart

The auto-shutdown feature can be configured to allow automatic restarts of the module following a shutdown event. This is enabled by setting the P1RSEN bit of the ECCP1DEL register (ECCP1DEL<7>).

In Shutdown mode with P1RSEN = 1 (Figure 17-10), the ECCP1ASE bit will remain set for as long as the cause of the shutdown continues. When the shutdown condition clears, the ECCP1ASE bit is cleared. If P1RSEN = 0 (Figure 17-11), once a shutdown condition occurs, the ECCP1ASE bit will remain set until it is cleared by firmware. Once ECCP1ASE is cleared, the Enhanced PWM will resume at the beginning of the next PWM period.

Note:	Writing to the ECCP1ASE bit is disabled
	while a shutdown condition is active.

Independent of the P1RSEN bit setting, if the auto-shutdown source is one of the comparators, the shutdown condition is a level. The ECCP1ASE bit cannot be cleared as long as the cause of the shutdown persists.

The Auto-Shutdown mode can be forced by writing a '1' to the ECCP1ASE bit.


# 17.4.8 START-UP CONSIDERATIONS

When the ECCP1 module is used in the PWM mode, the application hardware must use the proper external pull-up and/or pull-down resistors on the PWM output pins. When the microcontroller is released from Reset, all of the I/O pins are in the high-impedance state. The external circuits must keep the power switch devices in the OFF state until the microcontroller drives the I/O pins with the proper signal levels, or activates the PWM output(s).


The CCP1M1:CCP1M0 bits (CCP1CON<1:0>) allow the user to choose whether the PWM output signals are active-high or active-low for each pair of PWM output pins (P1A/P1C and P1B/P1D). The PWM output polarities must be selected before the PWM pins are configured as outputs. Changing the polarity configuration while the PWM pins are configured as outputs is not recommended since it may result in damage to the application circuits.

The P1A, P1B, P1C and P1D output latches may not be in the proper states when the PWM module is initialized. Enabling the PWM pins for output at the same time as the ECCP1 module may cause damage to the application circuit. The ECCP1 module must be enabled in the proper output mode and complete a full PWM cycle before configuring the PWM pins as outputs. The completion of a full PWM cycle is indicated by the TMR2IF bit being set as the second PWM period begins.

# FIGURE 17-10: PWM AUTO-SHUTDOWN (P1RSEN = 1, AUTO-RESTART ENABLED)



# FIGURE 17-11: PWM AUTO-SHUTDOWN (P1RSEN = 0, AUTO-RESTART DISABLED)



# 17.4.9 SETUP FOR PWM OPERATION

The following steps should be taken when configuring the ECCP1 module for PWM operation:

- 1. Configure the PWM pins P1A and P1B (and P1C and P1D, if used) as inputs by setting the corresponding TRIS bits.
- 2. Set the PWM period by loading the PR2 (PR4) register.
- Configure the ECCP1 module for the desired PWM mode and configuration by loading the CCP1CON register with the appropriate values:
  - Select one of the available output configurations and direction with the P1M1:P1M0 bits.
  - Select the polarities of the PWM output signals with the CCP1M3:CCP1M0 bits.
- 4. Set the PWM duty cycle by loading the CCPR1L register and the CCP1CON<5:4> bits.
- 5. For auto-shutdown:
  - Disable auto-shutdown; ECCP1ASE = 0
  - · Configure auto-shutdown source
  - · Wait for Run condition
- 6. For Half-Bridge Output mode, set the dead-band delay by loading ECCP1DEL<6:0> with the appropriate value.
- 7. If auto-shutdown operation is required, load the ECCP1AS register:
  - Select the auto-shutdown sources using the ECCP1AS2:ECCP1AS0 bits.
  - Select the shutdown states of the PWM output pins using PSS1AC1:PSS1AC0 and PSS1BD1:PSS1BD0 bits.
  - Set the ECCP1ASE bit (ECCP1AS<7>).

- 8. If auto-restart operation is required, set the P1RSEN bit (ECCP1DEL<7>).
- 9. Configure and start TMR2 (TMR4):
  - Clear the TMRx interrupt flag bit by clearing the TMRxIF bit (PIR1<1> for Timer2 or PIR3<3> for Timer4).
  - Set the TMRx prescale value by loading the TxCKPS bits (T2CON<1:0> for Timer2 or T4CON<1:0> for Timer4).
  - Enable Timer2 (or Timer4) by setting the TMRxON bit (T2CON<2> for Timer2 or T4CON<2> for Timer4).
- 10. Enable PWM outputs after a new PWM cycle has started:
  - Wait until TMR2 (TMR4) overflows (TMRxIF bit is set).
  - Enable the ECCP1/P1A, P1B, P1C and/or P1D pin outputs by clearing the respective TRIS bits.
  - Clear the ECCP1ASE bit (ECCP1AS<7>).

### 17.4.10 EFFECTS OF A RESET

Both Power-on Reset and subsequent Resets will force all ports to Input mode and the CCPx/ECCPx registers to their Reset states.

This forces the Enhanced CCPx modules to reset to a state compatible with the standard CCPx modules.

IABLE 1/-	5: REGIS	FIERS ASS	OCIATED	WITHEC		JLES AND	TIMERI		4
Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
RCON	IPEN	—	CM	RI	TO	PD	POR	BOR	60
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR2	OSCFIF	CMIF	ETHIF	r	BCL1IF	—	TMR3IF	CCP2IF	61
PIE2	OSCFIE	CMIE	ETHIE	r	BCL1IE	—	TMR3IE	CCP2IE	61
IPR2	OSCFIP	CMIP	ETHIP	r	BCL1IP	—	TMR3IP	CCP2IP	61
PIR3	SSP2IF	BCL2IF	RC2IF	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE	BCL2IE	RC2IE	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP	BCL2IP	RC2IP	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
TRISB	TRISB7	TRISB6	TRISB5	TRISB4	TRISB3	TRISB2	TRISB1	TRISB0	61
TRISC	TRISC7	TRISC6	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	61
TRISD <sup>(1)</sup>	TRISD7	TRISD6	TRISD5	TRISD4	TRISD3	TRISD2	TRISD1	TRISD0	61
TRISE	TRISE7 <sup>(2)</sup>	TRISE6 <sup>(2)</sup>	TRISE5	TRISE4	TRISE3	TRISE2	TRISE1	TRISE0	61
TRISG	TRISG7	TRISG6	TRISG5	TRISG4	TRISG3 <sup>(2)</sup>	TRISG2	TRISG1	TRISG0 <sup>(2)</sup>	61
TRISH <sup>(2)</sup>	TRISH7	TRISH6	TRISH5	TRISH4	TRISH3	TRISH2	TRISH1	TRISH0	61
TMR1L	Timer1 Regis	ter Low Byte							60
TMR1H	Timer1 Regis	ter High Byte							60
T1CON	RD16	T1RUN	T1CKPS1	T1CKPS0	T1OSCEN	T1SYNC	TMR1CS	TMR10N	60
TMR2	Timer2 Regis	ter							60
T2CON	_	T2OUTPS3	T2OUTPS2	T2OUTPS1	T2OUTPS0	TMR2ON	T2CKPS1	T2CKPS0	60
PR2	Timer2 Period	d Register							60
TMR3L	Timer3 Regis	ter Low Byte							60
TMR3H	Timer3 Regis	ter High Byte							60
T3CON	RD16	T3CCP2	T3CKPS1	T3CKPS0	T3CCP1	T3SYNC	TMR3CS	TMR3ON	61
TMR4	Timer4 Regis	ter							62
T4CON	_	T4OUTPS3	T4OUTPS2	T4OUTPS1	T4OUTPS0	TMR4ON	T4CKPS1	T4CKPS0	62
PR4	Timer4 Period	d Register							62
CCPRxL <sup>(3)</sup>	Capture/Com	pare/PWM Re	gister x Low I	Byte					60
CCPRxH <sup>(3)</sup>	Capture/Com	pare/PWM Re	gister x High	Byte					60
CCPxCON <sup>(3)</sup>	PxM1	PxM0	DCxB1	DCxB0	CCPxM3	CCPxM2	CCPxM1	CCPxM0	60
ECCPxAS <sup>(3)</sup>	ECCPXASE	ECCPxAS2	ECCPxAS1	ECCPxAS0	PSSxAC1	PSSxAC0	PSSxBD1	PSSxBD0	60, 63
ECCPxDEL <sup>(3)</sup>	PxRSEN	PxDC6	PxDC5	PxDC4	PxDC3	PxDC2	PxDC1	PxDC0	63
			-				_		

# TABLE 17-5: REGISTERS ASSOCIATED WITH ECCPx MODULES AND TIMER1 TO TIMER4

Legend: — = unimplemented, read as '0', r = reserved. Shaded cells are not used during ECCPx operation.

Note 1: Applicable to 64-pin devices only.

2: Registers and/or specific bits are unimplemented on 64-pin devices.

3: Generic term for all of the identical registers of this name for all Enhanced CCPx modules, where 'x' identifies the individual module (ECCP1, ECCP2 or ECCP3). Bit assignments and Reset values for all registers of the same generic name are identical.

# 18.0 ETHERNET MODULE

All members of the PIC18F97J60 family of devices feature an embedded Ethernet controller module. This is a complete connectivity solution, including full implementations of both Media Access Control (MAC) and Physical Layer transceiver (PHY) modules. Two pulse transformers and a few passive components are all that are required to connect the microcontroller directly to an Ethernet network.

The Ethernet module meets all of the IEEE 802.3 specifications for 10-BaseT connectivity to a twisted-pair network. It incorporates a number of packet filtering schemes to limit incoming packets. It also provides an internal DMA module for fast data throughput and hardware assisted IP checksum calculations. Provisions are also made for two LED outputs to indicate link and network activity.

A simple block diagram of the module is shown in Figure 18-1.

The Ethernet module consists of five major functional blocks:

- The PHY transceiver module that encodes and decodes the analog data that is present on the twisted-pair interface and sends or receives it over the network.
- 2. The MAC module that implements IEEE 802.3 compliant MAC logic and provides Media Independent Interface Management (MIIM) to control the PHY.
- 3. An independent, 8-Kbyte RAM buffer for storing packets that have been received and packets that are to be transmitted.
- 4. An arbiter to control access to the RAM buffer when requests are made from the microcontroller core, DMA, transmit and receive blocks.
- 5. The register interface that functions as an interpreter of commands and internal status signals between the module and the microcontroller's SFRs.




FIGURE 18-1: ETHERNET MODULE BLOCK DIAGRAM

# 18.1 Physical Interfaces and External Connections

# 18.1.1 SIGNAL AND POWER INTERFACES

PIC18F97J60 family devices all provide a dedicated 4-pin signal interface for the Ethernet module. No other microcontroller or peripheral functions are multiplexed with these pins, so potential device configuration conflicts do not need to be considered. The pins are:

- TPIN+: Differential plus twisted-pair input
- · TPIN-: Differential minus twisted-pair input
- TPOUT+: Differential plus twisted-pair output
- TPOUT-: Differential minus twisted-pair output

No provisions are made for providing or receiving digital Ethernet data from an external Ethernet PHY.

In addition to the signal connections, the Ethernet module has its own independent voltage source and ground connections for the PHY module. Separate connections are provided for the receiver (VDDRX and VSSRX), the transmitter (VDDTX and VSSTX) and the transmitter's internal PLL (VDDPLL and VSSPLL). Although the voltage requirements are the same as VDD and VSS for the microcontroller, the pins are not internally connected. For the Ethernet module to operate properly, supply voltage and ground must be connected to these pins. All of the microcontroller's power and ground supply pins should be externally connected to the same power source or ground node, with no inductors or other filter components between the microcontroller and Ethernet module's VDD pins.

Besides the independent voltage connections, the PHY module has a separate bias current input pin, RBIAS. A bias current, derived from an external resistor, must be applied to RBIAS for proper transceiver operation.

#### 18.1.2 LED CONFIGURATION

The PHY module provides separate outputs to drive the standard Ethernet indicators, LEDA and LEDB. The LED outputs are multiplexed with PORTA pins RA0 and RA1. Their use as LED outputs is enabled by setting the Configuration bit, ETHLED (Register 24-6, CONFIG3H<2>). When configured as LED outputs, RA0/LEDA and RA1/LEDB have sufficient drive capacity (up to 25 mA) to directly power the LEDs. The pins must always be configured to supply (source) current to the LEDs. Users must also configure the pins as outputs by clearing TRISA<1:0>.

The LEDs can be individually configured to automatically display link status, RX/TX activity, etc. A configurable stretch capability prolongs the LED blink duration for short events, such as a single packet transmit, allowing human perception. The options are controlled by the PHLCON register (Register 18-13). Typical values for blink stretch are listed in Table 18-1.

TABLE 18-1: LED BLINK STRETCH LENGTH

Stretch Length	Typical Stretch (ms)
TNSTRCH (normal)	40
TMSTRCH (medium)	70
TLSTRCH (long)	140

# 18.1.3 OSCILLATOR REQUIREMENTS

The Ethernet module is designed to operate at 25 MHz. This is provided by the primary microcontroller clock, either with a 25 MHz crystal connected to the OSC1 and OSC2 pins or an external clock source connected to the OSC1 pin. No provision is made to clock the module from a different source.

To maintain the required clock frequency, the microcontroller can operate only from the primary oscillator source (PRI\_RUN or PRI\_IDLE modes) while the Ethernet module is enabled. Using any other power-managed mode will require that the Ethernet module be disabled.

#### 18.1.3.1 Start-up Timer

The Ethernet module contains a start-up timer, independent of the microcontroller's OST, to ensure that the PHY module's PLL has stabilized before operation. Clearing the module enable bit, ETHEN (ECON2<5>), clears the PHYRDY status bit (ESTAT<0>). Setting the ETHEN bit causes this start-up timer to start counting. When the timer expires, after 1 ms, the PHYRDY bit will be automatically set.

After enabling the module by setting the ETHEN bit, the application software should always poll PHYRDY to determine when normal Ethernet operation can begin.

# 18.1.4 MAGNETICS, TERMINATION AND OTHER EXTERNAL COMPONENTS

To complete the Ethernet interface, the Ethernet module requires several standard components to be installed externally. These components should be connected as shown in Figure 18-2.


The internal analog circuitry in the PHY module requires that an external resistor (2.26 k $\Omega$ ) be attached from RBIAS to ground. The resistor influences the TPOUT+/-signal amplitude. It should be placed as close as possible to the chip with no immediately adjacent signal traces to prevent noise capacitively coupling into the pin and affecting the transmit behavior. It is recommended that the resistor be a surface mount type.

On the TPIN+/TPIN- and TPOUT+/TPOUT- pins, 1:1 center-tapped pulse transformers rated for Ethernet operations (10/100 or 10/100/1000) are required. When the Ethernet module is enabled, current is continually sunk through both TPOUT pins. When the PHY is actively transmitting, a differential voltage is created on the Ethernet cable by varying the relative current sunk by TPOUT+ compared to TPOUT-.

A common-mode choke on the PHY side of the interface (i.e., between the microcontrollers's TPOUT pins and the Ethernet transformer) is not recommend. If a common-mode choke is used to reduce EMI emissions, it should be placed between the Ethernet transformer and pins 1 and 2 of the RJ-45 connector. Many Ethernet transformer modules include common-mode chokes inside the same device package. The transformers should have at least the isolation rating specified in Table 27-28 to protect against static voltages and meet IEEE 802.3 isolation requirements (see Section 27.5 "Ethernet Specifications and Requirements" for specific transformer requirements). Both transmit and receive interfaces additionally require two resistors and a capacitor to properly terminate the transmission line, minimizing signal reflections.

All power supply pins must be externally connected to the same power source. Similarly, all ground references must be externally connected to the same ground node. Each VDD and Vss pin pair should have a 0.1  $\mu$ F ceramic bypass capacitor placed as close to the pins as possible.

Since relatively high currents are necessary to operate the twisted-pair interface, all wires should be kept as short as possible. Reasonable wire widths should be used on power wires to reduce resistive loss. If the differential data lines cannot be kept short, they should be routed in such a way as to have a  $100\Omega$  characteristic impedance.



# FIGURE 18-2: EXTERNAL COMPONENTS REQUIRED FOR ETHERNET OPERATION


# 18.2 Ethernet Buffer and Register Spaces

The Ethernet module uses three independent memory spaces for its operations:

- An Ethernet RAM buffer which stores packet data as it is received and being prepared for transmission.
- A set of 8-bit Special Function Registers (SFRs), used to control the module and pass data back and forth between the module and microcontroller core.
- A separate set of 16-bit PHY registers used specifically for PHY control and status reporting.

The Ethernet buffer and PHY control registers are contained entirely within the Ethernet module and cannot be accessed directly by the microcontroller. Data is transferred between the Ethernet and microcontroller by using buffer and pointer registers mapped in the microcontroller's SFR space. The relationships between the SFRs and the Ethernet module's memory spaces are shown in Figure 18-3.

# FIGURE 18-3: RELATIONSHIP BETWEEN MICROCONTROLLER AND ETHERNET MEMORY SPACES



# 18.2.1 ETHERNET BUFFER AND BUFFER POINTER REGISTERS

The Ethernet buffer contains the transmit and receive memory used by the Ethernet controller. The entire buffer is 8 Kbytes, divided into separate receive and transmit buffer spaces. The sizes and locations of transmit and receive memory are fully definable using the pointers in the Ethernet SFR space. The organization of the memory space and the relationships of the pointers are shown in Figure 18-4.

The buffer is always accessible through the EDATA and Ethernet Pointer SFRs, regardless of whether or not the Ethernet module is enabled. This makes the buffer potentially useful for applications requiring large amounts of RAM and that do not require Ethernet communication. In these instances, disabling the Ethernet module reduces overall power usage but does not prevent buffer access.

# 18.2.1.1 Reading and Writing to the Buffer

The Ethernet buffer contents are accessed through the EDATA register, which acts as a window from the microcontroller data bus into the buffer. The location of that window is determined by either the ERDPT or EWRPT Pointers, depending on the operation being performed. For example, writing to EDATA causes a write to the Ethernet buffer at the address currently indicated by EWRPT register pair. Similarly, moving the contents of EDATA to another register actually moves the buffer contents at the address indicated by the ERDPT Pointer.


When the AUTOINC bit (ECON2<7>) is set, the associated Read or Write Pointer increments by one address following each read or write operation. This eliminates the need to constantly update a pointer after each read or write, simplifying multiple sequential operations. By default, the AUTOINC bit is set.

While sequentially reading from the receive buffer, a wrapping condition will occur at the end of the receive buffer. A read of EDATA from the address programmed into the ERXND Pointers will cause the ERDPT registers to be incremented to the value contained in the ERXST Pointers. Writing to the buffer, on the other hand, does not result in automatic wrapping.

By design, the Ethernet memory buffer is unable to support a set of operations where EDATA is used as both an operand and a data destination. Failure to observe these restrictions will result in a corrupted read or write. Also, due to the read-modify-write architecture of the processor core, single-cycle instructions which write to the EDATA register will have a side effect of automatically incrementing the ERDPT registers when AUTOINC is set. Using double-cycle MOVFF, MOVSF and MOVSS instructions to write to EDATA will not affect the Read Pointer. See the following note for examples.

	•						
Note:	Any single instruction that performs both a read and write to the EDATA SFR register will result in a corrupted operation. Unsupported examples:						
	INCF EDATA, F XORWF EDATA, F MOVFF EDATA, EDATA MOVFF INDF0, EDATA; (FSR0 = F61h)						
	Instructions that only perform one read or one write are permitted. Supported examples:						
	INCF EDATA, W MOVF EDATA, W MOVFF INDFO, EDATA; (FSR0 != F61h)						
	Single-cycle, write-only instructions, while valid, will have a side effect of also incre- menting the ERDPT registers when AUTOINC is enabled. Examples incrementing both ERDPT and EWRPT:						
	CLRF EDATA SETF EDATA MOVWF EDATA						

# FIGURE 18-4: ETHERNET BUFFER ORGANIZATION



### 18.2.1.2 Receive Buffer

The receive buffer constitutes a circular FIFO buffer managed by hardware. The register pairs, ERXSTH:ERXSTL and ERXNDH:ERXNDL, serve as pointers to define the buffer's size and location within the memory. The byte pointed to by the ERXST pair and the byte pointed to by the ERXND pair are both included in the FIFO buffer.


As bytes of data are received from the Ethernet interface, they are written into the receive buffer sequentially. However, after the memory pointed to by the ERXND Pointers is written to, the hardware will automatically write the next byte of received data to the memory pointed to by the ERXST pair. As a result, the receive hardware will never write outside the boundaries of the FIFO.

The user may program the ERXST and ERXND Pointers while the receive logic is disabled. The pointers must not be modified while the receive logic is enabled (ERXEN (ECON1<2>) is set).

The buffer hardware uses an Internal Pointer (not mapped to any user-accessible registers) to determine where unvalidated incoming data is to be written. When a packet has been completely received and validated, the read-only ERXWRPTH:ERXWRPTL registers are updated with the Internal Pointer's value. Thus, the ERXWRPT registers define the general area in the receive buffer where data is currently being written. This makes it useful for determining how much free space is available within the FIFO.

The ERXRDPT registers define a location within the FIFO where the receive hardware is forbidden to write to. In normal operation, the receive hardware will write data up to, but not including, the memory pointed to by the ERXRDPT registers. If the FIFO fills up with data and new data continues to arrive, the hardware will not overwrite the previously received data. Instead, the incoming data will be thrown away and the old data will be preserved. In order to continuously receive new data, the application must periodically advance this pointer whenever it finishes processing some, or all, of the old received data.

An example of how the Receive Buffer Pointers and packet data are related in the circular buffer scheme is shown in Figure 18-5. Note that while four packets are shown in this example, the actual number of packets may be greater or lesser.



#### FIGURE 18-5: CIRCULAR FIFO BUFFER AND THE RELATIONSHIPS OF THE POINTERS

# 18.2.1.3 Transmit Buffer

Any space within the 8-Kbyte memory which is not programmed as part of the receive FIFO buffer is considered to be the transmit buffer. The responsibility of managing where packets are located in the transmit buffer belongs to the application. Whenever the application decides to transmit a packet, the ETXST and ETXND Pointers are programmed with addresses specifying where, within the transmit buffer, the particular packet to transmit is located. The hardware does not check that the start and end addresses do not overlap with the receive buffer. To prevent buffer corruption, the firmware must not transmit a packet while the ETXST and ETXND Pointers are overlapping the receive buffer, or while the ETXND Pointers are too close to the receive buffer. See Section 18.5.2 "Transmitting Packets" for more information.

# 18.2.1.4 Buffer Arbiter and Access Arbitration

The Ethernet buffer is clocked at one-half of the microcontroller clock rate. Varying amounts of memory access bandwidth are available depending on the clock speed. The total bandwidth available, in bytes per second, is equal to twice the instruction rate (2 \* FCY, or FOSC/2). For example, at a system clock speed of 41.667 MHz, the total available memory bandwidth that is available is 20.834 Mbyte/s. At an Ethernet signaling rate of 10 Mbit/s, the Ethernet RX engine requires 1.25 Mbyte/s of buffer memory bandwidth to operate without causing an overrun. If Full-Duplex mode is used, an additional 1.25 Mbyte/s is required to allow for simultaneous RX and TX activity.

Because of the finite available memory bandwidth, a three-channel arbiter is used to allocate bandwidth between the RX engine, the TX and DMA engines, and the microcontroller's CPU (i.e., the application access-

ing EDATA). The arbiter gives the EDATA register accesses first priority, while all remaining bandwidth is shared between the RX and TX/DMA blocks.

With arbitration, bandwidth limitations require that some care be taken in balancing the needs of the module's hardware with that of the application. Accessing the EDATA register too often may result in the RX or TX blocks causing a buffer overrun or underrun, respectively. If such a memory access failure occurs, the BUFER bit (ESTAT<6>) and either the TXERIF or RXERIF interrupt flag becomes set, and a TX or RX interrupt occurs (if enabled). In either case, the current packet will be lost or aborted.

To eliminate the risk of lost packets, run the microcontroller core at higher speeds. Following the arbitration restrictions shown in Table 18-2 will prevent memory access failures from occurring. Also, avoid using segments of application code which perform back-to-back accesses of the EDATA register. Instead, insert one or more instructions (including NOP instructions) between each read or write to EDATA.

# 18.2.1.5 DMA Access to the Buffer

The integrated DMA controller must read from the buffer when calculating a checksum, and it must read and write to the buffer when copying memory. The DMA follows the same wrapping rules as previously described for the receive buffer. While it sequentially reads, it will be subject to a wrapping condition at the end of the receive buffer. All writes it does will not be subject to any wrapping conditions. See Section 18.9 "Direct Memory Access Controller" for more information.

TABLE TO		1	_	-			
Fosc	FCY	Available Bandwidth (Mbyte/s)		(MDyte/S)	Application Restrictions		
(MHz)	(MHz) (MHz)		Total After RX After TX		to Prevent Underrun/Overrun		
41.667	10.42	20.83	19.58	18.33	Access EDATA no more than once every 2 Tcy		
31.250	7.81	15.63	14.38	13.13	Access EDATA no more than once every 2 TCY		
25.000	6.25	12.50	11.25	10.00	Access EDATA no more than once every 2 TCY		
20.833	5.21	10.42	9.17	7.92	Access EDATA no more than once every 2 TCY		
13.889	3.47	6.94	5.69	4.44	Access EDATA no more than once every 2 TCY		
12.500	3.13	6.25	5.00	3.75	Access EDATA no more than once every 2 TCY		
8.333	2.08	4.17	2.92	1.67	Access EDATA no more than once every 3 TCY		
6.250	1.56	3.13	1.88	0.63	Access EDATA no more than once every 5 TCY		
4.167	1.04	2.08	0.83	< 0	Do not use DMA, do not use full duplex,		
					access EDATA no more than once every 3 Tcy		
2.778	0.69	1.39	0.14	< 0	Do not use DMA, do not use full duplex,		
					access EDATA no more than once every 10 Tcy		

TABLE 18-2: BUFFER ARBITRATION RESTRICTIONS VS. CLOCK SPEED

### 18.2.2 SFRs AND THE ETHERNET MODULE

Like other peripherals, direct control of the Ethernet module is accomplished through a set of SFRs. Because of their large number, the majority of these registers are located in the bottom half of Bank 14 of the microcontroller's data memory space.

Five key SFRs for the Ethernet module are located in the microcontroller's regular SFR area in Bank 15, where fast access is possible. They are:

- ECON1
- EDATA

-n = Value at POR

- EIR
- The Ethernet Buffer Read Pointer pair (ERDPTH and ERDPTL)

ECON1 is described along with other Ethernet control registers in the following section. EDATA and ERDPTH:ERDPTL are the Ethernet Data Buffer registers and its pointers during read operations (see Section 18.2.1 "Ethernet Buffer and Buffer Pointer Registers"). EIR is part of the Ethernet interrupt structure and is described in Section 18.3 "Ethernet Interrupts".

Many of the Ethernet SFRs in Bank 14 serve as pointer registers to indicate addresses within the dedicated Ethernet buffer for storage and retrieval of packet data. Others store information for packet pattern masks or checksum operations. Several are used for controlling overall module operations, as well as specific MAC and PHY functions.

# 18.2.3 ETHERNET CONTROL REGISTERS

The ECON1 register (Register 18-1) is used to control the main functions of the module. Receive enable, transmit request and DMA control bits are all located here. The ECON2 register (Register 18-2) is used to control other top level functions of the module. The ESTAT register (Register 18-3) is used to report the high-level status of the module and Ethernet communications.

The Ethernet SFRs with the 'E' prefix are always accessible, regardless of whether or not the module is enabled.

x = Bit is unknown

# REGISTER 18-1: ECON1: ETHERNET CONTROL REGISTER 1

'1' = Bit is set

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0	U-0
TXRST	RXRST	DMAST	CSUMEN	TXRTS	RXEN	—	—
bit 7	•		•	•	•		bit 0
Legend:							
R = Readable bit W = Writable bit			U = Unimplem	nented bit, read	as '0'		

'0' = Bit is cleared

bit 7	TXRST: Transmit Logic Reset bit
	1 = Transmit logic is held in Reset
	0 = Normal operation
bit 6	RXRST: Receive Logic Reset bit
	1 = Receive logic is held in Reset
	0 = Normal operation
bit 5	DMAST: DMA Start and Busy Status bit
	<ul> <li>1 = DMA copy or checksum operation is in progress (set by software, cleared by hardware or software)</li> <li>0 = DMA hardware is Idle</li> </ul>
bit 4	CSUMEN: DMA Checksum Enable bit
	1 = DMA hardware calculates checksums
	0 = DMA hardware copies buffer memory
bit 3	TXRTS: Transmit Request to Send bit
	<ul> <li>1 = The transmit logic is attempting to transmit a packet (set by software, cleared by hardware or software)</li> <li>0 = The transmit logic is Idle</li> </ul>
bit 2	RXEN: Receive Enable bit
	<ul> <li>1 = Packets which pass the current filter configuration will be written into the receive buffer</li> <li>0 = All packets received will be discarded by hardware</li> </ul>
bit 1-0	Unimplemented: Read as '0'

# **REGISTER 18-2: ECON2: ETHERNET CONTROL REGISTER 2**

R/W-1	R/W-0 <sup>(1)</sup>	R/W-0	U-0	U-0	U-0	U-0	U-0
AUTOINC	PKTDEC	ETHEN	—	—	—	—	_
bit 7	•	<u> </u>				•	bit 0
Legend:							
R = Readable bit W = Writable bit			bit	U = Unimpler	nented bit, read	as '0'	
-n = Value at P	OR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown

bit 7	AUTOINC: Automatic Buffer Pointer Increment Enable bit 1 = Automatically increment ERDPT or EWRPT registers on reading from or writing to EDATA 0 = Do not automatically change ERDPT and EWRPT registers after EDATA is accessed
bit 6	PKTDEC: Packet Decrement bit
	<ul> <li>1 = Decrement the EPKTCNT register by one</li> <li>0 = Leave EPKTCNT unchanged</li> </ul>
bit 5	ETHEN: Ethernet Module Enable bit
	<ul><li>1 = Ethernet module enabled</li><li>0 = Ethernet module disabled</li></ul>
bit 4-0	Unimplemented: Read as '0'

Note 1: This bit is automatically cleared once it is set.

# REGISTER 18-3: ESTAT: ETHERNET STATUS REGISTER

U-0	R/C-0	U-0	R/C-0	U-0	R-0	R/C-0	R-0
—	BUFER	—	r	—	RXBUSY	TXABRT	PHYRDY
bit 7 bit 0						bit 0	

Legend:			
R = Readable bit	C = Clearable bit	U = Unimplemented bit, r	read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7	Unimplemented: Read as '0'				
bit 6	BUFER: Ethernet Buffer Error Status bit				
	<ul> <li>1 = An Ethernet read or write has generated a buffer error (overrun or underrun)</li> <li>0 = No buffer error has occurred</li> </ul>				
bit 5	Unimplemented: Read as '0'				
bit 4	Reserved: Write as '0'				
bit 3	Unimplemented: Read as '0'				
bit 2	RXBUSY: Receive Busy bit				
	<ul><li>1 = Receive logic is receiving a data packet</li><li>0 = Receive logic is idle</li></ul>				
bit 1	TXABRT: Transmit Abort Error bit				
	<ul><li>1 = The transmit request was aborted</li><li>0 = No transmit abort error</li></ul>				
bit 0	PHYRDY: Ethernet PHY Clock Ready bit				
	1 = Ethernet PHY start-up timer has expired; PHY is ready				
	0 = Ethernet PHY start-up timer is still counting; PHY is not ready				

#### 18.2.4 MAC AND MII REGISTERS

These SFRs are used to control the operations of the MAC and, through the MIIM, the PHY. The MAC and MII registers occupy data addresses E80h-E85h, E8Ah, and EA0h through EB9h.

Although MAC and MII registers appear in the general memory map of the microcontroller, these registers are embedded inside the MAC module. Host interface logic translates the microcontroller data/address bus data to be able to access these registers. The host interface logic imposes restrictions on how firmware is able to access the MAC and MII SFRs. See the following notes.

#### **Note 1:** Do not access the MAC and MII SFRs unless the Ethernet module is enabled (ETHEN = 1).

 Back-to-back accesses of MAC or MII registers are not supported. Between any instruction which addresses a MAC or MII register, at least one NOP or other instruction must be executed.

The three MACON registers control specific MAC operations and packet configuration operations. They are shown in Register 18-4 through Register 18-6.

The MII registers are used to control the MIIM interface and serve as the communication channel with the PHY registers. They are shown in Register 18-7 and Register 18-8.

U-0	U-0	U-0	R-0	R/W-0	R/W-0	R/W-0	R/W-0
—			r	TXPAUS	RXPAUS	PASSALL	MARXEN
bit 7							bit 0

#### REGISTER 18-4: MACON1: MAC CONTROL REGISTER 1

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-5	Unimplemented: Read as '0'
bit 4	Reserved: Do not use
bit 3	TXPAUS: Pause Control Frame Transmission Enable bit
	<ul> <li>1 = Allow the MAC to transmit pause control frames (needed for flow control in full duplex)</li> <li>0 = Disallow pause frame transmissions</li> </ul>
bit 2	RXPAUS: Pause Control Frame Reception Enable bit
	<ul> <li>1 = Inhibit transmissions when pause control frames are received (normal operation)</li> <li>0 = Ignore pause control frames which are received</li> </ul>
bit 1	PASSALL: Pass All Received Frames Enable bit
	<ul> <li>1 = Control frames received by the MAC will be written into the receive buffer if not filtered out</li> <li>0 = Control frames will be discarded after being processed by the MAC (normal operation)</li> </ul>
bit 0	MARXEN: MAC Receive Enable bit
	<ul> <li>1 = Enable packets to be received by the MAC</li> <li>0 = Disable packet reception</li> </ul>

#### REGISTER 18-5: MACON3: MAC CONTROL REGISTER 3

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
PADCFG2	PADCFG1	PADCFG0	TXCRCEN	PHDREN	HFRMEN	FRMLNEN	FULDPX
bit 7						÷	bit
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, rea	d as '0'	
-n = Value at POR		'1' = Bit is set		'0' = Bit is cle		x = Bit is unkn	iown
bit 7-5	111 = All sho	ADCFG0: Auto ort frames are z tomatic padding	ero-padded to	64 bytes and		ill then be apper	nded
	matica a valid 100 = No aut 011 = All sho 010 = No aut 001 = All sho		es. If the frame ded. g of short fram ero-padded to g of short fram ero-padded to	e is not a VLAN es 64 bytes and es 60 bytes and	frame, it is pad a valid CRC is		
bit 4		ransmit CRC E	-				
						s of the PADCI	=G<2:0> bit
	0 = MAC doe		a CRC. The			C is appended. d if it is an inva	alid CRC, it
bit 3	PHDREN: Pro	oprietary Head	er Enable bit				
	calculatin	presented to the ng the CRC ietary header is			-	which is not use	ed when
bit 2		ige Frame Ena	-			,	
		ames and fram				smitted and rece ceived	eieved
bit 1	1 = The type frame siz		ransmitted an and mismatch	d received frai les are reporte	ed in the transm	I. If it represents hit/receive status	
bit 0	1 = MAC ope	C Full-Duplex erates in Full-D erates in Half-D	uplex mode, a			XMD (PHCON1 DPXMD	<8>)

#### REGISTER 18-6: MACON4: MAC CONTROL REGISTER 4

U-0	R/W-0	R/W-0	R/W-0	U-0	U-0	R-0	R-0
—	DEFER	r	r	—	—	r	r
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit,	read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7	Unimplemented: Read as '0'
bit 6	DEFER: Defer Transmission Enable bit (applies to half duplex only)
	<ul> <li>1 = When the medium is occupied, the MAC waits indefinitely for it to become free when attempting to transmit (use this setting for IEE 802.3 compliance)</li> <li>0 = When the medium is occupied, the MAC aborts the transmission after the excessive deferral limit is reached</li> </ul>
bit 5-4	Reserved: Maintain as '0'
bit 3-2	Unimplemented: Read as '0'
bit 1-0	Reserved: Maintain as '0'

#### **REGISTER 18-7: MICMD: MII COMMAND REGISTER**

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0	R/W-0
—	—	—	—	—	—	MIISCAN	MIIRD
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit,	read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-2	Unimplemented: Read as '0'
bit 1	MIISCAN: MII Scan Enable bit
	<ul> <li>1 = PHY register at MIREGADR is continuously read and the data is placed in the MIRD registers</li> <li>0 = No MII Management scan operation is in progress</li> </ul>
bit 0	<ul> <li>MIIRD: MII Read Enable bit</li> <li>1 = PHY register at MIREGADR is read once and the data is placed in the MIRD registers</li> <li>0 = No MII Management read operation is in progress</li> </ul>

#### REGISTER 18-8: MISTAT: MII STATUS REGISTER

U-0	U-0	U-0	U-0	R-0	R-0	R-0	R-0
—				r	NVALID	SCAN	BUSY
bit 7							bit 0

R = Readable bit W = Writable bit	U = Unimplemented bit,	read as '0'
-n = Value at POR '1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-4	Unimplemented: Read as '0'
bit 3	Reserved: Do not use
bit 2	<ul> <li>NVALID: MII Management Read Data Not Valid bit</li> <li>1 = The contents of the MIRD registers are not valid yet</li> <li>0 = The MII Management read cycle has completed and the MIRD registers have been updated</li> </ul>
bit 1	SCAN: MII Management Scan Operation bit
	<ul> <li>1 = MII Management scan operation is in progress</li> <li>0 = No MII Management scan operation is in progress</li> </ul>
bit 0	<ul> <li>BUSY: MII Management Busy bit</li> <li>1 = A PHY register is currently being read or written to. For internal synchronization, the hardware will delay setting this bit for two TCY following a firmware command which sets the MIISCAN or MIIRD bits, or writes to the MIWRH register.</li> <li>0 = The MII Management interface is Idle</li> </ul>

#### 18.2.5 PHY REGISTERS

The PHY registers provide configuration and control of the PHY module, as well as status information about its operation. All PHY registers are 16 bits in width.

PHY registers are accessed with a 5-bit address, for a total of 32 possible registers; of these, only 7 addresses are implemented. The implemented registers are listed in Table 18-3. The main PHY Control registers are described in Register 18-9 through Register 18-13. The other PHY Control and Status registers are described later in this chapter.

Unimplemented registers must never be written to; reading these locations will return indeterminate data. Within implemented registers, all reserved bit locations that are listed as writable must always be written with the value provided in the register description. When read, these reserved bits can be ignored.

Thy PHY registers are only accessible through the MII Management interface. They must not be read or written to until the PHY start-up timer has expired and the PHYRDY bit (ESTAT<0>) is set.

#### 18.2.5.1 PHSTAT Registers

The PHSTAT1 and PHSTAT2 registers contain read-only bits that show the current status of the PHY module's operations, particularly the conditions of the communications link to the rest of the network.

The PHSTAT1 register (Register 18-10) contains the LLSTAT bit; it clears and latches low if the physical layer link has gone down since the last read of the register. The application can periodically poll LLSTAT to determine exactly when the link fails. It may be particularly useful if the link change interrupt is not used.

The PHSTAT2 register (Register 18-12) contains status bits which report if the PHY module is linked to the network and whether or not it is transmitting or receiving.

#### 18.2.5.2 Accessing PHY Registers

As already mentioned, the PHY registers exist in a different memory space and are not directly accessible by the microcontroller. Instead, they are addressed through a special set of MII registers in the Ethernet SFR bank that implement a Media Independent Interface Management (MIIM).

Access is similar to that of the Ethernet buffer, but uses separate read and write buffers (MIRDH:MIRDL and MIWRH:MIWRL) and a 5-bit address register (MIREGADR). In addition, the MICMD and MISTAT registers are used to control read and write operations. To read from a PHY register:

- 1. Write the address of the PHY register to be read into the MIREGADR register.
- Set the MIIRD bit (MICMD<0>). The read operation begins and the BUSY bit (MISTAT<0>) is set after two Tcy.
- Wait 10.24 μs, then poll the BUSY bit to be certain that the operation is complete. When the MAC has obtained the register contents, the BUSY bit will clear itself. While BUSY is set, the user application should not start any MIISCAN operations or write to the MIWRH register.
- 4. Clear the MIIRD bit.
- 5. Read the entire 16 bits of the PHY register from the MIRDL and MIRDH registers.

To write to a PHY register:

- 1. Write the address of the PHY register to be written into the MIREGADR register.
- 2. Write the lower 8 bits of data to write into the MIWRL register.
- Write the upper 8 bits of data to write into the MIWRH register. Writing to this register automatically begins the MII transaction, so it must be written to after MIWRL. The BUSY bit is set automatically after two Tcy.

The PHY register is written after the MII operation completes, which takes 10.24  $\mu$ s. When the write operation has completed, the BUSY bit will clear itself. The application should not start any MII scan or read operations while busy.

When a PHY register is written to, the entire 16 bits is written at once; selective bit and/or byte writes are not implemented. If it is necessary to reprogram only select bits in the register, the controller must first read the PHY register, modify the resulting data and then write the data back to the PHY register. The MAC can also be configured to perform automatic back-to-back read operations on a PHY register. To perform this scan operation:

- 1. Write the address of the PHY register to be scanned into the MIREGADR register.
- Set the MIISCAN bit (MICMD<1>). The scan operation begins and the BUSY bit is set after two Tcy.

After MIISCAN is set, the NVALID (MISTAT<2>), SCAN and BUSY bits are also set. The first read operation will complete after 10.24  $\mu$ s. Subsequent reads will be done and the MIRDL and MIRDH registers will be continuously updated automatically at the same interval until the operation is cancelled. The NVALID bit may be polled to determine when the first read operation is complete.

There is no status information which can be used to determine when the MIRD registers are updated. Since only one MII register can be read at a time, it must not be assumed that the values of MIRDL and MIRDH were read from the PHY at exactly the same time during a scan operation.

MIISCAN should remain set as long as the scan operation is desired. The BUSY and SCAN bits are automatically cleared after MIISCAN is set to '0' and the last read sequence is completed. MIREGADR should not be updated while MIISCAN is set.

Starting new PHY operations, such as a read operation or writing to the MIWRH register, must not be done while a scan is underway. The operation can be cancelled by clearing the MIISCAN bit and then polling the BUSY bit. New operations may be started after the BUSY bit is cleared.

TAB	TABLE 18-3: PIC18F97J60 FAMILY PHY REG	PIC	18F97J(	60 FAN	ЛГҮ РН	IY REG	<b>ISTER SUMMARY</b>	SUMM/	<b>ARY</b>									
Addr	Addr Name	Bit 15	Bit 14 Bit 13 Bit 12	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	<b>Reset Values</b>
400	PHCON1	-	-	I	I	-	-		PDPXMD	L	1		1	1	1	I		00-0000
01h	PHSTAT1			I	L	L	I		I	Ι		Ι	I	I	LLSTAT	L	I	1 100-
10h	PHCON2		FRCLNK	г	L	L	r	L	HDLDIS	L	L	r	RXAPDIS	L	r	L	L	-000 0000 0000 0000
11h	PHSTAT2			TXSTAT	TXSTAT RXSTAT COLSTAT	COLSTAT	LSTAT	г		Ι	I	r	Ι		Ι	Ι		0×00 00
12h	PHIE	L	L	L	L	L	L	L	L	L	r	r	PLNKIE	г	L	PGEIE	L	хххх хххх хх00 хх00
13h	PHIR	L	L	L	L	L	L	Ŀ	L	L	L	L	PLNKIF	L	PGIF	L	<u>ـ</u>	XXXX XXXX XX00 00x0
14h	PHLCON	-	L	L	-	LACFG3	LACFG2	LACFG1	LACFG0	LBCFG3	LBCFG2	LBCFG1	LACFG2 LACFG1 LACFG0 LBCFG3 LBCFG2 LBCFG1 LBCFG0 LFRQ1 LFRQ0 STRCH	LFRQ1	LFRQ0	STRCH	-	0011 0100 0010 001×

Legend: x = unknown, u = unchanged, - = unimplemented, read as '0', r = reserved, do not modify. Shaded cells are unimplemented, read as '0'.

# PIC18F97J60 FAMILY

#### REGISTER 18-9: PHCON1: PHY CONTROL REGISTER 1

R/W-0	R/W-0	U-0	U-0	R/W-0	R/W-0	U-0	R/W-0
r	r	—	—	r	r	—	PDPXMD
bit 15							bit 8
R/W-0	U-0	U-0	U-0	U-0	U-0	U-0	U-0
r							
bit 7							bit 0
Legend:							
R = Readab	le bit	W = Writable	bit	U = Unimplen	nented bit, read	l as '0'	
-n = Value a	POR	'1' = Bit is set		'0' = Bit is clea	ared	x = Bit is unkr	nown
bit 15-14	Reserved: W	rite as '0'					
bit 13-12	Unimplemen	ted: Read as '	) <b>'</b>				
bit 11-10	Reserved: W	/rite as '0'					
bit 9	Unimplemen	ted: Read as '	כ'				
bit 8	PDPXMD: PH	HY Duplex Mod	e bit				
		rates in Full-Du		plication must	also set FULDI	PX (MACON3<	0>)
	0 = PHY ope	rates in Half-D	uplex mode, ap	oplication must	also clear FUL	DPX	
bit 7	Reserved: M	aintain as '0'					
bit 6-0	Unimplemen	ted: Read as '	o'				

#### REGISTER 18-10: PHSTAT1: PHYSICAL LAYER STATUS REGISTER 1

U-0	U-0	U-0	R-1	R-1	U-0	U-0	U-0
—	—	—	r	r	—	—	—
bit 15							bit 8

U-0	U-0	U-0	U-0	U-0	R/LL-0	R/LH-0	U-0
—	—	—	—	—	LLSTAT	r	—
bit 7							bit 0

Legend:	'1' = Bit is set		
R = Read-only bit	'0' = Bit is cleared	U = Unimplemented bit, read	d as '0'
-n = Value at POR	R/L = Read-only latch bit	LL = Bit latches low	LH = Bit latches high

bit 15-13	Unimplemented: Read as '0'
-----------	----------------------------

bit 12-11 **Reserved:** Read as '1'

bit 10-3 Unimplemented: Read as '0'

- bit 2 LLSTAT: PHY Latching Link Status bit
  - 1 = Link is up and has been up continously since PHSTAT1 was last read
  - 0 = Link is down or was down for a period since PHSTAT1 was last read
- bit 1 Reserved: Ignore on read
- bit 0 Unimplemented: Read as '0'

#### REGISTER 18-11: PHCON2: PHY CONTROL REGISTER 2

U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
	FRCLNK	r	r	r	r	r	HDLDIS
bit 15	·						bit 8
R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
r	r	r	RXAPDIS	r	r	r	r
bit 7							bit 0
Legend:							
R = Readab	ole bit	W = Writable	bit	U = Unimplen	nented bit, rea	d as '0'	
-n = Value a	at POR	'1' = Bit is se	t	'0' = Bit is clea	ared	x = Bit is unkr	nown
bit 15	Unimplemen	ted: Read as '	0'				
bit 14	FRCLNK: PH	Y Force Linku	p bit				
						always allowed partner is attach	
bit 13-9	Reserved: W	rite as '0'					
bit 8	HDLDIS: PHY	/ Half-Duplex	Loopback Disal	ble bit			
	1 = Normal P	•					
	0 = Reserved						
bit 7-5	Reserved: W						
bit 4	RXAPDIS: R)	•	ing mode bit				
	1 = Normal o 0 = Reserved						
bit 3-0	Reserved: W	rite as '0'					
	mproper Etherne Always initialize tl					d, which is the	Reset default.

#### REGISTER 18-12: PHSTAT2: PHYSICAL LAYER STATUS REGISTER 2

U-0	U-0	R-0	R-0	R-0	R-0	R-x	U-0
_	_	TXSTAT	RXSTAT	COLSTAT	LSTAT	r	_
oit 15							bit
U-0	U-0	R-0	U-0	U-0	U-0	U-0	U-0
_	—	r	_	—	—		—
bit 7							bit
Legend:							
R = Readab	le bit	W = Writable	oit	U = Unimplem		d as '0'	
-n = Value a	It POR	'1' = Bit is set		'0' = Bit is clea	red	x = Bit is unkn	own
bit 12	<b>RXSTAT:</b> PH 1 = PHY is r	not transmitting Y Receive Statu eceiving data not receiving dat	ıs bit				
bit 11	1 = A collisio	HY Collision States on is occuring (For the second se	PHY is both tra	insmitting and re	ceiving while	in Half-Duplex r	node)
		Collision Status	bit				
bit 10	1 = Link is u 0 = Link is d						
oit 10 oit 9	0 = Link is d						
pit 9	୦ = Link is d <b>Reserved:</b> Iଣ୍	own	)'				
	0 = Link is d Reserved: lલ્ Unimpleme	own gnore on read	)'				

## REGISTER 18-13: PHLCON: PHY MODULE LED CONTROL REGISTER

R/W-0	R/W-0	R/W-1	R/W-1	R/W-0	R/W-1	R/W-0	R/W-0
r	r	r	r	LACFG3	LACFG2	LACFG1	LACFG0
bit 15					·		bit 8
R/W-0	R/W-0	R/W-1	R/W-0	R/W-0	R/W-0	R/W-1	R/W-x
LBCFG3	LBCFG2	LBCFG1	LBCFG0	LFRQ1	LFRQ0	STRCH	r
bit 7							bit 0
Legend:							
R = Readable	e bit	W = Writable b	bit	U = Unimplem	ented bit, read	as '0'	
-n = Value at I	POR	'1' = Bit is set		'0' = Bit is clea	,	x = Bit is unkno	own
bit 15-14	Reserved: Wr	rite as '0'					
bit 13-12	Reserved: Wr	rite as '1'					
bit 11-8	LACFG3:LAC	FG0: LEDA Co	nfiguration bits				
	0000 = Reser		<i></i>				
		y transmit activi v receive activit					
		y collision activi					
	0100 <b>= Displa</b>	y link status	,				
		y duplex status					
	0110 = Reser	ved ly transmit and r	eceive activity (	stretchable)			
	1000 <b>= On</b>	ly transmit and t		stretenable)			
	1001 <b>= Off</b>						
	1010 = Blink f						
	1011 = Blink s	siow iy link status and	ł receive activity	v (always stretch	hed)		
		y link status and					
	111x = Reser	ved			. ,		
bit 7-4	LBCFG3:LBC	FG0: LEDB Co	nfiguration bits				
	0000 = Reser		t. (stastala a b.l.a.)				
		y transmit activi v receive activit					
		y collision activi					
	0100 <b>= Displa</b>	y link status	,				
		y duplex status					
	0110 = Reser	veo ly transmit and r	eceive activity (	stretchable)			
	1000 <b>= On</b>	ly danomic and r					
	1001 <b>= Off</b>						
	1010 = Blink f						
	1011 = Blink s 1100 = Displa	iy link status and	d receive activity	v (alwavs stretcl	hed)		
		y link status and	-		,		
	111x = Reser	ved					
bit 3-2		0: LED Pulse S	tretch Time Cor	figuration bits (	see Table 18-1)		
	11 = Reserved	d .ED events by Ti	STROLL				
		ED events by T					
		ED events by T					
bit 1	STRCH: LED	Pulse Stretching	g Enable bit				
						RQ1:LFRQ0 cor	figuration
		le LED events v	vill only be displ	ayed while they	are occurring		
bit 0	Reserved: Wr	rite as '0'					

## **18.3 Ethernet Interrupts**

The Ethernet module can generate multiple interrupt conditions. To accommodate all of these sources, the module has its own interrupt logic structure, similar to that of the microcontroller. Separate sets of registers are used to enable and flag different interrupt conditions.

The EIE register contains the individual interrupt enable bits for each source, while the EIR register contains the corresponding interrupt flag bits. When an interrupt occurs, the interrupt flag is set. If the interrupt is enabled in the EIE register, and the corresponding ETHIE global interrupt enable bit is set, the microcontroller's master Ethernet Interrupt Flag (ETHIF) is set, as appropriate (see Figure 18-6). Note: Except for the LINKIF interrupt flag, interrupt flag bits are set when an interrupt condition occurs, regardless of the state of its corresponding enable bit or the associated global enable bit. User software should ensure the appropriate interrupt flag bits are clear prior to enabling an interrupt. This feature allows for software polling.

#### 18.3.1 CONTROL INTERRUPT (ETHIE)

The four registers associated with the control interrupts are shown in Register 18-14 through Register 18-17.




FIGURE 18-6: ETHERNET MODULE INTERRUPT LOGIC

U-0	R/W-0	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0
	PKTIE	DMAIE		TXIE		TXERIE	RXERIE
bit 7	I KIL	DIVIAL		TAL		TXENIE	bit 0
							bit 0
Legend:							
R = Readab	le bit	W = Writable	bit	U = Unimpler	mented bit, read	d as '0'	
-n = Value a	t POR	'1' = Bit is se	t	'0' = Bit is cle		x = Bit is unkr	nown
bit 7	Unimplemen	ted: Read as	0'				
bit 6	PKTIE: Rece	ive Packet Per	nding Interrupt	Enable bit			
		eceive packet					
	0 = Disable r	eceive packet	pending interr	rupt			
bit 5	DMAIE: DMA	Interrupt Enal	ble bit				
	1 = Enable E						
		DMA interrupt					
bit 4		Status Change	-				
		nk change inte ink change inte	•	PHY			
bit 3	TXIE: Transm	•	mupt				
bit o		ransmit interru	ht				
		ransmit interru					
bit 2	Unimplemen	ted: Read as	0'				
bit 1	TXERIE: Trai	nsmit Error Inte	errupt Enable	bit			
	1 = Enable tr	ransmit error ir	iterrupt				
	0 = Disable t	ransmit error i	nterrupt				
bit 0	RXERIE: Red	ceive Error Inte	errupt Enable b	pit			
		eceive error int					
	0 = Disable r	eceive error in	terrupt				

#### REGISTER 18-14: EIE: ETHERNET INTERRUPT ENABLE REGISTER

# REGISTER 18-15: EIR: ETHERNET INTERRUPT REQUEST (FLAG) REGISTER

					,		
U-0	R-0	R/C-0	R-0	R/C-0	U-0	R/C-0	R/C-0
	PKTIF	DMAIF	LINKIF	TXIF	_	TXERIF	RXERIF
bit 7		• •					bit (
Legend:							
R = Readable	bit	C = Clearable	e bit	U = Unimpler	nented bit, rea	d as '0'	
-n = Value at P	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7	Unimplemer	nted: Read as '	0'				
bit 6	-	ive Packet Per		Flag bit			
			• ·	•	l packets; clea	ared only when	EPKTCNT is
	decreme	ented to 0 by se	etting PKTDE	C (ECON2<6>			
	0 = Receive	buffer is empty					
bit 5		A Interrupt Flag					
		py or checksum		as completed			
bit 4	LINKIF: Link	Change Interru	upt Flag bit				
				hanged; read F	PHIR register to	o clear	
	0 = Link stat	us has not cha	nged				
bit 3		nit Interrupt Fla	•				
		t request has e					
		mit interrupt is					
bit 2	-	nted: Read as '					
bit 1		nsmit Error Inte					
		nit error has oco					
		mit error has o					
bit 0		ceive Error Inte					
		t was aborted b ve error interru		is insufficient b	utter space, or	a buffer overrur	has occurre
			pris penulty				

#### REGISTER 18-16: PHIE: PHY INTERRUPT ENABLE REGISTER

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0			
r	r	r	r	r	r	r	r			
bit 15							bit 8			
R-0	R-0 R/W-0 R/W-0			R-0	R-0	R/W-0	R/W-0			
r	r	r	PLNKIE	r	r	PGEIE	r			
bit 7		•					bit 0			
Legend:										
R = Readable bit W = Writable bit				U = Unimplem	nented bit, read	d as '0'				
-n = Value a	at POR	'1' = Bit is set	:	'0' = Bit is cleared x = Bit is unknown						
bit 15-6	Reserved: W	rite as '0', igno	ore on read							
bit 5	Reserved: Ma									
bit 4	PLNKIE: PHY	/ Link Change	Interrupt Enab	le bit						
	1 = PHY link	change interru change interru	pt is enabled							
bit 3-2	Reserved: W	rite as '0', igno	ore on read							
bit 1		Global Interrup								
		rrupts are enal rrupts are disa								
bit 0	Reserved: Ma	Reserved: Maintain as '0'								

# REGISTER 18-17: PHIR: PHY INTERRUPT REQUEST (FLAG) REGISTER

R-x	R-x	R-x	R-x	R-x	R-x	R-x	R-x	
r	r	r	r	r	r	r	r	
bit 15							bit 8	
R-x	R-x	R-0	R/SC-0	R-0	R/SC-0	R-x	R-0	
r	r	r	PLNKIF	r	PGIF	r	r	
bit 7							bit 0	
Legend:								
R = Readable	e bit	SC = Self-cle	earing bit	U = Unimpler	mented bit, read	as '0'		
-n = Value at	-n = Value at POR '1' = Bit is set				'0' = Bit is cleared x = Bit is unknow			
bit 15-6	Reserved: Ig	nore on read						
bit 5	Reserved: Re	ead as '0'						
bit 4	PLNKIF: PHY	/ Link Change	Interrupt Flag I	bit				
					ad; resets to '0'	when read		
	0 = PHY link	status has not	changed since	PHIR was las	t read			
bit 3	Reserved: Re	ead as '0'						
bit 2	PGIF: PHY G	lobal Interrupt	Flag bit					
		ore enabled Pl interrupts have		ve occurred sin	ce PHIR was las	st read; resets to	oʻ0' when read	
L:1 4		nore on read						
bit 1								

#### 18.3.1.1 Receive Error Interrupt (RXERIF)

The receive error interrupt is used to indicate that a packet being received was aborted due to an error condition. Three errors are possible:

- 1. No buffer space is available to store the incoming packet (buffer overflow);
- Receiving another packet would cause the EPKTCNT counter to overflow, because it already contains the value 255; or
- 3. The Ethernet RX hardware was not allocated enough memory bandwidth to write the incoming data to the buffer.

When a packet is being received and the receive error occurs, the packet being received will be aborted (permanently lost) and the RXERIF bit will be set to '1'. Once set, RXERIF can only be cleared by firmware or by a Reset condition. If the receive error interrupt and Ethernet interrupt are enabled (both RXERIE and ETHIE are set), an Ethernet interrupt is generated. If the receive error interrupt is not enabled (either RXERIE or ETHIE are cleared), the application may poll RXERIF and take appropriate action.

Normally, upon the first two receive error conditions (buffer overflow or potential EPKTCNT overflow), the application would process any packets pending from the receive buffer and then make additional room for future packets by advancing the ERXRDPT registers (low byte first) and decrementing the EPKTCNT register. See Section 18.5.3.3 "Freeing Receive Buffer Space" for more information on processing packets. Once processed, the application should clear the RXERIF bit.

The third condition (insufficient RX memory bandwidth) can be identified by checking if the BUFER bit (ESTAT<6>) has been set. Memory access errors that set BUFER are generally transient in nature, and do not require run-time resolution. Adjustments to the application and its allocation of buffer memory bandwidth may be necessary if BUFER errors are frequent or persistent.

#### 18.3.1.2 Transmit Error Interrupt (TXERIF)

The transmit error interrupt is used to indicate that a transmit abort has occurred. An abort can occur because of any of the following conditions:

- 1. More than 15 collisions occurred while attempting to transmit a given packet.
- 2. A late collision (collision after 64 bytes of a packet had been transmitted) has occurred.
- The transmission was unable to gain an opportunity to transmit the packet because the medium was constantly occupied for too long. The deferral limit was reached and the DEFER bit (MACON4<6>) was clear.

- An attempt to transmit a packet larger than the maximum frame length defined by the MAMXFL registers was made without setting the HFRMEN bit (MACON3<2>) or per-packet POVERRIDE and PHUGEEN bits.
- 5. The Ethernet buffer did not have enough memory bandwidth to maintain the required 10 Mbit/s transfer rate (buffer underrun).

Upon any of these conditions, the TXERIF flag is set to '1'. Once set, it can only be cleared by firmware or by a Reset condition. If the transmit error interrupt is enabled (TXERIE and ETHIE are both set), an Ethernet interrupt is generated. If the transmit error interrupt is not enabled (either TXERIE or ETHIE is cleared), the application may poll TXERIF and take appropriate action. Once the interrupt is processed, the flag bit should be cleared.

After a transmit abort, the TXRTS bit (ECON1<3>) will be cleared, the TXABRT bit (ESTAT<1>) becomes set and the transmit status vector will be written at the ETXND registers + 1. The MAC will not automatically attempt to retransmit the packet. The application may wish to read the transmit status vector and BUFER bit to determine the cause of the abort. After determining the problem and solution, the application should clear the BUFER (if set) and TXABRT bits so that future aborts can be detected accurately.

In Full-Duplex mode, conditions 4 and 5 are the only ones that should cause this interrupt. Condition 5 can be further distinguished as it also sets the BUFER bit. Collisions and other problems related to sharing the network are not possible on full-duplex networks. The conditions which cause the transmit error interrupt meet the requirements of the transmit interrupt. As a result, when this interrupt occurs, TXIF will also be simultaneously set.

#### 18.3.1.3 Transmit Interrupt (TXIF)

The transmit interrupt is used to indicate that the requested packet transmission has ended (the TXRTS bit has transitioned from '1' to '0'). Upon transmission completion, abort, or transmission cancellation by the application, the TXIF flag will be set to '1'. If the application did not clear the TXRTS bit, and the TXABRT bit is not set, the packet was successfully transmitted. Once TXIF is set, it can only be cleared in software or by a Reset condition. If the transmit interrupt is generated. If the transmit interrupt is not enabled (either TXIE or ETHIE is cleared), the application may poll the TXIF bit and take appropriate action.

#### 18.3.1.4 Link Change Interrupt (LINKIF)

The LINKIF indicates that the link status has changed. The actual current link status can be obtained from the LLSTAT (PHSTAT1<2>) or LSTAT (PHSTAT2<10>) bits (see Register 18-10 and Register 18-12). Unlike other interrupt sources, the link status change interrupt is created in the integrated PHY module; additional steps must be taken to enable it.

By Reset default, LINKIF is never set for any reason. To receive it, both the PLNKIE and PGEIE bits must be set. When the interrupt is enabled, the LINKIF bit will shadow the contents of the PGIF bit. The PHY only supports one interrupt, so the PGIF bit will always be the same as the PLNKIF bit (when both PHY enable bits are set).

Once LINKIF is set, it can only be cleared in software or by a Reset. If the link change interrupt is enabled (LINKIE, PLNKIE, PGEIE and ETHIE are all set), an interrupt is generated. If the link change interrupt is not enabled (LINKIE, PLNKIE, PGEIE or ETHIE are cleared), the user application may poll the PLNKIF flag and take appropriate action.

The LINKIF bit is read-only. Because reading PHY registers requires a non-negligible period of time, the application may instead set PLNKIE and PGEIE, then poll the LINKIF flag bit. Performing an MII read on the PHIR register will clear the LINKIF, PGIF and PLNKIF bits automatically and allow for future link status change interrupts. See **Section 18.2.5 "PHY Registers"** for information on accessing the PHY registers.

#### 18.3.1.5 DMA Interrupt (DMAIF)

The DMA interrupt indicates that the DMA module has completed its memory copy or checksum calculation (the DMAST bit has transitioned from '1' to '0'). Additionally, this interrupt will be caused if the application cancels a DMA operation by manually clearing the DMAST bit. Once set, DMAIF can only be cleared by the firmware or by a Reset condition. If the DMA interrupt is enabled, an Ethernet interrupt is generated. If the DMA interrupt is not enabled, the user application may poll the DMAIF flag status and take appropriate action. Once processed, the flag bit should be cleared.

#### 18.3.1.6 Receive Packet Pending Interrupt (PKTIF)

The receive packet pending interrupt is used to indicate the presence of one or more data packets in the receive buffer and to provide a notification means for the arrival of new packets. When the receive buffer has at least one packet in it, the PKTIF flag bit is set. In other words, this interrupt flag will be set any time the Ethernet Packet Count register (EPKTCNT) is non-zero. When the receive packet pending interrupt is enabled (both PKTIE and ETHIE are set), an Ethernet interrupt is generated whenever a new packet is successfully received and written into the receive buffer. If the receive packet pending interrupt is not enabled (either PKTIE or ETHIE is cleared), the user application may poll the PKTIF bit and take appropriate action.

The PKTIF bit can only be cleared indirectly in software, by decrementing the EPKTCNT register to '0', or by a Reset condition. See **Section 18.5.3 "Receiving Packets"** for more information about clearing the EPKTCNT register. When the last data packet in the receive buffer is processed, EPKTCNT becomes zero and the PKTIF bit is automatically cleared.

# 18.3.2 ETHERNET INTERRUPTS AND WAKE-ON-LAN

The Ethernet interrupt structure implements a version of Wake-on-LAN, also called Remote Wake-up, using a Magic Packet data packet. This allows the application to conserve power in Idle mode, and then return to full-power operation only when a specific wake-up packet is received.

For Remote Wake-up to work, the Ethernet module must remain enabled at all times. It also necessary to configure the receive filters to select for Magic Packets. For more information on filter configuration, see **Section 18.8 "Receive Filters"**.

To configure the microcontroller for Remote Wake-up:

- With the Ethernet module enabled and in normal operating configuration, enable the CRC post-filter and Magic Packets filter (ERXFCON<5,3> = 1).
- 2. Finish processing any pending packets in the Ethernet buffer.
- 3. Enable Ethernet interrupts at the microcontroller level (PIE2<5> = 1), and the receive packet pending interrupt at the module level (EIE<6> = 1).
- Place the microcontroller in PRI\_IDLE mode (with the primary clock source selected and OSCCON<7> = 1, execute the SLEEP instruction).

In this configuration, the receipt of a Magic Packet data packet will cause a receive packet pending interrupt; this in turn will cause the microcontroller to wake-up from the interrupt.

# 18.4 Module Initialization

Before the Ethernet module can be used to transmit and receive packets, certain device settings must be initialized. Depending on the application, some configuration options may need to be changed. Normally, these tasks may be accomplished once after Reset and do not need to be changed thereafter.

Before any other configuration actions are taken, it is recommended that the module be enabled by setting the ETHEN bit (ECON2<5>). This reduces the Idle time that might otherwise result while waiting for the PHYRDY flag to become set.

#### 18.4.1 RECEIVE BUFFER

Before receiving any packets, the receive buffer must be initialized by setting the ERXST and ERXND Pointers. All memory between and including the ERXST and ERXND addresses will be dedicated to the receive hardware. The ERXST Pointers must be programmed with an even address while the ERXND Pointers must be programmed with an odd address.

Applications expecting large amounts of data and frequent packet delivery may wish to allocate most of the memory as the receive buffer. Applications that may need to save older packets, or have several packets ready for transmission, should allocate less memory.

When programming the ERXST or ERXND Pointers, the ERXWRPT Pointer registers will automatically be updated with the value in the ERXST registers. The address in the ERXWRPT registers will be used as the starting location when the receive hardware begins writing received data. When the ERXST and ERXND Pointers are initialized, the ERXRDPT registers should additionally be programmed with the value of the ERXND registers. To program the ERXRDPT registers, write to ERXRDPTL first, followed by ERXRDPTH. See **Section 18.5.3.3 "Freeing Receive Buffer Space"** for more information.

#### 18.4.2 TRANSMISSION BUFFER

All memory which is not used by the receive buffer is considered to be transmission buffer. Data which is to be transmitted should be written into any unused space. After a packet is transmitted, however, the hardware will write a 7-byte status vector into memory after the last byte in the packet. Therefore, the application should leave at least 7 bytes between each packet and the beginning of the receive buffer.

#### 18.4.3 RECEIVE FILTERS

The appropriate receive filters should be enabled or disabled by writing to the ERXFCON register. See **Section 18.8 "Receive Filters"** for information on how to configure it.

# 18.4.4 WAITING FOR THE PHY START-UP TIMER

If the initialization procedure is being executed immediately after enabling the module (setting the ETHEN bit to '1'), the PHYRDY bit should be polled to make certain that enough time (1 ms) has elapsed before proceeding to modify the PHY registers. For more information on the PHY start-up timer, see **Section 18.1.3.1 "Start-up Timer"**.

#### 18.4.5 MAC INITIALIZATION SETTINGS

Several of the MAC registers require configuration during initialization. This only needs to be done once during initialization; the order of programming is unimportant.

- Set the MARXEN bit (MACON1<0>) to enable the MAC to receive frames. If using full duplex, most applications should also set TXPAUS and RXPAUS to allow IEEE defined flow control to function.
- 2. Configure the PADCFG<2:0>, TXCRCEN and FULDPX bits in the MACON3 register. Most applications should enable automatic padding to at least 60 bytes and always append a valid CRC. For convenience, many applications may wish to set the FRMLNEN bit as well to enable frame length status reporting. The FULDPX bit should be set if the application will be connected to a full-duplex configured remote node; otherwise leave it clear.
- Configure the bits in MACON4. For maintaining compliance with IEEE 802.3, be certain to set the DEFER bit (MACON4<6>).
- Program the MAMXFL registers with the maximum frame length to be permitted to be received or transmitted. Normal network nodes are designed to handle packets that are 1518 bytes or less; larger packets are not supported by IEEE 802.3.
- Configure the MAC Back-to-Back Inter-Packet Gap register, MABBIPG, with 15h (when Full-Duplex mode is used) or 12h (when Half-Duplex mode is used). Refer to Register 18-18 for a more detailed description of configuring the inter-packet gap.
- 6. Configure the MAC Non Back-to-Back Inter-Packet Gap Low Byte register, MAIPGL, with 12h.
- 7. If half duplex is used, configure the MAC Non Back-to-Back Inter-Packet Gap High Byte register, MAIPGH, with 0Ch.
- 8. Program the local MAC address into the MAADR1:MAADR6 registers.

U-0	R/W-0						
—	BBIPG6	BBIPG5	BBIPG4	BBIPG3	BBIPG2	BBIPG1	BBIPG0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit,	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7 Unimplemented: Read as '0'

bit 6-0 BBIPG6:BBIPG0: Back-to-Back Inter-Packet Gap Delay Time bits

When FULDPX (MACON3<0>) = 1:

Nibble time offset delay between the end of one transmission and the beginning of the next in a back-to-back sequence. The register value should be programmed to the desired period in nibble times minus 3. The recommended setting is 15h which represents the minimum IEEE specified Inter-Packet Gap (IPG) of 9.6  $\mu$ s.

When FULDPX (MACON3<0>) = 0:

Nibble time offset delay between the end of one transmission and the beginning of the next in a back-to-back sequence. The register value should be programmed to the desired period in nibble times minus 6. The recommended setting is 12h which represents the minimum IEEE specified Inter-Packet Gap (IPG) of 9.6  $\mu$ s.

#### 18.4.6 PHY INITIALIZATION SETTINGS

Depending on the application, bits in three of the PHY module's registers may also require configuration.

The PDPXMD bit (PHCON1<8>) controls the PHY half/full-duplex configuration. The application must program the bit properly, along with the FULDPX bit (MACON3<0>).

The HDLDIS bit (PHCON2<8>) disables automatic loopback of data. For proper operation, always set both HDLDIS and RXAPDIS (PHCON2<4>).

The PHY register, PHLCON (Register 18-13), controls the outputs of LEDA and LEDB. If an application requires a LED configuration other than the default, alter this register to match the new requirements. The settings for LED operation are discussed in **Section 18.1.2 "LED Configuration"**.

#### 18.4.7 DISABLING THE ETHERNET MODULE

There may be circumstances during which the Ethernet module is not needed for prolonged periods. For example, in situations where the application only needs to transmit or receive Ethernet packets on the occurrence of a particular event. In these cases, the module can be selectively powered down.

To selectively disable the module:

- 1. Turn off packet reception by clearing the RXEN bit.
- Wait for any in-progress packets to finish being received by polling the RXBUSY bit (ESTAT<2>). This bit should be clear before proceeding.
- Wait for any current transmissions to end by confirming that the TXRTS bit (ECON1<3>) is clear.
- Clear the ETHEN bit. This removes power and clock sources from the module, and makes the PHY registers inaccessible. The PHYRDY bit is also cleared automatically.

## 18.5 Transmitting and Receiving Data

The Ethernet protocol (IEEE Standard 802.3) provides an extremely detailed description of the 10 Mbps, frame-based serial communications system. Before discussing the actual use of the Ethernet module, a brief review of the structure of a typical Ethernet data frame may be appropriate. It is assumed that users already have some familiarity with IEEE 802.3. Those requiring more information should refer to the official standard, or other Ethernet reference texts, for a more comprehensive explanation.

#### 18.5.1 PACKET FORMAT

Normal IEEE 802.3 compliant Ethernet frames are between 64 and 1518 bytes long. They are made up of five or six different fields: a destination MAC address, a source MAC address, a type/length field, data payload, an optional padding field and a Cyclic Redundancy Check (CRC). Additionally, when transmitted on the Ethernet medium, a 7-byte preamble field and Start-of-Frame delimiter byte are appended to the beginning of the Ethernet packet. Thus, traffic seen on the twisted-pair cabling will appear as shown in Figure 18-7.

#### 18.5.1.1 Preamble/Start-of-Frame Delimiter

When transmitting and receiving data with the Ethernet module, the preamble and Start-of-Frame delimiter bytes are automatically generated, or stripped from the packets, when they are transmitted or received. It can also automatically generate CRC fields and padding as needed on transmission, and verify CRC data on reception. The user application does not need to create or process these fields, or manually verify CRC data. However, the padding and CRC fields are written into the receive buffer when packets arrive, so they may be evaluated by the user application as needed.




FIGURE 18-7: ETHERNET PACKET FORMAT

#### 18.5.1.2 Destination Address

The destination address field is a 6-byte field filled with the MAC address of the device that the packet is directed to. If the Least Significant bit in the first byte of the MAC address is set, the address is a Multicast destination. For example, 01-00-00-00-F0-00 and 33-45-67-89-AB-CD are Multicast addresses, while 00-00-00-F0-00 and 32-45-67-89-AB-CD are not.

Packets with Multicast destination addresses are designed to arrive and be important to a selected group of Ethernet nodes. If the destination address field is the reserved Multicast address, FF-FF-FF-FF-FF, the packet is a Broadcast packet and it will be directed to everyone sharing the network. If the Least Significant bit in the first byte of the MAC address is clear, the address is a Unicast address and will be designed for usage by only the addressed node.

The Ethernet module incorporates receive filters which can be used to discard or accept packets with Multicast, Broadcast and/or Unicast destination addresses. When transmitting packets, the application is responsible for writing the desired destination address into the transmit buffer.

#### 18.5.1.3 Source Address

The source address field is a 6-byte field filled with the MAC address of the node which created the Ethernet packet. Users of the Ethernet module must generate a unique MAC address for each and every microcontroller used.

MAC addresses consist of two portions. The first three bytes are known as the Organizationally Unique Identifier (OUI). OUIs are distributed by the IEEE. The last three bytes are address bytes at the discretion of the company that purchased the OUI.

When transmitting packets, the assigned source MAC address must be written into the transmit buffer by the application. The module will not automatically transmit the contents of the MAADR registers which are used for the Unicast receive filter.

#### 18.5.1.4 Type/Length

The type/length field is a 2-byte field which defines which protocol the following packet data belongs to. Alternately, if the field is filled with the contents of 05DCh (1500) or any smaller number, the field is considered a length field, and it specifies the amount of non-padding data which follows in the data field. Users implementing proprietary networks may choose to treat this field as a length field, while applications implementing protocols such as the Internet Protocol (IP), or Address Resolution Protocol (ARP), should program this field with the appropriate type defined by the protocol's specification when transmitting packets.

## 18.5.1.5 Data

The data field is a variable length field anywhere from 0 to 1500 bytes. Larger data packets will violate Ethernet standards and will be dropped by most Ethernet nodes. The Ethernet module, however, is capable of transmitting and receiving larger packets when the Huge Frame Enable bit, HFRMEN, is set (MACON3<2> = 1).

#### 18.5.1.6 Padding

The padding field is a variable length field added to meet IEEE 802.3 specification requirements when small data payloads are used. The destination, source, type, data and padding of an Ethernet packet must be no smaller than 60 bytes. Adding the required 4-byte CRC field, packets must be no smaller than 64 bytes. If the data field is less than 46 bytes long, a padding field is required.

When transmitting packets, the Ethernet module automatically generates zero-padding if the PADCFG2:PADCFG0 bits (MACON3<7:5>) are configured for this. Otherwise, the user application will need to add any padding to the packet before transmitting it. The module will not prevent the transmission of undersized packets should the application command such an action.

When receiving packets, the module automatically rejects packets which are less than 18 bytes. All packets, 18 bytes and larger, will be subject to the standard receive filtering criteria and may be accepted as normal traffic. Since the module only rejects packets smaller than 18 bytes, it is important that the firmware check the length of every received packet and reject packets which are smaller than 64 bytes to meet IEEE 802.3 specification requirements.

### 18.5.1.7 CRC

The CRC field is a 4-byte field which contains an industry standard, 32-bit CRC, calculated with the data from the destination, source, type, data and padding fields. It provides a way of detecting corrupted Ethernet frames, as well as junk data fragments resulting from packet collisions or another host's aborted transmissions.

When receiving packets, the Ethernet module will check the CRC of each incoming packet. If the CRCEN bit is set, packets with invalid CRCs will automatically be discarded. If CRCEN is clear and the packet meets all other receive filtering criteria, the packet will be written into the receive buffer and the application will be able to determine if the CRC was valid by reading the receive status vector (see Section 18.5.3 "Receiving Packets").

When transmitting packets, the module automatically generates a valid CRC and transmits it if the PADCFG2:PADCFG0 bits are configured for this. Otherwise, the user application must generate the CRC and place it in the transmit buffer. Given the complexity of calculating a CRC, it is highly recommended to allow the module to automatically calculate and include the CRC.

#### 18.5.2 TRANSMITTING PACKETS

The Ethernet module's MAC will automatically generate the preamble and Start-of-Frame (SOF) delimiter fields when transmitting. Additionally, the MAC can generate any padding (if needed) and the CRC if configured to do so. The application must generate and write all other frame fields into the buffer memory for transmission.

In addition, the Ethernet module requires a single per-packet control byte to precede the packet for transmission. The control byte is organized as shown in Figure 18-8. Before transmitting packets, the MAC registers, which alter the transmission characteristics, should be initialized as documented in **Section 18.4 "Module Initialization"**.

#### FIGURE 18-8: FORMAT FOR PER-PACKET CONTROL BYTES

	<u> </u>			PHUGEEN	PPADN	PCRCEN	POVERRIDE						
bit 7							bit C						
bit 7-4	Unimploment	od: Dood oo	'o'										
	-	Unimplemented: Read as '0'											
bit 3	PHUGEEN: P		ige ⊢rame Ena	DIE DIT									
	When POVER		omitted in who										
			smitted in who	r of bytes speci	fied by the MA	MXEL registe	rs If the nacke						
				ill be aborted a									
	When POVER	RIDE = 0:											
	This bit is igno	red.											
bit 2	PPADN: Per-F	acket Paddi	ng Enable bit										
	When POVER	RIDE = 1:											
				bytes if it is les		es							
	•		smitted withou	t adding any pa	adding bytes								
	When POVER												
	This bit is igno												
bit 1	PCRCEN: Per		C Enable bit										
	When POVER			4 la l 4 - 4 la - <b>6</b>									
				tached to the fr bytes of the fra		ecked for vali	idity as a CRC						
	When POVER			bytes of the fra									
	This bit is igno												
bit 0	POVERRIDE:	Per-Packet	Override bit										
	1 = The value MACON3	s of PCRCE	EN, PPADN an	d PHUGEEN	will override t	he configurat	ion defined by						
			o			will be transn							

An example of how the entire assembled transmit packet looks in memory is shown in Figure 18-9. To construct and transmit a packet in this fashion:

- 1. Set the ETXST Pointers to an appropriate unused location in the buffer. This will be the location of the per-packet control byte. In the example, it would be 0120h. It is recommended that an even address be used for the ETXST Pointers.
- 2. Using EDATA and the EWRPT registers, sequentially write the packet data to the Ethernet buffer. In order, write the data for the per-packet control byte, the destination address, the source MAC address, the type/length and the data payload.
- 3. Set the ETXND Pointers to point to the last byte in the data payload. In the example, it would be programmed to 0156h.
- Clear the TXIF flag bit (EIR<3>), and set the TXIE (EIE<3>) and ETHIE bits to enable an interrupt when done (if desired).
- 5. Start the transmission process by setting the TXRTS bit (ECON1<3>).

If a DMA operation was in progress while the TXRTS bit was set, the module will wait until the DMA operation is complete before attempting to transmit the packet. This possible delay is required because the DMA and transmission engine share the same memory arbiter channel. Similarly, if the DMAST bit is set after TXRTS is already set, the DMA will wait until the TXRTS bit becomes clear before doing anything.

While the transmission is in progress, the ETXST and ETXND Pointers should not be modified. If it is necessary to cancel the transmission, clear the TXRTS bit.

When the packet is finished transmitting, or was aborted due to an error/cancellation, several things occur:

- The TXRTS bit is cleared.
- A 7-byte transmit status vector is written to the buffer at the location pointed to by the ETXND Pointers + 1.
- · The TXIF flag is set
- An interrupt will be generated (if enabled)
- The ETXST and ETXND Pointers will not be modified.

To check if the packet was successfully transmitted, read the TXABRT bit. If it has been set, poll the BUFER bit in addition to the various fields in the transmit status vector to determine the cause. The transmit status vector is organized as shown in Table 18-4. Multi-byte fields are written in little-endian format.

Buffer Pointers	Address	Memory	Description			
ETXST = 0120h	0120h	0Eh	Control	PHUGEEN, PPADN, PCRCEN and POVERRIDE		
	0121h	data[1]	<u> </u>	FURGEN allu FUVERRIDE		
	0122h	data[2]				
			Data Packet 🛛 >	Destination Address, Source Address, Type/Length and Data		
ETXND = 0156h	0156h	data[m]				
	0157h	tsv[7:0]				
	0158h	tsv[15:8]				
	0159h	tsv[23:16]		Obstant Marshare		
	015Ah	tsv[31:24]	Status Vector	Status Vector Written by the Hardware		
	015Bh	tsv[39:32]				
	015Ch	tsv[47:40]				
	015Dh	tsv[55:48]				
	015Eh		Ì	Start of the Next Packet		

### FIGURE 18-9: SAMPLE TRANSMIT PACKET LAYOUT

Bit	Field	Description
55-52	Zero	0
51	Transmit VLAN Tagged Frame	Frame's length/type field contained 8100h which is the VLAN protocol identifier.
50	Backpressure Applied	Reserved, do not use.
49	Transmit Pause Control Frame	The frame transmitted was a control frame with a valid pause opcode.
48	Transmit Control Frame	The frame transmitted was a control frame.
47-32	Total Bytes Transmitted on Wire	Total bytes transmitted on the wire for the current packet, including all bytes from collided attempts.
31	Transmit Underrun	The transmission was aborted due to insufficient buffer memory bandwidth to sustain the 10 Mbit/s transmit rate.
30	Transmit Giant	Byte count for frame was greater than the MAMXFL registers.
29	Transmit Late Collision	Collision occurred after 64 bytes had already been transmitted.
28	Transmit Excessive Collision	Packet was aborted after the number of collisions exceeded 15, the retransmission maximum.
27	Transmit Excessive Defer	Packet was deferred in excess of 24,287 bit times (2.4287 ms), due to a continuously-occupied medium.
26	Transmit Packet Defer	Packet was deferred for at least one attempt but less than an excessive defer.
25	Transmit Broadcast	Packet's destination address was a Broadcast address.
24	Transmit Multicast	Packet's destination address was a Multicast address.
23	Transmit Done	Transmission of the packet was completed successfully.
22	Transmit Length Out of Range	Indicates that frame type/length field was larger than 1500 bytes (type field).
21	Transmit Length Check Error	Indicates that frame length field value in the packet does not match the actual data byte length and is not a type field. The FRMLNEN bit (MACON3<1>) must be set to get this error.
20	Transmit CRC Error	The attached CRC in the packet did not match the internally generated CRC.
19-16	Transmit Collision Count	Number of collisions the current packet incurred during transmission attempts. It applies to successfully transmitted packets and as such, will not show the possible maximum count of 16 collisions.
15-0	Transmit Byte Count	Total bytes in frame not counting collided bytes.

#### TABLE 18-4: TRANSMIT STATUS VECTORS

#### 18.5.3 RECEIVING PACKETS

Assuming that the receive buffer has been initialized, the MAC has been properly configured and the receive filters have been configured, the application should perform these steps to receive Ethernet packets:

- 1. Set the PKTIE and ETHIE bits to generate an Ethernet interrupt whenever a packet is received (if desired).
- Clear the RXERIF flag and set both RXERIE and ETHIE to generate an interrupt whenever a packet is dropped due to insufficient buffer space or memory access bandwidth (if desired).
- 3. Enable reception by setting the RXEN bit (ECON1<2>).

After setting RXEN, the Duplex mode and the Receive Buffer Start and End Pointers should not be modified. Additionally, to prevent unexpected packets from arriving, it is recommended that RXEN be cleared before altering the receive filter configuration (ERXFCON) and MAC address.

After reception is enabled, packets which are not filtered out will be written into the circular receive buffer. Any packet which does not meet the necessary filter


criteria will be discarded and the application will not have any means of identifying that a packet was thrown away. When a packet is accepted and completely written into the buffer:

- the EPKTCNT register is incremented,
- the PKTIF bit is set,
- an interrupt is generated (if enabled), and
- the Hardware Write Pointers, ERXWRPT, are automatically advanced.

#### 18.5.3.1 Receive Packet Layout

Figure 18-10 shows the layout of a received packet. The packets are preceded by a 6-byte header which contains a Next Packet Pointer in addition to a receive status vector which contains receive statistics, including the packet's size. The receive status vectors are shown in Table 18-5.

If the last byte in the packet ends on an odd value address, the hardware will automatically add a padding byte when advancing the Hardware Write Pointer. As such, all packets will start on an even boundary.



#### FIGURE 18-10: SAMPLE RECEIVE PACKET LAYOUT

Bit	Field	Description
31	Zero	·0,
30	Receive VLAN Type Detected	Current frame was recognized as a VLAN tagged frame.
29	Receive Unknown Opcode	Current frame was recognized as a control frame but it contained an unknown opcode.
28	Receive Pause Control Frame	Current frame was recognized as a control frame containing a valid pause frame opcode and a valid destination address.
27	Receive Control Frame	Current frame was recognized as a control frame for having a valid type/length designating it as a control frame.
26	Dribble Nibble	Indicates that after the end of this packet, an additional 1 to 7 bits were received. The extra bits were thrown away.
25	Receive Broadcast Packet	Indicates packet received had a valid Broadcast address.
24	Receive Multicast Packet	Indicates packet received had a valid Multicast address.
23	Received OK	Indicates that the packet had a valid CRC and no symbol errors.
22	Length Out of Range	Indicates that frame type/length field was larger than 1500 bytes (type field).
21	Length Check Error	Indicates that frame length field value in the packet does not match the actual data byte length.
20	CRC Error	Indicates that the frame CRC field value does not match the CRC calculated by the MAC.
19	Reserved	
18	Carrier Event Previously Seen	Indicates that at some time since the last receive, a carrier event was detected. The carrier event is not associated with this packet. A carrier event is activity on the receive channel that does not result in a packet receive attempt being made.
17	Reserved	
16	Long Event/Drop Event	Indicates a packet over 50,000 bit times occurred or that a packet was dropped since the last receive.
15-0	Received Byte Count	Indicates length of the received frame. This includes the destination address, source address, type/length, data, padding and CRC fields. This field is stored in little-endian format.

#### TABLE 18-5: RECEIVE STATUS VECTORS

#### 18.5.3.2 Reading Received Packets

To process the packet, an application will normally start reading from the beginning of the Next Packet Pointer. The application will save the Next Packet Pointer, any necessary bytes from the receive status vector, and then proceed to read the actual packet contents. If the AUTOINC bit is set, it will be able to sequentially read the entire packet without ever modifying the ERDPT registers. The Read Pointer would automatically wrap at the end of the circular receive buffer to the beginning. In the event that the application needed to randomly access the packet, it would be necessary to manually calculate the proper ERDPT registers, taking care to not exceed the end of the receive buffer, if the packet spans the ERXND to ERXST buffer boundary. In other words, given the packet start address and a desired offset, the application should follow the logic shown in Equation 18-1.

#### EQUATION 18-1: RANDOM ACCESS ADDRESS CALCULATION

```
If Packet Start Address + Offset > ERXND, then
ERDPT = Packet Start Address + Offset - (ERXND - ERXST + 1)
else
```

ERDPT = Packet Start Address + Offset

#### 18.5.3.3 Freeing Receive Buffer Space

After the user application has processed a packet (or part of the packet) and needs to free the occupied buffer space used by the processed data, it must advance the Receive Buffer Read Pointer pair, ERXRDPT. The module always writes up to, but not over, the memory pointed to by the ERXRDPT registers. If an attempt to overwrite the Receive Buffer Read Pointer location occurs, the packet in progress is aborted, the RXERIF flag is set and an interrupt is generated (if enabled). In this manner, the hardware will never overwrite unprocessed packets. Normally, the ERXRDPT pair is advanced close to a value pointed to by the Next Packet Pointer which precedes the receive status vector for the current packet.

The Receive Buffer Read Pointer Low Byte (ERXRDPTL register) is internally buffered to prevent the pointer from moving when only one byte is updated. To move the ERXRDPT pair, the application must write to ERXRDPTL first. The write will update the internal buffer but will not affect the register. When the application writes to ERXRDPTH, the internally buffered low byte will be loaded into the ERXRDPTL register at the same time. The ERXRDPT bytes can be read in any order. When they are read, the actual value of the registers will be returned. As a result, the buffered low byte is not readable.

In addition to advancing the Receive Buffer Read Pointer, after each packet is fully processed, the application must set the PKTDEC bit (ECON2<6>). This causes the EPKTCNT register to decrement by 1. After decrementing, if EPKTCNT is '0', the PKTIF flag bit is automatically cleared. Otherwise, it remains set, indicating that additional packets are in the receive buffer and are waiting to be processed. Attempting to decrement EPKTCNT below 0 does not cause an underflow to 255, but may cause an unintentional interrupt; the application should avoid decrementing EPKTCNT in this situation.

Additionally, if the EPKTCNT register ever maximizes at 255, all new packets which are received will be aborted, even if buffer space is available. To indicate the error, the RXERIF is set and an interrupt is generated (if enabled). To prevent this condition, the user application must properly decrement the counter whenever a packet is processed. Because only one pointer is available to control buffer area ownership, the application must process packets in the order they are received. If a packet is to be saved and processed later, the application should copy the packet to an unused location in memory. This can be done efficiently using the integrated DMA controller (see **Section 18.9 "Direct Memory Access Controller"**).

#### 18.5.3.4 Receive Buffer Free Space

At any time the application needs to know how much receive buffer space is remaining, it should read the Hardware Write Pointers (ERXWRPT registers) and compare it with the ERXRDPT registers. Combined with the known size of the receive buffer, the free space can be derived.

Note: The ERXWRPT registers only update when a packet has been successfully received. If the application reads it just before another packet is to be successfully completed, the value returned could be stale and off by the maximum frame length permitted (MAMXFLH:MAMXFLL) plus 8. Furthermore, as the application reads one byte of the ERXWRPT registers, a new packet may arrive and update the 13-bit pointer before the application has an opportunity to read the other byte of the ERXWRPT registers.

When reading the ERXWRPT registers with the receive hardware enabled, special care must be taken to ensure the low and high bytes are read as a matching set.

To be assured that a matching set is obtained:

- 1. Read the EPKTCNT register and save its contents.
- 2. Read ERXWRPTL and ERXWRPTH.
- 3. Read the EPKTCNT register again.
- 4. Compare the two packet counts. If they are not the same, go back to step 2.

With the Hardware Write Pointers obtained, the free space can be calculated as shown in Example 18-2. The hardware prohibits moving the Write Pointer to the same value occupied by the ERXRDPT registers, so at least one byte will always go unused in the buffer. The Equation 18-2 calculation reflects the lost byte.

#### EQUATION 18-2: RECEIVE BUFFER FREE SPACE CALCULATION

```
If ERXWRPT > ERXRDPT, then

Free Space = (ERXND - ERXST) - (ERXWRPT - ERXRDPT)

else

if ERXWRPT = ERXRDPT, then

Free Space = (ERXND - ERXST)

else

Free Space = ERXRDPT - ERXWRPT - 1
```

Register Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
EIE	—	PKTIE	DMAIE	LINKIE	TXIE	—	TXERIE	RXERIE	63
EIR	—	PKTIF	DMAIF	LINKIF	TXIF	_	TXERIF	RXERIF	63
ESTAT	—	BUFER	_	r		RXBUSY	TXABRT	PHYRDY	63
ECON1	TXRST	RXRST	DMAST	CSUMEN	TXRTS	RXEN	_	_	60
ETXSTL	Transmit St	art Register	Low Byte (E	TXST<7:0>)					64
ETXSTH	—	_	_	Transmit Sta	irt Register H	igh Byte (ET	XST<12:8>)		64
ETXNDL	Transmit Er	nd Register	Low Byte (E	TXND<7:0>)					64
ETXNDH	—	_	_	Transmit En	d Register Hi	gh Byte (ET)	(ND<12:8>)		64
MACON1	—	—	_	r	TXPAUS	RXPAUS	PASSALL	MARXEN	65
MACON3	PADCFG2	PADCFG1	PADCFG0	TXCRCEN	PHDREN	HFRMEN	FRMLNEN	FULDPX	65
MACON4	—	DEFER	r	r		_	r	r	65
MABBIPG	—	BBIPG6	BBIPG5	BBIPG4	BBIPG3	BBIPG2	BBIPG1	BBIPG0	65
MAIPGL	—	MAC Non E	Back-to-Bacl	k Inter-Packe	t Gap Regist	er Low Byte (	MAIPGL<6:0	>)	65
MAIPGH	_	— MAC Non Back-to-Back Inter-Packet Gap Register High Byte (MAIPGH<6:0>)							
MAMXFLL	Maximum F	Maximum Frame Length Register Low Byte (MAMXFL<7:0>)							
MAMXFLH	Maximum F	rame Lengt	h Register H	ligh Byte (MA	AMXFL<15:8	>)			64
Lanandi			1.1.14			1			

#### TABLE 18-6: SUMMARY OF REGISTERS ASSOCIATED WITH PACKET TRANSMISSION

**Legend:** — = unimplemented, r = reserved bit. Shaded cells are not used.

#### TABLE 18-7: SUMMARY OF REGISTERS ASSOCIATED WITH PACKET RECEPTION

Reset Values on Page:	Bit 0	Bit 1	Bit 2	Bit 3	Bit 4	Bit 5	Bit 6	Bit 7	Register Name
E 63	RXERIE	TXERIE	—	TXIE	LINKIE	DMAIE	PKTIE	—	EIE
F 63	RXERIF	TXERIF	_	TXIF	LINKIF	DMAIF	PKTIF	_	EIR
0Y 63	PHYRDY	TXABRT	RXBUSY	_	r	_	BUFER	_	ESTAT
63	_	_	_	_	_	ETHEN	PKTDEC	AUTOINC	ECON2
60	_	_	RXEN	TXRTS	CSUMEN	DMAST	RXRST	TXRST	ECON1
64					XST<7:0>)	ow Byte (ER	art Register L	Receive Sta	ERXSTL
64	— — Receive Start Register High Byte (ERXST<12:8>)								ERXSTH
64					XND<7:0>)	ow Byte (ER	d Register Lo	Receive En	ERXNDL
64		XND<12:8>)	gh Byte (ER	d Register Hi	Receive End	_	_	_	ERXNDH
63				T<7:0>)	te (ERXRDP	inter Low By	ffer Read Po	Receive Bu	ERXRDPTL
63	T<12:8>)	te (ERXRDP	nter High By	fer Read Poi	Receive Buf	_	_	_	ERXRDPTH
I 64	BCEN	MCEN	HTEN	MPEN	PMEN	CRCEN	ANDOR	UCEN	ERXFCON
64						Register	icket Count F	Ethernet Pa	EPKTCNT
N 65	MARXEN	PASSALL	RXPAUS	TXPAUS	r	_	_	_	MACON1
YX 65	FULDPX	FRMLNEN	HFRMEN	PHDREN	TXCRCEN	PADCFG0	PADCFG1	PADCFG2	MACON3
64	Maximum Frame Length Register Low Byte (MAMXFL<7:0>)								MAMXFLL
64			)	MXFL<15:8>	gh Byte (MAN	Register Hig	rame Length	Maximum F	MAMXFLH
EN KE	BCE	te (ERXRDP MCEN PASSALL	nter High By HTEN RXPAUS HFRMEN	T<7:0>) fer Read Poi MPEN TXPAUS PHDREN IXFL<7:0>) MXFL<15:8>	te (ERXRDP Receive Buf PMEN r TXCRCEN w Byte (MAN gh Byte (MAN	CRCEN Register PADCFG0 Register Lo Register Hig	— ANDOR Icket Count F — PADCFG1 frame Length	UCEN Ethernet Pa — PADCFG2 Maximum F Maximum F	ERXRDPTL ERXRDPTH ERXFCON EPKTCNT MACON1 MACON3 MAMXFLL

**Legend:** — = unimplemented, r = reserved bit. Shaded cells are not used.

#### 18.6 Duplex Mode Configuration and Negotiation

The Ethernet module does not support Automatic Duplex mode negotiation. If it is connected to an automatic duplex negotiation enabled network switch or Ethernet controller, the module will be detected as a half-duplex device. To communicate in full duplex, the module and the remote node (switch, router or Ethernet controller) must be manually configured for full-duplex operation.

#### 18.6.1 HALF-DUPLEX OPERATION

The Ethernet module operates in Half-Duplex mode when the FULDPX (MACON3<0>) and PDPXMD (PHCON1<8>) bits are cleared (= 0). If only one of these two bits is set, the module will be in an indeterminate state and not function correctly. Since switching between Full and Half-Duplex modes may result in this indeterminate state, it is recommended that the application not transmit any packets (maintain the TXRTS bit clear), and disable packet reception (maintain the RXEN bit clear) during this period.

In Half-Duplex mode, only one Ethernet controller may be transmitting on the physical medium at any time. If the application requests a packet to be transmitted by setting the TXRTS bit while another Ethernet controller is already transmitting, the Ethernet module will delay, waiting for the remote transmitter to stop. When it stops, the module will attempt to transmit its packet. Should another Ethernet controller start transmitting at approximately the same time, the data on the wire will become corrupt and a collision will occur.

The hardware will handle this condition in one of two ways. If the collision occurs before 64 bytes have been transmitted, the following events occur:

- 1. the TXRTS bit remains set;
- 2. the transmit error interrupt does not occur;
- 3. a random exponential backoff delay elapses, as defined by the IEEE 802.3 specification;
- 4. a new attempt to transmit the packet from the beginning occurs. The application does not need to intervene.

If the number of retransmission attempts reaches 15 and another collision occurs, the packet is aborted and the TXRTS bit is cleared. The application will then be responsible for taking appropriate action. The application will be able to determine that the packet was aborted instead of being successfully transmitted by reading the TXABRT flag. For more information, see **Section 18.5.2 "Transmitting Packets"**.

If the collision occurs after 64 bytes have already been transmitted, the packet is immediately aborted without any retransmission attempts. Ordinarily, in IEEE 802.3 compliant networks which are properly configured, this late collision will not occur. User intervention may be required to correct the issue. This problem may occur as a result of a full-duplex node attempting to transmit on the half-duplex medium. Alternately, the module may be attempting to operate in Half-Duplex mode while it may be connected to a full-duplex network. Excessively long cabling and network size may also be a possible cause of late collisions.

#### 18.6.2 FULL-DUPLEX OPERATION

The Ethernet module operates in Full-Duplex mode when the FULDPX (MACON3<0>) and PDPXMD (PHCON1<8>) bits are both set (= 1). If only one of these two bits is clear, the module will be in an indeterminate state and not function correctly. Again, since switching between Full and Half-Duplex modes may result in this indeterminate state, it is recommended that the application not transmit any packets and should disable packet reception during this period.

In Full-Duplex mode, packets will be transmitted while simultaneously packets may be received. Given this, it is impossible to cause any collisions when transmitting packets.

### 18.7 Flow Control

The Ethernet module implements hardware flow control for both Full and Half-Duplex modes. The operation of this feature differs depending on which mode is being used.

#### 18.7.1 HALF-DUPLEX MODE

In Half-Duplex mode, setting the FCEN0 bit (EFLOCON<0>) causes flow control to be enabled. When FCEN0 is set, a continuous preamble pattern of alternating '1's and '0's (55h) will automatically be transmitted on the Ethernet medium. Any connected nodes will see the transmission and either not transmit anything, waiting for the transmission to end, or will attempt to transmit and immediately cause a collision. Because a collision will always occur, no nodes on the network will be able to communicate with each other and no new packets will arrive.

When the application causes the module to transmit a packet by setting the TXRTS bit, the preamble pattern will stop being transmitted. An inter-packet delay will pass as configured by register MABBIPG, and then the module will attempt to transmit its packet. After the inter-packet delay, other nodes may begin to transmit. Because all traffic was jammed previously, several nodes may begin transmitting and a series of collisions may occur. When the module successfully finishes transmitting its packet or aborts it, the transmission of the preamble pattern will automatically restart. When the application wishes to no longer jam the network, it should clear the FCEN0 bit. The preamble transmission will resume.

Given the detrimental network effects that are possible and lack of effectiveness, it is not recommend that half-duplex flow control be used unless the application will be in a closed network environment with proper testing.

#### 18.7.2 FULL-DUPLEX MODE

In Full-Duplex mode (MACON3<0> = 1), hardware flow control is implemented by means of transmitting pause control frames, as defined by the IEEE 802.3 specification. Pause control frames are 64-byte frames consisting of the reserved Multicast destination address of 01-80-C2-00-00-01, the source address of the sender, a special pause opcode, a 2-byte pause timer value and padding/CRC.


Normally, when a pause control frame is received by a MAC, the MAC will finish the packet it is transmitting and then stop transmitting any new frames. The pause timer value will be extracted from the control frame and used to initialize an internal timer. The timer will automatically decrement every 512 bit times, or 51.2  $\mu$ s. While the timer is counting down, reception of packets is still enabled. If new pause frames arrive, the timer will be re-initialized with the new pause timer value. When

the timer reaches zero, or was sent a frame with a zero pause timer value, the MAC that received the pause frame will resume transmitting any pending packets. To prevent a pause frame from stopping all traffic on the entire network, Ethernet switches and routers do not propagate pause control frames in Full-Duplex mode. The pause operation only applies to the direct recipient.

A sample network is shown in Figure 18-11. If Computer A were to be transmitting too much data to the microcontroller-based application in Full-Duplex mode, the Ethernet module could transmit a pause control frame to stop the data which is being sent to it. The Ethernet Switch would take the pause frame and stop sending data to the application. If Computer A continues to send data, the Ethernet Switch will buffer the data so it can be transmitted later when its pause timer expires. If the Ethernet Switch begins to run out of buffer space, it will likely transmit a pause control frame of its own to Computer A.

If, for some reason the Ethernet Switch does not generate a pause control frame of its own, or one of the nodes does not properly handle the pause frame it receives, then packets will inevitably be dropped. In any event, any communication between Computer A and Computer B will always be completely unaffected.

#### FIGURE 18-11: SAMPLE FULL-DUPLEX NETWORK



To enable flow control in Full-Duplex mode, set the TXPAUS and RXPAUS bits in the MACON1 register. Then, at any time that the receiver buffer is running out of space, set the Flow Control Enable bits, FCEN1:FCEN0 (EFLOCON<1:0>). The module will automatically finish transmitting anything that was in progress and then send a valid pause frame loaded with the selected pause timer value. Depending on the mode selected, the application may need to eventually clear Flow Control mode by again writing to the FCEN bits.

When the RXPAUS bit is set and a valid pause frame arrives with a non-zero pause timer value, the module will automatically inhibit transmissions. If the TXRTS bit becomes set to send a packet, the hardware will simply wait until the pause timer expires before attempting to send the packet and subsequently, clearing the TXRTS bit. Normally, this is transparent to the microcontroller, and it will never know that a pause frame had been received. Should it be desirable to know when the MAC is paused or not, the user should set the PASSALL bit (MACON1<1>), then manually interpret the pause control frames which may arrive.

### REGISTER 18-19: EFLOCON: ETHERNET FLOW CONTROL REGISTER

U-0	U-0	U-0	U-0	U-0	R-0	R/W-0	R/W-0
—	—	—	—	_	r	FCEN1	FCEN0
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-3	Unimplemented: Read as '0'
bit 2	Reserved: Do not use
bit 1-0	FCEN1:FCEN0: Flow Control Enable bits
	When FULDPX (MACON3<0>) = 1:
	11 = Send one pause frame with a '0' timer value and then turn flow control off
	10 = Send pause frames periodically
	01 = Send one pause frame then turn flow control off
	00 = Flow control off
	When FULDPX (MACON3<0>) = 0:
	x1 = Flow control on
	x0 = Flow control off

#### TABLE 18-8: SUMMARY OF REGISTERS USED WITH FLOW CONTROL

Register Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
ECON1	TXRST	RXRST	DMAST	CSUMEN	TXRTS	RXEN			60
MACON1	—	—	_	r	TXPAUS	RXPAUS	PASSALL	MARXEN	65
MABBIPG	_	BBIPG6	BBIPG5	BBIPG4	BBIPG3	BBIPG2	BBIPG1	BBIPG0	65
EFLOCON	rrFCEN1FCEN0								
EPAUSL	EPAUSL Pause Timer Value Register Low Byte (EPAUS<7:0>)								65
EPAUSH Pause Timer Value Register High Byte (EPAUS<15:8>)							65		

**Legend:** — = unimplemented, r = reserved bit. Shaded cells are not used.

Γ.

## 18.8 Receive Filters

To minimize microcontroller processing overhead, the Ethernet module incorporates a range of different receive filters which can automatically reject packets which are not needed. Six different types of packet filters are implemented:

- Unicast
- Multicast
- Broadcast
- Pattern Match
- Magic Packet<sup>™</sup>
- · Hash Table

The individual filters are all configured by the ERXFCON register (Register 18-20). More than one filter can be active at any given time. Additionally, the filters can be configured by the ANDOR bit to either logically AND or logically OR the tests of several filters. In other words, the filters may be set so that only packets accepted by all active filters are accepted, or a packet accepted by any one filter is accepted. The flowcharts in Figure 18-12 and Figure 18-13 show the effect that each of the filters will have, depending on the setting of ANDOR.

The device can enter Promiscuous mode and receive all legal packets by setting the ERXFCON register to 20h (enabling only the CRC filter for valid packets). The proper setting of the register will depend on the application requirements.

#### 18.8.1 UNICAST FILTER

The Unicast receive filter checks the destination address of all incoming packets. If the destination address exactly matches the contents of the MAADR registers, the packet meets the Unicast filter criteria.

#### 18.8.2 MULTICAST FILTER

The Multicast receive filter checks the destination address of all incoming packets. If the Least Significant bit of the first byte of the destination address is set, the packet meets the Multicast filter criteria.

#### 18.8.3 BROADCAST FILTER

The Broadcast receive filter checks the destination address of all incoming packets. If the destination address is FF-FF-FF-FF-FF, the packet meets the Broadcast filter criteria.

#### 18.8.4 HASH TABLE FILTER

The Hash Table receive filter is typically used to receive traffic sent to a specific Multicast group address. Because it checks the specific destination address of packets, it is capable of filtering out more unwanted packets than the Multicast filter.

The filter performs a 32-bit CRC over the six destination address bytes in the packet, using the polynomial 4C11DB7h. From the resulting 32-bit binary number, a 6-bit value is derived from bits 28:23. This value in turn points to location in a table formed by the Ethernet Hash Table registers, ETH0 through ETH7. If the bit in that location is set, the packet meets the Hash Table filter criteria and is accepted. The specific pointer values for each bit location in the table are shown in Table 18-9.

An example of the Hash Table operation is shown in Example 18-1. In this case, the destination address 01-00-00-00-01-2C produces a Table Pointer value of 34h, which points to bit 4 of ETH6. If this bit is '1', the packet will be accepted.

By extension, clearing every bit in the Hash Table registers means that the filter criteria will never be met. Similarly, if every bit in the Hash Table is set, the filter criteria will always be met.

TABLE 18-9:	<b>BIT ASSIGNMENTS IN HASH</b>
	TABLE REGISTERS

Register	Bit Number in Hash Table							
	7	6	5	4	3	2	1	0
EHT0	07	06	05	04	03	02	01	00
EHT1	0F	0E	0D	0C	0B	0A	09	08
EHT2	17	16	15	14	13	12	11	10
EHT3	1F	1E	1D	1C	1B	1A	19	18
EHT4	27	26	25	24	23	22	21	20
EHT5	2F	2E	2D	2C	2B	2A	29	28
EHT6	37	36	35	34	33	32	31	30
EHT7	3F	3E	3D	3C	3B	ЗA	39	38


# EXAMPLE 18-1: DERIVING A HASH TABLE LOCATION

Packet Destination Address: 01-00-00-00-01-2C (hex) ResultofCRC-32with4C11DB7h: 1101 1010 0000 1011 0100 0101 0111 0101 (binary) Pointerderivedfrombits28:23ofCRCresult: 110100 (binary), or 34 (hex) CorrespondingHashTableLocation: ETH6<4>


## REGISTER 18-20: ERXFCON: ETHERNET RECEIVE FILTER CONTROL REGISTER

R/W-1	R/W-0	R/W-1	R/W-0	R/W-0	R/W-0	R/W-0	R/W-1	
UCEN	ANDOR	CRCEN	PMEN	MPEN	HTEN	MCEN	BCEN	
bit 7							bit (	
Legend:	- h:4				mantad hit was			
R = Readable		W = Writable	DIT	-	mented bit, rea			
-n = Value at	PUR	'1' = Bit is set		'0' = Bit is cle	eared	x = Bit is unkr	nown	
bit 7	When ANDO 1 = Packets r 0 = Filter disa When ANDO	not having a des abled <u>R = 0:</u> with a destinatio	stination add	-				
bit 6	1 = AND: Pa	D/OR Filter Sele ckets will be reje kets will be acce	ected unless					
bit 5	1 = All packe	t-Filter CRC Ch ts with an invali validity will be	d CRC will be					
bit 4	When ANDO 1 = Packets r 0 = Filter disa When ANDO	must meet the F abled <u>R = 0:</u> which meet the	attern Match			led		
bit 3	When ANDO 1 = Packets r 0 = Filter disa When ANDO	must be Magic F abled <u>R = 0:</u> ackets for the loo	Packets for th			will be discarde	d	
bit 2	HTEN: Hash Table Filter Enable bit         When ANDOR = 1:         1 = Packets must meet the Hash Table criteria or they will be discarded         0 = Filter disabled         When ANDOR = 0:         1 = Packets which meet the Hash Table criteria will be accepted         0 = Filter disabled							
bit 1	MCEN: Multicast Filter Enable bit         When ANDOR = 1:         1 = The LSb of the first byte of the packet's destination address must be set, or they will be discarded         0 = Filter disabled         When ANDOR = 0:         1 = Packets which have the LSb of the first byte in the destination address set, will be accepted         0 = Filter disabled							
bit 0	When ANDO 1 = Packets r 0 = Filter disa When ANDO	must have a des abled <u>R = 0:</u> which have a de	stination addı			-		





#### FIGURE 18-13: RECEIVE FILTERING USING AND LOGIC



#### 18.8.5 PATTERN MATCH FILTER

The Pattern Match filter selects up to 64 bytes from the incoming packet and calculates an IP checksum of the bytes. The checksum is then compared to the EPMCS registers. The packet meets the Pattern Match filter criteria if the calculated checksum matches the EPMCS registers. The Pattern Match filter may be useful for filtering packets which have expected data inside them.

To use the Pattern Match filter, the application must program the Pattern Match offset (EPMOH:EPMOL), all of the Pattern Match mask bytes (EPMM0:EPMM7) and the Pattern Match Checksum register pair (EPMCSH:EPMCSL). The Pattern Match offset should be loaded with the offset from the beginning of the destination address field to the 64-byte window which will be used for the checksum computation. Within the 64-byte window, each individual byte can be selectively included or excluded from the checksum computation by setting or clearing the respective bit in the Pattern Match mask. If a packet is received which would cause the 64 byte window to extend past the end of the CRC, the filter criteria will immediately not be met, even if the corresponding mask bits are all '0'.

Note: In all cases, the value of the Pattern Match offset must be even for proper operation. Programming the EMPO register pair with an odd value will cause unpredictable results. The Pattern Match Checksum registers should be programmed to the checksum which is expected for the selected bytes. The checksum is calculated in the same manner that the DMA module calculates checksums (see **Section 18.9.2 "Checksum Calculations"**). Data bytes which have corresponding mask bits programmed to '0' are completely removed for purposes of calculating the checksum, as opposed to treating the data bytes as zero.

As an example, if the application wished to filter all packets having a particular source MAC address of 00-04-A3-FF-FF-FF, it could program the Pattern Match offset to 0000h and then set bits 6 and 7 of EPMM0 and bits 0, 1, 2 and 3 of EPMM1 (assuming all other mask bits are '0'). The proper checksum to program into the EPMCS registers would be 5BFCh. As an alternative configuration, it could program the offset to 0006h and set bits 0, 1, 2, 3, 4 and 5 of EPMM0. The checksum would still be 5BFCh. However, the second case would be less desirable as packets less than 70 bytes long could never meet the Pattern Match criteria, even if they would generate the proper checksum given the mask configuration.

Another example of a Pattern Match filter is illustrated in Figure 18-14.


### FIGURE 18-14: SAMPLE PATTERN MATCH FORMAT

#### Input Configuration: EMPOH:EPMOL = 0006h EPMM7:EPMM0 = 000000000001F0Ah EPMCSH:EPMCSL = 563Fh FCS Field DA SA Type/Length Data Received Data 11 22 33 44 55 66 77 88 99 AA BB CC 00 5A 09 0A 0B 0C 0D ... 40 ... FE 45 23 01 Byte # 0 1 2 3 4 5 6 789 10 11 12 13 17 18 . . . 70 . . . 15 16 Bytes Used for **Checksum Computation** 64-Byte Window Used for Pattern Match Values Used for Checksum Computation = {88h, AAh, 09h, 0Ah, 0Bh, 0Ch, 0Dh, 00h} (00h padding byte added by hardware) Note: Received data is shown in hexadecimal. Byte numbers are shown in decimal format.

#### 18.8.6 MAGIC PACKET FILTER

The Magic Packet pattern consists of a sync pattern of six FFh bytes, followed by 16 repeats of the destination address (Figure 18-15). The Magic Packet filter checks the destination address and data fields of all incoming packets. If the destination address matches the MAADR registers and the data field holds a valid Magic Packet pattern someplace within it, then the packet will meet the Magic Packet filter criteria.

#### FIGURE 18-15: SAMPLE MAGIC PACKET™ FORMAT



### 18.9 Direct Memory Access Controller

The Ethernet module incorporates a dual purpose DMA controller, which can be used to copy data between locations within the 8-Kbyte memory buffer. It can also be used to calculate a 16-bit checksum which is compatible with various industry standard communication protocols, including TCP, UDP, IP, ICMP, etc.

The DMA is controlled using three pointers and several status/control bits:

- EDMASTH:EDMASTL: Source Start Address
- EDMANDH:EDMANDL: Source End Address
- EDMADSTH:EDMADSTL: Destination Start Address
- DMAST and CSUMEN (ECON1<5,4>): DMA Start/Busy and Checksum Enable bits
- DMAIE and DMAIF (EIE<5> and EIR<5>): DMA Interrupt Enable and Flag bits

The Source and End Pointers define what data will be copied or checksumed. The Destination Pointer, used only when copying data, defines where copied data will be placed. All three pointers are with respect to the 8-Kbyte Ethernet memory and cannot be used to access memory in the PIC<sup>®</sup> microcontroller data memory space.

When a DMA operation begins, the EDMAST register pair is copied into an Internal Source Pointer. The DMA will execute on one byte at a time and then increment the Internal Source Pointer. However, if a byte is processed and the Internal Source Pointer is equal to the Receive Buffer End Pointer pair, ERXND, the Source Pointer will not be incremented. Instead, the Internal Source Pointer will be loaded with the Receive Buffer Start Pointer pair, ERXST. In this way, the DMA will follow the circular FIFO structure of the receive buffer and received packets can be processed using one operation. The DMA operation will end when the Internal Source Pointer matches the EDMAND Pointers.

While any DMA operation is in progress, the DMA Pointers and the CSUMEN bit (ECON1<4>) should not be modified. The DMA operation can be canceled at any time by clearing the DMAST bit (ECON1<5>). No registers will change; however, some memory bytes may already have been copied if a DMA copy was in progress.

Some operational requirements must always be kept in mind when using the DMA. Failure to observe these requirements may result in loss of Ethernet buffer data, or even complete failure of Ethernet operation:

- If the EDMAND Pointers cannot be reached because of the receive buffer wrapping behavior, the DMA operation will never end.
- By design, the DMA module cannot be used to copy or calculate a checksum over only one byte (EDMAST = EDMAND). An attempt to do so may overwrite all memory in the buffer and never end.

- After termination of a DMA operation (DMAST is cleared by hardware or firmware), the application must not set DMAST again within 4 instruction cycles.
- To ensure reliable operation, avoid having the application access EDATA during a DMA copy operation. EDATA may be safely accessed during DMA checksum operations.

### 18.9.1 COPYING MEMORY

To copy memory within the buffer:

- 1. Program the EDMAST, EDMAND, and EDMADST register pairs with the appropriate start, end and destination addresses. The EDMAST registers should point to the first byte to copy from, the EDMAND registers should point to the last byte to copy and the EDMADST registers should point to the first byte in the destination range. The destination range will always be linear, never wrapping at any values except from 8191 to 0 (the 8-Kbyte memory boundary). Extreme care should be taken when calculating the End Pointer to prevent a never ending DMA operation which would overwrite the entire 8-Kbyte buffer.
- If desired, set the DMAIE (EIE<5>) and ETHIE (PIE2<5>) bits, and clear the DMAIF (EIR<5>) flag bit to enable an interrupt at the end of the copy process.
- 3. Clear the CSUMEN (ECON1<4>) bit.
- 4. Start the DMA copy by setting the DMAST (ECON1<5>) bit.

If a transmit operation is in progress (TXRTS bit is set) while the DMAST bit is set, the module will wait until the transmit operation is complete before attempting to do the DMA copy. This possible delay is required because the DMA and transmission engine are unable to access the buffer at the same time.

When the copy is complete, the DMA hardware will clear the DMAST bit, set the DMAIF bit and generate an interrupt (if enabled). The pointers and the EDMACS registers will not be modified.

After the DMA module has been initialized and has begun its copy, one instruction cycle (TCY) will be required for each byte copied. However, if the Ethernet receive hardware accumulates one byte of data, the DMA will stall that cycle, yielding to the higher priority operation. If a maximum size, 1518-byte packet was copied while no other memory bandwidth was being used, the DMA module would require slightly more than 145.7  $\mu$ s to complete at a core frequency of 41.667 MHz. The time required to copy a minimum size packet of 64 bytes would be approximately 6.2  $\mu$ s (at 41.667 MHz) plus register configuration time.

### 18.9.2 CHECKSUM CALCULATIONS

The checksum calculation logic treats the source data as a series of 16-bit big-endian integers. If the source range contains an odd number of bytes, a padding byte of 00h is effectively added to the end of the series for purposes of calculating the checksum.

The calculated checksum is the 16-bit, one's complement of the one's complement sum of all 16-bit integers. For example, if the bytes included in the checksum were {89h, ABh, CDh}, the checksum would begin by computing 89ABh + CD00h. A carry out of the 16th bit would occur in the example, so in 16-bit one's complement arithmetic, it would be added back to the first bit. The resulting value of 56ACh would finally be complemented to achieve a checksum of A953h.

To calculate a checksum:

- 1. Set the EDMAST and EDMAND register pairs to point to the first and last bytes of buffer data to be included in the checksum. Care should be taken when programming these pointers to prevent a never-ending checksum calculation due to receive buffer wrapping.
- To generate an optional interrupt when the checksum calculation is done, set the DMAIE (EIE<5>) and ETHIE (PIE2<5>) bits and clear the DMAIF (EIR<5>) bit.
- 3. Start the calculation by setting the CSUMEN (ECON1<4>) and DMAST (ECON1<5>) bits.

When the checksum is finished being calculated, the hardware will clear the DMAST bit, set the DMAIF bit and an interrupt will be generated if enabled. The DMA Pointers will not be modified, and no memory will be written to. The EDMACSH and EDMACSL registers will contain the calculated checksum. The application may write this value into a packet, compare this value with zero (to validate a received block of data containing a checksum field in it), or compare it with some other checksum, such as a pseudo header checksum used in various protocols (TCP, UDP, etc.).

When operating the DMA in Checksum mode, it takes one instruction cycle (TCY) for every byte included in the checksum. As a result, if a checksum over 1446 bytes was performed, the DMA module would require slightly more than 138.8  $\mu$ s to complete the operation at 41.667 MHz.

At the same frequency, a small 20-byte header field would take approximately 1.9  $\mu$ s plus DMA setup time to calculate a sum. These estimated times assume that the Ethernet receive hardware does not need memory access bandwidth and the CPU does not issue any reads or writes to the EDATA register while the DMA is computing.

Like the DMA Copy mode, the checksum operation will not start until the TXRTS bit (ECON1<3>) is clear. This may considerably increase the checksum calculation time if the application transmits a large packet and immediately attempts to validate a checksum on a received packet.

Register Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page
EIE		PKTIE	DMAIE	LINKIE	TXIE	_	TXERIE	RXERIE	63
EIR		PKTIF	DMAIF	LINKIF	TXIF	_	TXERIF	RXERIF	63
ECON1	TXRST	RXRST	ST DMAST CSUMEN TXRTS RXEN — —						60
ERXNDL	Receive E	nd Registe	er Low Byte	(ERXND<7	:0>)				63
ERXNDH	— — — Receive End Register High Byte (ERXND<12:8>)							63	
EDMASTL	DMA Start Register Low Byte (EDMAST<7:0>)							63	
EDMASTH		—		DMA Start I	Register Hig	jh Byte (ED	MAST<12:8	8>)	63
EDMANDL	DMA End Register Low Byte (EDMAND<7:0>)								63
EDMANDH		_	_	DMA End F	Register Hig	h Byte (EDN	/IAND<12:8	>)	63
EDMADSTL	DMA Destination Register Low Byte (EDMADST<7:0>)							63	
EDMADSTH	— — — DMA Destination Register High Byte (EDMADST<12:8>)						63		
EDMACSL	DMA Checksum Register Low Byte (EDMACS<7:0>)							63	
EDMACSH	DMA Che	cksum Reg	gister High	Byte (EDMA	CS<15:8>)				63

Legend: — = unimplemented. Shaded cells are not used.

### 18.10 Module Resets

The Ethernet module provides selective module Resets:

- Transmit Only Reset
- Receive Only Reset

#### 18.10.1 MICROCONTROLLER RESETS

Following any standard Reset event, the Ethernet module returns to a known state. The contents of the Ethernet buffer memory are unknown. All SFR and PHY registers are loaded with their specified Reset values, depending on the type of Reset event. However, the PHY registers must not be accessed until the PHY start-up timer has expired and the PHYRDY bit (ESTAT<0>) becomes set, or at least 1 ms has passed since the ETHEN bit was set. For more details, see **Section 18.1.3.1 "Start-up Timer"**.

### 18.10.2 TRANSMIT ONLY RESET

The Transmit Only Reset is performed by writing a '1' to the TXRST bit (ECON1<7>). This resets the transmit logic only. Other register and control blocks, such as buffer management and host interface, are not affected by a Transmit Only Reset event. To return to normal operation, the TXRST bit must be cleared in software. After clearing TXRST, firmware must not write to any Ethernet module SFRs for at least 1.6  $\mu$ s. After the delay, normal operation can resume.

#### 18.10.3 RECEIVE ONLY RESET

The Receive Only Reset is performed by writing a '1' to the RXRST bit (ECON1<6>). This action resets receive logic only. Other register and control blocks, such as the buffer management and host interface blocks, are not affected by a Receive Only Reset event. To return to normal operation, the RXRST bit is cleared in software. After clearing RXRST, firmware must not write to any Ethernet module SFRs for at least 1.6  $\mu$ s. After the delay, normal operation can resume.

NOTES:

### 19.0 MASTER SYNCHRONOUS SERIAL PORT (MSSP) MODULE

### 19.1 Master SSP (MSSP) Module Overview

The Master Synchronous Serial Port (MSSP) module is a serial interface, useful for communicating with other peripheral or microcontroller devices. These peripheral devices may be serial EEPROMs, shift registers, display drivers, A/D converters, etc. The MSSP module can operate in one of two modes:

- Serial Peripheral Interface (SPI)
- Inter-Integrated Circuit (I<sup>2</sup>C<sup>™</sup>)
  - Full Master mode
  - Slave mode (with general address call)

The  $\mathrm{I}^2\mathrm{C}$  interface supports the following modes in hardware:

- · Master mode
- Multi-Master mode
- Slave mode

The 64-pin and 80-pin devices of the PIC18F97J60 family have one MSSP module, designated as MSSP1. The 100-pin devices have two MSSP modules, designated as MSSP1 and MSSP2. Each module operates independently of the other.

Note:	Throughout this section, generic refer- ences to an MSSP module in any of its operating modes may be interpreted as being equally applicable to MSSP1 or MSSP2. Register names and module I/O signals use the generic designator 'x' to
	indicate the use of a numeral to distinguish a particular module when required. Control bit names are not individuated.

### **19.2 Control Registers**

Each MSSP module has three associated control registers. These include a status register (SSPxSTAT) and two control registers (SSPxCON1 and SSPxCON2). The use of these registers and their individual configuration bits differ significantly depending on whether the MSSP module is operating in SPI or  $I^2C$  mode.

Additional details are provided under the individual sections.

Note:	In devices with more than one MSSP
	module, it is very important to pay close
	attention to the SSPxCON register names.
	SSP1CON1 and SSP1CON2 control
	different operational aspects of the same
	module, while SSP1CON1 and
	SSP2CON1 control the same features for
	two different modules.

### 19.3 SPI Mode

The SPI mode allows 8 bits of data to be synchronously transmitted and received simultaneously. All four modes of SPI are supported. To accomplish communication, typically three pins are used:


- Serial Data Out (SDOx) RC5/SDO1 (or RD4/SDO2 for 100-pin devices)
- Serial Data In (SDIx) RC4/SDI1/SDA1 (or RD5/SDI2/SDA2 for 100-pin devices)
- Serial Clock (SCKx) RC3/SCK1/SCL1 (or RD6/SCK2/SCL2 for 100-pin devices)

Additionally, a fourth pin may be used when in a Slave mode of operation:

 Slave Select (SSx) – RF7/SS1 (or RD7/SS2 for 100-pin devices)

Figure 19-1 shows the block diagram of the MSSP module when operating in SPI mode.

FIGURE 19-1:	MSSP BLOCK DIAGRAM
	(SPI MODE)



### 19.3.1 REGISTERS

Each MSSP module has four registers for SPI mode operation. These are:

- MSSPx Control Register 1 (SSPxCON1)
- MSSPx Status Register (SSPxSTAT)
- Serial Receive/Transmit Buffer Register (SSPxBUF)
- MSSPx Shift Register (SSPxSR) Not directly accessible

SSPxCON1 and SSPxSTAT are the control and status registers in SPI mode operation. The SSPxCON1 register is readable and writable. The lower 6 bits of the SSPxSTAT are read-only. The upper two bits of the SSPxSTAT are read/write.

SSPxSR is the shift register used for shifting data in or out. SSPxBUF is the buffer register to which data bytes are written to or read from.

In receive operations, SSPxSR and SSPxBUF together create a double-buffered receiver. When SSPxSR receives a complete byte, it is transferred to SSPxBUF and the SSPxIF interrupt is set.

During transmission, the SSPxBUF is not double-buffered. A write to SSPxBUF will write to both SSPxBUF and SSPxSR.

### REGISTER 19-1: SSPxSTAT: MSSPx STATUS REGISTER (SPI MODE)

R/W-0	R/W-0	R-0	R-0	R-0	R-0	R-0	R-0				
SMP	CKE <sup>(1)</sup>	D/A	Р	S	R/W	UA	BF				
bit 7		•					bit				
Legend:											
R = Readab	le bit	W = Writable	bit	U = Unimplem	nented bit, rea	d as '0'					
-n = Value a	t POR	'1' = Bit is set		'0' = Bit is clea	ared	x = Bit is unkr	nown				
bit 7	SMP: Samp	le bit									
	SPI Master										
		L = Input data sampled at end of data output time									
	-	SPI Slave mode:									
		e cleared when	SPI is used i	n Slave mode.							
bit 6	CKE: SPI Clock Select bit <sup>(1)</sup>										
	1 = Transmit occurs on transition from active to Idle clock state										
	_	t occurs on trans	ition from Id	le to active clock	state						
bit 5	D/A: Data/A										
	Used in I <sup>2</sup> C	mode only.									
bit 4	P: Stop bit										
		mode only. This	bit is cleared	d when the MSS	P module is di	sabled, SSPEN	is cleared.				
bit 3	S: Start bit										
	Used in I <sup>2</sup> C	•									
bit 2		R/W: Read/Write Information bit									
	Used in I <sup>2</sup> C	•									
bit 1	UA: Update										
	Used in I <sup>2</sup> C	3									
bit 0		ull Status bit (Re		only)							
		complete, SSP> not complete, S		moty							
		not complete, S		sinply							
Note 1: P	olarity of clock s	state is set by the	CKP bit (S	SPxCON1<4>)							

#### REGISTER 19-2: SSPxCON1: MSSPx CONTROL REGISTER 1 (SPI MODE)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
WCOL	SSPOV <sup>(1)</sup>	SSPEN <sup>(2)</sup>	CKP	SSPM3 <sup>(3)</sup>	SSPM2 <sup>(3)</sup>	SSPM1 <sup>(3)</sup>	SSPM0 <sup>(3)</sup>		
bit 7	·					•	bit (		
Legend:									
R = Readabl		W = Writable		-	mented bit, read				
-n = Value at POR		'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unki	nown		
1.11.7				· · · · · · · · · · · · · · · · · · ·					
bit 7		Collision Dete	-	• •		in the second (marked	the cleared in		
	software)	•	s written whil	e it is still transr	nitting the prev	ious word (mus	t be cleared in		
	0 = No collis								
bit 6	SSPOV: Rec	eive Overflow I	ndicator bit <sup>(1)</sup>	)					
	SPI Slave mo								
				PxBUF register					
				Overflow can o					
	software)		Unity transm	itting data, to a	avoid setting d	wennow (musi	be cleared in		
	0 = No overf								
bit 5	SSPEN: Mas	ter Synchronou	is Serial Port	: Enable bit <sup>(2)</sup>					
		nables serial port and configures SCKx, SDOx, SDIx and $\overline{SSx}$ as serial port pins							
	0 = Disables	serial port and	configures th	iese pins as I/O	port pins				
bit 4	CKP: Clock Polarity Select bit								
		for clock is a h	•						
h:+ 0 0		for clock is a lo		sial David Maria	0 - 1 + + :+- (3)				
bit 3-0				erial Port Mode		-			
				n, <u>SSx</u> pin contr in, SSx pin cont		x can be used a	is I/O pin		
		/laster mode, cl							
		/laster mode, cl		•					
		/laster mode, cl							
	0000 <b>= SPI N</b>	/laster mode, cl	ock = Fosc/4	4					
Note 1: In	n Master mode, th	ne overflow bit i	s not set sind	ce each new red	ception (and tra	Insmission) is ir	nitiated by		
W	riting to the SSP	xBUF register.			-	-	-		
0. \/	Ihan this hit is an	chlad thas a		roporty configu		at.			

- 2: When this bit is enabled, these pins must be properly configured as input or output.
- **3:** Bit combinations not specifically listed here are either reserved or implemented in  $I^2C^{\text{TM}}$  mode only.

### 19.3.2 OPERATION

When initializing the SPI, several options need to be specified. This is done by programming the appropriate control bits (SSPxCON1<5:0> and SSPxSTAT<7:6>). These control bits allow the following to be specified:

- Master mode (SCKx is the clock output)
- Slave mode (SCKx is the clock input)
- Clock Polarity (Idle state of SCKx)
- Data Input Sample Phase (middle or end of data output time)
- Clock Edge (output data on rising/falling edge of SCKx)
- Clock Rate (Master mode only)
- · Slave Select mode (Slave mode only)

Each MSSP module consists of a transmit/receive shift register (SSPxSR) and a buffer register (SSPxBUF). The SSPxSR shifts the data in and out of the device, MSb first. The SSPxBUF holds the data that was written to the SSPxSR until the received data is ready. Once the 8 bits of data have been received, that byte is moved to the SSPxBUF register. Then, the Buffer Full detect bit, BF (SSPxSTAT<0>), and the interrupt flag bit, SSPxIF, are set. This double-buffering of the received data (SSPxBUF) allows the next byte to start reception before reading the data that was just received. Any write to the SSPxBUF register during transmission/reception of data will be ignored and the Write Collision detect bit, WCOL (SSPxCON1<7>), will be set. User software must clear the WCOL bit so that it can be determined if the following write(s) to the SSPxBUF register completed successfully.

When the application software is expecting to receive valid data, the SSPxBUF should be read before the next byte of data to transfer is written to the SSPxBUF. The Buffer Full bit, BF (SSPxSTAT<0>), indicates when SSPxBUF has been loaded with the received data (transmission is complete). When the SSPxBUF is read, the BF bit is cleared. This data may be irrelevant if the SPI is only a transmitter. Generally, the MSSP interrupt is used to determine when the transmission/reception has completed. The SSPxBUF must be read and/or written. If the interrupt method is not going to be used, then software polling can be done to ensure that a write collision does not occur. Example 19-1 shows the loading of the SSP1BUF (SSP1SR) for data transmission.

The SSPxSR is not directly readable or writable and can only be accessed by addressing the SSPxBUF register. Additionally, the SSPxSTAT register indicates the various status conditions.

### EXAMPLE 19-1: LOADING THE SSP1BUF (SSP1SR) REGISTER

LOOP	BTFSS BRA MOVF	LOOP	;Has data been received (transmit complete)? ;No ;WREG reg = contents of SSP1BUF
	MOVWF	RXDATA	;Save in user RAM, if data is meaningful
	MOVF MOVWF	TXDATA, W SSP1BUF	;W reg = contents of TXDATA ;New data to xmit

### 19.3.3 ENABLING SPI I/O

To enable the serial port, MSSP Enable bit, SSPEN (SSPxCON1<5>), must be set. To reset or reconfigure SPI mode, clear the SSPEN bit, reinitialize the SSPxCON registers and then set the SSPEN bit. This configures the SDIx, SDOx, SCKx and SSx pins as serial port pins. For the pins to behave as the serial port function, some must have their data direction bits (in the TRIS register) appropriately programmed as follows:


- SDIx is automatically controlled by the SPI module
- SDOx must have TRISC<5> (or TRISD<4>) bit cleared
- SCKx (Master mode) must have TRISC<3> (or TRISD<6>) bit cleared
- SCKx (Slave mode) must have TRISC<3> (or TRISD<6>) bit set
- SSx must have TRISF<7> (or TRISD<7>) bit set

Any serial port function that is not desired may be overridden by programming the corresponding data direction (TRIS) register to the opposite value.

### 19.3.4 TYPICAL CONNECTION

Figure 19-2 shows a typical connection between two microcontrollers. The master controller (Processor 1) initiates the data transfer by sending the SCKx signal. Data is shifted out of both shift registers on their programmed clock edge and latched on the opposite edge of the clock. Both processors should be programmed to the same Clock Polarity (CKP), then both controllers would send and receive data at the same time. Whether the data is meaningful (or dummy data) depends on the application software. This leads to three scenarios for data transmission:

- · Master sends data Slave sends dummy data
- Master sends data Slave sends data
- · Master sends dummy data Slave sends data



#### FIGURE 19-2: SPI MASTER/SLAVE CONNECTION

### 19.3.5 MASTER MODE

The master can initiate the data transfer at any time because it controls the SCKx. The master determines when the slave (Processor 2, Figure 19-2) will broadcast data by the software protocol.

In Master mode, the data is transmitted/received as soon as the SSPxBUF register is written to. If the SPI is only going to receive, the SDOx output could be disabled (programmed as an input). The SSPxSR register will continue to shift in the signal present on the SDIx pin at the programmed clock rate. As each byte is received, it will be loaded into the SSPxBUF register as if a normal received byte (interrupts and status bits appropriately set). This could be useful in receiver applications as a "Line Activity Monitor" mode. The clock polarity is selected by appropriately programming the CKP bit (SSPxCON1<4>). This then, would give waveforms for SPI communication as shown in Figure 19-3, Figure 19-5 and Figure 19-6, where the MSB is transmitted first. In Master mode, the SPI clock rate (bit rate) is user-programmable to be one of the following:

- Fosc/4 (or Tcy)
- Fosc/16 (or 4 Tcy)
- Fosc/64 (or 16 Tcy)
- Timer2 output/2

This allows a maximum data rate (at 40 MHz) of 10.00 Mbps.

Figure 19-3 shows the waveforms for Master mode. When the CKE bit is set, the SDOx data is valid before there is a clock edge on SCKx. The change of the input sample is shown based on the state of the SMP bit. The time when the SSPxBUF is loaded with the received data is shown.




FIGURE 19-3: SPI MODE WAVEFORM (MASTER MODE)

### 19.3.6 SLAVE MODE

In Slave mode, the data is transmitted and received as the external clock pulses appear on SCKx. When the last bit is latched, the SSPxIF interrupt flag bit is set.

Before enabling the module in SPI Slave mode, the clock line must match the proper Idle state. The clock line can be observed by reading the SCKx pin. The Idle state is determined by the CKP bit (SSPxCON1<4>).

While in Slave mode, the external clock is supplied by the external clock source on the SCKx pin. This external clock must meet the minimum high and low times as specified in the electrical specifications.

While in Sleep mode, the slave can transmit/receive data. When a byte is received, the device will wake-up from Sleep.

### 19.3.7 SLAVE SELECT SYNCHRONIZATION

The  $\overline{SSx}$  pin allows a Synchronous Slave mode. The SPI must be in Slave mode with  $\overline{SSx}$  pin control enabled (SSPxCON1<3:0> = 04h). When the  $\overline{SSx}$  pin is low, transmission and reception are enabled and the


SDOx pin is driven. When the SSx pin goes high, the SDOx pin is no longer driven, even if in the middle of a transmitted byte, and becomes a floating output. External pull-up/pull-down resistors may be desirable depending on the application.


- Note 1: When the SPI is in Slave mode with SSx pin control enabled (SSPxCON1<3:0> = 0100), the SPI module will reset if the SSx pin is set to VDD.
  - 2: If the SPI is used in Slave mode with CKE set, then the SSx pin control must be enabled.

When the SPI module resets, the bit counter is forced to '0'. This can be done by either forcing the SSx pin to a high level or clearing the SSPEN bit.


To emulate two-wire communication, the SDOx pin can be connected to the SDIx pin. When the SPI needs to operate as a receiver, the SDOx pin can be configured as an input. This disables transmissions from the SDOx. The SDIx can always be left as an input (SDIx function) since it cannot create a bus conflict.

### FIGURE 19-4: SLAVE SYNCHRONIZATION WAVEFORM





### FIGURE 19-6: SPI MODE WAVEFORM (SLAVE MODE WITH CKE = 1)



#### 19.3.8 OPERATION IN POWER-MANAGED MODES

In SPI Master mode, module clocks may be operating at a different speed than when in full power mode. In the case of Sleep mode, all clocks are halted.

In Idle modes, a clock is provided to the peripherals. That clock should be from the primary clock source, the secondary clock (Timer1 oscillator at 32.768 kHz) or the INTRC source. See **Section 2.7 "Clock Sources and Oscillator Switching"** for additional information.

In most cases, the speed that the master clocks SPI data is not important; however, this should be evaluated for each system.

If MSSP interrupts are enabled, they can wake the controller from Sleep mode, or one of the Idle modes, when the master completes sending data. If an exit from Sleep or Idle mode is not desired, MSSP interrupts should be disabled.

If the Sleep mode is selected, all module clocks are halted and the transmission/reception will remain in that state until the devices wakes. After the device returns to Run mode, the module will resume transmitting and receiving data.

In SPI Slave mode, the SPI Transmit/Receive Shift register operates asynchronously to the device. This allows the device to be placed in any power-managed mode and data to be shifted into the SPI Transmit/Receive Shift register. When all 8 bits have been received, the MSSP interrupt flag bit will be set, and if enabled, will wake the device.

### 19.3.9 EFFECTS OF A RESET

A Reset disables the MSSP module and terminates the current transfer.

### 19.3.10 BUS MODE COMPATIBILITY

Table 19-1 shows the compatibility between the standard SPI modes and the states of the CKP and CKE control bits.

TABLE 19-1:	SPI BUS MODES
-------------	---------------

Standard SPI Mode	Control E	Bits State	
Terminology	СКР	СКЕ	
0, 0	0	1	
0, 1	0	0	
1, 0	1	1	
1, 1	1	0	

There is also an SMP bit which controls when the data is sampled.

### 19.3.11 SPI CLOCK SPEED AND MODULE INTERACTIONS

Because MSSP1 and MSSP2 are independent modules, they can operate simultaneously at different data rates. Setting the SSPM3:SSPM0 bits of the SSPxCON1 register determines the rate for the corresponding module.

An exception is when both modules use Timer2 as a time base in Master mode. In this instance, any changes to the Timer2 operation will affect both MSSP modules equally. If different bit rates are required for each module, the user should select one of the other three time base options for one of the modules.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	<b>GIE/GIEH</b>	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR3	SSP2IF <sup>(1)</sup>	BCL2IF	RC2IF	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE <sup>(1)</sup>	BCL2IE	RC2IE	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP <sup>(1)</sup>	BCL2IP	RC2IP	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
TRISC	TRISC7	TRISC6	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	61
TRISD	TRISD7 <sup>(1)</sup>	TRISD6 <sup>(1)</sup>	TRISD5 <sup>(1)</sup>	TRISD4 <sup>(1)</sup>	TRISD3	TRISD2	TRISD1	TRISD0	61
TRISF	TRISF7	TRISF6	TRISF5	TRISF4	TRISF3	TRISF2	TRISF1	TRISF0	61
SSP1BUF	MSSP1 Re	ceive Buffer	/Transmit R	egister					60
SSP1CON1	WCOL	SSPOV	SSPEN	CKP	SSPM3	SSPM2	SSPM1	SSPM0	60
SSP1STAT	SMP	CKE	D/Ā	Р	S	R/W	UA	BF	60
SSP2BUF MSSP2 Receive Buffer/Transmit Register									63
SSP2CON1	WCOL	SSPOV	SSPEN	CKP	SSPM3	SSPM2	SSPM1	SSPM0	63
SSP2STAT	SMP	CKE	D/A	Р	S	R/W	UA	BF	63

### TABLE 19-2: REGISTERS ASSOCIATED WITH SPI OPERATION

Legend: Shaded cells are not used by the MSSP module in SPI mode.

Note 1: These bits are only available in 100-pin devices; otherwise, they are unimplemented and read as '0'.

### 19.4 I<sup>2</sup>C Mode


The MSSP module in I<sup>2</sup>C mode fully implements all master and slave functions (including general call support) and provides interrupts on Start and Stop bits in hardware to determine a free bus (multi-master function). The MSSP module implements the standard mode specifications, as well as 7-bit and 10-bit addressing.

Two pins are used for data transfer:

- Serial clock (SCLx) RC3/SCK1/SCL1 (or RD6/SCK2/SCL2 for 100-pin devices)
- Serial data (SDAx) RC4/SDI1/SDA1 (or RD5/SDI2/SDA2 for 100-pin devices)

The user must configure these pins as inputs by setting the TRISC<4:3> or TRISD<5:4> bits.

### FIGURE 19-7: MSSP BLOCK DIAGRAM (I<sup>2</sup>C™ MODE)



### 19.4.1 REGISTERS

The MSSP module has six registers for  $\mathsf{I}^2\mathsf{C}$  operation. These are:

- MSSPx Control Register 1 (SSPxCON1)
- MSSPx Control Register 2 (SSPxCON2)
- MSSPx Status Register (SSPxSTAT)
- MSSPx Receive Buffer/Transmit Register (SSPxBUF)
- MSSPx Shift Register (SSPxSR) Not directly accessible
- MSSPx Address Register (SSPxADD)

SSPxCON1, SSPxCON2 and SSPxSTAT are the control and status registers in I<sup>2</sup>C mode operation. The SSPxCON1 and SSPxCON2 registers are readable and writable. The lower 6 bits of the SSPxSTAT are read-only. The upper two bits of the SSPxSTAT are read/write.

Many of the bits in SSPxCON2 assume different functions, depending on whether the module is operating in Master or Slave mode. SSPxCON2<5:1> also assume different names in Slave mode. The different aspects of SSPxCON2 are shown in Register 19-5 (for Master mode) and Register 19-6 (Slave mode).

SSPxSR is the shift register used for shifting data in or out. SSPxBUF is the buffer register to which data bytes are written to or read from.

SSPxADD register holds the slave device address when the MSSP is configured in  $I^2C$  Slave mode. When the MSSP is configured in Master mode, the lower seven bits of SSPxADD act as the Baud Rate Generator reload value.

In receive operations, SSPxSR and SSPxBUF together create a double-buffered receiver. When SSPxSR receives a complete byte, it is transferred to SSPxBUF and the SSPxIF interrupt is set.

During transmission, the SSPxBUF is not double-buffered. A write to SSPxBUF will write to both SSPxBUF and SSPxSR.

R/W-0	R/W-0	R-0	R-0	R-0		R-0	R-0	R-0		
SMP	CKE	D/A	P <sup>(1)</sup>	S <sup>(1)</sup>		R/W <sup>(2,3)</sup>	UA	BF		
bit 7								bit		
Legend:	a hit	\\/ _ \\/::tab	la hit			unted bit was	d aa (0'			
R = Readabl		W = Writabl		-		ented bit, rea				
-n = Value at	PUR	'1' = Bit is s	et	'0' = Bit is	clear	ed	x = Bit is unkr	IOWN		
bit 7	SMP: Slew	Rate Control b	oit							
		Slave mode:								
			bled for Standa bled for High-S				1 MHz)			
bit 6	CKE: SMBu		0			,				
		Slave mode:								
		SMBus specifi SMBus specif								
bit 5	D/A: Data/A	-								
	In Master mode:									
	Reserved.									
	In Slave mode: 1 = Indicates that the last byte received or transmitted was data									
			byte received c							
bit 4	P: Stop bit <sup>(1</sup>									
		s that a Stop b was not detec	it has been det ted last	ected last						
bit 3	S: Start bit <sup>(1</sup>									
			oit has been de	ected last						
<b>h</b> # 0		was not detec		(2.3)						
bit 2	In Slave mo		ion bit (I <sup>2</sup> C mod	ie only)(=,=,						
	1 = Read	<u>uc.</u>								
	0 = Write									
	In Master mode: 1 = Transmit is in progress									
		t is not in prog								
bit 1	UA: Update	Address bit (1	0-Bit Slave mo	de only)						
	<ul> <li>1 = Indicates that the user needs to update the address in the SSPxADD register</li> <li>0 = Address does not need to be updated</li> </ul>									
bit 0		Full Status bit		4						
	In Transmit mode:									
	1 = SSPxBL 0 = SSPxBL									
	In Receive r									
	1 = SSPxBL	JF is full (does	not include the							
	0 = SSPxBL	JF is empty (de	oes not include	the ACK and	d Sto	p bits)				
	his bit is cleared									
			nation following		lress	match. This	bit is only valid	from the		

### REGISTER 19-3: SSPxSTAT: MSSPx STATUS REGISTER (I<sup>2</sup>C<sup>™</sup> MODE)

address match to the next Start bit, Stop bit or not ACK bit.

3: ORing this bit with SEN, RSEN, PEN, RCEN or ACKEN will indicate if the MSSP is in Active mode.

### REGISTER 19-4: SSPxCON1: MSSPx CONTROL REGISTER 1 (I<sup>2</sup>C<sup>™</sup> MODE)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
WCOL	SSPOV	SSPEN	CKP	SSPM3	SSPM2	SSPM1	SSPM0		
bit 7							bit C		
Legend:									
R = Readable	e bit	W = Writable	bit	U = Unimpler	mented bit, read	d as '0'			
-n = Value at	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown		
bit 7	WCOL: Write	e Collision Dete	ct bit						
	In Master Transmit mode:								
	1 = A write to the SSPxBUF register was attempted while the I <sup>2</sup> C conditions were not valid for								
	transmission to be started (must be cleared in software)								
	0 = No collision								
	In Slave Trar 1 = The SSF software	PxBUF register	is written whil	e it is still transı	mitting the prev	ious word (mus	t be cleared ir		
	0 = No collision								
	In Receive mode (Master or Slave modes):								
	This is a "don't care" bit.								
bit 6	SSPOV: Receive Overflow Indicator bit								
	In Receive mode: 1 = A byte is received while the SSPxBUF register is still holding the previous byte (must be cleare in software)								
	0 = No overflow								
	<u>In Transmit mode:</u> This is a "don't care" bit in Transmit mode.								
bit 5	SSPEN: Master Synchronous Serial Port Enable bit								
	<ul> <li>1 = Enables the serial port and configures the SDAx and SCLx pins as the serial port pins<sup>(1)</sup></li> <li>0 = Disables serial port and configures these pins as I/O port pins<sup>(1)</sup></li> </ul>								
bit 4	CKP: SCKx Release Control bit								
	In Slave mode: 1 = Releases clock 0 = Holds slock (stratsh), used to shourd data actual time								
	<ul> <li>0 = Holds clock low (clock stretch), used to ensure data setup time</li> <li><u>In Master mode:</u></li> <li>Unused in this mode.</li> </ul>								
bit 3-0	SSPM3:SSPM0: Master Synchronous Serial Port Mode Select bits								
	1111 = I <sup>2</sup> C Slave mode, 10-bit addressing with Start and Stop bit interrupts enabled <sup>(2)</sup> 1110 = I <sup>2</sup> C Slave mode, 7-bit addressing with Start and Stop bit interrupts enabled <sup>(2)</sup> 1011 = I <sup>2</sup> C Firmware Controlled Master mode (slave Idle) <sup>(2)</sup> 1000 = I <sup>2</sup> C Master mode, clock = Fosc/(4 * (SSPADD + 1)) <sup>(2)</sup> 0111 = I <sup>2</sup> C Slave mode, 10-bit addressing <sup>(2)</sup> 0110 = I <sup>2</sup> C Slave mode, 7-bit addressing <sup>(2)</sup>								

2: Bit combinations not specifically listed here are either reserved or implemented in SPI mode only.

### REGISTER 19-5: SSPxCON2: MSSPx CONTROL REGISTER 2 (I<sup>2</sup>C<sup>™</sup> MASTER MODE)

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
GCEN	ACKSTAT	ACKDT <sup>(1)</sup>	ACKEN <sup>(2)</sup>	RCEN <sup>(2)</sup>	PEN <sup>(2)</sup>	RSEN <sup>(2)</sup>	SEN <sup>(2)</sup>		
bit 7			·				bit (		
Logondi									
Legend:	- I- :+		1. 14			-1 (0)			
R = Readable		W = Writable							
-n = Value at	POR	'1' = Bit is set		$0^{\circ} = Bit is clea$	ared	x = Bit is unkn	iown		
bit 7	GCEN: Gene	ral Call Enable	bit (Slave mo	de only)					
	Unused in Master mode.								
bit 6 ACKSTAT: Acknowledge Status bit (Master Transmit mode on									
	1 = Acknowledge was not received from slave								
		edge was receiv							
bit 5	ACKDT: Acknowledge Data bit (Master Receive mode only) <sup>(1)</sup>								
	1 = Not Acknowledge								
	0 = Acknowledge								
bit 4	<b>ACKEN:</b> Acknowledge Sequence Enable bit <sup>(2)</sup> 1 = Initiate Acknowledge sequence on SDAx and SCLx pins and transmit ACKDT data bi								
		Acknowledge s		SDAX and S	CLX pins an	a transmit ACK	UI data di		
		edge sequence	•						
bit 3	RCEN: Receive Enable bit (Master Receive mode only) <sup>(2)</sup>								
		Receive mode							
bit 2	PEN: Stop Condition Enable bit <sup>(2)</sup>								
	1 = Initiate St 0 = Stop cond		n SDAx and SO	CLx pins. Autor	natically clear	ed by hardware.			
bit 1	RSEN: Repeated Start Condition Enable bit <sup>(2)</sup>								
	<ul> <li>1 = Initiate Repeated Start condition on SDAx and SCLx pins. Automatically cleared by hardware.</li> <li>0 = Repeated Start condition Idle</li> </ul>								
bit 0	SEN: Start Condition Enable/Stretch Enable bit <sup>(2)</sup>								
	1 = Initiate St 0 = Start cond		n SDAx and S	CLx pins. Autor	matically clear	ed by hardware.			
Note 1: Va			en the user init	iates an Ackno	wledge seque	ence at the end c	of a receiv		

**2:** If the I<sup>2</sup>C module is active, these bits may not be set (no spooling) and the SSPxBUF may not be written (or writes to the SSPxBUF are disabled).

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
GCEN	ACKSTAT	ADMSK5	ADMSK4	ADMSK3	ADMSK2	ADMSK1	SEN <sup>(1)</sup>		
bit 7							bit C		
Legend:									
R = Readable	bit	W = Writable	hit	II = I Inimpler	nented bit, read	l as 'O'			
-n = Value at POR		'1' = Bit is set		'0' = Bit is cleared		x = Bit is unknown			
-									
bit 7	GCEN: General Call Enable bit (Slave mode only)								
		terrupt when a all address dis		ddress (0000h	) is received in	the SSPxSR			
bit 6	ACKSTAT: Acknowledge Status bit								
	Unused in Slave mode.								
bit 5-2	ADMSK5:ADMSK2: Slave Address Mask Select bits								
	•	of correspondir	•	xADD enabled xADD disabled					
bit 1	ADMSK1: Slave Address Least Significant Mask Select bit								
	In 7-Bit Addressing mode:								
	1 = Masking of SSPxADD<1> is only enabled								
	0 = Masking of SSPxADD<1> is only disabled								
	In 10-Bit Addressing mode: 1 = Masking of SSPxADD<1:0> enabled								
	0 = Masking of SSPxADD<1:0> disabled								
bit 0	SEN: Stretch Enable bit <sup>(1)</sup>								
	<ul> <li>1 = Clock stretching is enabled for both slave transmit and slave receive (stretch enabled)</li> <li>0 = Clock stretching is disabled</li> </ul>								

### REGISTER 19-6: SSPxCON2: MSSPx CONTROL REGISTER 2 (I<sup>2</sup>C<sup>™</sup> SLAVE MODE)

**Note 1:** If the I<sup>2</sup>C module is active, this bit may not be set (no spooling) and the SSPxBUF may not be written (or writes to the SSPxBUF are disabled).

### 19.4.2 OPERATION

The MSSP module functions are enabled by setting the MSSP Enable bit, SSPEN (SSPxCON1<5>).

The SSPxCON1 register allows control of the  $I^2C$  operation. Four mode selection bits (SSPxCON1<3:0>) allow one of the following  $I^2C$  modes to be selected:

- I<sup>2</sup>C Master mode, clock = (Fosc/4) x (SSPxADD + 1)
- I<sup>2</sup>C Slave mode (7-bit addressing)
- I<sup>2</sup>C Slave mode (10-bit addressing)
- I<sup>2</sup>C Slave mode (7-bit addressing) with Start and Stop bit interrupts enabled
- I<sup>2</sup>C Slave mode (10-bit addressing) with Start and Stop bit interrupts enabled
- I<sup>2</sup>C Firmware Controlled Master mode, slave is Idle

Selection of any I<sup>2</sup>C mode, with the SSPEN bit set, forces the SCLx and SDAx pins to be open-drain, provided these pins are programmed to inputs by setting the appropriate TRISC or TRISD bits. To ensure proper operation of the module, pull-up resistors must be provided externally to the SCLx and SDAx pins.

### 19.4.3 SLAVE MODE

In Slave mode, the SCLx and SDAx pins must be configured as inputs (TRISC<4:3> or TRISD<5:4> are set). The MSSP module will override the input state with the output data when required (slave-transmitter).

The I<sup>2</sup>C Slave mode hardware will always generate an interrupt on an exact address match. In addition, address masking will also allow the hardware to generate an interrupt for more than one address (up to 31 in 7-bit addressing, and up to 63 in 10-bit addressing). Through the mode select bits, the user can also choose to interrupt on Start and Stop bits.

When an address is matched, or the data transfer after an address match is received, the hardware automatically will generate the Acknowledge (ACK) pulse and load the SSPxBUF register with the received value currently in the SSPxSR register.

Any combination of the following conditions will cause the MSSP module not to give this ACK pulse:

- The Buffer Full bit, BF (SSPxSTAT<0>), was set before the transfer was received.
- The MSSP Overflow bit, SSPOV (SSPxCON1<6>), was set before the transfer was received.

In this case, the SSPxSR register value is not loaded into the SSPxBUF, but bit SSPxIF is set. The BF bit is cleared by reading the SSPxBUF register, while bit SSPOV is cleared through software. The SCLx clock input must have a minimum high and low for proper operation. The high and low times of the  $I^2C$  specification, as well as the requirement of the MSSP module, are shown in timing parameter 100 and parameter 101.

### 19.4.3.1 Addressing

Once the MSSP module has been enabled, it waits for a Start condition to occur. Following the Start condition, the 8 bits are shifted into the SSPxSR register. All incoming bits are sampled with the rising edge of the clock (SCLx) line. The value of register SSPxSR<7:1> is compared to the value of the SSPxADD register. The address is compared on the falling edge of the eighth clock (SCLx) pulse. If the addresses match and the BF and SSPOV bits are clear, the following events occur:

- 1. The SSPxSR register value is loaded into the SSPxBUF register.
- 2. The Buffer Full bit, BF, is set.
- 3. An ACK pulse is generated.
- 4. The MSSP Interrupt Flag bit, SSPxIF, is set (and the interrupt is generated, if enabled) on the falling edge of the ninth SCLx pulse.

In 10-Bit Addressing mode, two address bytes need to be received by the slave. The five Most Significant bits (MSbs) of the first address byte specify if this is a 10-bit address. Bit  $R/\overline{W}$  (SSPxSTAT<2>) must specify a write so the slave device will receive the second address byte. For a 10-bit address, the first byte would equal '11110 A9 A8 0', where 'A9' and 'A8' are the two MSbs of the address. The sequence of events for 10-bit addressing is as follows, with steps 7 through 9 for the slave-transmitter:

- 1. Receive first (high) byte of address (bits SSPxIF, BF and UA are set).
- 2. Update the SSPxADD register with second (low) byte of address (clears bit UA and releases the SCLx line).
- 3. Read the SSPxBUF register (clears bit BF) and clear flag bit, SSPxIF.
- 4. Receive second (low) byte of address (bits SSPxIF, BF and UA are set).
- 5. Update the SSPxADD register with the first (high) byte of address. If match releases SCLx line, this will clear bit UA.
- 6. Read the SSPxBUF register (clears bit BF) and clear flag bit, SSPxIF.
- 7. Receive Repeated Start condition.
- 8. Receive first (high) byte of address (bits SSPxIF and BF are set).
- 9. Read the SSPxBUF register (clears bit BF) and clear flag bit SSPxIF.

### 19.4.3.2 Address Masking

Masking an address bit causes that bit to become a "don't care". When one address bit is masked, two addresses will be Acknowledged and cause an interrupt. It is possible to mask more than one address bit at a time, which makes it possible to Acknowledge up to 31 addresses in 7-bit mode, and up to 63 addresses in 10-bit mode (see Example 19-2).

The  $l^2C$  Slave behaves the same way whether address masking is used or not. However, when address masking is used, the  $l^2C$  slave can Acknowledge multiple addresses and cause interrupts. When this occurs, it is necessary to determine which address caused the interrupt by checking SSPxBUF.

In 7-Bit Addressing mode, address mask bits, ADMSK<5:1> (SSPxCON2<5:1>), mask the corresponding address bits in the SSPxADD register. For any ADMSK bits that are set (ADMSK<n> = 1), the corresponding address bit is ignored (SSPxADD<n> = x). For the module to issue an address Acknowledge, it is sufficient to match only on addresses that do not have an active address mask.

EXAMPLE 19-2: ADDRESS MASKING EXAMPLES

#### 7-Bit Addressing:

SSPxADD<7:1> = A0h (1010000) (SSPxADD<0> is assumed to be '0') ADMSK<5:1> = 00111 Addresses Acknowledged: A0h, A2h, A4h, A6h, A8h, AAh, ACh, AEh

#### 10-Bit Addressing:

SSPxADD<7:0> = A0h (10100000) (the two MSb of the address are ignored in this example since they are not affected by masking) ADMSK<5:1> = 00111

Addresses Acknowledged: A0h, A1h, A2h, A3h, A4h, A5h, A6h, A7h, A8h, A9h, AAh, ABh, ACh, ADh, AEh, AFh

In 10-Bit Addressing mode, bits ADMSK<5:2> mask the corresponding address bits in the SSPxADD register. In addition, ADMSK1 simultaneously masks the two LSbs of the address (SSPxADD<1:0>). For any ADMSK bits that are active (ADMSK<n> = 1), the corresponding address bit is ignored (SSPxADD<n> = x). Also note, that although in 10-Bit Addressing mode, the upper address bits reuse part of the SSPxADD register bits. The address mask bits do not interact with those bits; they only affect the lower address bits.

- Note 1: ADMSK1 masks the two Least Significant bits of the address.
  - The two Most Significant bits of the address are not affected by address masking.

### 19.4.3.3 Reception

When the R/W bit of the address byte is clear and an address match occurs, the R/W bit of the SSPxSTAT register is cleared. The received address is loaded into the SSPxBUF register and the SDAx line is held low (ACK).

When the address byte overflow condition exists, then the no Acknowledge (ACK) pulse is given. An overflow condition is defined as either bit BF (SSPxSTAT<0>) is set, or bit SSPOV (SSPxCON1<6>) is set.

An MSSP interrupt is generated for each data transfer byte. The interrupt flag bit, SSPxIF, must be cleared in software. The SSPxSTAT register is used to determine the status of the byte.


If SEN is enabled (SSPxCON2<0> = 1), SCKx/SCLx (RC3 or RD6) will be held low (clock stretch) following each data transfer. The clock must be released by setting bit, CKP (SSPxCON1<4>). See **Section 19.4.4** "**Clock Stretching**" for more details.

### 19.4.3.4 Transmission


When the R/W bit of the incoming address byte is set and an address match occurs, the R/W bit of the SSPxSTAT register is set. The received address is loaded into the SSPxBUF register. The ACK pulse will be sent on the ninth bit and pin RC3 or RD6 is held low, regardless of SEN (see **Section 19.4.4** "**Clock Stretching**" for more details). By stretching the clock, the master will be unable to assert another clock pulse until the slave is done preparing the transmit data. The transmit data must be loaded into the SSPxBUF register which also loads the SSPxSR register. Then, pin RC3 or RD6 should be enabled by setting bit, CKP (SSPxCON1<4>). The eight data bits are shifted out on the falling edge of the SCLx input. This ensures that the SDAx signal is valid during the SCLx high time (Figure 19-10).


The ACK pulse from the master-receiver is latched on the rising edge of the ninth SCLx input pulse. If the SDAx line is high (not ACK), then the data transfer is complete. In this case, when the ACK is latched by the slave, the slave logic is reset (resets SSPxSTAT register) and the slave monitors for another occurrence of the Start bit. If the SDAx line was low (ACK), the next transmit data must be loaded into the SSPxBUF register. Again, pin RC3 or RD6 must be enabled by setting bit CKP.

An MSSP interrupt is generated for each data transfer byte. The SSPxIF bit must be cleared in software and the SSPxSTAT register is used to determine the status of the byte. The SSPxIF bit is set on the falling edge of the ninth clock pulse.



### FIGURE 19-9: I<sup>2</sup>C<sup>™</sup> SLAVE MODE TIMING WITH SEN = 0 AND ADMSK<5:1> = 01011 (RECEPTION, 7-BIT ADDRESS)










FIGURE 19-12: I<sup>2</sup>C<sup>™</sup> SLAVE MODE TIMING WITH SEN = 0 AND ADMSK<5:1> = 01001 (RECEPTION, 10-BIT ADDRESS)





### 19.4.4 CLOCK STRETCHING

Both 7-Bit and 10-Bit Slave modes implement automatic clock stretching during a transmit sequence.

The SEN bit (SSPxCON2<0>) allows clock stretching to be enabled during receives. Setting SEN will cause the SCLx pin to be held low at the end of each data receive sequence.

### 19.4.4.1 Clock Stretching for 7-Bit Slave Receive Mode (SEN = 1)

In 7-Bit Slave Receive mode, <u>on</u> the falling edge of the ninth clock at the end of the ACK sequence, if the BF bit is set, the CKP bit in the SSPxCON1 register is automatically cleared, forcing the SCLx output to be held low. The CKP being cleared to '0' will assert the SCLx line low. The CKP bit must be set in the user's ISR before reception is allowed to continue. By holding the SCLx line low, the user has time to service the ISR and read the contents of the SSPxBUF before the master device can initiate another receive sequence. This will prevent buffer overruns from occurring (see Figure 19-15).

- Note 1: If the user reads the contents of the SSPxBUF before the falling edge of the ninth clock, thus clearing the BF bit, the CKP bit will not be cleared and clock stretching will not occur.
  - 2: The CKP bit can be set in software regardless of the state of the BF bit. The user should be careful to clear the BF bit in the ISR before the next receive sequence in order to prevent an overflow condition.

### 19.4.4.2 Clock Stretching for 10-Bit Slave Receive Mode (SEN = 1)

In 10-Bit Slave Receive mode during the address sequence, clock stretching automatically takes place but CKP is not cleared. During this time, if the UA bit is set after the ninth clock, clock stretching is initiated. The UA bit is set after receiving the upper byte of the 10-bit address and following the receive of the second byte of the 10-bit address with the R/W bit cleared to '0'. The release of the clock line occurs upon updating SSPxADD. Clock stretching will occur on each data receive sequence as described in 7-bit mode.

**Note:** If the user polls the UA bit and clears it by updating the SSPxADD register before the falling edge of the ninth clock occurs and if the user hasn't cleared the BF bit by reading the SSPxBUF register before that time, then the CKP bit will still NOT be asserted low. Clock stretching on the basis of the state of the BF bit only occurs during a data sequence, not an address sequence.

### 19.4.4.3 Clock Stretching for 7-Bit Slave Transmit Mode

The 7-Bit Slave Transmit mode implements clock stretching by clearing the CKP bit after the falling edge of the ninth clock, if the BF bit is clear. This occurs regardless of the state of the SEN bit.

The user's ISR must set the CKP bit before transmission is allowed to continue. By holding the SCLx line low, the user has time to service the ISR and load the contents of the SSPxBUF before the master device can initiate another transmit sequence (see Figure 19-10).

- Note 1: If the user loads the contents of SSPxBUF, setting the BF bit before the falling edge of the ninth clock, the CKP bit will not be cleared and clock stretching will not occur.
  - **2:** The CKP bit can be set in software regardless of the state of the BF bit.


### 19.4.4.4 Clock Stretching for 10-Bit Slave Transmit Mode


In 10-Bit Slave Transmit mode, clock stretching is controlled during the first two address sequences by the state of the UA bit, just as it is in 10-Bit Slave Receive mode. The first two addresses are followed by a third address sequence which contains the high-order bits of the 10-bit address and the R/W bit set to '1'. After the third address sequence is performed, the UA bit is not set, the module is now configured in Transmit mode and clock stretching is controlled by the BF flag as in 7-Bit Slave Transmit mode (see Figure 19-13).


### 19.4.4.5 Clock Synchronization and the CKP bit


When the CKP bit is cleared, the SCLx output is forced to '0'. However, clearing the CKP bit will not assert the SCLx output low until the SCLx output is already sampled low. Therefore, the CKP bit will not assert the SCLx line until an external  $I^2C$  master device has

already asserted the SCLx line. The SCLx output will remain low until the CKP bit is set and all other devices on the  $I^2$ C bus have deasserted SCLx. This ensures that a write to the CKP bit will not violate the minimum high time requirement for SCLx (see Figure 19-14).









#### 19.4.5 GENERAL CALL ADDRESS SUPPORT

The addressing procedure for the  $I^2C$  bus is such that the first byte after the Start condition usually determines which device will be the slave addressed by the master. The exception is the general call address, which can address all devices. When this address is used, all devices should, in theory, respond with an Acknowledge.

The general call address is one of eight addresses reserved for specific purposes by the I<sup>2</sup>C protocol. It consists of all '0's with R/W = 0.


The general call address is recognized when the General Call Enable bit, GCEN, is enabled (SSPxCON2<7> set). Following a Start bit detect, 8 bits are shifted into the SSPxSR and the address is compared against the SSPxADD. It is also compared to the general call address and fixed in hardware.

If the general call address matches, the SSPxSR is transferred to the SSPxBUF, the BF flag bit is set (eighth bit) and on the falling edge of the ninth bit (ACK bit), the SSPxIF interrupt flag bit is set.

When the interrupt is serviced, the source for the interrupt can be checked by reading the contents of the SSPxBUF. The value can be used to determine if the address was device specific or a general call address.

In 10-Bit Addressing mode, the SSPxADD is required to be updated for the second half of the address to match and the UA bit is set (SSPxSTAT<1>). If the general call address is sampled when the GCEN bit is set, while the slave is configured in 10-Bit Addressing mode, then the second half of the address is not necessary, the UA bit will not be set and the slave will begin receiving data after the Acknowledge (Figure 19-17).





### 19.4.6 MASTER MODE

Master mode is enabled by setting and clearing the appropriate SSPM bits in SSPxCON1 and by setting the SSPEN bit. In Master mode, the SCLx and SDAx lines are manipulated by the MSSP hardware.

Master mode of operation is supported by interrupt generation on the detection of the Start and Stop conditions. The Stop (P) and Start (S) bits are cleared from a Reset or when the MSSP module is disabled. Control of the  $I^2C$  bus may be taken when the P bit is set, or the bus is Idle, with both the S and P bits clear.

In Firmware Controlled Master mode, user code conducts all  $I^2C$  bus operations based on Start and Stop bit conditions.


Once Master mode is enabled, the user has six options.

- 1. Assert a Start condition on SDAx and SCLx.
- 2. Assert a Repeated Start condition on SDAx and SCLx.
- 3. Write to the SSPxBUF register initiating transmission of data/address.
- 4. Configure the I<sup>2</sup>C port to receive data.
- 5. Generate an Acknowledge condition at the end of a received byte of data.
- 6. Generate a Stop condition on SDAx and SCLx.

Note: The MSSP module, when configured in I<sup>2</sup>C Master mode, does not allow queueing of events. For instance, the user is not allowed to initiate a Start condition and immediately write the SSPxBUF register to initiate transmission before the Start condition is complete. In this case, the SSPxBUF will not be written to and the WCOL bit will be set, indicating that a write to the SSPxBUF did not occur.

The following events will cause the MSSP Interrupt Flag bit, SSPxIF, to be set (and MSSP interrupt, if enabled):

- Start Condition
- Stop Condition
- Data Transfer Byte Transmitted/Received
- Acknowledge Transmit
- Repeated Start



### FIGURE 19-18: MSSP BLOCK DIAGRAM (I<sup>2</sup>C<sup>™</sup> MASTER MODE)

### 19.4.6.1 I<sup>2</sup>C Master Mode Operation

The master device generates all of the serial clock pulses and the Start and Stop conditions. A transfer is ended with a Stop condition or with a Repeated Start condition. Since the Repeated Start condition is also the beginning of the next serial transfer, the I<sup>2</sup>C bus will not be released.

In Master Transmitter mode, serial data is output through SDAx, while SCLx outputs the serial clock. The first byte transmitted contains the slave address of the receiving device (7 bits) and the Read/Write (R/W) bit. In this case, the R/W bit will be logic '0'. Serial data is transmitted 8 bits at a time. After each byte is transmitted, an Acknowledge bit is received. Start and Stop conditions are output to indicate the beginning and the end of a serial transfer.

In Master Receive mode, the first byte transmitted contains the slave address of the transmitting device (7 bits) and the  $R/\overline{W}$  bit. In this case, the  $R/\overline{W}$  bit will be logic '1'. Thus, the first byte transmitted is a 7-bit slave address followed by a '1' to indicate the receive bit. Serial data is received via SDAx, while SCLx outputs the serial clock. Serial data is received 8 bits at a time. After each byte is received, an Acknowledge bit is transmitted. Start and Stop conditions indicate the beginning and end of transmission.

The Baud Rate Generator used for the SPI mode operation is used to set the SCLx clock frequency for either 100 kHz, 400 kHz or 1 MHz I<sup>2</sup>C operation. See **Section 19.4.7 "Baud Rate"** for more detail.

A typical transmit sequence would go as follows:

- 1. The user generates a Start condition by setting the Start Enable bit, SEN (SSPxCON2<0>).
- SSPxIF is set. The MSSP module will wait the required start time before any other operation takes place.
- 3. The user loads the SSPxBUF with the slave address to transmit.
- 4. Address is shifted out on the SDAx pin until all 8 bits are transmitted.
- 5. The MSSP module shifts in the ACK bit from the slave device and writes its value into the SSPxCON2 register (SSPxCON2<6>).
- 6. The MSSP module generates an interrupt at the end of the ninth clock cycle by setting the SSPxIF bit.
- 7. The user loads the SSPxBUF with eight bits of data.
- 8. Data is shifted out on the SDAx pin until all 8 bits are transmitted.
- The MSSP module shifts in the ACK bit from the slave device and writes its value into the SSPxCON2 register (SSPxCON2<6>).
- 10. The MSSP module generates an interrupt at the end of the ninth clock cycle by setting the SSPxIF bit.
- 11. The user generates a Stop condition by setting the Stop Enable bit, PEN (SSPxCON2<2>).
- 12. Interrupt is generated once the Stop condition is complete.

### 19.4.7 BAUD RATE

In I<sup>2</sup>C Master mode, the Baud Rate Generator (BRG) reload value is placed in the lower 7 bits of the SSPxADD register (Figure 19-19). When a write occurs to SSPxBUF, the Baud Rate Generator will automatically begin counting. The BRG counts down to 0 and stops until another reload has taken place. The BRG count is decremented twice per instruction cycle (TcY) on the Q2 and Q4 clocks. In I<sup>2</sup>C Master mode, the BRG is reloaded automatically.

Once the given operation is complete (i.e., transmission of the last data bit is followed by ACK), the internal clock will automatically stop counting and the SCLx pin will remain in its last state.


Table 19-3 demonstrates clock rates based on instruction cycles and the BRG value loaded into SSPxADD.

### 19.4.7.1 Baud Rate and Module Interdependence

Because MSSP1 and MSSP2 are independent, they can operate simultaneously in I<sup>2</sup>C Master mode at different baud rates. This is done by using different BRG reload values for each module.

Because this mode derives its basic clock source from the system clock, any changes to the clock will affect both modules in the same proportion. It may be possible to change one or both baud rates back to a previous value by changing the BRG reload value.

### FIGURE 19-19: BAUD RATE GENERATOR BLOCK DIAGRAM



### TABLE 19-3: I<sup>2</sup>C<sup>™</sup> CLOCK RATE w/BRG

Fosc	BRG Value	FscL (2 Rollovers of BRG)
41.667 MHz	19h	400 kHz <sup>(1)</sup>
41.667 MHz	67h	100 kHz
31.25 MHz	13h	400 kHz <sup>(1)</sup>
31.25 MHz	4Dh	100 kHz
20.833 MHz	09h	400 kHz <sup>(1)</sup>
20.833 MHz	33h	100 kHz


**Note 1:** The I<sup>2</sup>C<sup>™</sup> interface does not conform to the 400 kHz I<sup>2</sup>C specification (which applies to rates greater than 100 kHz) in all details, but may be used with care where higher rates are required by the application.

#### 19.4.7.2 Clock Arbitration

Clock arbitration occurs when the master, during any receive, transmit or Repeated Start/Stop condition, deasserts the SCLx pin (SCLx allowed to float high). When the SCLx pin is allowed to float high, the Baud Rate Generator (BRG) is suspended from counting until the SCLx pin is actually sampled high. When the

SCLx pin is sampled high, the Baud Rate Generator is reloaded with the contents of SSPxADD<6:0> and begins counting. This ensures that the SCLx high time will always be at least one BRG rollover count in the event that the clock is held low by an external device (Figure 19-20).





#### 19.4.8 I<sup>2</sup>C MASTER MODE START CONDITION TIMING


To initiate a Start condition, the user sets the Start Enable bit, SEN (SSPxCON2<0>). If the SDAx and SCLx pins are sampled high, the Baud Rate Generator is reloaded with the contents of SSPxADD<6:0> and starts its count. If SCLx and SDAx are both sampled high when the Baud Rate Generator times out (TBRG), the SDAx pin is driven low. The action of the SDAx being driven low while SCLx is high is the Start condition and causes the S bit (SSPxSTAT<3>) to be set. Following this, the Baud Rate Generator is reloaded with the contents of SSPxADD<6:0> and resumes its count. When the Baud Rate Generator times out (TBRG), the SEN bit (SSPxCON2<0>) will be automatically cleared by hardware. The Baud Rate Generator is suspended, leaving the SDAx line held low and the Start condition is complete.

Note: If, at the beginning of the Start condition, the SDAx and SCLx pins are already sampled low, or if during the Start condition, the SCLx line is sampled low before the SDAx line is driven low, a bus collision occurs. The Bus Collision Interrupt Flag, BCLxIF, is set, the Start condition is aborted and the I<sup>2</sup>C module is reset into its Idle state.

#### 19.4.8.1 WCOL Status Flag

If the user writes the SSPxBUF when a Start sequence is in progress, the WCOL is set and the contents of the buffer are unchanged (the write doesn't occur).

**Note:** Because queueing of events is not allowed, writing to the lower 5 bits of SSPxCON2 is disabled until the Start condition is complete.



#### FIGURE 19-21: FIRST START BIT TIMING

#### 19.4.9 I<sup>2</sup>C MASTER MODE REPEATED START CONDITION TIMING

A Repeated Start condition occurs when the RSEN bit (SSPxCON2<1>) is programmed high and the I<sup>2</sup>C logic module is in the Idle state. When the RSEN bit is set, the SCLx pin is asserted low. When the SCLx pin is sampled low, the Baud Rate Generator is loaded with the contents of SSPxADD<6:0> and begins counting. The SDAx pin is released (brought high) for one Baud Rate Generator count (TBRG). When the Baud Rate Generator times out, if SDAx is sampled high, the SCLx pin will be deasserted (brought high). When SCLx is sampled high, the Baud Rate Generator is reloaded with the contents of SSPxADD<6:0> and begins counting. SDAx and SCLx must be sampled high for one TBRG. This action is then followed by assertion of the SDAx pin (SDAx = 0) for one TBRG while SCLx is high. Following this, the RSEN bit (SSPxCON2<1>) will be automatically cleared and the Baud Rate Generator will not be reloaded, leaving the SDAx pin held low. As soon as a Start condition is detected on the SDAx and SCLx pins, the S bit (SSPxSTAT<3>) will be set. The SSPxIF bit will not be set until the Baud Rate Generator has timed out.

- Note 1: If RSEN is programmed while any other event is in progress, it will not take effect.
  - **2:** A bus collision during the Repeated Start condition occurs if:
    - SDAx is sampled low when SCLx goes from low-to-high.
    - SCLx goes low before SDAx is asserted low. This may indicate that another master is attempting to transmit a data '1'.


Immediately following the SSPxIF bit getting set, the user may write the SSPxBUF with the 7-bit address in 7-bit mode or the default first address in 10-bit mode. After the first eight bits are transmitted and an ACK is received, the user may then transmit an additional eight bits of address (10-bit mode) or eight bits of data (7-bit mode).

### 19.4.9.1 WCOL Status Flag

If the user writes the SSPxBUF when a Repeated Start sequence is in progress, the WCOL is set and the contents of the buffer are unchanged (the write doesn't occur).

Note: Because queueing of events is not allowed, writing of the lower 5 bits of SSPxCON2 is disabled until the Repeated Start condition is complete.

### FIGURE 19-22: REPEATED START CONDITION WAVEFORM



#### 19.4.10 I<sup>2</sup>C MASTER MODE TRANSMISSION

Transmission of a data byte, a 7-bit address or the other half of a 10-bit address is accomplished by simply writing a value to the SSPxBUF register. This action will set the Buffer Full flag bit, BF, and allow the Baud Rate Generator to begin counting and start the next transmission. Each bit of address/data will be shifted out onto the SDAx pin after the falling edge of SCLx is asserted (see data hold time specification parameter 106). SCLx is held low for one Baud Rate Generator rollover count (TBRG). Data should be valid before SCLx is released high (see data setup time specification parameter 107). When the SCLx pin is released high, it is held that way for TBRG. The data on the SDAx pin must remain stable for that duration and some hold time after the next falling edge of SCLx. After the eighth bit is shifted out (the falling edge of the eighth clock), the BF flag is cleared and the master releases SDAx. This allows the slave device being addressed to respond with an ACK bit during the ninth bit time if an address match occurred, or if data was received properly. The status of ACK is written into the ACKDT bit on the falling edge of the ninth clock. If the master receives an Acknowledge, the Acknowledge Status bit, ACKSTAT, is cleared; if not, the bit is set. After the ninth clock, the SSPxIF bit is set and the master clock (Baud Rate Generator) is suspended until the next data byte is loaded into the SSPxBUF, leaving SCLx low and SDAx unchanged (Figure 19-23).

After the write to the SSPxBUF, each bit of the address will be shifted out on the falling edge of SCLx until all seven address bits and the R/W bit are completed. On the falling edge of the eighth clock, the master will deassert the SDAx pin, allowing the slave to respond with an Acknowledge. On the falling edge of the ninth clock, the master will sample the SDAx pin to see if the address was recognized by a slave. The status of the ACK bit is loaded into the ACKSTAT status bit (SSPxCON2<6>). Following the falling edge of the ninth clock transmission of the address, the SSPxIF is set, the BF flag is cleared and the Baud Rate Generator is turned off until another write to the SSPxBUF takes place, holding SCLx low and allowing SDAx to float.

#### 19.4.10.1 BF Status Flag

In Transmit mode, the BF bit (SSPxSTAT<0>) is set when the CPU writes to SSPxBUF, and is cleared when all 8 bits are shifted out.

#### 19.4.10.2 WCOL Status Flag

If the user writes to the SSPxBUF when a transmit is already in progress (i.e., SSPxSR is still shifting out a data byte), the WCOL is set and the contents of the buffer are unchanged (the write doesn't occur) after 2 TcY after the SSPxBUF write. If SSPxBUF is rewritten within 2 TcY, the WCOL bit is set and SSPxBUF is updated. This may result in a corrupted transfer. The user should verify that the WCOL is clear after each write to SSPxBUF to ensure the transfer is correct. In all cases, WCOL must be cleared in software.

#### 19.4.10.3 ACKSTAT Status Flag

In Transmit mode, the ACKSTAT bit (SSPxCON2<6>) is cleared when the slave has sent an Acknowledge  $(\overline{ACK} = 0)$  and is set when the slave does not Acknowledge  $(\overline{ACK} = 1)$ . A slave sends an Acknowledge when it has recognized its address (including a general call), or when the slave has properly received its data.

#### 19.4.11 I<sup>2</sup>C MASTER MODE RECEPTION

Master mode reception is enabled by programming the Receive Enable bit, RCEN (SSPxCON2<3>).

Note:	The MSSP module must be in an Idle state
	before the RCEN bit is set or the RCEN bit
	will be disregarded.

The Baud Rate Generator begins counting and on each rollover. The state of the SCLx pin changes (high-to-low/low-to-high) and data is shifted into the SSPxSR. After the falling edge of the eighth clock, the receive enable flag is automatically cleared, the contents of the SSPxSR are loaded into the SSPxBUF, the BF flag bit is set, the SSPxIF flag bit is set and the Baud Rate Generator is suspended from counting, holding SCLx low. The MSSP is now in Idle state awaiting the next command. When the buffer is read by the CPU, the BF flag bit is automatically cleared. The user can then send an Acknowledge bit at the end of reception by setting the Acknowledge Sequence Enable bit, ACKEN (SSPxCON2<4>).

#### 19.4.11.1 BF Status Flag


In receive operation, the BF bit is set when an address or data byte is loaded into SSPxBUF from SSPxSR. It is cleared when the SSPxBUF register is read.


#### 19.4.11.2 SSPOV Status Flag

In receive operation, the SSPOV bit is set when 8 bits are received into the SSPxSR and the BF flag bit is already set from a previous reception.

#### 19.4.11.3 WCOL Status Flag

If the user writes the SSPxBUF when a receive is already in progress (i.e., SSPxSR is still shifting in a data byte), the WCOL bit is set and the contents of the buffer are unchanged (the write doesn't occur).





#### 19.4.12 ACKNOWLEDGE SEQUENCE TIMING

An Acknowledge sequence is enabled by setting the Acknowledge Sequence Enable bit. ACKEN (SSPxCON2<4>). When this bit is set, the SCLx pin is pulled low and the contents of the Acknowledge data bit are presented on the SDAx pin. If the user wishes to generate an Acknowledge, then the ACKDT bit should be cleared. If not, the user should set the ACKDT bit before starting an Acknowledge sequence. The Baud Rate Generator then counts for one rollover period (TBRG) and the SCLx pin is deasserted (pulled high). When the SCLx pin is sampled high (clock arbitration), the Baud Rate Generator counts for TBRG. The SCLx pin is then pulled low. Following this, the ACKEN bit is automatically cleared, the Baud Rate Generator is turned off and the MSSP module then goes into Idle mode (Figure 19-25).

#### 19.4.12.1 WCOL Status Flag

If the user writes the SSPxBUF when an Acknowledge sequence is in progress, then WCOL is set and the contents of the buffer are unchanged (the write doesn't occur).


#### 19.4.13 STOP CONDITION TIMING

A Stop bit is asserted on the SDAx pin at the end of a receive/transmit by setting the Stop Sequence Enable bit, PEN (SSPxCON2<2>). At the end of a receive/transmit, the SCLx line is held low after the falling edge of the ninth clock. When the PEN bit is set, the master will assert the SDAx line low. When the SDAx line is sampled low, the Baud Rate Generator is reloaded and counts down to '0'. When the Baud Rate Generator times out, the SCLx pin will be brought high and one TBRG (Baud Rate Generator rollover count) later, the SDAx pin will be deasserted. When the SDAx pin is sampled high while SCLx is high, the P bit (SSPxSTAT<4>) is set. A TBRG later, the PEN bit is cleared and the SSPxIF bit is set (Figure 19-26).


#### 19.4.13.1 WCOL Status Flag

If the user writes the SSPxBUF when a Stop sequence is in progress, then the WCOL bit is set and the contents of the buffer are unchanged (the write doesn't occur).

#### FIGURE 19-25: ACKNOWLEDGE SEQUENCE WAVEFORM



#### FIGURE 19-26: STOP CONDITION RECEIVE OR TRANSMIT MODE



#### 19.4.14 SLEEP OPERATION

While in Sleep mode, the  $I^2C$  module can receive addresses or data and when an address match or complete byte transfer occurs, wake the processor from Sleep (if the MSSP interrupt is enabled).

#### 19.4.15 EFFECTS OF A RESET

A Reset disables the MSSP module and terminates the current transfer.

#### 19.4.16 MULTI-MASTER MODE

In Multi-Master mode, the interrupt generation on the detection of the Start and Stop conditions allows the determination of when the bus is free. The Stop (P) and Start (S) bits are cleared from a Reset or when the MSSP module is disabled. Control of the I<sup>2</sup>C bus may be taken when the P bit (SSPxSTAT<4>) is set, or the bus is Idle, with both the S and P bits clear. When the bus is busy, enabling the MSSP interrupt will generate the interrupt when the Stop condition occurs.

In multi-master operation, the SDAx line must be monitored for arbitration to see if the signal level is the expected output level. This check is performed in hardware with the result placed in the BCLxIF bit.

The states where arbitration can be lost are:

- · Address Transfer
- Data Transfer
- · A Start Condition
- · A Repeated Start Condition
- An Acknowledge Condition

#### 19.4.17 MULTI -MASTER COMMUNICATION, BUS COLLISION AND BUS ARBITRATION

Multi-Master mode support is achieved by bus arbitration. When the master outputs address/data bits onto the SDAx pin, arbitration takes place when the master outputs a '1' on SDAx, by letting SDAx float high and another master asserts a '0'. When the SCLx pin floats high, data should be stable. If the expected data on SDAx is a '1' and the data sampled on the SDAx pin = 0, then a bus collision has taken place. The master will set the Bus Collision Interrupt Flag, BCLxIF and reset the I<sup>2</sup>C port to its Idle state (Figure 19-27).

If a transmit was in progress when the bus collision occurred, the transmission is halted, the BF flag is cleared, the SDAx and SCLx lines are deasserted and the SSPxBUF can be written to. When the user services the bus collision Interrupt Service Routine and if the I<sup>2</sup>C bus is free, the user can resume communication by asserting a Start condition.


If a Start, Repeated Start, Stop or Acknowledge condition was in progress when the bus collision occurred, the condition is aborted, the SDAx and SCLx lines are deasserted and the respective control bits in the SSPxCON2 register are cleared. When the user services the bus collision Interrupt Service Routine and if the I<sup>2</sup>C bus is free, the user can resume communication by asserting a Start condition.

The master will continue to monitor the SDAx and SCLx pins. If a Stop condition occurs, the SSPxIF bit will be set.

A write to the SSPxBUF will start the transmission of data at the first data bit regardless of where the transmitter left off when the bus collision occurred.

In Multi-Master mode, the interrupt generation on the detection of Start and Stop conditions allows the determination of when the bus is free. Control of the  $I^2C$  bus can be taken when the P bit is set in the SSPxSTAT register, or the bus is Idle and the S and P bits are cleared.

#### FIGURE 19-27: BUS COLLISION TIMING FOR TRANSMIT AND ACKNOWLEDGE



#### 19.4.17.1 Bus Collision During a Start Condition

During a Start condition, a bus collision occurs if:

- a) SDAx or SCLx are sampled low at the beginning of the Start condition (Figure 19-28).
- b) SCLx is sampled low before SDAx is asserted low (Figure 19-29).

During a Start condition, both the SDAx and the SCLx pins are monitored.

If the SDAx pin is already low, or the SCLx pin is already low, then all of the following occur:


- · the Start condition is aborted;
- · the BCLxIF flag is set; and
- the MSSP module is reset to its Idle state (Figure 19-28).

The Start condition begins with the SDAx and SCLx pins deasserted. When the SDAx pin is sampled high, the Baud Rate Generator is loaded from SSPxADD<6:0> and counts down to 0. If the SCLx pin is sampled low while SDAx is high, a bus collision occurs, because it is assumed that another master is attempting to drive a data '1' during the Start condition.


If the SDAx pin is sampled low during this count, the BRG is reset and the SDAx line is asserted early (Figure 19-30). If, however, a '1' is sampled on the SDAx pin, the SDAx pin is asserted low at the end of the BRG count. The Baud Rate Generator is then reloaded and counts down to 0. If the SCLx pin is sampled as '0' during this time, a bus collision does not occur. At the end of the BRG count, the SCLx pin is asserted low.


Note: The reason that bus collision is not a factor during a Start condition is that no two bus masters can assert a Start condition at the exact same time. Therefore, one master will always assert SDAx before the other. This condition does not cause a bus collision because the two masters must be allowed to arbitrate the first address following the Start condition. If the address is the same, arbitration must be allowed to continue into the data portion, Repeated Start or Stop conditions.














### 19.4.17.2 Bus Collision During a Repeated Start Condition

During a Repeated Start condition, a bus collision occurs if:

- a) A low level is sampled on SDAx when SCLx goes from low level to high level.
- SCLx goes low before SDAx is asserted low, indicating that another master is attempting to transmit a data '1'.

When the user deasserts SDAx and the pin is allowed to float high, the BRG is loaded with SSPxADD<6:0> and counts down to 0. The SCLx pin is then deasserted and when sampled high, the SDAx pin is sampled.


If SDAx is low, a bus collision has occurred (i.e., another master is attempting to transmit a data '0', see Figure 19-31). If SDAx is sampled high, the BRG is

reloaded and begins counting. If SDAx goes from high-to-low before the BRG times out, no bus collision occurs because no two masters can assert SDAx at exactly the same time.


If SCLx goes from high-to-low before the BRG times out and SDAx has not already been asserted, a bus collision occurs. In this case, another master is attempting to transmit a data '1' during the Repeated Start condition (see Figure 19-32).

If, at the end of the BRG time-out, both SCLx and SDAx are still high, the SDAx pin is driven low and the BRG is reloaded and begins counting. At the end of the count, regardless of the status of the SCLx pin, the SCLx pin is driven low and the Repeated Start condition is complete.





#### FIGURE 19-32: BUS COLLISION DURING REPEATED START CONDITION (CASE 2)




#### 19.4.17.3 Bus Collision During a Stop Condition

Bus collision occurs during a Stop condition if:


- a) After the SDAx pin has been deasserted and allowed to float high, SDAx is sampled low after the BRG has timed out.
- b) After the SCLx pin is deasserted, SCLx is sampled low before SDAx goes high.

The Stop condition begins with SDAx asserted low. When SDAx is sampled low, the SCLx pin is allowed to float. When the pin is sampled high (clock arbitration), the Baud Rate Generator is loaded with SSPxADD<6:0> and counts down to 0. After the BRG times out, SDAx is sampled. If SDAx is sampled low, a bus collision has occurred. This is due to another master attempting to drive a data '0' (Figure 19-33). If the SCLx pin is sampled low before SDAx is allowed to float high, a bus collision occurs. This is another case of another master attempting to drive a data '0' (Figure 19-34).

### FIGURE 19-33: BUS COLLISION DURING A STOP CONDITION (CASE 1)



#### FIGURE 19-34: BUS COLLISION DURING A STOP CONDITION (CASE 2)



Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR2	OSCFIF	CMIF	ETHIF	r	BCL1IF	—	TMR3IF	CCP2IF	61
PIE2	OSCFIE	CMIE	ETHIE	r	BCL1IE	_	TMR3IE	CCP2IE	61
IPR2	OSCFIP	CMIP	ETHIP	r	BCL1IP	_	TMR3IP	CCP2IP	61
PIR3	SSP2IF <sup>(1)</sup>	BCL2IF <sup>(1)</sup>	RC2IF	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE <sup>(1)</sup>	BCL2IE <sup>(1)</sup>	RC2IE	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP <sup>(1)</sup>	BCL2IP <sup>(1)</sup>	RC2IP	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
TRISC	TRISC7	TRISC6	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	61
TRISD	TRISD7	TRISD6 <sup>(1)</sup>	TRISD5 <sup>(1)</sup>	TRISD4	TRISD3	TRISD2	TRISD1	TRISD0	61
SSP1BUF	MSSP1 Red	ceive Buffer/	ransmit Reg	ister					60
SSP1ADD	MSSP1 Add	ress Register	. (I <sup>2</sup> C™ Slave	e mode), MSS	SP1 Baud Rat	e Reload Reg	gister (I <sup>2</sup> C Ma	ster mode)	63
SSP1CON1	WCOL	SSPOV	SSPEN	CKP	SSPM3	SSPM2	SSPM1	SSPM0	60
SSP1CON2	GCEN	ACKSTAT	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN	60
	GCEN	ACKSTAT	ADMSK5(2)	ADMSK4 <sup>(2)</sup>	ADMSK3(2)	ADMSK2(2)	ADMSK1(2)	SEN	
SSP1STAT	SMP	CKE	D/A	Р	S	R/W	UA	BF	60
SSP2BUF	MSSP2 Red	ceive Buffer/	ransmit Reg	ister					60
SSP2ADD	MSSP2 Add	ress Register	· (I <sup>2</sup> C Slave m	node), MSSP2	2 Baud Rate I	Reload Regis	ter (I <sup>2</sup> C Maste	er mode)	63
SSP2CON1	WCOL	SSPOV	SSPEN	CKP	SSPM3	SSPM2	SSPM1	SSPM0	63
SSP2CON2	GCEN	ACKSTAT	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN	63
	GCEN	ACKSTAT	ADMSK5 <sup>(2)</sup>	ADMSK4 <sup>(2)</sup>	ADMSK3(2)	ADMSK2 <sup>(2)</sup>	ADMSK1(2)	SEN	
SSP2STAT	SMP	CKE	D/A	Р	S	R/W	UA	BF	63

**Legend:** — = unimplemented, read as '0', r = reserved. Shaded cells are not used by the MSSP module in  $I^2C^{TM}$  mode.

Note 1: These bits are only available in 100-pin devices; otherwise, they are unimplemented and read as '0'.

**2:** Alternate bit definitions in  $I^2C^{TM}$  Slave mode.

NOTES:

### 20.0 ENHANCED UNIVERSAL SYNCHRONOUS ASYNCHRONOUS RECEIVER TRANSMITTER (EUSART)

The Enhanced Universal Synchronous Asynchronous Receiver Transmitter (EUSART) module is one of two serial I/O modules. (Generically, the EUSART is also known as a Serial Communications Interface or SCI.) The EUSART can be configured as a full-duplex asynchronous system that can communicate with peripheral devices, such as CRT terminals and personal computers. It can also be configured as a half-duplex synchronous system that can communicate with peripheral devices, such as A/D or D/A integrated circuits, serial EEPROMs, etc.

The Enhanced USART module implements additional features, including automatic baud rate detection and calibration, automatic wake-up on Sync Break reception and 12-bit Break character transmit. These features make it ideally suited for use in Local Interconnect Network bus (LIN bus) systems.

The 64-pin devices of the PIC18F97J60 family are equipped with one EUSART module, referred to as EUSART1. The 80-pin and 100-pin devices each have two independent EUSART modules, referred to as EUSART1 and EUSART2. They can be configured in the following modes:

- Asynchronous (full-duplex) with:
  - Auto-Wake-up on Character Reception
  - Auto-Baud Calibration
- 12-Bit Break Character Transmission
- Synchronous Master (half-duplex) with Selectable Clock Polarity
- Synchronous Slave (half-duplex) with Selectable Clock Polarity

The pins of EUSART1 and EUSART2 are multiplexed with the functions of PORTC (RC6/TX1/CK1 and RC7/RX1/DT1) and PORTG (RG1/TX2/CK2 and RG2/RX2/DT2), respectively. In order to configure these pins as an EUSART:

- For EUSART1:
  - bit SPEN (RCSTA1<7>) must be set (= 1)
  - bit TRISC<7> must be set (= 1)
  - bit TRISC<6> must be cleared (= 0) for Asynchronous and Synchronous Master modes
  - bit TRISC<6> must be set (= 1) for Synchronous Slave mode
- For EUSART2:
  - bit SPEN (RCSTA2<7>) must be set (= 1)
  - bit TRISG<2> must be set (= 1)
  - bit TRISG<1> must be cleared (= 0) for Asynchronous and Synchronous Master modes
  - bit TRISG<1> must be set (= 1) for Synchronous Slave mode

Note: The EUSARTx control will automatically reconfigure the pin from input to output as needed.

The operation of each Enhanced USART module is controlled through three registers:

- Transmit Status and Control (TXSTAx)
- Receive Status and Control (RCSTAx)
- Baud Rate Control (BAUDCONx)

These are detailed on the following pages in Register 20-1, Register 20-2 and Register 20-3, respectively.

Note:	Throughout this section, references to
	register and bit names that may be associ-
	ated with a specific EUSART module are
	referred to generically by the use of 'x' in
	place of the specific module number.
	Thus, "RCSTAx" might refer to the
	Receive Status register for either
	EUSART1 or EUSART2.

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R-1	R/W-0
CSRC	TX9	TXEN <sup>(1)</sup>	SYNC	SENDB	BRGH	TRMT	TX9D
bit 7	•						bit
Legend:							
R = Readabl		W = Writable		-	nented bit, rea		
n = Value at	POR	'1' = Bit is set		'0' = Bit is clea	ared	x = Bit is unki	nown
bit 7	CSRC: Cloc	k Source Select	bit				
	Asynchrono						
	Don't care.						
	<u>Synchronou</u>						
		node (clock gen					
-: -		ode (clock from		ce)			
bit 6		ransmit Enable 9-bit transmissic					
		8-bit transmissic					
oit 5		smit Enable bit <sup>(1</sup>					
	1 = Transmi						
	0 = Transmi	t disabled					
bit 4	SYNC: EUS	ARTx Mode Sel	ect bit				
	1 = Synchro						
	-	onous mode	-4 h !4				
bit 3		nd Break Chara	cter dit				
	Asynchrono 1 = Send Sv	<u>us mode:</u> /nc Break on ne:	xt transmissio	n (cleared by h	ardware upon	completion)	
		eak transmission			and the oppose	oop.oo)	
	<u>Synchronou</u>	<u>s mode:</u>					
	Don't care.						
bit 2	-	n Baud Rate Sel	ect bit				
	Asynchrono 1 = High spe						
	0 = Low spe						
	<u>Synchronou</u>						
	Unused in th	nis mode.					
bit 1	TRMT: Tran	smit Shift Regist	er Status bit				
	1 = TSR em						
	0 = TSR full		1.				
oit 0		it of Transmit Da					
	Can be add						

#### REGISTER 20-1: TXSTAX: TRANSMIT STATUS AND CONTROL REGISTER x

#### REGISTER 20-2: RCSTAX: RECEIVE STATUS AND CONTROL REGISTER x

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R-0	R-0	R-x
SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D
bit 7			1				bit (
Legend:	- 6:4		L :4				
R = Readabl		W = Writable		-	nented bit, rea		
-n = Value at	POR	'1' = Bit is set	[	'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7	SPEN: Seria	al Port Enable b	it				
		ort enabled (con ort disabled (hel		Tx and TXx/Cł	(x pins as seri	al port pins)	
bit 6	<b>RX9:</b> 9-Bit F	Receive Enable I	bit				
		9-bit reception 8-bit reception					
bit 5	SREN: Sing	le Receive Enal	ble bit				
	<u>Asynchrono</u> Don't care.	<u>us mode:</u>					
		<u>s mode – Maste</u>	er:				
		s single receive					
		s single receive eared after rece		ete.			
		s mode – Slave					
	Don't care.						
bit 4		tinuous Receive	Enable bit				
	Asynchrono 1 = Enables						
	1 = Disables 0 = Disables						
	Synchronou						
	1 = Enables			ble bit, CREN, is	s cleared (CR	EN overrides SF	REN)
bit 3	ADDEN: Ad	dress Detect Er	nable bit				
		nronous mode (I					
						e buffer when R n be used as pa	
	<u>9-Bit Asynch</u> Don't care.	nronous mode (F	RX9 = 0):				
bit 2	FERR: Fran	ning Error bit					
	1 = Framing 0 = No fram		pdated by rea	ding RCREGx	register and re	eceiving next val	id byte)
bit 1	OERR: Ove	rrun Error bit					
	1 = Overrun 0 = No over	error (can be cl run error	leared by clea	ring bit, CREN)			
bit 0	<b>RX9D:</b> 9th b	it of Received D	Data				

R/W-0	R-1	R/W-0	R/W-0	R/W-0	U-0	R/W-0	R/W-0
ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	_	WUE	ABDEN
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	-	mented bit, rea	d as '0'	
-n = Value at F	POR	'1' = Bit is set		'0' = Bit is cle	eared	x = Bit is unk	nown
bit 7		uto-Baud Acqui	sition Rollove	Status bit			
	1 = A BRG I	rollover has occ rollover has occ	urred during A		e Detect mode	(must be cleare	ed in software)
bit 6	RCIDL: Rece	eive Operation I	dle Status bit				
		operation is Idle operation is act					
bit 5	RXDTP: Rec	eived Data Pola	arity Select bit	t			
		<u>us mode:</u> data (RXx) is in sion of receive o					
	Synchronous				-		
	0 = No invers	sion of data (DT	x). Idle state i	is a high level.			
bit 4		ck and Data Pol	arity Select bi	it			
		<u>us mode:</u> data (TXx) is ir sion of transmit					
		<u>s modes:</u> e for clock (CKx) e for clock (CKx)	•		-		
bit 3	BRG16: 16-I	Bit Baud Rate R	egister Enabl	e bit			
		ud Rate Genera Id Rate Generat				ed (Compatible	mode)
bit 2	Unimpleme	nted: Read as '	0'				
bit 1	WUE: Wake	-up Enable bit					
	hardwar	<u>us mode:</u> Tx will continue e on following r not monitored o	sing edge		errupt generated	d on falling edge	e; bit cleared i
	Synchronous Unused in th						
bit 0	ABDEN: Aut	o-Baud Detect	Enable bit				
	cleared	<u>us mode:</u> baud rate meas in hardware upo te measuremen	on completion		ter. Requires re	eception of a Sy	ync field (55h
	Synchronous Unused in th	<u>s mode:</u>		·			

#### REGISTER 20-3: BAUDCONX: BAUD RATE CONTROL REGISTER x

#### 20.1 Baud Rate Generator (BRG)

The BRG is a dedicated 8-bit or 16-bit generator that supports both the Asynchronous and Synchronous modes of the EUSARTx. By default, the BRG operates in 8-bit mode; setting the BRG16 bit (BAUDCONx<3>) selects 16-bit mode.

The SPBRGHx:SPBRGx register pair controls the period of a free-running timer. In Asynchronous mode, bits BRGH (TXSTAx<2>) and BRG16 (BAUDCONx<3>) also control the baud rate. In Synchronous mode, BRGH is ignored. Table 20-1 shows the formula for computation of the baud rate for different EUSARTx modes which only apply in Master mode (internally generated clock).

Given the desired baud rate and FOSC, the nearest integer value for the SPBRGHx:SPBRGx registers can be calculated using the formulas in Table 20-1. From this, the error in baud rate can be determined. An example calculation is shown in Example 20-1. Typical baud rates and error values for the various Asynchronous modes are shown in Table 20-2. It may be advantageous to use the high baud rate (BRGH = 1), or the 16-bit BRG to reduce the baud rate error, or achieve a slow baud rate for a fast oscillator frequency.

Writing a new value to the SPBRGHx:SPBRGx registers causes the BRG timer to be reset (or cleared). This ensures that the BRG does not wait for a timer overflow before outputting the new baud rate.

#### 20.1.1 OPERATION IN POWER-MANAGED MODES

The device clock is used to generate the desired baud rate. When one of the power-managed modes is entered, the new clock source may be operating at a different frequency. This may require an adjustment to the value in the SPBRGx register pair.

#### 20.1.2 SAMPLING

The data on the RXx pin (either RC7/RX1/DT1 or RG2/RX2/DT2) is sampled three times by a majority detect circuit to determine if a high or a low level is present at the RXx pin.

Co	onfiguration B	its	DDC/EUCADTy Made	David Data Commula		
SYNC	BRG16	BRGH	BRG/EUSARTx Mode	Baud Rate Formula		
0	0	0	8-bit/Asynchronous	Fosc/[64 (n + 1)]		
0	0	1	8-bit/Asynchronous	Fosc/[16 (n + 1)]		
0	1	0	16-bit/Asynchronous			
0	1	1	16-bit/Asynchronous			
1	0	х	8-bit/Synchronous	Fosc/[4 (n + 1)]		
1	1	х	16-bit/Synchronous			

#### TABLE 20-1: BAUD RATE FORMULAS

**Legend:** x = Don't care, n = value of SPBRGHx:SPBRGx register pair

#### EXAMPLE 20-1: CALCULATING BAUD RATE ERROR

For a device with Fost	6 MHz, desired baud rate of 9600, Asynchronous mode, 8-bit BRG:	
Desired Baud Rate	Fosc/(64 ([SPBRGHx:SPBRGx] + 1))	
Solving for SPBRGHx	BRGx:	
Х	((FOSC/Desired Baud Rate)/64) – 1	
	((16000000/9600)/64) – 1	
	[25.042] = 25	
Calculated Baud Rate	1600000/(64 (25 + 1))	
	9615	
Error	(Calculated Baud Rate - Desired Baud Rate)/Desired Baud Rate	
	(9615 - 9600)/9600 = 0.16%	

#### TABLE 20-2: REGISTERS ASSOCIATED WITH BAUD RATE GENERATOR

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
TXSTAx	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	61
RCSTAx	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	61
BAUDCONx	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16		WUE	ABDEN	62
SPBRGHx	EUSARTx Baud Rate Generator Register High Byte								
SPBRGx	EUSARTx	Baud Rate	Generator I	Register Lov	w Byte				62
	EUSARTx	Baud Rate	Generator I	Register Lo					62 62

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used by the BRG.

					SYNC	= 0, BRG1	6 = 0, BRG	i <b>H =</b> 0				
BAUD	Fosc = 41.667 MHz Fosc = 31.25 MHz				Fosc	= 25.00	0 MHz	Fosc	Fosc = 20.833 MHz			
RATE (K)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)
0.3	—		_	—	_		—	_	—	_		—
1.2		_	_	_	_	_	_	_	_	1.271	5.96	255
2.4	2.543	5.96	255	2.405	0.22	202	2.396	-0.15	162	2.393	-0.27	135
9.6	9.574	-0.27	67	9.574	-0.27	50	9.527	-0.76	40	9.574	-0.27	33
19.2	19.148	-0.27	33	19.531	1.73	24	19.531	1.73	19	19.147	-0.27	16
57.6	59.186	2.75	10	61.035	5.96	7	55.804	-3.12	6	54.253	-5.81	5
115.2	108.508	-5.81	5	122.070	5.96	3	130.208	13.03	2	108.505	-5.81	2

TABLE 20-3: BAUD RATES FOR ASTNURRUNUUS MODE	TABLE 20-3:	BAUD RATES FOR ASYNCHRONOUS MODES
--	-------------	-----------------------------------

			S	YNC = 0, E	NC = 0, BRG16 = 0, BRGH = 0							
BAUD	Fosc	= 13.88	9 MHz	Fos	c = 6.250	MHz	Fosc = 4.167 MHz					
RATE (K)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)			
0.3		_		_		_	0.300	0.01	216			
1.2	1.198	-0.08	180	1.206	0.47	80	1.206	0.48	53			
2.4	2.411	0.47	89	2.382	-0.76	40	2.411	0.48	26			
9.6	9.435	-1.71	22	9.766	1.73	9	9.301	-3.11	6			
19.2	19.279	2.75	10	19.531	1.73	4	21.703	13.04	2			
57.6	54.254	-5.81	3	48.828	-15.23	1	65.109	13.04	0			
115.2	108.508	-5.81	1	97.656	-15.23	0	65.109	-43.48	0			

					SYNC	= 0, BRG1	6 = 0, BRG	<b>H =</b> 1				
BAUD	Fosc = 41.667 MHz			Fosc = 31.25 MHz			Fosc = 25.000 MHz			Fosc = 20.833 MHz		
RATE (K)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)
0.3				_		_	_			_	_	_
1.2	—	—	—	—		—	—	—	—	—	_	—
2.4	_	_	_	_	_	_	—	_	_	—	_	_
9.6	10.172	5.96	255	9.621	0.22	202	9.586	-0.15	162	9.573	-0.27	135
19.2	19.148	-0.27	135	19.148	-0.27	101	19.290	0.47	80	19.147	-0.27	67
57.6	57.871	0.47	44	57.445	-0.27	33	57.870	0.47	26	56.611	-1.72	22
115.2	113.226	-1.71	22	114.890	-0.27	16	111.607	-3.12	13	118.369	2.75	10

			S	YNC = 0, E	NC = 0, BRG16 = 0, BRGH = 1							
BAUD	Fosc	= 13.88	9 MHz	Fos	c = 6.250	MHz	Fosc = 4.167 MHz					
RATE (K)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)			
0.3		_	_	_		_		_	_			
1.2	—	—	—	—	_	—	1.200	0.01	216			
2.4	—	—	—	2.396	-0.15	162	2.389	-0.44	108			
9.6	9.645	0.47	89	9.527	-0.76	40	9.645	0.48	26			
19.2	19.290	0.47	44	19.531	1.73	19	18.603	-3.11	13			
57.6	57.871	0.47	14	55.804	-3.12	6	52.088	-9.57	4			
115.2	108.508	-5.81	7	130.208.	13.03	2	130.219	13.04	1			

					SYNC	= 0, BRG1	6 = 1, BRG	i <b>H =</b> 0				
BAUD	Fosc = 41.667 MHz			Fosc = 31.25 MHz			Fosc = 25.000 MHz			Fosc = 20.833 MHz		
RATE (K)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)
0.3	0.300	0.00	8680	0.300	0.00	6509	0.300	0.01	5207	0.300	0.00	4339
1.2	1.200	0.01	2169	1.200	-0.02	1627	1.200	0.01	1301	1.200	0.00	1084
2.4	2.400	0.01	1084	2.399	-0.02	813	2.400	0.01	650	2.398	-0.09	542
9.6	9.609	0.10	270	9.621	0.22	202	9.586	-0.15	162	9.574	-0.27	135
19.2	19.148	-0.27	135	19.148	-0.27	101	19.290	0.47	80	19.148	-0.27	67
57.6	57.871	0.47	44	57.444	-0.27	33	57.870	0.47	26	56.611	-1.72	22
115.2	113.226	-1.71	22	114.890	-0.27	16	111.607	-3.12	13	118.369	2.75	10

### TABLE 20-3: BAUD RATES FOR ASYNCHRONOUS MODES (CONTINUED)

			S	YNC = 0, E	BRG16 = 1, BRGH = 0						
BAUD	Fosc	: = 13.88	9 MHz	Fos	c = 6.250	) MHz	Fosc = 4.167 MHz				
RATE (K) 0.3	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)		
0.3	0.300	-0.02	2893	0.300	0.01	1301	0.300	0.01	867		
1.2	1.201	0.05	722	1.198	-0.15	325	1.200	0.01	216		
2.4	2.398	-0.08	361	2.396	-0.15	162	2.389	-0.44	108		
9.6	9.645	0.47	89	9.527	-0.76	40	9.646	0.48	26		
19.2	19.290	0.47	44	19.531	1.73	19	18.603	-3.11	13		
57.6	57.871	0.47	14	55.804	-3.12	6	52.088	-9.57	4		
115.2	108.508	-5.81	7	130.208	13.03	2	130.218	13.04	1		

				SYNC = 0,	BRG16	= 1, BRGH	I = 1 or SYNC = 1, BRG16 = 1							
BAUD	Fosc = 41.667 MHz			Fosc = 31.25 MHz			Fosc = 25.000 MHz			Fosc = 20.833 MHz				
RATE (K)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)		
0.3	0.300	0.00	34722	0.300	0.00	26041	0.300	0.00	20832	0.300	0.00	17360		
1.2	1.200	0.00	8680	1.200	0.01	6509	1.200	0.01	5207	1.200	0.00	4339		
2.4	2.400	0.01	4339	2.400	0.01	3254	2.400	0.01	2603	2.400	0.00	2169		
9.6	9.601	0.01	1084	9.598	-0.02	813	9.601	0.01	650	9.592	-0.09	542		
19.2	19.184	-0.08	542	19.195	-0.02	406	19.172	-0.15	325	19.219	0.10	270		
57.6	57.551	-0.08	180	57.445	-0.27	135	57.339	-0.45	108	57.869	0.47	89		
115.2	115.742	0.47	89	114.890	-0.27	67	115.741	0.47	53	115.739	0.47	44		

		SY	NC = 0, BR	G16 = 1, BRGH = 1 or SYNC = 1, BRG16 = 1								
BAUD	Fosc	= 13.88	9 MHz	Fos	c = 6.250	) MHz	Fosc = 4.167 MHz					
RATE (K)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)	Actual Rate (K)	% Error	SPBRG Value (decimal)			
0.3	0.300	0.00	11573	0.300	0.01	5207	0.300	-0.01	3472			
1.2	1.200	-0.02	2893	1.200	0.01	1301	1.200	0.01	867			
2.4	2.400	-0.02	1446	2.400	0.01	650	2.400	0.01	433			
9.6	9.592	-0.08	361	9.586	-0.15	162	9.557	-0.44	108			
19.2	19.184	-0.08	180	19.290	0.47	80	19.292	0.48	53			
57.6	57.870	0.47	59	57.870	0.47	26	57.875	0.48	17			
115.2	115.742	0.47	29	111.607	-3.12	13	115.750	0.48	8			

#### 20.1.3 AUTO-BAUD RATE DETECT

The Enhanced USARTx module supports the automatic detection and calibration of baud rate. This feature is active only in Asynchronous mode and while the WUE bit is clear.

The automatic baud rate measurement sequence (Figure 20-1) begins whenever a Start bit is received and the ABDEN bit is set. The calculation is self-averaging.

In the Auto-Baud Rate Detect (ABD) mode, the clock to the BRG is reversed. Rather than the BRG clocking the incoming RXx signal, the RXx signal is timing the BRG. In ABD mode, the internal Baud Rate Generator is used as a counter to time the bit period of the incoming serial byte stream.

Once the ABDEN bit is set, the state machine will clear the BRG and look for a Start bit. The Auto-Baud Rate Detect must receive a byte with the value 55h (ASCII "U", which is also the LIN bus Sync character) in order to calculate the proper bit rate. The measurement is taken over both a low and high bit time in order to minimize any effects caused by asymmetry of the incoming signal. After a Start bit, the SPBRGx begins counting up, using the preselected clock source on the first rising edge of RXx. After eight bits on the RXx pin or the fifth rising edge, an accumulated value totalling the proper BRG period is left in the SPBRGHx:SPBRGx register pair. Once the 5th edge is seen (this should correspond to the Stop bit), the ABDEN bit is automatically cleared.

If a rollover of the BRG occurs (an overflow from FFFFh to 0000h), the event is trapped by the ABDOVF status bit (BAUDCONx<7>). It is set in hardware by BRG rollovers and can be set or cleared by the user in software. ABD mode remains active after rollover events and the ABDEN bit remains set (Figure 20-2).

While calibrating the baud rate period, the BRG registers are clocked at 1/8th the preconfigured clock rate. Note that the BRG clock will be configured by the BRG16 and BRGH bits. Independent of the BRG16 bit setting, both the SPBRGx and SPBRGHx will be used as a 16-bit counter. This allows the user to verify that no carry occurred for 8-bit modes by checking for 00h in the SPBRGHx register. Refer to Table 20-4 for counter clock rates to the BRG. While the ABD sequence takes place, the EUSARTx state machine is held in Idle. The RCxIF interrupt is set once the fifth rising edge on RXx is detected. The value in the RCREGx needs to be read to clear the RCxIF interrupt. The contents of RCREGx should be discarded.

Note 1:	If the WUE bit is set with the ABDEN bit,
	Auto-Baud Rate Detection will occur on
	the byte following the Break character.

2: It is up to the user to determine that the incoming character baud rate is within the range of the selected BRG clock source. Some combinations of oscillator frequency and EUSARTx baud rates are not possible due to bit error rates. Overall system timing and communication baud rates must be taken into consideration when using the Auto-Baud Rate Detection feature.

#### TABLE 20-4: BRG COUNTER CLOCK RATES

BRG16	BRGH	BRG Counter Clock
0	0	Fosc/512
0	1	Fosc/128
1	0	Fosc/128
1	1	Fosc/32

**Note:** During the ABD sequence, SPBRGx and SPBRGHx are both used as a 16-bit counter, independent of the BRG16 setting.


#### 20.1.3.1 ABD and EUSARTx Transmission

Since the BRG clock is reversed during ABD acquisition, the EUSARTx transmitter cannot be used during ABD. This means that whenever the ABDEN bit is set, TXREGx cannot be written to. Users should also ensure that ABDEN does not become set during a transmit sequence. Failing to do this may result in unpredictable EUSARTx operation.

BRG Value	XXXXh	0000h		001Ch
RXx pin		Start	-Edge #1 -Edge #2 -Edge #3 -Edge #4 Bit 0 Bit 1 Bit 2 Bit 3 Bit 4 Bit 5 Bit 6 Bit 7	Edge #5 Stop Bit
BRG Clock		hunnun		
ABDEN bit	Set by User			Auto-Cleared
RCxIF bit (Interrupt)				
Read RCREGx				ſ
SPBRGx	i		XXXXh	1Ch
SPBRGHx			XXXXh	00h

#### FIGURE 20-1: AUTOMATIC BAUD RATE CALCULATION

#### FIGURE 20-2: BRG OVERFLOW SEQUENCE



### 20.2 EUSARTx Asynchronous Mode

The Asynchronous mode of operation is selected by clearing the SYNC bit (TXSTAx<4>). In this mode, the EUSARTx uses standard Non-Return-to-Zero (NRZ) format (one Start bit, eight or nine data bits and one Stop bit). The most common data format is 8 bits. An on-chip, dedicated 8-bit/16-bit Baud Rate Generator can be used to derive standard baud rate frequencies from the oscillator.

The EUSARTx transmits and receives the LSb first. The EUSARTx module's transmitter and receiver are functionally independent but use the same data format and baud rate. The Baud Rate Generator produces a clock, either x16 or x64 of the bit shift rate, depending on the BRGH and BRG16 bits (TXSTAx<2> and BAUDCONx<3>). Parity is not supported by the hardware but can be implemented in software and stored as the 9th data bit.

The TXCKP (BAUDCONx<4>) and RXDTP (BAUDCONx<5>) bits allow the TXx and RXx signals to be inverted (polarity reversed). Devices that buffer signals between TTL and RS-232 levels also invert the signal. Setting the TXCKP and RXDTP bits allows for the use of circuits that provide buffering without inverting the signal.

When operating in Asynchronous mode, the EUSARTx module consists of the following important elements:

- Baud Rate Generator
- · Sampling Circuit
- Asynchronous Transmitter
- Asynchronous Receiver
- Auto-Wake-up on Sync Break Character
- 12-Bit Break Character Transmit
- Auto-Baud Rate Detection

#### 20.2.1 EUSARTX ASYNCHRONOUS TRANSMITTER

The EUSARTx transmitter block diagram is shown in Figure 20-3. The heart of the transmitter is the Transmit (Serial) Shift Register (TSR). The Shift register obtains its data from the Read/Write Transmit Buffer register, TXREGx. The TXREGx register is loaded with data in software. The TSR register is not loaded until the Stop bit has been transmitted from the previous load. As soon as the Stop bit is transmitted, the TSR is loaded with new data from the TXREGx register (if available).

Once the TXREGx register transfers the data to the TSR register (occurs in one TcY), the TXREGx register is empty and the TXxIF flag bit is set. This interrupt can be enabled or disabled by setting or clearing the interrupt enable bit, TXxIE. TXxIF will be set regardless of the state of TXxIE; it cannot be cleared in software. TXxIF is also not cleared immediately upon loading TXREGx, but becomes valid in the second instruction cycle following the load instruction. Polling TXxIF immediately following a load of TXREGx will return invalid results.

While TXxIF indicates the status of the TXREGx register, another bit, TRMT (TXSTAx<1>), shows the status of the TSR register. TRMT is a read-only bit which is set when the TSR register is empty. No interrupt logic is tied to this bit so the user has to poll this bit in order to determine if the TSR register is empty.


**Note 1:** The TSR register is not mapped in data memory, so it is not available to the user.

2: Flag bit, TXxIF, is set when enable bit TXEN is set.


To set up an Asynchronous Transmission:

- 1. Initialize the SPBRGHx:SPBRGx registers for the appropriate baud rate. Set or clear the BRGH and BRG16 bits, as required, to achieve the desired baud rate.
- 2. Enable the asynchronous serial port by clearing the SYNC bit and setting bit, SPEN.
- 3. If the signal from the TXx pin is to be inverted, set the TXCKP bit.
- 4. If interrupts are desired, set enable bit, TXxIE.
- 5. If 9-bit transmission is desired, set transmit bit, TX9. Can be used as address/data bit.
- 6. Enable the transmission by setting the TXEN bit which will also set bit, TXxIF.
- 7. If 9-bit transmission is selected, the ninth bit should be loaded in bit, TX9D.
- 8. Load data to the TXREGx register (starts transmission).
- If using interrupts, ensure that the GIE and PEIE bits in the INTCON register (INTCON<7:6>) are set.


#### FIGURE 20-3: EUSARTx TRANSMIT BLOCK DIAGRAM







#### FIGURE 20-5: ASYNCHRONOUS TRANSMISSION (BACK-TO-BACK), TXCKP = 0 (TXx NOT INVERTED)



Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:		
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INTOIE	RBIE	TMR0IF	INT0IF	RBIF	59		
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61		
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61		
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61		
PIR3	SSP2IF	BCL2IF	RC2IF	TX2IF <sup>(1)</sup>	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61		
PIE3	SSP2IE	BCL2IE	RC2IE	TX2IE <sup>(1)</sup>	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61		
IPR3	SSP2IP	BCL2IP	RC2IP	TX2IP <sup>(1)</sup>	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61		
RCSTAx	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	61		
TXREGx	EUSARTx	Transmit Re	gister						61		
TXSTAx	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	61		
BAUDCONx	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	—	WUE	ABDEN	62		
SPBRGHx	EUSARTx	USARTx Baud Rate Generator Register High Byte									
SPBRGx	EUSARTx	USARTx Baud Rate Generator Register Low Byte									

#### TABLE 20-5: REGISTERS ASSOCIATED WITH ASYNCHRONOUS TRANSMISSION

**Legend:** — = unimplemented locations read as '0'. Shaded cells are not used for asynchronous transmission.

**Note 1:** These bits are only available in 80-pin and 100-pin devices; otherwise, they are unimplemented and read as '0'.

#### 20.2.2 EUSARTx ASYNCHRONOUS RECEIVER

The receiver block diagram is shown in Figure 20-6. The data is received on the RXx pin and drives the data recovery block. The data recovery block is actually a high-speed shifter operating at x16 times the baud rate, whereas the main receive serial shifter operates at the bit rate or at Fosc. This mode would typically be used in RS-232 systems.

The RXDTP bit (BAUDCON<5>) allows the RXx signal to be inverted (polarity reversed). Devices that buffer signals from RS-232 to TTL levels also perform an inversion of the signal (when RS-232 = positive, TTL = 0). Inverting the polarity of the RXx pin data by setting the RXDTP bit allows for the use of circuits that provide buffering without inverting the signal.

To set up an Asynchronous Reception:


- 1. Initialize the SPBRGHx:SPBRGx registers for the appropriate baud rate. Set or clear the BRGH and BRG16 bits, as required, to achieve the desired baud rate.
- 2. Enable the asynchronous serial port by clearing the SYNC bit and setting bit, SPEN.
- 3. If the signal at the RXx pin is to be inverted, set the RXDTP bit.
- 4. If interrupts are desired, set enable bit, RCxIE.
- 5. If 9-bit reception is desired, set bit, RX9.
- 6. Enable the reception by setting bit, CREN.
- 7. Flag bit, RCxIF, will be set when reception is complete and an interrupt will be generated if enable bit, RCxIE, was set.
- 8. Read the RCSTAx register to get the 9th bit (if enabled) and determine if any error occurred during reception.
- 9. Read the 8-bit received data by reading the RCREGx register.
- 10. If any error occurred, clear the error by clearing enable bit, CREN.
- 11. If using interrupts, ensure that the GIE and PEIE bits in the INTCON register (INTCON<7:6>) are set.

## 20.2.3 SETTING UP 9-BIT MODE WITH ADDRESS DETECT


This mode would typically be used in RS-485 systems. To set up an Asynchronous Reception with Address Detect Enable:

- 1. Initialize the SPBRGHx:SPBRGx registers for the appropriate baud rate. Set or clear the BRGH and BRG16 bits, as required, to achieve the desired baud rate.
- 2. Enable the asynchronous serial port by clearing the SYNC bit and setting the SPEN bit.
- 3. If the signal at the RXx pin is to be inverted, set the RXDTP bit. If the signal from the TXx pin is to be inverted, set the TXCKP bit.
- 4. If interrupts are required, set the RCEN bit and select the desired priority level with the RCxIP bit.
- 5. Set the RX9 bit to enable 9-bit reception.
- 6. Set the ADDEN bit to enable address detect.
- 7. Enable reception by setting the CREN bit.
- 8. The RCxIF bit will be set when reception is complete. The interrupt will be Acknowledged if the RCxIE and GIE bits are set.
- 9. Read the RCSTAx register to determine if any error occurred during reception, as well as read bit 9 of data (if applicable).
- 10. Read RCREGx to determine if the device is being addressed.
- 11. If any error occurred, clear the CREN bit.
- 12. If the device has been addressed, clear the ADDEN bit to allow all received data into the receive buffer and interrupt the CPU.









Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:	
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59	
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61	
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61	
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61	
PIR3	SSP2IF	BCL2IF	RC2IF <sup>(1)</sup>	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61	
PIE3	SSP2IE	BCL2IE	RC2IE <sup>(1)</sup>	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61	
IPR3	SSP2IP	BCL2IP	RC2IP <sup>(1)</sup>	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61	
RCSTAx	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	61	
RCREGx	EUSARTx Receive Register								61	
TXSTAx	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	61	
BAUDCONx	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	_	WUE	ABDEN	62	
SPBRGHx	EUSARTx Baud Rate Generator Register High Byte								62	
SPBRGx	EUSARTx Baud Rate Generator Register Low Byte							62		
Legend: $=$ unimplemented locations read as '0'. Shaded cells are not used for asynchronous recention										

**Legend:** — = unimplemented locations read as '0'. Shaded cells are not used for asynchronous reception.

Note 1: These bits are only available in 80-pin and 100-pin devices; otherwise, they are unimplemented and read as '0'.

#### 20.2.4 AUTO-WAKE-UP ON SYNC BREAK CHARACTER

During Sleep mode, all clocks to the EUSARTx are suspended. Because of this, the Baud Rate Generator is inactive and a proper byte reception cannot be performed. The auto-wake-up feature allows the controller to wake-up due to activity on the RXx/DTx line while the EUSARTx is operating in Asynchronous mode.

The auto-wake-up feature is enabled by setting the WUE bit (BAUDCONx<1>). Once set, the typical receive sequence on RXx/DTx is disabled and the EUSARTx remains in an Idle state, monitoring for a wake-up event independent of the CPU mode. A wake-up event consists of a high-to-low transition on the RXx/DTx line. (This coincides with the start of a Sync Break or a Wake-up Signal character for the LIN protocol.)

Following a wake-up event, the module generates an RCxIF interrupt. The interrupt is generated synchronously to the Q clocks in normal operating modes (Figure 20-8) and asynchronously if the device is in Sleep mode (Figure 20-9). The interrupt condition is cleared by reading the RCREGx register.

The WUE bit is automatically cleared once a low-to-high transition is observed on the RXx line following the wake-up event. At this point, the EUSARTx module is in Idle mode and returns to normal operation. This signals to the user that the Sync Break event is over.

#### 20.2.4.1 Special Considerations Using Auto-Wake-up

Since auto-wake-up functions by sensing rising edge transitions on RXx/DTx, information with any state changes before the Stop bit may signal a false End-of-Character (EOC) and cause data or framing errors. To work properly, therefore, the initial character in

the transmission must be all '0's. This can be 00h (8 bytes) for standard RS-232 devices or 000h (12 bits) for LIN bus.


Oscillator start-up time must also be considered, especially in applications using oscillators with longer start-up intervals (i.e., HS or HSPLL mode). The Sync Break (or Wake-up Signal) character must be of sufficient length and be followed by a sufficient interval to allow enough time for the selected oscillator to start and provide proper initialization of the EUSARTx.

### 20.2.4.2 Special Considerations Using the WUE Bit


The timing of WUE and RCxIF events may cause some confusion when it comes to determining the validity of received data. As noted, setting the WUE bit places the EUSARTx in an Idle mode. The wake-up event causes a receive interrupt by setting the RCxIF bit. The WUE bit is cleared after this when a rising edge is seen on RXx/DTx. The interrupt condition is then cleared by reading the RCREGx register. Ordinarily, the data in RCREGx will be dummy data and should be discarded.

The fact that the WUE bit has been cleared (or is still set), and the RCxIF flag is set, should not be used as an indicator of the integrity of the data in RCREGx. Users should consider implementing a parallel method in firmware to verify received data integrity.

To assure that no actual data is lost, check the RCIDL bit to verify that a receive operation is not in process. If a receive operation is not occurring, the WUE bit may then be set just prior to entering the Sleep mode.







#### 20.2.5 BREAK CHARACTER SEQUENCE

The EUSARTx module has the capability of sending the special Break character sequences that are required by the LIN bus standard. The Break character transmit consists of a Start bit, followed by twelve '0' bits and a Stop bit. The Frame Break character is sent whenever the SENDB and TXEN bits (TXSTAx<3> and TXSTAx<5>) are set while the Transmit Shift Register (TSR) is loaded with data. Note that the value of data written to TXREGx will be ignored and all '0's will be transmitted.

The SENDB bit is automatically reset by hardware after the corresponding Stop bit is sent. This allows the user to preload the transmit FIFO with the next transmit byte following the Break character (typically, the Sync character in the LIN specification).

Note that the data value written to the TXREGx for the Break character is ignored. The write simply serves the purpose of initiating the proper sequence.

The TRMT bit indicates when the transmit operation is active or Idle, just as it does during normal transmission. See Figure 20-10 for the timing of the Break character sequence.

#### 20.2.5.1 Break and Sync Transmit Sequence

The following sequence will send a message frame header made up of a Break, followed by an Auto-Baud Sync byte. This sequence is typical of a LIN bus master.

- 1. Configure the EUSARTx for the desired mode.
- 2. Set the TXEN and SENDB bits to set up the Break character.
- 3. Load the TXREGx with a dummy character to initiate transmission (the value is ignored).
- 4. Write '55h' to TXREGx to load the Sync character into the transmit FIFO buffer.
- 5. After the Break has been sent, the SENDB bit is reset by hardware. The Sync character now transmits in the preconfigured mode.

When the TXREGx becomes empty, as indicated by the TXxIF, the next data byte can be written to TXREGx.


#### 20.2.6 RECEIVING A BREAK CHARACTER

The Enhanced USARTx module can receive a Break character in two ways.

The first method forces configuration of the baud rate at a frequency of 9/13 the typical speed. This allows for the Stop bit transition to be at the correct sampling location (13 bits for Break versus Start bit and 8 data bits for typical data).

The second method uses the auto-wake-up feature described in **Section 20.2.4 "Auto-Wake-up on Sync Break Character"**. By enabling this feature, the EUSARTx will sample the next two transitions on RXx/DTx, cause an RCxIF interrupt and receive the next data byte followed by another interrupt.

Note that following a Break character, the user will typically want to enable the Auto-Baud Rate Detect feature. For both methods, the user can set the ABDEN bit once the TXxIF interrupt is observed.



#### FIGURE 20-10: SEND BREAK CHARACTER SEQUENCE

#### 20.3 EUSARTx Synchronous Master Mode

The Synchronous Master mode is entered by setting the CSRC bit (TXSTAx<7>). In this mode, the data is transmitted in a half-duplex manner (i.e., transmission and reception do not occur at the same time). When transmitting data, the reception is inhibited and vice versa. Synchronous mode is entered by setting bit, SYNC (TXSTAx<4>). In addition, enable bit, SPEN (RCSTAx<7>), is set in order to configure the TXx and RXx pins to CKx (clock) and DTx (data) lines, respectively.

Clock polarity (CKx) is selected with the TXCKP bit (BAUDCON<4>). Setting TXCKP sets the Idle state on CKx as high, while clearing the bit sets the Idle state as low. Data polarity (DTx) is selected with the RXDTP bit (BAUDCONx<5>). Setting RXDTP sets the Idle state on DTx as high, while clearing the bit sets the Idle state as low. DTx is sampled when CKx returns to its Idle state. This option is provided to support Microwire devices with this module.

#### 20.3.1 EUSARTx SYNCHRONOUS MASTER TRANSMISSION


The EUSARTx transmitter block diagram is shown in Figure 20-3. The heart of the transmitter is the Transmit (Serial) Shift Register (TSR). The Shift register obtains its data from the Read/Write Transmit Buffer register, TXREGx. The TXREGx register is loaded with data in software. The TSR register is not loaded until the last bit has been transmitted from the previous load. As soon as the last bit is transmitted, the TSR is loaded with new data from the TXREGx (if available).

Once the TXREGx register transfers the data to the TSR register (occurs in one TcY), the TXREGx is empty and the TXxIF flag bit is set. The interrupt can be enabled or disabled by setting or clearing the interrupt enable bit, TXxIE. TXxIF is set regardless of the state of enable bit, TXxIE; it cannot be cleared in software. It will reset only when new data is loaded into the TXREGx register.


While flag bit, TXxIF, indicates the status of the TXREGx register, another bit, TRMT (TXSTAx<1>), shows the status of the TSR register. TRMT is a read-only bit which is set when the TSR is empty. No interrupt logic is tied to this bit, so the user must poll this bit in order to determine if the TSR register is empty. The TSR is not mapped in data memory so it is not available to the user.

To set up a Synchronous Master Transmission:

- 1. Initialize the SPBRGHx:SPBRGx registers for the appropriate baud rate. Set or clear the BRG16 bit, as required, to achieve the desired baud rate.
- 2. Enable the synchronous master serial port by setting bits, SYNC, SPEN and CSRC.
- 3. If the signal from the CKx pin is to be inverted, set the TXCKP bit. If the signal from the DTx pin is to be inverted, set the RXDTP bit.
- 4. If interrupts are desired, set enable bit, TXxIE.
- 5. If 9-bit transmission is desired, set bit, TX9.
- 6. Enable the transmission by setting bit, TXEN.
- 7. If 9-bit transmission is selected, the ninth bit should be loaded in bit, TX9D.
- 8. Start transmission by loading data to the TXREGx register.
- If using interrupts, ensure that the GIE and PEIE bits in the INTCON register (INTCON<7:6>) are set.



#### FIGURE 20-11: SYNCHRONOUS TRANSMISSION



#### FIGURE 20-12: SYNCHRONOUS TRANSMISSION (THROUGH TXEN)

<b>TABLE 20-7:</b>	REGISTERS ASSOCIATED WITH SYNCHRONOUS MASTER TRANSMISSION
--------------------	---

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR3	SSP2IF	BCL2IF	RC2IF	TX2IF <sup>(1)</sup>	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE	BCL2IE	RC2IE	TX2IE <sup>(1)</sup>	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP	BCL2IP	RC2IP	TX2IP <sup>(1)</sup>	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
RCSTAx	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	61
TXREGx	EUSARTx Transmit Register								
TXSTAx	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	61
BAUDCONx	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	—	WUE	ABDEN	62
SPBRGHx	EUSARTx Baud Rate Generator Register High Byte								62
SPBRGx	EUSARTx Baud Rate Generator Register Low Byte								62

Legend: — = unimplemented, read as '0'. Shaded cells are not used for synchronous master transmission.

Note 1: These bits are only available in 80-pin and 100-pin devices; otherwise, they are unimplemented and read as '0'.

#### 20.3.2 EUSARTx SYNCHRONOUS MASTER RECEPTION


Once Synchronous mode is selected, reception is enabled by setting either the Single Receive Enable bit, SREN (RCSTAx<5>), or the Continuous Receive Enable bit, CREN (RCSTAx<4>). Data is sampled on the RXx pin on the falling edge of the clock.

If enable bit, SREN, is set, only a single word is received. If enable bit, CREN, is set, the reception is continuous until CREN is cleared. If both bits are set, then CREN takes precedence.

To set up a Synchronous Master Reception:

- 1. Initialize the SPBRGHx:SPBRGx registers for the appropriate baud rate. Set or clear the BRG16 bit, as required, to achieve the desired baud rate.
- 2. Enable the synchronous master serial port by setting bits, SYNC, SPEN and CSRC.
- 3. Ensure bits, CREN and SREN, are clear.

- 4. If the signal from the CKx pin is to be inverted, set the TXCKP bit. If the signal from the DTx pin is to be inverted, set the RXDTP bit.
- 5. If interrupts are desired, set enable bit, RCxIE.
- 6. If 9-bit reception is desired, set bit, RX9.
- 7. If a single reception is required, set bit, SREN. For continuous reception, set bit, CREN.
- 8. Interrupt flag bit, RCxIF, will be set when reception is complete and an interrupt will be generated if the enable bit, RCxIE, was set.
- 9. Read the RCSTAx register to get the 9th bit (if enabled) and determine if any error occurred during reception.
- 10. Read the 8-bit received data by reading the RCREGx register.
- 11. If any error occurred, clear the error by clearing bit, CREN.
- 12. If using interrupts, ensure that the GIE and PEIE bits in the INTCON register (INTCON<7:6>) are set.



#### FIGURE 20-13: SYNCHRONOUS RECEPTION (MASTER MODE, SREN)

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR3	SSP2IF	BCL2IF	RC2IF <sup>(1)</sup>	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE	BCL2IE	RC2IE <sup>(1)</sup>	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP	BCL2IP	RC2IP <sup>(1)</sup>	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
RCSTAx	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	61
RCREGx	EUSARTx Receive Register								
TXSTAx	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	61
BAUDCONx	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	_	WUE	ABDEN	62
SPBRGHx	EUSARTx Baud Rate Generator Register High Byte								62
SPBRGx	EUSARTx Baud Rate Generator Register Low Byte								62

#### TABLE 20-8: REGISTERS ASSOCIATED WITH SYNCHRONOUS MASTER RECEPTION

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used for synchronous master reception.

Note 1: These bits are only available in 80-pin and 100-pin devices; otherwise, they are unimplemented and read as '0'.

#### 20.4 EUSARTx Synchronous Slave Mode

Synchronous Slave mode is entered by clearing bit, CSRC (TXSTAx<7>). This mode differs from the Synchronous Master mode in that the shift clock is supplied externally at the CKx pin (instead of being supplied internally in Master mode). This allows the device to transfer or receive data while in any low-power mode.

#### 20.4.1 EUSARTx SYNCHRONOUS SLAVE TRANSMISSION

The operation of the Synchronous Master and Slave modes is identical, except in the case of Sleep mode.

If two words are written to the TXREGx and then the  ${\tt SLEEP}$  instruction is executed, the following will occur:

- a) The first word will immediately transfer to the TSR register and transmit.
- b) The second word will remain in the TXREGx register.
- c) Flag bit, TXxIF, will not be set.
- d) When the first word has been shifted out of TSR, the TXREGx register will transfer the second word to the TSR and flag bit, TXxIF, will now be set.
- e) If enable bit, TXxIE, is set, the interrupt will wake the chip from Sleep. If the global interrupt is enabled, the program will branch to the interrupt vector.

To set up a Synchronous Slave Transmission:

- Enable the synchronous slave serial port by setting bits, SYNC and SPEN, and clearing bit, CSRC.
- 2. Clear bits, CREN and SREN.
- 3. If the signal from the CKx pin is to be inverted, set the TXCKP bit. If the signal from the DTx pin is to be inverted, set the RXDTP bit.
- 4. If interrupts are desired, set enable bit, TXxIE.
- 5. If 9-bit transmission is desired, set bit, TX9.
- 6. Enable the transmission by setting enable bit, TXEN.
- 7. If 9-bit transmission is selected, the ninth bit should be loaded in bit TX9D.
- 8. Start transmission by loading data to the TXREGx register.
- If using interrupts, ensure that the GIE and PEIE bits in the INTCON register (INTCON<7:6>) are set.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	<b>GIE/GIEH</b>	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR3	SSP2IF	BCL2IF	RC2IF	TX2IF <sup>(1)</sup>	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE	BCL2IE	RC2IE	TX2IE <sup>(1)</sup>	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP	BCL2IP	RC2IP	TX2IP <sup>(1)</sup>	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
RCSTAx	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	61
TXREGx	EUSARTx	Transmit Reg	gister						61
TXSTAx	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	61
BAUDCONx	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	—	WUE	ABDEN	62
SPBRGHx	RGHx EUSARTx Baud Rate Generator Register High Byte								62
SPBRGx	BRGx EUSARTx Baud Rate Generator Register Low Byte								62

#### TABLE 20-9: REGISTERS ASSOCIATED WITH SYNCHRONOUS SLAVE TRANSMISSION

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used for synchronous slave transmission.

Note 1: These bits are only available in 80-pin and 100-pin devices; otherwise, they are unimplemented and read as '0'.

#### 20.4.2 EUSARTX SYNCHRONOUS SLAVE RECEPTION

The operation of the Synchronous Master and Slave modes is identical, except in the case of Sleep or any Idle mode, and bit SREN, which is a "don't care" in Slave mode.

If receive is enabled by setting the CREN bit prior to entering Sleep or any Idle mode, then a word may be received while in this low-power mode. Once the word is received, the RSR register will transfer the data to the RCREGx register. If the RCxIE enable bit is set, the interrupt generated will wake the chip from the low-power mode. If the global interrupt is enabled, the program will branch to the interrupt vector. To set up a Synchronous Slave Reception:

- 1. Enable the synchronous master serial port by setting bits, SYNC and SPEN, and clearing bit, CSRC.
- 2. If interrupts are desired, set enable bit, RCxIE.
- 3. If the signal from the CKx pin is to be inverted, set the TXCKP bit. If the signal from the DTx pin is to be inverted, set the RXDTP bit.
- 4. If 9-bit reception is desired, set bit, RX9.
- 5. To enable reception, set enable bit, CREN.
- Flag bit, RCxIF, will be set when reception is complete. An interrupt will be generated if enable bit, RCxIE, was set.
- 7. Read the RCSTAx register to get the 9th bit (if enabled) and determine if any error occurred during reception.
- 8. Read the 8-bit received data by reading the RCREGx register.
- 9. If any error occurred, clear the error by clearing bit, CREN.
- 10. If using interrupts, ensure that the GIE and PEIE bits in the INTCON register (INTCON<7:6>) are set.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR3	SSP2IF	BCL2IF	RC2IF <sup>(1)</sup>	TX2IF	TMR4IF	CCP5IF	CCP4IF	CCP3IF	61
PIE3	SSP2IE	BCL2IE	RC2IE <sup>(1)</sup>	TX2IE	TMR4IE	CCP5IE	CCP4IE	CCP3IE	61
IPR3	SSP2IP	BCL2IP	RC2IP <sup>(1)</sup>	TX2IP	TMR4IP	CCP5IP	CCP4IP	CCP3IP	61
RCSTAx	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	61
RCREGx	EUSARTx	Receive Reg	gister						61
TXSTAx	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	61
BAUDCONx	ABDOVF	RCIDL	RXDTP	TXCKP	BRG16	—	WUE	ABDEN	62
SPBRGHx	RGHx EUSARTx Baud Rate Generator Register High Byte								62
SPBRGx	EUSARTx	Baud Rate G	Generator R	egister Low	Byte				62

#### TABLE 20-10: REGISTERS ASSOCIATED WITH SYNCHRONOUS SLAVE RECEPTION

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used for synchronous slave reception.

Note 1: These bits are only available in 80-pin and 100-pin devices; otherwise, they are unimplemented and read as '0'.

## 21.0 10-BIT ANALOG-TO-DIGITAL CONVERTER (A/D) MODULE

The Analog-to-Digital (A/D) converter module has 11 inputs for the 64-pin devices, 15 inputs for the 80-pin devices and 16 inputs for the 100-pin devices. This module allows conversion of an analog input signal to a corresponding 10-bit digital number.

The module has five registers:

- A/D Result Register High Byte (ADRESH)
- A/D Result Register Low Byte (ADRESL)
- A/D Control Register 0 (ADCON0)
- A/D Control Register 1 (ADCON1)
- A/D Control Register 2 (ADCON2)

The ADCON0 register, shown in Register 21-1, controls the operation of the A/D module. The ADCON1 register, shown in Register 21-2, configures the functions of the port pins. The ADCON2 register, shown in Register 21-3, configures the A/D clock source, programmed acquisition time and justification.

### REGISTER 21-1: ADCON0: A/D CONTROL REGISTER 0

R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
ADCAL		CHS3	CHS2	CHS1	CHS0	GO/DONE	ADON
bit 7	·					· · ·	bit C
Legend:							
R = Reada	able bit	W = Writable	bit	U = Unimpler	mented bit, rea	ad as '0'	
-n = Value		'1' = Bit is set		'0' = Bit is cle		x = Bit is unkn	own
				0 2.1.0 0.0			•••••
bit 7	ADCAL: A/D	Calibration bit					
		n is performed					
	0 = Normal A	/D converter op	peration (no c	alibration is pe	rformed)		
bit 6	Unimplemen	ted: Read as '	כ'				
bit 5-2		Analog Chann	el Select bits				
	0000 <b>= Chan</b>	· /					
	0001 <b>= Chan</b> 0010 <b>= Chan</b>	( )					
	0010 <b>– Chan</b>						
	0100 <b>= Chan</b>						
		nel 5 (AN5) <sup>(1,3)</sup>	1				
	0110 <b>= Chan</b>						
	0111 = Chan	( )					
	1000 <b>= Chan</b>						
	1001 <b>= Chan</b>	nel 9 (AN9) nel 10 (AN10)					
		nel 11 (AN11)					
		nel 12 (AN12) <sup>(2</sup>	2,3)				
	1101 <b>= Chan</b>	nel 13 (AN13) <sup>(2</sup>	2,3)				
		nel 14 (AN14) <sup>(2</sup>					
	1111 <b>= Chan</b>	nel 15 (AN15) <sup>(2</sup>	2,3)				
bit 1		/D Conversion	Status bit				
	When ADON						
	1 = A/D conve 0 = A/D Idle	ersion in progre	ess				
hit O		)n hit					
bit 0	<b>ADON:</b> A/D C		anablad				
		erter module is erter module is					
Note 1:	This channel is imp	plemented on 1	00-pin device	es only.			
2:	These channels ar	e implemented	on 80-pin an	d 100-pin devi	ces only.		
3:	Performing a conv	ersion on unim	plemented ch	annels will retu	irn random val	lues	

3: Performing a conversion on unimplemented channels will return random values.

REGISTER 21-2: AD	DCON1: A/D CONTROL	REGISTER 1
-------------------	--------------------	------------

U-0	U-0		R/V	V-0	F	R/W-0		R/W-	0	R	2/W-0		R/\	N-0		R/W	/-0
_	_		VCF	G1	V	CFG0		PCFC	63	P	CFG2		PC	FG1		PCF	G0
bit 7																	bit
Legend:																	
R = Readabl	le bit	V	v = w	ritable	bit		U	= Uni	mplen	nenteo	d bit, ı	read a	is '0'				
-n = Value at	t POR	، ،	1' = Bi	t is se	t		'O'	= Bit	is cle	ared		X	c = Bit	is un	know	'n	
bit 7-6	Unimpler	nente	d: Re	ad as	'0'												
bit 5	VCFG1: \	/oltage	e Refe	erence	Confi	guratio	on bit	(Vref	- sour	ce)							
	1 = VREF-	(AN2	)														
	0 = AVss																
bit 4	VCFG0: \	•		erence	Confi	guratio	on bit	(Vref	+ sou	rce)							
	1 = VREF+	- (AN3	3)														
	0 <b>= AV</b> DD			<b>-</b> · -			•										
bit 3-0	PCFG3:P				-	uration	Cont	rol bit	S:			1		1	T		
	PCFG3:	AN15 <sup>(1)</sup>	AN14 <sup>(1)</sup>	AN13 <sup>(1)</sup>	AN12 <sup>(1)</sup>	~	0					(2)	_			(3)	(3)
	PCFG0	N1	ľ,	ľ,	ľN1	AN11	AN10	AN9	AN8	AN7	AN6	AN5 <sup>(2)</sup>	AN4	AN3	AN2	AN1 <sup>(3)</sup>	AN0 <sup>(3)</sup>
							-	-	-	-			-	-			
	0000	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A
	0001	D	D	A	A	A	A	A	A	A	A	A	A	A	A	A	A
	0010	D D	D	D	A D	A A	A	A	A A	A A	A	A A	A A	A A	A	A A	A
	0011	D	D	D	D	D	A A	A	A	A	A	A	A	A	A A	A	A
	0100	D	D	D	D	D	 D	A	A	A	A	A	A	A	A	A	A
	0101	D	D	D	D	D	D	D	A	A	A	A	A	A	A	A	A
	0111	D	D	D	D	D	D	D	D	A	A	A	A	A	A	A	A
	1000	D	D	D	D	D	D	D	D	D	А	А	Α	Α	Α	А	A
	1001	D	D	D	D	D	D	D	D	D	D	А	А	Α	Α	Α	A
	1010	D	D	D	D	D	D	D	D	D	D	D	Α	Α	Α	Α	Α
	1011	D	D	D	D	D	D	D	D	D	D	D	D	Α	Α	Α	A
	1100	D	D	D	D	D	D	D	D	D	D	D	D	D	Α	Α	Α
	1101	D	D	D	D	D	D	D	D	D	D	D	D	D	D	Α	A
	1110	D	D	D	D	D	D	D	D	D	D	D	D	D	D	D	A
	1111	D	D	D	D	D	D	D	D	D	D	D	D	D	D	D	D
	A = Analo	na inn	4					= Digi									

Note 1: AN12 through AN15 are available in 80-pin and 100-pin devices only.

- 2: AN5 is available in 100-pin devices only.
- 3: AN0 and AN1 can also operate as Ethernet LED outputs in either Analog or Digital I/O modes.

REGISTER 2	21-3: ADCO	N2: A/D COI	NTROL REG	SISTER 2			
R/W-0	U-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
ADFM		ACQT2	ACQT1	ACQT0	ADCS2	ADCS1	ADCS0
bit 7	•			·		·	bit
Legend:							
R = Readable	e bit	W = Writable	bit	U = Unimpler	nented bit, read	l as '0'	
-n = Value at I	POR	'1' = Bit is set	t	'0' = Bit is cle	ared	x = Bit is unki	nown
bit 7	<b>ADFM:</b> A/D R 1 = Right justi 0 = Left justifie	fied	Select bit				
bit 6	Unimplement	t <b>ed:</b> Read as '	0'				
	111 = 20 TAD 110 = 16 TAD 101 = 12 TAD 100 = 8 TAD 011 = 6 TAD 010 = 4 TAD 001 = 2 TAD 000 = 0 TAD <sup>(1</sup>	)					
bit 2-0	ADCS2:ADC3 111 = FRC (cl 110 = Fosc/6 101 = Fosc/1 100 = Fosc/4 011 = FRC (cl 010 = Fosc/3 001 = Fosc/8 000 = Fosc/2	ock derived fro 4 6 ock derived fro 2	om A/D RC os	scillator) <sup>(1)</sup>			

## REGISTER 21-3: ADCON2: A/D CONTROL REGISTER 2

**Note 1:** If the A/D FRC clock source is selected, a delay of one TCY (instruction cycle) is added before the A/D clock starts. This allows the SLEEP instruction to be executed before starting a conversion.

The analog reference voltage is software selectable to either the device's positive and negative supply voltage (AVDD and AVSS), or the voltage level on the RA3/AN3/VREF+ and RA2/AN2/VREF- pins.

The A/D converter has a unique feature of being able to operate while the device is in Sleep mode. To operate in Sleep, the A/D conversion clock must be derived from the A/D converter's internal RC oscillator.

The output of the sample and hold is the input into the converter, which generates the result via successive approximation.

Each port pin associated with the A/D converter can be configured as an analog input or as a digital I/O. The ADRESH and ADRESL registers contain the result of




FIGURE 21-1: A/D BLOCK DIAGRAM

the A/D conversion. When the A/D conversion is complete, the result is loaded into the ADRESH:ADRESL register pair, the GO/DONE bit (ADCON0<1>) is cleared and A/D Interrupt Flag bit, ADIF, is set.

A device Reset forces all registers to their Reset state. This forces the A/D module to be turned off and any conversion in progress is aborted. The value in the ADRESH:ADRESL register pair is not modified for a Power-on Reset. These registers will contain unknown data after a Power-on Reset.

The block diagram of the A/D module is shown in Figure 21-1.


After the A/D module has been configured as desired, the selected channel must be acquired before the conversion is started. The analog input channels must have their corresponding TRIS bits selected as inputs. To determine acquisition time, see **Section 21.1 "A/D Acquisition Requirements"**. After this acquisition time has elapsed, the A/D conversion can be started. An acquisition time can be programmed to occur between setting the GO/DONE bit and the actual start of the conversion.

The following steps should be followed to do an A/D conversion:

- 1. Configure the A/D module:
  - Configure analog pins, voltage reference and digital I/O (ADCON1)
  - Select A/D input channel (ADCON0)
  - Select A/D acquisition time (ADCON2)
  - Select A/D conversion clock (ADCON2)
  - Turn on A/D module (ADCON0)

### FIGURE 21-2: ANALOG INPUT MODEL

- 2. Configure A/D interrupt (if desired):
  - Clear ADIF bit
  - Set ADIE bit
  - Set GIE bit
- 3. Wait the required acquisition time (if required).
- 4. Start conversion:
  - Set GO/DONE bit (ADCON0<1>)
- 5. Wait for A/D conversion to complete, by either:
  Polling for the GO/DONE bit to be cleared OR
  - Waiting for the A/D interrupt
- 6. Read A/D Result registers (ADRESH:ADRESL); clear bit, ADIF, if required.
- 7. For next conversion, go to step 1 or step 2, as required. The A/D conversion time per bit is defined as TAD. A minimum wait of 2 TAD is required before next acquisition starts.



## 21.1 A/D Acquisition Requirements

For the A/D converter to meet its specified accuracy, the charge holding capacitor (CHOLD) must be allowed to fully charge to the input channel voltage level. The Analog Input model is shown in Figure 21-2. The source impedance (Rs) and the internal sampling switch (Rss) impedance directly affect the time required to charge the capacitor, CHOLD. The sampling switch (Rss) impedance varies over the device voltage (VDD). The source impedance affects the offset voltage at the analog input (due to pin leakage current). The maximum recommended impedance for analog sources is 2.5 k $\Omega$ . After the analog input channel is selected (changed), the channel must be sampled for at least the minimum acquisition time before starting a conversion.

Note:	When	the	conversion	is	started,	the
	holding	) capa	acitor is disco	nne	ected from	the
	input p	in.				

EQUATION 21-1: ACQUISITION TIME

TACQ = Amplifier Settling Time + Holding Capacitor Charging Time + Temperature Coefficient = TAMP + TC + TCOFF

#### EQUATION 21-2: A/D MINIMUM CHARGING TIME

VHOLD	=	$(\text{VREF} - (\text{VREF}/2048)) \cdot (1 - e^{(-\text{TC/CHOLD}(\text{RIC} + \text{RSS} + \text{RS}))})$
or		
TC	=	-(CHOLD)(RIC + RSS + RS) ln(1/2048)

#### EQUATION 21-3: CALCULATING THE MINIMUM REQUIRED ACQUISITION TIME

TACQ	=	TAMP + TC + TCOFF
TAMP	=	0.2 μs
TCOFF	=	(Temp – 25°C)(0.02 μs/°C) (85°C – 25°C)(0.02 μs/°C) 1.2 μs
Tempera	ture c	oefficient is only required for temperatures $> 25^{\circ}$ C. Below 25°C, TCOFF = 0 ms.
Тс	=	-(CHOLD)(RIC + Rss + Rs) ln(1/2048) $\mu$ s -(25 pF) (1 k $\Omega$ + 2 k $\Omega$ + 2.5 k $\Omega$ ) ln(0.0004883) $\mu$ s 1.05 $\mu$ s
TACQ	=	0.2 μs + 1 μs + 1.2 μs 2.4 μs

To calculate the minimum acquisition time, Equation 21-1 may be used. This equation assumes that 1/2 LSb error is used (1024 steps for the A/D). The 1/2 LSb error is the maximum error allowed for the A/D to meet its specified resolution.

Equation 21-3 shows the calculation of the minimum required acquisition time, TACQ. This calculation is based on the following application system assumptions:

=	25 pF
=	2.5 kΩ
$\leq$	1/2 LSb
=	$3V \rightarrow Rss = 2 k\Omega$
=	85°C (system max.)
	= ≤

## 21.2 Selecting and Configuring Automatic Acquisition Time

The ADCON2 register allows the user to select an acquisition time that occurs each time the GO/DONE bit is set.

When the GO/DONE bit is set, sampling is stopped and a conversion begins. The user is responsible for ensuring the required acquisition time has passed between selecting the desired input channel and setting the GO/DONE bit. This occurs when the ACQT2:ACQT0 bits (ADCON2<5:3>) remain in their Reset state ('000') and is compatible with devices that do not offer programmable acquisition times.

If desired, the ACQT bits can be set to select a programmable acquisition time for the A/D module. When the GO/DONE bit is set, the A/D module continues to sample the input for the selected acquisition time, then automatically begins a conversion. Since the acquisition time is programmed, there may be no need to wait for an acquisition time between selecting a channel and setting the GO/DONE bit.

In either case, when the conversion is completed, the GO/DONE bit is cleared, the ADIF flag is set and the A/D begins sampling the currently selected channel again. If an acquisition time is programmed, there is nothing to indicate if the acquisition time has ended or if the conversion has begun.

### 21.3 Selecting the A/D Conversion Clock

The A/D conversion time per bit is defined as TAD. The A/D conversion requires 11 TAD per 10-bit conversion. The source of the A/D conversion clock is software selectable.

There are seven possible options for TAD:

- 2 Tosc
- 4 Tosc
- 8 Tosc
- 16 Tosc
- 32 Tosc
- 64 Tosc
- Internal RC Oscillator

For correct A/D conversions, the A/D conversion clock (TAD) must be as short as possible but greater than the minimum TAD. See **Section 27.0** "**Electrical Characteristics**", A/D parameter 130 in Table 27-27 for more information.

Table 21-1 shows the resultant TAD times derived from the device operating frequencies and the A/D clock source selected.

TABLE 21-1:	TAD VS. DEVICE OPERATING
	FREQUENCIES

AD Clock	AD Clock Source (TAD)						
Operation	ADCS2:ADCS0	Device Frequency					
2 Tosc	000	2.68 MHz					
4 Tosc	100	5.71 MHz					
8 Tosc	001	11.43 MHz					
16 Tosc	101	22.86 MHz					
32 Tosc	010	41.67 MHz					
64 Tosc	110	41.67 MHz					
RC <sup>(2)</sup>	x11	1.00 MHz <sup>(1)</sup>					

Note 1:	The RC source has a typical TAD time of
	4 ms.

**<sup>2:</sup>** See parameter 130 in Table 27-27 for A/D RC clock specifications.

## 21.4 Configuring Analog Port Pins

The ADCON1, TRISA, TRISF and TRISH registers control the operation of the A/D port pins. The port pins needed as analog inputs must have their corresponding TRIS bits set (input). If the TRIS bit is cleared (output), the digital output level (VOH or VOL) will be converted.

The A/D operation is independent of the state of the CHS3:CHS0 bits and the TRIS bits.

- Note 1: When reading the PORT register, all pins configured as analog input channels will read as cleared (a low level). Pins configured as digital inputs will convert an analog input. Analog levels on a digitally configured input will be accurately converted.
  - 2: Analog levels on any pin defined as a digital input may cause the digital input buffer to consume current out of the device's specification limits.

## 21.5 A/D Conversions

Figure 21-3 shows the operation of the A/D converter after the GO/DONE bit has been set and the ACQT2:ACQT0 bits are cleared. A conversion is started after the following instruction to allow entry into Sleep mode before the conversion begins.

Figure 21-4 shows the operation of the A/D converter after the GO/DONE bit has been set, the ACQT2:ACQT0 bits are set to '010' and a 4 TAD acquisition time has been selected before the conversion starts.

Clearing the GO/DONE bit during a conversion will abort the current conversion. The A/D Result register pair will NOT be updated with the partially completed A/D conversion sample. This means the ADRESH:ADRESL registers will continue to contain the value of the last completed conversion (or the last value written to the ADRESH:ADRESL registers).

After the A/D conversion is completed or aborted, a 2 TAD wait is required before the next acquisition can be started. After this wait, acquisition on the selected channel is automatically started.


Note:	The GO/DONE bit should NOT be set in
	the same instruction that turns on the A/D.

## 21.6 Use of the ECCP2 Trigger


An A/D conversion can be started by the "Special Event Trigger" of the ECCP2 module. This requires that the CCP2M3:CCP2M0 bits (CCP2CON<3:0>) be programmed as '1011' and that the A/D module is enabled (ADON bit is set). When the trigger occurs, the GO/DONE bit will be set, starting the A/D acquisition and conversion and the Timer1 (or Timer3) counter will be reset to zero. Timer1 (or Timer3) is reset to automatically repeat the A/D acquisition period with minimal software overhead (moving ADRESH/ADRESL to the desired location). The appropriate analog input channel must be selected and the minimum acquisition period is either timed by the user, or an appropriate TACQ time is <u>selected</u> before the Special Event Trigger sets the GO/DONE bit (starts a conversion).

If the A/D module is not enabled (ADON is cleared), the Special Event Trigger will be ignored by the A/D module but will still reset the Timer1 (or Timer3) counter.

#### FIGURE 21-3: A/D CONVERSION TAD CYCLES (ACQT2:ACQT0 = 000, TACQ = 0)



#### FIGURE 21-4: A/D CONVERSION TAD CYCLES (ACQT2:ACQT0 = 010, TACQ = 4 TAD)



## 21.7 A/D Converter Calibration

The A/D converter in the PIC18F97J60 family of devices includes a self-calibration feature which compensates for any offset generated within the module. The calibration process is automated and is initiated by setting the ADCAL bit (ADCON0<7>). The next time the GO/DONE bit is set, the module will perform a "dummy" conversion (that is, with reading none of the input channels) and store the resulting value internally to compensate for offset. Thus, subsequent offsets will be compensated.

The calibration process assumes that the device is in a relatively steady-state operating condition. If A/D calibration is used, it should be performed after each device Reset, or if there are other major changes in operating conditions.

### 21.8 Operation in Power-Managed Modes

The selection of the automatic acquisition time and A/D conversion clock is determined in part by the clock source and frequency while in a power-managed mode.

If the A/D is expected to operate while the device is in a power-managed mode, the ACQT2:ACQT0 and ADCS2:ADCS0 bits in ADCON2 should be updated in accordance with the power-managed mode clock that will be used. After the power-managed mode is entered (either of the power-managed Run modes), an A/D acquisition or conversion may be started. Once an acquisition or conversion is started, the device should continue to be clocked by the same power-managed mode clock source until the conversion has been completed. If desired, the device may be placed into the corresponding power-managed Idle mode during the conversion.

If the power-managed mode clock frequency is less than 1 MHz, the A/D RC clock source should be selected.

Operation in Sleep mode requires the A/D RC clock to be selected. If bits, ACQT2:ACQT0, are set to '000' and a conversion is started, the conversion will be delayed one instruction cycle to allow execution of the SLEEP instruction and entry to Sleep mode. The IDLEN and SCS bits in the OSCCON register must have already been cleared prior to starting the conversion.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR1	PSPIF	ADIF	RC1IF	TX1IF	SSP1IF	CCP1IF	TMR2IF	TMR1IF	61
PIE1	PSPIE	ADIE	RC1IE	TX1IE	SSP1IE	CCP1IE	TMR2IE	TMR1IE	61
IPR1	PSPIP	ADIP	RC1IP	TX1IP	SSP1IP	CCP1IP	TMR2IP	TMR1IP	61
PIR2	OSCFIF	CMIF	ETHIF	r	BCL1IF	—	TMR3IF	CCP2IF	61
PIE2	OSCFIE	CMIE	ETHIE	r	BCL1IE	_	TMR3IE	CCP2IE	61
IPR2	OSCFIP	CMIP	ETHIP	r	BCL1IP	_	TMR3IP	CCP2IP	61
ADRESH	A/D Resul	t Register Hi	gh Byte						60
ADRESL	A/D Resul	t Register Lo	w Byte						60
ADCON0	ADCAL	_	CHS3	CHS3	CHS1	CHS0	GO/DONE	ADON	60
ADCON1	_		VCFG1	VCFG0	PCFG3	PCFG2	PCFG1	PCFG0	60
ADCON2	ADFM		ACQT2	ACQT1	ACQT0	ADCS2	ADCS1	ADCS0	60
CCP2CON	P2M1	P2M0	DC2B1	DC2B0	CCP2M3	CCP2M2	CCP2M1	CCP2M0	60
PORTA	RJPU	_	RA5	RA4	RA3	RA2	RA1	RA0	62
TRISA	_		TRISA5	TRISA4	TRISA3	TRISA2	TRISA1	TRISA0	61
PORTF	RF7	RF6	RF5	RF4	RF3	RF2	RF1	RF0 <sup>(1)</sup>	62
TRISF	TRISF7	TRISF6	TRISF5	TRISF4	TRISF3	TRISF2	TRISF1	TRISF0 <sup>(1)</sup>	61
PORTH <sup>(2)</sup>	RH7	RH6	RH5	RH4	RH3	RH2	RH1	RH0	62
TRISH <sup>(2)</sup>	TRISH7	TRISH6	TRISH5	TRISH4	TRISH3	TRISH2	TRISH1	TRISH0	61

TABLE 21-2: SUMMARY OF A/D REGISTERS

**Legend:** — = unimplemented, read as '0', r = reserved. Shaded cells are not used for A/D conversion.

Note 1: Implemented in 100-pin devices only.

**2:** This register is not implemented on 64-pin devices.

NOTES:

## 22.0 COMPARATOR MODULE

The analog comparator module contains two comparators that can be configured in a variety of ways. The inputs can be selected from the analog inputs multiplexed with pins, RF1 through RF6, as well as the on-chip voltage reference (see Section 23.0 "Comparator Voltage Reference Module"). The digital outputs (normal or inverted) are available at the pin level and can also be read through the control register.

The CMCON register (Register 22-1) selects the comparator input and output configuration. Block diagrams of the various comparator configurations are shown in Figure 22-1.

#### REGISTER 22-1: CMCON: COMPARATOR CONTROL REGISTER

R-0	R-0	R/W-0	R/W-0	R/W-0	R/W-1	R/W-1	R/W-1
C2OUT	C1OUT	C2INV	C1INV	CIS	CM2	CM1	CM0
bit 7							bit 0
Legend:							
R = Readable	e bit	W = Writable	bit	-	mented bit, rea	ad as '0'	
-n = Value at	POR	'1' = Bit is set		'0' = Bit is cle	eared	x = Bit is unkr	nown
bit 7	When C2INV           1 = C2 VIN+ >           0 = C2 VIN+ <	> C2 VIN- < C2 VIN- <u>= 1:</u> < C2 VIN-	ut bit				
bit 6	0 = C2 VIN+ > C1OUT: Com When C1INV 1 = C1 VIN+ > 0 = C1 VIN+ - When C1INV 1 = C1 VIN+ - 0 = C1 VIN+ >	parator 1 Outp = 0: > C1 VIN- < C1 VIN- <u>= 1:</u> < C1 VIN-	ut bit				
bit 5	<b>C2INV</b> : Comp 1 = C2 output 0 = C2 output		t Inversion bi	t			
bit 4	<b>C1INV</b> : Comp 1 = C1 output 0 = C1 output		t Inversion bi	t			
bit 3	When CM2:C           1 = C1 VIN-C           C2 VIN-C           0 = C1 VIN-C           C2 VIN-C	connects to RFS connects to RFS connects to RF6 connects to RA	5/AN10/CVRE 3/AN8 6/AN11 4/AN9	F			
bit 2-0		omparator Mod hows the Com		s and the CM2	:CM0 bit settin	gs.	

© 2007 Microchip Technology Inc.

## 22.1 Comparator Configuration

FIGURE 22-1:

There are eight modes of operation for the comparators, shown in Figure 22-1. Bits CM2:CM0 of the CMCON register are used to select these modes. The TRISF register controls the data direction of the comparator pins for each mode. If the Comparator

**COMPARATOR I/O OPERATING MODES** 

mode is changed, the comparator output level may not be valid for the specified mode change delay shown in **Section 27.0 "Electrical Characteristics"**.

Note:	Comparator interrupts should be disabled
	during a Comparator mode change;
	otherwise, a false interrupt may occur.


**Comparator Outputs Disabled** Comparators Off (POR Default Value) CM2:CM0 = 111 CM2:CM0 = 000 RF6/AN11 A VIN-RF6/AN11 D VIN-Off (Read as '0') Off (Read as '0') C1 C1 VIN+ VIN+ RF5/AN10/ \_D RF5/AN10/ A + **CVREF** CVREF VIN-D Vin-RF4/AN9 А RF4/AN9 C2 Off (Read as '0') C2 Off (Read as '0') VIN+ VIN+ D RF3/AN8 Α RF3/AN8 Two Independent Comparators with Outputs Two Independent Comparators CM2:CM0 = 010 CM2:CM0 = 011 VIN-Α VIN-RF6/AN11 A RF6/AN11 C1 C10UT C1 C10UT VIN+ VIN+ RF5/AN10/ A RF5/AN10/ \_\_\_\_ **CVREF CVREF** RF2/AN7/C1OUT\* VIN-А RF4/AN9 VIN RF4/AN9 C2OUT C2 VIN+ RF3/AN8 Α C2OUT C2 VINI RF3/AN8 RF1/AN6/C2OUT\* **Two Common Reference Comparators** Two Common Reference Comparators with Outputs CM2:CM0 = 100 CM2:CM0 = 101 VIN-A VIN-RF6/AN11 \_\_\_\_ **RF6/AN11** C10UT C10UT C1 C1 VIN+ Vin+ **RF5/AN10/** RF5/AN10/ \_A **CVREF CVREF** RF2/AN7/C1OUT\* VIN-A RF4/AN9 RF4/AN9 А Vin-C2 C2OUT VINI D RF3/AN8 RF3/AN8 C2 C2OUT D VIN+ RF1/AN6/C2OUT\* Four Inputs Multiplexed to Two Comparators One Independent Comparator with Output CM2:CM0 = 001 CM2:CM0 = 110 RF6/AN11 Α RF6/AN11 A VIN-CIS = 0VIN-**RF5/AN10/** C1 C10UT CIS = 1VIN+ C10UT RF5/AN10/ \_\_\_\_ C1 VIN+ **CVREF CVREF** RF2/AN7/C1OUT\* RF4/AN9 **CIS =** 0 VIN-**CIS =** 1 RF3/AN8 C2OUT VIN+ C2 D VIN-RF4/AN9 Off (Read as '0') C2 VIN+ D RF3/AN8 CVREF From VREF module D = Digital Input CIS (CMCON<3>) is the Comparator Input Switch A = Analog Input, port reads zeros always \* Setting the TRISF<2:1> bits will disable the comparator outputs by configuring the pins as inputs.

## 22.2 Comparator Operation

A single comparator is shown in Figure 22-2, along with the relationship between the analog input levels and the digital output. When the analog input at VIN+ is less than the analog input VIN-, the output of the comparator is a digital low level. When the analog input at VIN+ is greater than the analog input VIN-, the output of the comparator is a digital high level. The shaded areas of the output of the comparator in Figure 22-2 represent the uncertainty due to input offsets and response time.

#### 22.3 Comparator Reference

Depending on the comparator operating mode, either an external or internal voltage reference may be used. The analog signal present at VIN- is compared to the signal at VIN+ and the digital output of the comparator is adjusted accordingly (Figure 22-2).



#### FIGURE 22-2: SINGLE COMPARATOR

#### 22.3.1 EXTERNAL REFERENCE SIGNAL

When external voltage references are used, the comparator module can be configured to have the comparators operate from the same or different reference sources. However, threshold detector applications may require the same reference. The reference signal must be between Vss and VDD and can be applied to either pin of the comparator(s).

#### 22.3.2 INTERNAL REFERENCE SIGNAL

The comparator module also allows the selection of an internally generated voltage reference from the comparator voltage reference module. This module is described in more detail in **Section 23.0 "Comparator Voltage Reference Module"**.

The internal reference is only available in the mode where four inputs are multiplexed to two comparators (CM2:CM0 = 110). In this mode, the internal voltage reference is applied to the VIN+ pin of both comparators.

## 22.4 Comparator Response Time

Response time is the minimum time, after selecting a new reference voltage or input source, before the comparator output has a valid level. If the internal reference is changed, the maximum delay of the internal voltage reference must be considered when using the comparator outputs. Otherwise, the maximum delay of the comparators should be used (see Section 27.0 "Electrical Characteristics").

### 22.5 Comparator Outputs


The comparator outputs are read through the CMCON register. These bits are read-only. The comparator outputs may also be directly output to the RF1 and RF2 I/O pins. When enabled, multiplexors in the output path of the RF1 and RF2 pins will switch and the output of each pin will be the unsynchronized output of the comparator. The uncertainty of each of the comparators is related to the input offset voltage and the response time given in the specifications. Figure 22-3 shows the comparator output block diagram.

The TRISF bits will still function as an output enable/ disable for the RF1 and RF2 pins while in this mode.

The polarity of the comparator outputs can be changed using the C2INV and C1INV bits (CMCON<5:4>).

- Note 1: When reading the PORT register, all pins configured as analog inputs will read as '0'. Pins configured as digital inputs will convert an analog input according to the Schmitt Trigger input specification.
  - 2: Analog levels on any pin defined as a digital input may cause the input buffer to consume more current than is specified.


### FIGURE 22-3: COMPARATOR OUTPUT BLOCK DIAGRAM



## 22.6 Comparator Interrupts

The comparator interrupt flag is set whenever there is a change in the output value of either comparator. Software will need to maintain information about the status of the output bits, as read from CMCON<7:6>, to determine the actual change that occurred. The CMIF bit (PIR2<6>) is the Comparator Interrupt Flag. The CMIF bit must be reset by clearing it. Since it is also possible to write a '1' to this register, a simulated interrupt may be initiated.

Both the CMIE bit (PIE2<6>) and the PEIE bit (INTCON<6>) must be set to enable the interrupt. In addition, the GIE bit (INTCON<7>) must also be set. If any of these bits are clear, the interrupt is not enabled, though the CMIF bit will still be set if an interrupt condition occurs.



The user, in the Interrupt Service Routine, can clear the interrupt in the following manner:

- a) Any read or write of CMCON will end the mismatch condition.
- b) Clear flag bit, CMIF.

A mismatch condition will continue to set flag bit, CMIF. Reading CMCON will end the mismatch condition and allow flag bit, CMIF, to be cleared.

## 22.7 Comparator Operation During Sleep

When a comparator is active and the device is placed in Sleep mode, the comparator remains active and the interrupt is functional, if enabled. This interrupt will wake-up the device from Sleep mode, when enabled. Each operational comparator will consume additional current, as shown in the comparator specifications. To minimize power consumption while in Sleep mode, turn off the comparators (CM2:CM0 = 111) before entering Sleep. If the device wakes up from Sleep, the contents of the CMCON register are not affected.

#### 22.8 Effects of a Reset


A device Reset forces the CMCON register to its Reset state, causing the comparator modules to be turned off (CM2:CM0 = 111). However, the input pins (RF3 through RF6) are configured as analog inputs by default on device Reset. The I/O configuration for these pins is determined by the setting of the PCFG3:PCFG0 bits (ADCON1<3:0>). Therefore, device current is minimized when analog inputs are present at Reset time.

## 22.9 Analog Input Connection Considerations

A simplified circuit for an analog input is shown in Figure 22-4. Since the analog pins are connected to a digital output, they have reverse biased diodes to VDD and Vss. The analog input, therefore, must be between Vss and VDD. If the input voltage deviates from this

range by more than 0.6V in either direction, one of the diodes is forward biased and a latch-up condition may occur. A maximum source impedance of 10 k $\Omega$  is recommended for the analog sources. Any external component connected to an analog input pin, such as a capacitor or a Zener diode, should have very little leakage current.





Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
INTCON	GIE/GIEH	PEIE/GIEL	TMR0IE	INT0IE	RBIE	TMR0IF	INT0IF	RBIF	59
PIR2	OSCFIF	CMIF	ETHIF	r	BCL1IF	—	TMR3IF	CCP2IF	61
PIE2	OSCFIE	CMIE	ETHIE	r	BCL1IE	—	TMR3IE	CCP2IE	61
IPR2	OSCFIP	CMIP	ETHIP	r	BCL1IP	_	TMR3IP	CCP2IP	61
CMCON	C2OUT	C10UT	C2INV	C1INV	CIS	CM2	CM1	CM0	60
CVRCON	CVREN	CVROE	CVRR	CVRSS	CVR3	CVR2	CVR1	CVR0	60
PORTF	RF7	RF6	RF5	RF4	RF3	RF2	RF1	RF0	62
TRISF	TRISF7	TRISF6	TRISF5	TRISF4	TRISF3	TRISF2	TRISF1	TRISF0	61

Legend: — = unimplemented, read as '0', r = reserved. Shaded cells are not used by the comparator module.

NOTES:

## 23.0 COMPARATOR VOLTAGE REFERENCE MODULE

The comparator voltage reference is a 16-tap resistor ladder network that provides a selectable reference voltage. Although its primary purpose is to provide a reference for the analog comparators, it may also be used independently of them.

A block diagram of the module is shown in Figure 23-1. The resistor ladder is segmented to provide two ranges of CVREF values and has a power-down function to conserve power when the reference is not being used. The module's supply reference can be provided from either device VDD/VSS or an external voltage reference.

### 23.1 Configuring the Comparator Voltage Reference

The voltage reference module is controlled through the CVRCON register (Register 23-1). The comparator voltage reference provides two ranges of output voltage, each with 16 distinct levels. The range to be used

is selected by the CVRR bit (CVRCON<5>). The primary difference between the ranges is the size of the steps selected by the CVREF selection bits (CVR3:CVR0), with one range offering finer resolution. The equations used to calculate the output of the comparator voltage reference are as follows:

<u>If CVRR = 1:</u> CVREF = ((CVR3:CVR0)/24) x (CVRSRC) <u>If CVRR = 0:</u> CVREF = (CVRSRC/4) + ((CVR3:CVR0)/32) x (CVRSRC)

The comparator reference supply voltage can come from either VDD and VSS, or the external VREF+ and VREF- that are multiplexed with RA2 and RA3. The voltage source is selected by the CVRSS bit (CVRCON<4>).


The settling time of the comparator voltage reference must be considered when changing the CVREF output (see Table 27-3 in **Section 27.0 "Electrical Characteristics"**).

## REGISTER 23-1: CVRCON: COMPARATOR VOLTAGE REFERENCE CONTROL REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
CVREN	CVROE <sup>(1)</sup>	CVRR	CVRSS	CVR3	CVR2	CVR1	CVR0
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	l as '0'	
-n = Value at F	POR	'1' = Bit is set		'0' = Bit is cle	ared	x = Bit is unkr	nown
bit 7	CVREN: Com	parator Voltage	e Reference E	Enable bit			
		rcuit powered or rcuit powere					
bit 6	CVROE: Com	parator VREF (	Output Enable	e bit <sup>(1)</sup>			
		0		the RF5/AN10 he RF5/AN10/			
bit 5	1 = 0 to 0.66	•	n CVRsRc/24	step size (low r	ange) size (high rang	e)	
bit 4		parator VREF S				,	
				RC = (VREF+) – RC = VDD – VSS	· · ·		
bit 3-0	CVR3:CVR0:	Comparator V	REF Value Se	lection bits (0 $\leq$	(CVR3:CVR0)	≤ 15)	
	<u>When CVRR</u> CVREF = ((CV	<u>= 1:</u> ′R3:CVR0)/24)	• (CVRSRC)				
	When CVRR CVREF = (CVF						

**Note 1:** CVROE overrides the TRISF<5> bit setting.

© 2007 Microchip Technology Inc.



#### FIGURE 23-1: COMPARATOR VOLTAGE REFERENCE BLOCK DIAGRAM

## 23.2 Comparator Voltage Reference Accuracy/Error

The full range of voltage reference cannot be realized due to the construction of the module. The transistors on the top and bottom of the resistor ladder network (Figure 23-1) keep CVREF from approaching the reference source rails. The voltage reference is derived from the reference source; therefore, the CVREF output changes with fluctuations in that source. The tested absolute accuracy of the voltage reference can be found in **Section 27.0 "Electrical Characteristics"**.

## 23.3 Operation During Sleep

When the device wakes up from Sleep through an interrupt, or a Watchdog Timer time-out, the contents of the CVRCON register are not affected. To minimize current consumption in Sleep mode, the voltage reference should be disabled.

## 23.4 Effects of a Reset


A device Reset disables the voltage reference by clearing bit, CVREN (CVRCON<7>). This Reset also disconnects the reference from the RA2 pin by clearing bit, CVROE (CVRCON<6>), and selects the high-voltage range by clearing bit, CVRR (CVRCON<5>). The CVR value select bits are also cleared.

## 23.5 Connection Considerations

The voltage reference module operates independently of the comparator module. The output of the reference generator may be connected to the RF5 pin if the CVROE bit is set. Enabling the voltage reference output onto RA2 when it is configured as a digital input will increase current consumption. Connecting RF5 as a digital output with CVRSS enabled will also increase current consumption.

The RF5 pin can be used as a simple D/A output with limited drive capability. Due to the limited current drive capability, a buffer must be used on the voltage reference output for external connections to VREF. Figure 23-2 shows an example buffering technique.

#### FIGURE 23-2: COMPARATOR VOLTAGE REFERENCE OUTPUT BUFFER EXAMPLE



#### TABLE 23-1: REGISTERS ASSOCIATED WITH COMPARATOR VOLTAGE REFERENCE

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
CVRCON	CVREN	CVROE	CVRR	CVRSS	CVR3	CVR2	CVR1	CVR0	60
CMCON	C2OUT	C10UT	C2INV	C1INV	CIS	CM2	CM1	CM0	60
TRISF	TRISF7	TRISF6	TRISF5	TRISF4	TRISF3	TRISF2	TRISF1	TRISF0	61

Legend: — = unimplemented, read as '0'. Shaded cells are not used with the comparator voltage reference module.

NOTES:

## 24.0 SPECIAL FEATURES OF THE CPU

PIC18F97J60 family devices include several features intended to maximize reliability and minimize cost through elimination of external components. These are:

- · Oscillator Selection
- Resets:
  - Power-on Reset (POR)
  - Power-up Timer (PWRT)
  - Oscillator Start-up Timer (OST)
- Brown-out Reset (BOR)
- Interrupts
- Watchdog Timer (WDT)
- Fail-Safe Clock Monitor
- Two-Speed Start-up
- Code Protection
- In-Circuit Serial Programming

The oscillator can be configured for the application depending on frequency, power, accuracy and cost. All of the options are discussed in detail in **Section 2.0 "Oscillator Configurations"**.

A complete discussion of device Resets and interrupts is available in previous sections of this data sheet.

In addition to their Power-up and Oscillator Start-up Timers provided for Resets, the PIC18F97J60 family of devices has a configurable Watchdog Timer which is controlled in software.

The inclusion of an internal RC oscillator also provides the additional benefits of a Fail-Safe Clock Monitor (FSCM) and Two-Speed Start-up. FSCM provides for background monitoring of the peripheral clock and automatic switchover in the event of its failure. Two-Speed Start-up enables code to be executed almost immediately on start-up while the primary clock source completes its start-up delays.

All of these features are enabled and configured by setting the appropriate Configuration register bits.

## 24.1 Configuration Bits

The Configuration bits can be programmed (read as '0') or left unprogrammed (read as '1') to select various device configurations. These bits are mapped starting at program memory location 300000h. A complete list is shown in Table 24-1. A detailed explanation of the various bit functions is provided in Register 24-1 through Register 24-8.

#### 24.1.1 CONSIDERATIONS FOR CONFIGURING THE PIC18F97J60 FAMILY DEVICES

Devices of the PIC18F97J60 family do not use persistent memory registers to store configuration information. The configuration bytes are implemented as volatile memory which means that configuration data must be programmed each time the device is powered up.

Configuration data is stored in the four words at the top of the on-chip program memory space, known as the Flash Configuration Words, which are located in the program memory space as shown in Table 5-1. The Configuration Words are stored in the same order shown in Table 24-1, with CONFIG1L at the lowest address and CONFIG3H at the highest. The data is automatically loaded in the proper Configuration registers during device power-up.

When creating applications for these devices, users should always specifically allocate the location of the Flash Configuration Word for configuration data. This is to make certain that program code is not stored in this address when the code is compiled.

The volatile memory cells used for the Configuration bits always reset to '1' on Power-on Resets. For all other types of Reset events, the previously programmed values are maintained and used without reloading from program memory.

The four Most Significant bits of CONFIG1H, CONFIG2H and CONFIG3H in program memory should also be '1111'. This makes these Configuration Words appear to be NOP instructions in the remote event that their locations are ever executed by accident. Since Configuration bits are not implemented in the corresponding locations, writing '1's to these locations has no effect on device operation.

To prevent inadvertent configuration changes during code execution, all programmable Configuration bits are write-once. After a bit is initially programmed during a power cycle, it cannot be written to again. Changing a device configuration requires that power to the device be cycled.

#### TABLE 24-1: CONFIGURATION BITS AND DEVICE IDs

File	Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Default/ Unprogrammed Value <sup>(1)</sup>
300000h	CONFIG1L	DEBUG	XINST	STVREN	_	_		_	WDTEN	1101
300001h	CONFIG1H	(2)	(2)	(2)	(2)	(3)	CP0	_	_	01
300002h	CONFIG2L	IESO	FCMEN	_	_	_	FOSC2	FOSC1	FOSC0	11111
300003h	CONFIG2H	(2)	(2)	(2)	(2)	WDTPS3	WDTPS2	WDTPS1	WDTPS0	1111
300004h	CONFIG3L	WAIT <sup>(4)</sup>	BW <sup>(4)</sup>	EMB1 <sup>(4)</sup>	EMB0 <sup>(4)</sup>	EASHFT <sup>(4)</sup>		—	-	1111 1
300005h	CONFIG3H	(2)	(2)	(2)	(2)	_	ETHLED	ECCPMX <sup>(5)</sup>	CCP2MX <sup>(5)</sup>	111
3FFFFEh	DEVID1	DEV2	DEV1	DEV0	REV4	REV3	REV2	REV1	REV0	×××× ××××× (6)
3FFFFFh	DEVID2	DEV10	DEV9	DEV8	DEV7	DEV6	DEV5	DEV4	DEV3	XXXX XXXX <sup>(6)</sup>

 $\label{eq:logend: Legend: Legend: Legend: u = unchanged, - = unimplemented. Shaded cells are unimplemented, read as '0'.$ 

**Note 1:** Values reflect the unprogrammed state as received from the factory and following Power-on Resets. In all other Reset states, the configuration bytes maintain their previously programmed states.

2: The value of these bits in program memory should always be '1'. This ensures that the location is executed as a NOP if it is accidentally executed.

**3:** This bit should always be maintained as '0'.

4: Implemented on 100-pin devices only.

**5:** Implemented on 80-pin and 100-pin devices only.

6: See Register 24-7 and Register 24-8 for DEVID values. These registers are read-only and cannot be programmed by the user.

#### REGISTER 24-1: CONFIG1L: CONFIGURATION REGISTER 1 LOW (BYTE ADDRESS 300000h)

					· ·		,
R/WO-1	R/WO-1	R/WO-0	U-0	U-0	U-0	U-0	R/WO-1
DEBUG	XINST	STVREN	—	_	—	—	WDTEN
bit 7							bit C
Legend:							
R = Readable	e bit	WO = Write-C	nce bit	U = Unimplem	nented bit, read	l as '0'	
-n = Value wh	ien device is ur	nprogrammed		'1' = Bit is set		'0' = Bit is clea	ared
oit 7	DEBUG: Bac	kground Debug	ger Enable bit				
	•			•	•	l purpose I/O p	ins
	0 = Backgrou	und debugger e	nabled; RB6 a	nd RB7 are de	dicated to In-Ci	rcuit Debug	
oit 6	XINST: Exten	ded Instruction	Set Enable bit				
		n set extensior		•			
		n set extensior		-	de disabled (Le	gacy mode)	
oit 5	STVREN: Sta	ick Overflow/Ur	nderflow Reset	Enable bit			
		stack overflow					
	0 = Reset on	stack overflow	/underflow disa	abled			
bit 4-1	Unimplemen	ted: Read as '	כ'				
bit 0	WDTEN: Wat	chdog Timer E	nable bit				
	1 = WDT ena	abled					
	0 = WDT disa	abled (control is	s placed on SV	VDTEN bit)			

#### REGISTER 24-2: CONFIG1H: CONFIGURATION REGISTER 1 HIGH (BYTE ADDRESS 300001h)

U-0	U-0	U-0	U-0	U-0 <sup>(1)</sup>	R/WO-1	U-0	U-0
(2)	(2)	(2)	(2)	—	CP0	—	—
bit 7							bit 0

Legend:					
R = Readable bit	WO = Write-Once bit	U = Unimplemented bit, read as '0'			
-n = Value when device is ur	nprogrammed	'1' = Bit is set	'0' = Bit is cleared		

bit 7-3 Unimplemented: Read as '0'

bit 2 CP0: Code Protection bit

1 = Program memory is not code-protected

- 0 = Program memory is code-protected
- bit 1-0 Unimplemented: Read as '0'

**Note 1:** This bit should always be maintained as '0'.

2: The value of these bits in program memory should always be '1'. This ensures that the location is executed as a NOP if it is accidentally executed.

## REGISTER 24-3: CONFIG2L: CONFIGURATION REGISTER 2 LOW (BYTE ADDRESS 300002h)

					- (		,
R/WO-1	R/WO-1	U-0	U-0	U-0	R/WO-1	R/WO-1	R/WO-1
IESO	FCMEN	_	_	—	FOSC2	FOSC1	FOSC0
bit 7							bit C
Legend:							
R = Readab	ole bit	WO = Write-C	nce bit	U = Unimplen	nented bit, read	d as '0'	
-n = Value w	vhen device is ur	nprogrammed		'1' = Bit is set		'0' = Bit is clea	ared
bit 7	IESO: Two-S	peed Start-up (	nternal/Extern	al Oscillator Sw	vitchover) Cont	rol bit	
	1 = Two-Spee	ed Start-up ena	bled				
	0 = Two-Spee	ed Start-up disa	bled				
bit 6	FCMEN: Fail-	-Safe Clock Mo	nitor Enable b	it			
		Clock Monitor					
	0 = Fail-Safe	Clock Monitor	disabled				
bit 5-3	Unimplemen	ted: Read as '	)'				
bit 2	FOSC2: Defa	ult/Reset Syste	em Clock Sele	ct bit			
				system clock is o OSCCON<1:0>		OSCCON<1:0>	> = 00
bit 1-0	FOSC1:FOS	<b>C0:</b> Oscillator S	election bits				
		illator, PLL ena illator, CLKO fu		r software contr	ol, CLKO func	tion on OSC2	
				,∠ r software contr	ol		
	00 = HS osci	,			-		

## REGISTER 24-4: CONFIG2H: CONFIGURATION REGISTER 2 HIGH (BYTE ADDRESS 300003h)

					-		
U-0	U-0	U-0	U-0	R/WO-1	R/WO-1	R/WO-1	R/WO-1
(1)	(1)	(1)	(1)	WDTPS3	WDTPS2	WDTPS1	WDTPS0
oit 7							bit (
Legend:							
R = Readab	ole bit	WO = Write-O	nce bit	U = Unimplem	nented bit, read	l as '0'	
-n = Value v	when device is ur	nprogrammed		'1' = Bit is set		'0' = Bit is clea	ared
bit 7-4	Unimplemen	ted: Read as '0	,				
bit 3-0	WDTPS3:WD	TPS0: Watchde	og Timer Post	scale Select bit	S		
	1111 <b>= 1:32</b> ,	768					
	1110 <b>= 1:16</b> ,3	384					
	1101 <b>= 1:8,1</b> 9						
	1100 <b>= 1:4,0</b>						
	1011 = 1:2,04						
	1010 = 1:1,02						
	1001 = 1:512 1000 = 1:256						
	0111 = 1:128						
	0110 = <b>1</b> :64	•					
	0101 = 1:32						
	0100 = 1:16						
	0011 <b>= 1:8</b>						
	0010 <b>= 1:4</b>						
	0001 <b>= 1:2</b>						
	0000 = 1:1						

**Note 1:** The value of these bits in program memory should always be '1'. This ensures that the location is executed as a NOP if it is accidentally executed.

© 2007 Microchip Technology Inc.

## REGISTER 24-5: CONFIG3L: CONFIGURATION REGISTER 3 LOW (BYTE ADDRESS 300004h)

R/WO-1 WAIT <sup>(1)</sup> bit 7 Legend: R = Readable	R/WO-1 BW <sup>(1)</sup>	R/WO-1 EMB1 <sup>(1)</sup>	R/WO-1 EMB0 <sup>(1)</sup>	R/WO-1 EASHFT <sup>(1)</sup>	U-0 —	U-0 —	U-0 — bit (
bit 7 Legend:		EMB1 <sup>(1)</sup>	EMB0 <sup>(1)</sup>	EASHFT <sup>(1)</sup>	_	-	— bit (
Legend:							bit (
-							DIL
-							
R = Readable							
	bit	WO = Write-C	nce bit	U = Unimpleme	ented bit, read	as '0'	
-n = Value whe	en device is un	programmed		'1' = Bit is set		'0' = Bit is clea	red
bit 7 bit 6	1 = Wait state 0 = Wait state <b>BW:</b> Data Bus 1 = 16-Bit Da	es for operation Width Select ta Width mode	is on external is on external	memory bus disa memory bus ena		cted by MEMC0	ON<5:4>
bit 5-4				guration bits <sup>(1)</sup> lisabled			
	10 = Extende	ed Microcontrol ed Microcontrol	ler mode,12-E ler mode,16-E	Bit Addressing mo Bit Addressing mo Bit Addressing mo	de		
bit 3	1 = Address		d; address on	ble bit <sup>(1)</sup> external bus is of external bus refle			
bit 2-0	Unimplement	ted: Read as '	)'				

**Note 1:** Implemented on 100-pin devices only.

## REGISTER 24-6: CONFIG3H: CONFIGURATION REGISTER 3 HIGH (BYTE ADDRESS 300005h)

					•		,
U-0	U-0	U-0	U-0	U-0	R/WO-1	R/WO-1	R/WO-1
(1)	(1)	(1)	(1)	_	ETHLED	ECCPMX <sup>(2)</sup>	CCP2MX <sup>(2)</sup>
bit 7	÷					•	bit C
Legend:							
R = Read	dable bit	WO = Write-C	nce bit	U = Unimplem	nented bit, read	d as '0'	
-n = Valu	e when device is	unprogrammed		'1' = Bit is set		'0' = Bit is clea	ared
bit 7-3	Unimplem	ented: Read as '	)'				
bit 2	ETHLED: E	Ethernet LED Ena	ble bit				
	1 = RA0/R	A1 are multiplexe	d with LEDA/L	EDB when the	Ethernet modu	le is enabled a	nd function as
		en the Ethernet is					
	0 = RA0/R	A1 function as I/C	) regardless of	Ethernet modu	ile status		
bit 1	ECCPMX:	ECCP MUX bit <sup>(2)</sup>					
		1 outputs (P1B/P <sup>2</sup>					
		3 outputs (P3B/P3					
		1 outputs (P1B/P					
		3 outputs (P3B/P3	<i>,</i> .	exed with RH5	and RH4		
bit 0	CCP2MX:	ECCP2 MUX bit <sup>(2</sup>	)				
		2/P2A is multiplex					
		2/P2A is multiplex					evices)
	or with	RB3 in Extended	Microcontrolle	er mode (100-pi	in devices only	)	
Note 1:	The value of the	ese bits in progra	m memory sho	ould always be '	1'. This ensure	es that the locat	tion is
		NOP if it is accider					

**2:** Implemented on 80-pin and 100-pin devices only.

#### REGISTER 24-7: DEVID1: DEVICE ID REGISTER 1 FOR PIC18F97J60 FAMILY DEVICES

R	R	R	R	R	R	R	R
DEV2	DEV1	DEV0	REV4	REV3	REV2	REV1	REV0
bit 7	•		•		•		bit 0
Legend:							

R = Read-only bit	P = Programmable bit	U = Unimplemented bit, read as '0'
-n = Value when device	is unprogrammed	u = Unchanged from programmed state

bit 7-5	DEV2:DEV0: Device ID bits
	See Register 24-8 for a complete listing.
bit 4-0	REV4:REV0: Revision ID bits
	These bits are used to indicate the device revision.

#### REGISTER 24-8: DEVID2: DEVICE ID REGISTER 2 FOR PIC18F97J60 FAMILY DEVICES

R	R	R	R	R	R	R	R
DEV10	DEV9	DEV8	DEV7	DEV6	DEV5	DEV4	DEV3
bit 7							bit 0

## Legend:

R = Read-only bit	P = Programmable bit	U = Unimplemented bit, read as '0'
-n = Value when device is u	inprogrammed	u = Unchanged from programmed state

#### bit 7-0 **DEV10:DEV3:** Device ID bits:

DEV10:DEV3 (DEVID2<7:0>)	DEV2:DEV0 (DEVID1<7:5>)	Device
0001 1000	000	PIC18F66J60
0001 1111	000	PIC18F66J65
0001 1111	001	PIC18F67J60
0001 1000	001	PIC18F86J60
0001 1111	010	PIC18F86J65
0001 1111	011	PIC18F87J60
0001 1000	010	PIC18F96J60
0001 1111	100	PIC18F96J65
0001 1111	101	PIC18F97J60

## 24.2 Watchdog Timer (WDT)


For PIC18F97J60 family devices, the WDT is driven by the INTRC oscillator. When the WDT is enabled, the clock source is also enabled. The nominal WDT period is 4 ms and has the same stability as the INTRC oscillator.

The 4 ms period of the WDT is multiplied by a 16-bit postscaler. Any output of the WDT postscaler is selected by a multiplexor, controlled by the WDTPS bits in Configuration Register 2H. Available periods range from 4 ms to 131.072 seconds (2.18 minutes). The WDT and postscaler are cleared whenever a SLEEP or CLRWDT instruction is executed, or a clock failure (primary or Timer1 oscillator) has occurred.

- Note 1: The CLRWDT and SLEEP instructions clear the WDT and postscaler counts when executed.
  - 2: When a CLRWDT instruction is executed, the postscaler count will be cleared.

### 24.2.1 CONTROL REGISTER

The WDTCON register (Register 24-9) is a readable and writable register. The SWDTEN bit enables or disables WDT operation. This allows software to override the WDTEN Configuration bit and enable the WDT only if it has been disabled by the Configuration bit.



#### REGISTER 24-9: WDTCON: WATCHDOG TIMER CONTROL REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0
—	—	—	—	—	—	—	SWDTEN <sup>(1)</sup>
bit 7							bit 0

Legend:			
R = Readable bit	W = Writable bit	U = Unimplemented bit	, read as '0'
-n = Value at POR	'1' = Bit is set	'0' = Bit is cleared	x = Bit is unknown

bit 7-1 Unimplemented: Read as '0'

bit 0 SWDTEN: Software Controlled Watchdog Timer Enable bit<sup>(1)</sup>

- 1 = Watchdog Timer is on
- 0 = Watchdog Timer is off

**Note 1:** This bit has no effect if the Configuration bit, WDTEN, is enabled.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Reset Values on Page:
RCON	IPEN		CM	RI	TO	PD	POR	BOR	60
WDTCON	_			—				SWDTEN	60

**Legend:** — = unimplemented, read as '0'. Shaded cells are not used by the Watchdog Timer.

## 24.3 On-Chip Voltage Regulator

All of the PIC18F97J60 family devices power their core digital logic at a nominal 2.5V. This may create an issue for designs that are required to operate at a higher typical voltage, such as 3.3V. To simplify system design, all devices in the PIC18F97J60 family incorporate an on-chip regulator that allows the device to run its core logic from VDD.

The regulator is controlled by the ENVREG pin. Tying VDD to the pin enables the regulator, which in turn, provides power to the core from the other VDD pins. When the regulator is enabled, a low-ESR filter capacitor must be connected to the VDDCORE/VCAP pin (Figure 24-2). This helps to maintain the stability of the regulator. The recommended value for the filter capacitor is provided in Section 27.3 "DC Characteristics: PIC18F97J60 Family (Industrial)".

If ENVREG is tied to Vss, the regulator is disabled. In this case, separate power for the core logic, at a nominal 2.5V, must be supplied to the device on the VDDCORE/VCAP pin to run the I/O pins at higher voltage levels, typically 3.3V. Alternatively, the VDDCORE/VCAP and VDD pins can be tied together to operate at a lower nominal voltage. Refer to Figure 24-2 for possible configurations.

#### 24.3.1 ON-CHIP REGULATOR AND BOR


When the on-chip regulator is enabled, PIC18F97J60 family devices also have a simple brown-out capability. If the voltage supplied to the regulator is inadequate to maintain a regulated level, the regulator Reset circuitry will generate a Brown-out Reset. This event is captured by the BOR flag bit (RCON<0>).

The operation of the BOR is described in more detail in Section 4.4 "Brown-out Reset (BOR)" and Section 4.4.1 "Detecting BOR". The Brown-out Reset voltage levels are specific in Section 27.1 "DC Characteristics: Supply Voltage".

#### 24.3.2 POWER-UP REQUIREMENTS

The on-chip regulator is designed to meet the power-up requirements for the device. If the application does not use the regulator, then strict power-up conditions must be adhered to. While powering up, VDDCORE must never exceed VDD by 0.3 volts.

## FIGURE 24-2: CONNECTIONS FOR THE ON-CHIP REGULATOR



## 24.4 Two-Speed Start-up

The Two-Speed Start-up feature helps to minimize the latency period, from oscillator start-up to code execution, by allowing the microcontroller to use the INTRC oscillator as a clock source until the primary clock source is available. It is enabled by setting the IESO Configuration bit.


Two-Speed Start-up should be enabled only if the primary oscillator mode is HS or HSPLL (Crystal-Based) modes. Since the EC and ECPLL modes do not require an Oscillator Start-up Timer delay, Two-Speed Start-up should be disabled.

When enabled, Resets and wake-ups from Sleep mode cause the device to configure itself to run from the internal oscillator block as the clock source, following the time-out of the Power-up Timer after a Power-on Reset is enabled. This allows almost immediate code execution while the primary oscillator starts and the OST is running. Once the OST times out, the device automatically switches to PRI\_RUN mode. In all other power-managed modes, Two-Speed Start-up is not used. The device will be clocked by the currently selected clock source until the primary clock source becomes available. The setting of the IESO bit is ignored.

#### 24.4.1 SPECIAL CONSIDERATIONS FOR USING TWO-SPEED START-UP

While using the INTRC oscillator in Two-Speed Start-up, the device still obeys the normal command sequences for entering power-managed modes, including serial SLEEP instructions (refer to **Section 3.1.4 "Multiple Sleep Commands"**). In practice, this means that user code can change the SCS1:SCS0 bit settings, or issue SLEEP instructions, before the OST times out. This would allow an application to briefly wake-up, perform routine "housekeeping" tasks and return to Sleep before the device starts to operate from the primary oscillator.

User code can also check if the primary clock source is currently providing the device clocking by checking the status of the OSTS bit (OSCCON<3>). If the bit is set, the primary oscillator is providing the clock. Otherwise, the internal oscillator block is providing the clock during wake-up from Reset or Sleep mode.




#### FIGURE 24-3: TIMING TRANSITION FOR TWO-SPEED START-UP (INTRC TO HSPLL)

## 24.5 Fail-Safe Clock Monitor

The Fail-Safe Clock Monitor (FSCM) allows the microcontroller to continue operation in the event of an external oscillator failure by automatically switching the device clock to the internal oscillator block. The FSCM function is enabled by setting the FCMEN Configuration bit.

When FSCM is enabled, the INTRC oscillator runs at all times to monitor clocks to peripherals and provide a backup clock in the event of a clock failure. Clock monitoring (shown in Figure 24-4) is accomplished by creating a sample clock signal which is the INTRC output divided by 64. This allows ample time between FSCM sample clocks for a peripheral clock edge to occur. The peripheral device clock and the sample clock are presented as inputs to the Clock Monitor latch (CM). The CM is set on the falling edge of the device clock source but cleared on the rising edge of the sample clock.





Clock failure is tested for on the falling edge of the sample clock. If a sample clock falling edge occurs while CM is still set, a clock failure has been detected (Figure 24-5). This causes the following:

- the FSCM generates an oscillator fail interrupt by setting bit, OSCFIF (PIR2<7>);
- the device clock source is switched to the internal oscillator block (OSCCON is not updated to show the current clock source – this is the fail-safe condition); and
- the WDT is reset.

During switchover, the postscaler frequency from the internal oscillator block may not be sufficiently stable for timing sensitive applications. In these cases, it may be desirable to select another clock configuration and enter an alternate power-managed mode. This can be done to attempt a partial recovery or execute a controlled shutdown. See Section 3.1.4 "Multiple Sleep Commands" and Section 24.4.1 "Special Considerations for Using Two-Speed Start-up" for more details.

The FSCM will detect failures of the primary or secondary clock sources only. If the internal oscillator block fails, no failure would be detected, nor would any action be possible.

#### 24.5.1 FSCM AND THE WATCHDOG TIMER

Both the FSCM and the WDT are clocked by the INTRC oscillator. Since the WDT operates with a separate divider and counter, disabling the WDT has no effect on the operation of the INTRC oscillator when the FSCM is enabled.


As already noted, the clock source is switched to the INTRC clock when a clock failure is detected. This may mean a substantial change in the speed of code execution. If the WDT is enabled with a small prescale value, a decrease in clock speed allows a WDT time-out to occur and a subsequent device Reset. For this reason, Fail-Safe Clock events also reset the WDT and postscaler, allowing it to start timing from when execution speed was changed and decreasing the likelihood of an erroneous time-out.

#### 24.5.2 EXITING FAIL-SAFE OPERATION

The fail-safe condition is terminated by either a device Reset or by entering a power-managed mode. On Reset, the controller starts the primary clock source specified in Configuration Register 2H (with any required start-up delays that are required for the oscillator mode, such as OST or PLL timer). The INTRC oscillator provides the device clock until the primary clock source becomes ready (similar to a Two-Speed Start-up). The clock source is then switched to the primary clock (indicated by the OSTS bit in the OSCCON register becoming set). The Fail-Safe Clock Monitor then resumes monitoring the peripheral clock.

The primary clock source may never become ready during start-up. In this case, operation is clocked by the INTRC oscillator. The OSCCON register will remain in its Reset state until a power-managed mode is entered.





#### 24.5.3 FSCM INTERRUPTS IN POWER-MANAGED MODES

By entering a power-managed mode, the clock multiplexor selects the clock source selected by the OSCCON register. Fail-Safe Monitoring of the power-managed clock source resumes in the power-managed mode.

If an oscillator failure occurs during power-managed operation, the subsequent events depend on whether or not the oscillator failure interrupt is enabled. If enabled (OSCFIF = 1), code execution will be clocked by the INTRC multiplexor. An automatic transition back to the failed clock source will not occur.

If the interrupt is disabled, subsequent interrupts while in Idle mode will cause the CPU to begin executing instructions while being clocked by the INTRC source.

#### 24.5.4 POR OR WAKE-UP FROM SLEEP

The FSCM is designed to detect oscillator failure at any point after the device has exited Power-on Reset (POR) or low-power Sleep mode. When the primary device clock is either EC or INTRC, monitoring can begin immediately following these events. For HS or HSPLL modes, the situation is somewhat different. Since the oscillator may require a start-up time considerably longer than the FSCM sample clock time, a false clock failure may be detected. To prevent this, the internal oscillator block is automatically configured as the device clock and functions until the primary clock is stable (the OST and PLL timers have timed out). This is identical to Two-Speed Start-up mode. Once the primary clock is stable, the INTRC returns to its role as the FSCM source.

Note: The same logic that prevents false oscillator failure interrupts on POR, or wake from Sleep, will also prevent the detection of the oscillator's failure to start at all following these events. This can be avoided by monitoring the OSTS bit and using a timing routine to determine if the oscillator is taking too long to start. Even so, no oscillator failure interrupt will be flagged.

As noted in Section 24.4.1 "Special Considerations for Using Two-Speed Start-up", it is also possible to select another clock configuration and enter an alternate power-managed mode while waiting for the primary clock to become stable. When the new power-managed mode is selected, the primary clock is disabled.

## 24.6 Program Verification and Code Protection

For all devices in the PIC18F97J60 family, the on-chip program memory space is treated as a single block. Code protection for this block is controlled by one Configuration bit, CP0. This bit inhibits external reads and writes to the program memory space. It has no direct effect in normal execution mode.

#### 24.6.1 CONFIGURATION REGISTER PROTECTION

The Configuration registers are protected against untoward changes or reads in two ways. The primary protection is the write-once feature of the Configuration bits which prevents reconfiguration once the bit has been programmed during a power cycle. To safeguard against unpredictable events, Configuration bit changes resulting from individual cell level disruptions (such as ESD events) will cause a parity error and trigger a device Reset.

The data for the Configuration registers is derived from the Flash Configuration Words in program memory. When the CP0 bit is programmed (cleared), the source data for device configuration is also protected as a consequence.

## 24.7 In-Circuit Serial Programming

PIC18F97J60 family microcontrollers can be serially programmed while in the end application circuit. This is simply done with two lines for clock and data and three other lines for power, ground and the programming voltage. This allows customers to manufacture boards with unprogrammed devices and then program the microcontroller just before shipping the product. This also allows the most recent firmware or a custom firmware to be programmed.

## 24.8 In-Circuit Debugger

When the DEBUG Configuration bit is programmed to a '0', the In-Circuit Debugger functionality is enabled. This function allows simple debugging functions when used with MPLAB<sup>®</sup> IDE. When the microcontroller has this feature enabled, some resources are not available for general use. Table 24-3 shows which resources are required by the background debugger.

<b>TABLE 24-3</b> :	DEBUGGER RESOURCES
---------------------	--------------------

I/O pins:	RB6, RB7			
Stack:	2 levels			
Program Memory:	512 bytes			
Data Memory:	10 bytes			

#### 25.0 INSTRUCTION SET SUMMARY

The PIC18F97J60 family of devices incorporates the standard set of 75 PIC18 core instructions, as well as an extended set of 8 new instructions for the optimization of code that is recursive or that utilizes a software stack. The extended set is discussed later in this section.

#### 25.1 Standard Instruction Set

The standard PIC18 instruction set adds many enhancements to the previous PIC<sup>®</sup> MCU instruction sets, while maintaining an easy migration from these PIC MCU instruction sets. Most instructions are a single program memory word (16 bits), but there are four instructions that require two program memory locations.

Each single-word instruction is a 16-bit word divided into an opcode, which specifies the instruction type and one or more operands, which further specify the operation of the instruction.

The instruction set is highly orthogonal and is grouped into four basic categories:

- Byte-oriented operations
- Bit-oriented operations
- · Literal operations
- Control operations

The PIC18 instruction set summary in Table 25-2 lists **byte-oriented**, **bit-oriented**, **literal** and **control** operations. Table 25-1 shows the opcode field descriptions.

Most byte-oriented instructions have three operands:

- 1. The file register (specified by 'f')
- 2. The destination of the result (specified by 'd')
- 3. The accessed memory (specified by 'a')

The file register designator 'f' specifies which file register is to be used by the instruction. The destination designator 'd' specifies where the result of the operation is to be placed. If 'd' is zero, the result is placed in the WREG register. If 'd' is one, the result is placed in the file register specified in the instruction.

All **bit-oriented** instructions have three operands:

- 1. The file register (specified by 'f')
- 2. The bit in the file register (specified by 'b')
- 3. The accessed memory (specified by 'a')

The bit field designator 'b' selects the number of the bit affected by the operation, while the file register designator 'f' represents the number of the file in which the bit is located.

The **literal** instructions may use some of the following operands:

- A literal value to be loaded into a file register (specified by 'k')
- The desired FSR register to load the literal value into (specified by 'f')
- No operand required (specified by '—')

The **control** instructions may use some of the following operands:

- A program memory address (specified by 'n')
- The mode of the CALL or RETURN instructions (specified by 's')
- The mode of the table read and table write instructions (specified by 'm')
- No operand required (specified by '—')

All instructions are a single word, except for four double-word instructions. These instructions were made double-word to contain the required information in 32 bits. In the second word, the 4 MSbs are '1's. If this second word is executed as an instruction (by itself), it will execute as a NOP.

All single-word instructions are executed in a single instruction cycle, unless a conditional test is true or the program counter is changed as a result of the instruction. In these cases, the execution takes two instruction cycles with the additional instruction cycle(s) executed as a NOP.

The double-word instructions execute in two instruction cycles.

One instruction cycle consists of four oscillator periods. Thus, for an oscillator frequency of 4 MHz, the normal instruction execution time is 1  $\mu$ s. If a conditional test is true, or the program counter is changed as a result of an instruction, the instruction execution time is 2  $\mu$ s. Two-word branch instructions (if true) would take 3  $\mu$ s.

Figure 25-1 shows the general formats that the instructions can have. All examples use the convention 'nnh' to represent a hexadecimal number.

The Instruction Set Summary, shown in Table 25-2, lists the standard instructions recognized by the Microchip MPASM<sup>™</sup> Assembler.

Section 25.1.1 "Standard Instruction Set" provides a description of each instruction.

#### TABLE 25-1: OPCODE FIELD DESCRIPTIONS

Field	Description								
a	RAM access bit:								
	a = 0: RAM location in Access RAM (BSR register is ignored)								
	a = 1: RAM bank is specified by BSR register								
bbb	Bit address within an 8-bit file register (0 to 7).								
BSR	Bank Select Register. Used to select the current RAM bank.								
C, DC, Z, OV, N	ALU Status bits: Carry, Digit Carry, Zero, Overflow, Negative.								
d	Destination select bit:								
	d = 0: store result in WREG d = 1: store result in file register f								
-l+	Destination: either the WREG register or the specified register file location.								
dest f	8-bit Register file address (00h to FFh), or 2-bit FSR designator (0h to 3h).								
	12-bit Register file address (000 to FFFh). This is the source address.								
f <sub>s</sub>	12-bit Register file address (000h to FFFh). This is the destination address.								
f <sub>d</sub>	Global Interrupt Enable bit.								
GIE k	Literal field, constant data or label (may be either an 8-bit, 12-bit or a 20-bit value).								
label	Label name.								
	The mode of the TBLPTR register for the table read and table write instructions.								
mm	Only used with table read and table write instructions:								
*	No Change to register (such as TBLPTR with table reads and writes)								
*+	Post-Increment register (such as TBLPTR with table reads and writes)								
*_	Post-Decrement register (such as TBLPTR with table reads and writes)								
+*	Pre-Increment register (such as TBLPTR with table reads and writes)								
n	The relative address (2's complement number) for relative branch instructions or the direct address for								
	Call/Branch and Return instructions.								
PC	Program Counter.								
PCL	Program Counter Low Byte.								
PCH	Program Counter High Byte.								
PCLATH	Program Counter High Byte Latch.								
PCLATU	Program Counter Upper Byte Latch.								
PD	Power-Down bit.								
PRODH	Product of Multiply High Byte.								
PRODL	Product of Multiply Low Byte.								
S	Fast Call/Return mode select bit:								
	s = 0: do not update into/from shadow registers								
	s = 1: certain registers loaded into/from shadow registers (Fast mode)								
TBLPTR	21-bit Table Pointer (points to a program memory location).								
TABLAT	8-bit Table Latch.								
TO	Time-out bit.								
TOS	Top-of-Stack.								
u MDF	Unused or Unchanged.								
WDT	Watchdog Timer. Working register (accumulator).								
WREG	Don't care ('0' or '1'). The assembler will generate code with $x = 0$ . It is the recommended form of use for								
х	compatibility with all Microchip software tools.								
Zs	7-bit offset value for indirect addressing of register files (source).								
z <sub>d</sub>	7-bit offset value for indirect addressing of register files (destination).								
{ }	Optional argument.								
[text]	Indicates an indexed address.								
(text)	The contents of text.								
[expr] <n></n>	Specifies bit n of the register indicated by the pointer expr.								
→	Assigned to.								
, < >	Register bit field.								
e	In the set of.								

Byte-oriented file register operations	Example Instruction
<u>15 10 9 8 7 0</u>	
OPCODE d a f (FILE #)	ADDWF MYREG, W, B
<ul> <li>d = 0 for result destination to be WREG register</li> <li>d = 1 for result destination to be file register (f)</li> <li>a = 0 to force Access Bank</li> <li>a = 1 for BSR to select bank</li> <li>f = 8-bit file register address</li> </ul>	
Byte to Byte move operations (2-word)	
<u>15 12 11 0</u>	
OPCODE f (Source FILE #)	MOVFF MYREG1, MYREG2
15 12 11 0	
1111 f (Destination FILE #)	
f = 12-bit file register address	
Bit-oriented file register operations	
<u>15 12 11 9 8 7 0</u>	
OPCODE b (BIT #) a f (FILE #)	BSF MYREG, bit, B
<ul> <li>b = 3-bit position of bit in file register (f)</li> <li>a = 0 to force Access Bank</li> <li>a = 1 for BSR to select bank</li> <li>f = 8-bit file register address</li> </ul>	
Literal operations	
<u>15 8 7 0</u>	
OPCODE k (literal)	MOVLW 7Fh
k = 8-bit immediate value	
Control operations	
CALL, GOTO and Branch operations	
15 8 7 0	
OPCODE n<7:0> (literal)	GOTO Label
15 12 11 0	
1111 n<19:8> (literal)	
n = 20-bit immediate value	
15 8 7 0	
OPCODE S n<7:0> (literal)	CALL MYFUNC
15 12 11 0	
1111 n<19:8> (literal)	
S = Fast bit	
15 11 10 0	
OPCODE n<10:0> (literal)	BRA MYFUNC
15 8 7 0 OPCODE n<7:0> (literal)	BC MYFUNC

TABLE 25-2:	PIC18F97J60 FAMILY INSTRUCTION SET

Operands         Image: Construct of the second	Mnemonic, Operands		Description		16-Bit Instruction Word				Status	Neter
ADDWFf, d, aAdd WREG and f1001001daffffffffC, DC, Z, OV, N1, 1ADDWFCf, d, aAND WREG with f1001000daffffffffC, DC, Z, OV, N1, 1ANDWFf, d, aAND WREG with f10010101affffffffZ2COMFf, d, aComplement f10110101affffffffZ2COMFf, aCompare f with WREG, skip =1(2 or 3)0110010affffffffNone4CPFSEQf, aCompare f with WREG, skip >1(2 or 3)0110000affffffffNone4CPFSLTf, aDecrement f, Skip if 01(2 or 3)0110010affffffffNone1,DCFSNZf, d, aDecrement f, Skip if 01(2 or 3)011010daffffffffNone1,INCFf, d, aIncrement f, Skip if 01(2 or 3)011010daffffffffNone1,INCFf, d, aIncrement f, Skip if Not 01(2 or 3)010110daffffffffNone1,INCFf, d, aIncrement f, Skip if Not 01(2 or 3)010110daffffffffNone1,INCFf, d, aMove fsGsurce) to1st word1010110daffffffffNone1,1,INFSNZ			Description	Cycles	MSb			LSb	Affected	Notes
$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	BYTE-ORI	ENTED	OPERATIONS							
$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	ADDWF	f, d, a	Add WREG and f	1	0010	01da	ffff	ffff	C, DC, Z, OV, N	1, 2
$ \begin{array}{c} {\rm CLRF} & {\rm f, a} & {\rm Clear f} & 1 & 0110 & 101a & {\rm ffff} & {\rm ffff} & {\rm Z} & 2 & 2 \\ {\rm COMF} & {\rm f, d, a} & {\rm Complement f} & 1 & 0010 & 111a & {\rm ffff} & {\rm ffff} & {\rm S, N} & 1, 1 \\ {\rm CPFSQD} & {\rm f, a} & {\rm Compare f with WREG, skip > 1 & (2 or 3)} & 0110 & 010a & {\rm ffff} & {\rm ffff} & {\rm None} & 4 \\ {\rm CPFSLT} & {\rm f, a} & {\rm Compare f with WREG, skip > 1 & (2 or 3)} & 0110 & 001a & {\rm ffff} & {\rm ffff} & {\rm None} & 4 \\ {\rm CPFSLT} & {\rm f, a} & {\rm Decrement f} & 1 & 0000 & 01da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm DECFSZ} & {\rm f, d, a} & {\rm Decrement f} & 1 & 0000 & 01da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm DCFSNZ} & {\rm f, d, a} & {\rm Decrement f} & 1 & 0010 & 10da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm INCFSZ} & {\rm f, d, a} & {\rm Increment f} & {\rm Skip if 0} & 1 & (2 or 3) & 0100 & 11da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm INFSNZ} & {\rm f, d, a} & {\rm Increment f, Skip if 0} & 1 & (2 or 3) & 0100 & 10da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm INFSNZ} & {\rm f, d, a} & {\rm Increment f, Skip if 0} & 1 & (2 or 3) & 0100 & 10da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm IORWF} & {\rm f, d, a} & {\rm Increment f, Skip if Not 0} & 1 & (2 or 3) & 0100 & 10da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm MOVF} & {\rm f, d, a} & {\rm Increment f, Skip if Not 0} & 1 & (2 or 3) & 0100 & 10da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm MOVFF} & {\rm f_s, f_d} & {\rm Move f} & {\rm source} & {\rm to tsword} & 1 & 0101 & 00da & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm MOVFF} & {\rm f_s, a} & {\rm Move f_s} & {\rm source} & {\rm to tsword} & 1 & 0110 & 110a & {\rm ffff} & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm NOVFF} & {\rm f, d, a} & {\rm Rotate Left f (No Carry)} & 1 & 0100 & 01da & {\rm ffff} & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm SUBFWB} & {\rm f, d, a} & {\rm Subtract WREG with f} & 1 & 0110 & 100a & {\rm ffff} & {\rm ffff} & {\rm ffff} & {\rm None} & 1, 1 \\ {\rm SUBFWB} & {\rm f, d, a} & {\rm Subtract WREG from f & 1 \\ {\rm SUBFWB} & {\rm f, d, a} & {\rm Subtract WREG from f f} & 1 & 01010 & 100a & {\rm ffff} & {\rm$	ADDWFC	f, d, a	Add WREG and Carry bit to f	1	0010	00da	ffff	ffff	C, DC, Z, OV, N	1, 2
$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	ANDWF	f, d, a	AND WREG with f	1	0001	01da	ffff	ffff	Z, N	1,2
$\begin{array}{c} \mbox{CPFSEQ} f,a \\ \mbox{CPFSGT} f,a \\ \mbox{Compare f with WREG, skip > } 1 (2 or 3) \\ \mbox{1} ($	CLRF	f, a	Clear f	1	0110	101a	ffff	ffff	Z	
CPFSGTf, aCompare f with WREG, skip >1 (2 or 3)0110010affffffffNone4CPFSLTf, aCompare f with WREG, skip <	COMF	f, d, a	Complement f	1	0001	11da	ffff	ffff	Z, N	1, 2
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	CPFSEQ	f, a	Compare f with WREG, skip =	1 (2 or 3)	0110	001a	ffff	ffff	None	4
$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	CPFSGT	f, a	Compare f with WREG, skip >	1 (2 or 3)	0110	010a	ffff	ffff	None	4
$\begin{array}{cccccccccccccccccccccccccccccccccccc$	CPFSLT	f, a	Compare f with WREG, skip <	1 (2 or 3)	0110	000a	ffff	ffff	None	1, 2
$\begin{array}{c} DCFSNZ & f, d, a \\ INCF & f, d, a \\ Incrementf, SkipifNot0 \\ Incrementf, d, a \\ Incrementf, d, a \\ Incrementf, Skipif0 \\ Incrementf, Skipif0 \\ Incrementf, Skipif0 \\ Incrementf, Skipif0 \\ Incrementf, SkipifNon0 \\ I(2or3) \\ O010 \\ I0da \\ ffff \\ ffff \\ ffff \\ ffff \\ ffff \\ None \\ None \\ 1, I, None \\ Incrementf, SkipifNo10 \\ Incrementf, SkipifNo10 \\ I(2or3) \\ O011 \\ I0da \\ ffff \\ None \\ None \\ f, d, a \\ NoveKREGofn \\ MOVFF \\ f, a \\ NoveWREGvithf \\ f \\ Nove \\ ff, d, a \\ NoteWREGwithf \\ f \\ none \\ None \\ f, d, a \\ NoteLefffhroughCarry \\ RLCF \\ f, d, a \\ RotateLefffhroughCarry \\ RCarry \\ RRCF \\ f, d, a \\ RotateRightfhroughCarry \\ RRCF \\ f, d, a \\ SubtractRightfhroughCarry \\ 1 \\ O101  010a  \mathfrak{ffff} \\ ffff \\ ffff \\ ffff \\ ffff \\ None \\ SUBWF \\ f, d, a \\ SubtractWREGfromf \\ subtractWREGfromf \\ f \\ f \\ subtractWREGfromf \\ f \\ f \\ d \\ subtractWREGfromf \\ f \\ f \\ f \\ f \\ d \\ subtractWREGfromf \\ f \\$	DECF	f, d, a	Decrement f	1	0000	01da	ffff	ffff	C, DC, Z, OV, N	1, 2, 3, 4
$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	DECFSZ	f, d, a	Decrement f, Skip if 0	1 (2 or 3)	0010	11da	ffff	ffff	None	1, 2, 3, 4
INCFSZf, d, aIncrement f, Skip if 01 (2 or 3)001111daffffffffNone4INFSNZf, d, aIncrement f, Skip if Not 01 (2 or 3)010010daffffffffNone1, 1IORWFf, d, aInclusive OR WREG with f1000100daffffffffZ, N1, 1MOVFf, d, aMove f1010100daffffffffZ, N1, 1MOVFFf, d, aMove f1010100daffffffffNone1, 1MOVFFf, aMove f1010100daffffffffNone1, 1MOVFFf, aMove WREG to f10110111afffffffffNone1, 1MULWFf, aNegate f10110110affffffffNone1, 1NEGFf, d, aRotate Left f through Carry10110110affffffffC, Z, N1, 1RLCFf, d, aRotate Left f (No Carry)1010001daffffffffZ, N1, 1RRCFf, d, aRotate Right f through Carry10101100affffffffNone1, 1SUBFWBf, d, aSubtract MREG from f10101100affffffffNone1, 1SUBWFFf, d, aSubtract WREG from f1010110daffffffffC, DC, Z, OV, N1, 1SUBWFB <td>DCFSNZ</td> <td>f, d, a</td> <td>Decrement f, Skip if Not 0</td> <td>1 (2 or 3)</td> <td>0100</td> <td>11da</td> <td>ffff</td> <td>ffff</td> <td>None</td> <td>1, 2</td>	DCFSNZ	f, d, a	Decrement f, Skip if Not 0	1 (2 or 3)	0100	11da	ffff	ffff	None	1, 2
INFSNZf, d, aIncrement f, Skip if Not 01 (2 or 3)010010daffffffffNone1, 1IORWFf, d, aInclusive OR WREG with f1000100daffffffffZ, N1, 1MOVFf, d, aMove fMove f1010100daffffffffZ, N1, 1MOVFFfs, fdMove fMove f1010100daffffffffZ, N1, 1MOVFFf, aMove fMove f1010100daffffffffNone1, 1MOVWFf, aMove WREG to f10110111affffffffNone1, 1MULWFf, aMultiply WREG with f10000001affffffffNone1, 1NEGFf, aNegate f10110110affffffffNone1, 1NEGFf, d, aRotate Left fthrough Carry1001101daffffffffC, DC, Z, OV, N1, 1RLNCFf, d, aRotate Right fthrough Carry10110010affffffffZ, N1, 1RRNCFf, d, aSubtract ffrom WREG with10101010affffffffNone1, 1SUBWFf, d, aSubtract WREG from f1010110daffffffffC, DC, Z, OV, N1, 1SUBWFBf, d, aSubtract WREG from f with1010110dafffffffffff	INCF	f, d, a	Increment f	1	0010	10da	ffff	ffff	C, DC, Z, OV, N	1, 2, 3, 4
$\begin{array}{cccccccccccccccccccccccccccccccccccc$	INCFSZ	f, d, a	Increment f, Skip if 0	1 (2 or 3)	0011	11da	ffff	ffff	None	4
$\begin{array}{cccccccccccccccccccccccccccccccccccc$	INFSNZ			. ,	0100	10da	ffff	ffff	None	1, 2
$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	IORWF			1 ΄		00da	ffff	ffff	Z, N	1, 2
$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	MOVF		Move f	1	0101	00da	ffff	ffff	Z, N	
fd (destination) 2nd word1111 ffff ffffffffMOVWF f, aMove WREG to f10110 111a ffff ffffNoneMULWF f, aMultiply WREG with f10000 001a ffff ffffNone1, 3NEGF f, aNegate f10110 110a ffff ffffC, DC, Z, OV, N1, 3RLCF f, d, aRotate Left f through Carry10011 01da ffff ffffC, DC, Z, OV, N1, 3RLNCF f, d, aRotate Left f (No Carry)10100 01da ffff ffffC, Z, N1, 3RRCF f, d, aRotate Right f through Carry10011 00da ffff ffffC, Z, N1, 3RRNCF f, d, aRotate Right f (No Carry)10100 00da ffff ffffC, Z, N1, 3SETF f, aSet f10110 100a ffff ffffC, DC, Z, OV, N1, 3SUBFWB f, d, aSubtract ffrom WREG with borrow10101 11da ffff ffffC, DC, Z, OV, N1, 3SWAPF f, d, aSwap nibbles in f10011 10da ffffffffNone4	MOVFF		Move f <sub>s</sub> (source) to 1st word	2	1100	ffff	ffff	ffff	None	
MOVWFf, aMove WREG to f10110111affffffffNoneMULWFf, aMultiply WREG with f10000001affffffffNone1, 3NEGFf, aNegate f10110110affffffffC, DC, Z, OV, N1RLCFf, d, aRotate Left f through Carry1001101daffffffffC, Z, N1, 3RLNCFf, d, aRotate Left f (No Carry)1010001daffffffffC, Z, N1, 3RRCFf, d, aRotate Right f through Carry1010101daffffffffC, Z, N1, 3RRNCFf, d, aRotate Right f (No Carry)1010100daffffffffC, Z, N1, 3SETFf, aSet f10110100affffffffC, DC, Z, OV, N1, 3SUBFWBf, d, aSubtract from WREG with1010110daffffffffC, DC, Z, OV, N1, 3SUBWFf, d, aSubtract WREG from f1010111daffffffffC, DC, Z, OV, N1, 3SWAPFf, d, aSwap nibbles in f1001110daffffffffNone4		3. u			1111	ffff	ffff	ffff		
MULWFf, aMultiply WREG with f10000001affffffffNone1, 7NEGFf, aNegate f10110110affffffffC, DC, Z, OV, N1RLCFf, d, aRotate Left f through Carry1001101daffffffffC, Z, N1, 7RLNCFf, d, aRotate Left f (No Carry)1011001daffffffffC, Z, N1, 7RRCFf, d, aRotate Right f through Carry1010001daffffffffC, Z, N1, 7RRNCFf, d, aRotate Right f (No Carry)1001100daffffffffC, Z, N1, 7SETFf, aSet f10110100affffffffC, Z, N1, 7SUBFWBf, d, aSubtract f from WREG with10101100affffffffC, DC, Z, OV, N1, 7SUBWFf, d, aSubtract WREG from f1010111daffffC, DC, Z, OV, N1, 7SWAPFf, d, aSwap nibbles in f1001110daffffffffNone4	MOVWF	f, a		1	0110	111a	ffff	ffff	None	
NEGFf, aNegate f10110110affffffffC, DC, Z, OV, NRLCFf, d, aRotate Left f through Carry1001101daffffffffC, Z, N1, 3RLNCFf, d, aRotate Left f (No Carry)1010001daffffffffC, Z, N1, 3RRCFf, d, aRotate Right f through Carry1010001daffffffffC, Z, N1, 3RRNCFf, d, aRotate Right f (No Carry)1010000daffffffffC, Z, N1, 3SETFf, aSet f10110100affffffffC, DC, Z, OV, N1, 3SUBFWBf, d, aSubtract f from WREG with borrow1010111daffffffffC, DC, Z, OV, N1, 3SUBWFf, d, aSubtract WREG from f1010111daffffffffC, DC, Z, OV, N1, 3SWAPFf, d, aSwap nibbles in f1001110daffffffffNone4	MULWF		Multiply WREG with f	1	0000	001a	ffff	ffff	None	1, 2
RLCFf, d, aRotate Left f through Carry1001101daffffffffC, Z, N1, 7RLNCFf, d, aRotate Left f (No Carry)1010001daffffffffZ, N1, 7RRCFf, d, aRotate Right f through Carry1010001daffffffffZ, N1, 7RRNCFf, d, aRotate Right f through Carry1010000daffffffffC, Z, N1, 7SETFf, aSet f10110100affffffffC, Z, N1, 7SUBFWBf, d, aSubtract f from WREG with borrow10101100affffffffC, DC, Z, OV, N1, 7SUBWFf, d, aSubtract WREG from f1010111daffffffffC, DC, Z, OV, N1, 7SWAPFf, d, aSwap nibbles in f1001110daffffffffNone4	NEGF	f, a		1	0110	110a	ffff	ffff	C, DC, Z, OV, N	<i>'</i>
RLNCFf, d, aRotate Left f (No Carry)1010001daffffffffZ, NRRCFf, d, aRotate Right f through Carry1010000daffffffffC, Z, NRRNCFf, d, aRotate Right f (No Carry)1010000daffffffffZ, NSETFf, aSet f10110100affffffffZ, NSUBFWBf, d, aSubtract f from WREG with1010101daffffffffC, DC, Z, OV, NSUBWFf, d, aSubtract WREG from f1010111daffffC, DC, Z, OV, N1, 2SUBWFBf, d, aSubtract WREG from f with1010110daffffC, DC, Z, OV, N1, 3SWAPFf, d, aSwap nibbles in f1001110daffffffffNone4	RLCF	-		1	0011	01da	ffff			1, 2
RRCFf, d, aRotate Right f through Carry1001100daffffffffC, Z, NRRNCFf, d, aRotate Right f (No Carry)1010000daffffffffZ, NSETFf, aSet f10110100affffffffK, NSUBFWBf, d, aSubtract f from WREG with1010101daffffffffC, DC, Z, OV, NSUBWFf, d, aSubtract WREG from f1010111daffffC, DC, Z, OV, N1, 2SUBWFBf, d, aSubtract WREG from f with1010111daffffC, DC, Z, OV, N1, 2SWAPFf, d, aSwap nibbles in f1001110daffffffffNone4	RLNCF	f, d, a	<b>a</b> ,	1	0100	01da	ffff	ffff	Z, N	<i>'</i>
RRNCF       f, d, a       Rotate Right f (No Carry)       1       0100       00da       ffff       ffff       Z, N         SETF       f, a       Set f       1       0110       100a       ffff       ffff       None       1, 3         SUBFWB       f, d, a       Subtract f from WREG with borrow       1       0101       01da       ffff       ffff       C, DC, Z, OV, N       1, 3         SUBWF       f, d, a       Subtract WREG from f       1       0101       11da       ffff       C, DC, Z, OV, N       1, 3         SUBWFB       f, d, a       Subtract WREG from f with borrow       1       0101       10da       ffff       C, DC, Z, OV, N       1, 3         SWAPF       f, d, a       Swap nibbles in f       1       0011       10da       ffff       Mone       4	RRCF			1	0011	00da	ffff	ffff	C, Z, N	
SETFf, aSet f10110100affffffffNone1, iSUBFWBf, d, aSubtract f from WREG with borrow1010101daffffffffC, DC, Z, OV, N1, iSUBWFf, d, aSubtract WREG from f1010111daffffffffC, DC, Z, OV, N1, iSUBWFBf, d, aSubtract WREG from f with borrow1010111daffffffffC, DC, Z, OV, N1, iSWAPFf, d, aSwap nibbles in f1001110daffffffffNone4	RRNCF			1	0100	00da	ffff	ffff		
SUBFWB       f, d, a       Subtract f from WREG with borrow       1       0101       01da       ffff       ffff       C, DC, Z, OV, N       1         SUBWF       f, d, a       Subtract WREG from f       1       0101       11da       ffff       ffff       C, DC, Z, OV, N       1, Z         SUBWFB       f, d, a       Subtract WREG from f with borrow       1       0101       10da       ffff       ffff       C, DC, Z, OV, N       1, Z         SWAPF       f, d, a       Swap nibbles in f       1       0011       10da       ffff       ffff       None       4	SETF			1	0110	100a	ffff			1, 2
SUBWFf, d, aSubtract WREG from f1010111daffffC, DC, Z, OV, N1, 2SUBWFBf, d, aSubtract WREG from f with borrow1010110daffffffffC, DC, Z, OV, N1, 2SWAPFf, d, aSwap nibbles in f1001110daffffffffK14	SUBFWB	,	Subtract f from WREG with	1	0101	01da	ffff	ffff	C. DC. Z. OV. N	,
SUBWFf, d, aSubtract WREG from f1010111daffffC, DC, Z, OV, N1, 2SUBWFBf, d, aSubtract WREG from f with borrow1010110daffffffffC, DC, Z, OV, N1, 2SWAPFf, d, aSwap nibbles in f1001110daffffffffNone4	_	, -,							, -, ,	
SUBWFB       f, d, a       Subtract WREG from f with borrow       1       0101       10da       ffff       C, DC, Z, OV, N         SWAPF       f, d, a       Swap nibbles in f       1       0011       10da       ffff       ffff       None       4	SUBWF	f. d. a		1	0101	11da	ffff	ffff	C. DC. Z. OV. N	1, 2
borrow       SWAPF     f, d, a       Swap nibbles in f     1       0011     10da       fff     fff       None     4				1						,
SWAPF     f, d, a     Swap nibbles in f     1     0011     10da     ffff     None     4		,,							-,, -, - ,, .	
	SWAPF	f. d. a		1	0011	10da	ffff	ffff	None	4
	-			-						1, 2
XORWF f, d, a Exclusive OR WREG with f 1 0001 10da ffff ffff Z, N				`` '						., _

**Note 1:** When a PORT register is modified as a function of itself (e.g., MOVF PORTB, 1, 0), the value used will be that value present on the pins themselves. For example, if the data latch is '1' for a pin configured as input and is driven low by an external device, the data will be written back with a '0'.

2: If this instruction is executed on the TMR0 register (and, where applicable, d = 1), the prescaler will be cleared if assigned.

**3:** If Program Counter (PC) is modified or a conditional test is true, the instruction requires two cycles. The second cycle is executed as a NOP.

4: Some instructions are two-word instructions. The second word of these instructions will be executed as a NOP unless the first word of the instruction retrieves the information embedded in these 16 bits. This ensures that all program memory locations have a valid instruction.

Mnom	onic			16-	Bit Instr	uction V	Vord	Status	
Mnemonic, Operands		Description	Cycles	MSb			LSb	Affected	Notes
BIT-ORIEN		PERATIONS							
BCF	f, b, a	Bit Clear f	1	1001	bbba	ffff	ffff	None	1, 2
BSF	f, b, a	Bit Set f	1	1000	bbba	ffff		None	1, 2
BTFSC	f, b, a	Bit Test f, Skip if Clear	1 (2 or 3)	1011	bbba	ffff		None	3, 4
BTFSS	f, b, a	Bit Test f, Skip if Set	1 (2 or 3)	1010	bbba	ffff		None	3, 4
BTG	f, b, a	Bit Toggle f	1	0111	bbba	ffff	ffff	None	1, 2
CONTROL		ATIONS							
BC	n	Branch if Carry	1 (2)	1110	0010	nnnn	nnnn	None	
BN	n	Branch if Negative	1 (2)	1110	0110	nnnn	nnnn	None	
BNC	n	Branch if Not Carry	1 (2)	1110	0011	nnnn	nnnn	None	
BNN	n	Branch if Not Negative	1 (2)	1110	0111	nnnn	nnnn	None	
BNOV	n	Branch if Not Overflow	1 (2)	1110	0101	nnnn	nnnn	None	
BNZ	n	Branch if Not Zero	1 (2)	1110	0001	nnnn	nnnn	None	
BOV	n	Branch if Overflow	1 (2)	1110	0100	nnnn	nnnn	None	
BRA	n	Branch Unconditionally	2	1101	0nnn	nnnn	nnnn	None	
BZ	n	Branch if Zero	1 (2)	1110	0000	nnnn	nnnn	None	
CALL	n, s	Call subroutine 1st word	2	1110	110s	kkkk	kkkk	None	
		2nd word		1111	kkkk	kkkk	kkkk		
CLRWDT	_	Clear Watchdog Timer	1	0000	0000	0000	0100	TO, PD	
DAW	—	Decimal Adjust WREG	1	0000	0000	0000	0111	С	
GOTO	n	Go to address 1st word	2	1110	1111	kkkk	kkkk	None	
		2nd word		1111	kkkk	kkkk	kkkk		
NOP	—	No Operation	1	0000	0000	0000	0000	None	
NOP	—	No Operation	1	1111	XXXX	XXXX	XXXX	None	4
POP	_	Pop top of return stack (TOS)	1	0000	0000	0000	0110	None	
PUSH	—	Push top of return stack (TOS)	1	0000	0000	0000	0101	None	
RCALL	n	Relative Call	2	1101	1nnn	nnnn	nnnn	None	
RESET		Software device Reset	1	0000	0000	1111	1111	All	
RETFIE	S	Return from interrupt enable	2	0000	0000	0001	000s	GIE/GIEH, PEIE/GIEL	
RETLW	k	Return with literal in WREG	2	0000	1100	kkkk	kkkk		
RETURN	S	Return from Subroutine	2	0000	0000	0001	001s	None	
SLEEP	_	Go into Standby mode	1	0000	0000	0000		TO, PD	

#### TABLE 25-2: PIC18F97J60 FAMILY INSTRUCTION SET (CONTINUED)

**Note 1:** When a PORT register is modified as a function of itself (e.g., MOVF PORTB, 1, 0), the value used will be that value present on the pins themselves. For example, if the data latch is '1' for a pin configured as input and is driven low by an external device, the data will be written back with a '0'.

2: If this instruction is executed on the TMR0 register (and, where applicable, d = 1), the prescaler will be cleared if assigned.

**3:** If Program Counter (PC) is modified or a conditional test is true, the instruction requires two cycles. The second cycle is executed as a NOP.

4: Some instructions are two-word instructions. The second word of these instructions will be executed as a NOP unless the first word of the instruction retrieves the information embedded in these 16 bits. This ensures that all program memory locations have a valid instruction.

<b>TABLE 25-2</b> :	PIC18F97J60 FAMILY INSTRUCTION SET (	(CONTINUED)

Opera		Description	Cycles				Word	Status	Notes
LITERAL	OPERA			MSb			LSb	Affected	Notes
		LITERAL OPERATIONS							
ADDLW	k	Add literal and WREG	1	0000	1111	kkkk	kkkk	C, DC, Z, OV, N	
ANDLW	k	AND literal with WREG	1	0000	1011	kkkk	kkkk	Z, N	
IORLW	k	Inclusive OR literal with WREG	1	0000	1001	kkkk	kkkk	Z, N	
LFSR	f, k	Move literal (12-bit) 2nd word	2	1110	1110	00ff	kkkk	None	
		to FSR(f) 1st word		1111	0000	kkkk	kkkk		
MOVLB	k	Move literal to BSR<3:0>	1	0000	0001	0000	kkkk	None	
MOVLW	k	Move literal to WREG	1	0000	1110	kkkk	kkkk	None	
MULLW	k	Multiply literal with WREG	1	0000	1101	kkkk	kkkk	None	
RETLW	k	Return with literal in WREG	2	0000	1100	kkkk	kkkk	None	
SUBLW	k	Subtract WREG from literal	1	0000	1000	kkkk	kkkk	C, DC, Z, OV, N	
XORLW	k	Exclusive OR literal with WREG	1	0000	1010	kkkk	kkkk	Z, N	
DATA MEI	MORY +	PROGRAM MEMORY OPERATI	ONS						
TBLRD*		Table Read	2	0000	0000	0000	1000	None	
TBLRD*+		Table Read with post-increment		0000	0000	0000	1001	None	
TBLRD*-		Table Read with post-decrement		0000	0000	0000	1010	None	
TBLRD+*		Table Read with pre-increment		0000	0000	0000	1011	None	
TBLWT*		Table Write	2	0000	0000	0000	1100	None	
TBLWT*+		Table Write with post-increment		0000	0000	0000	1101	None	
TBLWT*-		Table Write with post-decrement		0000	0000	0000	1110	None	
TBLWT+*		Table Write with pre-increment		0000	0000	0000	1111	None	

**Note 1:** When a PORT register is modified as a function of itself (e.g., MOVF PORTB, 1, 0), the value used will be that value present on the pins themselves. For example, if the data latch is '1' for a pin configured as input and is driven low by an external device, the data will be written back with a '0'.

2: If this instruction is executed on the TMR0 register (and, where applicable, d = 1), the prescaler will be cleared if assigned.

**3:** If Program Counter (PC) is modified or a conditional test is true, the instruction requires two cycles. The second cycle is executed as a NOP.

4: Some instructions are two-word instructions. The second word of these instructions will be executed as a NOP unless the first word of the instruction retrieves the information embedded in these 16 bits. This ensures that all program memory locations have a valid instruction.

ADD W to f

f {,d {,a}}

01da

Add W to register 'f'. If 'd' is '0', the result is stored in W. If 'd' is '1', the

result is stored back in register 'f'

If 'a' is '0', the Access Bank is selected. If 'a' is '1', the BSR is used to select the

If 'a' is '0' and the extended instruction set is enabled, this instruction operates in Indexed Literal Offset Addressing

mode whenever  $f \le 95$  (5Fh). See Section 25.2.3 "Byte-Oriented and **Bit-Oriented Instructions in Indexed** Literal Offset Mode" for details.

Q3

Process

Data

REG, 0, 0

ffff

ffff

Q4

Write to

destination

ADDWF

a ∈ [0,1]

 $0 \leq f \leq 255$  $d \in [0,1]$ 

 $(W) + (f) \rightarrow dest$ 

N, OV, C, DC, Z

GPR bank (default).

0010

(default).

Q2

Read register 'f'

ADDWF

=

=

W

REG

17h

0C2h

0D9h

0C2h

#### 25.1.1 STANDARD INSTRUCTION SET

ADDLW	ADD Litera	l to W				ADDWF	AI
Syntax:	ADDLW	k				Syntax:	A
Operands:	$0 \leq k \leq 255$					Operands:	0 :
Operation:	$(W) + k \rightarrow V$	Ν					d a
Status Affected:	N, OV, C, D	0C, Z				Operation:	a (W
Encoding:	0000	1111	kkl	kk	kkkk	Status Affected:	(V) N,
Description:	The conten 8-bit literal W.					Encoding: Description:	Ac
Words:	1						re
Cycles:	1						re: (d
Q Cycle Activity:							lf
Q1	Q2	Q3		1	Q4		lf '
Decode	Read literal 'k'	Proce Data		W	rite to W		GI If '
Example: Before Instruct W = After Instruction	ction 10h on	.5h					se in M Se Bi Li
W =	25h					Words:	1
						Cycles:	1
						Q Cycle Activity: Q1	
						Decode	F reg
						Example:	AI
						Before Instru W REG After Instruct	= =

Note: All PIC18 instructions may take an optional label argument preceding the instruction mnemonic for use in symbolic addressing. If a label is used, the instruction format then becomes: {label} instruction argument(s).

ADDWFC	ADD W an	d Carry bit t	o f
Syntax:	ADDWFC	f {,d {,a}}	
Operands:	$0 \le f \le 255$ $d \in [0,1]$ $a \in [0,1]$		
Operation:	(W) + (f) +	$(C) \rightarrow dest$	
Status Affected:	N,OV, C, D	C, Z	
Encoding:	0010	00da fi	fff ffff
Description:	location 'f'. placed in V	Carry flag an If 'd' is '0', th /. If 'd' is '1', ata memory l	the result is
	,	he BSR is us	ank is selected. ed to select the
	set is enabl in Indexed mode wher Section 25 Bit-Oriente	led, this instru- Literal Offset never f ≤ 95 ( 5 <b>.2.3 "Byte-C</b>	5Fh). See riented and ns in Indexed
Words:	1		
Cycles:	1		
Q Cycle Activity:			
Q1	Q2	Q3	Q4
Decode	Read register 'f'	Process Data	Write to destination
		Data	destination
Example:	ADDWFC	REG, 0,	1
Before Instruc Carry bit REG W After Instructic	= 1 = 02h = 4Dh		
Carry bit REG W			

ANDLW	AND Litera	al with W	'	
Syntax:	ANDLW	k		
Operands:	$0 \le k \le 255$			
Operation:	(W) .AND.	$k \to W$		
Status Affected:	N, Z			
Encoding:	0000	1011	kk}	k kkkk
Description:				IDed with the s placed in W
Words:	1			
Cycles:	1			
Q Cycle Activity:				
Q1	Q2	Q3		Q4
Decode	Read literal 'k'	Proce Data		Write to W
Example:	ANDLW	05Fh		
Before Instruc	tion			
W After Instructio	= A3h			
W	= 03h			

ANDWF	AND W wi	th f		BC	BC		Carry	
Syntax:	ANDWF	f {,d {,a}}		Synta	ax:	BC n		
Operands:	$0 \le f \le 255$			Oper	ands:	-128 ≤ n ≤ ′	127	
	$d \in [0,1]$ Operation: a $\in [0,1]$		ation:	if Carry bit is '1', (PC) + 2 + 2n $\rightarrow$ PC				
Operation:	(W) .AND.	(f) $\rightarrow$ dest		Statu	s Affected:	None		
Status Affected:	N, Z			Enco	dina <sup>.</sup>	1110	0010 nni	nn nnnn
Encoding: Description:		nts of W are A			ription:		bit is '1', then	
	•	s '1', the resul	result is stored t is stored back			added to th	nplement num e PC. Since th d to fetch the r	e PC will have
	-	the BSR is use	ank is selected. ed to select the			,	the new addre	
	lf 'a' is '0' a	and the extend	led instruction	Word	ls:	1		
		,	iction operates	Cycle	es:	1(2)		
		Literal Offset $f \le 95$ (5		QC	ycle Activity:			
		5.2.3 "Byte-O		lf Ju	mp:			
			ns in Indexed		Q1	Q2	Q3	Q4
		set Mode" for	details.		Decode	Read literal	Process	Write to
Words:	1				No	ʻn' No	Data No	PC No
Cycles:	1				operation	operation	operation	operation
Q Cycle Activity:				lf No	o Jump:			
Q1	Q2	Q3	Q4		Q1	Q2	Q3	Q4
Decode	Read	Process	Write to		Decode	Read literal	Process	No
	register 'f'	Data	destination			'n'	Data	operation
Example:	ANDWF	REG, 0, 0	)	Exan	nple:	HERE	BC 5	
Before Instruc					Before Instrue	ction		
W REG	= 17h = C2h				PC		dress (HERE)	)
After Instructi					After Instructi			
W	= 02h				If Carry PC	= 1; = ad	dress (HERE	+ 12)
REG	= C2h				If Carry	= 0;		,
					PC	= ad	dress (HERE	+ 2)

BCF	Bit Clear f		BN	Branch if N	legative		
Syntax:	BCF f, b {,a}		Syntax:	BN n			
Operands:	$0 \leq f \leq 255$		Operands:	-128 ≤ n ≤ 1	127		
	$\begin{array}{l} 0 \leq b \leq 7 \\ a \in [0,1] \end{array}$		Operation:	if Negative bit is '1', (PC) + 2 + 2n $\rightarrow$ PC			
Operation:	$0 \rightarrow f \le b >$		Status Affected:	None			
Status Affected:	None		Encoding:	1110	0110 nni	nn nnnn	
Encoding:	1001 bbba ff	ff ffff	Description:	If the Negat	tive bit is '1', th	nen the	
Description:	Bit 'b' in register 'f' is clea	ared.		program wi			
	If 'a' is '0', the Access Ba If 'a' is '1', the BSR is use GPR bank (default).		added to the incremente	d to fetch the r	e PC will have next		
	If 'a' is '0' and the extend set is enabled, this instru in Indexed Literal Offset /	ction operates		instruction, the new address will be PC + 2 + 2n. This instruction is then a two-cycle instruction.			
	mode whenever $f \le 95$ (5	0	Words:	1			
	Section 25.2.3 "Byte-Or		Cycles:	1(2)			
	Bit-Oriented Instruction Literal Offset Mode" for		Q Cycle Activity: If Jump:				
Words:	1		Q1	Q2	Q3	Q4	
Cycles:	1		Decode	Read literal	Process	Write to	
Q Cycle Activity:				'n'	Data	PC	
Q1	Q2 Q3	Q4	No	No	No	No	
Decode	Read Process register 'f' Data	Write register 'f'	operation If No Jump:	operation	operation	operation	
	Tegloter 1 Data	regioter i	Q1	Q2	Q3	Q4	
Example:	BCF FLAG REG,	7, 0	Decode	Read literal	Process	No	
Before Instruc		, -		'n'	Data	operation	
	EG = C7h						
After Instruction			Example:	HERE	BN Jump		
FLAG_R	EG = 47h		Before Instruc PC After Instruction	= ad	dress (HERE)		
			lf Negati PC If Negati PC	= ad ve = 0;	dress (Jump) dress (HERE		

BNC	Branch if N	lot Carry		BNN		Branch if N	lot Negative	
Syntax:	BNC n			Syntax:		BNN n		
Operands:	-128 ≤ n ≤ 1	127		Operand	ds:	-128 ≤ n ≤ 1	$-128 \le n \le 127$	
Operation:	if Carry bit i (PC) + 2 + 2	,		Operatio	on:	if Negative bit is '0', (PC) + 2 + 2n $\rightarrow$ PC		
Status Affected:	None			Status A	ffected:	None		
Encoding:	1110	0011 nn	nn nnnn	Encodin	ig:	1110	0111 nn:	nn nnnn
Description:	If the Carry bit is '0', then the program will branch.		Descript	Description:		tive bit is '0', tl ll branch.	hen the	
	added to the incremented instruction,	d to fetch the i the new addre n. This instruct	e PC will have next ess will be			added to the incremented instruction,	nplement num e PC. Since th d to fetch the i the new addre n. This instruction.	e PC will hav next ess will be
Nords:	1			Words:		1		
Cycles:	1(2)			Cycles:		1(2)		
Q Cycle Activity: If Jump:				Q Cycle If Jump	e Activity:			
Q1	Q2	Q3	Q4		Q1	Q2	Q3	Q4
Decode	Read literal 'n'	Process Data	Write to PC	l	Decode	Read literal 'n'	Process Data	Write to PC
No	No	No	No		No	No	No	No
operation	operation	operation	operation		peration	operation	operation	operation
If No Jump:	~~	00	0.4	lf No Ju	•	00	00	04
Q1	Q2	Q3	Q4		Q1	Q2	Q3	Q4
Decode	Read literal 'n'	Process Data	No operation		Decode	Read literal 'n'	Process Data	No operation
Example:	HERE	BNC Jump		Example	<u>e:</u>	HERE	BNN Jump	
Before Instruc PC After Instructio If Carry PC	= ade on = 0;	dress (HERE dress (Jump)			fore Instruct PC er Instruction If Negati PC	= ad on ve = 0;	dress (HERE dress (Jump	,

BNO	v	Branch if N	Not Overflow		BNZ	Branch if I	Not Zero	
Synta	ax:	BNOV n			Syntax:	BNZ n		
Oper	ands:	-128 ≤ n ≤ ′	127		Operands:	-128 ≤ n ≤	127	
Oper	ation:	if Overflow (PC) + 2 + 2	,		Operation:	if Zero bit is (PC) + 2 +	,	
Statu	s Affected:	None			Status Affected:	None		
Enco	ding:	1110	0101 nnr	nn nnnn	Encoding:	1110	0001 nn	inn nnnn
Desc	ription:	If the Overf program wi	low bit is '0', th Il branch.	nen the	Description:	If the Zero will branch	bit is '0', then	the program
		added to the incremente instruction,	nplement num e PC. Since th d to fetch the r the new addre n. This instruct nstruction.	e PC will have next ess will be		added to th incremente instruction,	d to fetch the the new addr n. This instruc	ne PC will have next ress will be
Word	ls:	1			Words:	1		
Cycle	es:	1(2)			Cycles:	1(2)		
Q C If Ju	ycle Activity: mp:				Q Cycle Activity: If Jump:	:		
	Q1	Q2	Q3	Q4	Q1	Q2	Q3	Q4
	Decode	Read literal 'n'	Process Data	Write to PC	Decode	Read literal 'n'	Process Data	Write to PC
	No	No	No	No	No	No	No	No
	operation	operation	operation	operation	operation	operation	operation	operation
If No	o Jump:			<i>.</i>	If No Jump:			<b>.</b>
	Q1	Q2	Q3	Q4	Q1	Q2	Q3	Q4
	Decode	Read literal 'n'	Process Data	No operation	Decode	Read literal 'n'	Process Data	No operation
		11	Data	operation		11	Data	operation
<u>Exan</u>	nple:	HERE	BNOV Jump		Example:	HERE	BNZ Jum <u>r</u>	>
	Before Instruct PC After Instruction If Overflo PC If Overflo PC	= ad on ow = 0; = ad ow = 1;	dress (HERE) dress (Jump) dress (HERE	)	Before Instr PC After Instruc If Zero P If Zero P	= ad tion = 0; C = ad = 1;	dress (HERE dress (Jump dress (HERE	)

BRA		Unconditio	onal Branch						
Synta	ax:	BRA n	BRA n						
Oper	ands:	-1024 ≤ n ≤	$-1024 \le n \le 1023$						
Oper	ation:	(PC) + 2 + 2	$(PC) + 2 + 2n \rightarrow PC$						
Statu	s Affected:	None	None						
Enco	ding:	1101	0nnn n	nnn	nnnn				
Description: Add the 2's complement number '2n the PC. Since the PC will have incremented to fetch the next instruction, the new address will be PC + 2 + 2n. This instruction is a two-cycle instruction.					e vill be				
Word	s:	1							
Cycle	es:	2							
QC	ycle Activity:								
	Q1	Q2	Q3		Q4				
	Decode	Read literal 'n'	Process Data	V	Vrite to PC				
	No operation	No operation	No operation	ор	No peration				
	nple: Before Instruc PC After Instructio PC	= ad	BRA Jum dress (HER dress (Jum	E)					

BSF	Bit Set f			
Syntax:	BSF f, b {	{,a}		
Operands:	$\begin{array}{l} 0 \leq f \leq 255 \\ 0 \leq b \leq 7 \\ a \in [0,1] \end{array}$			
Operation:	$1 \rightarrow \text{f}$			
Status Affected:	None			
Encoding:	1000	bbba	ffff	ffff
Description:	Bit 'b' in reo	gister 'f' is	s set.	
If 'a' is '0', the Access Bank is selected If 'a' is '1', the BSR is used to select th GPR bank (default). If 'a' is '0' and the extended instruction set is enabled, this instruction operate in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed				
	Literal Offs	set Mode	" for deta	ils.
Words:	1			
Cycles:	1			
Q Cycle Activity:				
Q1	Q2	Q3		Q4
Decode	Read register 'f'	Proce: Data		Write gister 'f'
	iegistel i	Dala		JISICI I

FLAG\_REG, 7, 1

Example:

Before Instruction FLAG\_REG = 0Ah After Instruction FLAG\_REG = 8Ah

BSF

© 2007 Microchip Technology Inc.

BTFSC		Bit Test File	, Skip if Clear		BTFSS	5	Bit Test File	, Skip if Set	
Syntax:		BTFSC f, b	{,a}		Syntax	:	BTFSS f, b {	,a}	
Operand	ls:	$\begin{array}{l} 0 \leq f \leq 255 \\ 0 \leq b \leq 7 \\ a \in [0,1] \end{array}$			Opera	nds:	0 ≤ f ≤ 255 0 ≤ b < 7 a ∈ [0,1]		
Operatio	on:	skip if (f <b>)</b>	= 0		Operat	ion:	skip if (f <b>)</b>	= 1	
Status A	ffected:	None			Status	Affected:	None		
Encoding	a:	1011	bbba ff	ff ffff	Encod	ng:	1010	bbba fff	ff ffff
Descripti	ion:	instruction is the next instruction current instruction and a NOP is	gister 'f' is '0', t skipped. If bit uction fetched uction executio executed inste cle instruction.	'b' is '0', then during the n is discarded	Descri	otion:	instruction is the next instruction current instruction and a NOP is	gister 'f' is '1', t skipped. If bit uction fetched uction execution executed inste cle instruction.	'b' is '1', then during the n is discarded
			BSR is used to	is selected. If select the				e Access Bank BSR is used to lefault).	
		is enabled, th Indexed Liter whenever f ≤ Section 25.2 Bit-Oriented	d the extended nis instruction of ral Offset Addro 95 (5Fh). See 2.3 "Byte-Orie I Instructions et Mode" for do	nted and in Indexed			set is enable Indexed Liter whenever f ≤ Section 25.2 Bit-Oriented	d the extended d, this instruction ral Offset Addre 295 (5Fh). See 2.3 "Byte-Orient I Instructions of Mode" for de	on operates in essing mode nted and in Indexed
Words:		1			Words	:	1		
Cycles:			cles if skip and 2-word instruc		Cycles	:		vcles if skip and a 2-word instruc	
Q Cycle	e Activity:				Q Cyc	le Activity:			
	Q1	Q2	Q3	Q4	_	Q1	Q2	Q3	Q4
I	Decode	Read	Process	No		Decode	Read	Process	No
lf skip:		register 'f'	Data	operation	lf skip		register 'f'	Data	operation
n skip.	Q1	Q2	Q3	Q4	ii Ship	Q1	Q2	Q3	Q4
	No	No	No	No	Γ	No	No	No	No
0	operation	operation	operation	operation		operation	operation	operation	operation
lf skip a		by 2-word inst			lf skip		by 2-word inst		
	Q1	Q2	Q3	Q4	Г	Q1	Q2	Q3	Q4
	No	No	No	No		No	No	No	No operation
0	operation No	operation No	operation No	operation No		operation No	operation No	operation No	No
0	operation	operation	operation	operation		operation	operation	operation	operation
<u>Example</u>	<u>9:</u>	HERE BI FALSE : TRUE :	FSC FLAG	, 1, 0	<u>Examp</u>	<u>le:</u>	HERE BI FALSE : TRUE :	FSS FLAG	, 1, 0
	fore Instruct PC er Instruction If FLAG<1 PC If FLAG<1 PC	ion = add n = 0; = add 1> = 0;	ress (HERE) ress (TRUE) ress (FALSE	)		efore Instruct PC fter Instructio If FLAG< PC If FLAG< PC	ion = add n = 0; = add 1> = 0; 1> = 1;	ress (HERE) ress (False) ress (TRUE)	

BTG	Bit Toggle f	BOV	Branch if C	Overflow		
Syntax:	BTG f, b {,a}	Syntax:	BOV n			
Operands:	$0 \le f \le 255$	Operands:	$-128 \le n \le 127$			
	0 ≤ b < 7 a ∈ [0,1]	Operation:	if Overflow (PC) + 2 + 2	,		
Operation:	$(f < b^>) \rightarrow f < b^>$	Status Affected:	None			
Status Affected:	None	Encoding:	1110	0100 nn	nn nnnn	
Encoding: Description:	0111 bbba ffff ffff Bit 'b' in data memory location 'f' is	Description:	If the Overflow bit is '1', then the program will branch.			
inverted. If 'a' is '0', the Access Bank is selected. If 'a' is '1', the BSR is used to select the GPR bank (default). If 'a' is '0' and the extended instruction			The 2's complement number '2n' is added to the PC. Since the PC will have incremented to fetch the next instruction, the new address will be PC + 2 + 2n. This instruction is then a			
	If 'a' is '0' and the extended instruction		two-cycle ir		uon is uien a	
	set is enabled, this instruction operates in Indexed Literal Offset Addressing	Words:	1			
	mode whenever $f \le 95$ (5Fh). See	Cycles:	1(2)			
	Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed Literal Offset Mode" for details.	Q Cycle Activity: If Jump:				
Words:	1	Q1	Q2	Q3	Q4	
Cycles:	1	Decode	Read literal 'n'	Process Data	Write to PC	
Q Cycle Activity:		No	No	No	No	
Q1	Q2 Q3 Q4	operation	operation	operation	operation	
Decode	Read Process Write	If No Jump:			_	
	register 'f' Data register 'f'	Q1	Q2	Q3	Q4	
Example:	BTG PORTC, 4, 0	Decode	Read literal 'n'	Process Data	No operation	
Before Instru PORTO	iction:	Example:	HERE	BOV Jump		
After Instruct PORTC	ion:	Example: Before Instruc PC After Instructi If Overflu PC	ction = ad on ow = 1;	dress (HERE dress (Jump	)	

ΒZ		Branch if	Zero			
Synta	ax:	BZ n				
Oper	rands:	-128 $\leq$ n $\leq$	127			
Oper	ration:	if Zero bit i (PC) + 2 +	- ,	;		
Statu	is Affected:	None				
Enco	oding:	1110	0000	nnr	n	nnnn
Desc	cription:	If the Zero will branch		then t	he pro	gram
		The 2's complement number '2n' is added to the PC. Since the PC will have incremented to fetch the next instruction, the new address will be PC + 2 + 2n. This instruction is then a two-cycle instruction.				
Words: 1						
Cycles: 1(2)						
	ycle Activity:					
	Q1	Q2	Q	3	(	<b>Q</b> 4
	Decode	Read literal	Proce			te to
	Ne	ʻn'	Dat	-		C
	No operation	No operation	No operat		-	lo ation
lf No	o Jump:	oporation	opora		opoi	ation
	Q1	Q2	Q	3	(	<b>Q</b> 4
	Decode	Read literal 'n'	Proce Dat		-	lo ation
Exan	<u>nple:</u>	HERE	ΒZ	Jump		
	Before Instruction PC = address (HERE)					
	PC		dress (	HERE)		
	PC After Instruction	on	ldress (	HERE)		
	PC	on = 1;		,		
	PC After Instruction If Zero	on = 1; = ac = 0;	ldress (	HERE) Jump) HERE		

<b>•</b> •	L	Subroutin						
Synt	ax:	CALL k {,	CALL k {,s}					
Oper	rands:	$0 \le k \le 104$ s $\in$ [0,1]	$0 \le k \le 1048575$ s $\in$ [0,1]					
Oper	ration:	$\begin{array}{l} (PC) + 4 - \\ k \to PC < 2 \\ if s = 1, \\ (W) \to WS \\ (STATUS) \\ (BSR) \to E \end{array}$	0:1>; ; → STATI	JSS,				
Statu	is Affected:	None						
Encoding: 1st word (k<7:0>) 2nd word(k<19:8>)		1110 1111	110s k <sub>19</sub> kkk	/		kkk} kkk}		
		(PC+ 4) is If 's' = 1, th registers a respective STATUSS update occ	memory range. First, return address (PC+ 4) is pushed onto the return stac If 's' = 1, the W, STATUS and BSR registers are also pushed into their respective shadow registers, WS, STATUSS and BSRS. If 's' = 0, no update occurs (default). Then, the 20-bit value 'k' is loaded into PC<20:1					
		CALLISU	wo-cycic	mouu	CliOI			
Word	ds:	2						
Word		2 2						
Cycle	es:							
Cycle			Q3	5		Q4		
Cycle	es: cycle Activity:	2	Q3 Push P stac	C to	'k'≤			
Cycle	es: cycle Activity: Q1	2 Q2 Read literal	Push P	C to k	'k'≺ Wrii	Q4 ad litera <19:8>		
Cycle	es: ycle Activity: Q1 Decode No operation	2 Q2 Read literal 'k'<7:0>, No	Push P stac No	C to k	'k' Writ op	Q4 ad litera <19:8> te to P No eratior		
Cycle Q C	es: ycle Activity: Q1 Decode No operation nple: Before Instruc	2 Q2 Read literal 'k'<7:0>, No operation HERE tion	Push P stac No operat	C to k ion	'k' Writ op	Q4 ad litera <19:8> te to P No eratior		
Cycle Q C	es: ycle Activity: Q1 Decode No operation nple:	2 Q2 Read literal 'k'<7:0>, No operation HERE tion = addres	Push P stac No operat	C to k ion	'k' Writ op	Q4 ad litera <19:8> te to P No eratior		

CLRF	Clear f						
Syntax:	CLRF f{,	a}					
Operands:	0 ≤ f ≤ 255 a ∈ [0,1]						
Operation:	$\begin{array}{l} 000h \rightarrow f, \\ 1 \rightarrow Z \end{array}$						
Status Affected:	Z						
Encoding:	0110	101a	ffff	ffff			
Description:	Clears the oregister.	Clears the contents of the specified register.					
	lf 'a' is '1', t	If 'a' is '0', the Access Bank is selected. If 'a' is '1', the BSR is used to select the GPR bank (default).					
	If 'a' is '0' and the extended instruction set is enabled, this instruction operates in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed Literal Offset Mode" for details.						
Words:	1						
Cycles:	1						
Q Cycle Activity:							
Q1	Q2	Q3		Q4			
Decode	Read	Proce		Write			
	register 'f'	Data	a r	egister 'f'			
Example: Before Instruc	CLRF	FLAG_	REG,1				
FLAG_R FLAG_R After Instructio FLAG_R	EG = 5A on						

CLRWDT	Clear Wate	hdog Ti	mer				
Syntax:	CLRWDT						
Operands:	None	None					
Operation:							
Status Affected:	TO, PD						
Encoding:	0000	0000	0000	0100			
Description:	CLRWDT instruction resets the Watchdog Timer. It also resets the postscaler of the WDT. Status bits, TO and PD, are set.						
Words:	1	1					
Cycles:	1						
Q Cycle Activity:							
Q1	Q2	Q3	3	Q4			
Decode	No operation	Proce Data		No operation			
Example:	CLRWDT						
Before Instruction WDT Counter = ?							

=	?
=	00h
=	0
=	1
=	1
	= = = =

COMF	Compleme	ent f		CPFSEQ		Compare f	with W, Skip	if f = W
Syntax:	COMF f	{,d {,a}}		Syntax:		CPFSEQ	f {,a}	
Operands:	$0 \le f \le 255$	,		Operands	s:	$0 \leq f \leq 255$		
·	d ∈ [0,1]					a ∈ [0,1]		
	a ∈ [0,1]			Operation	1:	(f) – (W),		
Operation:	$(\overline{f}) \rightarrow dest$					skip if (f) = (unsigned c	(VV) comparison)	
Status Affected:	N, Z			Status Aff	ected.	None	ompanoon	
Encoding:	0001	11da ff	ff ffff	Encoding		0110	001a ff:	ff ffff
Description:	The conten	ts of register 'I	" are	Descriptio				f data memory
	•	ted. If 'd' is '0		2000			o the contents	
		'. If 'd' is '1', th ( in register 'f'				performing	an unsigned s	ubtraction.
		-	. ,			· · · · ·	en the fetched	
			nk is selected. d to select the				ind a NOP is ex	
	GPR bank					instruction.	iking this a two	J-Cycle
		nd the extend				lf 'a' is '0', t	he Access Bai	nk is selected.
			ction operates			lf 'a' is '1', t	he BSR is use	
		Literal Offset A lever f ≤ 95 (5	-			GPR bank	(default).	
		.2.3 "Byte-Or	,				nd the extende	
		d Instruction					ed, this instruc Literal Offset A	•
		set Mode" for	details.				ever f $\leq$ 95 (5)	0
Words:	1						.2.3 "Byte-Or	
Cycles:	1						ed Instruction set Mode" for	
Q Cycle Activity			<b>.</b>	Words:		1		dotano.
Q1	Q2	Q3	Q4 Write to	Cycles:		1(2)		
Decode	Read register 'f'	Process Data	destination	- ,		( )	cles if skip and	d followed
						by a	2-word instrue	ction.
Example:	COMF	REG, 0, 0		Q Cycle	-			<b>.</b>
Before Inst	ruction				Q1	Q2 Read	Q3 Process	Q4 No
REG	= 13h				ecode	register 'f'	Data	operation
After Instru				lf skip:		- 5		
REG W	= 13h = ECh				Q1	Q2	Q3	Q4
					No	No	No	No
					eration	operation d by 2-word in	operation	operation
				ii ship ai	Q1	Q2	Q3	Q4
					No	No	No	No
				ор	eration	operation	operation	operation
				00	No eration	No operation	No operation	No operation
								•••
				Example:		HERE	CPFSEQ REG	G, O
						NEQUAL EQUAL	:	
				Refo	re Instruc			
				2010	PC Addr	ess = HE	RE	
					W REG	= ? = ?		
				After	· Instructio			

After Instruction If REG PC If REG PC

= = ≠ W; Address (EQUAL) W; Address (NEQUAL)

CPFS	GT	Compare f	with W, Skip	if f > W			
Synta	ax:	CPFSGT f {,a}					
Oper	ands:	$0 \le f \le 255$					
•		a ∈ [0,1]					
Oper	ation:	(f) - (W),					
•		skip if (f) >	(W)				
		(unsigned o	comparison)				
Statu	s Affected:	None					
Enco	ding:	0110	010a fff	ff ffff			
Desc	ription:	Compares	the contents of	data memory			
		location 'f' t	o the contents an unsigned s	of the W by			
		If the conte	nts of 'f' are gro	eater than the			
			WREG, then t				
			is discarded ar				
		executed in two-cycle ir	stead, making	this a			
		lf 'a' is '0', t	he Access Bar	nk is selected.			
			he BSR is use	d to select the			
		GPR bank	(default).				
			nd the extende				
			ed, this instruc	•			
			Literal Offset A	•			
			ever f ≤ 95 (5F . <b>2.3 "Byte-Ori</b>				
			d Instruction				
			set Mode" for				
Word	s:	1					
Cycle		1(2)					
Oyoic	.0.	. ,	ycles if skip ar	nd followed			
			a 2-word instru				
QC	cle Activity:						
	Q1	Q2	Q3	Q4			
	Decode	Read	Process	No			
		register 'f'	Data	operation			
lf sk		<b>6</b> -	<b>6</b> -	<b>A</b> :			
	Q1	Q2	Q3	Q4			
	No	No	No	No			
lf ok	operation	operation	operation struction:	operation			
11 51	ip and followe Q1	Q2	Q3	Q4			
	No	No	No	No			
	operation	operation	operation	operation			
	No	No	No	No			
	operation	operation	operation	operation			
_							
Exam	<u>iple:</u>	HERE	CPFSGT RE	G, 0			
		NGREATER GREATER	:				
	Before Instruc	tion					
	PC		dress (HERE)	)			
	W Aftor Instructio	= ?					
	After Instructic If REG						
	PC		dress (GREA	FER)			
	If REG	≤ W;					
	PC	= Ad	dress (NGREA	ATER)			

CPF	SLT	Compare f	Compare f with W, Skip if f < W				
Synt	ax:	CPFSLT	f {,a}				
Oper	rands:	$0 \leq f \leq 255$					
		a ∈ [0,1]	a ∈ [0,1]				
Oper	ration:	(f) - (W),					
		skip if (f) <	. ,				
Stati	us Affected:	None	(unsigned comparison)				
Encoding:			0110 000a ffff ffff				
	0						
Dest	pription:	location 'f' f	to the contents of an unsigned s				
		contents of instruction	nts of 'f' are le W, then the fe is discarded an istead, making istruction.	etched nd a NOP is			
			he Access Bai he BSR is use (default).				
Word	ds:	1					
Cycles:		1(2)					
			ycles if skip an				
		by a	a 2-word instru	iction.			
QC	cycle Activity:	00	00	04			
	Q1 Decode	Q2 Read	Q3 Process	Q4 No			
	Decoue	register 'f'	Data	operation			
lf sk	kip:	<u> </u>					
	Q1	Q2	Q3	Q4			
	No	No	No	No			
	operation	operation operation		operation			
lf sk	tip and followe			04			
	Q1 No	Q2 No	Q3 No	Q4 No			
	operation	operation	operation	operation			
	No	No	No	No			
	operation	operation	operation	operation			
<u>Exar</u>	<u>nple:</u>	NLESS	CPFSLT REG, : :	1			
	Before Instruc	tion					
	PC		Idress (HERE	)			
	W After Instructio	= ?					
	If REG	< W					
	PC If REG	= Ac ≥ W	dress (LESS	)			
	PC		dress (NLES	S)			

DAW Decimal Adjust W Register		DECF	Decrement f				
Syntax:	ax: DAW Syntax:	Syntax:	DECF f {,d {,a}}				
Operands:	None			Operands:	$0 \le f \le 255$		
Operation:	•	> 9] or [DC = 1	•		d ∈ [0,1]		
	(W<3:0>) + else	$-6 \rightarrow W<3:0>;$		Operation:	a ∈ [0,1] (f) – 1 → de	oct	
	(W<3:0>) –	→ W<3:0>		Status Affected:			
					C, DC, N, C		
	•	> 9] or [C = 1], - 6 $\rightarrow$ W<7:4>,		Encoding: Description:		01da ff register 'f'. If	ff fff:
	C = 1;	<b>o</b> <i>i</i> <b>n</b> <i>n n n n n n n n n n</i>		Description.		red in W. If 'c	
	else	. \\/ .7.4>			result is sto	red back in re	
$(W<7:4>) \rightarrow W<7:4>$			(default).				
Status Affected:	C					he Access Ba	
Encoding: 0000 0000 0000 0111				If 'a' is '1', the BSR is used to select th GPR bank (default).			
Description:		ts the eight-bit om the earlier a				nd the extend	ded instructio
	0	each in packed				ed, this instru	•
	and produc result.	es a correct pa	acked BCD			Literal Offset iever f ≤ 95 (5	•
A/anda.						.2.3 "Byte-O	,
Words:	1					d Instruction	
Cycles:	1					set Mode" for	r details.
Q Cycle Activity: Q1	Q2	Q3	Q4	Words:	1		
Decode	Read	Process	Write	Cycles:	1		
	register W	Data	W	Q Cycle Activity: Q1	Q2	Q3	Q4
European la Au				Decode	Read	Process	Write to
Example 1:	DAW				register 'f'	Data	destination
Before Instru W	ction = A5h						
С	= 0			Example:	DECF	CNT, 1, (	C
DC After Instruct	= 0			Before Instru			
W	= 05h			CNT Z	= 01h = 0		
C DC	= 1 = 0			After Instructi	on		
Example 2:	-			CNT Z	= 00h = 1		
Before Instru	ction			-	•		
	= CEh						
W	= 0 = 0						
С							
C DC After Instruct	ion						
C DC	•						

DEC	FSZ	Decrement	f, Skip if 0			
Synta	ax:	DECFSZ f	DECFSZ f {,d {,a}}			
Oper	ands:	$0 \le f \le 255$ $d \in [0,1]$ $a \in [0,1]$	d ∈ [0,1]			
Oper	ation:	(f) – 1 $\rightarrow$ de skip if resul				
Statu	s Affected:	None				
Enco	oding:	0010	11da fff	f ffff		
Desc	cription:	decremente placed in W	ts of register 'f ed. If 'd' is '0', f /. If 'd' is '1', th < in register 'f'	the result is ne result is		
		which is alroad a NOP i	is '0', the nex eady fetched i s executed ins le instruction.	s discarded		
			ne Access Bar ne BSR is use (default).			
		set is enabl in Indexed I mode when Section 25 Bit-Oriente	nd the extended ed, this instruct Literal Offset A ever $f \le 95$ (50 .2.3 "Byte-Or ed Instruction set Mode" for	ction operates Addressing Fh). See <b>iented and</b> <b>s in Indexed</b>		
Word	ls:	1				
Cycle	es:	•	cles if skip an 2-word instru			
QC	ycle Activity:					
	Q1	Q2	Q3	Q4		
	Decode	Read register 'f'	Process Data	Write to destination		
lf sk	ip:		ł	4		
	Q1	Q2	Q3	Q4		
	No	No	No	No		
lf als	operation	operation d by 2-word in:	operation	operation		
11 56	Q1	Q2	Q3	Q4		
	No	No	No	No		
	operation	operation	operation	operation		
	No	No	No	No		
	operation	operation	operation	operation		
<u>Exan</u>	nple:	HERE	DECFSZ GOTO	CNT, 1, 1 LOOP		
	Before Instruc	CONTINUE				
	PC After Instructio CNT					
	If CNT	= CNT – 1 = 0;				
	PC If CNT	= Address ≠ 0;	G (CONTINUE	.)		
	PC	≠ 0, = Address	6 (HERE + 2	)		

Description:       The contents of register 'f' are decremented. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed back in register 'f' (default).         If the result is not '0', the next instruction which is already fetched discarded and a NOP is executed instead, making it a two-cycle instruction.         If 'a' is '0', the Access Bank is select instruction.         If 'a' is '0', the Access Bank is select if 'a' is '0', the BSR is used to select GPR bank (default).         If 'a' is '0' and the extended instruct set is enabled, this instruction oper in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented an Bit-Oriented Instructions in Index Literal Offset Mode" for details.         Words:       1         Cycles:       1(2)         Note:       3 cycles if skip and followe by a 2-word instruction.         Q 1       Q2       Q3       Q4         Decode       Read       Process       Write to the second s	-	x:	DCESNZ					
d ∈ [0,1] a ∈ [0,1]         Operation:       (f) – 1 → dest, skip if result ≠ 0         Status Affected:       None         Encoding:       0100       11da       ffff       ff         Description:       The contents of register 'f' are decremented. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed back in register 'f' (default).         If the result is not '0', the next instruction which is already fetched discarded and a NOP is executed instead, making it a two-cycle instruction.         If 'a' is '0', the Access Bank is select If 'a' is '1', the BSR is used to select GPR bank (default).         If 'a' is '0' and the extended instruct set is enabled, this instruction operation in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented an Bit-Oriented Instructions in Indez Literal Offset Mode" for details.         Words:       1         Cycles:       1(2) Note:         3 cycles if skip and followe by a 2-word instruction.         Q1       Q2       Q3         Q1       Q2       Q3         Q1       Q2       Q3	Opera			DCFSNZ f {,d {,a}}				
skip if result ≠ 0         Status Affected:       None         Encoding:       0100       11da       ffff       fff         Description:       The contents of register 'f' are decremented. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed back in register 'f' (default).         If the result is not '0', the next instruction which is already fetched discarded and a NOP is executed instead, making it a two-cycle instruction.         If 'a' is '0', the Access Bank is select If 'a' is '1', the BSR is used to select GPR bank (default).         If 'a' is '0' and the extended instruct set is enabled, this instruction operation Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented an Bit-Oriented Instructions in Index Literal Offset Mode" for details.         Words:       1         Cycles:       1(2)         Note:       3 cycles if skip and followe by a 2-word instruction.         Q Cycle Activity:       Q1       Q2       Q3       Q4         Decode       Read       Process       Write to the selection operation.		ands:	$d \in [0,1]$	d ∈ [0,1]				
Encoding:       0100       11da       ffff       fff         Description:       The contents of register 'f' are decremented. If 'd' is '0', the result placed in W. If 'd' is '1', the result is placed back in register 'f' (default). If the result is not '0', the next instruction which is already fetched discarded and a NOP is executed instead, making it a two-cycle instruction.         If 'a' is '0', the Access Bank is select if 'a' is '1', the BSR is used to select GPR bank (default).         If 'a' is '0' and the extended instruct set is enabled, this instruction operatin Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented an Bit-Oriented Instructions in Index Literal Offset Mode" for details.         Words:       1         Cycles:       1(2)         Note:       3 cycles if skip and followe by a 2-word instruction.         Q1       Q2       Q3       Q4         Decode       Read       Process       Write to the second process	Opera	ation:	()	$(f) - 1 \rightarrow dest,$				
Description:       The contents of register 'f' are decremented. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed back in register 'f' (default).         If the result is not '0', the next instruction which is already fetched discarded and a NOP is executed instead, making it a two-cycle instruction.         If 'a' is '0', the Access Bank is select if 'a' is '0', the Access Bank is select GPR bank (default).         If 'a' is '0', the Access Bank is select if 'a' is '0' and the extended instruction oper in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented an Bit-Oriented Instructions in Index Literal Offset Mode" for details.         Words:       1         Cycles:       1(2)         Note:       3 cycles if skip and followe by a 2-word instruction.         Q 1       Q2       Q3       Q4         Decode       Read       Process       Write to the second s	Status	Affected:	None					
decremented. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed back in register 'f' (default).         If the result is not '0', the next instruction which is already fetched discarded and a NOP is executed instead, making it a two-cycle instruction.         If 'a' is '0', the Access Bank is select instruction.         If 'a' is '0', the Access Bank is select if 'a' is '1', the BSR is used to select GPR bank (default).         If 'a' is '0' and the extended instruct set is enabled, this instruction operation in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented an Bit-Oriented Instructions in Index Literal Offset Mode" for details.         Words:       1         Cycles:       1(2)         Note:       3 cycles if skip and followe by a 2-word instruction.         Q Cycle Activity:       Q1       Q2       Q3       Q4         Decode       Read       Process       Write to the second instruction.	Encod	ding:	0100	0100 11da ffff ffff				
instruction which is already fetched         discarded and a NOP is executed         instead, making it a two-cycle         instruction.         If 'a' is '0', the Access Bank is select         GPR bank (default).         If 'a' is '0' and the extended instruct         set is enabled, this instruction operation         mode whenever f ≤ 95 (5Fh). See         Section 25.2.3 "Byte-Oriented an         Bit-Oriented Instructions in Index         Literal Offset Mode" for details.         Words:       1         Cycles:       1(2)         Note:       3 cycles if skip and follower         by a 2-word instruction.         Q Cycle Activity:         Q1       Q2       Q3       Q4         Decode       Read       Process       Write to	Descr	iption:	decrement placed in V	decremented. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is				
If 'a' is '1', the BSR is used to select GPR bank (default).         If 'a' is '0' and the extended instruct set is enabled, this instruction operation in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented an Bit-Oriented Instructions in Index Literal Offset Mode" for details.         Words:       1         Cycles:       1(2)         Note:       3 cycles if skip and followe by a 2-word instruction.         Q Cycle Activity:       Q1       Q2       Q3       Q4         Decode       Read       Process       Write to the test of the test of the test of test of the test of test			instruction discarded a instead, ma	which is alre and a NOP is aking it a two	ady fetched is executed			
set is enabled, this instruction operation in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented an Bit-Oriented Instructions in Index Literal Offset Mode" for details.         Words:       1         Cycles:       1(2)         Note:       3 cycles if skip and followe by a 2-word instruction.         Q Cycle Activity:       Q1       Q2       Q3       Q4         Decode       Read       Process       Write to the second secon			lf 'a' is '1', t	he BSR is us				
Words: 1 Cycles: 1(2) Note: 3 cycles if skip and followe by a 2-word instruction. Q Cycle Activity: Q1 Q2 Q3 Q4 Decode Read Process Write to			set is enab in Indexed mode wher Section 25 Bit-Oriente	led, this instr Literal Offse never f ≤ 95 ( 5.2.3 "Byte-C ed Instructio	uction operates t Addressing (5Fh). See Driented and ons in Indexed			
Note:     3 cycles if skip and followe by a 2-word instruction.       Q Cycle Activity:     Q1     Q2     Q3     Q4       Decode     Read     Process     Write to the second sec	Words	3:						
Q1 Q2 Q3 Q4 Decode Read Process Write t	Cycle	S:	Note: 3 d	• •				
Decode Read Process Write t	Q Cy	cle Activity:						
	-	Q1	Q2	Q3	Q4			
		Decode			Write to			
			register 'f'	Data	destination			
lf skip: Q1 Q2 Q3 Q4	II SKI		02	03	04			
No         No         No         No	Г			1	-			
					operation			
If skip and followed by 2-word instruction:	lf ski	p and followed	d by 2-word in	struction:				
Q1 Q2 Q3 Q4	_	Q1	Q2	Q3	Q4			
		No	No	No	No			
	-	•	•		operation			
operation operation operation operation					-			
operation         operation         operation         operation           No         No         No         No	L <u>Exam</u>	•	•	1 •				
operation         operation         operation         operation           No         No         No         No           operation         operation         operation         operation           Example:         HERE         DCFSNZ         TEMP, 1, 0           ZERO         :         HERE         DCFSNZ	E			_				
operation         operation         operation         operation         operation           No         No         No         No         No         No         operation	,	TEMP	=	?				
operation         operation         operation         operation         operation           No         No         No         No         No         operation           operation         operation         operation         operation         operation         operation           Example:         HERE         DCFSNZ         TEMP, 1, 0         ZERO         ZERO         ZERO         TEMP	F		n =	TEMP – 1				
operation         operation         operation         operation         operation           No         No         No         No         No         operation           operation         operation         operation         operation         operation           Example:         HERE         DCFSNZ         TEMP, 1, 0           ZERO         :         NZERO         :           Before Instruction         TEMP         = ?           After Instruction         *         *		If TEMP	=	0;				
operation         operation         operation         operation           No         No         No         No         No           operation         operation         operation         operation         operation           Example:         HERE         DCFSNZ         TEMP, 1, 0           ZERO         :         NZERO         :           Before Instruction         TEMP         = ?           After Instruction         TEMP         = 0;		PC If TEMP	= ≠	Address 0;	(ZERO)			
operation         operation         operation         operation         operation           No         No         No         No         No         operation         operation           Example:         HERE         DCFSNZ         TEMP, 1, 0         ZERO         ZERO         ZERO         ZERO         ZERO         TEMP, 1, 0         ZERO         ZERO </td <td></td> <td>PC</td> <td>=</td> <td>Äddress</td> <td>(NZERO)</td>		PC	=	Äddress	(NZERO)			

GOTO		Unconditi	onal Brai	nch		
Syntax:		GOTO k				
Operands:		$0 \le k \le 10^4$	48575			
Operation:		$k \rightarrow PC<2$	0:1>			
Status Affected	:	None				
Encoding: 1st word (k<7:0>) 2nd word(k<19:8>)		1110 1111	1111 k <sub>19</sub> kkk	k <sub>7</sub> k kkł		kkkk <sub>0</sub> kkkk <sub>8</sub>
Description:		GOTO allow anywhere range. The PC<20:1> instruction	within enti 20-bit va . GOTO is	re 2-N lue 'k'	/byte is lo	e memory baded into
Words:		2				
Cycles:		2				
Q Cycle Activi	ty:					
Q1		Q2	Q3			Q4
Decode	9	Read literal 'k'<7:0>,	No operat	ion	'k'	ad literal <19:8>, te to PC
No		No	No			No
operatio	n	operation	operat	ion	ор	eration
<u>Example:</u> After Instr PC		GOTO THE n Address (1				

INCF	Increment	f		
Syntax:	INCF f{,c	d {,a}}		
Operands:	$0 \le f \le 255$ $d \in [0,1]$ $a \in [0,1]$			
Operation:	(f) + 1 $\rightarrow$ de	est		
Status Affected:	C, DC, N,	OV, Z		
Encoding:	0010	10da	ffff	ffff
Description:	The conten incremente placed in V placed bac	d. If'd'is V. If'd'is	'0', the '1', the	result is result is
		he BSR i		is selected. to select the
	set is enab in Indexed mode wher <b>Section 25</b>	led, this i Literal Of never f ≤ 5 5.2.3 "Byt ed Instru	nstruction fset Ad 95 (5Fh te-Orien ctions	). See nted and in Indexed
Words:	1			
Cycles:	1			
Q Cycle Activity:				
Q1	Q2	Q3		Q4
Decode	Read register 'f'	Proce Data		Write to destination
Example:	INCF	CNT,	1, 0	
Before Instruc CNT Z DC After Instructio CNT Z C DC	= FFh = 0 = ? = ?			

INCF	SZ	Increment	f, Skip if 0				
Synta	ax:	INCFSZ f	INCFSZ f {,d {,a}}				
Oper	ands:	$\begin{array}{l} 0 \leq f \leq 255 \\ d  \in  [0,1] \\ a  \in  [0,1] \end{array}$	d ∈ [0,1]				
Oper	ation:	(f) + 1 $\rightarrow$ de skip if result					
Statu	s Affected:	None					
Enco	ding:	0011	11da ffi	ff ffff			
Desc	ription:	incremented placed in W placed back	ts of register 'f d. If 'd' is '0', th /. If 'd' is '1', th < in register 'f'.	ne result is e result is (default)			
		which is alre	is '0', the next eady fetched is s executed ins le instruction.	s discarded			
			he Access Bar he BSR is use (default).				
		set is enabl in Indexed I mode when Section 25 Bit-Oriente	nd the extended ed, this instruct Literal Offset A ever $f \le 95$ (5F 2.3 "Byte-Ori d Instruction set Mode" for	ction operates addressing Fh). See iented and s in Indexed			
Word	ls:	1					
Cycle	es:		ycles if skip a a 2-word instr				
QC	ycle Activity:						
	Q1	Q2	Q3	Q4			
	Decode	Read register 'f'	Process Data	Write to destination			
lf sk	ip:	regioter r	Data	destinution			
	Q1	Q2	Q3	Q4			
	No	No	No	No			
	operation	operation	operation	operation			
lf sk	•	d by 2-word in		04			
	Q1	Q2	Q3	Q4 No			
	No operation	No operation	No operation	operation			
	No	No	No	No			
	operation	operation	operation	operation			
<u>Exan</u>	<u>nple:</u>	HERE 1 NZERO : ZERO :	:	т, 1, 0			
	Before Instruc PC	= Address	G (HERE)				
	After Instructic CNT If CNT	= CNT + 1 = 0;					
	PC If CNT	= Address ≠ 0;	(ZERO)				
	PC	= Address	(NZERO)				

INFSNZ	Increment	f, Skip if Not	0
Syntax:	INFSNZ f	{,d {,a}}	
Operands:	$0 \leq f \leq 255$		
	d ∈ [0,1]		
<b>_</b>	a ∈ [0,1]		
Operation:	(f) + 1 $\rightarrow$ de skip if resul		
Status Affected:	None	., .	
Encoding:	0100	10da ff	ff ffff
Description:		ts of register 'f	
	incremente placed in W	d. If 'd' is '0', th /. If 'd' is '1', th k in register 'f'	he result is ie result is
	instruction discarded a	is not '0', the which is alread and a NOP is e: aking it a two-c	dy fetched is xecuted
	, -	he BSR is use	nk is selected. d to select the
	If 'a' is '0' a set is enabl in Indexed mode wher <b>Section 25</b>	nd the extend ed, this instruc Literal Offset A iever f ≤ 95 (5 <b>.2.3 "Byte-Or</b>	ction operates Addressing Fh). See <b>iented and</b>
			s in Indexed
Words	Literal Offs	set Mode" for	
Words:	Literal Offs		
Words: Cycles:	Literal Offs 1 1(2) Note: 3 cy		details. d followed
	Literal Offs 1 1(2) Note: 3 cy	set Mode" for vcles if skip an	details. d followed
Cycles:	Literal Offs 1 1(2) Note: 3 cy	set Mode" for vcles if skip an	details. d followed
Cycles: Q Cycle Activity:	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read	set Mode" for vcles if skip an a 2-word instru	details. d followed iction. Q4 Write to
Cycles: Q Cycle Activity: Q1 Decode	Literal Offs 1 1(2) Note: 3 cy by a	cles if skip an 2-word instru	details. d followed iction. Q4
Cycles: Q Cycle Activity: Q1 Decode If skip:	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f'	set Mode" for /cles if skip an a 2-word instru Q3 Process Data	details. d followed action. Q4 Write to destination
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2	set Mode" for (cles if skip an a 2-word instru- Q3 Process Data Q3	details. d followed action. Q4 Write to destination Q4
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No	set Mode" for (cles if skip an a 2-word instru- Q3 Process Data Q3 No	details. d followed action. Q4 Write to destination Q4 No
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation	set Mode" for vcles if skip an a 2-word instru Q3 Process Data Q3 No operation	details. d followed action. Q4 Write to destination Q4
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in	set Mode" for vcles if skip an a 2-word instru Q3 Process Data Q3 No operation struction:	details. d followed action. Q4 Write to destination Q4 No operation
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation	set Mode" for vcles if skip an a 2-word instru Q3 Process Data Q3 No operation	details. d followed action. Q4 Write to destination Q4 No
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe Q1	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in Q2	cles if skip and 2-word instru Q3 Process Data Q3 No operation struction: Q3	details. d followed iction. Q4 Write to destination Q4 No operation Q4
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe Q1 No	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in Q2 No	cles if skip and a 2-word instru Q3 Process Data Q3 No operation struction: Q3 No	details. d followed action. Q4 Write to destination Q4 No operation Q4 No
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe Q1 No operation	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in Q2 No operation	cles if skip and a 2-word instru Q3 Process Data Q3 No operation struction: Q3 No operation	details. d followed action. Q4 Write to destination Q4 No operation Q4 No operation
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe Q1 No operation No operation No	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in Q2 No operation No operation	set Mode" for (cles if skip and a 2-word instru- Q3 Process Data Q3 No operation struction: Q3 No operation No operation	details. d followed action. Q4 Write to destination Q4 No operation Q4 No operation No
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe Q1 No operation No operation Example: Before Instruct PC	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in Q2 No operation Ko operation HERE ZERO NZERO stion = Address	set Mode" for vcles if skip an a 2-word instru- Q3 Process Data Q3 No operation struction: Q3 No operation No operation No operation No operation	details. d followed action. Q4 Write to destination Q4 No operation Q4 No operation No operation
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe Q1 No operation No operation Example: Before Instructor PC After Instructor	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in Q2 No operation d by 2-word in Q2 No operation HERE ZERO NZERO Stion = Address	set Mode" for vcles if skip an a 2-word instru- Q3 Process Data Q3 No operation struction: Q3 No operation No operation INFSNZ REC	details. d followed action. Q4 Write to destination Q4 No operation Q4 No operation No operation
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe Q1 No operation No operation Example: Before Instruction REG If REG	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in Q2 No operation d by 2-word in Q2 No operation HERE ZERO NZERO Stion = Address on = REG + $\neq$ 0;	set Mode" for (cles if skip an a 2-word instru- Q3 Process Data Q3 No operation struction: Q3 No operation No operation INFSNZ REC S (HERE) 1	details. d followed action. Q4 Write to destination Q4 No operation Q4 No operation No operation
Cycles: Q Cycle Activity: Q1 Decode If skip: Q1 No operation If skip and followe Q1 No operation No operation Example: Before Instruction REG	Literal Offs 1 1(2) Note: 3 cy by a Q2 Read register 'f' Q2 No operation d by 2-word in Q2 No operation d by 2-word in Q2 No operation HERE ZERO NZERO tion = Address n = REG +	set Mode" for (cles if skip an a 2-word instru- Q3 Process Data Q3 No operation struction: Q3 No operation No operation INFSNZ REC S (HERE) 1	details. d followed action. Q4 Write to destination Q4 No operation Q4 No operation No operation

IORI	_w	Inclusive	OR Litera	al with \	w	
Synt	ax:	IORLW k				
Operands:		$0 \le k \le 25$	5			
Operation:		(W) .OR. k	$x \to W$			
Status Affected:		N, Z				
Encoding:		0000	1001	kkkk	kkkk	
Description:		The conte eight-bit lit in W.			ed with the It is placed	
Words:		1				
Cycles:		1				
QC	ycle Activity:					
	Q1	Q2	Q3	5	Q4	
	Decode	Read literal 'k'	Proce Data		Write to W	
_						
Exar	<u>nple:</u>	IORLW	35h			
Before Instruction W = 9Ah After Instruction						

BFh

=

IORWF Inclusive OR W with f							
Syntax:	IORWF f	{,d {,a}}					
Operands:	$\begin{array}{l} 0 \leq f \leq 255 \\ d  \in  [0,1] \\ a  \in  [0,1] \end{array}$						
Operation:	(W) .OR. (f)	$\rightarrow$ dest					
Status Affected:	N, Z						
Encoding:	0001	00da	ffff	ffff			
Description:	iption: Inclusive OR W with register 'f'. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed back in register 'f' (default).						
If 'a' is '0', the Access Bank is selected If 'a' is '1', the BSR is used to select the GPR bank (default).							
	If 'a' is '0' an set is enabli in Indexed I mode when Section 25. Bit-Oriente Literal Offs	ed, this i _iteral Of ever f ≤ .2.3 "By d Instru	nstruction ffset Addre 95 (5Fh). te-Oriente ctions in	operates essing See ed and Indexed			
Words:	1						
Cycles:	1						
Q Cycle Activity:							
Q1	Q2	Q3		Q4			
Decode	Read register 'f'	Proce Data		Vrite to stination			
Example:	IORWF RE	ESULT,	0, 1				
Before Instruc	tion						

fore	Instruction	

RESULT	=	13h 91h
After Instruction	n	
RESULT	=	13h
W	=	93h

DS39762C-page 382

W

LFSF	ર	Load FSR	Load FSR				
Synta	ax:	LFSR f, k					
Oper	ands:	$\begin{array}{l} 0 \leq f \leq 2 \\ 0 \leq k \leq 408 \end{array}$	95				
Oper	ation:	$k\toFSRf$					
Statu	s Affected:	None					
Enco	ding:	1110 1111	1110 0000	00f: k <sub>7</sub> kk			
Desc	ription:		The 12-bit literal 'k' is loaded into the file select register pointed to by 'f'.				
Word	ls:	2					
Cycle	es:	2					
QC	ycle Activity:						
	Q1	Q2	Q3		Q4		
	Decode	Read literal 'k' MSB	Process Data				Write literal 'k' MSB to FSRfH
	Decode	Read literal 'k' LSB	Proce: Data		Write literal k' to FSRfL		
<u>Exan</u>	<u>nple:</u> After Instructio FSR2H FSR2L	LFSR 2, on = 03 = AB	lh				

моу	′F	Move f			
Synta	ax:	MOVF f	{,d {,a}}		
Oper	ands:	$0 \le f \le 255$ $d \in [0,1]$ $a \in [0,1]$			
Oper	ation:	$f \to \text{dest}$			
Statu	is Affected:	N, Z			
Enco	oding:	0101	00da	ffff	ffff
Desc	ription:	The conter a destination status of 'd placed in V placed bac Location 'f 256-byte b	on depend i'. If 'd' is V. If 'd' is k in regis can be a	dent upor '0', the re '1', the re ter 'f' (de	n the sult is esult is fault).
		If 'a' is '0', If 'a' is '1', GPR bank	the BSR i	is used to	
		If 'a' is '0' a set is enab in Indexed mode whe Section 29 Bit-Orient Literal Off	led, this i Literal Of never f ≤ 5.2.3 "By ed Instru	nstruction ffset Add 95 (5Fh). te-Orient ctions in	n operates ressing See red and Indexed
Word	ls:	1			
Cycle	es:	1			
QC	ycle Activity:				
	Q1	Q2	Q3	8	Q4
	Decode	Read register 'f'	Proce Data		Write W

Example:	MOVF	REG,	Ο,	0
----------	------	------	----	---

Before Instruction		
REG	=	22h
W	=	FFh
After Instruction		
REG	=	22h
W	=	22h

© 2007 Microchip Technology Inc.

MOVFF	Move f to f			
Syntax:	MOVFF f <sub>s</sub>	,f <sub>d</sub>		
Operands:	$0 \le f_s \le 409$ $0 \le f_d \le 409$			
Operation:	$(f_s) \to f_d$			
Status Affected:	None			
Encoding: 1st word (source) 2nd word (destin.)	1100 1111	ffff ffff	ffff ffff	ffff <sub>s</sub> ffff <sub>d</sub>
Description:	The conten moved to d Location of in the 4096 FFFh) and can also be FFFh.	estination source 'f -byte dat location	n register s' can be a space ( of destina	ʻf <sub>d</sub> '. anywhere 000h to tion ʻf <sub>d</sub> '
		Either source or destination can be W (a useful special situation).		
	MOVFF is pa transferring peripheral r buffer or an	a data n egister (s	nemory lo such as th	cation to a
	The MOVFF PCL, TOSU destination	J, TOSH		
Words:	2			
Cycles:	2			
Q Cycle Activity:				
Q1	Q2	Q3		Q4
Decode	Read register 'f' (src)	Proce Data		No peration
Decode	No operation No dummy read	No operat	ion re	Write gister 'f' (dest)
Example:	MOVFF	REG1, F	REG2	

Before Instruction	on	
REG1	=	33h
REG2	=	11h
After Instruction	ı	
REG1	=	33h
REG2	=	33h

MOVLB	Move Liter	al to Lov	v Nibl	ble i	n BSR
Syntax:	MOVLW k	Ι.			
Operands:	$0 \le k \le 255$				
Operation:	$k \to BSR$				
Status Affected:	None				
Encoding:	0000	0001	kkk	k	kkkk
Description:	The eight-b Bank Selec of BSR<7:4 regardless	t Registe I> always	r (BSI rema	R). T ains '	he value
Words:	1				
Cycles:	1				
Q Cycle Activity:					
Q1	Q2	Q3			Q4
Decode	Read literal 'k'	Proce Data			te literal to BSR
Example:	MOVLB	5			
Before Instruct BSR Reg After Instructio BSR Reg	ister = 02 n				

Move W to f

MOVWF

MOVL	w	Mov	e Lite	ral to W			
Syntax	c	MOV	/LW	k			
Opera	nds:	$0 \le k$	s ≤ 25	5			
Opera	tion:	$k \to$	W				
Status	Affected:	None	Э				
Encod	ing:	0.0	000	1110	kkk	k	kkkk
Descri	ption:	The	eight-	bit literal '	k' is lo	ade	d into W.
Words	:	1					
Cycles	:	1					
Q Cyo	cle Activity:						
	Q1	Q	2	Q3	5		Q4
	Decode	Rea litera		Proce Data		W	/rite to W
Examp	ole:	MOVI	LW	5Ah			

5Ah

=

After Instruction W

Syntax:	MOVWF	f {,a}	
Operands:	0 ≤ f ≤ 255 a ∈ [0,1]		
Operation:	$(W) \to f$		
Status Affected:	None		
Encoding:	0110	111a f	fff ffff
Description:		from W to re can be anyw ank.	0
	,	he BSR is us	ank is selected. ed to select the
	set is enab in Indexed mode wher Section 25 Bit-Oriente	led, this instr Literal Offset never f ≤ 95 ( 5.2.3 "Byte-C	5Fh). See Priented and ns in Indexed
Words:	1		
Cycles:	1		
Q Cycle Activity:			
Q1	Q2	Q3	Q4
Decode	Read register 'f'	Process Data	Write register 'f'
		Data	
Example:	MOVWF	REG, O	
Before Instruct			
W REG	= 4Fh = FFh		
A ften lunation at a			

= = 4Fh 4Fh

After Instruction

W REG

© 2007 Microchip Technology Inc.

Syntax: Operands:	MULLW	k			
Operands:					
	$0 \le k \le 255$				
Operation:	(W) x k $\rightarrow$ l	PRODH:PRO	DL		
Status Affected:	None				
Encoding:	0000	1101 kk	kk kkkk		
Description:	out betwee 8-bit literal placed in P	'k'. The 16-bit	s of W and the result is L register pair.		
	W is uncha	nged.			
	None of the	None of the Status flags are affected.			
	possible in		w nor Carry is . A Zero result ted.		
Words:	1				
Cycles:	1				
Q Cycle Activity:					
Q1	Q2	Q3	Q4		
Decode	Read literal 'k'	Process Data	Write registers PRODH: PRODL		
<u>Example:</u>	MULLW	0C4h			
Before Instruc					
W PRODH PRODL After Instructi	= ?	'n			
W	= E2	'h )h			

MULWF	Multiply W w	ith f	
Syntax:	MULWF f{,	a}	
Operands:	0 ≤ f ≤ 255 a ∈ [0,1]		
Operation:	(W) x (f) $\rightarrow$ PF	RODH:PRO	DL
Status Affected:	None		
Encoding:	0000 (	001a ff	ff ffff
Description:	An unsigned multiplication is carried out between the contents of W and the register file location 'f'. The 16-bit result is stored in the PRODH:PRODL register pair. PRODH contains the high byte. Both W and 'f' are unchanged.		
	None of the S	tatus flags a	re affected.
	Note that neith possible in thi possible but n	s operation.	A Zero result i
	If 'a' is '0', the 'a' is '1', the B GPR bank (de	SR is used	nk is selected. to select the
	is enabled, thi	is instruction al Offset Add 95 (5Fh). Se <b>3 "Byte-Ori</b> Instruction	lressing mode e ented and s in Indexed
Words:	1		
Cycles:	1		
Q Cycle Activity:			
Q1	Q2	Q3	Q4
Decode	Read register 'f'	Process Data	Write registers PRODH:
			PRODL
Example:	MIIIWE	PEC 1	PRODL
Example: Before Instru	MULWF	REG, 1	PRODL
Example: Before Instru W REG PRODH PRODL After Instructi W REG	ction = C4 = B5 = ? = ?	ih 5h	PRODL

NEGF	Negate f
Syntax:	NEGF f {,a}
Operands:	$0 \le f \le 255$ a $\in [0,1]$
Operation:	$(\overline{f}) + 1 \rightarrow f$
Status Affected:	N, OV, C, DC, Z
Encoding:	0110 110a ffff ffff
Description:	Location 'f' is negated using two's complement. The result is placed in the data memory location 'f'. If 'a' is '0', the Access Bank is selected. If 'a' is '1', the BSR is used to select the GPR bank (default).
	If 'a' is '0' and the extended instruction set is enabled, this instruction operates in Indexed Literal Offset Addressing mode whenever $f \le 95$ (5Fh). See Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed Literal Offset Mode" for details.
Words:	1
Cycles:	1

NOP		No Opera	tion						
Synta	ax:	NOP							
Oper	ands:	None	None						
Oper	ation:	ion: No operation							
Status Affected: None									
Encoding:		0000	0000	000	0	0000			
		1111	XXXX	XXX	x	XXXX			
Desc	ription:	No operati	on.						
Word	ls:	1							
Cycle	es:	1							
QC	ycle Activity:								
	Q1	Q2	Q	3		Q4			
	Decode	No	No			No			
		operation	operat	tion	ор	peration			

Example:

None.

Q Cycle Activity:

Q1	Q2	Q3	Q4
Decode	Read	Process	Write
	register 'f'	Data	register 'f'

Example: NEGF REG, 1

 Before Instruction
 Image: Construction
 Image: Construction

POP		Pop Top of Return Stack							
Synta	ax:	POP							
Oper	ands:	None							
Oper	ation:	$(TOS) \rightarrow b$	it bucket						
Statu	is Affected:	None							
Enco	oding:	0000	0000	000	0	0110			
Description: The TOS value is pulled off the return stack and is discarded. The TOS value then becomes the previous value that was pushed onto the return stack. This instruction is provided to enable the user to properly manage the return stack to incorporate a software stack.									
Word	ls:	1							
Cycle	es:	1							
QC	ycle Activity:								
	Q1	Q2	Q	3		Q4			
	Decode	No operation	POP 1 valu		ор	No eration			
<u>Exan</u>	nple:	POP GOTO	NEW						
	Before Instruction TOS Stack (1 level		-	)031A2 )14332					
	After Instructio TOS PC	n	-	)14332 NEW	h				

PUS	н	Push Top o	Push Top of Return Stack					
Synta	ax:	PUSH						
Oper	ands:	None						
Oper	ation:	$(PC + 2) \rightarrow$	TOS					
Statu	s Affected:	None						
Enco	oding:	0000	0000	000	0	0101		
Desc	ription:	The PC + 2 the return s value is pus This instruct software sta then pushin	tack. shed d tion a ack by	The prev lown on t llows imp modifyir	ious the s blem ng Tr	TOS stack. enting a OS and		
Word	ls:	1	1					
Cycle	es:	1	1					
QC	ycle Activity:							
	Q1	Q2	Q3			Q4		
	Decode	PUSH PC + 2 onto return stack	No operation		ор	No eration		
Exan		PUSH						
	Before Instruc TOS PC	tion	= =	345Ah 0124h				
	After Instructio PC TOS Stack (1	on level down)	= = =	0126h 0126h 345Ah				

RCALL Relative Call								
Synta	vntax: RCALL n							
Oper	ands:	-1024 ≤ n ≤	1023					
Oper	ation:	· /	$      (PC) + 2 \rightarrow TOS, \\       (PC) + 2 + 2n \rightarrow PC $					
Statu	is Affected:	None						
Enco	oding:	ing: 1101 1nnn nnnn nnnn						
Desc	ription:	Subroutine call with a jump up to 1K from the current location. First, return address (PC + 2) is pushed onto the stack. Then, add the 2's complement number '2n' to the PC. Since the PC will have incremented to fetch the next instruction, the new address will be PC + 2 + 2n. This instruction is a two-cycle instruction.						
Word	ls:	1	1					
Cycle	es:	2						
QC	ycle Activity:							
	Q1	Q2	Q3	5	Q4			
	Decode	Read literal 'n' PUSH PC to stack	Proce Data		rite to PC			
	No	No	No		No			
	operation	operation	operat		peration			

Example: HERE RCALL Jump

Before Instruction

PC = Address (HERE) After Instruction PC = Address (Jump) TOS = Address (HERE + 2)

RES	ET	Reset							
Synta	ax:	RESET							
Oper	ands:	None	None						
Oper	ation:	Reset all registers and flags that are affected by a MCLR Reset.							
Statu	s Affected:	All							
Enco	ding:	0000	0000	111	1111 111				
Desc	ription:	This instrue							
Word	s:	1							
Cycle	es:	1							
QC	ycle Activity:								
	Q1	Q2	Q3	3		Q4			
	Decode	Start	No	No		No			
		reset	operat	tion	ор	eration			
Exan	<u>nple:</u>	RESET							

After Instruction

r Instruction	
Registers =	Reset Value
Flags* =	Reset Value

© 2007 Microchip Technology Inc.

Syntax:RETFLE (s)Operands:s $\in [0,1]$ Operation:(TOS) $\rightarrow$ PC,1 $\rightarrow$ GE/GE/GEH or PEE/GIEL;ff $s = 1$ ,if $s = 1$ ,(WS) $\rightarrow$ W,(STATUSS) $\rightarrow$ STATUS,(BSRS) $\rightarrow$ BSRPCLATU, PCLATH are unchangedStatus Affected:GE/GIEH, PEIE/GIEL.Encoding:0001 0001 0005Description:Return from interrupt Stack is popped and Top-of-Stack (TOS) is loaded into the PC. Interrupts are enabled by setting either the high or low priority global interrupt enable bit. If $s' = 1$ , the contents of the shadow registers W,Vords:1Quedee Activity:Q1Q1Q2Q Cycle Activity:Q1Q2Q Cycle Activity:PC=Q Cycle Activity:PC=PC=PC=PC=PC=PC=PC=PC=PC=PC=PC=PC=PC=PC=PC=	RET	FIE	Return from	m Interrupt		RET	LW	Return Lite	eral to W	
Operation:(TOS) $\rightarrow$ PC, 1 $\rightarrow$ GIE/GIEL or PEIE/GIEL; if s = 1, (WS) $\rightarrow$ W, (STATUSS) $\rightarrow$ STATUS, (BSRS) $\rightarrow$ BSR, (BSRS) $\rightarrow$ BSR (BSRS) $\rightarrow$ BSR (STATUSS) $\rightarrow$ STATUS, (BSRS) $\rightarrow$ BSR (STATUSS) $\rightarrow$ STATUS, (BSRS) $\rightarrow$ BSR (STATUSS) $\rightarrow$ STATUS, (BSRS) $\rightarrow$ BSR (CATU, PCLATH are unchanged Status Affected:Operation: (TOS) $\rightarrow$ PC, PCLATU, PCLATH are unchanged Status Affected:Status Affected:GIE/GIEH, PEIE/GIEL. Encoding:00001001000sDescription:Return from interrupt. Stack is popped and Top-of-Stack (TOS) is loaded into the contents of the shadow registers WS, STATUS and BSR. If 's' = 0, no update of these registers occurs (default).Words:1 C2Q Cycle Activity:Q1Q2Q3Q4 $\frac{Q}{Decode}$ $\overline{No}$ No operationNo operationNo operation $\frac{Q}{Q}$ Q3Q4 $\frac{Q}{Decode}$ $\overline{No}$ No operationNo operation $\frac{Q}{Q}$ Q3Q4 $\frac{Q}{Decode}$ $\overline{No}$ No operation $\frac{Q}{Q}$ Q3Q4 $\frac{Q}{Q}$	Synta	ax:	RETFIE {	\$}		Synt	ax:	RETLW k		
$\begin{array}{cccccccccccccccccccccccccccccccccccc$	Oper	ands:	$s \in [0,1]$			Ope	rands:	$0 \leq k \leq 255$		
$\begin{array}{cccccccccccccccccccccccccccccccccccc$	Oper	ation:	$1 \rightarrow GIE/G$	-	BIEL;	Ope	ration:	$(TOS) \rightarrow P$	,	nchanged
$\begin{array}{c cccc} [SSRs) \rightarrow SSR, \\ PCLATU, PCLATU are unchanged \\ Status Affected: \\ GIE/GIEH, PEIE/GIEL. \\ Encoding: \\ \hline 0000 & 0001 & 000s \\ \hline 0000 & 0000 & 000 & 000 \\ \hline 0000 & 0000 & 0000 & 000 \\ \hline 0000 & 0000 & 0000 & 0000 & 0000 \\ \hline 0000 & 0000 & 0000 & 0000 \\ \hline 0000 & 0000 & 0000 & 0$			( )			Statu	is Affected:	None		
PCLATU, PCLATH are unchanged Status Affected:Description:W is loaded with the eight-bit literal 'k'. The program counter is loaded from the top of the stack (the return address). The high address latch (PCLATH) remains unchanged.Description:Return from interrupt. Stack is popped and Top-of-Stack (TOS) is loaded into the PC. Interrupts are enabled by setting either the high or low priority global interrupt enable bit. If 's' = 1, the contents of the shadow registers WS, STATUS and BSR. If 's' = 0, no update of these registers occurs (default).Out of the stack (PCLATH) remains unchanged.Words:1Q1Q2Q3Q4DecodeRead From stack, from stack, Set GIEH or operationPOP PC from stack, Set GIEH or GIELQ1Q2Q3Q4Q4Call TABLE ; W contains table ; offset value ; w now has ; table valueNoNoNoNoNoNooperation <td></td> <td></td> <td>· · ·</td> <td></td> <td></td> <td>Enco</td> <td>oding:</td> <td>0000</td> <td>1100 kk</td> <td>kk kkkk</td>			· · ·			Enco	oding:	0000	1100 kk	kk kkkk
$\begin{array}{cccc} \text{Call of Notices} & \overrightarrow{\text{OUCL}} & \overrightarrow{\text{OUCL}} & \overrightarrow{\text{OUCL}} & \overrightarrow{\text{OUCL}} \\ \hline \text{Description:} & \text{Return from interrupt. Stack is popped and Top-of-Stack (TOS) is loaded into the PC. Interrupts are enabled by setting either the high or low priority global interrupt enable bit. If s' = 1, the contents of the shadow registers WS, STATUSS and BSR. Br. If s' = 0, no update of these registers occurs (default). \\ \hline \text{Vords:} & 1 \\ \hline \text{Cycles:} & 2 \\ \hline \text{Q Cycle Activity:} & \hline \text{Q1} & \boxed{\text{Q2}} & \boxed{\text{Q3}} & \boxed{\text{Q4}} \\ \hline \hline \hline \text{Decode} & \hline \text{no m stack} \\ \hline \text{STATUS and BSR. If s' = 0, no update of these registers occurs (default). \\ \hline \text{Vords:} & 1 \\ \hline \text{Cycles:} & 2 \\ \hline \text{Q Cycle Activity:} & \hline \text{Q1} & \boxed{\text{Q2}} & \boxed{\text{Q3}} & \boxed{\text{Q4}} \\ \hline \hline \hline \text{Decode} & \hline \text{operation} & \hline \text{operatio} & \hline \text{operation} & \hline \text{operatio} & $			· · ·		nchanged	Desc	cription:	W is loaded	with the eigh	nt-bit literal 'k'.
Encoding: 0000 0001 000s Description: Return from interrupt. Stack is popped and Top-of-Stack (TOS) is loaded into the PC. Interrupts are enabled by setting either the high or low priority global interrupt enable bit. If $s' = 1$ , the contents of the shadow registers W, STATUS and BSRs are loaded into their corresponding registers W, STATUS and BSRs. If $s' = 0$ , no update of these registers occurs (default). Words: 1 Cycles: 2 Q Cycle Activity: Q1 Q2 Q3 Q4 $\hline Decode \ No \ Operation \ Oper$	Statu	is Affected:	GIE/GIEH,	PEIE/GIEL.						
and Top-of-Stack (TOS) is loaded into the PC. Interrupts are enabled by setting either the high or low priority global interrupt enable bit. If 's' = 1, the contents of the shadow registers WS, STATUSS and BSRS are loaded into their corresponding registers W, STATUS and BSR are loaded into their corresponding registers w, STATUS are loaded into their corresponding registers w, STATUS and BSR are loaded into their corresponding registers w, STATUS are loaded into their corresponding registers w, STATUS are loaded into the loaded i		0						The high ac	,	
the PC. Interrupts are enabled by setting either the high or low priority global interrupt enable bit. If 's' = 1, the contents of the shadow registers WS, STATUSS and BSRS are loaded into their corresponding registers W, STATUS and BSR. If 's' = 0, no update of these registers occurs (default). Words: 1 Cycles: 2 Q Cycle Activity: Q1 Q2 Q3 Q4 Decode Read Process POP PC interrupt No No No No No operation operation operation Q1 Q2 Q3 Q4 Decode Read Process POP PC interrupt No No No No No operation operation operation POP PC from stack Set GIEH or GIEL No No No No No operation operation operation PC = TOS W = WS BSR = BSRS STATUSS GIE/GIEH, PEIE/GIEL = 1 W = 07h After Instruction	Desc	ription:		•		14/	1		changed.	
$\begin{array}{cccccccccccccccccccccccccccccccccccc$			the PC. Inte	errupts are ena	abled by					
$\begin{array}{c} \mbox{contents of the shadow registers WS, STATUSS and BSRS are loaded into their corresponding registers W, STATUS and BSR. If s' = 0, no update of these registers occurs (default). \\ \label{eq:starsecurve} Words: 1 \\ \mbox{Cycles: 2} \\ \mbox{Q Cycle Activity: } \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 1 } \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 2 } \mbox{Q 3 } \mbox{Q 4} \\ \hline \mbox{Q 6 } Q 6 $			•	•		,		2		
STATUSS and BSRS are loaded into their corresponding registers W, STATUS and BSR. If 's' = 0, no update of these registers occurs (default). $DecodeReadProcessPOP PCIteral 'k'POP PCIteral 'k'Words:1DecodeReadProcessIteral 'k'Datafrom stack,write to WQ Cycles:2QQ4NoNoNoQ1Q2Q3Q4CALL TABLE ; W contains table; offset value; w now hasExample:Q1Q2Q3Q4CALL TABLE ; W contains table; offset value; w now has:Q1Q2Q3Q4CALL TABLE ; W contains table; offset value; table value:MoNoNoNoNooperationoperationoperationoperationNoNoNoNoNooperationoperationoperation; table valueiTABLEADDWF PCL ; W = offsetRETIW k0 ; Begin tableRETIW k1 ;PC= TOSW= WSBSRBSR= BSRSSTATUSSGIE/GIEH, PEIE/GIEL = 1Before InstructionW= 07hAfter Instruction$			•	•		QC	,	00	00	04
Words:       1         Cycles:       2         Q Cycle Activity:       No         Q1       Q2       Q3         Q4       Q4       CALL TABLE         V       No       No         No       No       No					•		1	1		
STATUS and BSR. If S = 0, no update of these registers occurs (default).       write to W         Words:       1         Cycles:       2         Q Cycle Activity:							Decode			
Words:       1       No       No       No       No       No       No       No       No       operation       No       <					<i>i</i>					,
Cycles:       2         Q Cycle Activity:       Q1       Q2       Q3       Q4         Q Decode       No       No       POP PC       CALL TABLE       W contains table       CALL TABLE       W contains table         No	Word	ls.		,	()		-	-	-	
Q Cycle Activity:       Example:       Q1       Q2       Q3       Q4         Q       Decode       No       No       POP PC       from stack         Set GIEH or operation       operation       operation       GIEL       ; offset value         No       No       No       No       No       ; table value         No       No       No       No       operation       ; table value         No       No       No       No       operation       ; table value         No       No       No       No       operation       ; table value         Example:       RETFIE 1            After Interrupt       PC       = TOS           PC       = TOS       WS           BSR       = BSRS       STATUS       = STATUSS       Before Instruction         GIE/GIEH, PEIE/GIEL       = 1        W       = 07h         After Instruction       W       = 07h							operation	operation	operation	operation
Q1Q2Q3Q4DecodeNoNoPOP PC from stack Set GIEH or GIELfrom stack Set GIEH or GIEL; offset value ; w now has ; table valueNoNoNoNooperationoperationoperationoperationNoNoNoNoNooperationoperationoperationoperationPC=TOS W=STATUS GIE/GIEH, PEIE/GIEL:PC=TOS W:RETIW k1 :PC=STATUSS GIE/GIEH, PEIE/GIEL::BSR=BSRS STATUS GIE/GIEH, PEIE/GIEL::BSR=STATUSS GIE/GIEH, PEIE/GIEL::W=07h After InstructionW=			2			Ever	nnlo:			
DecodeNo operationNo operationPOP PC from stack Set GIEH or GIELNo operationExample: PC W BSR GIE/GIEH, PEIE/GIELRETFIE 1After Interrupt BSR GIE/GIEH, PEIE/GIELImage: Status statusCALL TABLE ; W contains table ; offset value ; TableExample: W BSR GIE/GIEH, PEIE/GIELTOS status statusRETLW k0 ; Begin table RETLW k1 ;Example: W BSR GIE/GIEH, PEIE/GIELTOS status statusStatus status statusPC W BSR GIE/GIEH, PEIE/GIELTOS status statusStatus status statusPC W BSR Status GIE/GIEH, PEIE/GIELTOS status statusStatus status statusPC W BSR Status GIE/GIEH, PEIE/GIELTOS status statusNo status statusPC W BSR Status Status Status StatusStatus status statusPC W BSR Status Status Status Status StatusStatus status statusPC W BSR Status Status Status StatusStatus status status status status st	QU		Q2	Q3	Q4		<u>npie.</u>			
Image: Set GIEH or GIEL       ; W now has         No       No       No         operation       operation       operation         operation       operation       operation         operation       operation       operation         No       No       No         operation       operation       operation         operation       operation       operation         Example:       RETFIE 1         After Interrupt       :         PC       = TOS         W       = WS         BSR       = BSRS         STATUS       = STATUSS         GIE/GIEH, PEIE/GIEL       = 1         Before Instruction       W         W       = 07h         After Instruction					1		CALL TABLE	; W conta:	ins table	
No       No       No       No       No       No       No       No       operation       operation <thoperation< th="">       operation       &lt;</thoperation<>			operation	operation	from stack					
No       No       No       No       No       No       No       Operation       operation <thoddotsic< th=""> <thoddotsics< th="">       operaticitities<!--</td--><td></td><td></td><td></td><td></td><td>Set GIEH or</td><td></td><td></td><td>-</td><td></td><td></td></thoddotsics<></thoddotsic<>					Set GIEH or			-		
No     No     No     Operation     Operation     Operation     Operation     TABLE       Example:     RETFIE     1     ADDWF PCL ; W = offset       Example:     RETFIE     1       After Interrupt     :       PC     =       W     =       BSR     =       STATUS     =       GIE/GIEH, PEIE/GIEL     =       1     W       W     =       01     00       W     =       01     00       W     =       01     01       W     =       01     01       W     =       01     01       01     01							:	, table va	arue	
Example:       RETFIE 1       RETLW k0 ; Begin table         After Interrupt       :         PC       = TOS         W       = WS         BSR       = BSRS         STATUS       = STATUSS         GIE/GIEH, PEIE/GIEL       = 1         W       = 07h         After Instruction		-	-	_	-					
Example:       RETFIE 1       RETLW k1 ;         After Interrupt       :       :         PC       =       TOS       :         W       =       WS       RETLW kn ; End of table         BSR       =       BSRS         STATUS       =       STATUSS         GIE/GIEH, PEIE/GIEL       =       1         W       =       07h         After Instruction       After Instruction		operation	operation	operation	operation		ADDWF PCL	; $W = offs$	set	
After Interrupt PC = TOS W = WS BSR = BSRS STATUS = STATUSS GIE/GIEH, PEIE/GIEL = 1 Before Instruction W = 07h After Instruction								5	able	
After Interrupt       :         PC       =       TOS         W       =       WS         BSR       =       BSRS         STATUS       =       STATUSS         GIE/GIEH, PEIE/GIEL       =       1         BEFore Instruction       W       =         W       =       07h         After Instruction	Exan	<u>nple:</u>	RETFIE	1				;		
PC       =       TOS       RETLW kn ; End of table         W       =       WS       RETLW kn ; End of table         BSR       =       BSRS         STATUS       =       STATUSS         GIE/GIEH, PEIE/GIEL       =       1         W       =       07h         After Instruction										
GIE/GIEH, PEIE/GIEL = 1 W = 07h After Instruction		W		= WS			RETLW kn	; End of t	table	
After Instruction		STATUS		= STATL						
							W		fkn	

RET	URN	m Subro	outine			
Syntax: RETURN {s}						
Oper	ands:	s ∈ [0,1]				
Operation: $(TOS) \rightarrow PC;$ if s = 1, $(WS) \rightarrow W,$ $(STATUSS) \rightarrow STATUS,$ $(BSRS) \rightarrow BSR,$ PCLATU, PCLATH are unchanged						
Status Affected: None						
Enco	ding:	0000	0000	0001	001s	
	ription:	Return fror popped an is loaded in 's'= 1, the registers W loaded into registers W 's' = 0, no occurs (de	d the top nto the pr contents /S, STAT o their con /, STATU update of	of the sta ogram co of the sha USS and respondin S and BS	ack (TOS) punter. If adow BSRS are ng SR. If	
Word	ls:	1				
Cycle	es:	2				
QC	ycle Activity:					
	Q1	Q2	Q	3	Q4	
	Decode	No operation	Proce Dat		POP PC om stack	
	No	No	No		No	
	operation	operation	opera	tion o	peration	
<u>Exan</u>	<u>nple:</u> After Instructio	RETURN				

After Instruction: PC = TOS

RLCF f {, $0 \le f \le 255$ $d \in [0,1]$ $a \in [0,1]$ (f <n>) <math>\rightarrow</math> des (f&lt;7&gt;) <math>\rightarrow</math> C, (C) <math>\rightarrow</math> dest</n>	st <n +="" 1="">,</n>	
$\begin{aligned} & d \in [0,1] \\ & a \in [0,1] \\ & (f < n >) \rightarrow des \\ & (f < 7 >) \rightarrow C, \\ & (C) \rightarrow dest < 0 \end{aligned}$		
$a \in [0,1]$ (f <n>) <math>\rightarrow</math> des (f&lt;7&gt;) <math>\rightarrow</math> C, (C) <math>\rightarrow</math> dest&lt;</n>		
$(f < n >) \rightarrow des$ $(f < 7 >) \rightarrow C,$ $(C) \rightarrow dest < 0$		
$(f < 7 >) \rightarrow C,$ (C) $\rightarrow dest < 0$		
	0-	
0011	01da fff	f ffff
	ult is stored ba	ack in registe
· · ·	o Accoss Bon	k is solocted
-		
If 'a' is '0' an	d the extende	d instruction
	,	
	```	,
Literal Offse		
C	<ul> <li>register</li> </ul>	°f ←
1		
•		
Q2	Q3	Q4
Read	Process	Write to
register 'f'	Data	destination
		0
RLCF	REG, 0,	0
RLCF	REG, 0,	U
tion = 1110 (		0
tion = 1110 ( = 0		0
tion = 1110 (	0110	0
tion = $1110$ ( = $0$ on = $1110$ ( = $1100$ (	0110	0
tion = 1110 ( = 0 on = 1110 (	0110	U
tion = $1110$ ( = $0$ on = $1110$ ( = $1100$ (	0110	U
	one bit to the If 'd' is '0', th is '1', the res 'f' (default). If 'a' is '0', th If 'a' is '1', th GPR bank (d If 'a' is '0' an set is enable in Indexed L mode whence Section 25.2 Bit-Oriented Literal Offset 1 1 2 Read	If 'a' is '0', the Access Ban If 'a' is '1', the BSR is used GPR bank (default). If 'a' is '0' and the extended set is enabled, this instruct in Indexed Literal Offset Ac mode whenever $f \le 95$ (5FI Section 25.2.3 "Byte-Orie Bit-Oriented Instructions Literal Offset Mode" for d C register 1 1 Q2 Q3 Read Process

RLNCF	Rotate Left f (no carry)		RRCF	Rotate Rig	ht f through	Carry
Syntax:	RLNCF f {,d {,a}}		Syntax:	RRCF f{,	d {,a}}	
Operands:	$\begin{array}{l} 0 \leq f \leq 255 \\ d  \in  [0,1] \\ a  \in  [0,1] \end{array}$		Operands:	$0 \le f \le 255$ $d \in [0,1]$ $a \in [0,1]$		
Operation:	$(f < n >) \rightarrow dest < n + 1 >,$ $(f < 7 >) \rightarrow dest < 0 >$		Operation:	$(f < n >) \rightarrow de$ $(f < 0 >) \rightarrow C$ $(C) \rightarrow dest$	,	
Status Affected:	N, Z		Status Affected:	C, N, Z		
Encoding:	0100 01da ffff	ffff	Encoding:	0011	00da ff	ff ffff
Description:	The contents of register 'f' ar one bit to the left. If 'd' is '0', is placed in W. If 'd' is '1', the stored back in register 'f' (de If 'a' is '0', the Access Bank is	the result e result is fault). s selected.	Description:	The contents of register 'f' are rotate one bit to the right through the Carry flag. If 'd' is '0', the result is placed in If 'd' is '1', the result is placed back i register 'f' (default).		
	If 'a' is '1', the BSR is used to select the GPR bank (default). If 'a' is '0' and the extended instruction set is enabled, this instruction operates		If 'a' is '0', the Access Bank is sele If 'a' is '1', the BSR is used to sele GPR bank (default).			
	in Indexed Literal Offset Add mode whenever f ≤ 95 (5Fh). Section 25.2.3 "Byte-Orient Bit-Oriented Instructions in Literal Offset Mode" for det register f	ressing . See ted and n Indexed		set is enabl in Indexed mode wher Section 25 Bit-Oriente	ed, this instru Literal Offset / ever f ≤ 95 (5 . <b>2.3 "Byte-O</b> r	Fh). See riented and is in Indexed
Words:	1			C C	- registe	er f 🗕 🗕
Cycles:	1				-	
Q Cycle Activity:			Words:	1		
Q1	Q2 Q3	Q4	Cycles:	1		
Decode		Vrite to	Q Cycle Activity:	00	00	0.4
	register 'f' Data de	stination	Q1 Decode	Q2 Read	Q3 Process	Q4 Write to
Example:	RLNCF REG, 1, 0		Decode	register 'f'	Data	destination
Before Instru					•	•
REG	= 1010 1011		Example:	RRCF	REG, 0,	0
After Instructi	on		Before Instruc	tion		
REG	= 0101 0111		REG C	= 1110 C = 0	110	
			After Instruction	°,		
			REG W C	= 1110 C = 0111 C = 0		

RRNCF		Rotate R	Rotate Right f (no carry)					
Syntax:		RRNCF f {,d {,a}}						
Operands	5:	$0 \le f \le 25$ $d \in [0,1]$ $a \in [0,1]$						
Operatior	1:	. ,	$(f \le n >) \rightarrow dest \le n - 1 >,$ $(f \le 0 >) \rightarrow dest \le 7 >$					
Status Aff	ected:	N, Z						
Encoding:		0100	00da	ffi	ff ffff			
Description:		one bit to is placed	The contents of register 'f' are rotated one bit to the right. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed back in register 'f' (default).					
		selected, is '1', the	If 'a' is '0', the Access Bank will be selected, overriding the BSR value. If 'a' is '1', then the bank will be selected as per the BSR value (default).					
		If 'a' is '0' and the extended instruction set is enabled, this instruction operates in Indexed Literal Offset Addressing mode whenever $f \le 95$ (5Fh). See Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed Literal Offset Mode" for details.						
		Γ	→ r	egister	f			
Words:		1						
Cycles:		1						
Q Cycle Activity:								
	Q1		Q	3	Q4			
D	ecode	Read	Proce	ess				
		register 'f'	Dat	а	Write to destination			
Example	1:	register 'f'	Dat					
Example Befo	<u>1:</u> re Instruc REG	RRNCF						
Befo	ore Instruc	RRNCF ction = 1101 cn	Dat					
Befo	re Instruc REG Instructic REG	RRNCF etion = 1101 on = 1110	Dat REG, 1 0111	, 0				
Befo After <u>Example</u>	re Instruc REG Instructio REG <u>2:</u> re Instruc	RRNCF etion = 1101 on = 1110 RRNCF	Dat REG, 1 0111 1011	, 0				
Befc After <u>Example</u> Befc	re Instruc REG Instructic REG <u>2:</u>	RRNCF etion = 1101 on = 1110 RRNCF etion = ? = 1101	Dat REG, 1 0111 1011	, 0				

f {,a} ≤ 255 (a),1] → f 10 11 (a) ontents of et to FFh s '0', the s '0', the s '1', the bank (de s '0' and enabled exed Lite whenev on 25.2.3 riented la Offset						
(0,1] $\rightarrow$ f 10 1 10 1 10 11 10 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11 11						
10 11 ontents of et to FFh s '0', the s '1', the bank (de s '0' and enabled exed Lite whenev on 25.2.3 riented I						
contents of et to FFh s '0', the s '1', the bank (de s '0' and enabled exed Lite whenev on 25.2.3 riented I						
contents of et to FFh s '0', the s '1', the bank (de s '0' and enabled exed Lite whenev on 25.2.3 riented I						
et to FFh s '0', the s '1', the bank (de s '0' and enabled exed Lite whenev on 25.2.3 riented I						
s '1', the bank (de s '0' and enabled exed Lite whenev on 25.2.3 riented I						
enabled exed Lite whenev on 25.2.3 riented I						
2						
d er 'f'						
Before Instruction REG = 5Ah After Instruction REG = FFh						

SLEEP	Enter Sle	Enter Sleep Mode		SUBFWB	Subtract f from W with Borrow		
Syntax:	SLEEP			Syntax:	SUBFWB f {,d {,a}}		
Operands:	None	None		Operands:	$0 \leq f \leq 255$		
Operation:	$00h \rightarrow WDT$ ,				$d \in [0,1]$		
		postscaler,		<b>.</b>	a ∈ [0,1]		
	$1 \rightarrow TO, 0 \rightarrow PD$			Operation:	$(W) - (f) - (\overline{C}) \rightarrow dest$		
Status Affastad	$\overline{TO}, \overline{PD}$			Status Affected:	N, OV, C, DC, Z		
Status Affected:			0.0011	Encoding:	0101 01da ffff ffff		
Encoding:	0000	0000 000		Description:	Subtract register 'f' and Carry flag		
Description:	The Power-Down status bit (PD) is cleared. The Time-out status bit $\overline{(TO)}$				(borrow) from W (2's complement method). If 'd' is '0', the result is stored in		
		Watchdog Tir			W. If 'd' is '1', the result is stored in		
	postscaler are cleared. The processor is put into Sleep mode				register 'f' (default).		
					If 'a' is '0', the Access Bank is selected. If		
		scillator stoppe	d.		'a' is '1', the BSR is used to select the GPR bank (default).		
Words:	1				If 'a' is '0' and the extended instruction		
Cycles:	1				set is enabled, this instruction operates		
Q Cycle Activity:					Indexed Literal Offset Addressing mod		
Q1	Q2	Q3	Q4		whenever $f \le 95$ (5Fh). See		
Decode	No operation	Process Data	Go to Sleep		Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed		
	operation	Dala	Sleep		Literal Offset Mode" for details.		
Example:	SLEEP			Words:	1		
Before Instruc				Cycles:	1		
1000000000000000000000000000000000000	?			Q Cycle Activity:			
PD =	?			Q1	Q2 Q3 Q4		
After <u>Ins</u> tructi TO =	on 1†			Decode	Read Process Write to		
<u>10</u> = PD =	0				register 'f' Data destinatio		
				Example 1:	SUBFWB REG, 1, 0		
† If WDT causes wake-up, this bit is cleared.				Before Instru REG			
				W	= 2		
				C After Instruc	= 1		
				REG	= FF		
				W	= 2 = 0		
				C Z	= 0		
				N Example 2:	= 1 ; result is negative		
				Example 2: Before Instru	SUBFWB REG, 0, 0		
				REG	= 2		
				W C	= 5 = 1		
				After Instruc	•		
				REG W	= 2 = 3		
				С	= 1		
				Z N	= 0 = 0 ; result is positive		
				Example 3:	SUBFWB REG, 1, 0		
				Defense heete			

Before Instruction REG = W = C =

After Instruction

REG W C Z N = 1 = 2 = 0

= 0 = 2 = 1 = 1 = 0

; result is zero

SUBLW Subtract W from Literal							
Syntax:	5	SUBLW	ł	<			
Operands:	(	$0 \le k \le 2$	25	5			
Operation:	ŀ	(W) – x	$\rightarrow$	W			
Status Affected:	1	N, OV, (	С,	DC, Z			
Encoding:		0000		1000	kk}	сk	kkkk
Description:				acted from		•	
Words:		1					
Cycles:		1					
Q Cycle Activity:							
Q1							Q4
Decode		Read Process teral 'k' Data				V	Vrite to W
Example 1:		SUBLW	(	)2h			
Before Instruction							
W	=	01h					
C After Instructio	= nn	?					
W	=	01h					
C Z	=	1 0	;	result is p	ositiv	/e	
Ñ	=	Õ					
Example 2:	5	SUBLW	(	)2h			
Before Instruc							
W C	=	02h ?					
After Instruction	on	-					
W C	=	00h 1		result is z	zero		
Z	=	1	,				
N Example 3:	=	0 SUBLW	C	)2h			
Before Instruc		JODIN		,211			
W	=	03h					
C After Instructio	=	?					
W	=	FFh	:	(2's com	pleme	ent)	
C Z	=	0		result is r			
N N	=	1					

SUBWF	Subtrac	t W	from f		
Syntax:	SUBWF	f	{,d {,a}}		
Operands:	$0 \le f \le 2$	55			
	d ∈ [0,1 a ∈ [0,1	•			
Operation:	(f) – (W	$\rightarrow$ 0	dest		
Status Affected:	N, OV, (	), D(	C, Z		
Encoding:	0101		11da fff	f ffff	
Description:		t W f	rom register 'f'		
	compler result is	nent store	method). If 'd' ed in W. If 'd' is ck in register 'f'	is '0', the '1', the result	
		⊥', <b>th</b>	e Access Bank e BSR is used default).		
	If 'a' is '0' and the extended instruction set is enabled, this instruction operates in Indexed Literal Offset Addressing mode whenever $f \le 95$ (5Fh). See Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed Literal Offset Mode" for details.				
Words:	1				
Cycles:	1				
Q Cycle Activity:					
Q1	Q2		Q3	Q4	
Decode	Read		Process	Write to	
	register	ʻf'	Data	destination	
Example 1:	SUBW	F	REG, 1, 0		
Before Instruc					
REG W	= 3 = 2 = ?				
С					
After Instructio	n = 1				
W	= 2				
C Z	= 1 = 0	; I	result is positiv	e	
Ň	= 0				
Example 2:	SUBW	F	REG, 0, 0		
Before Instruc	tion				
REG W	= 2 = 2				
C	= ?				
After Instructio					
REG W	= 2 = 0				
С	= 1	; I	result is zero		
Z N	= 1 = 0				
Example 3:	SUBW	F	REG, 1, 0		
Before Instruct	tion				
REG W C	= 1 = 2 = ?				
After Instructio	-				
REG	= FF	h ;(	2's complemer	nt)	
W C	= 2 = 0	: 1	result is negativ	/e	
Z N	= 0 = 1	, .			

SUBWFB	Subtract	W from f v	with Borr	ow		
Syntax:	SUBWFB	f {,d {,a}	}			
Operands:	$0 \le f \le 25$	5				
	d ∈ [0,1]					
	a ∈ [0,1]	_				
Operation:		$(\overline{C}) \rightarrow des$	st			
Status Affected:	N, OV, C,	DC, Z		<u> </u>		
Encoding:	0101	10da	ffff	ffff		
Description:	from regis method). I in W. If 'd'	V and the ter 'f' (2's o f 'd' is '0', is '1', the r 'f' (default	compleme the result result is st	ent is stored		
	lf 'a' is '1', GPR bank	,	s used to	select the		
	If 'a' is '0' and the extended instruction set is enabled, this instruction operates in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed Literal Offset Mode" for details.					
Words:	1					
Cycles:	1					
Q Cycle Activity:						
Q1	Q2	Q3	3	Q4		
Decode	Read	Proce	ess \	Write to		
	register 'f'	Data	a de	estination		
Example 1:	SUBWFB	REG, 1	, 0			
Before Instruct						
REG W	= 19h = 0Dh	(000)				
С	= 1	·	,			
After Instructio REG	n = 0Ch	(000)	0 1011)			
W	= 00h		$0 1011) \\ 0 1101)$			
C Z	= 1 = 0					
N	= 0	; resu	lt is positi	ve		
Example 2:	SUBWFB	REG, 0	, 0			
Before Instruct	tion					
REG W C	= 1Bh = 1Ah = 0	(000) (000)	1 1011) 1 1010)			
After Instructio REG W	n = 1Bh = 00h	(000)	1 1011)			
С	= 1		14 :			
Z N	= 1 = 0	; resu	lt is zero			
Example 3:	SUBWFB	REG, 1	, 0			
Before Instruct	tion					
REG W C	= 03h = 0Eh = 1		0 0011) 0 1101)			
After Instructio REG	n = F5h	(111); ; <b>[2's (</b>	1 0100) comp]			
W C	= 0Eh = 0		0 1101)			
Z N	= 0 = 0 = 1	; resu	lt is negat	ive		

SWAPF	Swap f						
Syntax:	SWAPF f	[,d {,a}}					
Operands:	$0 \le f \le 255$ $d \in [0,1]$ $a \in [0,1]$	d ∈ [0,1]					
Operation:	$(f<3:0>) \rightarrow$ $(f<7:4>) \rightarrow$						
Status Affected:	None						
Encoding:	0011	0011 10da ffff ffff					
Description:	The upper and lower nibbles of regis 'f' are exchanged. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed in register 'f' (default).						
	If 'a' is '0', the Access Bank is selected. If 'a' is '1', the BSR is used to select the GPR bank (default).						
	If 'a' is '0' a set is enabl in Indexed I mode when Section 25 Bit-Oriente Literal Offs	ed, this in _iteral Of ever f ≤ 9 .2.3 "Byt d Instrue	nstructio fset Add 95 (5Fh) te-Orien ctions in	n operates ressing . See ted and n Indexed			
	1						
Words:							
Words: Cycles:	1						
	1						
Cycles:	1 Q2	Q3		Q4			
Cycles: Q Cycle Activity:		Q3 Proce Data	ss	Q4 Write to estination			

Table Read (Continued)

TBL	RD	Table Read						
Synta	ax:	TBLRD (*;	TBLRD ( *; *+; *-; +*)					
Oper	ands:	None						
Oper	ation:	if TBLRD*, (Prog Mem (TBLPTR)) $\rightarrow$ TABLAT; TBLPTR – No Change if TBLRD*+, (Prog Mem (TBLPTR)) $\rightarrow$ TABLAT; (TBLPTR) + 1 $\rightarrow$ TBLPTR if TBLRD*-, (Prog Mem (TBLPTR)) $\rightarrow$ TABLAT; (TBLPTR) – 1 $\rightarrow$ TBLPTR if TBLRD +*, (TBLPTR) + 1 $\rightarrow$ TBLPTR; (Prog Mem (TBLPTR)) $\rightarrow$ TABLAT						
Statu	s Affected:	None						
Enco	ding:	0000	01	000	000	00	10nn nn=0 * =1 *+ =2 *- =3 +*	
Desc	ription:	This instruction is used to read the contents of Program Memory (P.M.). To address the program memory, a pointer called Table Pointer (TBLPTR) is used. The TBLPTR (a 21-bit pointer) points to each byte in the program memory. TBLPTR						
		has a 2-Mby						
		TBLPTR	)] = (				nt Byte of ory Word	
		TBLPTR[(	)] = 1				t Byte of bry Word	
		The TBLRD of TBLPTR				nodify	the value	
		no chang	е					
		<ul> <li>post-incre</li> </ul>	emei	nt				
		<ul> <li>post-decr</li> </ul>	eme	ent				
		<ul> <li>pre-increi</li> </ul>	men	t				
Word	s:	1						
Cycle	es:	2						
QC	ycle Activity:							
	Q1	Q2		C	13		Q4	
	Decode	No operation		N opera	-	op	No peration	

#### TBLRD \*+ ; Example 1: Before Instruction TABLAT TBLPTR MEMORY(00A356h) 55h 00A356h = = 34h After Instruction

TBLRD

TABLAT TBLPTR			= =	34h 00A357h
Example 2:	TBLRD	+*	;	
Before Instruction TABLAT TBLPTR MEMORY( MEMORY( After Instruction	01A357h	)	= = =	AAh 01A357h 12h 34h
TABLAT TBLPTR			= =	34h 01A358h

© 2007 Microchip Technology Inc.

No

operation

No operation

(Read Program

Memory)

No

operation

No operation

(Write

TABLAT)

Description: This instruction uses the 3 LSBs of TBLPTR to determine which of the 8 holding registers the TABLAT is without to. The holding registers are used to program the contents of Program Mericon (P.M.). (Refer to Section 5.0 "Mericon Organization" for additional details programming Flash memory.) The TBLPTR (a 21-bit pointer) pointe each byte in the program memory. TBLPTR has a 2-Mbyte address ran The LSb of the TBLPTR selects while byte of the program memory location access. TBLPTR[0] = 0: Least Significant Word TBLPTR[0] = 1: Most Significant	*+ *- +*					
Operation:if TBLWT*, (TABLAT) $\rightarrow$ Holding Register; TBLPTR – No Change if TBLWT*+, (TABLAT) $\rightarrow$ Holding Register; (TBLPTR) + 1 $\rightarrow$ TBLPTR if TBLWT*-, (TABLAT) $\rightarrow$ Holding Register; (TBLPTR) - 1 $\rightarrow$ TBLPTR; if TBLWT+*, (TBLPTR) + 1 $\rightarrow$ TBLPTR; (TABLAT) $\rightarrow$ Holding RegisterStatus Affected:NoneEncoding: $0000 \ 0000 \ 0000 \ 11$ mn=0 =1 =2 =3Description:This instruction uses the 3 LSBs of TBLPTR to determine which of the 8 holding registers are used to program the contents of Program Med (P.M.). (Refer to Section 5.0 "Memodor Organization" for additional details programming Flash memory.)The TBLPTR (a 21-bit pointer) point each byte in the program memory. TBLPTR has a 2-Mbyte address ran The LSb of the TBLPTR selects while byte of the program memory location access.TBLPTR[0] = 0:Least Significant of Program Mem WordTBLPTR[0] = 1:Most Significant of Program Mem WordThe TBLWT instruction can modify t value of TBLPTR as follows: • no change	* *+ *- +*					
TABLAT) → Holding Register; TBLPTR – No Change if TBLWT*+, (TABLAT) → Holding Register; (TBLPTR) + 1 → TBLPTR if TBLWT*-, (TABLAT) → Holding Register; (TBLPTR) = 1 → TBLPTR if TBLWT*, (TBLPTR) + 1 → TBLPTR; 	* *+ *- +*					
if TBLWT*-, (TABLAT) → Holding Register; (TBLPTR) = 1 → TBLPTR if TBLWT+*, (TBLPTR) + 1 → TBLPTR; (TABLAT) → Holding RegisterStatus Affected:NoneEncoding:0000 0000 0000 11 nn=0 =1 =2 =3Description:This instruction uses the 3 LSBs of 	* *+ *- +*					
if TBLWT+*, (TBLPTR) + 1 → TBLPTR; (TABLAT) → Holding RegisterStatus Affected:NoneEncoding: $0000$ $0000$ $0000$ $11$ nn=0 =1 =2 =3Description:This instruction uses the 3 LSBs of TBLPTR to determine which of the 8 holding registers the TABLAT is with to. The holding registers are used to 	* *+ *- +*					
(TABLAT) → Holding Register         Status Affected:         Encoding:         0000       0000         0000       0000         1         nn=0         =1         =2         =3         Description:       This instruction uses the 3 LSBs of TBLPTR to determine which of the 8 holding registers the TABLAT is wit to. The holding registers are used to program the contents of Program Men (P.M.). (Refer to Section 5.0 "Memo Organization" for additional details programming Flash memory.)         The TBLPTR (a 21-bit pointer) point each byte in the program memory.         TBLPTR has a 2-Mbyte address ran The LSb of the TBLPTR selects while byte of the program memory location access.         TBLPTR[0] = 0:       Least Significant of Program Men Word         TBLPTR[0] = 1:       Most Significant of Program Men Word         The TBLWT instruction can modify t value of TBLPTR as follows:         • no change	* *+ *- +*					
Encoding:00000000000011nn=0=1=2=3Description:This instruction uses the 3 LSBs of TBLPTR to determine which of the 8 holding registers the TABLAT is with to. The holding registers are used to program the contents of Program Med (P.M.). (Refer to Section 5.0 "Memodorganization" for additional details programming Flash memory.)The TBLPTR (a 21-bit pointer) point each byte in the program memory. TBLPTR has a 2-Mbyte address ran The LSb of the TBLPTR selects while byte of the program memory location access.TBLPTR[0] = 0:Least Significant of Program Men WordTBLPTR[0] = 1:Most Significant of Program Men WordThe TBLWT instruction can modify t value of TBLPTR as follows: • no change	* *+ *- +*					
Description:       This instruction uses the 3 LSBs of TBLPTR to determine which of the 8 holding registers the TABLAT is with to. The holding registers are used to program the contents of Program Med (P.M.). (Refer to Section 5.0 "Memodorganization" for additional details programming Flash memory.)         The TBLPTR (a 21-bit pointer) point each byte in the program memory.         TBLPTR has a 2-Mbyte address ram The LSb of the TBLPTR selects while byte of the program memory location access.         TBLPTR[0] = 0:       Least Significant of Program Memodord         TBLPTR[0] = 1:       Most Significant of Program Memodord         The TBLWT instruction can modify to value of TBLPTR as follows:       • no change	* *+ *- +*					
TBLPTR to determine which of the 8 holding registers the TABLAT is with to. The holding registers are used to program the contents of Program Med (P.M.). (Refer to Section 5.0 "Memodorganization" for additional details programming Flash memory.)The TBLPTR (a 21-bit pointer) point each byte in the program memory.TBLPTR has a 2-Mbyte address rand The LSb of the TBLPTR selects white byte of the program memory location access.TBLPTR[0] = 0: Least Significant of Program MemodordTBLPTR[0] = 1: Most Significant of Program MemodordThe TBLWT instruction can modify to value of TBLPTR as follows:• no change	emory D <b>ry</b>					
each byte in the program memory. TBLPTR has a 2-Mbyte address ran The LSb of the TBLPTR selects whi byte of the program memory location access. TBLPTR[0] = 0: Least Significan of Program Men Word TBLPTR[0] = 1: Most Significant of Program Men Word The TBLWT instruction can modify t value of TBLPTR as follows: • no change						
of Program Men Word TBLPTR[0] = 1: Most Significant of Program Men Word The TBLWT instruction can modify t value of TBLPTR as follows: • no change	TBLPTR has a 2-Mbyte address range. The LSb of the TBLPTR selects which byte of the program memory location to					
of Program Men Word The TBLWT instruction can modify t value of TBLPTR as follows: • no change	TBLPTR[0] = 0: Least Significant Byte of Program Memory Word					
value of TBLPTR as follows: <ul> <li>no change</li> </ul>	of Program Memory					
5	ne					
<ul> <li>post-increment</li> </ul>						
<ul> <li>post-decrement</li> </ul>						
pre-increment						
Words: 1						
Cycles: 2						
Q Cycle Activity:						
Q1 Q2 Q3 Q						
Decode No No N operation operation	4					
NoNoNoNoperationoperationoperationoperation(Read(WriTABLAT)HoldRegi	0					

#### TBLWT Table Write (Continued)

Example 1: TBLWT*+;		
Before Instruction		
TABLAT TBLPTR HOLDING REGISTER	= =	55h 00A356h
(00A356h)	=	FFh
After Instructions (table write	comp	letion)
TABLAT	=	55h
TBLPTR HOLDING REGISTER	=	00A357h
(00A356h)	=	55h
Example 2: TBLWT +*;		
Before Instruction		
TABLAT	=	34h
TBLPTR HOLDING REGISTER	=	01389Ah
(01389Ah) HOLDING REGISTER	=	FFh
(01389Bh)	=	FFh
After Instruction (table write c	omple	etion)
TABLAT	=	34h
TBLPTR HOLDING REGISTER	=	01389Bh
(01389Ah) HOLDING REGISTER	=	FFh
(01389Bh)	=	34h

TST	-sz	Test f, Skip	o if O			
Synta	ax:	TSTFSZ f {	,a}			
Oper	ands:	0 ≤ f ≤ 255 a ∈ [0,1]				
Oper	ation:	skip if f = 0				
Statu	s Affected:	None				
Enco	oding:	0110	011a fff	f fff		
Desc	ription:	during the c is discarded	If 'f' = 0, the next instruction fetched during the current instruction execution is discarded and a NOP is executed, making this a two-cycle instruction.			
		lf 'a' is '1', tl	If 'a' is '0', the Access Bank is selected. If 'a' is '1', the BSR is used to select the GPR bank (default).			
If 'a' is '0' and the extended instruction set is enabled, this instruction operates in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed Literal Offset Mode" for details.						
Word	ls:	1				
Cycles: 1(2) Note: 3 cycles if skip and followed by a 2-word instruction.						
QC	ycle Activity: Q1	Q2	Q3	Q4		
	Decode	Read	Process	No		
		register 'f'	Data	operation		
lf sk	ip:					
	Q1	Q2	Q3	Q4		
	No operation	No operation	No operation	No operation		
lf sk	ip and followed	1		operation		
	Q1	Q2	Q3	Q4		
	No	No	No	No		
	operation	operation	operation	operation		
	No operation	No operation	No operation	No operation		
Example: HERE TSTFSZ CNT, 1 NZERO : ZERO :						
	Before Instruc PC	= Ad	dress (HERE)	1		
	After Instruction If CNT PC	= 00 = Ad	dress (ZERO)	•		
	If CNT PC	≠ 00 = Ad	h, dress (NZERO	))		

XORLW Exclusive OR Literal with W							
Synt	ax:	XORLW	XORLW k				
Oper	ands:	$0 \le k \le 25$	$0 \le k \le 255$				
Oper	ation:	(W) .XOF	$k \to W$				
Statu	is Affected:	N, Z					
Enco	oding:	0000	1010	010 kkkk k			
Desc	cription:	The conte the 8-bit I in W.					
Word	ds:	1					
Cycle	es:	1					
QC	ycle Activity:						
	Q1	Q2	Q3		Q4		
	Decode	Read	Process		Vrite to		
		literal 'k'	Data	à	W		
<u>Exar</u>	<u>nple:</u>	XORLW	0AFh				
	Before Instruc W After Instructio	= B5h					

VV =

1Ah

XORWF	Exclusive	OR W with f				
Syntax:	XORWF	f {,d {,a}}				
Operands:	$\begin{array}{l} 0 \leq f \leq 255 \\ d  \in  [0,1] \\ a  \in  [0,1] \end{array}$	d ∈ [0,1]				
Operation:	(W) .XOR.	(f) $\rightarrow$ dest				
Status Affected:	N, Z	N, Z				
Encoding:	0001	10da ffi	ff ffff			
Description:	register 'f'. I in W. If 'd' is	Exclusive OR the contents of W with register 'f'. If 'd' is '0', the result is stored in W. If 'd' is '1', the result is stored back in the register 'f' (default).				
If 'a' is '0', the Access Bank is se If 'a' is '1', the BSR is used to sel GPR bank (default).						
	If 'a' is '0' and the extended instruction set is enabled, this instruction opera in Indexed Literal Offset Addressing mode whenever f ≤ 95 (5Fh). See Section 25.2.3 "Byte-Oriented and Bit-Oriented Instructions in Indexed Literal Offset Mode" for details.					
Words:	1					
Cycles:	1					
Q Cycle Activity:						
Q1	Q2	Q3	Q4			
Decode	Read register 'f'	Process Data	Write to destination			
Example:	XORWF 1	REG, 1, 0				
Before Instruct	tion					
REG W	= AFh = B5h					
After Instructio REG W	n = 1Ah = B5h					

## 25.2 Extended Instruction Set

In addition to the standard 75 instructions of the PIC18 instruction set, the PIC18F97J60 family of devices also provide an optional extension to the core CPU functionality. The added features include eight additional instructions that augment Indirect and Indexed Addressing operations and the implementation of Indexed Literal Offset Addressing for many of the standard PIC18 instructions.

The additional features of the extended instruction set are enabled by default on unprogrammed devices. Users must properly set or clear the XINST Configuration bit during programming to enable or disable these features.

The instructions in the extended set can all be classified as literal operations, which either manipulate the File Select Registers, or use them for Indexed Addressing. Two of the instructions, ADDFSR and SUBFSR, each have an additional special instantiation for using FSR2. These versions (ADDULNK and SUBULNK) allow for automatic return after execution.

The extended instructions are specifically implemented to optimize reentrant program code (that is, code that is recursive or that uses a software stack) written in high-level languages, particularly C. Among other things, they allow users working in high-level languages to perform certain operations on data structures more efficiently. These include:

- Dynamic allocation and deallocation of software stack space when entering and leaving subroutines
- Function Pointer invocation
- Software Stack Pointer manipulation
- Manipulation of variables located in a software stack

A summary of the instructions in the extended instruction set is provided in Table 25-3. Detailed descriptions are provided in **Section 25.2.2 "Extended Instruction Set"**. The opcode field descriptions in Table 25-1 (page 360) apply to both the standard and extended PIC18 instruction sets.

Note: The instruction set extension and the Indexed Literal Offset Addressing mode were designed for optimizing applications written in C; the user may likely never use these instructions directly in assembler. The syntax for these commands is provided as a reference for users who may be reviewing code that has been generated by a compiler.

## 25.2.1 EXTENDED INSTRUCTION SYNTAX

Most of the extended instructions use indexed arguments, using one of the File Select Registers and some offset to specify a source or destination register. When an argument for an instruction serves as part of Indexed Addressing, it is enclosed in square brackets ("[]"). This is done to indicate that the argument is used as an index or offset. The MPASM<sup>™</sup> Assembler will flag an error if it determines that an index or offset value is not bracketed.

When the extended instruction set is enabled, brackets are also used to indicate index arguments in byte-oriented and bit-oriented instructions. This is in addition to other changes in their syntax. For more details, see Section 25.2.3.1 "Extended Instruction Syntax with Standard PIC18 Commands".

Note: In the past, square brackets have been used to denote optional arguments in the PIC18 and earlier instruction sets. In this text and going forward, optional arguments are denoted by braces ("{ }").

Mnemonic, Operands		Description	Cycles 16-Bit Instruction Word			/ord	Status	
		Description	MSb				Affected	
ADDFSR	f, k	Add literal to FSR	1	1110	1000	ffkk	kkkk	None
ADDULNK	k	Add literal to FSR2 and return	2	1110	1000	11kk	kkkk	None
CALLW		Call subroutine using WREG	2	0000	0000	0001	0100	None
MOVSF	z <sub>s</sub> , f <sub>d</sub>	Move z <sub>s</sub> (source) to 1st word	2	1110	1011	0 z z z	ZZZZ	None
		f <sub>d</sub> (destination) 2nd word		1111	ffff	ffff	ffff	
MOVSS	z <sub>s</sub> , z <sub>d</sub>	Move z <sub>s</sub> (source) to 1st word	2	1110	1011	1zzz	ZZZZ	None
		z <sub>d</sub> (destination) 2nd word		1111	XXXX	XZZZ	ZZZZ	
PUSHL	k	Store literal at FSR2,	1	1110	1010	kkkk	kkkk	None
		decrement FSR2						
SUBFSR	f, k	Subtract literal from FSR	1	1110	1001	ffkk	kkkk	None
SUBULNK	k	Subtract literal from FSR2 and	2	1110	1001	11kk	kkkk	None
		return						

### TABLE 25-3: EXTENSIONS TO THE PIC18 INSTRUCTION SET

## 25.2.2 EXTENDED INSTRUCTION SET

ADD	FSR	Add Liter	Add Literal to FSR				
Synta	ax:	ADDFSR	ADDFSR f, k				
Operands:		$0 \le k \le 63$	$0 \le k \le 63$				
		$f \in [0, 1,$	2]				
Oper	ation:	FSR(f) + I	$s \rightarrow FSR($	f)			
Statu	s Affected:	None					
Enco	ding:	1110	1000	ffkk	kkkk		
Desc	ription:	The 6-bit	The 6-bit literal 'k' is added to the				
		contents of	contents of the FSR specified by 'f'.				
Word	ls:	1					
Cycle	es:	1					
Q Cycle Activity:							
	Q1	Q2	Q3		Q4		
	Decode	Read	Proces	ss V	Vrite to		
		literal 'k'	Data		FSR		

Example:

ADDFSR 2, 23h

Before Instruction				
FSR2	=	03FFh		
After Instruct	ion			
FSR2	=	0422h		

ADD	ULNK	Add Liter	al to FSR2	and R	eturn	
Synta	ax:	ADDULN	K k			
Oper	ands:	$0 \le k \le 63$				
Oper	ation:	FSR2 + k	$\rightarrow$ FSR2,			
		$(TOS) \rightarrow I$	$(TOS) \rightarrow PC$			
Status Affected:		None	None			
Enco	oding:	1110	1000 1	1kk	kkkk	
Description: The 6-bit literal 'k' is added to th contents of FSR2. A RETURN is the executed by loading the PC with TOS.			is then			
			ction takes NOP is per d cycle.			
		case of the	be thought of e ADDFSR in 3 (binary '1 SR2.	nstructi	on,	
Word	ls:	1				
Cycle	es:	2				
QC	ycle Activity:					
	Q1	Q2	Q3		Q4	
	Decode	Read literal 'k'	Process Data	V	Vrite to FSR	
	No	No	No		No	
	Operation	Operation	Operation	n Op	peration	
<u>Exan</u>	nple:	ADDULNK 2	23h			

<u>xample:</u>	ADI	DDULNK	
Before Instruction	on		
FSR2 :	=	03FFh	
PC :	=	0100h	
After Instruction	1		
FSR2 :	=	0422h	
PC :	=	(TOS)	

**Note:** All PIC18 instructions may take an optional label argument preceding the instruction mnemonic for use in symbolic addressing. If a label is used, the instruction format then becomes: {label} instruction argument(s).

CAL	LW	Subroutine	e Call using W	/REG			
Synta	ax:	CALLW					
Oper	ands:	None					
Operation:		(W) → PCL (PCLATH) -	$(PC + 2) \rightarrow TOS,$ $(W) \rightarrow PCL,$ $(PCLATH) \rightarrow PCH,$ $(PCLATU) \rightarrow PCU$				
Status Affected:		None	None				
Enco	oding:	0000	0000 000	01 0100			
Description		pushed ont contents of existing val contents of latched into respectively executed as	First, the return address (PC + 2) is pushed onto the return stack. Next, the contents of W are written to PCL; the existing value is discarded. Then, the contents of PCLATH and PCLATU are latched into PCH and PCU, respectively. The second cycle is executed as a NOP instruction while the new next instruction is fetched.				
			Unlike CALL, there is no option to update W, STATUS or BSR.				
Word	ls:	1					
Cycle	es:	2					
QC	ycle Activity:						
	Q1	Q2	Q3	Q4			
	Decode	Read WREG	Push PC to stack	No operation			
	No operation	No operation	No operation	No operation			
Example: Before Instruction		HERE tion	CALLW				
	PC PCLATH PCLATU W After Instructic PC TOS PCLATH PCLATU W	= 00h = 06h on = 001006 = address = 10h	h	)			

		<b>.</b>					
MOV		Move Inde					
Synta			ːs], f <sub>d</sub>				
Operands:		$0 \le z_s \le 127$ $0 \le f_d \le 409$					
Oper	ation:	((FSR2) + z	$f_{s}) \rightarrow f_{d}$				
Status Affected:		None					
Encoding: 1st word (source) 2nd word (destin.)		1110 1111		zzz zzzz <sub>s</sub> Eff ffff <sub>d</sub>			
Desc	ription:	The conten	ts of the sour	ce register are			
		actual addr determined offset 'z <sub>s</sub> ', in of FSR2. Th register is s 'f <sub>d</sub> ' in the se	ess of the so by adding th in the first wor he address of pecified by the cond word. Events where in the	gister 'f <sub>d</sub> '. The urce register is e 7-bit literal 'd, to the value the destination the 12-bit literal Both addresses 4096-byte data			
		PCL, TOSL	The MOVSF instruction cannot use the PCL, TOSU, TOSH or TOSL as the destination register.				
			If the resultant source address points to				
			an indirect addressing register, the				
10/000	l		value returned will be 00h.				
Word		2					
Cycle		2					
QC	ycle Activity:	02	02	04			
	Q1 Decode	Q2 Determine	Q3 Determine	Q4 Read			
	Decoue	source addr	source addr				
	Decode	No	No	Write			
		operation	operation	register 'f'			
		No dummy		(dest)			
		read					
Exan	nple:	MOVSF	[05h], REG	2			
	Before Instruc						
	FSR2 Contents	= 80 = 33					
of 85h REG2 After Instruction		= 11					
	FSR2 Contents	= 80	h				
	of 85h REG2	= 33 = 33					

MOVSS	Move Indexed to Indexed				
Syntax:	MOVSS [z <sub>s</sub> ], [z <sub>d</sub> ]				
Operands:	$\begin{array}{l} 0 \leq z_s \leq 127 \\ 0 \leq z_d \leq 127 \end{array}$				
Operation:	$((FSR2) + z_s) \to ((FSR2) + z_d)$				
Status Affected:	None				
Encoding: 1st word (source) 2nd word (dest.)	1110 1011 1zzz zzzz <sub>s</sub> 1111 xxxx xzzz zzzz <sub>d</sub>				
Description	The contents of the source register are moved to the destination register. The addresses of the source and destination registers are determined by adding the 7-bit literal offsets ' $z_s$ ' or ' $z_d$ ', respectively, to the value of FSR2. Both registers can be located anywhere in the 4096-byte data memory space (000h to FFFh). The MOVSS instruction cannot use the PCL, TOSU, TOSH or TOSL as the destination register.				
	If the resultant source address points to an indirect addressing register, the value returned will be 00h. If the resultant destination address points to an indirect addressing register, the instruction will execute as a NOP.				
Words:	2				
Cycles:	2				
Q Cycle Activity:					

Q1	Q2	Q3	Q4
Decode	Determine	Determine	Read
	source addr	source addr	source reg
Decode	Determine	Determine	Write
	dest addr	dest addr	to dest reg

Before Instruction		
FSR2	=	80h
Contents of 85h Contents	=	33h
of 86h	=	11h
After Instruction		
FSR2	=	80h
Contents of 85h Contents	=	33h
of 86h	=	33h

PUSHL		Store Liter	ai al FSR	z, Dech	ement FSR2
Syntax:		PUSHL k			
Operands	:	$0 \leq k \leq 255$			
Operation	:	$k \rightarrow (FSR2),$ FSR2 – 1 $\rightarrow$ FSR2			
Status Affe	ected:	None			
Encoding:	:	1111	1010	kkk}	k kkkk
		memory ad	uicoo obt	շմութն ե	
		FSR2 is de operation. This instruc	cremente	d by 1 a /s users	after the s to push
Words:		FSR2 is de operation. This instructivalues onto	cremente	d by 1 a /s users	after the s to push
Words:		FSR2 is de operation. This instruc	cremente	d by 1 a /s users	after the s to push
Cycles:	Activity:	FSR2 is de operation. This instructivalues onto 1	cremente	d by 1 a /s users	after the s to push
	Activity: Q1	FSR2 is de operation. This instructivalues onto 1	cremente tion allow a softwa	d by 1 a /s users	after the s to push

Before Instruction FSR2H:FSR2L Memory (01ECh)	= =	01ECh 00h
After Instruction FSR2H:FSR2L Memory (01ECh)	= =	01EBh 08h

SUBULNK k

 $FSR2 - k \rightarrow FSR2$ ,

 $0 \leq k \leq 63$ 

Subtract Literal from FSR2 and Return

SUBFSR	Subtract	Subtract Literal from FSR						
Syntax:	SUBFSR	SUBFSR f, k						
Operands:	$0 \le k \le 63$	$0 \le k \le 63$						
	f ∈ [ 0, 1, 2	2]						
Operation:	FSRf – k -	→ FSRf						
Status Affected:	None	None						
Encoding:	1110	1001	ffkk	kkkk				
Description:		The 6-bit literal 'k' is subtracted from the contents of the FSR specified by 'f'						
Words:	1							
Cycles:	1							
Q Cycle Activity:								
Q1	Q2	Q3		Q4				
Decode	Read register 'f'							
Example: Before Instruc	SUBFSR 2	2, 23h	I					

03FFh

03DCh

FSR2

After Instruction FSR2

=

=

	opo.		$(TOS) \rightarrow PC$					
	Statu	s Affected:	None					
	Enco	ding:	1110	1001	11kk	kkkk		
1	Desc	ription:	contents of		2. A ret	ed from the URN is then with the		
				•	,	les to during the		
n			of the SUE	be thought BESR instru 1'); it opera	iction, wh			
	Word	s:	1					
	Cycle	es:	2					
	QC	ycle Activity:						
		Q1	Q2		Q3	Q4		
		Decode	Read register		ocess ata	Write to destination		
		No Operation	No Operati		No	No Operation		
		Operation	Operation	Ji j Ope	ration	Operation		

Example: SUBULNK 23h

SUBULNK

Operands:

Operation:

Syntax:

Before Instru	ction	
FSR2	=	03FFh
PC	=	0100h
After Instruct	ion	
FSR2	=	03DCh
PC	=	(TOS)

© 2007 Microchip Technology Inc.

#### 25.2.3 BYTE-ORIENTED AND BIT-ORIENTED INSTRUCTIONS IN INDEXED LITERAL OFFSET MODE

Note:	Enabling the PIC18 instruction set exten-
	sion may cause legacy applications to
	behave erratically or fail entirely.

In addition to eight new commands in the extended set, enabling the extended instruction set also enables Indexed Literal Offset Addressing (Section 5.6.1 "Indexed Addressing with Literal Offset"). This has a significant impact on the way that many commands of the standard PIC18 instruction set are interpreted.

When the extended set is disabled, addresses embedded in opcodes are treated as literal memory locations: either as a location in the Access Bank (a = 0) or in a GPR bank designated by the BSR (a = 1). When the extended instruction set is enabled and a = 0, however, a file register argument of 5Fh or less is interpreted as an offset from the pointer value in FSR2 and not as a literal address. For practical purposes, this means that all instructions that use the Access RAM bit as an argument – that is, all byte-oriented and bit-oriented instructions, or almost half of the core PIC18 instructions – may behave differently when the extended instruction set is enabled.

When the content of FSR2 is 00h, the boundaries of the Access RAM are essentially remapped to their original values. This may be useful in creating backward-compatible code. If this technique is used, it may be necessary to save the value of FSR2 and restore it when moving back and forth between C and assembly routines in order to preserve the Stack Pointer. Users must also keep in mind the syntax requirements of the extended instruction set (see Section 25.2.3.1 "Extended Instruction Syntax with Standard PIC18 Commands").

Although the Indexed Literal Offset mode can be very useful for dynamic stack and pointer manipulation, it can also be very annoying if a simple arithmetic operation is carried out on the wrong register. Users who are accustomed to the PIC18 programming must keep in mind that, when the extended instruction set is enabled, register addresses of 5Fh or less are used for Indexed Literal Offset Addressing.

Representative examples of typical byte-oriented and bit-oriented instructions in the Indexed Literal Offset mode are provided on the following page to show how execution is affected. The operand conditions shown in the examples are applicable to all instructions of these types.

## 25.2.3.1 Extended Instruction Syntax with Standard PIC18 Commands

When the extended instruction set is enabled, the file register argument 'f' in the standard byte-oriented and bit-oriented commands is replaced with the literal offset value 'k'. As already noted, this occurs only when 'f' is less than or equal to 5Fh. When an offset value is used, it must be indicated by square brackets ("[]"). As with the extended instructions, the use of brackets indicates to the compiler that the value is to be interpreted as an index or an offset. Omitting the brackets, or using a value greater than 5Fh within the brackets, will generate an error in the MPASM Assembler.

If the index argument is properly bracketed for Indexed Literal Offset Addressing, the Access RAM argument is never specified; it will automatically be assumed to be '0'. This is in contrast to standard operation (extended instruction set disabled), when 'a' is set on the basis of the target address. Declaring the Access RAM bit in this mode will also generate an error in the MPASM Assembler.

The destination argument 'd' functions as before.

In the latest versions of the MPASM Assembler, language support for the extended instruction set must be explicitly invoked. This is done with either the command line option,  $/_{y}$ , or the PE directive in the source listing.

### 25.2.4 CONSIDERATIONS WHEN ENABLING THE EXTENDED INSTRUCTION SET

It is important to note that the extensions to the instruction set may not be beneficial to all users. In particular, users who are not writing code that uses a software stack may not benefit from using the extensions to the instruction set.

Additionally, the Indexed Literal Offset Addressing mode may create issues with legacy applications written to the PIC18 assembler. This is because instructions in the legacy code may attempt to address registers in the Access Bank below 5Fh. Since these addresses are interpreted as literal offsets to FSR2 when the instruction set extension is enabled, the application may read or write to the wrong data addresses.

When porting an application to the PIC18F97J60 family, it is very important to consider the type of code. A large, reentrant application that is written in C and would benefit from efficient compilation will do well when using the instruction set extensions. Legacy applications that heavily use the Access Bank will most likely not benefit from using the extended instruction set.

ADDWF		/ to Indexed ed Literal Offset mode)				
Syntax:	ADDWF	[k] {,d}				
Operands:	$\begin{array}{l} 0 \leq k \leq 95 \\ d  \in  [0,1] \end{array}$					
Operation:	(W) + ((FSF	R2) + k) →	→ dest			
Status Affected:	N, OV, C, E	DC, Z				
Encoding:	0010	01d0	kkkk	kkkk		
Description:	The content contents of FSR2, offse	the regist	er indica			
	If 'd' is '0', the result is stored in W. I is '1', the result is stored back in register 'f' (default).					
Words:	1					
Cycles:	1					
Q Cycle Activity:						
Q1	Q2	Q3		Q4		
Decode	Read 'k'	Proces Data		/rite to stination		
Example:	ADDWF	[OFST],	0			
Before Instructio W OFST FSR2 Contents of 0A2Ch After Instruction W Contents of 0A2Ch	= = = =	17h 2Ch 0A00h 20h 37h 20h				

BSF	Bit Set Ind (Indexed L	exed iteral Offset	mode)				
Syntax:	BSF [k], b						
Operands:	$\begin{array}{l} 0 \leq f \leq 95 \\ 0 \leq b \leq 7 \end{array}$						
Operation:	$1 \rightarrow ((FSR2))$	$1 \rightarrow ((FSR2) + k) < b >$					
Status Affected:	None						
Encoding:	1000	bbb0 kk	kk kkkk				
Description:		register indic e value 'k', is	ated by FSR2, set.				
Words:	1						
Cycles:	1						
Q Cycle Activity:							
Q1	Q2	Q3	Q4				
Decode	Read register 'f'	Process Data	Write to destination				
Example:	BSF [	FLAG_OFST]	, 7				
Before Instruc FLAG_O FSR2		0Ah 0A00h					
Contents of 0A0Ah		55h					
After Instructio		0011					
Contents of 0A0Ah		D5h					
		2011					
SETF	Set Indexe (Indexed L	d iteral Offset	mode)				
SETF Syntax:			mode)				
-	(Indexed L		mode)				
Syntax:	(Indexed L SETF [k]	iteral Offset	mode)				
Syntax: Operands:	(Indexed L SETF [k] 0 ≤ k ≤ 95	iteral Offset	mode)				
Syntax: Operands: Operation:	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS	iteral Offset SR2) + k)	mode) kk kkkk				
Syntax: Operands: Operation: Status Affected:	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten	<b>3R2) + k)</b>	kk kkkk				
Syntax: Operands: Operation: Status Affected: Encoding:	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten	BR2) + k)	kk kkkk				
Syntax: Operands: Operation: Status Affected: Encoding: Description:	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The contem FSR2, offset	BR2) + k)	kk kkkk				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words:	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offse 1	BR2) + k)	kk kkkk				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles:	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offse 1	BR2) + k)	kk kkkk				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles: Q Cycle Activity:	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offset 1 1	R2) + k) 1000 kk ts of the regisiset by 'k', are s Q3 Process	kk kkkk ter indicated by et to FFh. Q4 Write				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles: Q Cycle Activity: Q1	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offset 1 1 2	R2) + k) 1000 kk ts of the regist t by 'k', are s	kk kkkk ter indicated by et to FFh. Q4				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles: Q Cycle Activity: Q1	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offse 1 1 2 Read 'k'	R2) + k) 1000 kk ts of the regisiset by 'k', are s Q3 Process	kk kkkk ter indicated by et to FFh. Q4 Write				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles: Q Cycle Activity: Q1 Decode Example: Before Instruc	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offse 1 1 2 Read 'k' SETF [	R2) + k) 1000 kk sof the regist of the regist Q3 Process Data OFST]	kk kkkk ter indicated by et to FFh. Q4 Write				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles: Q Cycle Activity: Q1 Decode Example: Before Instruc OFST	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offse 1 1 2 Read 'k' SETF [ tion = 20	R2) + k) 1000 kk s of the regist t by 'k', are s Q3 Process Data OFST] h	kk kkkk ter indicated by et to FFh. Q4 Write				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles: Q Cycle Activity: Q1 Decode Example: Before Instruc OFST FSR2 Contents	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offset 1 1 Q2 Read 'k' SETF [ tion = 2C = 0A	R2) + k) 1000 kk ts of the regist t by 'k', are s Q3 Process Data OFST] h 00h	kk kkkk ter indicated by et to FFh. Q4 Write				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles: Q Cycle Activity: Q1 Decode Example: Before Instruc OFST FSR2 Contents of 0A2Ch	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offset 1 1 2 Read 'k' SETF [ SETF [ = 0A n = 00	R2) + k) 1000 kk ts of the regist t by 'k', are s Q3 Process Data OFST] h 00h	kk kkkk ter indicated by et to FFh. Q4 Write				
Syntax: Operands: Operation: Status Affected: Encoding: Description: Words: Cycles: Q Cycle Activity: Q1 Decode Example: Before Instruc OFST FSR2 Contents	(Indexed L SETF [k] $0 \le k \le 95$ FFh $\rightarrow$ ((FS None 0110 The conten FSR2, offset 1 1 2 Read 'k' SETF [ tion = 2C = 0A n = 00 on	R2) + k) 1000 kk 1000 kk 10	kk kkkk ter indicated by et to FFh. Q4 Write				

## 25.2.5 SPECIAL CONSIDERATIONS WITH MICROCHIP MPLAB<sup>®</sup> IDE TOOLS

The latest versions of Microchip's software tools have been designed to fully support the extended instruction set for the PIC18F97J60 family. This includes the MPLAB C18 C Compiler, MPASM assembly language and MPLAB Integrated Development Environment (IDE).

When selecting a target device for software development, MPLAB IDE will automatically set default Configuration bits for that device. The default setting for the XINST Configuration bit is '0', disabling the extended instruction set and Indexed Literal Offset Addressing. For proper execution of applications developed to take advantage of the extended instruction set, XINST must be set during programming.

To develop software for the extended instruction set, the user must enable support for the instructions and the Indexed Addressing mode in their language tool(s). Depending on the environment being used, this may be done in several ways:

- A menu option or dialog box within the environment that allows the user to configure the language tool and its settings for the project
- A command line option
- · A directive in the source code

These options vary between different compilers, assemblers and development environments. Users are encouraged to review the documentation accompanying their development systems for the appropriate information.

## 26.0 DEVELOPMENT SUPPORT

The PIC<sup>®</sup> microcontrollers are supported with a full range of hardware and software development tools:

- Integrated Development Environment
  - MPLAB® IDE Software
- Assemblers/Compilers/Linkers
  - MPASM<sup>™</sup> Assembler
  - MPLAB C18 and MPLAB C30 C Compilers
  - MPLINK™ Object Linker/
  - MPLIB™ Object Librarian
  - MPLAB ASM30 Assembler/Linker/Library
- Simulators
  - MPLAB SIM Software Simulator
- Emulators
  - MPLAB ICE 2000 In-Circuit Emulator
  - MPLAB REAL ICE™ In-Circuit Emulator
- In-Circuit Debugger
  - MPLAB ICD 2
- Device Programmers
  - PICSTART® Plus Development Programmer
  - MPLAB PM3 Device Programmer
  - PICkit<sup>™</sup> 2 Development Programmer
- Low-Cost Demonstration and Development Boards and Evaluation Kits

## 26.1 MPLAB Integrated Development Environment Software

The MPLAB IDE software brings an ease of software development previously unseen in the 8/16-bit microcontroller market. The MPLAB IDE is a Windows<sup>®</sup> operating system-based application that contains:

- A single graphical interface to all debugging tools
  - Simulator
  - Programmer (sold separately)
  - Emulator (sold separately)
  - In-Circuit Debugger (sold separately)
- · A full-featured editor with color-coded context
- A multiple project manager
- Customizable data windows with direct edit of contents
- · High-level source code debugging
- Visual device initializer for easy register initialization
- · Mouse over variable inspection
- Drag and drop variables from source to watch windows
- · Extensive on-line help
- Integration of select third party tools, such as HI-TECH Software C Compilers and IAR C Compilers

The MPLAB IDE allows you to:

- Edit your source files (either assembly or C)
- One touch assemble (or compile) and download to PIC MCU emulator and simulator tools (automatically updates all project information)
- · Debug using:
  - Source files (assembly or C)
  - Mixed assembly and C
  - Machine code

MPLAB IDE supports multiple debugging tools in a single development paradigm, from the cost-effective simulators, through low-cost in-circuit debuggers, to full-featured emulators. This eliminates the learning curve when upgrading to tools with increased flexibility and power.

## 26.2 MPASM Assembler

The MPASM Assembler is a full-featured, universal macro assembler for all PIC MCUs.

The MPASM Assembler generates relocatable object files for the MPLINK Object Linker, Intel<sup>®</sup> standard HEX files, MAP files to detail memory usage and symbol reference, absolute LST files that contain source lines and generated machine code and COFF files for debugging.

The MPASM Assembler features include:

- Integration into MPLAB IDE projects
- User-defined macros to streamline assembly code
- Conditional assembly for multi-purpose source files
- Directives that allow complete control over the assembly process

### 26.3 MPLAB C18 and MPLAB C30 C Compilers

The MPLAB C18 and MPLAB C30 Code Development Systems are complete ANSI C compilers for Microchip's PIC18 and PIC24 families of microcontrollers and the dsPIC30 and dsPIC33 family of digital signal controllers. These compilers provide powerful integration capabilities, superior code optimization and ease of use not found with other compilers.

For easy source level debugging, the compilers provide symbol information that is optimized to the MPLAB IDE debugger.

## 26.4 MPLINK Object Linker/ MPLIB Object Librarian

The MPLINK Object Linker combines relocatable objects created by the MPASM Assembler and the MPLAB C18 C Compiler. It can link relocatable objects from precompiled libraries, using directives from a linker script.

The MPLIB Object Librarian manages the creation and modification of library files of precompiled code. When a routine from a library is called from a source file, only the modules that contain that routine will be linked in with the application. This allows large libraries to be used efficiently in many different applications.

The object linker/library features include:

- Efficient linking of single libraries instead of many smaller files
- Enhanced code maintainability by grouping related modules together
- Flexible creation of libraries with easy module listing, replacement, deletion and extraction

## 26.5 MPLAB ASM30 Assembler, Linker and Librarian

MPLAB ASM30 Assembler produces relocatable machine code from symbolic assembly language for dsPIC30F devices. MPLAB C30 C Compiler uses the assembler to produce its object file. The assembler generates relocatable object files that can then be archived or linked with other relocatable object files and archives to create an executable file. Notable features of the assembler include:

- Support for the entire dsPIC30F instruction set
- · Support for fixed-point and floating-point data
- · Command line interface
- Rich directive set
- Flexible macro language
- · MPLAB IDE compatibility

## 26.6 MPLAB SIM Software Simulator

The MPLAB SIM Software Simulator allows code development in a PC-hosted environment by simulating the PIC MCUs and dsPIC<sup>®</sup> DSCs on an instruction level. On any given instruction, the data areas can be examined or modified and stimuli can be applied from a comprehensive stimulus controller. Registers can be logged to files for further run-time analysis. The trace buffer and logic analyzer display extend the power of the simulator to record and track program execution, actions on I/O, most peripherals and internal registers.

The MPLAB SIM Software Simulator fully supports symbolic debugging using the MPLAB C18 and MPLAB C30 C Compilers, and the MPASM and MPLAB ASM30 Assemblers. The software simulator offers the flexibility to develop and debug code outside of the hardware laboratory environment, making it an excellent, economical software development tool.

## 26.7 MPLAB ICE 2000 High-Performance In-Circuit Emulator

The MPLAB ICE 2000 In-Circuit Emulator is intended to provide the product development engineer with a complete microcontroller design tool set for PIC microcontrollers. Software control of the MPLAB ICE 2000 In-Circuit Emulator is advanced by the MPLAB Integrated Development Environment, which allows editing, building, downloading and source debugging from a single environment.

The MPLAB ICE 2000 is a full-featured emulator system with enhanced trace, trigger and data monitoring features. Interchangeable processor modules allow the system to be easily reconfigured for emulation of different processors. The architecture of the MPLAB ICE 2000 In-Circuit Emulator allows expansion to support new PIC microcontrollers.

The MPLAB ICE 2000 In-Circuit Emulator system has been designed as a real-time emulation system with advanced features that are typically found on more expensive development tools. The PC platform and Microsoft<sup>®</sup> Windows<sup>®</sup> 32-bit operating system were chosen to best make these features available in a simple, unified application.

## 26.8 MPLAB REAL ICE In-Circuit Emulator System

MPLAB REAL ICE In-Circuit Emulator System is Microchip's next generation high-speed emulator for Microchip Flash DSC and MCU devices. It debugs and programs PIC<sup>®</sup> Flash MCUs and dsPIC<sup>®</sup> Flash DSCs with the easy-to-use, powerful graphical user interface of the MPLAB Integrated Development Environment (IDE), included with each kit.

The MPLAB REAL ICE probe is connected to the design engineer's PC using a high-speed USB 2.0 interface and is connected to the target with either a connector compatible with the popular MPLAB ICD 2 system (RJ11) or with the new high-speed, noise tolerant, Low-Voltage Differential Signal (LVDS) interconnection (CAT5).

MPLAB REAL ICE is field upgradeable through future firmware downloads in MPLAB IDE. In upcoming releases of MPLAB IDE, new devices will be supported, and new features will be added, such as software breakpoints and assembly code trace. MPLAB REAL ICE offers significant advantages over competitive emulators including low-cost, full-speed emulation, real-time variable watches, trace analysis, complex breakpoints, a ruggedized probe interface and long (up to three meters) interconnection cables.

## 26.9 MPLAB ICD 2 In-Circuit Debugger

Microchip's In-Circuit Debugger, MPLAB ICD 2, is a powerful, low-cost, run-time development tool, connecting to the host PC via an RS-232 or high-speed USB interface. This tool is based on the Flash PIC MCUs and can be used to develop for these and other PIC MCUs and dsPIC DSCs. The MPLAB ICD 2 utilizes the in-circuit debugging capability built into the Flash devices. This feature, along with Microchip's In-Circuit Serial Programming<sup>™</sup> (ICSP<sup>™</sup>) protocol, offers costeffective, in-circuit Flash debugging from the graphical user interface of the MPLAB Integrated Development Environment. This enables a designer to develop and debug source code by setting breakpoints, single stepping and watching variables, and CPU status and peripheral registers. Running at full speed enables testing hardware and applications in real time. MPLAB ICD 2 also serves as a development programmer for selected PIC devices.

## 26.10 MPLAB PM3 Device Programmer

The MPLAB PM3 Device Programmer is a universal, CE compliant device programmer with programmable voltage verification at VDDMIN and VDDMAX for maximum reliability. It features a large LCD display (128 x 64) for menus and error messages and a modular, detachable socket assembly to support various package types. The ICSP™ cable assembly is included as a standard item. In Stand-Alone mode, the MPLAB PM3 Device Programmer can read, verify and program PIC devices without a PC connection. It can also set code protection in this mode. The MPLAB PM3 connects to the host PC via an RS-232 or USB cable. The MPLAB PM3 has high-speed communications and optimized algorithms for quick programming of large memory devices and incorporates an SD/MMC card for file storage and secure data applications.

## 26.11 PICSTART Plus Development Programmer

The PICSTART Plus Development Programmer is an easy-to-use, low-cost, prototype programmer. It connects to the PC via a COM (RS-232) port. MPLAB Integrated Development Environment software makes using the programmer simple and efficient. The PICSTART Plus Development Programmer supports most PIC devices in DIP packages up to 40 pins. Larger pin count devices, such as the PIC16C92X and PIC17C76X, may be supported with an adapter socket. The PICSTART Plus Development Programmer is CE compliant.

## 26.12 PICkit 2 Development Programmer

The PICkit<sup>™</sup> 2 Development Programmer is a low-cost programmer and selected Flash device debugger with an easy-to-use interface for programming many of Microchip's baseline, mid-range and PIC18F families of Flash memory microcontrollers. The PICkit 2 Starter Kit includes a prototyping development board, twelve sequential lessons, software and HI-TECH's PICC<sup>™</sup> Lite C compiler, and is designed to help get up to speed quickly using PIC<sup>®</sup> microcontrollers. The kit provides everything needed to program, evaluate and develop applications using Microchip's powerful, mid-range Flash memory family of microcontrollers.

## 26.13 Demonstration, Development and Evaluation Boards

A wide variety of demonstration, development and evaluation boards for various PIC MCUs and dsPIC DSCs allows quick application development on fully functional systems. Most boards include prototyping areas for adding custom circuitry and provide application firmware and source code for examination and modification.

The boards support a variety of features, including LEDs, temperature sensors, switches, speakers, RS-232 interfaces, LCD displays, potentiometers and additional EEPROM memory.

The demonstration and development boards can be used in teaching environments, for prototyping custom circuits and for learning about various microcontroller applications.

In addition to the PICDEM<sup>™</sup> and dsPICDEM<sup>™</sup> demonstration/development board series of circuits, Microchip has a line of evaluation kits and demonstration software for analog filter design, KEELOQ<sup>®</sup> security ICs, CAN, IrDA<sup>®</sup>, PowerSmart battery management, SEEVAL<sup>®</sup> evaluation system, Sigma-Delta ADC, flow rate sensing, plus many more.

Check the Microchip web page (www.microchip.com) for the complete list of demonstration, development and evaluation kits.

## 27.0 ELECTRICAL CHARACTERISTICS

## Absolute Maximum Ratings<sup>(†)</sup>

Ambient temperature under bias	40°C to +100°C
Storage temperature	65°C to +150°C
Voltage on any digital only input pin or MCLR with respect to Vss (except VDD)	0.3V to 6.0V
Voltage on any combined digital and analog pin with respect to Vss	0.3V to (VDD + 0.3V)
Voltage on VDDCORE with respect to Vss	0.3V to 2.75V
Voltage on VDD with respect to Vss	0.3V to 4.0V
Total power dissipation (Note 1)	1.0W
Maximum current out of Vss pin	300 mA
Maximum current into VDD pin	250 mA
Input clamp current, Iικ (Vι < 0 or Vι > VDD) (Note 2)	±0 mA
Output clamp current, IOK (VO < 0 or VO > VDD) (Note 2)	±0 mA
Maximum output current sunk by any PORTB and PORTC I/O pins	25 mA
Maximum output current sunk by any PORTD, PORTE and PORTJ I/O pins	8 mA
Maximum output current sunk by any PORTA, PORTF, PORTG and PORTH I/O pins (Note 3	)2 mA
Maximum output current sourced by any PORTB and PORTC I/O pins	25 mA
Maximum output current sourced by any PORTD, PORTE and PORTJ I/O pins	8 mA
Maximum output current sourced by any PORTA, PORTF, PORTG and PORTH I/O pins (Not	t <b>e 3)</b> 2 mA
Maximum current sunk by all ports combined	200 mA
Maximum current sourced by all ports combined	200 mA


Note 1: Power dissipation is calculated as follows:

 $Pdis = VDD x \{IDD - \sum IOH\} + \sum \{(VDD - VOH) x IOH\} + \sum (VOL x IOL) + \sum (VTPOUT x ITPOUT)$ 


- 2: No clamping diodes are present.
- 3: Exceptions are RA<1> and RA<0>, which are capable of directly driving LEDs up to 25 mA.

**† NOTICE:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operation listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

## FIGURE 27-1: PIC18F97J60 FAMILY VOLTAGE-FREQUENCY GRAPH, REGULATOR ENABLED (ENVREG TIED TO VDD)



## FIGURE 27-2: PIC18F97J60 FAMILY VOLTAGE-FREQUENCY GRAPH, REGULATOR DISABLED (ENVREG TIED TO Vss)



	7 <b>J60 Fam</b> Istrial)	ily	Standard Operating Conditions (unless otherwise stated)Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial				
Param No.	Symbol	Characteristic	Min	Тур	Мах	Units	Conditions
D001	Vdd	Supply Voltage	VDDCORE 2.7 3.1		3.6 3.6 3.6	> > >	ENVREG tied to Vss ENVREG tied to Vpp Ethernet module enabled (ECON2<5> = 1)
D001B	VDDCORE	External Supply for Microcontroller Core	2.0	_	2.7	V	
D001C	AVdd	Analog Supply Voltage	VDD - 0.3	_	VDD + 0.3	V	
D002	Vdr	RAM Data Retention Voltage <sup>(1)</sup>	1.5	_	—	V	
D003	VPOR	VDD Power-on Reset Voltage	—	_	0.7	V	See Section 4.3 "Power-on Reset (POR)" for details
D004	Svdd	VDD Rise Rate to ensure internal Power-on Reset	0.05	_	_	V/ms	See Section 4.3 "Power-on Reset (POR)" for details

## 27.1 DC Characteristics: Supply Voltage, PIC18F97J60 Family (Industrial)

**Note 1:** This is the limit to which VDD can be lowered in Sleep mode, or during a device Reset, without losing RAM data.

	7J60 Family strial)	Standard Operating Conditions (unless otherwise stated)Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial					
Param No.	Device	Тур	Max	Units	Cond	itions	
	Power-Down Current (IPD) <sup>(1)</sup>						
	All devices	19.0	69.0	μA	-40°C	VDD = 2.0V,	
		21.0	69.0	μA	+25°C	VDDCORE = $2.0V^{(4)}$	
		45.0	149.0	μA	+85°C	(Sleep mode)	
	All devices	26.0	104.0	μA	-40°C	VDD = 2.5V,	
		29.0	104.0	μA	+25°C	VDDCORE = 2.5V <sup>(4)</sup>	
		60.0	184.0	μA	+85°C	(Sleep mode)	
	All devices	40.0	203.0	μA	-40°C		
		44.0	203.0	μA	+25°C	VDD = 3.3V <sup>(5)</sup> (Sleep mode)	
		105.0	209.0	μA	+85°C	(Gieep mode)	

**Note 1:** The power-down current in Sleep mode does not depend on the oscillator type. Power-down current is measured with the part in Sleep mode, with all I/O pins in high-impedance state and tied to VDD or Vss and all features that add delta current disabled (such as WDT, Timer1 oscillator, etc.).

2: The supply current is mainly a function of operating voltage, frequency and mode. Other factors, such as I/O pin loading and switching rate, oscillator type and circuit, internal code execution pattern and temperature, also have an impact on the current consumption.

The test conditions for all IDD measurements in active operation mode are:

OSC1 = external square wave, from rail-to-rail; all I/O pins tri-stated, pulled to VDD;

MCLR = VDD; WDT enabled/disabled as specified.

- **3:** Standard, low-cost 32 kHz crystals have an operating temperature range of -10°C to +70°C. Extended temperature crystals are available at a much higher cost.
- 4: Voltage regulator disabled (ENVREG = 0, tied to Vss).
- 5: Voltage regulator enabled (ENVREG = 1, tied to VDD).
- 6: For △IETH, the specified current includes current sunk through TPOUT+ and TPOUT-. LEDA and LEDB are disabled for all testing.

	IC18F97J60 Family (Industrial)       Standard Operating Conditions (unless otherwise stated) Operating temperature       -40°C ≤ TA ≤ +85°C for industrial							
Param No.	Device	Тур	Max	Units	Conditions			
	Supply Current (IDD) <sup>(2,3)</sup>							
	All devices	12.0	34.0	μΑ	-40°C			
		12.0	34.0	μΑ	+25°C	$VDD = 2.0V,$ $VDDCORE = 2.0V^{(4)}$		
		74.0	108.0	μΑ	+85°C	VBBOOKE 2.0V		
	All devices	20.0	45.0	μA	-40°C		Fosc = 31 kHz ( <b>RC_RUN</b> mode, Internal Oscillator Source)	
		20.0	45.0	μA	+25°C	VDD = 2.5V, $VDDCORE = 2.5V(4)$		
		82.0	126.0	μA	+85°C			
	All devices	105.0	168.0	μΑ	-40°C			
		105.0	168.0	μA	+25°C	VDD = 3.3V <sup>(5)</sup>		
		182.0	246.0	μA	+85°C			
	All devices	8.0	32.0	μΑ	-40°C			
		8.0	32.0	μA	+25°C	$VDD = 2.0V,$ $VDDCORE = 2.0V^{(4)}$		
		62.0	98.0	μA	+85°C			
	All devices	12.0	35.0	μΑ	-40°C		Fosc = 31 kHz	
		12.0	35.0	μA	+25°C	VDD = 2.5V, $VDDCORE = 2.5V(4)$	(RC_IDLE mode,	
		70.0	95.0	μA	+85°C		Internal Oscillator Source	
	All devices	90.0	152.0	μΑ	-40°C			
		90.0	152.0	μA	+25°C	VDD = 3.3V <sup>(5)</sup>		
		170.0	225.0	μA	+85°C			

Note 1: The power-down current in Sleep mode does not depend on the oscillator type. Power-down current is measured with the part in Sleep mode, with all I/O pins in high-impedance state and tied to VDD or Vss and all features that add delta current disabled (such as WDT, Timer1 oscillator, etc.).

2: The supply current is mainly a function of operating voltage, frequency and mode. Other factors, such as I/O pin loading and switching rate, oscillator type and circuit, internal code execution pattern and temperature, also have an impact on the current consumption.

The test conditions for all IDD measurements in active operation mode are:

OSC1 = external square wave, from rail-to-rail; all I/O pins tri-stated, pulled to VDD;

MCLR = VDD; WDT enabled/disabled as specified.

- **3:** Standard, low-cost 32 kHz crystals have an operating temperature range of -10°C to +70°C. Extended temperature crystals are available at a much higher cost.
- **4:** Voltage regulator disabled (ENVREG = 0, tied to Vss).
- 5: Voltage regulator enabled (ENVREG = 1, tied to VDD).
- 6: For △IETH, the specified current includes current sunk through TPOUT+ and TPOUT-. LEDA and LEDB are disabled for all testing.

PIC18F97J60 Family (Industrial)       Standard Operating Conditions (unless otherwise stated)         Operating temperature       -40°C ≤ TA ≤ +85°C for industrial						al		
Param No.	Device	Тур	Max	Units	Conditions			
	Supply Current (IDD) <sup>(2)</sup>							
	All devices	0.8	1.5	mA	-40°C			
		0.8	1.5	mA	+25°C	VDD = 2.0V, $VDDCORE = 2.0V(4)$		
		0.9	1.7	mA	+85°C	VBBOOKE 2.0V		
	All devices	1.1	1.8	mA	-40°C		Fosc = 1 MHz	
		1.1	1.8	mA	+25°C	VDD = 2.5V, $VDDCORE = 2.5V^{(4)}$	( <b>PRI_RUN</b> mode, EC oscillator)	
		1.2	2.0	mA	+85°C	VEBOOKE 2.0V		
	All devices	2.1	3.4	mA	-40°C			
		2.0	3.4	mA	+25°C	VDD = 3.3V <sup>(5)</sup>		
		2.1	3.4	mA	+85°C			
	All devices	9.2	14.5	mA	-40°C		Fosc = 25 MHz	
		9.0	14.5	mA	+25°C	VDD = 2.5V, $VDDCORE = 2.5V^{(4)}$		
		9.2	14.5	mA	+85°C	VEBOOKE 2.0V		
	All devices	13.0	18.4	mA	-40°C		( <b>PRI_RUN</b> mode, EC oscillator)	
		12.4	18.4	mA	+25°C	VDD = 3.3V <sup>(5)</sup>	20 000	
		13.0	18.4	mA	+85°C			
	All devices	13.4	19.8	mA	-40°C	$\lambda = 0.5 t$		
		13.0	19.8	mA	+25°C	VDD = 2.5V, $VDDCORE = 2.5V^{(4)}$	_	
		13.4	19.8	mA	+85°C		Fosc = 41.6667 MHz	
	All devices	14.5	21.6	mA	-40°C		( <b>PRI_RUN</b> mode, EC oscillator)	
		14.4	21.6	mA	+25°C	VDD = 3.3V <sup>(5)</sup>	,	
		14.5	21.6	mA	+85°C			

**Note 1:** The power-down current in Sleep mode does not depend on the oscillator type. Power-down current is measured with the part in Sleep mode, with all I/O pins in high-impedance state and tied to VDD or VSS and all features that add delta current disabled (such as WDT, Timer1 oscillator, etc.).

2: The supply current is mainly a function of operating voltage, frequency and mode. Other factors, such as I/O pin loading and switching rate, oscillator type and circuit, internal code execution pattern and temperature, also have an impact on the current consumption.

The test conditions for all IDD measurements in active operation mode are:

- OSC1 = external square wave, from rail-to-rail; all I/O pins tri-stated, pulled to VDD;
- MCLR = VDD; WDT enabled/disabled as specified.
- **3:** Standard, low-cost 32 kHz crystals have an operating temperature range of -10°C to +70°C. Extended temperature crystals are available at a much higher cost.
- 4: Voltage regulator disabled (ENVREG = 0, tied to Vss).
- 5: Voltage regulator enabled (ENVREG = 1, tied to VDD).
- 6: For △IETH, the specified current includes current sunk through TPOUT+ and TPOUT-. LEDA and LEDB are disabled for all testing.

PIC18F97J60 Family (Industrial)		Standard Operating Conditions (unless otherwise stated)Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial								
Param No.	Device	Тур	Max	Units		Conditions				
	Supply Current (IDD) <sup>(2)</sup>									
	All devices	2.8	5.2	mA	-40°C					
		2.5	5.2	mA	+25°C	VDD = 2.5V, $VDDCORE = 2.5V^{(4)}$				
		2.8	5.2	mA	+85°C	VEDOCIAL 2.0V	Fosc = 25 MHz, 2.7778 MHz internal			
	All devices	3.6	6.4	mA	-40°C		( <b>PRI_RUN HS</b> mode)			
		3.3	6.4	mA	+25°C	VDD = 3.3V <sup>(5)</sup>	(			
		3.6	6.4	mA	+85°C					
	All devices	6.4	11.0	mA	-40°C					
		6.0	11.0	mA	+25°C	VDD = 2.5V, VDDCORE = 2.5V <sup>(4)</sup>	Fosc = 25 MHz, 13.8889 MHz internal ( <b>PRI_RUN HSPLL</b> mode)			
		6.4	11.0	mA	+85°C					
	All devices	7.8	12.5	mA	-40°C					
		7.4	12.5	mA	+25°C	VDD = 3.3V <sup>(5)</sup>				
		7.8	12.5	mA	+85°C					
	All devices	9.2	14.5	mA	-40°C					
		9.0	14.5	mA	+25°C	$V_{DD} = 2.5V,$ $V_{DDCORE} = 2.5V^{(4)}$				
		9.2	14.5	mA	+85°C		Fosc = 25 MHz, 25 MHz internal			
	All devices	13.0	18.4	mA	-40°C		(PRI RUN HS mode)			
		12.4	18.4	mA	+25°C	VDD = 3.3V <sup>(5)</sup>	· _ /			
		13.0	18.4	mA	+85°C					
	All devices	13.4	19.8	mA	-40°C					
		13.0	19.8	mA	+25°C	VDD = 2.5V, VDDCORE = 2.5V <sup>(4)</sup>				
		13.4	19.8	mA	+85°C		Fosc = 25 MHz, 41.6667 MHz internal			
	All devices	14.5	21.6	mA	-40°C		(PRI RUN HSPLL mode			
		14.4	21.6	mA	+25°C	VDD = 3.3V <sup>(5)</sup>	· _			
		14.5	21.6	mA	+85°C					

**Note 1:** The power-down current in Sleep mode does not depend on the oscillator type. Power-down current is measured with the part in Sleep mode, with all I/O pins in high-impedance state and tied to VDD or VSs and all features that add delta current disabled (such as WDT, Timer1 oscillator, etc.).

2: The supply current is mainly a function of operating voltage, frequency and mode. Other factors, such as I/O pin loading and switching rate, oscillator type and circuit, internal code execution pattern and temperature, also have an impact on the current consumption.

The test conditions for all IDD measurements in active operation mode are:

OSC1 = external square wave, from rail-to-rail; all I/O pins tri-stated, pulled to VDD;

MCLR = VDD; WDT enabled/disabled as specified.

- **3:** Standard, low-cost 32 kHz crystals have an operating temperature range of -10°C to +70°C. Extended temperature crystals are available at a much higher cost.
- 4: Voltage regulator disabled (ENVREG = 0, tied to Vss).
- **5**: Voltage regulator enabled (ENVREG = 1, tied to VDD).
- 6: For △IETH, the specified current includes current sunk through TPOUT+ and TPOUT-. LEDA and LEDB are disabled for all testing.

PIC18F97J60 Family (Industrial)		Standard Operating Conditions (unless otherwise stated)Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial							
Param No.	Device		Max	Units	Conditions				
	Supply Current (IDD) <sup>(2)</sup>								
	All devices	0.5	1.1	mA	-40°C				
		0.5	1.1	mA	+25°C	$VDD = 2.0V,$ $VDDCORE = 2.0V^{(4)}$			
		0.6	1.2	mA	+85°C	VBBOOKE 2.0V			
	All devices	0.9	1.4	mA	-40°C		Fosc = 1 MHz		
		0.9	1.4	mA	+25°C	$VDD = 2.5V,$ $VDDCORE = 2.5V^{(4)}$	( <b>PRI_IDLE</b> mode, EC oscillator)		
		1.0	1.5	mA	+85°C				
	All devices	1.9	2.6	mA	-40°C				
		1.8	2.6	mA	+25°C	VDD = 3.3V <sup>(5)</sup>			
		1.9	2.6	mA	+85°C				
	All devices	5.9	9.5	mA	-40°C				
		5.6	9.5	mA	+25°C	$VDD = 2.5V,$ $VDDCORE = 2.5V^{(4)}$			
		5.9	9.5	mA	+85°C		Fosc = 25 MHz ( <b>PRI IDLE</b> mode,		
	All devices	7.5	13.2	mA	-40°C		EC oscillator)		
		7.2	13.2	mA	+25°C	VDD = 3.3V <sup>(5)</sup>	,		
		7.5	13.2	mA	+85°C				
	All devices	8.6	14.0	mA	-40°C				
		8.0	14.0	mA	+25°C	$VDD = 2.5V,$ $VDDCORE = 2.5V^{(4)}$			
		8.6	14.0	mA	+85°C		Fosc = 41.6667 MHz ( <b>PRI IDLE</b> mode,		
	All devices	9.8	16.0	mA	-40°C		EC oscillator)		
		9.4	16.0	mA	+25°C	VDD = 3.3V <sup>(5)</sup>			
		9.8	16.0	mA	+85°C				

**Note 1:** The power-down current in Sleep mode does not depend on the oscillator type. Power-down current is measured with the part in Sleep mode, with all I/O pins in high-impedance state and tied to VDD or VSs and all features that add delta current disabled (such as WDT, Timer1 oscillator, etc.).

2: The supply current is mainly a function of operating voltage, frequency and mode. Other factors, such as I/O pin loading and switching rate, oscillator type and circuit, internal code execution pattern and temperature, also have an impact on the current consumption.

The test conditions for all IDD measurements in active operation mode are:

- OSC1 = external square wave, from rail-to-rail; all I/O pins tri-stated, pulled to VDD;
- MCLR = VDD; WDT enabled/disabled as specified.
- **3:** Standard, low-cost 32 kHz crystals have an operating temperature range of -10°C to +70°C. Extended temperature crystals are available at a much higher cost.
- 4: Voltage regulator disabled (ENVREG = 0, tied to Vss).
- 5: Voltage regulator enabled (ENVREG = 1, tied to VDD).
- 6: For △IETH, the specified current includes current sunk through TPOUT+ and TPOUT-. LEDA and LEDB are disabled for all testing.

PIC18F97J60 Family (Industrial)		Standard Operating Conditions (unless otherwise stated)Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial							
Param No.	Device	Тур	Мах	Units	Conditions				
	Supply Current (IDD) <sup>(2)</sup>								
	All devices	22.0	45.0	μΑ	-10°C				
		22.0	45.0	μΑ	+25°C	$VDD = 2.0V,$ $VDDCORE = 2.0V^{(4)}$			
		78.0	114.0	μA	+70°C				
	All devices	27.0	52.0	μA	-10°C		Fosc = 32 kHz <sup>(3)</sup>		
		27.0	52.0	μA	+25°C	$VDD = 2.5V,$ $VDDCORE = 2.5V^{(4)}$	( <b>SEC_RUN</b> mode, Timer1 as clock)		
		92.0	135.0	μA	+70°C				
	All devices	106.0	168.0	μA	-10°C				
		106.0	168.0	μA	+25°C	VDD = 3.3V <sup>(5)</sup>			
		188.0	246.0	μA	+70°C				
	All devices	18.0	37.0	μA	-10°C	)/== 0.0)/			
		18.0	37.0	μA	+25°C	$VDD = 2.0V,$ $VDDCORE = 2.0V^{(4)}$			
		75.0	105.0	μA	+70°C	VBBOOKE 2.0V			
	All devices	21.0	40.0	μA	-10°C		Fosc = 32 kHz <sup>(3)</sup>		
		21.0	40.0	μΑ	+25°C	$VDD = 2.5V,$ $VDDCORE = 2.5V^{(4)}$	(SEC_IDLE mode,		
		84.0	98.0	μΑ	+70°C		Timer1 as clock)		
	All devices	94.0	152.0	μΑ	-10°C				
		94.0	152.0	μΑ	+25°C	VDD = 3.3V <sup>(5)</sup>			
		182.0	225.0	μA	+70°C				

Note 1: The power-down current in Sleep mode does not depend on the oscillator type. Power-down current is measured with the part in Sleep mode, with all I/O pins in high-impedance state and tied to VDD or VSs and all features that add delta current disabled (such as WDT, Timer1 oscillator, etc.).

2: The supply current is mainly a function of operating voltage, frequency and mode. Other factors, such as I/O pin loading and switching rate, oscillator type and circuit, internal code execution pattern and temperature, also have an impact on the current consumption.

The test conditions for all IDD measurements in active operation mode are:

OSC1 = external square wave, from rail-to-rail; all I/O pins tri-stated, pulled to VDD;

MCLR = VDD; WDT enabled/disabled as specified.

- **3:** Standard, low-cost 32 kHz crystals have an operating temperature range of -10°C to +70°C. Extended temperature crystals are available at a much higher cost.
- 4: Voltage regulator disabled (ENVREG = 0, tied to Vss).
- 5: Voltage regulator enabled (ENVREG = 1, tied to VDD).
- 6: For △IETH, the specified current includes current sunk through TPOUT+ and TPOUT-. LEDA and LEDB are disabled for all testing.

	PIC18F97J60 Family (Industrial)		Standard Operating Conditions (unless otherwise stated)Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial								
Param No.	Device	Тур	Max	Units		Conditions					
	Module Differential Currents	(ΔΙWDT, ΔΙΟSCB, ΔΙΑD, ΔΙΕΤΗ)									
D022	Watchdog Timer	2.4	7.0	μA	-40°C	VDD = 2.0V,					
(∆IWDT)		2.4	7.0	μA	+25°C	VDD = 2.0V, $VDDCORE = 2.0V^{(4)}$					
		12.0	19.0	μA	+85°C	VBBOOKE 2.0V					
		3.0	8.0	μA	-40°C	VDD = 2.5V,					
		3.0	8.0	μA	+25°C	VDD = 2.5V, $VDDCORE = 2.5V^{(4)}$					
		14.0	22.0	μA	+85°C						
		5.0	12.0	μA	-40°C						
		5.0	12.0	μA	+25°C	VDD = 3.3V <sup>(5)</sup>					
		19.0	30.0	μA	+85°C						
D025	Timer1 Oscillator	12.0	20.0	μA	-40°C	VDD = 2.0V,					
(∆IOSCB)		12.0	20.0	μA	+25°C	VDD = 2.0V, VDDCORE = 2.0V <sup>(4)</sup>	32 kHz on Timer1 <sup>(3)</sup>				
		24.0	36.0	μA	+85°C						
		13.0	21.0	μA	-40°C						
		13.0	21.0	μA	+25°C	VDD = 2.5 V, VDDCORF = 2.5 V(4)	32 kHz on Timer1 <sup>(3)</sup>				
		26.0	38.0	μA	+85°C						
		14.0	25.0	μA	-40°C						
		14.0	25.0	μA	+25°C	VDD = 3.3V <sup>(5)</sup>	32 kHz on Timer1 <sup>(3)</sup>				
		29.0	40.0	μA	+85°C						
D026 (∆IAD)	A/D Converter	1.2	10.0	μΑ	-40°C to +85°C	VDD = 2.0V, VDDCORE = 2.0V <sup>(4)</sup>					
		1.2	10.0	μA	-40°C to +85°C	VDD = 2.5V, VDDCORE = 2.5V <sup>(4)</sup>	A/D on, not converting				
		1.2	11.0	μA	-40°C to +85°C	VDD = 3.3V <sup>(5)</sup>					
D027	Ethernet Module	130.0	156.0	mA	-40°C to +85°C		No transmit activity				
∆IETH <b>(6)</b>		180.0	214.0	mA	-40°C to +85°C	VDD = 3.3V <sup>(5)</sup>	Transmission in progress				

**Note 1:** The power-down current in Sleep mode does not depend on the oscillator type. Power-down current is measured with the part in Sleep mode, with all I/O pins in high-impedance state and tied to VDD or VSs and all features that add delta current disabled (such as WDT, Timer1 oscillator, etc.).

2: The supply current is mainly a function of operating voltage, frequency and mode. Other factors, such as I/O pin loading and switching rate, oscillator type and circuit, internal code execution pattern and temperature, also have an impact on the current consumption.

The test conditions for all IDD measurements in active operation mode are:

- OSC1 = external square wave, from rail-to-rail; all I/O pins tri-stated, pulled to VDD;
- MCLR = VDD; WDT enabled/disabled as specified.
- **3:** Standard, low-cost 32 kHz crystals have an operating temperature range of -10°C to +70°C. Extended temperature crystals are available at a much higher cost.
- 4: Voltage regulator disabled (ENVREG = 0, tied to Vss).
- 5: Voltage regulator enabled (ENVREG = 1, tied to VDD).
- 6: For △IETH, the specified current includes current sunk through TPOUT+ and TPOUT-. LEDA and LEDB are disabled for all testing.

DC CH4	ARACTE	RISTICS	Standard Operating Conditions (unless otherwise stated) Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial				
Param No.	Symbol	Characteristic	Min	Мах	Units	Conditions	
	VIL	Input Low Voltage					
		All I/O ports:					
D030		with TTL buffer	Vss	0.15Vdd	V	VDD<2.7V	
			Vss	0.8	V	$2.7V \le V\text{DD} \le 3.6V$	
D031		with Schmitt Trigger buffer	Vss	0.2 VDD	V		
D032		MCLR	Vss	0.2 VDD	V		
D033		OSC1	Vss	0.3 VDD	V	HS, HSPLL modes	
D033A		OSC1	Vss	0.2 VDD	V	EC mode	
D034		T13CKI	Vss	0.3	V		
	VIH	Input High Voltage					
		I/O ports, with analog functions:					
D040		with TTL buffer	0.25 VDD + 0.8V	Vdd	V		
D041		with Schmitt Trigger buffer	0.8 Vdd	Vdd	V		
		I/O ports, digital only:					
		with TTL buffer	0.25 VDD + 0.8V	5.5	V		
		with Schmitt Trigger buffer	0.8 Vdd	5.5	V		
D042		MCLR	0.8 VDD	Vdd	V		
D043		OSC1	0.7 Vdd	Vdd	V	HS, HSPLL modes	
D043A		OSC1	0.8 VDD	Vdd	V	EC mode	
D044		T13CKI	1.6	Vdd	V		
	lı∟	Input Leakage Current <sup>(1)</sup>					
D060		I/O ports	_	±1	μA	$Vss \le VPIN \le VDD,$ Pin at high-impedance	
D061		MCLR		±1	μA	$Vss \leq V PIN \leq V DD$	
D063		OSC1		±1	μA	$Vss \leq V PIN \leq V DD$	
	IPU	Weak Pull-up Current					
D070	IPURB	PORTB, PORTD, PORTE, PORTJ	80	400	μA	VDD = 3.3V, VPIN = VSS	

## 27.3 DC Characteristics: PIC18F97J60 Family (Industrial)

**Note 1:** Negative current is defined as current sourced by the pin.

## 27.3 DC Characteristics: PIC18F97J60 Family (Industrial) (Continued)

DC CHA				Standard Operating Conditions (unless otherwise stated) Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial				
Param No.	Symbol	Characteristic	Min	Мах	Units	Conditions		
	Vol	Output Low Voltage						
D080		I/O ports:						
		PORTD, PORTE, PORTJ	_	0.4	V	IOL = 4 mA, VDD = 3.3V, -40°C to +85°C		
		PORTA<5:2>, PORTF, PORTG, PORTH	_	0.4	V	IOL = 2 mA, VDD = 3.3V, -40°C to +85°C		
		PORTA<1:0>, PORTB, PORTC	_	0.4	V	IOL = 8 mA, VDD = 3.3V, -40°C to +85°C		
D083		OSC2/CLKO (EC, ECPLL modes)	_	0.4	V	IOL = 2 mA, VDD = 3.3V, -40°C to +85°C		
	Vон	Output High Voltage <sup>(1)</sup>						
D090		I/O ports:			V			
		PORTD, PORTE, PORTJ	2.4	_	V	IOH = -4 mA, VDD = 3.3V, -40°С to +85°С		
		PORTA<5:2>, PORTF, PORTG, PORTH	2.4	_	V	IOH = -2 mA, VDD = 3.3V, -40°С to +85°С		
		PORTA<1:0>, PORTB, PORTC	2.4	_	V	IOH = -8 mA, VDD = 3.3V, -40°С to +85°С		
D092		OSC2/CLKO (EC, ECPLL modes)	2.4	_	V	IOH = -1.0 mA, VDD = 3.3V, -40°C to +85°C		
		Capacitive Loading Specs on Output Pins						
D100	COSC2	OSC2 pin	_	15	pF	In HS mode when external clock is used to drive OSC1		
D101	Cio	All I/O pins and OSC2 (in Internal RC mode, EC, ECPLL)	-	50	pF	To meet the AC timing specifications		
D102	Св	SCLx, SDAx	_	400	pF	I <sup>2</sup> C <sup>™</sup> specification		

**Note 1:** Negative current is defined as current sourced by the pin.

			Standard Operating Conditions (unless otherwise stated) Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial					
Param No.	Sym	Characteristic	Min	Тур†	Max	Units	Conditions	
		Program Flash Memory						
D130	Eр	Cell Endurance	100	1K	—	E/W	-40°C to +85°C	
D131	Vpr	VDD for Read	VMIN	—	3.6	V	VMIN = Minimum operating voltage	
D132B	Vpew	Voltage for Self-Timed Erase or Write						
		VDD	2.70	—	3.6	V	ENVREG tied to VDD	
		VDDCORE	2.35	—	2.7	V	ENVREG tied to Vss	
D133A	Tiw	Self-Timed Write Cycle Time		2.8	—	ms		
D134	TRETD	Characteristic Retention	20	_	_	Year	Provided no other specifications are violated	
D135	IDDP	Supply Current during Programming	_	10		mA	Ethernet module disabled	

#### TABLE 27-1: MEMORY PROGRAMMING REQUIREMENTS

† Data in "Typ" column is at 3.3V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

### TABLE 27-2: COMPARATOR SPECIFICATIONS

<b>Operating Conditions:</b> $3.0V \le VDD \le 3.6V$ , $-40^{\circ}C \le TA \le +85^{\circ}C$ (unless otherwise stated)							
Param No.	Sym	Characteristics	Min	Тур	Мах	Units	Comments
D300	VIOFF	Input Offset Voltage*		±5.0	±10	mV	
D301	VICM	Input Common-Mode Voltage*	0	_	AVDD - 1.5	V	
D302	CMRR	Common-Mode Rejection Ratio*	55	—	—	dB	
300	TRESP	Response Time <sup>(1)*</sup>		150	400	ns	
301	Тмс2о∨	Comparator Mode Change to Output Valid*		_	10	μS	

\* These parameters are characterized but not tested.

**Note 1:** Response time measured with one comparator input at (AVDD – 1.5)/2, while the other input transitions from Vss to AVDD.

## TABLE 27-3: VOLTAGE REFERENCE SPECIFICATIONS

Operating	<b>Operating Conditions:</b> $3.0V \le V_{DD} \le 3.6V$ , $-40^{\circ}C \le T_A \le +85^{\circ}C$ (unless otherwise stated)						
Param No.	Sym	Characteristics	Min	Тур	Max	Units	Comments
D310	VRES	Resolution	VDD/24	_	VDD/32	LSb	
D311	VRAA	Absolute Accuracy	_	_	1/2	LSb	
D312	VRur	Unit Resistor Value (R)	_	2k	_	Ω	
310	TSET	Settling Time <sup>(1)</sup>		_	10	μS	

**Note 1:** Settling time measured while CVRR = 1 and CVR3:CVR0 transitions from '0000' to '1111'.

### TABLE 27-4: INTERNAL VOLTAGE REGULATOR SPECIFICATIONS

Operating	<b>Operating Conditions:</b> -40°C $\leq$ TA $\leq$ +85°C (unless otherwise stated)							
Param No.	Sym Characteristics Min Typ Max Units Comments							
	Vrgout	Regulator Output Voltage	_	2.5		V		
	Cf	External Filter Capacitor Value	1	10	_	μF	Capacitor must be low series resistance	

## 27.4 AC (Timing) Characteristics

#### 27.4.1 TIMING PARAMETER SYMBOLOGY

The timing parameter symbols have been created following one of the following formats:

1. TppS2ppS	5	3. Tcc:st	(I <sup>2</sup> C specifications only)
2. TppS		4. Ts	(I <sup>2</sup> C specifications only)
Т			
F	Frequency	Т	Time
Lowercase l	etters (pp) and their meanings:		
рр			
сс	ECCP1	osc	OSC1
ck	CLKO	rd	RD
cs	CS	rw	RD or WR
di	SDIx	SC	SCKx
do	SDOx	SS	SSx
dt	Data in	tO	TOCKI
io	I/O port	t1	T13CKI
mc	MCLR	wr	WR
Uppercase l	etters and their meanings:		
S			
F	Fall	Р	Period
н	High	R	Rise
I	Invalid (High-Impedance)	V	Valid
L	Low	Z	High-Impedance
I <sup>2</sup> C only			
AA	Output access	High	High
BUF	Bus free	Low	Low
Tcc:st (I <sup>2</sup> C :	specifications only)		
CC			
HD	Hold	SU	Setup
ST			
DAT	DATA input hold	STO	Stop condition
STA	Start condition		


### 27.4.2 TIMING CONDITIONS

The temperature and voltages specified in Table 27-5 apply to all timing specifications unless otherwise noted. Figure 27-3 specifies the load conditions for the timing specifications.


#### TABLE 27-5: TEMPERATURE AND VOLTAGE SPECIFICATIONS – AC

	Standard Operating Conditions (unless otherwise stated)							
AC CHARACTERISTICS	Operating temperature $-40^{\circ}C \le TA \le +85^{\circ}C$ for industrial							
AU UNARAUTERIUTIUU	Operating voltage VDD range as described in DC spec Section 27.1 and							
	Section 27.3.							

#### FIGURE 27-3: LOAD CONDITIONS FOR DEVICE TIMING SPECIFICATIONS



## 27.4.3 TIMING DIAGRAMS AND SPECIFICATIONS



## TABLE 27-6: EXTERNAL CLOCK TIMING REQUIREMENTS

Param. No.	Symbol	Characteristic	Min	Мах	Units	Conditions
1A	Fosc	External CLKI Frequency <sup>(1)</sup>	DC	41.6667	MHz	EC Oscillator mode
		Oscillator Frequency <sup>(1)</sup>	6	25	MHz	HS Oscillator mode
1	Tosc	External CLKI Period <sup>(1)</sup>	24	_	ns	EC Oscillator mode
		Oscillator Period <sup>(1)</sup>	40	167	ns	HS Oscillator mode
2	Тсү	Instruction Cycle Time <sup>(1)</sup>	96	_	ns	Tcy = 4/Fosc, Industrial
3	TosL, TosH	External Clock in (OSC1) High or Low Time	10	—	ns	EC Oscillator mode
4	TosR, TosF	External Clock in (OSC1) Rise or Fall Time	_	7.5	ns	EC Oscillator mode
5		Clock Frequency Tolerance	_	±50	ppm	Ethernet module enabled

**Note 1:** Instruction cycle period (TCY) equals four times the input oscillator time base period for all configurations except PLL. All specified values are based on characterization data for that particular oscillator type under standard operating conditions with the device executing code. Exceeding these specified limits may result in an unstable oscillator operation and/or higher than expected current consumption. All devices are tested to operate at "min." values with an external clock applied to the OSC1/CLKI pin. When an external clock input is used, the "max." cycle time limit is "DC" (no clock) for all devices.

Param No.	Sym	Characteristic	Min	Тур†	Max	Units	Conditions
F10	Fosc	Oscillator Frequency Range	8	_	25	MHz	HSPLL mode
			8	—	37.5	MHz	ECPLL mode
F11	Fsys	On-Chip VCO System Frequency	20	_	62.5	MHz	
F12	t <sub>rc</sub>	PLL Start-up Time (Lock Time)	—	—	2	ms	
F13	$\Delta CLK$	CLKO Stability (Jitter)	-2	—	+2	%	


### TABLE 27-7: PLL CLOCK TIMING SPECIFICATIONS (VDD = 2.6V TO 3.6V)

† Data in "Typ" column is at 3.3V, 25°C, unless otherwise stated. These parameters are for design guidance only and are not tested.

## TABLE 27-8: AC CHARACTERISTICS: INTERNAL RC ACCURACY PIC18F97J60 FAMILY (INDUSTRIAL)

Param No.	Characteristic	Min	Тур	Max	Units	Conditions
	INTRC Accuracy @ Freq = 31 kHz <sup>(1)</sup>	21.7	—	40.3	kHz	


**Note 1:** INTRC frequency changes as VDDCORE changes.



Param No.	Symbol	Characteristic	Min	Тур	Max	Units	Conditions
10	TosH2ckL	OSC1 ↑ to CLKO $↓$	_	75	200	ns	
11	TosH2cĸH	OSC1 ↑ to CLKO ↑	—	75	200	ns	
12	TCKR	CLKO Rise Time	—	15	30	ns	
13	ТскF	CLKO Fall Time	—	15	30	ns	
14	TckL2I0V	CLKO $\downarrow$ to Port Out Valid	_	_	0.5 Tcy + 20	ns	
15	TioV2скH	Port In Valid before CLKO ↑	0.25 Tcy + 25		_	ns	
16	TckH2iol	Port In Hold after CLKO ↑	0	_	—	ns	
17	TosH2IoV	OSC1 ↑ (Q1 cycle) to Port Out Valid	_	50	150	ns	
18	TosH2ıol	OSC1 ↑ (Q2 cycle) to Port Input Invalid (I/O in hold time)	100	_	_	ns	
19	TioV2osH	Port Input Valid to OSC1 ↑ (I/O in setup time)	0	—	_	ns	
20	TioR	Port Output Rise Time	—	_	6	ns	
21	TIOF	Port Output Fall Time	—		5	ns	
22†	TINP	INTx pin High or Low Time	Тсү	_	—	ns	
23†	Trbp	RB7:RB4 Change INTx High or Low Time	Тсү	_	—	ns	

#### TABLE 27-9: CLKO AND I/O TIMING REQUIREMENTS


† These parameters are asynchronous events not related to any internal clock edges.



#### FIGURE 27-6: PROGRAM MEMORY READ TIMING DIAGRAM


<b>TABLE 27-10:</b>	CLKO AND I/O TIMING REQUIREMENTS
---------------------	----------------------------------

Param. No	Symbol	Characteristics	Min	Тур	Мах	Units
150	TadV2alL	Address Out Valid to ALE ↓ (address setup time)	0.25 Tcy – 10	_	—	ns
151	TalL2adl	ALE $\downarrow$ to Address Out Invalid (address hold time)	5		—	ns
155	TalL2oeL	ALE $\downarrow$ to $\overline{OE} \downarrow$	10	0.125 Tcy	—	ns
160	TadZ2oeL	AD high-Z to $\overline{OE} \downarrow$ (bus release to $\overline{OE}$ )	0		_	ns
161	ToeH2adD	OE ↑ to AD Driven	0.125 Tcy – 5		_	ns
162	TadV2oeH	Least Significant Data Valid before $\overline{OE} \uparrow$ (data setup time)	20	—	_	ns
163	ToeH2adl	$\overline{OE}$ $\uparrow$ to Data In Invalid (data hold time)	0	_	_	ns
164	TalH2alL	ALE Pulse Width	—	Тсү	—	ns
165	ToeL2oeH	OE Pulse Width	0.5 TCY – 5	0.5 TCY	_	ns
166	TalH2alH	ALE $\uparrow$ to ALE $\uparrow$ (cycle time)	—	0.25 Tcy	—	ns
167	Тасс	Address Valid to Data Valid	0.75 Tcy – 25		—	ns
168	Тое	$\overline{OE}\downarrow$ to Data Valid		_	0.5 Tcy – 25	ns
169	TalL2oeH	ALE ↓ to OE ↑	0.625 Tcy – 10	_	0.625 Tcy + 10	ns
171	TalH2csL	Chip Enable Active to ALE $\downarrow$	0.25 Tcy – 20	_	—	ns
171A	TubL2oeH	AD Valid to Chip Enable Active		_	10	ns



Param. No	Symbol	Characteristics	Min	Тур	Мах	Units
150	TadV2alL	Address Out Valid to ALE $\downarrow$ (address setup time)	0.25 Tcy – 10	—	_	ns
151	TalL2adl	ALE $\downarrow$ to Address Out Invalid (address hold time)	5			ns
153	TwrH2adl	$\overline{WRn}$ $\uparrow$ to Data Out Invalid (data hold time)	5	_	_	ns
154	TwrL	WRn Pulse Width	0.5 Tcy – 5	0.5 TCY	_	ns
156	TadV2wrH	Data Valid before $\overline{WRn}$ $\uparrow$ (data setup time)	0.5 Tcy – 10	_	_	ns
157	TbsV2wrL	Byte Select Valid before $\overline{\text{WRn}} \downarrow$ (byte select setup time)	0.25 TCY	—	—	ns
157A	TwrH2bsl	$\overline{\text{WRn}}$ $\uparrow$ to Byte Select Invalid (byte select hold time)	0.125 Tcy – 5	_	_	ns
166	TalH2alH	ALE $\uparrow$ to ALE $\uparrow$ (cycle time)	_	0.25 TCY		ns
171	TalH2csL	Chip Enable Active to ALE $\downarrow$	0.25 Tcy – 20	_		ns
171A	TubL2oeH	AD Valid to Chip Enable Active		_	10	ns

© 2007 Microchip Technology Inc.



### FIGURE 27-8: RESET, WATCHDOG TIMER, OSCILLATOR START-UP TIMER AND POWER-UP TIMER TIMING

### TABLE 27-12:RESET, WATCHDOG TIMER, OSCILLATOR START-UP TIMER, POWER-UP TIMER<br/>AND BROWN-OUT RESET REQUIREMENTS

Param. No.	Symbol	Characteristic	Min	Тур	Мах	Units	Conditions
30	ТмсL	MCLR Pulse Width (low)	2		_	μS	
31	TWDT	Watchdog Timer Time-out Period (no postscaler)	2.8	4.1	5.4	ms	
32	Tost	Oscillation Start-up Timer Period	1024 Tosc		1024 Tosc	_	Tosc = OSC1 period
33	TPWRT	Power-up Timer Period	46.2	66	85.8	ms	
34	Tioz	I/O High-Impedance from MCLR	_		3Tcy + 2	μS	System clock available
		Low or Watchdog Timer Reset	_		415	μS	System clock unavailable (Sleep mode or primary oscillator off)
38	TCSD	CPU Start-up Time	—	200	_	μS	






TABLE 27-13:	TIMER0 AND TIMER1 EXTERNAL CLOCK REQUIREMENTS
--------------	-----------------------------------------------

Param No.	Symbol		Characteristic		Min	Max	Units	Conditions
40	T⊤0H	T0CKI High P	ulse Width	No prescaler	0.5 Tcy + 20	—	ns	
				With prescaler	10	_	ns	
41	T⊤0L	T0CKI Low Pu	ulse Width	No prescaler	0.5 Tcy + 20	_	ns	
				With prescaler	10	_	ns	
42	T⊤0P	T0CKI Period		No prescaler	Tcy + 10	—	ns	
				With prescaler	Greater of: 20 ns or (Tcy + 40)/N	_	ns	N = prescale value (1, 2, 4,, 256)
45	T⊤1H	1H T13CKI High Time	Synchronous, no prescaler		0.5 Tcy + 20	—	ns	
			Synchronous, with prescaler		10	—	ns	
			Asynchronous		30	—	ns	
46	T⊤1L	T13CKI Low	Synchronous, n	o prescaler	0.5 Tcy + 5	—	ns	
		Time	Synchronous, with prescaler		10	_	ns	
			Asynchronous		30	—	ns	
47	T⊤1P	T13CKI Input Period	Synchronous		Greater of: 20 ns or (Tcy + 40)/N	-	ns	N = prescale value (1, 2, 4, 8)
			Asynchronous		60		ns	
	F⊤1	T13CKI Oscill	ator Input Frequency Range		DC	50	kHz	
48	TCKE2TMRI	Delay from Ex Timer Increme	tternal T13CKI C ent	lock Edge to	2 Tosc	7 Tosc	_	







TABLE 27-14: CAPTURE/COMPARE/PWM REQUIREMENTS (INCLUDING ECCPx MODULES)

Param No.	Symbol	с	haracteristic	Min	Max	Units	Conditions
50	TccL	CCPx Input Low	No prescaler	0.5 TCY + 20		ns	
		Time	With prescaler	10	_	ns	
51	ТссН	CCPx Input	No prescaler	0.5 TCY + 20	_	ns	
		High Time	With prescaler	10	_	ns	
52	TCCP	CCPx Input Perio	od	<u>3 Tcy + 40</u> N	_	ns	N = prescale value (1, 4 or 16)
53	TccR	CCPx Output Fal	ll Time	—	25	ns	
54	TccF	CCPx Output Fal	II Time	—	25	ns	


#### TABLE 27-15: PARALLEL SLAVE PORT REQUIREMENTS

Param. No.	Symbol	Characteristic	Min	Max	Units	Conditions
62	TdtV2wrH	Data In Valid before $\overline{WR} \uparrow$ or $\overline{CS} \uparrow$ (setup time)	20		ns	
63	TwrH2dtl	$\overline{WR}$ $\uparrow$ or $\overline{CS}$ $\uparrow$ to Data–In Invalid (hold time)	20	_	ns	
64	TrdL2dtV	$\overline{RD} \downarrow$ and $\overline{CS} \downarrow$ to Data–Out Valid	_	80	ns	
65	TrdH2dtl	$\overline{RD}$ ↑ or $\overline{CS}$ $\downarrow$ to Data–Out Invalid	10	30	ns	
66	TibfINH	Inhibit of the IBF Flag bit being Cleared from $\overline{\rm WR}\uparrow$ or $\overline{\rm CS}\uparrow$		3 Тсү		



#### TABLE 27-16: EXAMPLE SPI MODE REQUIREMENTS (MASTER MODE, CKE = 0)


Param No.	Symbol	Characteristic	Min	Max	Units	Conditions
73	TDIV2scH, TDIV2scL	Setup Time of SDIx Data Input to SCKx Edge	100		ns	
74	TscH2diL, TscL2diL	Hold Time of SDIx Data Input to SCKx Edge	100	_	ns	
75	TDOR	SDOx Data Output Rise Time	—	25	ns	
76	TDOF	SDOx Data Output Fall Time	—	25	ns	
78	TscR	SCKx Output Rise Time	—	25	ns	
79	TscF	SCKx Output Fall Time	—	25	ns	
80	TscH2doV, TscL2doV	SDOx Data Output Valid after SCKx Edge	_	50	ns	



### FIGURE 27-12: EXAMPLE SPI MASTER MODE TIMING (CKE = 1)

### TABLE 27-17: EXAMPLE SPI MODE REQUIREMENTS (MASTER MODE, CKE = 1)

Param. No.	Symbol	Characteristic	Min	Max	Units	Conditions
73	TDIV2SCH, TDIV2SCL	Setup Time of SDIx Data Input to SCKx Edge	100		ns	
74	TscH2DIL, TscL2DIL	Hold Time of SDIx Data Input to SCKx Edge	100		ns	
75	TDOR	SDOx Data Output Rise Time	—	25	ns	
76	TdoF	SDOx Data Output Fall Time	—	25	ns	
78	TscR	SCKx Output Rise Time	—	25	ns	
79	TscF	SCKx Output Fall Time	—	25	ns	
80	TscH2doV, TscL2doV	SDOx Data Output Valid after SCKx Edge	—	50	ns	
81	TDOV2scH, TDOV2scL	SDOx Data Output Setup to SCKx Edge	Тсү	-	ns	



### TABLE 27-18: EXAMPLE SPI MODE REQUIREMENTS (SLAVE MODE TIMING, CKE = 0)

Param No.	Symbol	Characteristic	Characteristic		Max	Units	Conditions
70	TssL2scH, TssL2scL	$\overline{\text{SSx}} \downarrow$ to SCKx $\downarrow$ or SCKx $\uparrow$ Input	$\overline{Sx} \downarrow$ to SCKx $\downarrow$ or SCKx $\uparrow$ Input			ns	
71	TscH	SCKx Input High Time	CKx Input High Time Continuous 1			ns	
71A			Single Byte	40		ns	(Note 1)
72	TscL	SCKx Input Low Time	CKx Input Low Time Continuous 1.			ns	
72A		Single Byte		40	_	ns	(Note 1)
73	TDIV2scH, TDIV2scL	Setup Time of SDIx Data Input to SCKx	100		ns		
73A	Тв2в	Last Clock Edge of Byte 1 to the First Clo	ck Edge of Byte 2	1.5 Tcy + 40		ns	(Note 2)
74	TscH2DIL, TscL2DIL	Hold Time of SDIx Data Input to SCKx I	Edge	100		ns	
75	TDOR	SDOx Data Output Rise Time			25	ns	
76	TdoF	SDOx Data Output Fall Time			25	ns	
77	TssH2doZ	SSx ↑ to SDOx Output High-impedance	;	10	50	ns	
80	TscH2doV, TscL2doV	SDOx Data Output Valid after SCKx Edge		_	50	ns	
83	TscH2ssH, TscL2ssH	SSx ↑ after SCKx Edge	1.5 Tcy + 40		ns		

**Note 1:** Requires the use of Parameter #73A.

2: Only if Parameter #71A and #72A are used.

© 2007 Microchip Technology Inc.





TABLE 27-19:	EXAMPLE SPI SLAVE MODE REQUIREMENTS (CKE = 1)

Param No.	Symbol	Characteristic	Characteristic			Units	Conditions
70	TssL2scH, TssL2scL	$\overline{SSx} \downarrow$ to SCKx $\downarrow$ or SCKx $\uparrow$ Input		Тсү		ns	
71	TscH	SCKx Input High Time	Continuous	1.25 Tcy + 30	-	ns	
71A			Single Byte	40	_	ns	(Note 1)
72	TscL	SCKx Input Low Time	Continuous	1.25 Tcy + 30	_	ns	
72A			Single Byte		-	ns	(Note 1)
73A	Тв2в	Last Clock Edge of Byte 1 to the First C	1.5 Tcy + 40	_	ns	(Note 2)	
74	TscH2DIL, TscL2DIL	Hold Time of SDIx Data Input to SCK	100	_	ns		
75	TDOR	SDOx Data Output Rise Time		—	25	ns	
76	TDOF	SDOx Data Output Fall Time		_	25	ns	
77	TssH2doZ	SSx ↑ to SDOx Output High-Impedar	nce	10	50	ns	
80	TscH2doV, TscL2doV	SDOx Data Output Valid after SCKx Edge		_	50	ns	
82	TssL2DoV	SDOx Data Output Valid after $\overline{\text{SSx}} \downarrow \text{Edge}$		_	50	ns	
83	TscH2ssH, TscL2ssH	SSx ↑ after SCKx Edge	1.5 Tcy + 40	_	ns		

**Note 1:** Requires the use of Parameter #73A.


2: Only if Parameter #71A and #72A are used.



### TABLE 27-20: I<sup>2</sup>C<sup>™</sup> BUS START/STOP BITS REQUIREMENTS (SLAVE MODE)

Param. No.	Symbol	Characte	Characteristic		Max	Units	Conditions	
90	TSU:STA	Start Condition	100 kHz mode	4700	_	ns	Only relevant for Repeated	
		Setup Time	400 kHz mode	600	_		Start condition	
91	THD:STA	Start Condition	100 kHz mode	4000	_	ns	After this period, the first	
		Hold Time	400 kHz mode	600	_		clock pulse is generated	
92	Tsu:sto	Stop Condition	100 kHz mode	4700	—	ns		
		Setup Time	400 kHz mode	600	_			
93	THD:STO	Stop Condition	100 kHz mode	4000	_	ns		
		Hold Time	400 kHz mode	600	_			

### FIGURE 27-16: I<sup>2</sup>C<sup>™</sup> BUS DATA TIMING



© 2007 Microchip Technology Inc.

Param. No.	Symbol	Characteris	stic	Min	Max	Units	Conditions
100	Тнідн	Clock High Time	100 kHz mode	4.0	_	μS	PIC18F97J60 family must operate at a minimum of 1.5 MHz
			400 kHz mode	0.6	_	μS	PIC18F97J60 family must operate at a minimum of 10 MHz
			MSSP module	1.5 TCY	_		
101	TLOW		100 kHz mode	4.7	—	μS	PIC18F97J60 family must operate at a minimum of 1.5 MHz
			400 kHz mode	1.3	—	μS	PIC18F97J60 family must operate at a minimum of 10 MHz
			MSSP module	1.5 TCY	_		
102	TR	SDAx and SCLx Rise	100 kHz mode	—	1000	ns	
		Time	400 kHz mode	20 + 0.1 Св	300	ns	CB is specified to be from 10 to 400 pF
103	TF	SDAx and SCLx Fall	100 kHz mode	—	300	ns	
		Time	400 kHz mode	20 + 0.1 Св	300	ns	CB is specified to be from 10 to 400 pF
90	TSU:STA	Start Condition Setup	100 kHz mode	4.7	—	μS	Only relevant for Repeated
		Time	400 kHz mode	0.6	—	μS	Start condition
91	THD:STA	Start Condition Hold	100 kHz mode	4.0	_	μS	After this period, the first
		Time	400 kHz mode	0.6	—	μS	clock pulse is generated
106	THD:DAT	Data Input Hold Time	100 kHz mode	0	_	ns	
			400 kHz mode	0	0.9	μS	
107	TSU:DAT	Data Input Setup Time	100 kHz mode	250	—	ns	(Note 2)
			400 kHz mode	100	_	ns	
92	Tsu:sto	Stop Condition Setup	100 kHz mode	4.7	—	μS	
		Time	400 kHz mode	0.6	—	μS	
109	ΤΑΑ	Output Valid from Clock	100 kHz mode	—	3500	ns	(Note 1)
			400 kHz mode			ns	
110	TBUF	Bus Free Time	100 kHz mode	4.7	_	μS	Time the bus must be free
			400 kHz mode	1.3	—	μS	before a new transmission can start
D102	Св	Bus Capacitive Loading		_	400	pF	

### TABLE 27-21:I<sup>2</sup>C™ BUS DATA REQUIREMENTS (SLAVE MODE)

**Note 1:** As a transmitter, the device must provide this internal minimum delay time to bridge the undefined region (min. 300 ns) of the falling edge of SCLx to avoid unintended generation of Start or Stop conditions.

2: A Fast mode I<sup>2</sup>C<sup>™</sup> bus device can be used in a Standard mode I<sup>2</sup>C bus system, but the requirement, TSU:DAT ≥ 250 ns, must then be met. This will automatically be the case if the device does not stretch the LOW period of the SCLx signal. If such a device does stretch the LOW period of the SCLx signal, it must output the next data bit to the SDAx line,

TR max. + TSU:DAT = 1000 + 250 = 1250 ns (according to the Standard mode I<sup>2</sup>C bus specification), before the SCLx line is released.







TABLE 27-22: MASTER SSP I<sup>2</sup>C<sup>™</sup> BUS START/STOP BITS REQUIREMENTS

Param. No.	Symbol	Characte	eristic	Min	Max	Units	Conditions	
90	Tsu:sta	Start Condition	100 kHz mode	2(Tosc)(BRG + 1)		ns	Only relevant for	
		Setup Time	400 kHz mode	2(Tosc)(BRG + 1)	_		Repeated Start	
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	_		condition	
91	THD:STA	Start Condition	100 kHz mode	2(Tosc)(BRG + 1)	_	ns	After this period, the	
		Hold Time	400 kHz mode	2(Tosc)(BRG + 1)	_		first clock pulse is	
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	_		generated	
92	Tsu:sto	Stop Condition	100 kHz mode	2(Tosc)(BRG + 1)	_	ns		
		Setup Time	400 kHz mode	2(Tosc)(BRG + 1)	_			
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	_			
93	THD:STO	Stop Condition	100 kHz mode	2(Tosc)(BRG + 1)	_	ns		
		Hold Time	400 kHz mode	2(Tosc)(BRG + 1)	_	1		
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	_			

**Note 1:** Maximum pin capacitance = 10 pF for all  $I^2C^{TM}$  pins.

#### FIGURE 27-18: MASTER SSP I<sup>2</sup>C<sup>™</sup> BUS DATA TIMING



Param. No.	Symbol	Charac	teristic	Min	Max	Units	Conditions	
100	Тнідн	Clock High Time	100 kHz mode	2(Tosc)(BRG + 1)	—	ms		
			400 kHz mode	2(Tosc)(BRG + 1)	_	ms		
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	_	ms		
101	TLOW	Clock Low Time	100 kHz mode	2(Tosc)(BRG + 1)	—	ms		
			400 kHz mode	2(Tosc)(BRG + 1)	_	ms		
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	_	ms		
102	TR	SDAx and SCLx	100 kHz mode	—	1000	ns	CB is specified to be from	
		Rise Time	400 kHz mode	20 + 0.1 Св	300	ns	10 to 400 pF	
			1 MHz mode <sup>(1)</sup>	—	300	ns		
103	TF	SDAx and SCLx	100 kHz mode	—	300	ns	CB is specified to be from	
		Fall Time	400 kHz mode	20 + 0.1 Св	300	ns	10 to 400 pF	
			1 MHz mode <sup>(1)</sup>	_	100	ns		
90	TSU:STA	Start Condition	100 kHz mode	2(Tosc)(BRG + 1)	—	ms	Only relevant for	
		Setup Time	400 kHz mode	2(Tosc)(BRG + 1)	_	ms	Repeated Start	
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	_	ms	condition	
91 THD:S	THD:STA	Start Condition	100 kHz mode	2(Tosc)(BRG + 1)	—	ms	After this period, the first	
		Hold Time	400 kHz mode	2(Tosc)(BRG + 1)	_	ms	clock pulse is generated	
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	_	ms		
106	THD:DAT	Data Input	100 kHz mode	0	_	ns		
		Hold Time	400 kHz mode	0	0.9	ms		
			1 MHz mode <sup>(1)</sup>	TBD	—	ns		
107	TSU:DAT	Data Input	100 kHz mode	250	_	ns	(Note 2)	
		Setup Time	400 kHz mode	100	—	ns		
			1 MHz mode <sup>(1)</sup>	TBD	—	ns		
92	Tsu:sto	Stop Condition	100 kHz mode	2(Tosc)(BRG + 1)	_	ms		
		Setup Time	400 kHz mode	2(Tosc)(BRG + 1)	—	ms		
			1 MHz mode <sup>(1)</sup>	2(Tosc)(BRG + 1)	—	ms		
109	Таа	Output Valid	100 kHz mode	—	3500	ns		
		from Clock	400 kHz mode	_	1000	ns		
			1 MHz mode <sup>(1)</sup>	_	—	ns		
110	TBUF	Bus Free Time	100 kHz mode	4.7	—	ms	Time the bus must be free	
			400 kHz mode	1.3	—	ms	before a new transmission	
			1 MHz mode <sup>(1)</sup>	TBD	—	ms	can start	
D102	Св	Bus Capacitive Lo	bading	—	400	pF		


### TABLE 27-23: MASTER SSP I<sup>2</sup>C™ BUS DATA REQUIREMENTS

Legend: TBD = To Be Determined

**Note 1:** Maximum pin capacitance = 10 pF for all  $I^2C^{TM}$  pins.

2: A Fast mode I<sup>2</sup>C bus device can be used in a Standard mode I<sup>2</sup>C bus system, but parameter #107 ≥ 250 ns must then be met. This will automatically be the case if the device does not stretch the LOW period of the SCLx signal. If such a device does stretch the LOW period of the SCLx signal, it must output the next data bit to the SDAx line, parameter #102 + parameter #107 = 1000 + 250 = 1250 ns (for 100 kHz mode), before the SCLx line is released.


### FIGURE 27-19: EUSARTx SYNCHRONOUS TRANSMISSION (MASTER/SLAVE) TIMING



#### TABLE 27-24: EUSARTx SYNCHRONOUS TRANSMISSION REQUIREMENTS

Param No.	Symbol	Characteristic	Min	Max	Units	Conditions
120	TCKH2DTV	SYNC XMIT (MASTER and SLAVE) Clock High to Data Out Valid	_	40	ns	
121	TCKRF	Clock Out Rise Time and Fall Time (Master mode)	—	20	ns	
122	TDTRF	Data Out Rise Time and Fall Time	_	20	ns	

#### FIGURE 27-20: EUSARTx SYNCHRONOUS RECEIVE (MASTER/SLAVE) TIMING



#### TABLE 27-25: EUSARTx SYNCHRONOUS RECEIVE REQUIREMENTS


Param. No.	Symbol	Characteristic	Min	Max	Units	Conditions
125	TDTV2CKL	SYNC RCV (MASTER and SLAVE) Data Hold before $CKx \downarrow (DTx hold time)$	10	_	ns	
126	TCKL2DTL	Data Hold after CKx $\downarrow$ (DTx hold time)	15		ns	

Param No.	Symbol	Characteristic	Min	Тур	Мах	Units	Conditions
A01	NR	Resolution	_	_	10	bit	$\Delta VREF \ge 2.0V$
A03	EIL	Integral Linearity Error	_		<±1	LSb	$\Delta VREF \ge 2.0V$
A04	Edl	Differential Linearity Error	_		<±1	LSb	$\Delta VREF \ge 2.0V$
A06	EOFF	Offset Error	_		<±3	LSb	$\Delta VREF \ge 2.0V$
A07	Egn	Gain Error	_		<±3	LSb	$\Delta VREF \ge 2.0V$
A10	_	Monotonicity	Guaranteed <sup>(1)</sup>			—	$VSS \le VAIN \le VREF$
A20	$\Delta V$ REF	Reference Voltage Range (VREFH – VREFL)	1.8 3	_		V V	$\begin{array}{l} V\text{DD} < 3.0\text{V} \\ \text{VDD} \geq 3.0\text{V} \end{array}$
	VREFSUM	Reference Voltage Sum (VREFH + VREFL)	_	—	AVDD + 0.5	V	
A21	VREFH	Reference Voltage High	VREFL		AVdd	V	
A22	VREFL	Reference Voltage Low	AVss		VREFH	V	
A25	VAIN	Analog Input Voltage	VREFL		VREFH	V	
A30	ZAIN	Recommended Impedance of Analog Voltage Source	_	—	2.5	kΩ	
A50	IREF	VREF Input Current <sup>(2)</sup>		_	5 1000	μΑ μΑ	During VAIN acquisition. During A/D conversion cycle.

### TABLE 27-26: A/D CONVERTER CHARACTERISTICS: PIC18F97J60 FAMILY (INDUSTRIAL)

**Note 1:** The A/D conversion result never decreases with an increase in the input voltage and has no missing codes.

2: VREFH current is from RA3/AN3/VREF+ pin or AVDD, whichever is selected as the VREFH source. VREFL current is from RA2/AN2/VREF- pin or AVss, whichever is selected as the VREFL source.



#### FIGURE 27-21: A/D CONVERSION TIMING

#### TABLE 27-27: A/D CONVERSION REQUIREMENTS

Param No.	Symbol	Characteristic	Min	Мах	Units	Conditions
130	Tad	A/D Clock Period	0.7	25.0 <sup>(1)</sup>	μS	Tosc based, VREF $\geq 2.0V$
			TBD	1	μS	A/D RC mode
131	TCNV	Conversion Time (not including acquisition time) (Note 2)	11	12	Tad	
132	TACQ	Acquisition Time (Note 3)	1.4		μS	-40°C to +85°C
135	Tswc	Switching Time from Convert $\rightarrow$ Sample	_	(Note 4)		
TBD	TDIS	Discharge Time	0.2	_	μS	

**Legend:** TBD = To Be Determined

Note 1: The time of the A/D clock period is dependent on the device frequency and the TAD clock divider.

- 2: ADRES registers may be read on the following TCY cycle.
- **3:** The time for the holding capacitor to acquire the "New" input voltage when the voltage changes full scale after the conversion (VDD to Vss or Vss to VDD). The source impedance (Rs) on the input channels is 50 $\Omega$ .
- 4: On the following cycle of the device clock.

### 27.5 Ethernet Specifications and Requirements


#### TABLE 27-28: REQUIREMENTS FOR ETHERNET TRANSCEIVER EXTERNAL MAGNETICS

Parameter	Min	Norm	Max	Units	Conditions
RX Turns Ratio		1:1	_		
TX Turns Ratio	_	1:1	—		Transformer Center Tap = 3.3V
Insertion Loss	_	—	-1.1	dB	
Primary Inductance	350	—	—	μH	8 mA bias
Transformer Isolation	1.5	_	—	kVrms	Required to meet IEEE 802.3 requirements
Differential to Common-Mode Rejection	40	—	—	dB	0.1 to 10 MHz
Return Loss	-16	—	—	dB	

NOTES:

### 28.0 PACKAGING INFORMATION

### 28.1 Package Marking Information




### 28.2 Package Details

The following sections give the technical details of the packages.

#### 64-Lead Plastic Thin Quad Flatpack (PT) – 10x10x1 mm Body, 2.00 mm Footprint [TQFP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



#### Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Chamfers at corners are optional; size may vary.

3. Dimensions D1 and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25 mm per side.

4. Dimensioning and tolerancing per ASME Y14.5M.


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-085B

#### 80-Lead Plastic Thin Quad Flatpack (PT) – 12x12x1 mm Body, 2.00 mm Footprint [TQFP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units	MILLIMETERS		
Din	nension Limits	MIN	NOM	MAX
Number of Leads	N	80		
Lead Pitch	е	0.50 BSC		
Overall Height	А	-	-	1.20
Molded Package Thickness	A2	0.95	1.00	1.05
Standoff	A1	0.05	-	0.15
Foot Length	L	0.45	0.60	0.75
Footprint	L1		1.00 REF	
Foot Angle	φ	0°	3.5°	7°
Overall Width	E	14.00 BSC		
Overall Length	D	14.00 BSC		
Molded Package Width	E1	12.00 BSC		
Molded Package Length	D1	12.00 BSC		
Lead Thickness	С	0.09	-	0.20
Lead Width	b	0.17	0.22	0.27
Mold Draft Angle Top	α	11°	12°	13°
Mold Draft Angle Bottom	β	11°	12°	13°

#### Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Chamfers at corners are optional; size may vary.

3. Dimensions D1 and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25 mm per side.


- 4. Dimensioning and tolerancing per ASME Y14.5M.
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-092B

### 100-Lead Plastic Thin Quad Flatpack (PT) – 12x12x1 mm Body, 2.00 mm Footprint [TQFP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Chamfers at corners are optional; size may vary.

3. Dimensions D1 and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25 mm per side.


- 4. Dimensioning and tolerancing per ASME Y14.5M.
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-100B

#### 100-Lead Plastic Thin Quad Flatpack (PF) – 14x14x1 mm Body, 2.00 mm Footprint [TQFP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Chamfers at corners are optional; size may vary.

3. Dimensions D1 and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25 mm per side.

- 4. Dimensioning and tolerancing per ASME Y14.5M.
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-110B

NOTES:

### 29.0 DC AND AC CHARACTERISTICS GRAPHS AND TABLES

Graphs and tables are not available at this time.

NOTES:

### APPENDIX A: REVISION HISTORY

### Revision A (March 2006)

Original data sheet for the PIC18F97J60 family of devices.

#### Revision B (October 2006)

First revision. Includes preliminary electrical specifications; revised and updated material on the Ethernet module; updated material on Reset integration; and updates to the device memory map.

### Revision C (June 2007)

Corrected Table 10.2: Input Voltage Levels; added content on Ethernet module's reading and writing to the buffer; added new, 100-lead PT 12x12x1 mm TQFP package to "Package Marking Information" and "Package Details" sections; updated other package details drawings; changed Product Identification System examples.

### APPENDIX B: DEVICE DIFFERENCES

The differences between the devices listed in this data sheet are shown in Table B-1.

### TABLE B-1: DEVICE DIFFERENCES BETWEEN PIC18F97J60 FAMILY MEMBERS

Features	PIC18F66J60	PIC18F66J65	PIC18F67J60	PIC18F86J60	PIC18F86J65	PIC18F87J60	PIC18F96J60	PIC18F96J65	PIC18F97J60
Program Memory (Bytes)	64K	96K	128K	64K	96K	128K	64K	96K	128K
Program Memory (Instructions)	32764	49148	65532	32764	49148	65532	32764	49148	65532
Interrupt Sources	26		27		29				
I/O Ports (Pins)	Ports A	, B, C, D, (39)	E, F, G	Ports A, I	3, C, D, E, (55)	F, G, H, J	Ports A, B, C, D, E, F, G, H, J (70)		
Enhanced USART Modules		1		2					
MSSP Modules				1 2					
Parallel Slave Port Communications (PSP)	No			Yes					
External Memory Bus	No			Yes					
10-Bit Analog-to-Digital Module	11 input channels 15 input channels		nels	16 input channels					
Packages	6	4-pin TQF	P	80-pin TQFP 100-pin TQFP		-P			

NOTES:

### INDEX

Α

A/D	325
A/D Converter Interrupt, Configuring	329
Acquisition Requirements	
ADCAL Bit	
ADCON0 Register	325
ADCON1 Register	
ADCON2 Register	
ADRESH Register	
ADRESL Register	
Analog Port Pins, Configuring	
Associated Registers	
Automatic Acquisition Time	
Configuring the Module	
Conversion Clock (TAD)	
Conversion Requirements	
Conversion Status (GO/DONE Bit)	
Conversions	
Converter Calibration	
Converter Characteristics	
Operation in Power-Managed Modes	
Special Event Trigger (ECCP)	
Use of the ECCP2 Trigger	
Absolute Maximum Ratings	
AC (Timing) Characteristics	427
Load Conditions for Device Timing	
Specifications	
Parameter Symbology	427
Temperature and Voltage	
Specifications	
Timing Conditions	
Access Bank	93
ACKSTAT	
ACKSTAT Status Flag	290
ADCAL Bit	333
ADCON0 Register	325
GO/DONE Bit	328
ADCON1 Register	325
ADCON2 Register	325
ADDFSR	402
ADDLW	365
ADDULNK	402
ADDWF	
ADDWFC	366
ADRESH Register	
ADRESL Register	
Affected Instructions	
Analog-to-Digital Converter. See A/D.	
ANDLW	366
ANDWF	
Assembler	001
MPASM Assembler	410
	-10
В	
Baud Rate Generator	286
BC	
BCF	
BF	
BF Status Flag	
0	<b>∠</b> 90
Block Diagrams	111
16-Bit Byte Select Mode	
16-Bit Byte Write Mode	
16-Bit Word Write Mode	110

8-Bit Multiplexed Mode	113
A/D	
Analog Input Model	
Baud Rate Generator	
Capture Mode Operation	
Comparator Analog Input Model	
Comparator I/O Operating Modes	336
Comparator Output	
Comparator Voltage Reference	
Comparator Voltage Reference Output	
Buffer Example	343
Compare Mode Operation	
Connections for On-Chip Voltage Regulator	
Device Clock	
Enhanced PWM	
Ethernet Interrupt Logic	
Ethernet Module	
EUSARTx Receive	
EUSARTx Transmit	
External Power-on Reset Circuit	
(Slow VDD Power-up)	55
Fail-Safe Clock Monitor	
Generic I/O Port Operation	
Interrupt Logic	
MSSP (I <sup>2</sup> C Master Mode)	284
MSSP (I <sup>2</sup> C Mode)	
MSSP (SPI Mode)	
On-Chip Reset Circuit	
PIC18F66J60/66J65/67J60	
PIC18F86J60/86J65/87J60	
PIC18F96J60/96J65/97J60	
PORTD and PORTE (Parallel Slave Port)	
PWM Operation (Simplified)	
Reads from Flash Program Memory	99
Reads from Flash Program Memory Required External Components for Ethernet	99 207
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator	
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation	
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation	99 
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory	99 207 337 95 96 91
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode	99 207 337 95 96 96 101 164
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode	99 207 337 95 96 101 164 164
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1	99 207 337 95 96 101 164 164 164 168
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 Timer1 (16-Bit Read/Write Mode)	99 207 337 95 96 101 164 164 164 168 168
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 Timer1 Timer2	99 207 337 95 96 101 164 164 164 168 168 174
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 Timer1 Timer2 Timer3	99 207 337 95 96 101 164 164 164 168 168 168 174
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode)	99 207 337 95 96 101 164 164 168 168 168 174 176 176
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 Timer1 Timer2 Timer3	99 207 337 95 96 101 164 164 168 168 168 174 176 176 180
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4	99 207 337 95 96 101 164 164 168 168 168 174 176 176 180 353
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 180 353 368
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BN.	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 180 353 368 369
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 180 353 368 369 369
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 180 353 368 369 369 370
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN BNOV	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 180 353 368 369 369 370
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN BNOV BNZ	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 180 353 368 369 369 369 370 370
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN BNC BNN BNOV BNZ BOR. See Brown-out Reset.	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 180 353 368 369 369 370 370 373
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 180 353 368 369 369 370 370 373
Reads from Flash Program Memory         Required External Components for Ethernet         Single Comparator         Table Read Operation         Table Write Operation         Table Write Sto Flash Program Memory         Timer0 in 16-Bit Mode         Timer1         Timer1         Timer2         Timer3         Timer3         Timer4         Watchdog Timer         BN         BNC         BNN         BNOV         BNZ         BOR. See Brown-out Reset.         BOV         BRA         BRG. See Baud Rate Generator.	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 180 353 368 369 369 370 370 370 373 371
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BNC BNC BNN BNOV BNOV BNZ BOR. See Brown-out Reset. BOV BRA	99 207 337 95 96 101 164 164 168 168 168 174 176 176 180 353 368 369 369 370 370 370 371 55
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN BNC BNN BNOV BNZ BOR. See Brown-out Reset. BOV BRA BRG. See Baud Rate Generator. Brown-out Reset (BOR)	99 207 337 95 96 101 164 164 168 168 168 174 176 176 180 353 368 369 369 369 370 370 370 371 55 354
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN BNC BNN BNC BNN BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC	99 207 337 95 96 101 164 164 168 168 168 168 174 176 176 180 353 368 369 369 370 370 370 371 55 55 354 55
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN BNC BNN BNOV BNZ BOR. See Brown-out Reset. BOV BRA BRG. See Baud Rate Generator. Brown-out Reset (BOR) and On-Chip Voltage Regulator Detecting	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 180 353 368 369 370 370 370 370 370 371 55 354 55 371
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 (16-Bit Read/Write Mode) Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC BNC .	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 176 353 368 369 370 370 370 370 370 371 355 354 55 371 372
Reads from Flash Program Memory Required External Components for Ethernet Single Comparator Table Read Operation Table Write Operation Table Writes to Flash Program Memory Timer0 in 16-Bit Mode Timer0 in 8-Bit Mode Timer1 Timer1 (16-Bit Read/Write Mode) Timer2 Timer3 (16-Bit Read/Write Mode) Timer3 (16-Bit Read/Write Mode) Timer4 Watchdog Timer BN BNC BNN BNOV BNN BNOV BNC BNN BNOV BNR BOR. See Brown-out Reset. BOV BRA BRG. See Baud Rate Generator. Brown-out Reset (BOR) and On-Chip Voltage Regulator Detecting BTFSC	99 207 337 95 96 101 164 164 168 168 168 174 176 176 176 176 180 353 368 369 370 370 370 370 370 371 55 354 55 371 372 372

### С

C Compilers	
MPLAB C18	410
MPLAB C30	410
CALL	374
CALLW	
Capture (CCP Module)	
· · · · · · · · · · · · · · · · · · ·	
Associated Registers	
CCPRxH:CCPRxL Registers	
CCPx Pin Configuration	
Prescaler	183
Software Interrupt	183
Timer1/Timer3 Mode Selection	
Capture (ECCP Module)	
Capture/Compare/PWM (CCP)	181
Capture Mode. See Capture.	
CCPRxH Register	182
CCPRxL Register	182
CCPx/ECCPx Interconnect Configurations	
CCPx/ECCPx Mode and Timer Resources	
	102
Compare Mode. See Compare.	
Module Configuration	182
Clock Sources	
Default System Clock on Reset	44
Effects of Power-Managed Modes	
•	
Oscillator Switching	
CLRF	
CLRWDT	375
Code Examples	
16 x 16 Signed Multiply Routine	118
16 x 16 Unsigned Multiply Routine	
8 x 8 Signed Multiply Routine	
8 x 8 Unsigned Multiply Routine	117
Changing Between Capture Prescalers	183
Computed GOTO Using an Offset Value	
Erasing a Flash Program Memory Row	
Fast Register Stack	
	73
How to Clear RAM (Bank 1) Using	
Indirect Addressing	88
Implementing a Real-Time Clock Using	
a Timer1 Interrupt Service	171
Initializing PORTA	
Initializing PORTB	
Initializing PORTC	
Initializing PORTD	144
Initializing PORTE	147
Initializing PORTF	
Initializing PORTG	
Initializing PORTH	
Initializing PORTJ	
Loading the SSP1BUF (SSP1SR) Register	258
Reading a Flash Program Memory Word	
Saving STATUS, WREG and BSR Registers	
	404
in RAM	
Writing to Flash Program Memory	
Code Protection	345
COMF	376
Comparator	
Analog Input Connection Considerations	
Associated Registers	
Configuration	336
Effects of a Reset	338
Interrupts	
Operation	
Operation During Sleep	ააგ

Outputs	337
Reference	337
External Signal	337
Internal Signal	337
Response Time	337
Comparator Specifications	426
Comparator Voltage Reference	341
Accuracy and Error	342
Associated Registers	343
Configuring	
Connection Considerations	342
Effects of a Reset	342
Operation During Sleep	342
Compare (CCP Module)	184
Associated Registers	185
CCPRx Register	184
CCPx Pin Configuration	184
Software Interrupt	
Timer1/Timer3 Mode Selection	184
Compare (ECCP Module)	102
	192
Special Event Trigger	
	92, 332
Special Event Trigger 19	92, 332 73
Special Event Trigger	92, 332 73 345
Special Event Trigger	92, 332 73 345 55
Special Event Trigger	92, 332 73 345 55
Special Event Trigger	92, 332 73 345 55 358
Special Event Trigger	92, 332 73 345 55 358 7 7
Special Event Trigger	92, 332 73 345 55 358 7 7
Special Event Trigger	92, 332 73 345 55 358 7 7 7
Special Event Trigger	92, 332 73 345 55 358 7 7 7 7
Special Event Trigger	92, 332
Special Event Trigger	92, 332 73 345 55 358 7 7 7 7 7 7 7 
Special Event Trigger       19         Computed GOTO       19         Configuration Bits       19         Configuration Mismatch (CM) Reset       19         Configuration Register Protection       10         Core Features       19         Easy Migration       19         Expanded Memory       19         Extended Instruction Set       19         External Memory Bus       0scillator Options         CPFSEQ       10	92, 332
Special Event Trigger       19         Computed GOTO       19         Configuration Bits       19         Configuration Mismatch (CM) Reset       19         Configuration Register Protection       10         Core Features       19         Easy Migration       19         Expanded Memory       19         Extended Instruction Set       19         External Memory Bus       0scillator Options         CPFSEQ       10         CPFSGT       10	92, 332
Special Event Trigger       19         Computed GOTO	92, 332
Special Event Trigger       19         Computed GOTO	22, 332
Special Event Trigger       19         Computed GOTO	22, 332
Special Event Trigger       19         Computed GOTO	22, 332

### D

88
92
88
88
88
76
80
90
77
79
79
80
378
455

DC Characteristics	423
Power-Down and Supply Current	416
Supply Voltage	
DCFSNZ	379
DECF	378
DECFSZ	379
Default System Clock	
Development Support	409
Device Differences	
Device Overview	7
Details on Individual Family Members	8
Features (100-Pin Devices)	10
Features (64-Pin Devices)	9
Features (80-Pin Devices)	
Direct Addressing	

### Е

ECCP2	
Pin Assignment	182
Effect on Standard PIC Instructions	
Electrical Characteristics	413
Requirements for Ethernet Transceiver	
External Magnetics	447
Enhanced Capture/Compare/PWM (ECCP)	189
Associated Registers	204
Capture and Compare Modes	192
Capture Mode. See Capture (ECCP Module).	
ECCP1/ECCP3 Outputs and	
Program Memory Mode	190
ECCP2 Outputs and Program	
Memory Modes	
Enhanced PWM Mode	
Outputs and Configuration	
Pin Configurations for ECCP1	
Pin Configurations for ECCP2	
Pin Configurations for ECCP3	192
PWM Mode. See PWM (ECCP Module).	400
Standard PWM Mode	
Timer Resources Use of CCP4/CCP5 with ECCP1/ECCP3	
Enhanced Universal Synchronous Asynchronous	
Receiver Transmitter (EUSART). See EUSART	
Receiver Transmiller (EUSART). See EUSART	
ENVREG pin	
Equations	354
Equations A/D Acquisition Time	354 330
Equations A/D Acquisition Time A/D Minimum Charging Time	354 330
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required	354 330 330
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time	354 330 330 330
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time	354 330 330 330 239 240
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller Associated Registers, Flow Control	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller	
Equations A/D Acquisition Time	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller Associated Registers, Flow Control Associated Registers, Reception Associated Registers, Transmission Buffer and Buffer Pointers	
Equations A/D Acquisition Time	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller Associated Registers, Flow Control Associated Registers, Reception Associated Registers, Transmission Buffer and Buffer Pointers Buffer Arbiter DMA Access	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller Associated Registers, Flow Control Associated Registers, Reception Associated Registers, Transmission Buffer and Buffer Pointers Buffer Arbiter DMA Access Receive Buffer	
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller Associated Registers, Flow Control Associated Registers, Reception Associated Registers, Transmission Buffer and Buffer Pointers Buffer Arbiter DMA Access Receive Buffer Transmit Buffer	354 330 330 239 240 6 205 252 244 241 241 241 209 212 212 212 211 212
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller Associated Registers, Flow Control Associated Registers, Reception Associated Registers, Transmission Buffer and Buffer Pointers Buffer Arbiter DMA Access Receive Buffer Transmit Buffer Buffer and Register Spaces	354 330 330 239 240 6 205 252 244 241 241 241 209 212 212 212 212 212 212 212 208
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller Associated Registers, Flow Control Associated Registers, Reception Associated Registers, Transmission Buffer and Buffer Pointers Buffer Arbiter DMA Access Receive Buffer Transmit Buffer Buffer and Register Spaces Buffer Organization	354 330 330 239 240 6 205 252 244 241 241 241 209 212 212 212 212 212 212 212 212 212 21
Equations A/D Acquisition Time A/D Minimum Charging Time Calculating the A/D Minimum Required Acquisition Time Random Access Address Calculation Receive Buffer Free Space Calculation Errata Ethernet Module Associated Registers, Direct Memory Access Controller Associated Registers, Flow Control Associated Registers, Reception Associated Registers, Transmission Buffer and Buffer Pointers Buffer Arbiter DMA Access Receive Buffer Transmit Buffer Buffer and Register Spaces	354 330 330 239 240 6 205 252 244 241 241 241 209 212 212 212 212 212 212 212 212 212 21

	Direct Memory Access Controller	251
	Checksum Calculations	252
	Copying Memory	251
	Disabling	232
	Duplex Mode Configuration and Negotiation	242
	Ethernet and Microcontroller	
	Memory Relationship	208
	Ethernet Control Registers	213
	Flow Control	243
	Initializing	231
	Interrupts	225
	Interrupts and Wake-on-LAN	230
	LED Configuration	206
	MAC and MII Registers	
	Magnetics, Termination and Other	
	External Components	207
	Oscillator Requirements	
	Packet Format	
	Per-Packet Control Bytes	
	PHSTAT Registers	
	PHY Register Summary	
	PHY Registers	
	PHY Start-up Timer	
	Receive Filters	
	Broadcast	
	Hash Table	
	Magic Packet	
	Multicast	
	Pattern Match	
	Unicast	
	Resets	
	Microcontroller Reset	
	Receive Only Transmit Only	
	Signal and Power Interfaces	
	Special Function Registers (SFRs)	
	Transmitting and Receiving Data	
	Packet Field Definitions	
	Reading Received Packets	
	Receive Buffer Space	
	Receive Packet Layout	
	Receive Status Vectors	
	Receiving Packets	
	Transmit Packet Layout	
	Transmit Status Vectors	237
	Transmitting Packets	
	ernet Operation, Microcontroller Clock	41
EUS	SARTx	
	Asynchronous Mode	
	Associated Registers, Receive	
	Associated Registers, Transmit	
	Auto-Wake-up on Sync Break Character	
	Break Character Sequence	
	Receiving	318
	Receiver	
	Setting Up 9-Bit Mode with Address Detect	
	Transmitter	311
	Baud Rate Generator	
	Operation in Power-Managed Modes	305
	Baud Rate Generator (BRG)	305
	Associated Registers	306
	Auto-Baud Rate Detect	309
	Baud Rate Error, Calculating	
	Baud Rates, Asynchronous Modes	307
	High Baud Rate Select (BRGH Bit)	305
	Sampling	305

Synchronous Master Mode	
Associated Registers, Receive	
Associated Registers, Transmit	320
Reception	321
Transmission	
Synchronous Slave Mode	
Associated Registers, Receive	
Associated Registers, Transmit	323
Reception	323
Transmission	322
Extended Instruction Set	
ADDFSR	402
ADDULNK	402
CALLW	403
MOVSF	403
MOVSS	404
PUSHL	404
SUBFSR	405
SUBULNK	
External Clock Input (EC Modes)	40
External Memory Bus	
16-Bit Byte Select Mode	
16-Bit Byte Write Mode	109
16-Bit Data Width Modes	108
16-Bit Mode Timing	
16-Bit Word Write Mode	110
21-Bit Addressing	
8-Bit Data Width Mode	113
8-Bit Mode Timing	114
Address and Data Line Usage (table)	107
Address and Data Width	107
Address Shifting	107
Control	
I/O Port Functions	
Operation in Power-Managed Modes	115
Program Memory Modes	108
Extended Microcontroller	108
Microcontroller	108
Wait States	
Weak Pull-ups on Port Pins	108

### F

Fail-Safe Clock Monitor and the Watchdog Timer Exiting Operation	
Interrupts in Power-Managed Modes	
POR or Wake-up From Sleep	
Fast Register Stack	
Firmware Instructions	359
Flash Configuration Words	68, 345
Flash Program Memory	95
Associated Registers	103
Control Registers	96
EECON1 and EECON2	96
TABLAT (Table Latch) Register	
TBLPTR (Table Pointer) Register	
Erase Sequence	100
Erasing	100
Operation During Code-Protect	103
Reading	99
Table Pointer	
Boundaries Based on Operation	
Table Pointer Boundaries	
Table Reads and Table Writes	95
Write Sequence	

Writing	
Protection Against Spurious Writes	
Unexpected Termination	
Write Verify	103
FSCM. See Fail-Safe Clock Monitor.	
G	
с GOTO	380
	000
н	
Hardware Multiplier	117
Introduction	117
Operation	
Performance Comparison	117
I/O Ports	125
Pin Capabilities	
<sup>2</sup> C Mode (MSSP)	265
Acknowledge Sequence Timing	200
Associated Registers	
Baud Rate Generator	
Bus Collision	
During a Repeated Start Condition	297
During a Stop Condition	
Clock Arbitration	
Clock Rate w/BRG	
Clock Stretching	279
10-Bit Slave Receive Mode (SEN = 1)	
10-Bit Slave Transmit Mode	
7-Bit Slave Receive Mode (SEN = 1)	
7-Bit Slave Transmit Mode	279
Clock Synchronization and the CKP Bit	280
Effects of a Reset	294
General Call Address Support	283
Master Mode	284
Baud Rate Generator	
Operation	285
Reception	
Repeated Start Condition Timing	
Start Condition Timing	
Transmission	290
Multi-Master Communication, Bus Collision	004
and Arbitration	
Multi-Master Mode Operation	
Read/Write Bit Information (R/W Bit)	
Registers	
Serial Clock (SCKx/SCLx)	
Slave Mode	
Address Masking	
Addressing	
Reception	
Transmission	
Sleep Operation	
Stop Condition Timing	
INCFSZ	
In-Circuit Debugger	358
In-Circuit Serial Programming (ICSP)	358
Indexed Literal Offset Addressing	
and Standard PIC18 Instructions	
Indexed Literal Offset Mode 91, 93,	406
BSR	
Indirect Addressing	. 89

INFSNZ	
Initialization Conditions for All Registers	
Instruction Cycle	
Clocking Scheme	
Flow/Pipelining	
Instruction Set	
ADDLW	
ADDWF (Indexed Literal Offset Mode)	
ADDWF (Indexed Literal Onset Mode)	
ANDLW	
ANDWF	
BC	
BCF	368
BN	368
BNC	369
BNN	369
BNOV	370
BNZ	370
BOV	373
BRA	
BSF	
BSF (Indexed Literal Offset Mode)	
BTFSC	
BTFSS	
BTG	
BZ	
CALL CLRF	
CLRWDT	
COMF	
CPFSEQ	
CPFSGT	
CPFSLT	
DAW	
DCFSNZ	
DECF	378
DECFSZ	379
Extended Instructions	
Considerations when Enabling	
Syntax	
Use with MPLAB IDE Tools	
General Format	
GOTO	
INCFSZ	
IORLW IORWF	
LESR	
MOVF	
MOVFF	
MOVLB	
MOVLW	
MOVWF	
MULLW	
MULWF	
NEGF	387
NOP	387
POP	388
PUSH	
RCALL	389
RESET	
RETFIE	
RETLW	390

RETURN	
RLCF	
RLNCF	
RRCF	
RRNCF	
SETF	
SETF (Indexed Literal Offset Mode)	
SLEEP	
Standard Instructions	
SUBFWB	
SUBLW	
SUBWF	
SUBWFB	
SWAPF	
TBLRD	
TBLWT	
TSTFSZ	
XORLW	
XORWF	400
INTCON Register	
RBIF Bit	
INTCON Registers	121
Inter-Integrated Circuit. See I <sup>2</sup> C Mode.	
Internal Oscillator Block	41
Internal RC Oscillator	
Use with WDT	
Internal Voltage Regulator Specifications	
Internet Address	471
Interrupt Sources	
A/D Conversion Complete	329
Capture Complete (CCP)	
Compare Complete (CCP)	184
Interrupt-on-Change (RB7:RB4)	138
INTx Pin	
PORTB, Interrupt-on-Change	134
TMR0	134
TMR0 Overflow	165
TMR1 Overflow	167
TMR2 to PR2 Match (PWM)	193
TMR3 Overflow 175,	177
TMR4 to PR4 Match	180
TMR4 to PR4 Match (PWM)	179
Interrupts	119
Context Saving	134
Interrupts, Flag Bits	
Interrupt-on-Change (RB7:RB4) Flag	
(RBIF Bit)	138
INTRC. See Internal Oscillator Block.	
IORLW	382
IORWF	382
IPR Registers	130
L	
LFSR	383
M	
Master Clear (MCLR)	55
Master Synchronous Serial Port (MSSP). See MSSP.	
Memory Organization	67

MOVLB	
MOVLW	
MOVSF	
MOVSS	
MOVWF	
MPLAB ASM30 Assembler, Linker, Librarian	410
MPLAB ICD 2 In-Circuit Debugger	411
MPLAB ICE 2000 High-Performance	
Universal In-Circuit Emulator	411
MPLAB Integrated Development	
Environment Software	
MPLAB PM3 Device Programmer	
MPLAB REAL ICE In-Circuit Emulator System	411
MPLINK Object Linker/MPLIB Object Librarian	410
MSSP	
ACK Pulse	
Control Registers (general)	
Module Overview	
SPI Master/Slave Connection	
SSPxBUF Register	
SSPxSR Register	
MULLW	
MULWF	
Ν	
NEGF	207
NOP	
0	
Opcode Field Descriptions	360
Organizationally Unique Identifier (OUI)	
Oscillator Configuration	39
EC	
ECPLL	
HS	
HSPLL	
Internal Oscillator Block	

Internal Oscillator Block	41
INTRC	
Oscillator Selection	
Oscillator Start-up Timer (OST)	44
Oscillator Transitions	44
Oscillator, Timer1	167, 177
Oscillator, Timer3	
OUI. See Organizationally Unique Identifier.	

### Ρ

Packaging	
Details	
Marking	
Parallel Slave Port (PSP)	
Associated Registers	
PORTD	
Select (PSPMODE Bit)	
PICSTART Plus Development Programmer	
PIE Registers	
Pin Functions	
AVDD	
AVss	
ENVREG	
MCLR	
OSC1/CLKI	
OSC2/CLKO	
RA0/LEDA/AN0	
RA1/LEDB/AN1	
RA2/AN2/VREF	
RA3/AN3/VREF+	
	, ,

RA4/T0CKI	, , -
RA5/AN4	
RB0/INT0/FLT0	15, 22, 30
RB1/INT1	
RB2/INT2	15, 22, 30
RB3/INT3	
RB3/INT3/ECCP2/P2A	30
RB4/KBI0	15, 22, 30
RB5/KBI1	15, 22, 30
RB6/KBI2/PGC	15, 22, 30
RB7/KBI3/PGD	
RBIAS	
RC0/T1OSO/T13CKI	
RC1/T10SI/ECCP2/P2A	
RC2/ECCP1/P1A	
RC3/SCK1/SCL1	
RC4/SDI1/SDA1	
RC5/SD01	
RC6/TX1/CK1	
RC7/RX1/DT1	
RD0	
RD0/AD0/PSP0	
RD0/P1B	
RD1	
RD1/AD1/PSP1	
RD1/ECCP3/P3A	
RD2	
RD2/AD2/PSP2	
RD2/CCP4/P3D	
RD3/AD3/PSP3	
RD4/AD4/PSP4/SDO2	
RD5/AD5/PSP5/SDI2/SDA2	
RD6/AD6/PSP6/SCK2/SCL2	32
RD7/AD7/PSP7/SS2	32
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D	32 33
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D	32 33 18, 24
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C	32 33 18, 24 33
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C	32 33 18, 24 33 18, 24
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B RE3/AD11/P3C RE3/P3C	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B RE3/AD11/P3C RE3/P3C RE4/AD12/P3B	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B RE3/AD11/P3C RE3/P3C RE4/AD12/P3B	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B RE3/AD11/P3C RE3/P3C	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B RE3/AD11/P3C RE3/P3C RE4/AD12/P3B RE4/P3B	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B RE3/AD11/P3C RE3/P3C RE4/AD12/P3B RE4/P3B RE5/AD13/P1C RE5/P1C	
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/AD14/P1B	
RD7/AD7/PSP7/SS2 RE0/AD8/RD/P2D RE0/P2D RE1/AD9/WR/P2C RE1/P2C RE2/AD10/CS/P2B RE2/P2B RE3/AD11/P3C RE3/P3C RE4/AD12/P3B RE4/P3B RE5/AD13/P1C RE5/P1C	
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE6/P1B         RE7/AD15/ECCP2/P2A	
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/ECCP2/P2A	
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/ECCP2/P2A         RE0/AN5	
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE1/AN5         RF1/AN6/C2OUT	32         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         24         33         24         33         24         34         19, 25, 34
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP1/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP1/P2A	32         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         24         33         24         33         24         34         19, 25, 34         19, 25, 34
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RF1/AN6/C2OUT         RF2/AN7/C10UT         RF3/AN8	32         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         24         33         24         33         24         33         24         33         24         34         19, 25, 34         19, 25, 34         19, 25, 34
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RF1/AN6/C2OUT         RF2/AN7/C1OUT         RF3/AN8         RF4/AN9	32         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         24         33         24         33         24         33         24         33         24         33         24         34         19, 25, 34         19, 25, 34         19, 25, 34         19, 25, 34
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/AD12/P3B         RE4/AD12/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/COUT         RF1/AN6/C2OUT         RF2/AN7/C10UT         RF3/AN8         RF4/AN9         RF5/AN10/CVREF	32         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         18, 24         33         24         33         24         33         24         33         24         33         24         34         19, 25, 34         19, 25, 34         19, 25, 34         19, 25, 34
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/P3C         RE4/AD12/P3B         RE4/P3B         RE5/AD13/P1C         RE6/AD14/P1B         RE6/P1B         RE7/AD15/ECCP2/P2A         RF1/AN6/C2OUT         RF2/AN7/C1OUT         RF3/AN8         RF4/AN9         RF5/AN10/CVREF         RF6/AN11	32 33 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 24 33 24 33 24 33 24 19, 25, 34 19, 25, 34 19, 25, 34 19, 25, 34 19, 25, 34
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE2/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE4/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP1/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP2/P2A         RE7/AD15/ECCP1/P2A         RE7/AD15/ECCP1/P2A	32 33 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 24 33 24 33 24 19, 25, 34 19, 25, 34 10, 25, 35
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/P3C         RE4/AD12/P3B         RE4/P3B         RE5/AD13/P1C         RE6/P1C         RE6/AD14/P1B         RE7/AD15/ECCP2/P2A         RE7/AN8         RF1/AN6/C2OUT         RF3/AN8         RF4/AN9         RF5/AN10/CVREF         RF6/AN11         RF7/SS1         RG0/ECCP3/P3A	32 33 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 18, 24 33 24 33 24 33 24 19, 25, 34 19, 25, 34 35 36 37 37 38 38 39 39 39 30 30 30 30 30 30 30 30 30 30
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE3/P3C         RE4/AD12/P3B         RE4/P3B         RE5/AD13/P1C         RE6/AD14/P1B         RE6/AD14/P1B         RE7/AD15/ECCP2/P2A         RF1/AN6/C2OUT         RF2/AN7/C1OUT         RF3/AN8         RF4/AN9         RF5/AN10/CVREF         RF6/AN11         RF7/SS1         RG0/ECCP3/P3A         RG1/TX2/CK2	32 33 33 33 34 35 36 36 37 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 37 38 38 39 39 39 39 39 39 39 30 30 30 30 30 30 30 30 30 30 30 30 30
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE2/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE3/AD11/P3C         RE3/AD11/P3C         RE3/P3C         RE4/AD12/P3B         RE4/P3B         RE5/AD13/P1C         RE5/P1C         RE6/AD14/P1B         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/ANS         RF1/AN6/C2OUT         RF2/AN7/C1OUT         RF3/AN8         RF4/AN9         RF5/AN10/CVREF         RF6/AN11         RF7/SS1         RG0/ECCP3/P3A         RG1/TX2/CK2         RG2/RX2/DT2	
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE1/AD9/WR/P2C         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE2/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE3/AD11/P3C         RE3/AD11/P3C         RE4/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AN10/CVREF         RE4/N9         RF4/AN9         RF5/AN10/CVREF         RE6/AN11         RF7/SS1         RG0/ECCP3/P3A         RG1/TX2/CK2         RG3/CCP4/P3D	$\begin{array}{cccccccccccccccccccccccccccccccccccc$
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE0/P2D         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE2/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE3/AD11/P3C         RE4/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AN10/CVREF         RE4/N9         RF4/AN9         RF4/AN9         RF5/AN10/CVREF         RE6/AN11         RF7/SS1         RG0/ECCP3/P3A         RG1/TX2/CK2         RG3/CCP4/P3D         RG4/CCP5/P1D	$\begin{array}{cccccccccccccccccccccccccccccccccccc$
RD7/AD7/PSP7/SS2         RE0/AD8/RD/P2D         RE1/AD9/WR/P2C         RE1/AD9/WR/P2C         RE1/P2C         RE2/AD10/CS/P2B         RE3/AD11/P3C         RE3/AD11/P3C         RE3/AD11/P3C         RE4/P3B         RE5/AD13/P1C         RE5/P1C         RE6/P1B         RE7/AD15/ECCP2/P2A         RE7/AN10/CVREF         RE6/AN11         RF5/AN10/CVREF         RE6/AN11         RE7/SS1         RG0/ECCP3/P3A         RG1/TX2/CK2         RG2/RX2/DT2         RG3/CCP4/P3D	$\begin{array}{cccccccccccccccccccccccccccccccccccc$

			_
	RG7	35	C
	RH0	27	7
	RH0/A16		
	RH1	27	7
	RH1/A17	36	3
	RH2	27	(
	RH2/A18	36	3
	RH3	21	(
	RH3/A19	36	3
	RH4/AN12/P3C	27 36	3
	RH5/AN13/P3B	27, 36	Ċ
	RH6/AN14/P1C	27.36	3
	RH7/AN15/P1B		
		'	
	RJ0/ALE	37	7
	RJ1/OE	37	7
	RJ2/WRL		
	RJ3/WRH	37	7
	RJ4	28	5
	RJ4/BA0	37	7
	RJ5	28	R
	RJ5/ <u>CE</u>	37	(
	RJ6/LB	37	7
	RJ7/UB		
	TPIN	28, 38	3
	TPIN+	28 38	R
	TPOUT	28, 38	3
	TPOUT+	28. 38	3
	VDD	'	
	VDDCORE/VCAP	28, 38	3
	VDDPLL	28 38	R
		'	
	VDDRX	28, 38	3
		20 20	2
	VDD1X	20. JC	5
	VDDTX		
	Vss	28, 38	3
		28, 38	3
	Vss	28, 38 28, 38	3
	Vss	28, 38 28, 38 28, 38	3
	Vss	28, 38 28, 38 28, 38	3
Pino	Vss         20,           VssPLL         20,           VssRX         20,           VssRX         20,           vssrx         20,           vssrx         20,           vssrx         20,	28, 38 28, 38 28, 38 28, 38 28, 38	888
Pino	Vss         20,           VssPLL         20,           VssRX         20,           VssRX         20,           vssrx         20,           vssrx         20,           vssrx         20,	28, 38 28, 38 28, 38 28, 38 28, 38	888
Pino	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSRX         20,           VSSTX         20,           ut I/O Descriptions         20,           PIC18F66J60/66J65/67J60	28, 38 28, 38 28, 38 28, 38 28, 38	3 3 3 3 4
Pino	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSTX         20,           vt I/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60	28, 38 28, 38 28, 38 28, 38 28, 38 14 21	3 3 3 3 4
Pino	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSTX         20,           vt I/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60	28, 38 28, 38 28, 38 28, 38 28, 38 14 21	3 3 3 3 4
	Vss         20,           VssPLL         20,           VssRX         20,           vsssrx </td <td>28, 38 28, 38 28, 38 28, 38 28, 38  14  21  29</td> <td>3 3 3 3 4 1 9</td>	28, 38 28, 38 28, 38 28, 38 28, 38 14 21 29	3 3 3 3 4 1 9
PIR	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSTX         20,           ut I/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60           PIC18F96J60/96J65/97J60         PIC18F96J60/96J65/97J60	28, 38 28, 38 28, 38 28, 38 28, 38 14 21 29 124	3 3 3 3 3 3 4 1 9 1
PIR	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSTX         20,           vtl/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60           PIC18F96J60/96J65/97J60         PIC18F96J60/96J65/97J60           Registers         Block	28, 38 28, 38 28, 38 28, 38 14 21 29 124 41	3334191
PIR	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSTX         20,           vtl/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60           PIC18F96J60/96J65/97J60         PIC18F96J60/96J65/97J60           Registers         Block	28, 38 28, 38 28, 38 28, 38 14 21 29 124 41	3334191
PIR I PLL	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSTX         20,           vtl/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60           PIC18F96J60/96J65/97J60         PIC18F96J60/96J65/97J60           Registers         Block           Clock Speeds for Various Configurations	28, 38 28, 38 28, 38 28, 38 14 21 21 29 124 41 42	333419412
PIR I PLL POP	Vss         20,           VssPLL         20,           VssRx         20,           vsssrx </td <td>28, 38 28, 38 28, 38 28, 38  14  21  21  29  124  41  42</td> <td>333419412</td>	28, 38 28, 38 28, 38 28, 38 14 21 21 29 124 41 42	333419412
PIR I PLL POP	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSTX         20,           vtl/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60           PIC18F96J60/96J65/97J60         PIC18F96J60/96J65/97J60           Registers         Block           Clock Speeds for Various Configurations	28, 38 28, 38 28, 38 28, 38 14 21 21 29 124 41 42	333419412
PIR I PLL POP POR	Vss         20,           VssPLL         20,           VssRx         20,           vsssrx </td <td>28, 38 28, 38 28, 38 28, 38  14  21  21  29  124  41  42</td> <td>333419412</td>	28, 38 28, 38 28, 38 28, 38 14 21 21 29 124 41 42	333419412
PIR I PLL POP	Vss         20,           VssPLL         20,           VssRx         20,           vsssrx </td <td>28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 20, 39 20, 39 20, 30 20, 30 20</td> <td>3333 4194123</td>	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 20, 39 20, 39 20, 30 20, 30 20	3333 4194123
PIR I PLL POP POR	Vss         20,           VssPLL         20,           VssRx         20,           vsspector         20,	28, 38 28, 38 28, 38 28, 38 28, 38 14 29 124 41 42 388 388	3333 4194123 7
PIR I PLL POP POR	Vss         20,           VssPLL         20,           VssRx         20,           vsspector         20,	28, 38 28, 38 28, 38 28, 38 28, 38 14 29 124 41 42 388 388	3333 4194123 7
PIR I PLL POP POR	Vss         20,           VssPLL         20,           VssRx         20,           vsssociated Registers         20,           strain         20,           vssociated Registers         20,           LATA Register         20,	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20	3333 4194123 75
PIR I PLL POP POR	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSTX         20,           vtl/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60           PIC18F96J60/96J65/97J60         PIC18F96J60/96J65/97J60           Registers         Block           Clock Speeds for Various Configurations         Clock Speeds for Various Configurations           X. See Power-on Reset.         TTA           Associated Registers         LATA Register           PORTA Register         PORTA Register	28, 38 28, 38 28, 38 28, 38 28, 38 14 29 124 41 42 388 137 136 136	3333 4194123 755
PIR I PLL POP POR	Vss         20,           VssPLL         20,           VssRx         20,           vsssociated Registers         20,           strain         20,           vssociated Registers         20,           LATA Register         20,	28, 38 28, 38 28, 38 28, 38 28, 38 14 29 124 41 42 388 137 136 136	3333 4194123 755
PIR I PLL POP POR	VSS         20,           VSSPLL         20,           VSSRX         20,           VSSRX         20,           VSSTX         20,           vtl/O Descriptions         20,           PIC18F66J60/66J65/67J60         PIC18F86J60/86J65/87J60           PIC18F96J60/96J65/97J60         PIC18F96J60/96J65/97J60           Registers         Block           Clock Speeds for Various Configurations         See Power-on Reset.           TTA         Associated Registers           LATA Register         PORTA Register           PORTA Register         TRISA Register	28, 38 28, 38 28, 38 28, 38 28, 38 14 29 124 41 42 388 137 136 136	3333 4194123 755
PIR I PLL POP POR POR	Vss         20,           VssPLL         20,           VssRx         20,           vsssrx </td <td>28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20</td> <td>3 3 3 3 3 4 1 9 4 1 2 3 7 5 5 5</td>	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20	3 3 3 3 3 4 1 9 4 1 2 3 7 5 5 5
PIR I PLL POP POR POR	Vss         20,           VssPLL         20,           VssRx         20,           vsspir         20,           Vssrx         20,           vsspir         20,           PlC18F66J60/66J65/67J60         PlC18F86J60/86J65/87J60           PlC18F96J60/96J65/97J60         Plc18F96J60/96J65/97J60           Registers         Slock           Clock Speeds for Various Configurations         Scieck           Clock Speeds for Various Configurations         Scieck           Clock Speeds for Various Configurations         Scieck           LTA         Associated Register         Plottataa           PORTA Register	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20	3 3 3 3 3 4 1 9 4 1 2 3 7 6 6 6 0
PIR I PLL POP POR POR	Vss         20,           VssPLL         20,           VssRx         20,           vsssrx </td <td>28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20</td> <td>3 3 3 3 3 4 1 9 4 1 2 3 7 6 6 6 0</td>	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20	3 3 3 3 3 4 1 9 4 1 2 3 7 6 6 6 0
PIR I PLL POP POR POR	Vss         20,           VssPLL         20,           VssRx         20,           vsssolisteds         20,           vssociated Registers         20,           vssociated Register         20,           vssociated Register         20,           vssociated Register         20,           vssociated Registers         20,           vssociated Registers         20,           Vssociated Register         20,           vssociated Register         20,           Vssociated Register         20,           Vsssociated Register         20,	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20	3 3 3 3 4 1 9 4 1 2 3 7 5 5 0 3
PIR I PLL POP POR POR	Vss         20,           VssPLL         20,           VssRx         20,           vsssociated Solo/66J65/67J60         PIC18F86J60/86J65/87J60           Registers         See Power-on Reset.           Clock Speeds for Various Configurations         See           Clock Speeds for Various Configurations         See           LATA Register         PORTA Register           TB         Associated Register           LATB Register         See           PORTB Register	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20	3 3 3 3 4 1 9 4 1 2 3 7 5 5 0 3
PIR I PLL POP POR POR	VSS	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20	3       3       3       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1
PIR I PLL POP POR POR	VSS	28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 29, 38 20, 30 20, 30 20	3       3       3       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1       1
PIR I PLL POP POR POR	VSS	28, 38 28, 38 29, 38 29, 38 20, 30 20, 30 20	3       3         3       3         4       1         2       3         7       5         5       3         3       3         3       3         4       1         2       3         7       5         5       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3
PIR I PLL POP POR POR	VSS	28, 38 28, 38 29, 38 29, 38 20, 30 20, 30 20	3       3         3       3         4       1         2       3         7       5         5       3         3       3         3       3         4       1         2       3         7       5         5       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3       3         3
PIR I PLL POP POR POR	VSS	28, 388 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 29, 39, 39, 39, 39, 39, 39, 39, 39, 39, 3	3333       4194123         7555       033333
PIR I PLL POP POR POR	VSS	28, 388 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 29, 39, 39, 39, 39, 39, 39, 39, 39, 39, 3	3333       4194123         7555       033333
PIR I PLL POP POR POR	VSS	28, 388 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 29, 39, 392 29, 392 39, 392 39, 392 39, 392 39, 392 39, 392 39, 392 39, 392 39, 392 39	3       3         3       3         4       1         2       7         5       5         3       3         3       3         4       1         2       7         5       5         5       3         3       3         3       3         3       3
PIR I PLL POP POR POR	VSS	28, 388 28, 382 28, 382 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 41 29 29 20 20 20 20 20 20 20 20 20 20 20 20 20	333       4       1       2       3         7       5       5       0       3       3         1       7       7       5       5       0       3       3       1
PIR I PLL POP POR POR	VSS	28, 388 28, 382 28, 382 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 28, 38 41 29 29 20 20 20 20 20 20 20 20 20 20 20 20 20	333       4       1       2       3         7       5       5       0       3       3         1       7       7       5       5       0       3       3       1
PIR I PLL POP POR POR	VSS	28, 388 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 29, 392 29, 39	3333         4194123         7666         033         311
PIR I PLL POP POR POR	Vss       20,         VssPLL       20,         VssRx       20,         vsssrx       20,         vssrx <td>28, 388 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 29, 392 29, 39</td> <td>3333       4194123         7666       03333112</td>	28, 388 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 29, 392 29, 39	3333       4194123         7666       03333112
PIR I PLL POP POR POR	VSS	28, 388 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 28, 382 29, 392 29, 39	3333       4194123         7666       03333112

PORTD	
Associated Registers	146
LATD Register	144
PORTD Register	
TRISD Register	144
PORTE	
Associated Registers	149
LATE Register	
PORTE Register	147
PSP Mode Select (PSPMODE Bit)	
RE0/AD8/RD/P2D Pin	
RE1/AD9/WR/P2C Pin	
RE2/AD10/CS/P2B Pin	
TRISE Register	
PORTF	
Associated Registers	151
LATF Register	
PORTF Register	
TRISF Register	
PORTG	
Associated Registers	154
LATG Register	
PORTG Register	
TRISG Register	
PORTH	
Associated Registers	156
LATH Register	
PORTH Register	
TRISH Register	
PORTJ	100
Associated Registers	158
LATJ Register	
PORTJ Register	
TRISJ Register	
Power-Managed Modes	
and SPI Operation	
Clock Sources	
Clock Transitions and Status Indicators	
Entering	
Exiting Idle and Sleep Modes	
By Interrupt	
By Reset	
By WDT Time-out	
Without an Oscillator Start-up Timer Delay .	
Idle Modes	
PRI IDLE	
RC IDLE	
SEC IDLE	
Multiple Sleep Commands	
Run Modes	
PRI RUN	
RC RUN	
SEC RUN	
Selecting	
Sleep Mode	
Sleep Mode	
Power-on Reset (POR)	
Power-up Timer (PWRT)	
Time-out Sequence	
Power-up Delays Power-up Timer (PWRT)	
Power-up Timer (PWRT) Prescaler	44, 00
Timer2	104
	194

Prescaler, Timer2 187
PRI_IDLE Mode50
PRI_RUN Mode46
Program Counter71
PCL, PCH and PCU Registers71
PCLATH and PCLATU Registers71
Program Memory
Extended Instruction Set90
Instructions75
Two-Word75
Interrupt Vector68
Look-up Tables73
Memory Maps67
Hard Vectors and Configuration Words68
Memory Maps, Modes70
Modes
Memory Access (table)70
Reset Vector68
Program Memory Modes69
Address Shifting (Extended Microcontroller)70
Extended Microcontroller69
Microcontroller69
Program Verification and Code Protection
Programming, Device Instructions
PSP.See Parallel Slave Port.
Pulse-Width Modulation. See PWM (CCP Module)
and PWM (ECCP Module).
PUSH
PUSH and POP Instructions72
PUSHL
PWM (CCP Module)
Associated Registers 188
Associated Registers
Duty Cycle
Duty Cycle
Duty Cycle       186         Example Frequencies/Resolutions       187         Operation Setup       187
Duty Cycle    186      Example Frequencies/Resolutions    187      Operation Setup    187      Period    186
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193
Duty Cycle       186         Example Frequencies/Resolutions       187         Operation Setup       187         Period       186         TMR2 to PR2 Match       193         TMR4 to PR4 Match       179         PWM (ECCP Module)       193         CCPR1H:CCPR1L Registers       193         Direction Change in Full-Bridge Output Mode       198
Duty Cycle       186         Example Frequencies/Resolutions       187         Operation Setup       187         Period       186         TMR2 to PR2 Match       193         TMR4 to PR4 Match       179         PWM (ECCP Module)       193         CCPR1H:CCPR1L Registers       193         Direction Change in Full-Bridge Output Mode       198         Duty Cycle       194
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203
Duty Cycle       186         Example Frequencies/Resolutions       187         Operation Setup       187         Period       186         TMR2 to PR2 Match       193         TMR4 to PR4 Match       179         PWM (ECCP Module)       193         CCPR1H:CCPR1L Registers       193         Direction Change in Full-Bridge Output Mode       198         Duty Cycle       194         Effects of a Reset       203         Enhanced PWM Auto-Shutdown       200
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194
Duty Cycle       186         Example Frequencies/Resolutions       187         Operation Setup       187         Period       186         TMR2 to PR2 Match       193         TMR4 to PR4 Match       179         PWM (ECCP Module)       193         CCPR1H:CCPR1L Registers       193         Direction Change in Full-Bridge Output Mode       198         Duty Cycle       194         Effects of a Reset       203         Enhanced PWM Auto-Shutdown       200         Example Frequencies/Resolutions       194         Full-Bridge Application Example       198
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Application Example198Full-Bridge Mode197
Duty Cycle       186         Example Frequencies/Resolutions       187         Operation Setup       187         Period       186         TMR2 to PR2 Match       193         TMR4 to PR4 Match       179         PWM (ECCP Module)       193         CCPR1H:CCPR1L Registers       193         Direction Change in Full-Bridge Output Mode       198         Duty Cycle       194         Effects of a Reset       203         Enhanced PWM Auto-Shutdown       200         Example Frequencies/Resolutions       194         Full-Bridge Application Example       198         Full-Bridge Mode       197         Half-Bridge Mode       197
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Application Example198Full-Bridge Mode197Half-Bridge Mode196Half-Bridge Output Mode196
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Application Example198Full-Bridge Mode197Half-Bridge Mode196Half-Bridge Output Mode196Applications Example196
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Mode197Half-Bridge Mode196Applications Example196Output Configurations194
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Mode197Half-Bridge Mode196Applications Example196Output Configurations194Output Configurations194Output Relationships (Active-High)195
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Mode197Half-Bridge Mode196Half-Bridge Output Mode196Output Configurations194Output Configurations194Output Relationships (Active-High)195Output Relationships (Active-Low)195
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Mode197Half-Bridge Mode196Auff-Bridge Output Mode196Output Configurations194Output Configurations194Output Relationships (Active-High)195Output Relationships (Active-Low)193
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Mode197Half-Bridge Mode196Malf-Bridge Output Mode196Output Configurations194Output Relationships (Active-High)195Output Relationships (Active-Low)193Programmable Dead-Band Delay200
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Application Example198Full-Bridge Mode197Half-Bridge Output Mode196Output Configurations194Output Relationships (Active-High)195Output Relationships (Active-Low)193Programmable Dead-Band Delay200Setup for PWM Operation203
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Mode197Half-Bridge Mode196Malf-Bridge Output Mode196Output Configurations194Output Relationships (Active-High)195Output Relationships (Active-Low)193Programmable Dead-Band Delay200
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Application Example198Full-Bridge Mode197Half-Bridge Output Mode196Output Configurations194Output Relationships (Active-High)195Output Relationships (Active-Low)193Programmable Dead-Band Delay200Setup for PWM Operation203
Duty Cycle186Example Frequencies/Resolutions187Operation Setup187Period186TMR2 to PR2 Match193TMR4 to PR4 Match179PWM (ECCP Module)193CCPR1H:CCPR1L Registers193Direction Change in Full-Bridge Output Mode198Duty Cycle194Effects of a Reset203Enhanced PWM Auto-Shutdown200Example Frequencies/Resolutions194Full-Bridge Mode197Half-Bridge Mode196Output Configurations194Output Configurations194Output Relationships (Active-High)195Output Relationships (Active-Low)193Programmable Dead-Band Delay200Setup for PWM Operation203Start-up Considerations201

### R

RAM. See Data Memory.
RC_IDLE Mode
RC RUN Mode
RCALL
RCON Register
Bit Status During Initialization
Reader Response
Receive Filters
AND Logic Flow
Magic Packet Format
OR Logic Flow
Register File Summary
Registers
ADCON0 (A/D Control 0)
ADCON1 (A/D Control 1)
ADCON2 (A/D Control 2)
BAUDCONx (Baud Rate Control x)
CCPxCON (Capture/Compare/PWM Control,
CCP4 and CCP5) 181
CCPxCON (Enhanced Capture/Compare/PWM
Control, ECCP1/ECCP2/ECCP3) 189
CMCON (Comparator Control) 335
CONFIG1H (Configuration 1 High) 347
CONFIG1L (Configuration 1 Low) 347
CONFIG2H (Configuration 2 High) 349
CONFIG2L (Configuration 2 Low) 348
CONFIG3H (Configuration 3 High) 351
CONFIG3L (Configuration 3 Low) 69, 350
CVRCON (Comparator Voltage
Reference Control)
DEVID1 (Device ID 1)
DEVID2 (Device ID 2)
ECCPxAS (ECCPx Auto-Shutdown
Configuration)
ECCPxDEL (ECCPx Dead-Band Delay)
ECON1 (Ethernet Control 1) 213
ECON2 (Ethernet Control 2)
EECON1 (EEPROM Control 1)
EFLOCON (Ethernet Flow Control)
EIE (Ethernet Interrupt Enable)
EIR (Ethernet Interrupt Request, Flag)
ERXFCON (Ethernet Receive Filter Control)
ESTAT (Ethernet Status)
INTCON (Interrupt Control)
INTCON2 (Interrupt Control 2)
INTCON3 (Interrupt Control 3)
IPR1 (Peripheral Interrupt Priority 1)
IPR2 (Peripheral Interrupt Priority 2)
IPR3 (Peripheral Interrupt Priority 3)
MABBIPG (MAC Back-to-Back
Inter-Packet Gap)
MACON1 (MAC Control 1)
MACON1 (MAC Control 1)
MACONS (MAC Control 3)
MACON4 (MAC Control 4)
MICMD (MII Command)
MISTAT (MII Status)
OSCCON (Oscillator Control)
OSCTUNE (PLL Block Control) 41

PHCON1 (PHY Control 1)
PHIE (PHY Interrupt Enable)
PHIR (PHY Interrupt Request, Flag)228
PHLCON (PHY Module LED Control)
PHSTAT1 (Physical Layer Status 1)
PHSTAT2 (Physical Layer Status 2)
PIE1 (Peripheral Interrupt Enable 1)
PIE2 (Peripheral Interrupt Enable 2)128
PIE3 (Peripheral Interrupt Enable 3) 129
PIR1 (Peripheral Interrupt
Request (Flag) 1)124
PIR2 (Peripheral Interrupt
Request (Flag) 2)125
PIR3 (Peripheral Interrupt
Request (Flag) 3)
PSPCON (Parallel Slave Port Control)
RCON (Reset Control)
RCSTAx (Receive Status and Control x)
SSPxCON1 (MSSPx Control 1, I <sup>2</sup> C Mode)
SSPxCON1 (MSSPx Control 1, SPI Mode)257
SSPxCON2 (MSSPx Control 2,
I <sup>2</sup> C Master Mode)268
SSPxCON2 (MSSPx Control 2,
I <sup>2</sup> C Slave Mode)
SSPxSTAT (MSSPx Status, I <sup>2</sup> C Mode)
SSPxSTAT (MSSPx Status, SPI Mode)256
STATUS
STKPTR (Stack Pointer)72
T0CON (Timer0 Control) 163
T1CON (Timer1 Control)
T2CON (Timer2 Control) 173
T3CON (Timer3 Control)175
T4CON (Timer4 Control) 179
TXSTAx (Transmit Status and Control x)
TXSTAx (Transmit Status and Control x)302WDTCON (Watchdog Timer Control)353RESET389Reset53Brown-out Reset (BOR)53
TXSTAx (Transmit Status and Control x)
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During       20         Power-Managed Modes       53         MCLR Reset, Normal Operation       53         Power-on Reset (POR)       53         Reset Instruction       53         Stack Full Reset       53
TXSTAx (Transmit Status and Control x)
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During       9         Power-Managed Modes       53         MCLR Reset, Normal Operation       53         Power-on Reset (POR)       53         Reset Instruction       53         Stack Full Reset       53         Stack Underflow Reset       53         State of Registers       58
TXSTAx (Transmit Status and Control x)
TXSTAx (Transmit Status and Control x)
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During       9         Power-Managed Modes       53         MCLR Reset, Normal Operation       53         Power-on Reset (POR)       53         Reset Instruction       53         Stack Full Reset       53         Stack Underflow Reset       53         State of Registers       58         Watchdog Timer (WDT) Reset       53         Resets       345
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During       9         Power-Managed Modes       53         MCLR Reset, Normal Operation       53         Power-on Reset (POR)       53         Reset Instruction       53         Stack Full Reset       53         Stack Underflow Reset       53         State of Registers       58         Watchdog Timer (WDT) Reset       53         Resets       345         Brown-out Reset (BOR)       345
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During
TXSTAx (Transmit Status and Control x)302WDTCON (Watchdog Timer Control)353RESET389Reset53Brown-out Reset (BOR)53Configuration Mismatch (CM)53MCLR Reset, DuringPower-Managed Modes53MCLR Reset, Normal Operation53Power-on Reset (POR)53Reset Instruction53Stack Full Reset53Stack Underflow Reset53State of Registers58Watchdog Timer (WDT) Reset53Resets345Brown-out Reset (BOR)345Oscillator Start-up Timer (OST)345
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During       9         Power-Managed Modes       53         MCLR Reset, Normal Operation       53         Power-on Reset (POR)       53         Reset Instruction       53         Stack Full Reset       53         Stack Underflow Reset       53         State of Registers       58         Watchdog Timer (WDT) Reset       53         Resets       345         Brown-out Reset (BOR)       345         Oscillator Start-up Timer (OST)       345         Power-on Reset (POR)       345         Power-on Reset (POR)       345
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During       9         Power-Managed Modes       53         MCLR Reset, Normal Operation       53         Power-on Reset (POR)       53         Reset Instruction       53         Stack Full Reset       53         Stack Underflow Reset       53         State of Registers       58         Watchdog Timer (WDT) Reset       53         Resets       345         Brown-out Reset (BOR)       345         Oscillator Start-up Timer (OST)       345         Power-on Reset (POR)       345         Power-up Timer (PWRT)       345
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During
TXSTAx (Transmit Status and Control x)
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During
TXSTAx (Transmit Status and Control x)302WDTCON (Watchdog Timer Control)353RESET389Reset53Brown-out Reset (BOR)53Configuration Mismatch (CM)53MCLR Reset, DuringPower-Managed ModesPower-Managed Modes53MCLR Reset, Normal Operation53Power-on Reset (POR)53Stack Full Reset53Stack Full Reset53Stack Underflow Reset53State of Registers58Watchdog Timer (WDT) Reset53Resets345Brown-out Reset (BOR)345Oscillator Start-up Timer (OST)345Power-on Reset (POR)345Power-up Timer (PWRT)345Stack Full/Underflow73RETFIE390RETLW390RETURN391Return Address Stack71
TXSTAx (Transmit Status and Control x)302WDTCON (Watchdog Timer Control)353RESET389Reset53Brown-out Reset (BOR)53Configuration Mismatch (CM)53MCLR Reset, DuringPower-Managed ModesPower-Managed Modes53MCLR Reset, Normal Operation53Power-on Reset (POR)53Stack Full Reset53Stack Full Reset53Stack Underflow Reset53Stack Underflow Reset53Resets545Brown-out Reset (BOR)345Oscillator Start-up Timer (OST)345Power-on Reset (POR)345Power-on Reset (POR)345Reset Stack Full/Underflow73RETFIE390RETLW390RETLW391Return Address Stack71Return Address Stack71Return Stack Pointer (STKPTR)72
TXSTAx (Transmit Status and Control x)       302         WDTCON (Watchdog Timer Control)       353         RESET       389         Reset       53         Brown-out Reset (BOR)       53         Configuration Mismatch (CM)       53         MCLR Reset, During       Power-Managed Modes         Power-Managed Modes       53         MCLR Reset, Normal Operation       53         Power-on Reset (POR)       53         Stack Full Reset       53         Stack Full Reset       53         Stack Underflow Reset       53         Stack Underflow Reset       53         Stack Underflow Reset       53         State of Registers       58         Watchdog Timer (WDT) Reset       53         Resets       345         Brown-out Reset (BOR)       345         Oscillator Start-up Timer (OST)       345         Power-up Timer (PWRT)       345         Power-up Timer (PWRT)       345         Stack Full/Underflow       73         RETFIE       390         RETLW       390         RETURN       391         Return Address Stack       71         Return Address Stack       71
TXSTAx (Transmit Status and Control x)302WDTCON (Watchdog Timer Control)353RESET389Reset53Brown-out Reset (BOR)53Configuration Mismatch (CM)53MCLR Reset, DuringPower-Managed ModesPower-Managed Modes53MCLR Reset, Normal Operation53Power-on Reset (POR)53Stack Full Reset53Stack Full Reset53Stack Underflow Reset53Stack Underflow Reset53Resets545Brown-out Reset (BOR)345Oscillator Start-up Timer (OST)345Power-on Reset (POR)345Power-on Reset (POR)345Reset Stack Full/Underflow73RETFIE390RETLW390RETLW391Return Address Stack71Return Address Stack71Return Stack Pointer (STKPTR)72

RRCF	
S	
SCKx	255
SDIx	255
SDOx	255
SEC_IDLE Mode	. 50
SEC_RUN Mode	. 46
Serial Clock, SCKx	255
Serial Data In (SDIx)	255
Serial Data Out (SDOx)	255
Serial Peripheral Interface. See SPI Mode.	
SETF	
Slave Select (SSx)	255
SLEEP	394
Sleep	
OSC1 and OSC2 Pin States	
Software Simulator (MPLAB SIM)	410
Special Event Trigger. See Compare (ECCP Module).	
Special Features of the CPU	345
Special Function Registers	
Ethernet SFRs	80
SPI Mode (MSSP)	
Associated Registers	
Bus Mode Compatibility	
Clock Speed and Module Interactions	
Effects of a Reset	
Enabling SPI I/O	
Master Mode	
Master/Slave Connection	
Operation	
Operation in Power-Managed Modes	
Serial Clock	
Serial Data In	
Serial Data Out	
Slave Mode	
Slave Select	
Slave Select Synchronization	
SPI Clock	
Typical Connection	
SSPOV SSPOV Status Flag	
SSPOV status riag	290
	272
SSPxSTAT Register	212
R/W Bit	270
SSx	
SUBFSR	
SUBFWB	
SUBLW	
SUBULNK	
SUBWE	
SUBWFB	
SWAPF	
_	550
T	
Table Pointer Operations (table)	. 98

Timer0	
Associated Registers	165
Clock Source Select (T0CS Bit)	164
Operation	
Overflow Interrupt	
Prescaler	
Prescaler Assignment (PSA Bit)	
Prescaler Select (T0PS2:T0PS0 Bits)	
Prescaler, Switching Assignment	165
Prescaler. See Prescaler, Timer0.	
Reads and Writes in 16-Bit Mode	164
Source Edge Select (T0SE Bit)	
Timer1	
16-Bit Read/Write Mode	
Associated Registers	
Considerations in Asynchronous Counter Mode	
Interrupt	170
Operation	168
Oscillator1	67, 169
Layout Considerations	169
Overflow Interrupt	
Resetting, Using the ECCPx	107
	470
Special Event Trigger	
Special Event Trigger (ECCP)	
TMR1H Register	167
TMR1L Register	167
Use as a Clock Source	
Use as a Real-Time Clock	
Timer2	
Associated Registers	
Interrupt	
Operation	
Output	174
PR2 Register1	86, 193
TMR2 to PR2 Match Interrupt	193
Timer3	
16-Bit Read/Write Mode	
Associated Registers	
Operation	
Oscillator1	-
Overflow Interrupt1	75, 177
Resetting Using the ECCPx	
Special Event Trigger	177
TMR3H Register	
TMR3L Register	
Timer4	
Associated Registers	
MSSPx Clock, Output	
Operation	179
Postscaler. See Postscaler, Timer4.	
PR4 Register1	79, 186
Prescaler. See Prescaler, Timer4.	
TMR4 Register	179
TMR4 to PR4 Match Interrupt1	
•	73, 100
Timing Diagrams	4.40
A/D Conversion	446
Asynchronous Reception, RXDTP = 0	
(RXx Not Inverted)	315
Asynchronous Transmission (Back-to-Back),	
TXCKP = 0 (TXx Not Inverted)	312
Asynchronous Transmission, TXCKP = 0	
(TXx Not Inverted)	312
Automatic Baud Rate Calculation	
Auto-Wake-up Bit (WUE) During	04-
Normal Operation	317

Auto-Wake-up Bit (WUE) During Sleep	7			
Baud Rate Generator with Clock Arbitration				
BRG Overflow Sequence				
BRG Reset Due to SDAx Arbitration During				
Start Condition	3			
Capture/Compare/PWM (Including				
ECCPx Modules) 436				
CLKO and I/O 431				
Clock Synchronization	)			
Clock/Instruction Cycle74	ł			
EUSARTx Synchronous Receive				
(Master/Slave) 445	5			
EUSARTx Synchronous Transmission				
(Master/Slave)				
Example SPI Master Mode (CKE = 0)				
Example SPI Master Mode (CKE = 1)	3			
Example SPI Slave Mode (CKE = 0)	)			
Example SPI Slave Mode (CKE = 1)				
External Clock (All Modes Except PLL)	,			
External Memory Bus for Sleep (Extended				
Microcontroller Mode) 112, 114 External Memory Bus for TBLRD (Extended	ł			
Microcontroller Mode) 112, 114	•			
Fail-Safe Clock Monitor				
First Start Bit				
Full-Bridge PWM Output				
Half-Bridge PWM Output				
I <sup>2</sup> C Acknowledge Sequence				
I <sup>2</sup> C Bus Collision During a Repeated Start	,			
Condition (Case 1)	7			
I <sup>2</sup> C Bus Collision During a Repeated Start				
Condition (Case 2)	7			
I <sup>2</sup> C Bus Collision During a Stop				
Condition (Case 1)	3			
I <sup>2</sup> C Bus Collision During a Stop	·			
Condition (Case 2)	3			
I <sup>2</sup> C Bus Collision During Start				
Condition (SCLx = $0$ )				
I <sup>2</sup> C Bus Collision During Start				
Condition (SDAx Only)				
I <sup>2</sup> C Bus Collision for Transmit and				
Acknowledge				
I <sup>2</sup> C Bus Data				
I <sup>2</sup> C Bus Start/Stop Bits 441				
I <sup>2</sup> C Master Mode (7 or 10-Bit Transmission)				
I <sup>2</sup> C Master Mode (7-Bit Reception) 292	2			
I <sup>2</sup> C Slave Mode (10-Bit Reception, SEN = 0)	3			
$I^2C$ Slave Mode (10-Bit Reception, SEN = 0,				
ADMSK = 01001)277				
I <sup>2</sup> C Slave Mode (10-Bit Reception, SEN = 1)				
I <sup>2</sup> C Slave Mode (10-Bit Transmission)	3			
I <sup>2</sup> C Slave Mode (7-Bit Reception, SEN = 0)				
$I^2C$ Slave Mode (7-Bit Reception, SEN = 0,				
ADMSK = 01011)	ŀ			
I <sup>2</sup> C Slave Mode (7-Bit Reception, SEN = 1)	]			
I <sup>2</sup> C Slave Mode (7-Bit Transmission)				
I <sup>2</sup> C Slave Mode General Call Address Sequence				
(7 or 10-Bit Addressing Mode)				
I <sup>2</sup> C Stop Condition Receive or Transmit Mode 293	5			
Master SSP I <sup>2</sup> C Bus Data	5			
Master SSP I <sup>2</sup> C Bus Start/Stop Bits				
Parallel Slave Port (PSP) Read				
Parallel Slave Port (PSP) Write				
Program Memory Read	2			
- rogram memory write	,			

PWM Auto-Shutdown (P1RSEN = 0,
Auto-Restart Disabled)
PWM Auto-Shutdown (P1RSEN = 1,
Auto-Restart Enabled)
PWM Direction Change
PWM Direction Change at Near
100% Duty Cycle
PWM Output
Repeated Start Condition
Reset, Watchdog Timer (WDT), Oscillator Start-up
Timer (OST) and Power-up Timer (PWRT) 434
Send Break Character Sequence
Slave Synchronization
Slow Rise Time (MCLR Tied to VDD,
VDD Rise > TPWRT)57
SPI Mode (Master Mode)
SPI Mode (Slave Mode, CKE = 0)
SPI Mode (Slave Mode, CKE = 1)
Synchronous Reception (Master Mode, SREN) 321
Synchronous Transmission
Synchronous Transmission (Through TXEN)
Time-out Sequence on Power-up
(MCLR Not Tied to VDD), Case 1
Time-out Sequence on Power-up
(MCLR Not Tied to VDD), Case 2
Time-out Sequence on Power-up
(MCLR Tied to VDD, VDD Rise < TPWRT)
Timer0 and Timer1 External Clock435
Transition for Entry to Idle Mode 50
Transition for Entry to SEC_RUN Mode47
Transition for Entry to Sleep Mode
Transition for Two-Speed Start-up
(INTRC to HSPLL)
Transition for Wake From Idle to Run Mode
Transition for Wake From Sleep Mode (HSPLL) 49
Transition From RC_RUN Mode to
PRI_RUN Mode
Transition From SEC_RUN Mode to
PRI_RUN Mode (HSPLL)
Transition to RC_RUN Mode
Timing Diagrams and Specifications AC Characteristics
Internal RC Accuracy
Capture/Compare/PWM Requirements
(Including ECCPx Modules)
EUSARTx Synchronous Receive Requirements445
EUSARTX Synchronous Transmission
Requirements
Example SPI Mode Requirements

(Master Mode, CKE = 0) Example SPI Mode Requirements		437
		400
(Master Mode, CKE = 1)	••••••	438
Example SPI Mode Requirements		
(Slave Mode, CKE = 0)	••••••	439
Example SPI Slave Mode Requirements (CKE = 1)		440
External Clock Requirements		
I <sup>2</sup> C Bus Data Requirements (Slave Mode)		
I <sup>2</sup> C Bus Start/Stop Bits Requirements		
(Slave Mode)		441
Master SSP I <sup>2</sup> C Bus Data Requirements		
Master SSP I <sup>2</sup> C Bus Start/Stop Bits		• • •
Requirements		443
Parallel Slave Port Requirements		
PLL Clock		
Program Memory Write Requirements		
Reset, Watchdog Timer, Oscillator Start-up		100
Timer, Power-up Timer and Brown-out		
Reset Requirements		434
Timer0 and Timer1 External Clock		
Requirements		435
Top-of-Stack Access		
TRISE Register		
PSPMODE Bit		159
TSTFSZ		
Two-Speed Start-up		
Two-Word Instructions	,	
Example Cases		. 75
TXSTAx Register		
BRGH Bit		305
V		

VDDCORE/VCAP Pin	354
Voltage Reference Specifications	426
Voltage Regulator (On-Chip)	354

#### W

Watchdog Timer (WDT)	
Associated Registers	
Control Register	
Programming Considerations .	
WCOL	
WCOL Status Flag	
WWW Address	
WWW, On-Line Support	6

### Х

XORLW	 399
XORWF	 400

NOTES:

### THE MICROCHIP WEB SITE

Microchip provides online support via our WWW site at www.microchip.com. This web site is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the web site contains the following information:

- Product Support Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQ), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

### CUSTOMER CHANGE NOTIFICATION SERVICE

Microchip's customer notification service helps keep customers current on Microchip products. Subscribers will receive e-mail notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, access the Microchip web site at www.microchip.com, click on Customer Change Notification and follow the registration instructions.

### **CUSTOMER SUPPORT**

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Field Application Engineer (FAE)
- Technical Support
- Development Systems Information Line

Customers should contact their distributor, representative or field application engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.

Technical support is available through the web site at: http://support.microchip.com

### READER RESPONSE

It is our intention to provide you with the best documentation possible to ensure successful use of your Microchip product. If you wish to provide your comments on organization, clarity, subject matter, and ways in which our documentation can better serve you, please FAX your comments to the Technical Publications Manager at (480) 792-4150.

Please list the following information, and use this outline to provide us with your comments about this document.

To:	Technical Publications Manager	Total Pages Sent	
RE:	Reader Response		
From	: Name		
	City / State / ZIP / Country		
	Telephone: ()	FAX: ()	
Appli	cation (optional):		
Wou	d you like a reply?YN		
Devi	ce: PIC18F97J60 Family	Literature Number: DS39762C	
Ques	stions:		
1. V	What are the best features of this do	cument?	
_			
_			
2. H	low does this document meet your h	nardware and software development needs?	
_			
-			
3. E	3. Do you find the organization of this document easy to follow? If not, why?		
-			
4	What additions to the document do y	ou think would enhance the structure and subject?	
т. v	what additions to the document do y		
_			
5. V	What deletions from the document co	buld be made without affecting the overall usefulness?	
		-	
_			
6. I	s there any incorrect or misleading i	nformation (what and where)?	
_			
_			
7. H	low would you improve this docume	nt?	
_			
_			

### **PRODUCT IDENTIFICATION SYSTEM**

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO. Device	X <u>/XX XXX</u> Temperature Package Pattern Range	<ul> <li>Examples:</li> <li>a) PIC18F67J60-I/PT 301 = Industrial temp., TQFP package, QTP pattern #301.</li> <li>b) PIC18F67J60T-I/PT = Tape and reel, Industrial temp., TQFP package.</li> </ul>
Device	PIC18F66J60/66J65/67J60, PIC18F86J60/86J65/87J60, PIC18F96J60/96J65/97J60, PIC18F66J60/66J65/67J60T <sup>(1)</sup> , PIC18F86J60/86J65/87J60T <sup>(1)</sup> , PIC18F96J60/96J65/97J60T <sup>(1)</sup>	
Temperature Range	I = $-40^{\circ}$ C to $+85^{\circ}$ C (Industrial)	
Package	PT = 64, 80 and 100-Lead, 12x12x1 mm TQFP (Thin Quad Flatpack) PF = 100-Lead, 14x14x1 mm TQFP	Note 1: T = in tape and reel
Pattern	QTP, SQTP, Code or Special Requirements (blank otherwise)	



### WORLDWIDE SALES AND SERVICE

#### AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://support.microchip.com Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Farmington Hills, MI Tel: 248-538-2250 Fax: 248-538-2260

Kokomo Kokomo, IN Tel: 765-864-8360 Fax: 765-864-8387

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Santa Clara Santa Clara, CA Tel: 408-961-6444 Fax: 408-961-6445

Toronto Mississauga, Ontario, Canada Tel: 905-673-0699 Fax: 905-673-6509

#### ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway Habour City, Kowloon Hong Kong Tel: 852-2401-1200 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

**China - Beijing** Tel: 86-10-8528-2100 Fax: 86-10-8528-2104

**China - Chengdu** Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

**China - Fuzhou** Tel: 86-591-8750-3506 Fax: 86-591-8750-3521

**China - Hong Kong SAR** Tel: 852-2401-1200 Fax: 852-2401-3431

**China - Qingdao** Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

**China - Shanghai** Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

**China - Shenzhen** Tel: 86-755-8203-2660 Fax: 86-755-8203-1760

China - Shunde Tel: 86-757-2839-5507 Fax: 86-757-2839-5571

**China - Wuhan** Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

**China - Xian** Tel: 86-29-8833-7250 Fax: 86-29-8833-7256

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-4182-8400 Fax: 91-80-4182-8422

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-2566-1512 Fax: 91-20-2566-1513

**Japan - Yokohama** Tel: 81-45-471- 6166 Fax: 81-45-471-6122

**Korea - Gumi** Tel: 82-54-473-4301 Fax: 82-54-473-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

**Malaysia - Penang** Tel: 60-4-646-8870 Fax: 60-4-646-5086

Philippines - Manila Tel: 63-2-634-9065

Fax: 63-2-634-9069 Singapore Tel: 65-6334-8870 Fax: 65-6334-8850

**Taiwan - Hsin Chu** Tel: 886-3-572-9526 Fax: 886-3-572-6459

**Taiwan - Kaohsiung** Tel: 886-7-536-4818 Fax: 886-7-536-4803

Taiwan - Taipei Tel: 886-2-2500-6610 Fax: 886-2-2508-0102

**Thailand - Bangkok** Tel: 66-2-694-1351 Fax: 66-2-694-1350

#### EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**UK - Wokingham** Tel: 44-118-921-5869 Fax: 44-118-921-5820

12/08/06