Proximity Sensors Capacitive Thermoplastic Polyester Housing Types CA30CAN/CAF.....





- 4[™] Generation TRIPLESHIELD™
- Adjustable sensing distance: 2 20 mm Flush or 4-30 mm Non-flush
- Protection: short-circuit, transients and reverse polarity
- Dust and humidity compensation
- Dust or Temperature alarm output
- Rated operational voltage: 10-40 VDC
- Output: DC 200 mA, NPN or PNP
- Standard Output: NO and NC
- . LED indications for Power-supply, Output and Stability
- IP67, IP69K, Nema 1, 2, 4, 4X, 5, 6, 6P, 12
- Cable and M12 connector versions available



Product Description

The CA30CA.. capacitive proximity switches feature an improved 4[™] Generation TRIPLESHIELD™ technology. Furthermore, these sensors feature increased immunity to electromagnetic inteference (EMI), especially to frequency drives. Not only does 4TH Generation $TRIPLESHIELD^{\text{TM}}$ feature an increased EMI, but it also increases the immunity to humidity and dust. The implementation of stability indication eases the setup procedure as both Stable ON and Stable OFF positions are

indicated by the Green and yellow LEDs.

The sensing distance is increased by 20 – 25 % allowing room for additional stable detection.

The Dust Alarm function gives an early warning that the sensing surroundings have to be cleaned.

The Temperature alarm function raises an alarm if the sensing surface goes beyond 60 degree celcius.

The sensor housing is featuring IP69K as well as approval by ECOLAB for cleaning-and disinfection agents.

Ordering Key

CA30CAN25NAM1

Capacitive proximity switch Housing diameter (mm) Housing material Housing length Detection principle Rated operating dist. (mm) Output type Output configuration Connection type	<u> </u>
Detection principle Rated operating dist. (mm) Output type Output configuration	Housing diameter (mm) — Housing material
Rated operating dist. (mm) ——————————————————————————————————	
Output type — Output configuration — Output configuration	Detection principle ————
Output configuration	. , ,
	Output type —
Connection type	Output configuration —
	. •

Type Selection

Housing diameter	Sensor type	Output type	Output function	Connection	Rated operating distance (S _n)	Ordering no. Standard	Ordering no. Dust alarm	Ordering no. Temperature alarm
M 30	 Flush	NPN	NO+NC	Cable	2 - 16 mm	CA30CAF16NA		
M 30	Flush	NPN	NO+NC	M12 Plug	2 - 16 mm	CA30CAF16NAM1		
M 30	Flush	PNP	NO+NC	Cable	2 - 16 mm	CA30CAF16PA		
M 30	Flush	PNP	NO+NC	M12 Plug	2 - 16 mm	CA30CAF16PAM1		
M 30	Flush	PNP	NO	Cable	2 - 16 mm		CA30CAF16P0DU	CA30CAF16P0TA
M 30	Flush	PNP	NC	Cable	2 - 16 mm		CA30CAF16PCDU	CA30CAF16PCTA
M 30	Non-Flush	NPN	NO+NC	Cable	4 - 25 mm	CA30CAN25NA		
M 30	Non-Flush	NPN	NO+NC	M12 Plug	4 - 25 mm	CA30CAN25NAM1		
M 30	Non-Flush	PNP	NO+NC	Cable	4 - 25 mm	CA30CAN25PA		
M 30	Non-Flush	PNP	NO+NC	M12 Plug	4 - 25 mm	CA30CAN25PAM1		
M 30	Non-Flush	PNP	NO	Cable	4 - 25 mm		CA30CAN25PODU	CA30CAN25POTA
M 30	Non-Flush	PNP	NC	Cable	4 - 25 mm		CA30CAN25PCDU	CA30CAN25PCTA

Specifications EN 60947-5-2

Rated operating distance (S_n)

Non-flush mounted sensor

Flush mounted sensor

4 - 25 mm (factory setting 25 mm), (ref. target 75x75 mm ST37, 1 mm thick, grounded) 2 - 16 mm (factory setting 16 mm - non-flush mounted) (ref. target 48x48 mm ST37, 1 mm thick, grounded)

Sensitivity control	Adjustable by potentiometer
Electrical adjustment	11 turns
Mechanical adjustment	16 turns
Adjustable distance	
Flush types	2 to 20 mm
Non-flush types	4 to 30 mm
Effective operating dist. (S _r)	$0.9 \ x \ S_n \leq S_r \leq 1.1 \ x \ S_n$
Usable operating dist. (S _u)	$0.85 \times S_r \le S_u \le 1.15 \times S_r$




Specifications (cont.) EN 60947-5-2

Repeat accuracy (R)	≤ 5%
Hysteresis (H)	3 - 20%
Rated operational volt. (U _B)	10 to 40 VDC (ripple incl.)
Ripple	≤ 10%
Output function	NPN or PNP
Output switching function	N.O. and N.C.
Rated operational current (I _e)	≤ 200 mA (continuous)
Capacitive load	100 nF
No-load supply current (I _o)	≤ 12 mA
Voltage drop (U _d)	≤ 2.0 VDC @ 200 mA DC
Minimum operational current (I _m)	≥ 0.5 mA
OFF state current (I _r)	≤ 100 µA
Protection	Short-circuit, reverse polarity, transients
Frequency of operating cycles (f)	50 Hz
Response time OFF-ON (t _{on})	≤ 10 ms
Response time ON-OFF (toff)	≤ 10 ms
Power ON delay (t _v)	≤ 200 ms
Indication For output ON Power and signal stability	LED, yellow LED, green
Environment Installation category	III (IEC 60664, 60664A; 60947-1)
Degree of pollution	3 (IEC 60664, 60664A; 60947-1)
Degree of protection	IP 67, IP 68/60 min., IP69K* (IEC 60529; 60943-1)
NEMA type Operating temperature Max. temperature on sensing face Storage temperature	1, 2, 4, 4X, 5, 6, 6P, 12 -30 to +85°C (-22 to +185°F)
Rated insulation voltage	1 kVAC (rms) IEC protection class III (III)
Tightening torque	≤ 7.5 Nm
Connection Cable	PVC,
Plug (M1)	Ø5.2 x 2 m, 4 x 0.34 mm ² Oil proof, grey M12 x 1, - 4 pin

	<u> </u>
Temperature alarm output Response time examples	60°C ± 5°C
$T_A = 25$ °C	16 sec @ T _{EXC} = 800°C 390 sec @ T _{EXC} = 80°C
TRIPLESHIELDTM	
Exceeding the norms for	
capacitive sensors	
Electrostatic discharge	
(EN61000-4-2)	
Contact discharge	> 40 kV
Air discharge	> 40 kV
Electrical fast transients/burst	
(EN 61000-4-4)	±4kV
Surge	
(EN 61000-4-5)	
Power-supply	$>$ 2kV (with 500 Ω)
Sensor output	> 2kV (with 500 Ω)
Wire conducted disturbances	
(EN 61000-4-6)	> 20 Vrms
Power-frequency magnetic	
fields (EN 61000-4-8)	
Continous	> 60 A/m, 75.9 µ tesla
Short-time	> 600 A/m, 759 µ tesla
Radiated RF electromagnetic	
fields (EN 61000-4-3)	> 20 V/m
Shock (IEC 60068-2-27)	30 G / 11ms, 3 pos, 3 neg
	per axis
Rough handling shocks	
(IEC 60068-2-31)	2 times from 1m
	100 times from 0,5m
Vibration (IEC 60068-2-6)	10 to 150 Hz, 1 mm / 15 G
Housing material	
Body	PBT, grey,
	30% glass reinforced
Cable gland	PA12, black
Fingernuts	PA12, black
Trimmershaft	Nylon
Weight	
Cable version	190 g
Plug version	106 g
Approvals	cULus (UL508)
CE-marking	Yes
MTTF _d	829 years @ 40°C (+104°F)

^{*} The IP69K test according to DIN 40050-9 for high-pressure, high-temperature wash-down applications. The sensor must not only be dust tight (IP6X), but also able to withstand high-pressure and steam cleaning. The sensor is exposed to high pressure water from a spray nozzle that is fed with 80°C water at 8'000–10'000 KPa (80–100bar) and a flow rate of 14–6L/min. The nozzle is held 100 –150 mm from the sensor at angles of 0°, 30°, 60° and 90° for 30s each. The test device sits on a turntable that rotates with a speed of 5 times per minute. The sensor must not suffer any damaging effects from the high pressure water in appearance and function.





Adjustment Guide

The environments in which capacitive sensors are installed can often be unstable as regards to temperature, humidity, object distance and industrial (noise) interference. Because of this, Carlo Gavazzi offers


as standard features in all TRIPLESHIELDTM capacitive sensors a user-friendly sensitivity adjustment instead of a fixed sensing range. Likewise, these sensors provide an extended sensing range to accommodate

mechanically demanding areas and temperature stability to ensure high immunity to electromagnetic interference (EMI) and a minimum need for adjusting sensitivity if the temperature varies.


Note: Sensors are factory set

Sensors are factory set (default) to nominal sensing range S_n .

Wiring Diagram




Detection Diagram






Detection Stability Indication



Dimensions





Installation Hints

Capacitive sensors have a unique ability to detect almost any material in liquid or solid form. Capacitive sensors are able to detect metallic as well as non-metallic objects. However, their traditional use is for non-metallic materials such as:

 Plastics Industry Resins, regrinds or moulded products.

 Chemical Industry Cleansers, fertilizers, liquid soaps, corrosives and petrochemicals.

 Wood Industry Saw dust, paper products, door and window frames.


 Ceramics & Glass Industry

Raw materials, clay or finished products, bottles.

 Packaging Industry Package inspection for level or contents, dry goods, fruits and vegetables, dairy products.

Materials are detected due to their dielectric constant. The bigger the size of an object, the higher the density of material, the better or easier it is to detect the object.

The nominal sensing distance for a capacitive sensor is referred to a grounded metal plate (ST37). For additional information regarding dielectric ratings of materials please refer to Technical Information.



Delivery Contents

- Capacitive switch: CA30CAN/CAF......
- · Installation & Adjustment Guide
- 2 x M30 fingernuts
- Screwdriver
- Packaging: Cardboard box

Accessories

- Connector type CONM14NF.. -series.
- Mounting Brackets AMB30-S (straight), AMB30-A (angled)