

USB 3.1 Gen 1 Type C Connector

Superior performance up to 5Gb/s

COMPACT AND RELIABLE CONNECTOR

USB 3.1 Type C Gen 1 is the new standard plug and receptacle providing multifunction single cable solution for data, power, audio and video. The small form factor made this interconnection the unquestioned technology across all devices. The reversible design enables quick and easy connections no matter which way it is inserted. It supports power delivery up to 100W and perfromance speed up to 5Gb/s.

- Supports SuperSpeed 5Gb/s
- Reversible plug and cable orientation
- Slim and sleek design
- Better EMI shielding design



| FEATURES |
|----------|
|----------|

- Supports SuperSpeed communication 5Gb/s
- Reversible plug and cable orientation
- Robust and small form factor design
- Better EMI (Electromagnetic Interference) shielding design
- Various options available: Right angle dual SMT and Hybrid style, Top mount and Mid mount, Long shell and Short body
- RoHS compliant and lead-free

BENEFITS

- Minimizes user waiting time
- Ready for next-generation applications
- Ensures quick and easy connections whichever way it is inserted
- Tailored for emerging product designs
- Suitable for applications in very thin platforms and the I&I market
- Protects against EMI and ESD (Electromagnetic Discharge)
- Flexible solution for different applications
- Meets environmental, health and safety requirements

TECHNICAL INFORMATION

MATERIAL

• Housing: High Temperature Thermoplastic

Shell: Stainless SteelTerminal: Copper Alloy

MECHANICAL PERFORMANCE

Mating Force: 5 to 20N

• Durability: 10,000 mating cycles

ELECTRICAL PERFORMANCE

• Low Level Contact Resistance:

• Initial: $40m\Omega$ max.

• Δ R = +/- 10m Ω max. after environmental stress

• Insulation Resistance: $100M\Omega$ min.

Transfer SuperSpeed: 5Gb/s

Voltage Rating: 100VAC/DC

• Current Rating:

• 5.0A for VBUS and GND

■ 1.25A for Vconn and GND

• 0.25A for all other contacts

• Dielectric Withstand Voltage: 100VAC

PACKAGING

• Receptacle: Tape/Reel

• Plug: Tray

SPECIFICATION

Amphenol Product Specification: GS-12-1336

Amphenol Packaging Specification: GS-14-2487

ENVIRONMENTAL

■ Operating Temperature: -55°C to 85°C

TARGET MARKETS/APPLICATIONS



Infotainment



Adaptor
Flash Drive
Laptop
Phone
Portable Power Bank
Portable HDD
Tablet
Wearable Device



Motherboard Add-on Card Storage Adaptor Storage Enclosure



Factory Automation Equipment Industrial Equipment

PART NUMBERS

| Description | Orientation | Mounting Style | Part Numbers |
|---------------------------------|-------------|--------------------------------------|------------------|
| USB 3.1 Type C Gen 1 receptacle | Right angle | Top mount SMT + DIP (Long shell) | 0137060-00021LF |
| USB 3.1 Type C Gen 1 receptacle | Vertical | Top mount dual SMT | 10138002-10011LF |
| USB 3.1 Type C Gen 1 receptacle | Right angle | Mid mount dual SMT (Short body) | 10137064-00021LF |
| USB 3.1 Type C Gen 1 receptacle | Right angle | Top mount SMT + DIP (Short shell) | 10137061-00021LF |
| USB 3.1 Type C Gen 1 receptacle | Right angle | Top mount SMT + DIP (Short body) | 10137062-00021LF |
| USB 3.1 Type C Gen 1 receptacle | Right angle | Top mount dual SMT (Short body) | 10137065-00021LF |
| USB 3.1 Type C Gen 1 receptacle | Right angle | Top mount SMT+ DIP (Angled entrance) | 10137066-00021LF |