

Pneumatic impact screwdriver CP 772 H

Tightening torque 950 Nm



Application:

For heavy screw-driving work, particularly for suspension, automotive and bus maintenance, agricultural implements and construction implements.

Execution:

- 3 power levels in clockwise rotation, 1 power level in anti-clockwise rotation

Advantage:

- Automatic full unscrewing torque in anti-clockwise rotation

Delivery:

In cardboard box



Art. no.	75066 031
Brand	CP
Manufacturer Part Number	T024598
Model	CP772H
Suitable for screw	M22
Max. tightening torque	950 Nm
Max. idle speed	4200 rpm
Air consumption	678 l/min
Hammer mechanism system	Pin impact mechanism
Length	244 mm
Connection thread	3/8 inch
Inner hose diameter	10 mm
Weight	4.7 kg
With right/left-hand rotation	Yes
Gross Weight	5.083 kg
Product Group	752

EAN

0015451418120