


KRT series



Copper tube lugs for stranded and solid wires.
Meets the measure requirements according to DIN 46235.

Material: 99.9% pure copper
Surface: > 4 μ Sn
Temperature range: Up to 200° C (392° F)

Inscriptions on the lugs palm can for ie be: N35-12T
N = KRT // 35 = 35 mm² wire // 12 = M12 stud size.

Inscriptions on the lugs neck can for ie be: 12
12 = Outside diameter of the neck (F).

When crimping with hexagon dies neck inscription and die markings must conform.



Artikelnummer / Article No.	E-number	Area (mm ²), håll / Area, stud	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)	G (mm)	Antal/frp / Qty/box
KRT 10-5	E 08 470 30	10, M5	5.3	4.5	29	2.1	11	7	10	100
KRT 10-6	E 08 470 32	10, M6	6.5	4.5	29	2.1	11	7	10	100
KRT 10-8	E 08 470 34	10, M8	8.5	4.5	33	1.8	13.5	7	10	100
KRT 10-10	E 08 470 36	10, M10	10.5	4.5	36	1.5	16	7	10	100
KRT 10-12	E 08 470 37	10, M12	13	4.5	39	1.4	18	7	10	100
KRT 16-5	E 08 470 38	16, M5	5.3	5.5	34	3	12	8.5	13	100
KRT 16-6	E 08 470 39	16, M6	6.5	5.5	34	3	12	8.5	13	100
KRT 16-8	E 08 470 40	16, M8	8.5	5.5	37	2.4	15	8.5	13	100
KRT 16-10	E 08 470 42	16, M10	10.5	5.5	39	2.2	16	8.5	13	100
KRT 16-12	E 08 470 44	16, M12	13	5.5	44	1.9	19	8.5	13	100
KRT 25-5		25, M5	5.3	7	40.5	3	14	10	15	100
KRT 25-6	E 08 470 46	25, M6	6.5	7	40.5	3	14	10	15	100
KRT 25-8	E 08 470 48	25, M8	8.5	7	40.5	3	15	10	15	100
KRT 25-10	E 08 470 50	25, M10	10.5	7	43.5	2.7	17	10	15	100
KRT 25-12	E 08 470 52	25, M12	13	7	46	2.2	20	10	15	100
KRT 25-16	E 08 470 53	25, M16	17	7	57	1.7	25	10	15	100
KRT 35-6	E 08 470 54	35, M6	6.5	8.5	45	3.5	17	12	16	100
KRT 35-8	E 08 470 56	35, M8	8.5	8.5	45	3.5	17	12	16	100
KRT 35-10	E 08 470 58	35, M10	10.5	8.5	45	3.1	19	12	16	100
KRT 35-12	E 08 470 60	35, M12	13	8.5	49	2.9	21	12	16	100
KRT 35-16	E 08 470 61	35, M16	17	8.5	58	2.5	25	12	16	100
KRT 50-6	E 08 470 62	50, M6	6.5	10	53	4	20	14	20	50
KRT 50-8	E 08 470 63	50, M8	8.5	10	53	4	20	14	20	50
KRT 50-10	E 08 470 64	50, M10	10.5	10	53	4	20	14	20	50
KRT 50-12	E 08 470 66	50, M12	13	10	56	3.5	22	14	20	50
KRT 50-16	E 08 470 67	50, M16	17	10	63	3.4	25	14	20	50
KRT 70-6		70, M6	6.5	12	55	4	23	16	21	50
KRT 70-8	E 08 470 68	70, M8	8.5	12	55	4	23	16	21	50
KRT 70-10	E 08 470 70	70, M10	10.5	12	55	4	23	16	21	50
KRT 70-12	E 08 470 72	70, M12	13	12	58	4	23	16	21	50
KRT 70-16	E 08 470 73	70, M16	17	12	65	3.7	28	16	21	50
KRT 95-6		95, M6	6.5	13.5	60	4.5	26	18	24	50

Artikelnummer / Article No.	E-nummer	Area (mm ²), hål / Area, stud	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)	G (mm)	Antal/frp / Qty/box
KRT 95-8	E 08 470 74	95, M8	8.5	13.5	60	4.5	26	18	24	50
KRT 95-10	E 08 470 75	95, M10	10.5	13.5	60	4.5	26	18	24	50
KRT 95-12	E 08 470 76	95, M12	13	13.5	63	4.5	26	18	24	50
KRT 95-16	E 08 470 78	95, M16	17	13.5	69	4	28	18	24	50
KRT 95-20	E 08 470 79	95, M20	20,5	15	74	4	32	20	24	50
KRT 120-6		120, M6	6,5	15	64	4	28	19	24	50
KRT 120-8	E 08 470 80	120, M8	8,5	15	64	4	28	19	24	50
KRT 120-10	E 08 470 81	120, M10	10.5	15	64	4	28	19	24	50
KRT 120-12	E 08 470 82	120, M12	13	15	64	4	28	19	24	50
KRT 120-16	E 08 470 84	120, M16	17	15	70	4	28	19	24	50
KRT 120-20	E 08 470 85	120, M20	21	15	77	4	28	19	24	50
KRT 150-8		150, M8	8.5	17	76	5	32	22	28	50
KRT 150-10	E 08 470 86	150, M10	10.5	17	76	5	32	22	28	50
KRT 150-16	E 08 470 88	150, M16	17	17	76	5	32	22	28	50
KRT 150-12	E 08 470 87	150, M12	13	17	76	5	32	22	28	50
KRT 150-20	E 08 470 89	150, M20	21	17	83	5	32	22	28	50
KRT 185-10	E 08 470 90	185, M10	10.5	19	79	5	35	24	30	50
KRT 185-12	E 08 470 91	185, M12	13	19	79	5	35	24	30	50
KRT 185-16	E 08 470 92	185, M16	17	19	79	5	35	24	30	50
KRT 185-20	E 08 470 93	185, M20	21	19	86	5	35	24	30	50
KRT 240-12	E 08 470 94	240, M12	13	21	86	5	38	26	35	25
KRT 240-16	E 08 470 96	240, M16	17	21	86	5	38	26	35	25
KRT 240-20	E 08 470 98	240, M20	21	21	93	5	38	26	35	25
KRT 300-12	E 08 470 99	300, M12	13	24	100	6	44	30	40	25
KRT 300-16	E 08 471 00	300, M16	17	24	100	6	44	30	40	25
KRT 300-20	E 08 471 01	300, M20	21	24	100	6	44	30	40	25
KRT 400-12	E 08 471 02	400, M12	13	26	114	6	48	32	42	25
KRT 400-16	E 08 471 03	400, M16	17	26	114	6	48	32	42	25
KRT 400-20	E 08 471 04	400, M20	21	26	114	6	48	32	42	25