


PRODUCT DATASHEET CP17588_LEILA-SC-D

LEILA-SC-D

~14° diffused spot beam

SPECIFICATION:

Dimensions	Ø 21.6 mm
Height	14.8 mm
Fastening	clips
ROHS compliant	yes 🛈



MATERIALS:


Component LXP2-D LEILA-SC-HLD **Type** Single lens Holder

Material	Colour	Finish
PMMA	clear	
PC	black	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CP17588_LEILA-SC-D	Single lens	1680	336	112	7.7
» Box size: 480 x 280 x 300 mm					

PRODUCT DATASHEET CP17588_LEILA-SC-D



R

See also our general installation guide: www.ledil.com/installation_guide



OPTICAL RESULTS (MEASURED):

OSRAM Opto Semiconductors		50*
LED	OSLON Square CSSRM2/CSSRM3	75
FWHM / FWTM	14.0° / 31.5°	
Efficiency	87 %	605 60'
Peak intensity	8.1 cd/lm	3300
LEDs/each optic	1	
Light colour	White	47°
Required compone	ints:	450 24 25 0 27
OSRAM Opto Semiconductors		90*
LED	OSLON SSL 150	75.
FWHM / FWTM	13.0° / 30.0°	
Efficiency	89 %	60%
Peak intensity	9.8 cd/lm	
LEDs/each optic	1	
Light colour	White	43° 43°
Required compone	ints:	



OPTICAL RESULTS (SIMULATED):

CREES LED LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	CLR6A-TKW 14.0° / 34.0° 93 % 8.3 cd/lm 1 RGBW	50° 50° 50° 50° 60° 50° 60° 60° 600 60° 600 60° 600 60° 600 60°
LED FWHM / FWTM	XP-G3 12.0° / 24.0°	90° 97°
Efficiency Peak intensity LEDs/each optic Light colour	95 % 15.4 cd/lm 1 White	
Required components:		20° <u>10°</u> 20° 30°
)S	90* 90*
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	LUXEON C 10.0° / 21.0° 87 % 19.4 cd/lm 1 White	25 25 25 25 25 25 25 25 25 25
OSRAM Opto Semiconductors LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	OSCONIQ P 3737 (3W version) 14.0° / 32.0° 93 % 9.6 cd/lm 1 White	50° 50° 50° 50° 50° 50° 50° 50° 50° 50°



OPTICAL RESULTS (SIMULATED):

SEOUL SEMICONDUCTOR		30*
LED	Z5M4	21
FWHM / FWTM	12.0° / 30.0°	27
Efficiency	94 %	200
Peak intensity	9.9 cd/lm	
LEDs/each optic	1	
Light colour	White	g. <u>600</u>
Required component	S:	



PRODUCT DATASHEET CP17588_LEILA-SC-D

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc. 228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd. # 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support www.ledil.com/ where_to_buy

Shipping locations Salo, Finland Hong Kong, China

Distribution Partners www.ledil.com/ where_to_buy