

# SAFETY DATA SHEET

Regulation (EC) No 1907/2006 (REACH), Annex II  
(COMMISSION REGULATION (EU) No 453/2010)

Version 1  
Product Name WB Ink Red

Issue Date 30-Jun-2015  
Revision date 30-Jun-2015

## SECTION 1: Identification of the substance /mixture and of the company/undertaking

### 1.1. Product identifier

Product Name WB Ink Red  
Product Code BFB-3254  
REACH registration number No information available

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use Used to whiteboard marker-pen inks.  
Uses advised against No information available

### 1.3. Details of the supplier of the safety data sheet

Supplier Suzhou Xiongying Ink Technology Co., Ltd.  
Address No. 539, Yunli road, Economic development zone of Wujiang City, Jiangsu Province, China  
Postal Code 215217  
Phone +86-512-63331385  
FAX +86-512-63320778  
E-mail zhangshenghong001@126.com

### 1.4. Emergency telephone number

+86-512-63331385

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Flammable liquids Category 2 - (H225)  
Serious eye damage/eye irritation Category 2 - (H319)  
Specific target organ toxicity (single exposure) Category 3 - (H336)

### 2.2. Label elements

Symbols/Pictograms



Signal word

Danger

Hazard Statements

H225 - Highly flammable liquid and vapor  
H319 - Causes serious eye irritation  
H336 - May cause drowsiness or dizziness

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. – No smoking.  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P271 - Use only outdoors or in a well-ventilated area  
P405 - Store locked up  
P280 - Wear protective gloves/protective clothing/eye protection/face protection  
P370 + P378 - In case of fire: Use CO2, dry chemical powder, water spray to extinguish

**2.3. Other hazards**

No information available.

**SECTION 3: Composition/information on ingredients****3.1 Mixture**

Chemical Name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Ethanol	200-578-6	64-17-5	50-60	Flam. Liq. 2 (H225)
1-methoxypropan-2-ol	203-539-1	107-98-2	10-25	STOT SE 3 (H336) Flam. Liq. 3 (H226)
Propane-1,2-dio	200-338-0	57-55-6	10-25	Not classified
Propan-2-ol	200-661-7	67-63-0	2.5-10	Eye Irrit. 2 (H319) STOT SE 3 (H336) Flam. Liq. 2 (H225)
Vinyl Butyral Polymers	-	63148-65-2	3.5-5	Not classified
C.I. pigment red 254	-	84632-65-5	3.5-5	Not classified
Additive	247-569-3	26266-58-0	0.5-2	Not classified

**SECTION 4: First aid measures****4.1. Description of first aid measures****General advice**

In all cases of doubt, or when symptoms persist, seek medical attention.

**Inhalation**

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.

**Skin Contact**

Immediately wash with water and soap and rinse thoroughly.

**Eye contact**

Rinse eyes immediately with plenty of water for at least 15 minutes. Remove contact lenses and continue flushing. Get medical attention if irritation persists.

**Ingestion**

Induce vomiting, if person is conscious. Seek medical help.

**4.2. Most important symptoms and effects, both acute and delayed**

No information available

**4.3. Indication of any immediate medical attention and special treatment needed**

Treat symptomatically.

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media**

CO2, dry chemical powder, water spray.

**Unsuitable extinguishing media**

No information available.

**5.2. Special hazards arising from the substance or mixture**

Formation of toxic gases is possible during heating or in case of fire.  
 In case of fire, the following can be released:  
 Carbon monoxide (CO), Carbon dioxide  
 Other irritating and toxic gases.

### 5.3. Advice for firefighters

Fire-fighters should wear appropriate breathing apparatus and protective equipment. Prevent fire-fighting water from entering surface water or groundwater.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Refer to Section 8 for personal protective equipment. Ensure adequate ventilation. Remove all sources of ignition. Evacuate personnel to safe areas.

### 6.2. Environmental precautions

Do not allow material to be released into the soil, sewerage systems and surface water.  
 Inform respective authorities in case of seepage into water course or sewage system.

### 6.3. Methods and material for containment and cleaning up

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
 Dispose of the material collected according to regulations.

### 6.4. Reference to other sections

See Section 7 for more information  
 See section 8 for more information  
 See section 13 for more information

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Handle in accordance with good industrial hygiene and safety practice. Use personal protective equipment as required.  
 Do not get in eyes, on skin, or on clothing. Wash thoroughly after handling. Use this material with adequate ventilation.  
 Keep ignition sources away - Do not smoke.

### 7.2. Conditions for safe storage, including any incompatibilities

Store in cool, dry and well-ventilated place. Keep away from heat and ignition sources. Store away from incompatible materials.

### 7.3. Specific end use(s)

Apart from the uses mentioned in SECTION 1.2 no other specific uses are stipulated.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

Chemical Name	Australia	Austria	Belgium	Denmark	European Union
Ethanol (CAS #: 64-17-5)	1000 ppm 1880 mg/m <sup>3</sup>	STEL 2000 ppm STEL 3800 mg/m <sup>3</sup> TWA: 1000 ppm TWA: 1900 mg/m <sup>3</sup>	-	TWA: 1000 ppm TWA: 1900 mg/m <sup>3</sup>	-
Propane-1,2-dio(CAS #: 57-55-6)	150 ppm 474 mg/m <sup>3</sup> 10 mg/m <sup>3</sup>	-	-	-	-
Propan-2-ol (CAS #: 67-63-0)	400 ppm 983 mg/m <sup>3</sup> 500 ppm STEL 1230 mg/m <sup>3</sup> STEL	STEL 800 ppm STEL 2000 mg/m <sup>3</sup> TWA: 200 ppm TWA: 500 mg/m <sup>3</sup>	-	TWA: 200 ppm TWA: 490 mg/m <sup>3</sup>	-

1-methoxypropan-2-ol(CAS #: 107-98-2)	100 ppm 369 mg/m <sup>3</sup> 150 ppm STEL 553 mg/m <sup>3</sup> STEL	Skin STEL 50 ppm STEL 187 mg/m <sup>3</sup> TWA: 50 ppm TWA: 187 mg/m <sup>3</sup> Ceiling 50 ppm Ceiling 187 mg/m <sup>3</sup>	-	TWA: 50 ppm TWA: 185 mg/m <sup>3</sup> Skin	S* TWA 100 ppm TWA 375 mg/m <sup>3</sup> STEL 150 ppm STEL 568 mg/m <sup>3</sup>
---------------------------------------	--	---	---	---	--

Chemical Name	Latvia	France	Finland	Germany	Italy
Ethanol (CAS #: 64-17-5)	TWA: 1000 mg/m <sup>3</sup>	TWA: 1000 ppm TWA: 1900 mg/m <sup>3</sup> STEL: 5000 ppm STEL: 9500 mg/m <sup>3</sup>	TWA: 1000 ppm TWA: 1900 mg/m <sup>3</sup> STEL: 1300 ppm STEL: 2500 mg/m <sup>3</sup>	TWA: 500 ppm TWA: 960 mg/m <sup>3</sup> Ceiling / Peak: 1000 ppm Ceiling / Peak: 1920 mg/m <sup>3</sup> Skin	-
Propane-1,2-dio(CAS #: 57-55-6)	TWA: 7 mg/m <sup>3</sup>	-	-	-	-
Propan-2-ol (CAS #: 67-63-0)	TWA: 350 mg/m <sup>3</sup> STEL: 600 mg/m <sup>3</sup>	STEL: 400 ppm STEL: 980 mg/m <sup>3</sup>	TWA: 200 ppm TWA: 500 mg/m <sup>3</sup> STEL: 250 ppm STEL: 620 mg/m <sup>3</sup>	TWA: 200 ppm TWA: 500 mg/m <sup>3</sup> Ceiling / Peak: 400 ppm Ceiling / Peak: 1000 mg/m <sup>3</sup>	-
1-methoxypropan-2-ol(CAS #: 107-98-2)	TWA: 100 ppm TWA: 375 mg/m <sup>3</sup> STEL: 150 ppm STEL: 568 mg/m <sup>3</sup> Skin	TWA: 50 ppm TWA: 188 mg/m <sup>3</sup> STEL: 100 ppm STEL: 375 mg/m <sup>3</sup>	TWA: 100 ppm TWA: 370 mg/m <sup>3</sup> STEL: 150 ppm STEL: 560 mg/m <sup>3</sup> Skin	TWA: 100 ppm TWA: 370 mg/m <sup>3</sup> Ceiling / Peak: 200 ppm Ceiling / Peak: 740 mg/m <sup>3</sup>	TWA: 100 ppm TWA: 375 mg/m <sup>3</sup> STEL: 150 ppm STEL: 568 mg/m <sup>3</sup> Skin

Chemical Name	Poland	Portugal	Spain	Switzerland	Netherlands
Ethanol (CAS #: 64-17-5)	TWA: 1900 mg/m <sup>3</sup>	TWA: 1000 ppm	STEL: 1000 ppm STEL: 1910 mg/m <sup>3</sup> TWA: 1000 ppm TWA: 1910 mg/m <sup>3</sup>	STEL: 1000 ppm STEL: 1920 mg/m <sup>3</sup> TWA: 500 ppm TWA: 960 mg/m <sup>3</sup>	Skin STEL: 1900 mg/m <sup>3</sup> TWA: 260 mg/m <sup>3</sup>
Propan-2-ol (CAS #: 67-63-0)	STEL: 1200 mg/m <sup>3</sup> TWA: 900 mg/m <sup>3</sup>	STEL: 400 ppm TWA: 200 ppm	STEL: 400 ppm STEL: 1000 mg/m <sup>3</sup> TWA: 200 ppm TWA: 500 mg/m <sup>3</sup>	STEL: 400 ppm STEL: 1000 mg/m <sup>3</sup> TWA: 200 ppm TWA: 500 mg/m <sup>3</sup>	-
1-methoxypropan-2-ol(CAS #: 107-98-2)	STEL: 360 mg/m <sup>3</sup> TWA: 180 mg/m <sup>3</sup>	STEL: 150 ppm TWA: 100 ppm	S* STEL: 150 ppm STEL: 568 mg/m <sup>3</sup> TWA: 100 ppm TWA: 375 mg/m <sup>3</sup>	STEL: 200 ppm STEL: 720 mg/m <sup>3</sup> TWA: 100 ppm TWA: 360 mg/m <sup>3</sup>	Skin STEL: 563 mg/m <sup>3</sup> TWA: 375 mg/m <sup>3</sup>

Chemical Name	Norway	United Kingdom	ACGIH TLV	OSHA PEL	NIOSH IDLH
Ethanol (CAS #: 64-17-5)	TWA: 500 ppm TWA: 950 mg/m <sup>3</sup> STEL: 500 ppm STEL: 950 mg/m <sup>3</sup>	STEL: 3000 ppm STEL: 5760 mg/m <sup>3</sup> TWA: 1000 ppm TWA: 1920 mg/m <sup>3</sup>	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1900 mg/m <sup>3</sup> (vacated) TWA: 1000 ppm (vacated) TWA: 1900 mg/m <sup>3</sup>	IDLH: 3300 ppm TWA: 1000 ppm TWA: 1900 mg/m <sup>3</sup>
Propane-1,2-dio(CAS #: 57-55-6)	TWA: 25 ppm TWA: 79 mg/m <sup>3</sup> STEL: 25 ppm STEL: 79 mg/m <sup>3</sup>	-	-	-	-

Propan-2-ol (CAS #: 67-63-0)	TWA: 100 ppm TWA: 245 mg/m <sup>3</sup> STEL: 100 ppm STEL: 245 mg/m <sup>3</sup>	STEL: 500 ppm STEL: 1250 mg/m <sup>3</sup> TWA: 400 ppm TWA: 999 mg/m <sup>3</sup>	STEL: 400 ppm TWA: 200 ppm	TWA: 400 ppm TWA: 980 mg/m <sup>3</sup> (vacated) TWA: 400 ppm (vacated) TWA: 980 mg/m <sup>3</sup> (vacated) STEL: 500 ppm (vacated) STEL: 1225 mg/m <sup>3</sup>	IDLH: 2000 ppm TWA: 400 ppm TWA: 980 mg/m <sup>3</sup> STEL: 500 ppm STEL: 1225 mg/m <sup>3</sup>
1-methoxypropan-2-ol(CAS #: 107-98-2)	TWA: 50 ppm TWA: 180 mg/m <sup>3</sup> Skin STEL: 50 ppm STEL: 180 mg/m <sup>3</sup>	STEL: 150 ppm STEL: 560 mg/m <sup>3</sup> TWA: 100 ppm TWA: 375 mg/m <sup>3</sup> Skin	STEL: 100 ppm TWA: 50 ppm	(vacated) TWA: 100 ppm (vacated) TWA: 360 mg/m <sup>3</sup> (vacated) STEL: 150 ppm (vacated) STEL: 540 mg/m <sup>3</sup>	TWA: 100 ppm TWA: 360 mg/m <sup>3</sup> STEL: 150 ppm STEL: 540 mg/m <sup>3</sup>

**Derived No Effect Level (DNEL)**

No information available

**Predicted No Effect Concentration (PNEC)**

No information available

**8.2. Exposure controls**

**Engineering Controls**

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment. Provide local exhaust or process enclosure ventilation system. The work area set safety shower and eyewash equipment.

**Personal protective equipment**

- Eye/face protection                      Tightly sealed goggles.
- Hand Protection                            Wear protective gloves.
- Skin and body protection                Suitable protective clothing.
- Respiratory protection                    Use suitable respiratory protective device in case of insufficient ventilation.

**Environmental exposure controls**

Do not allow into any sewer, on the ground or into any body of water.

**SECTION 9: Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

<b>Appearance</b>	Liquid
<b>Color</b>	Red
<b>Odor</b>	Slight alcohol smell
<b>Odor Threshold</b>	Not determined
<b>pH</b>	Not determined
<b>Melting point/freezing point</b>	-114 °C
<b>Boiling point / boiling range</b>	78 °C
<b>Flash point</b>	Not determined
<b>Evaporation rate</b>	Not determined
<b>Flammability (solid, gas)</b>	Not determined
<b>Flammability Limit in Air</b>	Not determined
<b>Vapor Pressure</b>	Not determined
<b>Vapor density</b>	Not determined
<b>Density</b>	Not determined
<b>Relative density</b>	Not determined
<b>Specific gravity</b>	Not determined
<b>Water solubility</b>	Not miscible or difficult to mix.
<b>Partition coefficient (LogPow)</b>	Not determined

<b>Autoignition temperature</b>	Product is not selfigniting.
<b>Decomposition temperature</b>	Not determined
<b>Kinematic viscosity</b>	Not determined
<b>Dynamic viscosity</b>	Not determined
<b>Explosive properties</b>	Not an explosive
<b>Oxidizing properties</b>	Not determined

**9.2. Other information**  
No information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Stable under recommended storage and handling conditions (see section 7, handling and storage).

### 10.2. Chemical stability

Stable under normal conditions of use, storage and transport.

### 10.3. Possibility of hazardous reactions

None under normal processing.

### 10.4. Conditions to avoid

Strong heating, fire. Incompatible materials.

### 10.5. Incompatible materials

Strong acids, strong bases or strong oxidizing agents.

### 10.6. Hazardous decomposition products

Carbon monoxide and carbon dioxide  
Other irritating and toxic gases.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

#### Acute toxicity

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Ethanol (CAS #: 64-17-5)	10470 mg/kg bw (rat)	-	124.7 mg/L (Rat) 4h
Propane-1,2-dio(CAS #: 57-55-6)	22000 mg/kg bw(rat)	> 2000 mg/kg bw(rabbit)	> 317042 mg/m <sup>3</sup> (rabbit)
Propan-2-ol (CAS #: 67-63-0)	= 1870 mg/kg ( Rat )	= 4059 mg/kg ( Rabbit )	= 72600 mg/m <sup>3</sup> ( Rat ) 4 h
1-methoxypropan-2-ol(CAS #: 107-98-2)	= 5000 mg/kg ( Rat )	= 13 g/kg ( Rabbit )	> 6 mg/L ( Rat ) 4 h

#### Skin corrosion/irritation

Non-irritating to the skin.

#### Serious eye damage/eye irritation

Causes serious eye irritation.

#### Sensitization

No sensitization responses were observed.

#### Germ cell mutagenicity

No information available.

#### Carcinogenicity

Chemical Name	European Union	IARC
---------------	----------------	------

Ethanol (CAS #: 64-17-5)	-	Group 1
Propan-2-ol (CAS #: 67-63-0)	-	Group 1 Group 3

**Reproductive toxicity**

No information available.

**STOT - single exposure**

No information available.

**STOT - repeated exposure**

May cause drowsiness or dizziness.

**Aspiration hazard**

No information available.

**SECTION 12: Ecological information****12.1. Toxicity**

Chemical Name	Algae/aquatic plants EC50	Fish LC50	Crustacea EC50
Ethanol (CAS #: 64-17-5)	-	14200 mg/l/96h Pimephales promelas	5012 mg/L/48h Daphnia magna
Propane-1,2-dio(CAS #: 57-55-6)	19000: 96 h Pseudokirchneriella subcapitata mg/L EC50	51600: 96 h Oncorhynchus mykiss mg/L LC50 static 41 - 47: 96 h Oncorhynchus mykiss mL/L LC50 static 51400: 96 h Pimephales promelas mg/L LC50 static 710: 96 h Pimephales promelas mg/L LC50	-
Propan-2-ol (CAS #: 67-63-0)	1000: 96 h Desmodesmus subspicatus mg/L EC50 1000: 72 h Desmodesmus subspicatus mg/L EC50	9640: 96 h Pimephales promelas mg/L LC50 flow-through 11130: 96 h Pimephales promelas mg/L LC50 static 1400000: 96 h Lepomis macrochirus µg/L LC50	13299: 48 h Daphnia magna mg/L EC50
1-methoxypropan-2-ol(CAS #: 107-98-2)	-	20.8: 96 h Pimephales promelas g/L LC50 static 4600 - 10000: 96 h Leuciscus idus mg/L LC50 static	23300: 48 h Daphnia magna mg/L EC50

**12.2. Persistence and degradability**

No information available.

**12.3. Bioaccumulative potential**

Chemical Name	Partition coefficient (LogPow)
Ethanol (CAS #: 64-17-5)	-0.32
Propan-2-ol (CAS #: 67-63-0)	0.05
1-methoxypropan-2-ol(CAS #: 107-98-2)	-0.437

Chemical Name	Bioconcentration factor (BCF)
Propane-1,2-dio(CAS #: 57-55-6)	<1
1-methoxypropan-2-ol(CAS #: 107-98-2)	<2

**12.4. Mobility in soil**

No information available

**12.5. Results of PBT and vPvB assessment**

PBT/vPvB assessment information is not available as chemical safety assessment not conducted.

**12.6. Other adverse effects**

No information available

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

Waste from residues/unused products Disposal should be in accordance with applicable regional, national and local laws and regulations

Contaminated packaging Disposal should be in accordance with applicable regional, national and local laws and regulations

**SECTION 14: Transport information**

14.1 UN Number Not regulated

14.2 Proper shipping name Not regulated

14.3 Hazard Class Not regulated

14.4 Packing Group Not regulated

14.5 Environmental hazards Not applicable

14.6 Special precautions No information available

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Chemical Name	French RG number	Title
Ethanol (CAS #: 64-17-5)	RG 84	-
Propane-1,2-dio(CAS #: 57-55-6)	RG 84	-
Propan-2-ol (CAS #: 67-63-0)	RG 84	-
1-methoxypropan-2-ol(CAS #: 107-98-2)	RG 84	-

**European Union**

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Take note of Directive 94/33/EC on the protection of young people at work

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

**International Inventories**

Component	TSCA	DSL/NDSL	EINECS/ELI NCS	ENCS	IECSC	KECL	PICCS	AICS
Ethanol 64-17-5	X	X	X	X	X	X	X	X
Propane-1,2-dio 57-55-6	X	X	X	X	X	X	X	X
Propan-2-ol 67-63-0	X	X	X	X	X	X	X	X
1-methoxypropan-2- ol 107-98-2	X	X	X	X	X	X	X	X
Polyvinyl butyral 63148-65-2	X	X	-	X	X	X	X	X



C.I. pigment red 254 84632-65-5	X	X	X	X	X	X	X	X
Additive 26266-58-0	X	X	X	X	X	X	X	X

"-" Not Listed

"X" Listed

## 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006

**Issue Date** 30-Jun-2015  
**Revision date** 30-Jun-2015  
**Revision Note** Not applicable

### Key or legend to abbreviations and acronyms used in the safety data sheet

**TWA** - TWA (time-weighted average)

**STEL** - STEL (Short Term Exposure Limit)

**Ceiling** - Maximum limit value

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**EINECS/ELINCS** - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

**ENCS** - Japan Existing and New Chemical Substances

**IECSC** - China Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

### Full text of H-Statements referred to under section 3

H336 - May cause drowsiness or dizziness

H226 - Flammable liquid and vapor

H225 - Highly flammable liquid and vapor

H319 - Causes serious eye irritation

### Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

----- End of Safety Data Sheet -----