

Directional spool valves, direct operated, with solenoid actuation

Type WE

RE 23327

Edition: 2013-05 Replaces: 08.08



Features

- ► 4/3, 4/2 or 3/2 directional design
- High-power solenoid
- Porting pattern according to ISO 4401-05-04-0-05 and NFPA T3.5.1 R2-2002 D05
- ▶ Wet-pin AC solenoids with detachable coil
- Solenoid coil can be rotated by 90°
- The coil can be changed without having to open the pressure-tight chamber
- ► Electrical connection as individual or central connection
- Manual override, optional

- ► Size 10
- Component series 3X; 4X
- Maximum operating pressure 315 bar [4569 psi]
- ▶ Maximum flow 120 l/min [31.7 US gpm]

Contents

Features	1
Contents	1
Ordering codes	2
Symbols	3
Function, section	4
Function, section	5
Technical data	6, 7
Characteristic curves	8
Performance limits	9, 10
Dimensions	11 13
Mating connectors	14
Further information	14

Ordering codes

01	02	03	04	05		06	07	08	09	10	11		12	13	14	15	16
	WE	10			/		С					1					*

01	3 main ports	3
	4 main ports	4
02	Directional valve	WE
03	Size 10	10
04	Symbols e.g. C, E, EA, EB, etc; for the possible version, see page 3	
05	Component series 30 39 (30 39: Unchanged installation and mounting dimensions)	3X
	Component series 40 49 (40 49: Unchanged installation and mounting dimensions)	4X
06	With spring return	no code
	Without spring return	0
	Without spring return with detent	OF
07	High performance wet-pin solenoid with detachable coil	С
08	AC voltage 230 V 50/60 Hz	W230
	For further ordering codes for other voltages and frequencies, see page 7; for direct voltage, see data sheet 23340	
09	With concealed manual override (standard)	N9
	With manual override	N
	Without manual override	no code

Electrical connection

10	Individual connection			
	Without mating connector; connector DIN EN 175301-803K4 1)			
	Central connection			
	Cable entry at the cover, with indicator light	DL		
	Central plug-in connection at the cover, with indicator light (without mating connector)	DK6L		
	For further electrical connections, see data sheet 08010			

Spool position monitoring

11	Without position switch	no code
	- Inductive position switch type QM	
	Monitored spool position "a"	QMAG24
	Monitored spool position "b"	QMBG24
	Monitored rest position	QM0G24
	For further information, see data sheet 24830	

12	Without throttle insert	no code		
	Throttle Ø 0.8 mm [0.031 inch]	B08		
	Throttle Ø 1.0 mm [0.039 inch]	B10		
	Throttle Ø 1.2 mm [0.047 inch]	B12		
	Use with flows which exceed the performance limit of the valve (see page 4).			


Seal material


13	NBR seals	no code			
	FKM seals	V			
	Attention: Observe compatibility of seals with hydraulic fluid used! (Other seals upon request)				
14	Further details in the plain text				


¹⁾ Mating connectors, separate order, see page 14 and data sheet 08006.


Notice! Preferred types and standard units are contained in the EPS (standard price list).

Symbols










¹⁾ Example:

Symbol E with spool position "a", ordering code .. EA..



Representation according to DIN ISO 1219-1. Hydraulic interim positions are shown by dashes.



Function, section

The directional valve type WE is a solenoid actuated directional spool valve. It controls the start, stop and direction of a flow.


The directional valve basically consists of the housing (1), one or two electronic solenoids (2), the control spool (3), and the return springs (4).

In the de-energized condition, the control spool (3) is held in the central position or in the initial position by the return springs (4) (except for version "O"). The control spool (3) is actuated by wet-pin electronic solenoids (2). The force of electronic solenoid (2) acts via the plunger (5) on the control spool (3) and pushes the latter from its rest position to the required end position. This enables the necessary direction of flow from P to A and B to T or P to B and A to T. When the electronic solenoid (2) is de-energized, the return spring (4) pushes the control spool (3) back to its rest position.

A manual override (6) allows for the manual switching of the valve without solenoid energization.


To ensure proper functioning, make sure that the pressure chamber of the solenoid is filled with oil.

For additional functions, see page 5.



Throttle insert "B.."

Using a throttle insert (7) in channels P, A, B or T increases the flow resistance at the valve. Its use is required when due to prevailing operating conditions, flows occur during the switching processes, which exceed the performance limit of the valve.



Function, section

Without spring return "O" (only possible with symbols A, C and D)


This version is a directional valve with 2 spool positions and 2 electronic solenoids **without** detent. The valve without spring return at the control spool (3) has no defined basic position in the de-energized condition.

Without spring return with "OF" detent (only possible with symbols A, C and D)

This version is a directional valve with 2 spool positions and 2 electronic solenoids **with** detent. The detents are used to fix the control spool (3) in the relevant spool position. During operation, continuous application of current to the electronic solenoid can therefore be omitted which contributes to energy-efficient operation.

Notice!

Pressure peaks in the tank line to two or several valves can result in unwanted control spool movements in the case of valves with detent! We therefore recommend that separate return lines be provided or a check valve installed in the tank line.



Type .WE 10 ../OF...

Technical data

(for applications outside these parameters, please consult us!)

general				
Weight			Individual connection	Central connection
	- Valve with one solenoid	kg [lbs]	3.6 [7.9]	3.5 [7.7]
	- Valve with two solenoids	kg [lbs]	4.4 [9.7]	4.3 [9.5]
Installation posi	tion		Any	
Ambient temperature range °C [%]		-30 +50 [-22 +122] (NBR seals) -20 +50 [-4 +122] (FKM seals)		
MTTF _d values according to EN ISO 13849 Years		150 (for further details see data	sheet 08012)	

Maximum operating pressure	– Port A, B, P	bar [psi]	315 [4569]
	– Port T	bar [psi]	160 [2320]
			With symbols A and B, port T has to be used as leakage oil con- nection if the operating pressure exceeds the tank pressure.
Maximum flow		l/min [USgpm]	120 [31.7]
Flow cross-section (spool position 0)	– Symbol V	mm² [inch²]	11 [0.017] (A/B to T); 10.3 [0.016] (P to A/B)
	– Symbol W	mm² [inch²]	2.5 [0.004] (A/B to T)
	– Symbol Q	mm² [inch²]	5.5 [0.009] (A/B to T)
Hydraulic fluid			See table below
Hydraulic fluid temperature range °C [°F] (at the valve operating ports)			-30 +80 [-22 +176] (NBR seals) -20 +80 [-4 +176] (FKM seals)
Viscosity range mm ² /s [SUS]			2.8 500 [35 2320]
Maximum admissible degree of cleanliness class according to I		hydraulic fluid -	Class 20/18/15 1)

Hydraulic fluid		Classification	Suitable sealing materials	Standards	
Mineral oils		HL, HLP, HLPD, HVLP, HVLPD	NBR, FKM	DIN 51524	
	– insoluble in water	HETG	NBR, FKM	- VDMA 24568	
Bio-degradable	- insoluble in water	HEES	FKM		
	- soluble in water	HEPG	FKM	VDMA 24568	
	– water-free	HFDU, HFDR	FKM	ISO 12922	
Flame-resistant	– containing water	HFC (Fuchs Hydrotherm 46M, Petrofer Ultra Safe 620)	NBR	ISO 12922	

Important information on hydraulic fluids!

- ► For more information and data on the use of other hydraulic fluids, refer to data sheet 90220 or contact us!
- There may be limitations regarding the technical valve data (temperature, pressure range, life cycle, maintenance intervals, etc.)!
- ► The flash point of the hydraulic fluid used must be 40 K higher than the maximum solenoid surface temperature.

Flame-resistant – containing water:

Maximum pressure difference per control edge 50 bar
Pressure pre-loading at the tank port > 20% of the press

 Pressure pre-loading at the tank port > 20% of the pressure differential, otherwise increased cavitation

– Life cycle as compared to operation with mineral oil HL, HLP 50 to 100%

 Bio-degradable: When using bio-degradable hydraulic fluids that are simultaneously zinc-solving, zinc may accumulate in the fluid (per pole tube 700 mg zinc).

 The cleanliness classes specified for the components must be adhered to in hydraulic systems. Effective filtration prevents faults and at the same time increases the life cycle of the components. For the selection of the filters, see www.boschrexroth.com/filter.

Technical data

(for applications outside these parameters, please consult us!)

electric			
Voltage type			Alternating voltage 50/60 Hz
Available voltages ²⁾ (For ordering codes for AC voltage V solenoids, see below)			42, 110, 230
Voltage tolerance (nominal voltage) %			±10
Power consumption		W	-
Holding power		VA	90
Switch-on power		VA	550
Duty cycle (ED)		%	100
Switching time according	– ON	ms	15 25
to ISO 6403	– OFF	ms	20 30
Maximum switching frequenc	у	1/h	7200
Maximum surface temperatur	es of the coil ³⁾	°C [%]	180 [356]
Protection class according to	DIN EN 60529		IP 65 with mating connector mounted and locked
Insulation class VDE 0580			Н
Electrical protection			Every solenoid must be protected individually, using a suitable fuse with tripping characteristic K (inductive loads).
Behavior in case of an error (solenoid does not switch thoug	gh)	The solenoid surface temperature may be exceeded.

2) Special voltages on request

³⁾ Possible surface temperature > 50 °C, provide contact protection!

IF Notice!

- The solenoid coils must not be painted.
- Actuation of the manual override is only possible up to a tank pressure of approx. 50 bar [725 psi]. Avoid damage to the bore of the manual override! (Special tool for the operation, separate order, material no. **R900024943**). When the manual override is blocked, actuation of the opposite solenoid must be ruled out!
- The simultaneous actuation of 2 solenoids of one valve must be ruled out!
- ► Use cables that are approved for an operation temperature above 105 °C [221 °F].
- When solenoid coils are switched off, voltage peaks result which may cause failures or damage in the connected control electronics. The user has to provide for a suitable circuit for limiting the voltage peaks. It must be noted that a diode switched in an anti-parallel form extends the switching off time.
- Valves with individual connection and supply voltage 12 V or 24 V can be operated with twice the voltage for reducing the switching time. For this purpose, the voltage has to be reduced to the nominal valve voltage after 100 ms by means of pulse width modulation. The maximum admissible switching frequency is 5 1/s.
- Due to possible overloads of the printed-circuit board, valves with central connection must not be operated with twice the voltage.

Notice!


AC solenoids can be used for 2 or 3 mains; e.g. solenoid type W110 for: 110 V, 50 Hz; 110 V, 60 Hz; 120 V, 60 Hz

Ordering code	Mains
W42	42 V, 50 Hz 42 V, 60 Hz
W110	110 V, 50 Hz 110 V, 60 Hz 120 V, 60 Hz
W230	230 V, 50 Hz 230 V, 60 Hz

When establishing the electrical connection, the protective earthing conductor (PE \pm) has to be connected correctly.

Characteristic curves

(measured with HLP46, **9**_{oil} = 40 ± 5 °C [104 ± 9 °F])



Symbol		Directio	n of flow		
	P – A	P – B	A – T	В – Т	
А; В	3	3	-	-	
С	3	3	4	5	
D; Y	5	5	6	6	
E	1	1	4	4	
F	2	3	7	4	
G	3	3	6	7	
н	1	1	6	7	
J	1	1	3	3	
L	2	2	3	5	
М	1	1	4	5	
Р	4	2	5	7	
Q	1	2	1	3	
R	3	6	4	-	
т	3	3	6	7	
U; V	2	2	3	3	
W	2	2	4	5	

Symbol	Direction of flow							
	P – A	Р-В	В-Т	А – Т	P – T			
F	4	-	-	9	9			
Р	-	5	8	-	10			
G, T	-	_	_	-	9			
н	-	_	_	-	3			

Spool position:

Symbol	Direction of flow							
	P – A	B – A	А – Т	Р – Т				
R	-	9	-	-				

Bosch Rexroth AG, RE 23327, edition: 2013-05

Performance limits

(measured with HLP46, **9**_{oil} = 40 ± 5 °C [104 ± 9 °F])

IF Notice!

The specified performance limits are valid for operation with two directions of flow (e.g. from P to A and simultaneous return flow from B to T).

Due to the flow forces acting within the valves, the permissible performance limit may be considerably lower with only one direction of flow (e.g. from P to A while port B is blocked).

In such cases, please consult us.

The performance limits were determined when the solenoids were at operating temperature, at 10% undervoltage and without tank pre-loading.

Operating pressure in bar [psi] \rightarrow	[4569] [4000] [3000] [2000] [1000] -	- 315 - 300 - 250 - 200 - 150 - 100 - 50		5		4	4	5	8-		,7	3	2		
0	[0]	_ 0	1	0 2	0 3	0 4	0 5	0 6	0 7	/0 /0	80 9	4 00 1	00 11	0 120	0
		[0)]	[4]		Flov	[12] v in		16] n [US	[20 6 gpi	$n] \rightarrow$	24]	[28]	[31.7	7]
↑	[4569]	-315													

Characteristic curve	Symbol
1	C; C/O; C/OF; D; D/O; D/OF; Y
2	E; L; U; Q; W
3	A/O; A/OF; J
4	F; P
5	Т
6	Н
7	R
8 2)	L; U

²⁾ Central position only

42 V, 50 Hz; 110 V, 50 Hz; 120 V, 60 Hz; 127 V, 50 Hz; 220 V, 50 Hz; 240 V, 60 Hz

1	[4569]-	315		\mathbf{H}	+										
in bar [psi]	[4000]— —	- 250		10	\mathcal{A}	- 11			- 12			_ 9			
	[3000]—	- 200			N				12						
essure		- 150					K	11							
ing pr	_	- 100							\mathbb{R}						
Operating pressure	[1000]—	- 50						11		10					
	[0]—		1	0 2	0 3	04	05	06	07		09	l 0 10	00 11	0 12	20
		-						1							
		[0)]	[4]	[8		[12]		6]	[20]		24]	[28]	[31.	7]
						Flov	v in l	/mir	n [US	gpm] →				

Characteristic	Symbol				
curve					
9	Μ				
10	А, В				
11	G				
12	V				

42 V, 50 Hz; 110 V, 50 Hz; 120 V, 60 Hz; 127 V, 50 Hz; 220 V, 50 Hz; 240 V, 60 Hz

Performance limits

(measured with HLP46, **9**_{oil} = 40 ± 5 °C [104 ± 9 °F])


IF Notice!

The specified performance limits are valid for operation with two directions of flow (e.g. from P to A and simultaneous return flow from B to T).

Due to the flow forces acting within the valves, the permissible performance limit may be considerably lower with only one direction of flow (e.g. from P to A while port B is blocked).

In such cases, please consult us.


The performance limits were determined when the solenoids were at operating temperature, at 10% undervoltage and without tank pre-loading.




Characteristic curve	Symbol				
13	C; C/O; C/OF; D; D/O; D/OF; Y				
14	A/O; A/OF				
15	E				
16	М				
17	V				
18	Н				

42 V, 60 Hz; 110 V, 60 Hz; 127 V, 60 Hz; 220 V, 60 Hz Please consult us regarding the performance limits for other symbols.

Dimensions: Individual connection (dimensions in mm [inch])





Required surface quality of the valve contact surface


IF Notice!

- Deviating from ISO 4401, in this data sheet port T is called TA, port T1 is called TB.
- The dimensions are nominal dimensions which are subject to tolerances.

For item explanations, valve mounting screws and subplates, see page 13.

Dimensions: Central connection

(dimensions in mm [inch])



Terminal assignment with central connection:


▶ 1 solenoid:

Always connect the solenoid to terminals 1 and 2, the protective grounding conductor to terminal \bigoplus PE

► 2 solenoids:

Always connect solenoid "a" to terminals 1 and 2, solenoid "b" to terminals 3 and 4,

the protective grounding conductor to terminal $\textcircled{\blacksquare}$ PE



Required surface quality of the valve contact surface

IF Notice!

- Deviating from ISO 4401, in this data sheet port T is called TA, port T1 is called TB.
- The dimensions are nominal dimensions which are subject to tolerances.

For item explanations, valve mounting screws and subplates, see page 13.

Dimensions

- 1.1 Solenoid "a"
- 1.2 Solenoid "b"
 - 2 Dimension for solenoid **without** and **with concealed** manual override "N9" (standard)
 - 3 Dimension for solenoid with manual override "N"
 - 4 Cover
 - Attention!

The valve may only be operated with properly mounted cover.

- **5** Mating connector **without** circuitry (separate order, see page 14 and data sheet 08006)
- 6 Mating connector with circuitry (separate order, see page 14 and data sheet 08006)
- 7 Cable gland Pg 16 [1/2" NPT] "DL"
- 8 Angled socket (red, separate order) (material no. **R900005538**)
- 9 Name plate
- **10** Identical seal rings for ports A, B, P, TA, TB (for valves with throttle insert: O ring in channel P)
- 11 Plug screw for valves with one solenoid
- 12 Space required to remove the mating connector/ angled socket
- 13 Space required to remove the coil
- **14** Mounting nut, tightening torque $M_A = 6^{+2} \text{ Nm} [4.43^{+1.48} \text{ ft-lbs}]$
- **15** Porting pattern according to ISO 4401-05-04-0-05 and NFPA T3.5.1 R2-2002 D05
- **16** Connection TB can only be used in connection with separately produced bore.

Subplates according to data sheet 45054 (separate order) G 66/01 (G3/8) G 67/01 (G1/2) G 534/01 (G3/4) G 66/12 (SAE-6; 9/16-18)¹⁾ G 67/12 (SAE-8; 3/4-16)¹⁾ G 534/12 (SAE-12; 1-1/16-12)¹⁾ ¹⁾ On request

Valve mounting screws (separate order) 4 metric hexagon socket head cap screws ISO 4762 - M6 x 40 - 10.9-flZn-240h-L

(friction coefficient μ_{total} = 0.09 ... 0.14); tightening torque M_A = 12.5 Nm [9.2 ft-lbs] ± 10%, material no. **R913000058** or

4 hexagon socket head cap screws

ISO 4762 - M6 x 40 - 10.9 (self procurement) (friction coefficient μ_{total} = 0.12 ... 0.17); tightening torque **M**_A = 15.5 Nm [*11.4 ft-lbs*] ± 10%

4 UNC hexagon socket head cap screws 1/4-20 UNC x 1-1/2" ASTM-A574

(friction coefficient $\mu_{total} = 0.19 \dots 0.24$); tightening torque $M_A = 20 \text{ Nm} [14.7 \text{ ft-lbs}] \pm 15\%$, (friction coefficient $\mu_{total} = 0.12 \dots 0.17$); tightening torque $M_A = 14 \text{ Nm} [10.3 \text{ ft-lbs}] \pm 10\%$, material no. **R978800710**

With different friction coefficients, the tightening torques are to be adjusted accordingly!

Mating connectors according to DIN EN 175301-803

For details and more mating connectors see data sheet 08006							
	e			Material number			
Port	Valve side	Color	Without circuitry	With indicator light 12 240 V	With indicator light and Zener diodes- protection circuit 24 V		
	a	Gray	R901017010	-	-		
M16 x 1.5	b	Black	R901017011	-	-		
	a/b	Black	-	R901017022	R901017026		
	a	Red/brown	R900004823	-	-		
1/2" NPT (Pg 16)	b	Black	R900011039	-	-		
(1 g 10)	a/b	Black	-	R900057453	-		

Further information

- Subplates
- Inductive position switches and proximity sensors (contactless)
- Version with DC solenoids
- Hydraulic fluids on mineral oil basis
- ▶ Reliability characteristics according to EN ISO 13849
- General product information on hydraulic products
- ► Installation, commissioning and maintenance of industrial valves
- Selection of the filters

Data sheet 45054 Data sheet 24830 Data sheet 23340 Data sheet 90220 Data sheet 08012 Data sheet 07008 Data sheet 07300 www.boschrexroth.com/filter

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52/18-0 documentation@boschrexroth.de www.boschrexroth.de © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Notes

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52/18-0 documentation@boschrexroth.de www.boschrexroth.de © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Notes