

Rod P/N	Freq (MHz)	Type	Gain (dBi)	Thread	Length (mm)	Base 128	Base NCD	Base 2500	Base 1123	Base 1131	MiniMag	MidiMag	MaxiMag	ANT
313.01.00.00	27	Quarter	2	M6	600	X		X	X	X			X	X
3183.01.00.00	27	Quarter	2	M6	379	X		X	X	X				X
314	40	Quarter	2	M6	1000	X			X	X				
3100.03.00.00	65-1000	Quarter	2	M6	<1098	X		X	X	X		X	X	X
310.06.00.00	68-225	Quarter	2	M6	<1121	X		X	X	X			X	X
3183.02.00.00	68-88	Quarter	2	M6	379	X		X	X	X				X
3183.03.00.00	88-108	Quarter	2	M6	379	X		X	X	X				X
358.01	88-108	Quarter	2	M6	675	X		X	X	X				
351.04.00.00	144-225	Colinear	4	M6	<1350	X			X	X		X		X
810	365-510	Colinear	5	M6	860		X							
851-1	365-510	Quarter	2	M6	283		X							
3126.04.00.00	375-480	Colinear	5	M6	<735	X		X	X	X		X	X	X
3132.13.00.00	380-445	Quarter	2	M6	145	X		X	X			X	X	X
3178.3	380-395	Colinear	8	M6	910				X			X		
3122.13.00.00	415-430	Colinear	5	M6	600	X		X	X	X			X	X

Rod P/N	Freq (MHz)	Type	Gain (dBi)	Thread	Length (mm)	Base 128	Base NCD	Base 2500	Base 1123	Base 1131	MiniMag	MidiMag	MaxiMag	ANT
51274+	430-470	Quarter	2	M3	144						X			
3132.01.00.00	445-470	Quarter	2	M6	130	X		X	X			X	X	X
3178.1	450-466	Colinear	8	M6	910	X		X	X	X				X
3126.01.00.00	450-470	Colinear	5	M6	565	X		X	X	X		X	X	X
3122.01.00.00	452-468	Colinear	5	M6	605	X		X	X	X			X	X
3206.1	450-470	Quarter	2	M4	143			X						
3178.1	450-466	Colinear	8	M6	910				X			X		
3146.383	806-870	Colinear	5	M6	203	X		X	X	X		X		
3146.838	806-870	Colinear	5	M6	285	X		X	X	X		X		X
3146.01	824-894	Colinear	5	M6	314	X		X	X	X		X		X
3157.01	824-894	Colinear	5	M6	277	X		X	X	X		X		
3146.03	872-960	Colinear	5	M6	275	X		X	X	X		X		X
3157.03	872-960	Colinear	5	M6	263	X		X	X	X		X		
3205	1600-2690	Quarter	2	M4	17			X						
3122.02.00.00	415-430	Colinear	5	M6	600	X		X	X	X			X	X