

TY528M



CBL TIE 50LB 14 NAT NYLON 2-PC D

General Information

Extended Product Type	TY528M
Product ID	7TAG009170R0003
EAN	5414363065890
Catalog Description	CBL TIE 50LB 14 NAT NYLON 2-PC D
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum or as a Flexible Cable and Conduit Support, Length of 360.5mm (14.2 Inches), Width of 4.82mm (0.19 Inches), Thickness of 1.4mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

Ordering

EAN	5414363065890
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.005 lb 2.268 g
--------------------	--------------------

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	5 in 127 mm
Package Level 1 Depth / Length	17.5 in 445 mm
Package Level 2 Units	500 piece
Package Level 2 Width	5.8 in 147 mm
Package Level 2 Height	15.5 in 394 mm
Package Level 2 Depth / Length	5.5 in 140 mm

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.138 to 4.01 in 3.5 to 102 mm

Color	Natural
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Standard
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standards	UL E49405
Surface Finishing	Untreated
Tensile Strength	50 lb 222 N
Thickness	0.055 in 1.4 mm
UPC	786210805139

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY528M
Instructions and Manuals	TY528M

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

