



SIRIUS SOFT STARTER, S2, 63A, 30KW/400V, 40 DEGR., AC 200-480V, AC/DC 24V, SCREW TERMINALS, THERMISTOR MOTOR PROTECTION

| General technical data:  |   |   |
|--|---|---|
| <b>product brand name</b>  |   | SIRIUS                                  |
| <b>Product feature</b>   |   |   |
| • integrated bypass contact system   |   | Yes                                     |
| • Thyristors   |   | Yes                                     |
| <b>Product function</b>  |   |   |
| • Intrinsic device protection  |   | Yes                                     |
| • motor overload protection  |   | Yes                                     |
| • Evaluation of thermistor motor protection  |   | Yes                                     |
| • External reset   |   | Yes                                     |
| • Adjustable current limitation  |   | Yes                                     |
| • inside-delta circuit   |   | No                                      |
| <b>Product component Motor brake output</b>  |   | No                                      |
| <b>Equipment marking acc. to DIN EN 61346-2</b>  |   | Q                                       |
| <b>Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750</b> |   | G                                       |
| Power Electronics:   |   |   |
| <b>Product designation</b>   |   | soft starters for standard applications |
| <b>Operating current</b>   |   |   |
| • at 40 °C Rated value   | A | 63                                      |
| • at 50 °C Rated value   | A | 58                                      |
| • at 60 °C Rated value   | A | 53                                      |
| <b>Mechanical power output for three-phase motors</b>                                      |   |   |
| • at 230 V   |   |   |

|   |              |             |
|---|--------------|-------------|
| — at standard circuit at 40 °C Rated value  | W            | 18 500      |
| • at 400 V  |              |             |
| — at standard circuit at 40 °C Rated value  | W            | 30 000      |
| <b>yielded mechanical performance [hp] for three-phase AC motor at 200/208 V at standard circuit at 50 °C Rated value</b> | metric<br>hp | 15          |
| Operating frequency Rated value   | Hz           | 50 ... 60   |
| <b>Relative negative tolerance of the operating frequency</b>   | %            | -10         |
| <b>Relative positive tolerance of the operating frequency</b>   | %            | 10          |
| Operating voltage at standard circuit Rated value   | V            | 200 ... 480 |
| <b>Relative negative tolerance of the operating voltage at standard circuit</b>   | %            | -15         |
| <b>Relative positive tolerance of the operating voltage at standard circuit</b>   | %            | 10          |
| Minimum load in % of I <sub>M</sub>   | %            | 20          |
| Adjustable motor current for motor overload protection minimum rated value  | A            | 26          |
| Continuous operating current in % of I <sub>e</sub> at 40 °C  | %            | 115         |
| Active power loss at operating current at 40 °C during operation typical  | W            | 12          |

#### Control electronics:

|   |    |       |
|---|----|-------|
| Type of voltage of the control supply voltage                                     |    | AC/DC |
| Control supply voltage frequency 1 Rated value                                    | Hz | 50    |
| Control supply voltage frequency 2 Rated value                                    | Hz | 60    |
| <b>Relative negative tolerance of the control supply voltage frequency</b>        | %  | -10   |
| <b>Relative positive tolerance of the control supply voltage frequency</b>        | %  | 10    |
| Control supply voltage 1 with AC  |    |       |
| • at 50 Hz Rated value  | V  | 24    |
| • at 60 Hz Rated value  | V  | 24    |
| <b>Relative negative tolerance of the control supply voltage with AC at 60 Hz</b> | %  | -20   |
| <b>Relative positive tolerance of the control supply voltage with AC at 60 Hz</b> | %  | 20    |
| Control supply voltage 1 for DC Rated value                                       | V  | 24    |
| <b>Relative negative tolerance of the control supply voltage for DC</b>           | %  | -20   |
| <b>Relative positive tolerance of the control supply voltage for DC</b>           | %  | 20    |
| Display version for fault signal  |    | red   |

#### Mechanical data:

|                               |  |    |
|-------------------------------|--|----|
| Size of engine control device |  | S2 |
|-------------------------------|--|----|

|  |    |  |
|--|----|--|
| <b>Width</b>   | mm | 55   |
| <b>Height</b>  | mm | 160  |
| <b>Depth</b>   | mm | 170  |
| <b>Mounting type</b>                                   |    | screw and snap-on mounting   |
| <b>mounting position</b>                               |    | With additional fan: With vertical mounting surface +/- 90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back<br>Without additional fan: With vertical mounting surface +/- 10° rotatable, with vertical mounting surface +/- 10° t |
| <b>Required spacing with side-by-side mounting</b>     |    |  |
| • upwards  | mm | 60   |
| • at the side  | mm | 30   |
| • downwards  | mm | 40   |
| <b>Installation altitude at height above sea level</b> | m  | 5 000  |
| <b>Cable length maximum</b>                            | m  | 300  |
| <b>Number of poles for main current circuit</b>        |    | 3  |

#### Connections/ Terminals:

|   |  |                                  |
|---|--|----------------------------------|
| <b>Type of electrical connection</b>  |  |                                  |
| • for main current circuit  |  | screw-type terminals             |
| • for auxiliary and control current circuit   |  | screw-type terminals             |
| <b>Number of NC contacts for auxiliary contacts</b>   |  | 0                                |
| <b>Number of NO contacts for auxiliary contacts</b>   |  | 2                                |
| <b>Number of CO contacts for auxiliary contacts</b>   |  | 1                                |
| Type of connectable conductor cross-section for main contacts for box terminal using the front clamping point |  |                                  |
| • solid   |  | 2x (1.5 ... 16 mm <sup>2</sup> ) |
| • finely stranded with core end processing  |  | 0.75 ... 25 mm <sup>2</sup>      |
| • stranded  |  | 0.75 ... 35 mm <sup>2</sup>      |
| Type of connectable conductor cross-section for main contacts for box terminal using the back clamping point  |  |                                  |
| • solid   |  | 2x (1.5 ... 16 mm <sup>2</sup> ) |
| • finely stranded with core end processing  |  | 1.5 ... 25 mm <sup>2</sup>       |
| • stranded  |  | 1.5 ... 35 mm <sup>2</sup>       |
| Type of connectable conductor cross-section for main contacts for box terminal using both clamping points     |  |                                  |
| • solid   |  | 2x (1.5 ... 16 mm <sup>2</sup> ) |
| • finely stranded with core end processing  |  | 2x (1.5 ... 16 mm <sup>2</sup> ) |
| • stranded  |  | 2x (1.5 ... 25 mm <sup>2</sup> ) |
| Type of connectable conductor cross-section for AWG conductors for main contacts for box terminal             |  |                                  |
| • using the back clamping point   |  | 16 ... 2                         |

|   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• using the front clamping point</li> <li>• using both clamping points</li> </ul>  | 18 ... 2<br>2x (16 ... 2)  |
| <b>Type of connectable conductor cross-section for auxiliary contacts</b> <ul style="list-style-type: none"> <li>• solid</li> <li>• finely stranded with core end processing</li> </ul>                                     | 2x (0.5 ... 2.5 mm <sup>2</sup> )<br>2x (0.5 ... 1.5 mm <sup>2</sup> ) |
| <b>Type of connectable conductor cross-section for AWG conductors</b> <ul style="list-style-type: none"> <li>• for auxiliary contacts</li> <li>• for auxiliary contacts finely stranded with core end processing</li> </ul> | 2x (20 ... 14)<br>2x (20 ... 16)                                       |

#### Ambient conditions:

|   |    |                            |
|---|----|----------------------------|
| <b>Ambient temperature</b> <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> </ul> | °C | -25 ... +60<br>-40 ... +80 |
| <b>Derating temperature</b>   | °C | 40                         |
| <b>Protection class IP</b>  |    | IP00                       |

#### Certificates/ approvals:

|                                 |            |                                       |
|---------------------------------|------------|---------------------------------------|
| <b>General Product Approval</b> | <b>EMC</b> | <b>For use in hazardous locations</b> |
|---------------------------------|------------|---------------------------------------|



|                          |                          |
|--------------------------|--------------------------|
| <b>Test Certificates</b> | <b>Shipping Approval</b> |
|--------------------------|--------------------------|

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)



|              |
|--------------|
| <b>other</b> |
|--------------|

[Declaration of Conformity](#)

[Environmental Confirmations](#)

#### UL/CSA ratings:

yielded mechanical performance [hp] for three-phase AC motor

- at 220/230 V

— at standard circuit at 50 °C Rated value

• at 460/480 V

— at standard circuit at 50 °C Rated value

|   |    |
|---|----|
| metric hp   | 20 |
| metric hp   | 40 |
| Contact rating of the auxiliary contacts acc. to UL |    |
| B300 / R300   |    |

Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RW40371TB04>


**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RW40371TB04/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RW40371TB04&lang=en>





last modified:

15.01.2015