

horizontal clamp with variable clamping height

with open clamping arm and angular base



Application:


Quick-action clamp with infinitely adjustable balancing function for workpieces with different clamping widths.

Version:

- galvanised and passivated.
- ergonomic, oil-resistant handle with large hand rest and soft components.
- protection against the loss of the clamping screw on the end of the clamping arm. complete with zinc-plated clamping bolt
- Size 20 clamping bolt M6 x 40 mm
- Size 50 clamping bolt M8 x 55 mm

Advantage:

- variable clamping height, for clamping different workpieces
- used for small lot sizes
- infinitely adjustable clamping force
- ergonomic 2 component handle
- protection against loss on clamping arm



Art. no.	26213 110
Size	20
Distance	6 mm
Basic length	56 mm
Min./max. length	20-26 mm
Drill hole	5.6 mm
Drill hole 2	5.6 mm
Length 2	22 mm
Length 3	24 mm
Height	68 mm
Overall height of lower handle	94 mm
Overall height of upper handle	113 mm
Max. adjustment range	24 mm
Min. adjustment range	-3 mm
Thickness	10 mm
Distance 2	7.1 mm
Length	173 mm
Base plate width	45 mm
Hole distance 3	25.4 mm
Base plate length	38 mm
Tension force	2 kN
Height 2	8 mm

EAN-Code

4020772003654