

Circular metal saw blade, HSS, finely toothed, form A

For universal use up to 1000 N/mm² in thin-walled workpieces and shallow cutting depths, on conventional machines

ORION[®]

Application:


For making saw cuts in thin-walled workpieces and shallow cutting depths in the material groups of steel, stainless steel, cast iron and non-ferrous metals.

Execution:

- Precision-ground circular metal saw blade with tooth shape A, finely toothed, laterally hollow ground, hole without keyway, up to a diameter of 160 mm without collar, from a diameter of 200 mm with collar

Advantage:

- Innovative cutting geometry ensures very high dimensional accuracy, process reliability and chip removal
- High-quality cutting material for very high service life requirements
- Universal use in numerous applications



Art. no.	14002 770
Brand	ORION
Manufacturer Part Number	14002770
Tooth shape	A
Cutting material	HSS
Thickness of cutting edge	2 mm
Tolerance of cutting edge diameter	js15
Tolerance of cutting edge thickness	js11
Tolerance of hole diameter	H7
Cutting edge diameter	250 mm
Bore diameter	32 mm
Number of teeth	200 PCS
DIN	1837
Form	A
Gross Weight	0.700 kg
Product Group	1QK

EAN

405362536 1632