



## NCX I0560

E1665193

CRIMP TOOL INSULATED TERMINALS 0.5-6mm<sup>2</sup>, SYMMETRICAL

High quality crimping tool. CrimpXchange is available in several combinations with a frame equipped with crimping dies from the NCXD / DHD / DRG series. Two more pairs of NCXD crimping dies can be stored in the handles. Exchange of crimping dies is quick and easy with the release buttons on the front of the tool, no other tools are needed. CrimpXchange is a ratchet crimping tool which ensures that the crimping is completed. Equipped with ergonomic handles.

Length: 235 mm.

Choose between buying the frame and combine the crimping dies of your choice or buying one of our ready-made concepts.

Available in several ready-made alternatives equipped with 1 set of dies for crimping of:

- Deutsch- Insulated terminals.- End sleeves- Heatshrink insulated butt splices- Uninsulated terminals with open barrel (roller compaction)- Uninsulated copper tube splices and cable lugs (KST/KRT/KSF/KRF)

## Product Properties:

<b>With locking device (for mechanical tools)</b>	Yes
<b>Inserts exchangeable</b>	Yes
<b>With automatic return</b>	Yes
<b>Suitable for</b>	Cable lugs and connectors
<b>Construction/operation</b>	Mechanical
<b>For component</b>	Insulated terminals
<b>Compression shape</b>	Oval pressing
<b>Number of included inserts</b>	1 .
<b>Cycle time</b>	2 s

## Dimensions:

Unit	pcs
Cross section	0.5-6 mm <sup>2</sup>
Length	235 mm
MOQ	1 .

### **Approvals:**

### **Compliance:**

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (Latest)

### **Other information:**

Trademark	NEMIQ
ETIM-Class	EC000168 - Crimp tool cable lugs, cable end sleeves, screen connection
ETIM-Release	7.0
Product Group	One Hand (ratchet)
Search Description	PRESSVERKTYG ISOLERADE KABELSKOR
Alternative SKU	NCXI0560

### **Logistic information:**

Barcode	733117630548
E-no	E1665193
Country of origin	TW
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	NCX I0560
Taric code	82032000
Unit	pcs
MOQ	1 .