

## SSRC clamping holder, positive, right

For longitudinal turning with CC indexable insert

**ATORN**<sup>®</sup>

### Application

For longitudinal turning with CC indexable insert, 80°

### Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 75°, tip angle 90°, clearance angle 7°

### Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces
- Very good surface quality for medium infeed and finishing



<b>Art. no.</b>	<b>17830 824</b>
<b>ISO name</b>	SCRC R/L 2525 M12
<b>Shaft height</b>	25 mm
<b>Shank width</b>	25 mm
<b>Length</b>	150 mm
<b>Length of head</b>	24 mm
<b>Programming size</b>	27 mm
<b>Suitable for indexable inserts</b>	CC.. 1204..
<b>Tool design</b>	Right

### EAN-Code

4050293562767