

MATERIAL SAFETY DATA SHEET



SECTION 1: Identification of the Substance and Company/Undertaking

1.1	Product Identifier:	Remanufactured Laser Toner Brother TN3330 Black Rev 2 03.09.2013
1.2	Relevant identified uses of the substance and uses advised against	
	Use:	Toner for use in Laser Printers
	Relevant identified uses:	See Above
	Environmental release category:	ERC8c (Wide dispersive indoor use resulting in inclusion into or onto a matrix) ERC11a (Wide dispersive indoor use of long-life articles and materials with low release)
	Mixture supplied to that use in form of:	A Mixture
	Product Category by type of chemical:	PC18 (Ink and Toners)
	Sector of end use:	SU3, 21, 22 (Industrial, Consumer and Professional uses)
	Uses advised against:	All other uses
1.3	Details of the supplier of the Safety data Sheet	
	Address:	Dynamic Cassette International Limited Marsh Lane Boston Lincolnshire PE21 7TX England
	Telephone Number:	+44 (0)1205 355555
	Email Address:	sales@dci.co.uk
1.4	Emergency Telephone:	+44 (0)1205 355555 or 07901 825565

SECTION 2: Hazards Identification

2.1	Classification of the substance	
2.1.1	Classification according to Regulation (EC) No 1272/2008 (including	None

MATERIAL SAFETY DATA SHEET

amendments):	
2.1.2 Classification according to EU Directive 67/548/EEC (including amendments):	None
2.2 Label elements:	None
Signal word:	None
Hazard statements:	None
Precautionary statements:	None
Prevention:	None
Storage:	None
2.3 Other Hazards:	The product is a dry mixture of various ingredients producing only slight risk of irritation in their pure state, in particular to the respiratory tract when exposed to large amounts of toner dust
2.4 Additional Information:	The product is not classified as hazardous according to EC and National Regulations

SECTION 3: Composition / Information on Ingredients

3.1 Substances

Product identifier type in accordance with Article 18(2) of Regulation (EC) No 1272/2008	Identifier number	Identification name	Weight % content (or range)	EC Number
CAS Number	1333-86-4	Carbon Black (bound)	2.5-10%	215-609-9

SECTION 4: First-Aid Measures

4.1 Description of First Aid Measures

Ingestion:	Rinse mouth with water. Give 2 cups of water, do not induce vomiting; seek medical advice if symptoms occur
Skin contact:	Clean affected areas with plenty of water, soap or other non-irritating cleanser. If irritation persists consult a physician
Eye contact:	Flush eyes with plenty of water until clear; remove contact lenses; seek medical advice if irritation persists
Inhalation:	Move the exposed person to fresh air at once. Seek medical advice if

MATERIAL SAFETY DATA SHEET

breathing is difficult

First Aider Protection: None specific

4.2 Most important symptoms and effects, both acute and delayed

Ingestion: Slight irritation of the gastro-intestinal tract

Skin contact: Slight irritation

Eye contact: Slight irritation

Inhalation: Slight irritation of the respiratory tract

4.3 Indication of immediate medical attention and special treatment needed

General advice: None specific

SECTION 5: Fire-Fighting Measures

5.1 Extinguishing media (small and large fires)

Small Fire: Water, water mist, foam, dry powder, CO2

Large Fire: Water, water mist, foam, dry powder, CO2

Avoid: None

5.2.1 Specific Hazards: This is a combustible material. May create toxic materials, carbon dioxide, carbon monoxide, various hydrocarbons etc. on thermal decomposition. It may form dust-explosive mixtures in the air

5.2.2 Protective equipment and advice for fire fighters: Self-contained breathing apparatus and full protective clothing

SECTION 6: Accidental Release Measures

6.1 Personal precautions, protective equipment and emergency measures

6.1.1 For non-emergency personnel: None specific

6.1.2 For emergency responders: None specific

6.2 Environmental precautions: Take precautionary measures against discharges into the environment

6.3 Methods and material for containment and cleaning up

6.3.1 For containment: No specific hazards foreseen

MATERIAL SAFETY DATA SHEET

6.3.2 For cleaning up:

Vacuum spilled toner while minimising dust formation. If vacuum is used, the motor must be rated as dust tight. A conductive hose bonded to the machine should be used to reduce static build up. Transfer carefully into a sealable waste container. Residue can be removed with cold water and soap. Garments may be washed or dry-cleaned, after removal of any loose toner.

6.3.3 Other information:

None

6.4 Reference to other sections:

Section 8

SECTION 7: Handling and Storage

7.1 Precautions for Safe Handling:

Handle with care
 Use with adequate ventilation
 Avoid inhalation of dust and contact with eyes and skin
 Keep containers closed when not in use
 Keep away from sources of heat, sparks and open flames

7.2 Conditions for safe storage, including any incompatibilities:

Store at room temperature in original container, dry and tightly closed.
 Do not store with oxidisers

7.3 Specific end uses:

Never eat, drink or smoke in work areas. Practice good personal hygiene after using this material, especially before eating, drinking, using the toilet, or applying cosmetics

SECTION 8: Exposure Controls/Personal Protection

8.1 Control Parameters

Substance	Deliberately left empty			
	CAS No.			
	Limit value - Eight hours		Limit value - Short term	
	ppm	mg/m ³	ppm	mg/m ³
USA OSHA		TWA / PEL; 15 mg/m ³ (total dust) TWA / PEL; 5mg/m ³ (respirable fraction)		
USA ACGIH		TWA / TLV; 10mg/m ³ (inhalable fraction) TWA/TLV; 3MG/M ³ (respirable particulate)		
United Kingdom		WEL; 10mg/m ³ (inhalable dust) WEL 5mg/m ³ (respirable dust)		

MATERIAL SAFETY DATA SHEET

8.2 Exposure controls

8.2.1 Engineering controls:

Use in well ventilated areas. Use engineering controls to reduce air contaminants to below permissible limits

8.2.2 Personal protective equipment:

Wear dust resistant safety goggles if there is any danger of eye contact.
Wear protective gloves to prevent direct skin contact.
Wear an approved respirator for dust when exposure exceeds permissible limits

8.2.3 Environmental exposure controls:

Take precautionary measures against discharges into the environment

SECTION 9: Physical and Chemical Properties

9.1 Information on basic physical and chemical properties

Appearance:

Black fine powder

Odour:

Faint

Odour threshold:

N/A

pH:

N/A

Melting point:

Softening point; -100 degrees C

Initial boiling point and boiling range:

N/A

Flash point:

N/A

Evaporation rate:

N/A

Flammability:

N/A

Upper/lower flammability or explosive limits:

N/A

Vapour pressure:

N/A

Specific gravity:

1.3-1.8

Relative density (water=1):

N/A

Solubility:

Negligible in water; partial in toluene and xylene

Partition coefficient (n-octanol/water):

N/A

Auto-ignition temperature:

N/A

MATERIAL SAFETY DATA SHEET

Decomposition temperature:

Viscosity:

Explosive properties:

Oxidising properties:

9.2 Other information

Critical Temperature:

SECTION 10: Stability and Reactivity

10.1 **Reactivity:**

10.2 **Chemical stability:**

10.3 **Possibility of hazardous reactions:**

10.4 **Conditions to Avoid:**

10.5 **Incompatible materials:**

10.6 **Hazardous decomposition products:**

SECTION 11: Toxicological Information

11.1 Information on toxicological effects

Acute toxicity:

Skin corrosion/irritation:

Serious eye damage/irritation:

Respiratory or skin sensitisation:

Germ cell mutagenicity:

Carcinogenicity:

Reproductive toxicity:

STOT-single exposure:

MATERIAL SAFETY DATA SHEET

STOT-repeated exposure:

N/A

Aspiration hazard:

N/A

Further information:

None

SECTION 12: Ecological Information

12.1 Toxicity:

This product has not been tested for environmental effects

12.2 Persistence and degradability:

N/A

12.3 Bioaccumulative potential:

N/A

12.4 Mobility in soil:

N/A

12.5 Results of PBT and vPvB assessment:

The mixture does not contain any ingredients which are PBT, vPvB or Substances of Very high Concern

12.6 Other adverse effects:

N/A

SECTION 13: Disposal Considerations

13.1 Waste treatment methods:

Dispose of spilled or waste product in accordance with all local, state and federal regulations

SECTION 14: Transport Information

14.1 UN Number:

Not regulated

14.2 UN proper shipping name:

Not regulated

14.3 Transport hazard class:

Not regulated

14.4 Packing group:

Not regulated

14.5 Environmental hazards:

Not regulated

14.6 Special Precautions for user:

Not regulated

14.7 Transport in bulk according to Annex II of Marpol 73/78 and the IBC Code:

Not regulated

MATERIAL SAFETY DATA SHEET

SECTION 15: Regulatory Information

- 15.1 **Safety, health and environmental regulations/legislation specific for the substance/mixture:** The information contained in this safety data sheet does not constitute the users own assessment of workplace risks as required by other health and safety regulations
This product has been assessed to ensure of compliance to the EU REACH and CLP Regulations
- 15.2 **Chemical Safety Assessment:** The product is determined as not being hazardous

SECTION 16: Other Information

- Methods of evaluation:** None specific
- References:** None specific
- Abbreviations:** REACH – Registration, Evaluation, Authorisation and Restriction of Chemicals
CLP – Classification, labelling and Packaging of Substances and Mixtures
EC No – European Commission Number
UN Number - United Nations Committee of Experts
WEL – Workplace Exposure Limit
STOT – Specific Target Organ Toxicity
PBT – Persistent, Bioaccumulative and Toxic
vPvB - very Persistent and very Bioaccumulative
TWA- Time Weighted Average
OSHA – Occupational Safety and Health Administration

The information contained herein is carefully presented, based on the data we have. However, all precautions described herein are for normal handling, not for special handling. Please establish the safe usage in accordance with your handling procedures by reference to this SDS and applicable laws and guidance. In addition, the description, composition, and physical/chemical properties are typical values and not guaranteed for this product.

Appendix 1: Exposure Scenarios



Company Registration 175 7389