



### Description

- Temperature compensated voltage controlled crystal oscillator (TCVCXO)
- Model: IQXT-200-4-B
- Model Issue number: 1

### Frequency Parameters

- Frequency: 19.20MHz
- Frequency Tolerance @ 25°C: ±0.50ppm
- Frequency Stability: ±0.28ppm
- Operating Temperature Range: -20.00 to 70.00°C
- Ageing: ±0.02ppm max per day, ±1ppm max per year
- Supply Voltage Variation (measurement referenced to frequency observed with TA=25°C, Vs varied from 3.13V to 3.47V, VC=1.65V and load=10kΩ//10pF): ±0.1ppm max
- Load Variation (5% load change measurement referenced to frequency observed with TA=25°C, Vs=3.3V, VC=1.65V and load=10kΩ//10pF): ±0.1ppm max
- Frequency Tolerance (measurement referenced to frequency observed with TA=25°C, Vs=3.3V, VC=1.65V and within 30 days after ex-works): ±0.5ppm
- Short Term Stability (@ 25°C after 10mins power on): 5E-10/s typ @ 10MHz
- Frequency Stability: TA varied from -20°C to 70°C, measurement referenced to frequency observed with TA=25°C, Vs=3.3V, VC=1.65V, load=10kΩ//10pF and temperature variable speed less than 2°C per minute.
- Ageing: TA=25°C, Vs= 3.3V, VC=1.65V and after 1hr of operation.

### Electrical Parameters

- Supply Voltage: 3.3V
- Supply Voltage Tolerance: ±5%
- Current Draw: 10.00mA max
- Current: TA=25°C, Vs=3.3V, VC=1.65V and load=10kΩ//10pF

### Frequency Adjustment

- Pulling: ±10ppm to ±15ppm
- Control Voltage Details: 1.65V ±1.65V
- Linearity: ±10% max
- Input Impedance: 100kΩ min
- Slope: Positive

### Output Details


- Output Compatibility: Clipped Sine
- Output Load: 10kΩ//10pF
- Output Level: 0.8V pk-pk min

### Noise Parameters


- Phase Noise (@ 10MHz typ):
  - 90dBc/Hz @ 10Hz
  - 115dBc/Hz @ 100Hz
  - 135dBc/Hz @ 1kHz
  - 145dBc/Hz @ 10kHz
  - 148dBc/Hz @ 100kHz
  - 150dBc/Hz @ 1MHz



### Outline (mm)



- Pad Connections
- Voltage Control
  - GND
  - Output
  - +Vs
- D1, D2, D3, D4. N/C



### Sales Office Contact Details:

UK: +44 (0)1460 270200  
 Germany: +49 (0)7264 9145-62

France: +33 (0)5 34 50 91 18  
 USA: +1 408.273.4530

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)  
 Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)

