

Product information

98 01 22

- Cranked
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Box Wrench

IEC 60900 DIN EN 60900



⚡ 1000 V ♻️

General

Article No.	98 01 22
EAN	4003773020301
Weight	278 g
Dimensions	37 x 40 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Width across flats S	22 mm
Length l max.	225 mm
Head thickness a max.	15 mm
Depth of crank h max.	30 mm
Head width b max. mm	35 mm



technical change and errors excepted

