

Coaxial Cable Connector 16_SMA-50-2-56/199_N

Description

Right angle cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0042 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DCA-00005974
Assembly instruction	DOC-0000178742

Ordering Information

Bulk 100 pcs package	16_SMA-50-2-56/199_NH
Single package	16_SMA-50-2-56/199_NE

Additional Information

Suitable cables	K_02252_D, ENVIROFLEX_316_D, G_02232_D
-----------------	--