

Weldon surface chucks

In accordance with ISO 7388-1 (DIN 69871)

ORION[®]

Application:

For clamping tools with straight shanks and clamping surfaces in line with DIN 1835 B.

Execution:

- All tapers and tolerances are precision-ground.
- Taper tolerance AT3.
- Strength HRC 57-60.
- Core strength 1,000-1,200 N/mm².
- With Balluff chip hole.

Advantage:

- Prevents the tool from slipping while maintaining high concentricity.

Delivery:

1x surface chuck (Weldon) in accordance with ISO 7388-1 (DIN 69871).



Art. no.	23157 008
Brand	ORION
Manufacturer Part Number	23157008
Tool holding device	SK 40
Clamping diameter	10 mm
Projecting length	100 mm
Outer diameter	40 mm
Length	20 mm
Clear length	40 mm
Diameter 2	35 mm
Balancing quality	G 6.3 at 15 rpm
Form	AD/AF
Thread dimension	M10
Gross Weight	1.425 kg
Product Group	2AV

EAN

4053625290772