

Measuring beams

lightweight design, accuracy class I++



Application:

For simple and accurate checking of straightness and parallelism deviations on travelling axes of e.g. coordinate measuring instruments and machine tools.

Execution:

- Carefully selected and flawless South African hard stone material – Diabas.
- torsion-resistant, distortion-proof, anti-magnetic
- Exactly 2-sided. The two narrow longitudinal surfaces are finely machined to a high-quality finish to be flat and parallel to one another
- accuracy I++: finely ground and lapped
- screwed-on handles on both sides
- Calibration certificate included in the scope of delivery. measurement results are based on national standards
- DAkkS calibration certificate available on request

Advantage:

- solid material with perforations, reducing weight by approx. 40%



Art. no.	35342 510
Brand	JFA
Length x width x height	1000 x 60 x 160 mm
JFA accuracy I++	0.002 mm
Weight	18 kg
Gross Weight	18.000 kg
Product Group	341