




Relays, Contactors & Switches > Relays > Relay Accessories, Sockets & Clips



Relay Accessory, Socket & Clip Product Type: **Socket**

Relay Accessory, Socket & Clip Socket Type: **Track Mount**

Grounding Provision: **Without**

Relay Accessory, Socket & Clip Body Material: **Glass-Filled Polyester**

Relay Accessory, Socket & Clip For Use With: **KRPA Relays**

## Features

### Product Type Features

Terminal Configuration	Screw
Relay Accessory, Socket & Clip Product Type	Socket
Relay Accessory Type	Socket

### Configuration Features

Grounding Provision	Without
---------------------	---------

### Body Features

Relay Accessory, Socket & Clip Body Material	Glass-Filled Polyester
--	------------------------

### Contact Features

Terminal Length	5.33 mm[.21 in]
Contact Plating Material	Tin
Contact Base Material	Spring Brass
Relay Accessory, Socket & Clip Socket Type	Track Mount

### Termination Features

--	--



Number of Pins	8
----------------	---

### Mechanical Attachment

Relay Accessory, Socket & Clip Mounting Type	Panel, Rail
--	-------------

### Operation/Application

Relay Accessory, Socket & Clip For Use With	KRPA Relays
---	-------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1-1393105-2  
KRPA-11AG-24=RELAY,GENPUR,  
OCTA



TE Part # 4-1393104-3  
KRPA-11DG-12=KRPA



TE Part # 5-1393104-0  
KRPA-11DN-12=KRPA



TE Part # 2-1393104-4  
KRPA-11AG-12=KRPA



TE Part # 2-1393104-9  
KRPA-11AGP-120=KRPA



TE Part # 3-1393104-3  
KRPA-11AN-24=KRPA



TE Part # 3-1393104-4  
KRPA-11AN-240=KRPA



TE Part # 3-1393104-6  
KRPA-11AY-120=KRPA



TE Part # 3-1393104-7  
KRPA-11AY-24=KRPA



TE Part # 3-1393104-8  
KRPA-11AY-240=KRPA



TE Part # 4-1393104-7  
KRPA-11DG-6=KRPA



TE Part # 5-1393104-6  
KRPA-11DY-12=KRPA



TE Part # 5-1393104-7  
KRPA-11DY-24=KRPA



TE Part # 1393105-1  
KRPA-5AY-120=KRPA



TE Part # 1393105-3  
KRPA-5DG-12=KRPA



TE Part # 1393105-4  
KRPA-5DG-24=KRPA



TE Part # 1393105-6  
KRPA-5DY-12=KRPA



TE Part # 1393105-7  
KRPA-5DY-24=KRPA




TE Part # 3-1393104-1  
KRPA-11AN-12=KRPA



TE Part # 1393105-2  
KRPA-5DG-110=KRPA

Also in the Series | **Potter & Brumfield KRPA**




Power Relays(60)



Relay Accessories, Sockets &amp; Clips(5)

## Customers Also Bought

TE Part #1969357-1  
HSG .090 CLUSTER BLOCK 2 POSTE Part #1-1393105-2  
KRPA-11AG-24=RELAY,GENPUR,  
OCTATE Part #3-1393104-4  
KRPA-11AN-240=KRPATE Part #1742964-1  
2.29 DIA CLUSTER PIN AMPLV REC  
1600-4800TE Part #4-1393104-6  
KRPA-11DG-48=KRPATE Part #4-1393104-9  
KRPA-11DN-110=KRPATE Part #3-1393769-6  
R10-T2W3-J30.0K=R10TE Part #3-1437466-5  
VMAXBA=\*

## Documents

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393143-6\\_A.2d\\_dxf.zip](#)

English

### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393143-6\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393143-6\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### KR Sockets & Accessories

English



[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

---

[Product Specifications](#)

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English

---

[Product Environmental Compliance](#)

[TE Material Declaration](#)

English