

WITHDRAWABLE COIL FOR SIZE S10 FOR CONTACTORS 3RT106/3RT146 AC/DC OPERATION UC96-127V DRIVE: ELECTRONIC WITH 24 V DC PLC INTERFACE CAGE CLAMP CONNECTIONS



General technical data:		
product brand name		SIRIUS
Product designation		Magnet coil
Control circuit:		
Type of voltage of the control supply voltage		AC/DC
Control supply voltage		
<ul style="list-style-type: none"> • 1 with AC <ul style="list-style-type: none"> — at 50 Hz Rated value — at 60 Hz Rated value • 2 with AC <ul style="list-style-type: none"> — at 50 Hz Rated value — at 60 Hz Rated value 	<ul style="list-style-type: none"> V V V V 	<ul style="list-style-type: none"> 96 96 127 127
Control supply voltage		
<ul style="list-style-type: none"> • 1 for DC Rated value • 2 for DC Rated value 	<ul style="list-style-type: none"> V V 	<ul style="list-style-type: none"> 96 127
Certificates/ approvals:		

General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity	Test Certificates	Shipping Approval
--------------------------	---------------------------------------	---------------------------	-------------------	-------------------



[Type Examination](#)



[Special Test Certificate](#)



Shipping Approval



GL



LRS



PRS



RINA

Shipping Approval	other
-------------------	-------



[Confirmation](#)

[Environmental Confirmations](#)

[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT19655NF32>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RT19655NF32/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RT19655NF32&lang=en>

last modified:

09.03.2015