



21HDG-A

ERGO™ 14° Side Cutting Pliers with Self Opening Dual-Component Handle and Phosphate Finish

PRODUCT DETAILS

- Two-component ERGO™ handles: thermoplastic surface on tough polypropylene provides superior grip
- Heavy-duty side cutting pliers with angled head developed according to the scientific ERGO™ process
- Suitable for cutting Cu, Fe+ and piano wire
- Distance from joint to centre of cutting edges is reduced for greater leverage and increased cutting capacity
- Equipped with a patented return spring featuring an on/off function
- High-performance alloy steel
- Phosphate finish, anti-corrosion treated
- Heavy-duty cutting edge
- Metal frame with angled head at 14° designed to enhance accessibility in confined spaces
- Screw joint that provides excellent running and accurate alignment of the cutting edges
- Induction hardened cutting edges
- Maximum comfort with minimum effort due to the ergonomic design
- Comfortable two-component handles giving an excellent grip
- Heavy-duty induction hardened cutting edge with the head set at a 14° for better accessibility
- Self-opening handles when spring activated



PRODUCT ATTRIBUTES

Product								
21HDG-140A	140 mm	15.9 mm	21 mm	8 mm	2.0 mm	2.2 mm	2.0 mm	110 g
21HDG-160A	160 mm	18 mm	23 mm	9 mm	2.1 mm	2.5 mm	2.3 mm	150 g
21HDG-180A	180 mm	19.8 mm	25 mm	10 mm	2.3 mm	2.7 mm	2.5 mm	210 g
21HDG-200A	200 mm	22.4 mm	27 mm	10 mm	2.8 mm	3.2 mm	3.0 mm	270 g

Follow the Fish!

