


POTI-MODUL

MIRO 12.4, 24VDC/ outp. 0...10VDC

Transmitter
approx. 2.5 MOhm

[Link to Product](#)

Illustration



Product may differ from Image

Input

Input resistor	approx. 2.5 MOhm
Type	for 3-wire sensors or mechanical switches, NPN, (EN 61131-2)
Sensor supply US	12 V DC/15 mA

Technical Data

Operating voltage	24 V DC (20...30 V DC)
Current consumption	max. 20 mA
LED display	LED (green): Power; LED (red): Error
Linearity	max. 0.3 % from end value

General data

Protection	IP20
Connection	Screw terminals
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	-25...+55 °C (storage temperature -30...+80 °C)
Dimensions H × W × D	14.4×93×75.6

Description

Functional description	The module is designed to connect a potentiometer. The module's output voltage can be set from 0...10 V, independently of the measuring range of the potentiometer used. Even when the potentiometer is used to 50%, the output voltage can be covered in the c
------------------------	---

Output

Output voltage	0...10 V DC
Output current	10 mA (short-circuit protected)

Commercial data

country of origin	CZ
customs tariff number	85334010
minimum order quantity	1