

## Electronic crane scales HFM

with high resolution, up to a maximum of 10 tonnes

**KERN**

### Application:

For applications in production, quality control and logistics. Also suitable for continuous use in industrial environments thanks to the sturdy construction and robust design.

### Execution:

- Precision: 0.2 % of the respective MAX. value of the selected measuring range
- Data hold function
- Wireless remote control with a range of approx. 20 m
- large LCD display
- powered by internal rechargeable battery, operating time up to 50 h without backlight, charging time approx. 14 h
- HFM with robust die-cast aluminium housing
- HFM includes rotating hook with safety lock

### Advantage:

- If the hold function is activated, the value will be „frozen“ (no weight change) when not in use.

### Delivery:

Mains charger, radio remote control



|                                    |                    |
|------------------------------------|--------------------|
| <b>Art. no.</b>                    | <b>44267 210</b>   |
| <b>Brand</b>                       | KERN               |
| <b>Manufacturer Part Number</b>    | HFM 1T0.1          |
| <b>Type description</b>            | HFM 1T0.1          |
| <b>Max. weight measuring range</b> | 1000 kg            |
| <b>Digit increment, weight</b>     | 100 g              |
| <b>Housing dimensions (LxWxH)</b>  | 175 x 270 x 200 mm |
| <b>Weight</b>                      | 15 kg              |
| <b>Gross Weight</b>                | 16.000 kg          |
| <b>Product Group</b>               | 447                |

### EAN

4045761111691