

## WEV 17-125 Quick angle grinder

1700 W

**metabo**<sup>®</sup>

### Execution:

- Cut-out carbon brushes protect the motor
- Metabo S-automatic mechanical safety coupling

### Delivery:

protective cover, support flange, M-Quick clamping nut, additional Metabo Vibra Tech (MVT) handle



|   |                  |
|---|------------------|
| <b>Art. no.</b>                                   | <b>70373 328</b> |
| <b>Brand</b>                                      | METABO           |
| <b>Manufacturer Part Number</b>                   | 600516000        |
| <b>Model</b>                                      | WEV 17-125 Quick |
| <b>Manufacturer Article Number</b>                | 600516000        |
| <b>Battery included</b>                           | No               |
| <b>Number of rechargeable batteries/batteries</b> | 0                |
| <b>Washer diameter</b>                            | 125 mm           |
| <b>Power input</b>                                | 1700 W           |
| <b>Power output</b>                               | 1040 W           |
| <b>Thread dimension of spindle</b>                | M14              |
| <b>Min./max. idle speed</b>                       | 2800-11000 rpm   |
| <b>Weight</b>                                     | 2.5 kg           |
| <b>With restart protection</b>                    | Yes              |
| <b>With soft start</b>                            | Yes              |
| <b>With overload protection</b>                   | Yes              |
| <b>With electronic feedback</b>                   | Yes              |
| <b>With reverse switch off</b>                    | Yes              |
| <b>With disc brake</b>                            | No               |
| <b>With quick clamping system</b>                 | Yes              |
| <b>With dead man function</b>                     | No               |
| <b>Gross Weight</b>                               | 3.215 kg         |
| <b>Product Group</b>                              | 745              |

### EAN

4007430306593