



SAFETY DATA SHEET

e:dose - EC9 WASHROOM (red zone eco concentrate)

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	e:dose - EC9 WASHROOM (red zone eco concentrate)
Product number	A057 EV
Internal identification	Janitorial
UFI	UFI: 31QE-S12Y-EG09-0XHP

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Concentrated Acidic Hard Surface Cleaner for Washrooms. - For use in Evans e:dose system.
------------------------	---

1.3. Details of the supplier of the safety data sheet

Supplier	UK Supplier:	EU Supplier:
	Evans Vanodine International plc Brierley Road, Walton Summit, Preston. UK. PR5 8AH Tel: 01772 322 200 e-mail: productcompliance@evansvanodine.co.uk	Evans Vanodine Europe 6-9 Trinity Street, Dublin 2. D02 EY47. Republic of Ireland.

1.4. Emergency telephone number

Emergency telephone	New Safety Data Sheets - 01772 322 200 - Mon to Thur. 8.30am to 4.30pm - Fri 8.30am to 1.30pm (Also available 24/7 from our website www.evansvanodine.co.uk) For Technical Advice about this SDS - 01772 318 818 - Mon to Thur 8.30am to 4.45pm - Fri 8.30am to 1.30pm
----------------------------	--

National emergency telephone number	For Health Care Professionals only - For use in UK: Contact the National Poisons Information Service for further advice. For use in the Republic of Ireland: To report a poisoning incident contact The National Poisons Information Centre, Beaumont Hospital, Dublin (01-8092166). For use in Malta: Emergency services (Ambulance, Fire and Rescue, Police) : 112
--	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards	Not Classified
Health hazards	Skin Corr. 1B - H314 Eye Dam. 1 - H318
Environmental hazards	Aquatic Acute 1 - H400 Aquatic Chronic 3 - H412

2.2. Label elements

Hazard pictograms



e:dose - EC9 WASHROOM (red zone eco concentrate)

Signal word	Danger
Hazard statements	H314 Causes severe skin burns and eye damage. H400 Very toxic to aquatic life. H412 Harmful to aquatic life with long lasting effects.
Precautionary statements	P102 Keep out of reach of children. P260 Do not breathe mist. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P301+P330+P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower. P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P315 Get immediate medical advice/ attention. P501 Dispose of contents/ container in accordance with local regulations.
Contains	DIDECYL DIMETHYL AMMONIUM CHLORIDE

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients**3.2. Mixtures**

CITRIC ACID	20-25%
CAS number: 77-92-9	EC number: 201-069-1
Classification Eye Irrit. 2 - H319	
DIDECYL DIMETHYL AMMONIUM CHLORIDE	5-10%
CAS number: 7173-51-5	EC number: 230-525-2
M factor (Acute) = 10	
Classification Acute Tox. 4 - H302 Skin Corr. 1B - H314 Eye Dam. 1 - H318 Aquatic Acute 1 - H400 Aquatic Chronic 2 - H411	
ALCOHOL (C9-11) ETHOXYLATE	5-10%
CAS number: 68439-46-3 Alternative CAS Nos 160875-66-1, 68439-45-2	
Classification Acute Tox. 4 - H302 Eye Dam. 1 - H318	

e:dose - EC9 WASHROOM (red zone eco concentrate)

PROPAN-2-OL			1-3%
CAS number: 67-63-0	EC number: 200-661-7	REACH registration number: 01-2119457558-25-xxxx	
Classification			
Flam. Liq. 2 - H225			
Eye Irrit. 2 - H319			
STOT SE 3 - H336			

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures**4.1. Description of first aid measures**

Inhalation	Unlikely route of exposure as the product does not contain volatile substances. If spray/mist has been inhaled, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
Ingestion	Do not induce vomiting. Rinse mouth thoroughly with water. Give plenty of water to drink. Get medical attention immediately.
Skin contact	Wash with plenty of water. Get medical attention promptly if symptoms occur after washing.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse. Get medical attention immediately.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	Irritation of nose, throat and airway.
Ingestion	May cause chemical burns in mouth and throat.
Skin contact	Burning pain and severe corrosive skin damage. May cause serious chemical burns to the skin.
Eye contact	Severe irritation, burning and tearing. Prolonged contact causes serious eye and tissue damage.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

SECTION 5: Firefighting measures**5.1. Extinguishing media**

Suitable extinguishing media The product is not flammable. Use fire-extinguishing media suitable for the surrounding fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards Thermal decomposition or combustion products may include the following substances: Irritating gases or vapours.

5.3. Advice for firefighters

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

e:dose - EC9 WASHROOM (red zone eco concentrate)

Personal precautions Wear protective clothing, gloves, eye and face protection. For personal protection, see Section 8.

6.2. Environmental precautions

Environmental precautions Spillages or uncontrolled discharges into watercourses must be reported immediately to the Environmental Agency or other appropriate regulatory body.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Small Spillages: Flush away spillage with plenty of water. Large Spillages: Contain and absorb spillage with sand, earth or other non-combustible material. Collect and place in suitable waste disposal containers and seal securely.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Wear protective clothing, gloves, eye and face protection.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Keep only in the original container in a cool, well-ventilated place. Store away from the following materials: Oxidising materials. & Alkalis.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

Usage description See Product Information Sheet & Label for detailed use of this product.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

PROPAN-2-OL

Long-term exposure limit (8-hour TWA): WEL 400 ppm 999 mg/m³

Short-term exposure limit (15-minute): WEL 500 ppm 1250 mg/m³

WEL = Workplace Exposure Limit.

Ingredient comments No exposure limits known for ingredient(s).

8.2. Exposure controls

Protective equipment



Appropriate engineering controls Not applicable.

Eye/face protection The following protection should be worn: Chemical splash goggles or face shield.

Hand protection Wear protective gloves. (Household rubber gloves.)

Other skin and body protection Wear appropriate clothing to prevent any possibility of skin contact.

Respiratory protection Respiratory protection not required.

e:dose - EC9 WASHROOM (red zone eco concentrate)**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	Liquid.
Colour	Dark. Red.
Odour	Citrus.
pH	pH (concentrated solution): 1.60
Melting point	-1°C
Initial boiling point and range	101°C @ 760 mm Hg
Flash point	86°C . Measured using test method, Closed cup.
Relative density	1.084 @ 20°C
Solubility(ies)	Soluble in water.

9.2. Other information

Other information	None.
--------------------------	-------

SECTION 10: Stability and reactivity**10.1. Reactivity**

Reactivity	Reacts with alkalis and generates heat.
-------------------	---

10.2. Chemical stability

Stability	No particular stability concerns.
------------------	-----------------------------------

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	See sections 10.1,10.4 & 10.5
---	-------------------------------

10.4. Conditions to avoid

Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
----------------------------	---

10.5. Incompatible materials

Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
---------------------------	--

10.6. Hazardous decomposition products

Hazardous decomposition products	No known hazardous decomposition products.
---	--

SECTION 11: Toxicological information**11.1. Information on toxicological effects**

Toxicological effects	We have not carried out any animal testing for this product. Any ATE figures quoted below are from Toxicity Classifications that have been carried out using ATE (Acute Toxicity Estimate) Calculation Method using LD50 or ATE figures provided by the Raw Material Manufacturer.
Other health effects	Low oral toxicity, but ingestion may cause irritation of the gastro-intestinal tract.
Acute toxicity - oral	
Notes (oral LD₅₀)	Based on available data the classification criteria are not met.
ATE oral (mg/kg)	4,845.36

e:dose - EC9 WASHROOM (red zone eco concentrate)**SECTION 12: Ecological information**

Ecotoxicity Very toxic to aquatic life. Harmful to aquatic life with long lasting effects.

12.1. Toxicity

Toxicity We have not carried out any Aquatic testing, therefore we have no Aquatic Toxicity Data specifically for this product. The Aquatic Toxicity Data, where provided by the raw material manufacturer for ingredients with aquatic toxicity, can be made available on request.

12.2. Persistence and degradability

Persistence and degradability The surfactant(s) contained in this product complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No. 648/2004 on detergents. and UK Regulation: SI 2020 No. 1617 "The Detergents (Amendment) (EU Exit) Regulations 2020".

12.3. Bioaccumulative potential

Bioaccumulative potential The product does not contain any substances expected to be bioaccumulating.

12.4. Mobility in soil

Mobility Not known.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects Not known.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Disposal methods Discharge used solutions to drain. Small amounts (less than 5 Litres) of unwanted product may be flushed with water to sewer. Larger volumes must be sent for disposal as special waste. Rinse out empty container with water and consign to normal waste.

SECTION 14: Transport information

General 1L As supplied, this product is consigned under the Limited Quantities provisions.

14.1. UN number

UN No. (ADR/RID) 1760

UN No. (IMDG) 1760

UN No. (ICAO) 1760

14.2. UN proper shipping name

Proper shipping name (ADR/RID) CORROSIVE LIQUID N.O.S. (citric acid, didecyl dimethyl ammonium chloride)

Proper shipping name (IMDG) CORROSIVE LIQUID N.O.S. (citric acid, didecyl dimethyl ammonium chloride)

Proper shipping name (ICAO) CORROSIVE LIQUID N.O.S. (citric acid, didecyl dimethyl ammonium chloride)

14.3. Transport hazard class(es)

ADR/RID class Class 8: Corrosive Substances.

ADR/RID label 8

e:dose - EC9 WASHROOM (red zone eco concentrate)

IMDG class Class 8: Corrosive Substances.

ICAO class/division Class 8: Corrosive Substances.

Transport labels**14.4. Packing group**

ADR/RID packing group II

IMDG packing group II

ICAO packing group II

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

**14.6. Special precautions for user**

EmS F-A, S-B

Tunnel restriction code (E)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not relevant. for a packaged product.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU legislation**

Safety Data Sheet prepared in accordance with EU Regulation: "REACH Commission Regulation (EU) No 2015/830 (which amends Regulation (EC) No 453/2010 & 1907/2006)." and UK Regulation: "SI 2020 No. 1577 - The REACH etc. (Amendment etc.) (EU Exit) Regulations 2020.".

The product is as classified under - EU GHS: CLP - "Regulation (EC) No 1272/2008 classification, labelling & packaging of substances & mixtures." and UK GHS: "SI 2020 No. 1567 - The Chemicals (Health and Safety) and Genetically Modified Organisms (Contained Use) (Amendment etc.) (EU Exit) Regulations 2020.".

Ingredients are listed with classification under - EU GHS: CLP - "Regulation (EC) No 1272/2008 classification, labelling & packaging of substances & mixtures." and UK GHS: "SI 2020 No. 1567 - The Chemicals (Health and Safety) and Genetically Modified Organisms (Contained Use) (Amendment etc.) (EU Exit) Regulations 2020.".

15.2. Chemical safety assessment

No chemical safety assessment has been carried out as not applicable as this product is a mixture.

SECTION 16: Other information

e:dose - EC9 WASHROOM (red zone eco concentrate)

Abbreviations and acronyms used in the safety data sheet	<p>PBT: Persistent, Bioaccumulative and Toxic substance.</p> <p>vPvB: Very Persistent and Very Bioaccumulative.</p> <p>ATE: Acute Toxicity Estimate.</p> <p>REACH: Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006.</p> <p>GHS: Globally Harmonized System.</p> <p>Spec Conc Limits = Specific Concentration Limits.</p>
Classification abbreviations and acronyms	<p>Acute Tox. = Acute toxicity</p> <p>Aquatic Acute = Hazardous to the aquatic environment (acute)</p> <p>Aquatic Chronic = Hazardous to the aquatic environment (chronic)</p> <p>Eye Dam. = Serious eye damage</p> <p>Eye Irrit. = Eye irritation</p> <p>Flam. Liq. = Flammable liquid</p> <p>Skin Corr. = Skin corrosion</p> <p>STOT SE = Specific target organ toxicity-single exposure</p>
Key literature references and sources for data	Material Safety Data Sheet, Miscellaneous manufacturers. CLP Class - Table 3.1 List of harmonised classification and labelling of hazardous substances. ECHA - C&L Inventory database.
Classification procedures according to Regulation (EC) 1272/2008	Calculation Method.
Revision comments	Changed UN No & Proper Shipping Name in Transport section (Changes made to section 14+16) & Change to ingredient's name (Changes made to sections 2&3)
Revision date	07/09/2021
Revision	9
SDS status	The Hazard Statements listed below in this Section No 16 relate to the Raw Materials (Ingredients) in the Product (as listed in Section 3) and NOT the product itself. For the Hazard Statements relating to this Product see Section 2.
Hazard statements in full	<p>H225 Highly flammable liquid and vapour.</p> <p>H302 Harmful if swallowed.</p> <p>H314 Causes severe skin burns and eye damage.</p> <p>H318 Causes serious eye damage.</p> <p>H319 Causes serious eye irritation.</p> <p>H336 May cause drowsiness or dizziness.</p> <p>H400 Very toxic to aquatic life.</p> <p>H411 Toxic to aquatic life with long lasting effects.</p> <p>H412 Harmful to aquatic life with long lasting effects.</p>