Nitrylex[®] Classic

Product Description

- Superior Strength 2.8 mil, 3.6 gram, Powder Free Blue Nitrile Glove (AQL 1.5)
- Micro-texture with additional texture on the fingertips for Improved Pinch Grip
- Touch Screen Friendly suitable for use with/around Food/Foodstuffs
- Excellent Chemical Resistance and a Proven Barrier to Toxic Fibres (i.e. Fibreglass/Asbestos)
- Superior Strength and Toughness whilst maintaining Maximum Dexterity
- Durable Beaded Cuff
- Latex and Silicone Free

Specifications

Code:	RD3001900	Sizes:	S to XL
Thickness:	2.8 mil	Box Size:	100 gloves
Length:	240mm	Carton Size:	1000 gloves
Category:	CAT III - Type B	EN374-1:	KPT

Suggested Applications

•	Agriculture	•	Construction	•	Veterinary
•	Insulation	•	Engineering	•	Assembly
•	Automotive	•	Plumbing	•	Janitorial

Certification and Marking



Limitations of Use

Maintenance	Examine gloves for damages, splits and holes before each use. Always replace damaged gloves. Only properly fitting gloves guarantee protection and grip.
Storage	Store at normal room temperature in a dry, well ventilated area. Avoid direct heat radiation.
Disposal	Used gloves can be contaminated. Dispose with household waste or as instructed by your local authority.
Cleaning	Do not wash. The performance of the product after laundering is unknown. Beat or brush out after each use, depending on level of dirt.
Durability	The period of use depends on the degree or intensity of use in the retrospective application. It is therefore not possible to provide a 'life span' of the gloves.
Note	Due to the nature of this product the user is advised to carry out their own risk assessment before use, depending on application.

Just 1 Source & Supply Limited, Yorkshire House, Barton Hill, Whitwell, York, YO60 7JX T: 01653 617718 - E: sales@just1source.com - W: www.just1source.com





