



5mm 3.1V White LED Oval Diffused

Order code: **55-2194**

MPN: OSW5DL5HA2B-MN

Features:

- High luminous LEDs
- 5.1 x 4.3mm Standard directivity
- Low decay & long lifetime operation
- Superior weather-resistance
- UV Resistant epoxy
- White diffused type

Applications

- Electronic signs and signals
- Small area illuminations
- Back lighting
- Other lighting

Absolute maximum rating (Ta=25°C)

Item	Symbol	Value		Unit
DC forward current	I _F	30		mA
Pulse forward current*	I _{FP}	100		mA
Reverse voltage	V _R	5		V
Power dissipation	P _D	108		mW
Operating temperature	T _{opr}	-30 to +85		°C
Storage temperature	T _{stg}	-40 to +100		°C
Lead soldering temperature	T _{sol}	260°C/5 sec		-

*Pulse width max. 10ms. Duty ratio max. 1/10

Electrical – Optical characteristics (Ta=25°C)


Item	Symbol	Condition	Min.	Typ.	Max.	Unit
DC Forward voltage	V _F	I _F = 20mA	2.9	3.1	3.6	V
DC Reverse current	I _R	V _R = 5V	-	-	10	µA
Luminous intensity*	I _V	I _F = 20mA	1560	2180	3000	mcd
Chromaticity coordinates†	x	I _F = 20mA	-	0.27	-	
	y	I _F = 20mA	-	0.28	-	
50% Power angle	2θ _{1/2}	I _F = 20mA	-	100/40	-	deg

* Tolerance of chromaticity coordinates is ±10%

† Tolerance of luminous intensity is ±15%



Outline dimensions:



Directivity:

