

DG210 Allcut diamond cutting disc

Segment height 3.0 mm

RHODIUS

Application:

For cool cutting of stone, metal and many other materials. Suitable for wet and dry sanding

Version:

- segmented, soldered under a vacuum
- Reducing rings for bore diameters 20.0 mm and 22.2 mm are included with each 300 mm and 350 mm disc

Art. no.	76119 380
Washer diameter	180 mm
Washer thickness	2.8 mm
Bore diameter	22.23 mm
Max. rotation speed	8600 rpm
Form	Straight
Number of pieces per packet	1 PCS
Material to be processed	Stone, Concrete, Steel



EAN-Code

4011890071427