


# RFSMAA2JEGIGHE Datasheet

## Product Name // SMA Straight Jack 2 Hole Flange RF Connector

[View Product Page](#)



// Product Description:	
<ul style="list-style-type: none"> <li>SMA Straight Jack 2 Hole Flange RF Connector</li> <li>Maximum Voltage: 335V</li> <li>Temperature range: -65Å°C to +165Å°C</li> <li>Frecuency range: 0GHz - 18GHz</li> <li>VSWR:</li> </ul>	<ul style="list-style-type: none"> <li>Dielectric withstanding Voltage: &gt;750V</li> <li>Impedance: 50Ohm</li> <li>Body Material: Stainless Steel Passivation</li> <li>Contact Material: Beryllium Copper</li> </ul>

// General Information:	
Product Display Title:	SMA Series Pin with Extended PTFE 2 Hole Flange
Product Family:	Radio Frequency Connectors
Product Series:	SMA Series
Body Length:	9.40mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>26.7N
Contact Pin Material:	Beryllium Copper
Min Coupling Torque:	0.80Nm
Max Coupling Torque:	1.10Nm
Coupling Nut Retention Force:	>27.2Kg
Dielectric Withstanding Voltage:	>750V
Durability:	>500 cycles
Flange Mount Length:	15.80mm
Function:	Female Flange Mount RF Connector
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	Adapter ASTM D 1710
Max Operating Temperature:	+165°C
Min Operating Temperature:	-65°C
Mount Hole Distance:	12.20mm
Min Operating Frequency:	0GHz
Max Operating Frequency:	18GHz
Pin Diameter:	1.00mm
Pin Length:	3.00mm
Ptfe Diameter:	4.10mm
Ptfe Length:	4.00mm
Thread Size:	1/4 36UNS 2A
Voltage Max:	335V
Vswr:	<1.30

// Product PDF Links

[SMA Series Product Datasheet](#)