## SIEMENS

## Data sheet

product type designation

## 6GT2801-4BA10

. 3	
SIEMENS	And the second s

## RF350R reader

SIMATIC RF300; reader RF350R (GEN2); RS422 interface (3964R); without antenna IP65, -25 to +70  $^{\circ}$ C, 75x 75x 41 mm, can be operated with: ANT 1, 3, 3NO, 8, 12, 18, 30.

RF300, ISO 15693 and MOBY E transponder, for connecting to communication modules

radio frequencies				
operating frequency / rated value	13.56 MHz			
range / maximum	140 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964			
protocol / with radio transmission	RF300 specific, ISO 15693, ISO 18000-3, ISO 14443			
transfer rate / with radio transmission / maximum	106 kbit/s			
product feature / multitag-capable	No			
electrical data				
transfer rate / at the point-to-point connection / serial / maximum	115.2 kbit/s			
transmission time / for user data				
<ul> <li>for write access / per byte / typical</li> </ul>	0.13 ms			
<ul> <li>for read access / per byte / typical</li> </ul>	0.13 ms			
interfaces				
number of external antennas	1			
standard for interfaces / for communication	RS422			
type of electrical connection				
<ul> <li>for external antenna(s)</li> </ul>	M8, 4-pin			
<ul> <li>for communications interface</li> </ul>	M12, 8-pin			
mechanical data				
material	PA 12			
color	Ti gray			
tightening torque / of the screw for securing the equipment / maximum	1.5 N·m			
mounting distance / relating to metal surfaces / recommended / minimum	0 mm			
supply voltage, current consumption, power loss				
supply voltage				
<ul> <li>at DC / rated value</li> </ul>	24 V			
at DC	20.4 28.8 V			
consumed current / at DC				
• at 24 V / typical	0.06 A			
ambient conditions				
ambient temperature				
during operation	-25 +70 °C			
<ul> <li>during storage</li> </ul>	-40 +85 °C			
<ul> <li>during transport</li> </ul>	-40 +85 °C			

protection class IP	IP65		
shock resistance	EN 60721-3-7 Class 7 M2		
shock acceleration	500 m/s <sup>2</sup>		
vibrational acceleration	200 m/s <sup>2</sup>		
design, dimensions and weights			
width	75 mm		
height	41 mm		
depth	75 mm		
net weight	0.25 kg		
fastening method	2 x M5 screws		
wire length			
<ul> <li>of antenna wire / fixed value</li> </ul>	3 m		
<ul> <li>for RS 422 interface / maximum</li> </ul>	1000 m		
product features, product functions, product components / general			
display version	5-color LED		
product feature / silicon-free	Yes		
standards, specifications, approvals			
certificate of suitability	Radio acc. to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, cULus		
certificate of suitability			
• IECEx	No		
MTBF	260 y		
accessories			
accessories	Various antennas are available		
further information / internet-Links			
Internet-Link			
<ul> <li>to web page: selection aid TIA Selection Tool</li> </ul>	https://support.industry.siemens.com/cs/ww/en/view/67384964		
<ul> <li>to website: Industrial communication</li> </ul>	http://www.siemens.com/ident/rfid		
<ul> <li>to website: Industry Mall</li> </ul>	https://mall.industry.siemens.com		
<ul> <li>to website: Information and Download Center</li> </ul>	http://www.siemens.com/industry/infocenter		
<ul> <li>to website: Image database</li> </ul>	http://automation.siemens.com/bilddb		
<ul> <li>to website: CAx-Download-Manager</li> </ul>	http://www.siemens.com/cax		
to website: Industry Online Support	https://support.industry.siemens.com		

last modified:

12/18/2020 🖸