



the sensor people





Figure can vary

Part no.: 50123558 CML720i-R20-1590.A/D3-M12 Light curtain receiver





Contents

- Technical data
- . Dimensioned drawings
- Electrical connection
- · Operation and display
- Suitable transmitters
- · Part number code
- Notes
- Accessories



Technical data

Pasis data			
Basic data Series	720		
Series Operating principle	720 Throughbeam principle		
Operating principle			
Device type	Receiver		
Contains	2x BT-NC sliding block		
Application	Object measurement		
Special design			
Special design	Crossed-beam scanning Diagonal-beam scanning Parallel-beam scanning		
Ontical data			
Optical data	Currenteed energting range		
Operating range	Guaranteed operating range 0.3 7 m		
Operating range Operating range limit			
	Typical operating range		
Operating range limit	0.2 9 m		
Measurement field length	1,590 mm		
Number of beams	80 Piece(s)		
Beam spacing	20 mm		
Measurement data			
Minimum object diameter	30 mm		
Electrical data			
Protective circuit	Polarity reversal protection Short circuit protected Transient protection		
Performance data			
Supply voltage U _B	18 30 V , DC		
Residual ripple	0 15 % , From U _B		
Open-circuit current	0 350 mA , The specified values refer to the entire package consisting of transmitter and receiver.		
Inputs/outputs selectable			
Output current, max.	100 mA		
Input resistance	6,000 Ω		
Number of inputs/outputs selectable	2 Piece(s)		
Туре	Inputs/outputs selectable		
Voltage type, outputs	DC		
Switching voltage, outputs	Typ. U _B / 0 V		
Switching voltage, inputs	high: ≥6V low: ≤4V		
Input/output 1			
Activation/disable delay	1 ms		
Timing			
Cycle time	2.8 ms		
	30 µs		



Interface				
Туре	RS 485			
RS 485				
Function	Process			
Service interface				
Type IO-Link				
IO-Link				
Function	Configuration via software Service			
Connection				
Number of connections	2 Piece(s)			
Plug outlet	Axial			
Connection 1	7.000.			
Function	Configuration interface			
Tunction	Connection to transmitter			
	Signal IN Signal OUT			
	Voltage supply			
Type of connection	Connector			
Thread size	M12			
Туре	Male			
Material	Metal			
No. of pins	8 -pin			
Encoding	A-coded			
Connection 2				
Function	BUS IN BUS OUT			
Type of connection	Connector			
Thread size	M12			
Туре	Female			
Material	Metal			
No. of pins	5 -pin			
Encoding	B-coded			
Mechanical data				
Design	Cubic			
Dimension (W x H x L)	29 mm x 35.4 mm x 1,675 mm			
Housing material	Metal , Aluminum			
Lens cover material	Plastic			
Net weight	1,750 g			
Housing color	Silver			
Type of fastening	Groove mounting Via optional mounting device			
Operation and display				
Type of display	LED OLED display			
Number of LEDs	2 Piece(s)			
Type of configuration	Software Teach-in			
Operational controls	Membrane keyboard			
	<u> </u>			




Environmental data			
Ambient temperature, operation	-30 60 °C		
Ambient temperature, storage	-40 70 °C	-40 70 °C	
Certifications			
Degree of protection	IP 65		
Protection class	III		
Certifications	c CSA US		
Standards applied	IEC 60947-5-2		
Classification			
Customs tariff number	90314990		
eCl@ss 8.0	27270910		
eCl@ss 9.0	27270910		
ETIM 5.0	EC002549		
ETIM 6.0	EC002549		

Dimensioned drawings


All dimensions in millimeters





- A Beam spacing 20 mm B Measurement field length 1590 mm
- F M6 thread
- G Fastening groove
- L Profile length 1608 mm
- T Transmitter
- R Receiver
- Y 5 mm






A PWR / SW IN/OUT B BUS IN / OUT

Electrical connection

Connection 1		
Function	Configuration interface Connection to transmitter Signal IN Signal OUT Voltage supply	
Type of connection	Connector	
Thread size	M12	
Туре	Male	
Material	Metal	
No. of pins	8 -pin	
Encoding	A-coded	


Pin	Pin assignment			
1	V+			
2	I/O 1			
3	GND			
4	IO-Link			
5	I/O 2			
6	RS 485 Tx+			
7	RS 485 Tx+			
8	FE/SHIELD			



Connection 2	
Function	BUS IN BUS OUT
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins	5 -pin
Encoding	B-coded



Pin	Pin assignment	
1	V+	
2	Tx-	
3	PB GND	
4	Tx+	
5	FE/SHIELD	



Operation and display

LEDs

LED	Display	Meaning
1	Green, continuous light	Operational readiness
	Green, flashing	Teach / error
		Measurement frequency display
2 Yellow, continuous light Light path free, with function		Light path free, with function reserve
	Yellow, flashing	No function reserve
	Off	Object detected

Suitable transmitters

Part no.	Designation	Article	Description
50119432	CML720i- T20-1590.A-M12	Light curtain transmitter	Operating range: 0.3 6 m Connection: Connector, M12, Axial, 5 -pin

Part number code

Part designation: CML7XXi-YZZ-AAAA.BCCCDDD-EEEFFF

CML	Operating principle: Measuring light curtain		
7XXi	Series: 720i: 720i series 730i: 730i series		
Y	Device type: T: transmitter R: receiver		
ZZ	Beam spacing: 05: 5 mm 10: 10 mm 20: 20 mm 40: 40 mm		
AAAA	Measurement field length [mm], dependent on beam spacing		
В	Equipment: A: connector outlet, axial R: rear connector outlet		



ccc	Interface: L: IO-Link /CN: CANopen /PB: PROFIBUS /PN: PROFINET /CV: Analog current and voltage output /D3: RS 485 Modbus		
DDD	Special equipment: -PS: Power Setting		
EEE	Electrical connection: M12: M12 connector		
FFF	-EX: Explosion protection:		

Note

A list with all available device types can be found on the Leuze electronic website at www.leuze.com.

Notes

Observe intended use!

- · This product is not a safety sensor and is not intended as personnel protection.
- The product may only be put into operation by competent persons.
- · Only use the product in accordance with its intended use.

For UL applications:

- For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).
- These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/CYJV7 or PVVA/PVVA7)

Accessories

Connection technology - Connection cables

Part no.	Designation	Article	Description
50132079	KD U-M12-5A- V1-050	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connection 2: Open end Shielded: No Cable length: 5,000 mm Sheathing material: PVC

Leuze electronic GmbH + Co. KG, In der Braike 1, 73277 Owen Phone: +49 7021 573-0, Fax: +49 7021 573-199



Connection technology - Y distribution cables

	Part no.	Designation	Article	Description
	50118183	K-Y1 M12A-5m- M12A-S-PUR	Interconnection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connection 2: Connector, M12, Axial, Male, A-coded, 5 -pin Connection 3: Connector, M12, Axial, Female, A-coded, 8 -pin Shielded: Yes Cable length fork 1: 5,000 mm Cable length fork 2: 150 mm Sheathing material: PUR
	50123265	K-YPB M12A-5m- M12A-S-PUR	Interconnection cable	Suitable for interface: PROFIBUS DP Connection 1: Connector, M12, Axial, Male, B-coded, 5 -pin Connection 2: Connector, M12, Axial, Female, B-coded, 5 -pin Connection 3: Connector, M12, Axial, Male, B-coded, 5 -pin Shielded: Yes Cable length fork 1: 5,000 mm Cable length fork 2: 250 mm Sheathing material: PUR

Mounting technology - Mounting brackets

Part no.	Designation	Article	Description
50142900	BT 700M.5-2SET	Mounting device set	Contains: 2x mounting brackets, 1 teach template, 4 M6 x 10 screws Design of mounting device: Bracket mounting Fastening, at system: Through-hole mounting, T slotted hole Mounting bracket, at device: Screw type, Sliding block Type of mounting device: Rigid Material: Steel

Mounting technology - Swivel mounts

	Part no.	Designation	Article	Description
EE.	429046	BT-2R1	set	Contains: 2x BT-R swivel mount, 1 cylinder for mounting on the light curtain Fastening, at system: Through-hole mounting Mounting bracket, at device: Clampable Type of mounting device: Turning, 360° Material: Metal, Plastic

Services

Part no.	Designation	Article	Description
S981001	CS10-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours. Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses. Restrictions: No mechanical (mounting) and electrical (wiring) work performed, no changes (attachments, wiring, programming) to third-party components in the nearby environment.
S981005	CS10-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses. Restrictions: Travel costs and accommodation expenses charged separately and according to expenditure.

Note

A list with all available accessories can be found on the Leuze electronic website in the Download tab of the article detailed page.