

START Panel UGR19 600x600


START Panel UGR19 600x600 3800Lm 830 LILO

0042186



Product features

- START Panel is a range of backlit LED panels used in recessed ceilings. Ideal for general indoor applications such as corridors, breakrooms, offices and meeting rooms. Luminaire dimensions are compatible with common ceiling installation, and the shallow design makes it easy to install in low ceilings. 3800Lm; 36W; 106Lm/W; Drive current: 750mA; Average lifespan: 100.000Hrs; 3000K; CRI 80; Glare control <19; IK03; IP40 (from the front); SDCM<3; Class II; Loop in loop out connector for quick installation.



PRODUCT OVERVIEW

Product name	START Panel UGR19 600x600 3800Lm 830 LILO
Technology	LED
Housing	Aluminium, Steel
Mount	Ceiling recessed mounting
General application	Education, Office
ETIM Class	EC002892
E-number FI	4278357
Warranty	5 years
Fixture luminous flux (lm)	3800
Luminaire efficacy (lm/W)	106
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	90
Glare control	< 19
Photobiological Risk Group	RG0
Total power consumption (W)	36
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
LED Flickering Rate	Ultra low (5% or less)
Housing colour	RAL 9003 - Signal white
IP rating	IP40/20
IK rating	IK03
Product EAN number	5410288421865

DATA TABLE

General data

Product name	START Panel UGR19 600x600 3800Lm 830 LILO
--------------	---

START Panel UGR19 600x600

START Panel UGR19 600x600 3800Lm 830 LILO

0042186

Technology	LED
Housing	Aluminium, Steel
Mount	Ceiling recessed mounting
General application	Education, Office
Operating temperature range (°C)	-10°C...+45°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4278357
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3800
Luminaire efficacy (lm/W)	106
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	90
Distribution type	Symmetric
Glare control	< 19
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	36
Mains voltage (V)	220-240V
Lamp power factor	0.9
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	15.0
Electrical protection	Class II
Control gear required	No
Control gear type	LED driver constant current
Transformer required	No
Dimmable	No
Dimming method	N/A
Drive current (mA)	750
Inrush Current (A)	13.2
Inrush Duration (µs)	240
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	D
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Ultra low (5% or less)
Max. Luminaires per 10A C Breaker	43
Max. Luminaires per 13A C Breaker	57
Max. Luminaires per 16A C Breaker	70
Max. Luminaires per 20A C Breaker	88
Max. Luminaires per 10A B Breaker	25
Max. Luminaires per 13A B Breaker	33
Max. Luminaires per 16A B Breaker	41

START Panel UGR19 600x600

START Panel UGR19 600x600 3800Lm 830 LILO
0042186

Max. Luminaires per 20A B Breaker	52
-----------------------------------	----

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	71000

Physical data

Housing colour	RAL 9003 - Signal white
IP rating	IP40/20
IK rating	IK03
Diffuser finish	Prismatic
Diffuser material	Other
Nominal Product Length (mm)	595
Nominal Product Width (mm)	595
Nominal Product Height (mm)	35
Weight (kg)	1.948



Packaging

Single packaging type	Carton
Product EAN number	5410288421865
Packaging single length / height (cm)	60.0
Packaging single width (cm)	3.8
Packaging single depth (cm)	64.5
DUN14 (outer)	15410288421862
Units per outer package	1
Packaging outer length / height (cm)	60.0
Packaging outer width (cm)	3.8
Packaging outer depth (cm)	64.5

Safety data

Optimal operating condition (°C)	-10-45
----------------------------------	--------

PHOTOMETRY



START Panel UGR19 600x600

START Panel UGR19 600x600 3800Lm 830 LILO

0042186

TECHNICAL DRAWINGS

