

## Knurling tool (series RD2 model 141)

for knurl pressing on lathes and turning machines



### Application:

For knurl forming for knurl profiles in accordance with DIN 82 RAA, RBL30°/45°, RBR30°/45°, RGE 30° and RGE 45° in the steel, stainless steel and non-ferrous metals material groups.

### Execution:

- Hardened steel tool holder, integrated tip height, cemented carbide runner pins

### Advantage:

- click-pin design for user-friendly handling (only with 20x20 and 25x20 shaft designs)
- modular design enables right-handed and left-handed knurl forming
- Inexpensive knurl production
- Flexible centring and adjustable clearance angle



<b>Art. no.</b>	<b>19005 025</b>
<b>Brand</b>	ZEUS
<b>Manufacturer Part Number</b>	31002705
<b>Suitable for knurling size</b>	20 x 8 x 6 mm
<b>Shank width</b>	25 mm
<b>Shaft height</b>	20 mm
<b>For min./max. workpiece diameter</b>	10-110 mm
<b>Gross Weight</b>	0.550 kg
<b>Product Group</b>	1FP