

Cemented carbide stone drill with straight shank

For use in stone, concrete and masonry

ORION[®]

Application:

For drilling and hammer drilling in masonry, granite, natural and artificial stone and sand-lime brick.



Execution:

- Soldered cemented carbide cutting insert with straight shank, two cutters

Advantage:

- Standard cemented carbide for a long service life
- Excellent price-performance ratio

Art. no.	11185 150
Brand	ORION
Manufacturer Part Number	11185150
Cutting material	Carbide
Number of cutting edges	2 PCS
Tool holding device	HA parallel shank
Cutting edge diameter	15 mm
Shank diameter	12.7 mm
Chip flute length	100 mm
Length	160 mm
DIN	8039
Gross Weight	0.015 kg
Product Group	1AT

EAN

4039247034123